

Data sheet

Micro Plate Heat Exchanger **For increased chiller profits**


C22L-E Evaporator

40%

charge compared with a traditional BPHE. The ideal solution to meet the world's climate and energy spirations.



C22L-E Evaporator Micro Plate Heat Exchanger



Introduction

The C22L-E is an evaporator optimised for R407C for use in high-efficiency chillers with capacities of 3-20 kW. The heat exchanger features innovative Micro Plate technology that improves heat transfer and reduces the amount of material used.

To meet demands for higher seasonal efficiency, the C22L-E is designed to work efficiently and increase comfort in modern buildings without increasing the carbon footprint. Helping chillers perform more efficiently, it reduces both energy costs and environmental impact. The low hold-up volume reduces the system refrigerant charge and offers valuable savings.

Key features

- Minimal hold-up volume: Less refrigerant charge.
- Reduced pressure drop: For more efficient chillers.
- Smaller footprint: Enabling more compact chillers.
- Reduced CO₂ footprint: Environmentally friendly with high heat transfer and minimal refrigerant charge.

Technical data

n = number of plates

Min. working temperature: -196°C

Max. working temperature: 200°C

Max. working pressure: 45 bar

Hold-up volume: Q1-Q2/ Q3-Q4 (l): $0.021 \times n/2$ / $0.021 \times (n-2)/2$

Weight (kg): $0.77 + 0.045 \times n$

Max. no. of plates: 60

Standard materials

Cover plates: AISI 304

Connections: AISI 304

Plates: AISI 316

Brazing filler: Pure copper

Other material combinations are available on request. Please contact your Danfoss sales representative for more information.

Standard connections

Standard connections as per below are optimised for this product as condenser in chiller system. For other connections, please contact your Danfoss representative.

Q3 (Refrigerant outlet): soldering 1/4" or 3/8"

Q4 (Refrigerant inlet): soldering 1/2" or 5/8"

Q1-Q2 (Water side): External threaded G 3/4"



Third part approvals

Europe: Pressure Equipment Directive (PED). America: Underwriters Laboratory Inc (UL). The third party approvals stated are standard for all our products. For details of other existing approvals or to discuss how we can meet your local needs, please contact your Danfoss representative.

Accessories – stud bolts

Stud bolts on front and/or back cover plates for mounting support are available upon request. Contact your Danfoss sales representative for further information.

Accessibility

We will help you set up a logistics solution that will meet your needs.

Corresponding evaporators

A corresponding Micro Plate heat exchanger for evaporator duties (C22L-C) is also available.

Danfoss can accept no responsibility for possible errors in catalogues, brochures and other printed material. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alterations can be made without consequential changes being necessary in specifications already agreed. All trademarks in this material are property of the respective companies. Danfoss and the Danfoss Logotype are trademarks of Danfoss A/S. All rights reserved.