


IS04401 Size 05: ANSI/B93.7M-D05

Solenoid operated directional valve

DG4V-5-20/22 Design



Solenoid operated directional valve


DG4V-5-20/22 Design

General description

A range of four-port solenoid operated directional control valves with four-land spool design to facilitate provision of smooth, variable valve response speeds.

The range includes:

- AC and DC wet-armature solenoid options with ISO 4400 (DIN 43650) electrical connections and manual overrides.
- Variable speed changeover potential in all DC models; see "Response Times" section.
- Many spool types; in spring-offset, spring centered and detented arrangements.
- Compact, cost effective system design when used with Danfoss® SystemStak™ valves and subplates.



(F13-)	DG4V-5	***	*(L)	(J)	**	- (V) M	S*	- *	**	*	- 2*	- J**
1	2	3	4	5	6	7	8	9	10	11	12	13

1	Prefix, fluid compatibility Blank AC or DC-voltage models for petroleum oils, water-in-oil (invert) emulsions or phosphate esters. F13 AC - voltage models for water glycols. DC-voltage models for water glycols.	8	Spool position indicator switch Blank No spool position monitoring switch. S7 Spool position monitoring switch . Single solenoid valves only S9 Spool position monitoring function Refer to catalogue AF458770480968en-000101 for technical data
2	Model series D Directional G Gasket mounted 4 Solenoid operated V Pressure rating 315 bar (4568 psi) on P, A & B parts 5 ISO4401 Size 05	9	Coil type U ISO 4400 (DIN 43650) mounting(s) without plug(s) U1 ISO 4400 with fitted DIN plug U6 ISO 4400 with fitted DIN plug with lights KU Flying leads from top of the solenoid KUP4 Junior timer (AMP) connector KUP5D2 Moulded Deutsch connector with diode KUP6D2 Flying lead with Deutsch connector with diode
3	Spool type See "Functional Symbols" section on page 4	10	Coil rating A 110V AC 50 C 220V AC 50 ED 240V AC 50 EK 115V AC 60 EH 230V AC 60 G 12V DC H 24V DC HL 24V DC (32W) OJ 48V DC P 110V DC NN 24V AC 50HZ Others on request
4	Spool spring arrangement A Spring offset to A. Single end. AL As 'A', but left hand build B Spring centered. Single end. BL As 'B', but left hand build C Spring centered. Double End. N No spring detented. Double end.	11	Tank pressure rating 6 160 Bar Tank Pressure Rating - AC only 7 210 Bar Tank Pressure Rating - DC only
5	Spool design Blank- "0A" DC-valves and all AC valves except "8B(L)" and "8C"spool/ spring arrangements . J All DC valves except "0A"spool/ spring arrangements . AC valves with "8B(L)" and "8C" spool/spring arrangements .	12	Design number Subject to change . Installation dimensions unaltered for design numbers 20 to 29 inclusive.
6	Manual override option Blank- Standard plain override(s) in solenoid end(s) only ▼ H Water-resistant override(s) in solenoid end(s) ▼ W Twist and lock override in solenoid end only Z No overrides at either end Omit for standard plain override(s) in solenoid end(s) only ▼ ▼ No override in non-solenoid end of singlesolenoid valves.	13	Coil rating Speed Control Ori ce J06 0,6 mm orifice J08 0,8 mm orifice J10 1,0 mm orifice J12 1,2 mm orifice J99 No orifice . Must be specified Where future fitting of orifice is required, see page 5 , "Spool Speed Control Orifice
7	Solenoid energization identity V Solenoid "A" is at port A end and/ or solenoid "B" is at port B end, independent of spool type Note: Used to select the identification of the solenoid . Refer to page 4		

Functional symbols

Spool Options 4 & 5

5 Spool & Spring Arrangements

NOTE: Bolded spool numbers have standard lead time

	C Spring Centered Double Solenoid	A-Spring Offset N-Detent (a only) End to End → Right Hand Build	AL Spring Offset End to End → Left Hand Build	B Spring Offset Center to End → Right Hand Build	BL Spring Offset Center to End → Left Hand Build
0					
1					
2					
3					
6					
7					
8					
11					
31					
33					
13					
22					
52					
521					
56					

Standard lead time


Spool Transition/Crossover Function

* Spool 8 only offered in VM style nomenclature

* For more spool types see appendix

Electrical Nomenclature

Electrical Options 7 & 8



Feature	DG4V-5		
Pressure Limits			
P, A and B ports	315 bar (4500 psi)		
T port: TA	120 bar (1750 psi) for AC Sol.		
TB	210 bar (3000psi) for DC Sol.		
Flow rating	See performance data		
Relative duty factor	Continuous; ED = 100%		
Type of protection:			
ISO 4400 coils with plug fitted correctly	IEC 144 class IP65		
Coil winding	Class H		
Lead wires (coils type F***)	Class H		
Coil encapsulation	Class F		
Permissible voltage fluctuation:			
Maximum	Refer to temperature limits.		
Minimum	90% rated		
Typical response times at 100% rated volts measured from application/removal of voltage to full spool displacement of "2C" spool at:			
Flow rate P-A, B-T	120 l/min (32 USgpm)		
Pressure	175 bar (25 37 psi)		
AC (~) energizing	30 ms		
AC (~) de-energizing	40 ms		
DC (=) energizing	120 ms■		
DC (=) de-energizing	45 ms■*		
Power consumption, AC solenoids (for coils listed in model code).	Initial VA (RMS)	▲	Holding VA (RMS)
Full power coils:			
Dual frequency coils at 50 Hz	700		105
Dual frequency coils at 60 HZ	105		130
Power consumption, DC solenoids at rated voltage and 20 C (68 F).			
Full power coils:			
Others	38W		
Model type "HL"	32W		
Mass, Approx. kg (lb)			
Single solenoid models, AC coils	4,0 (8.8)		
Single solenoid models, DC coils	4,8 (10.6)		
Double solenoid models, AC coils	4,5 (9.9)		
Double solenoid models, DC coils	6,3 (13.9)		
Temperature Limits			
Minimum ambient	-20 °C (-4 °F)		
Maximum ambient:			
AC 50 Hz valves	50 °C (122 °F)		
AC 60 Hz valves	40 °C (104 °F)		
DC valves	70 °C (158 °F)		

MTTF'd information according to ISO 13849 - 150 years

Spool speed control orifice

For fine tuning of valve spool speed. Only applicable to valves already fitted with an orifice or blank plug, see model code, page 3.

Orifice kits

Orifice kits must be ordered separately, part number 02-350116. Kit comprises 1 off each as per code 13 on page 3:

* In pure switched conditions, devoid of the effects of any suppression diodes and full-wave rectifiers.

■ DG4V-5-2CJ valves. Longer response times can be obtained by fitting an orifice plug in a special pilot port, standard in all bodies. An orifice kit 459065, containing a selection of plugs of differing orifice size, can be ordered separately. Ask your Danfoss representative for details.

▲ 1st half cycle; armature fully retracted.

Seal kits:

DG4V-5-20 AC.....459057

DG4V-5-22 DC.....459058

Operating Data

Spool Position Indicator Models

Spool/spring arrangement types QA, 2A, 2AJ, 22A, 22AJ, 35A, 35AJ, OBJ, 2BJ, 6BJ

DC model type "57"

CE

This product has been designed and tested to meet specific standards outlined in the European Electromagnetic Compatibility Directive (EMC) 2004/108/EC. For instructions on installation requirements to achieve effective protection levels see this leaflet and the Installation Wiring Practices for Vickers Electronic Products leaflet 2468. Wiring practices relevant to this Directive are indicated by



⚡ Electromagnetic Compatibility (EMC).

Input:	
Supply voltage	20-32 VDC
Reverse Pol. Protection	Yes
outputs with alternating function - PNP	
Output:	
Max output load	<=400mA ; Duty Ratio 100%
Short Circuit Protection	Yes
Hysteresis	<=0.03mm
Electrical connector	M12x1 4-Pole
Thermal shift	<=10.1mm
Pin Connections:	
Pin 1	+ Supply
Pin 2	Normal Closed
Pin 3	ov
Pin 4	Normal Open
EMC Protection	
Humidity	DIN EN 61000-6-1/2/3/4, Aug 2002
Protection Class	0-95% rel. (nach DIN 40040)
Vibration 0-500Hz	IP65 DIN 40050
Shock	Max. 20g
	Max. 50g

Wiring Connections

Warning

All power must be switched off before connecting or disconnecting any plugs.



Customer protective ground connection



WARNING: Electromagnetic Compatibility (EMC)

It is necessary to ensure that the unit is wired up in accordance with the connection arrangements shown above. For effective protection of the user's electrical cabinet, the valve subplate manifold and the cable screens should be connected to efficient ground points. In all cases both valve and cable should be kept as far away as possible from any sources of electromagnetic radiation such as cables carrying heavy current, relays and certain kinds of portable radio transmitters, etc. Difficult environments could mean that extra screening may be necessary to avoid the interference.

Typical with mineral oil at 36 cSt (168 .6 SUS) and a specific gravity of 0 .87.

Max. Flow rates


Based on warm solenoid(s) operating at 10% below rated voltage. Flow limits applicable to following usages:

- All valves except those with types 22, 52, 56, 521 and 561 spools having simultaneous equal flow rates from P to A or B and from B or A to T.
- Valves with type 22 spools having flow from P to A or B, the other being blocked. T is drained at all times.
- Valves with types 52, 56, 521 and 561 spools having one service port connected to the full bore end of a 2:1 area ratio double-acting cylinder and the other service port to the annulus end .
- Valves with type 23 spools having single flow from A or B to T, P and the other service port being blocked.


Consult Danfoss with application details if any of the following are required:

- Single flow path, i.e. P to A, P to B, A to T or B to T.
- Substantially different simultaneous flow rates between P to A or B and B or A to T.
- Spools as in 3 above are to be used with cylinder ratios greater than about 3:1 at low flow rates or 2:1 at high flow rates .

AC Solenoid Valves





DC Solenoid Valves



Spool/spring code	AC valve graph curve	DC valve graph curve
0A(L)	3	2
0B(L) & 0C	2	4
1B(L) & 1C	6	7
2A(L)	3	2
2B(L), 2C & 2N	1	1
3B(L), 3C, 6B(L) & 6C	4	6
6N	3	3
7B(L) & 7C	1	1
8B(L) & 8C	7	5
11B(L), 11C & 22A(L)	6	7
23A(L)	5	6
31B(L) & 31C	4	6
33B(L), 33C	3	6
52B(L), 52C, 56BL, 56C, 521B, 521C, 561B & 561C	4	6


Performance data

Pressure Drops Typical with petroleum oil at 36 cSt (170 SUS) and a specific gravity of 0,87



Spool/spring code	Spool positions covered	P to A	P to B	A to	B to T	-	
0A(L)	Both	2	2	4	5	3t	-
0B(L) & 0C	De-energized	-	-	-	-	-	-
	Energized	1	1	6	7	6u	-
1B(L) & 1C	De-energized	-	-	-	-	-	-
	Energized	1	2	6	4	-	-
2A(L)	Both	3	3	5	6	-	-
2B(L) & 2C	All	2	2	4	5	-	-
2N	Both	3	3	5	6	-	-
3B(L) & 3C	De-energized	-	-	5	-	-	-
	Energized	2	3	6	5	-	-
6B(L) & 6C	De-energized	-	-	5m	6u	-	-
	Energized	3	3	6	7	-	-
6N	Both	4	4	4	5	-	-
7B(L) & 7C	De-energized	3m	3u	-	-	-	5
	Energized	2	2	5	6	-	-
8B(L) & 8C	All	2	2	7	8	8	-
11B(L) & 11C	De-energized	-	-	-	-	6m	-
	Energized	2	1	4	7	-	-
22A(L)	Both	3	3	-	-	-	-
23A(L)	Both	3	3	5	6	-	-
31B(L) & 31C	De-energized	-	-	-	6	-	-
	Energized	3	2	4	7	-	-
33B(L) & 33C	De-energized	-	-	12m	12u	-	-
	Energized	2	2	5	6	-	9
52BL & 52C	All	7m	8	4	-	-	-
56BL & 56C	De-energized	-	-	8m	10u	-	9
	Energized	7m	8	6	-	-	9
521B & 521C	All	8	7u	-	5	-	-
561B & 561C	De-energized	-	-	10m	8u	-	9
	Energized	8	7u	-	7	-	-

AC Solenoid models




- ▲ May vary according to plug source.
- ◆ The cable entry can be repositioned at 90° intervals from the position shown. This is done by reassembling the contact holder into the appropriate position inside the plug housing.

Model	Solenoid at:	C	D	E	F	G
DG4V-5-*A(L)/B(L)(-Z)-(V)M	Port A end	123 (4.84)	–	–	182 (7.17)	–
	Port B end	–	123 (4.84)	182 (7.17)	–	–
DG4V-5-*C/N(-Z)-(V)M	Both ends	123 (4.84)	123 (4.84)	–	–	246 (9.68)
DG4V-5-*C/N-H-(V)M	Both ends	138 (5.43)	138 (5.43)	–	–	276 (0.87)

Installation dimensions

DC Solenoid models




▲ May vary according to plug source.

◆ The cable entry can be repositioned at 90° intervals from the position shown. This is done by reassembling the contact holder into the appropriate position inside the plug housing.

Model	Solenoid at:	C	D	E	F	G
DG4V-5-*A(L)/B(L)(-Z)-(V)M	Port A end	156 (6.14)	–	–	215 (8.46)	–
	Port B end	–	156 (6.14)	215 (8.46)	–	–
DG4V-5-*C/N(-Z)-(V)M	Both ends	156 (6.14)	156 (6.14)	–	–	312 (12.28)
DG4V-5-*C/N-H-(V)M	Both ends	185 (7.28)	185 (7.28)	–	–	370 (14.57)

Installation dimensions in mm (inches)

Spool position indicator switch models



▲ For LH models ("L" in model code location) 4 solenoid and switch locations are reversed

⚠ Wiring: See warning note on page 5

Installation dimensions in mm (inches)

Electrical plugs and connectors

DIN 43650 Connector

Cable diameter range:

Wire section range:

Terminals:

Type of protection:

Connector can be positioned at 90° intervals on valve by re-assembling contact holder into appropriate position inside connector housing.

Connectors with and without indicator lights are available (order separately):

Ø6–10 mm (0.24–0.40)


Ø,5–1,5 mm²

(0.0008–0.0023 in²)

Screw type

IEC144 class IP65, when plugs are fitted correctly to the valves with interface seals (supplied with plugs) in place.

Recptacle	Voltage (AC or DC)	Part numbers Gray – "A" sol.	Black – "B" sol.
U1 Coils without lights		710776	710775
U6 Coils with lights	12-24	977467	977466
	100-125	977469	977468
	200-240	977471	977470



Connectors

U/U1/U6

KUP5/KUPSD2

KUP6

KUP4

KU

