

Remote Control

T70 1 ATEX Transmitter

The T70 1 ATEX is highly customizable with many features and accessories. From removable EEPROM SIM module to tandem system solutions, the T70 1 ATEX brings quality and reliability to lifting applications.

Features

- High-sensitivity two-step push button
- Multi-band Radio with Full-Duplex communication
- External removable EEPROM SIM module
- Frequency management against interferences

Benefits

- Highly customizable
- Easy and fast maintenance
- High resistance to impacts
- Improved ergonomics
- Intrinsically safe

Applications

- ATEX certified for hazardous applications
- Used in crane applications

Comprehensive technical literature is online at powersource.danfoss.com.





Technical data

Specification	Value
Stop function (400-900MHz)	Cat. 3-PLd
Ingress Protection	IP65/NEMA4
Anti-condensation system	N/A
Frequency band	433.050 to 434.040 MHz; ERP<1 mW
	434.040 to 434.790 MHz; ERP<10mW
	869.700 to 870.000 MHz; ERP<5 mW
	902.000 to 928.000 MHz; ERP<1mW
Range Line of Sight (guaranteed)	100m
Main mechanisms	2 Step Push button (6 total) + START + STOP + Key
Auxiliary mechanisms	Toggle and rotary switches
Removable EEPROM	External
Battery model	BT06K ATEX
Battery life	8h
Response Time	100ms
Operating temperature Range	-20° to 70° C (-4° to 158° F)
Storage Temperature Range (24h)	-25°C to 75°C (-13°F to 167°F)
Storage Temperature Range (long periods)	-25°C to 55°C (-13°F to 131°F)
Relative Humidity	max. 95% without condensation
Weight (with battery)	500 g
Dimensions LxWxH mm	270x71x64
Harness	Hand/shoulder strap
Available Options	
Display	N/A
Cable connection	N/A
Range limiter	N/A
Associated receivers	R13, R70, MPCAN, R70 ATEX Z1, R13 ATEX Z2

ATEX / IECEx

 II 2 GD
Ex ia IIC T4 Gb
Ex ia IIIC T135°C Db
CE0080
INERIS 08ATEX0006
IECEx INE 09.0014
CML 21UKEX21119