




NOTES:

1. The diameters of the lines and the bending radius are for all the tandems.
2. Bending of all pipes 1.5 x D.
3. Compressors equipped with non-return valve.
4. Restrictor mount according to drawing 8555010.
5. If the compressor is not DSH381-3, X=527.
If the compressor is DSH381-3, X=576.

AA
DSH MANIFOLDING MOUNTING
KIT 120Z0796
120Z0791

SCALE 1/1

OR

DSH MANIFOLDING MOUNTING
KIT 7777037
7777048

SCALE 1/1

SN	PART NUMBER	DESIGNATION	QUANTITY	SCREWING TORQUES Nm
1	5216779P01	OIL EQUALIZATION LINE (1"3/8)	1	144±15
2	5216804P01	DISCHARGE LINE ASSY	1	
3	5216784P01	SUCTION LINE ASSY	1	
4	5312660P01	TANDEM DSH RAILS	2	
5		SCREW HM10x100 CLASS 10.9	6	50±5
6	5311860P01	WASHER FOR TANDEM	6	
7	5603009P02	GROMMET ISOLATION	6	
8	X05090234P01	SLEEVE MOUNTING	6	
9	5603010P01	GROMMET WASHER ISOLATION	6	
10	6301011P01	WASHER FLAT LL10 ZN8	6	
11		SCREW HM10x30 CLASS 10.9	8	50±5
12	6302002P01	WASHER W10	8	
13	5603016P01	GROMMET MANIFOLD	6	
14	5321235P01	SLEEVE MOUNTING TANDEM	6	

MODEL	CP2/CP1	SUCTION RESTRICTOR ON CP1	
DSH620	DSH381+DSH240	5311579P05	Ø 29
DSH675	DSH381+DSH295	5311579P01	Ø 31

Part number
8556222P01AA

Drawing Status : Production print

Surface Area (m2)

Estimated Mass (kg)

Projection : 3/10

Size A0

Material : See Notes

Designation

TANDEM DSH620/675

Sheet 11 of 11

8556222

AA