

Data Sheet

Radiator Valves Type RA-N with Integrated Pre-setting

Application



Straight valve pattern



Angle valve pattern


RA-N valves are used for two-pipe heating systems together with liquid filled RTW sensors or gas filled sensors in the RA 2000 range.

RA-N valves are fitted with a k_v limiting device for pre-setting of max. water flow. Each valve body is supplied with a red protective cap, which can be used for manual regulation during the construction phase.

The protective cap must not be used as a manual shut off device. A special manual shut off device is available as an accessory.

RA-N valve bodies are manufactured from brass with nickel plating. The pressure pin of the gland seal is of chromium steel and works in a lifetime lubricated O-ring. The complete gland seal assembly can be replaced without draining down the system. In order to avoid deposition and corrosion the composition of the hot water must be in accordance with the VDI 2035 guideline (Verein Deutscher Ingenieure). It is recommended that formulations containing mineral oil are avoided.


System




Presetting

The presetting values of RA-N valves can be adjusted easily and accurately without the use of tools (factory setting = N):

- Remove protective cap / thermostatic sensor
- Find reference mark
- Lift and turn setting ring until the required pre-setting aligns with the reference mark.



Presetting can be selected in steps from 1 to 7. At setting N the valve is fully open. This setting can be used as a flushing position, if the system has to be flushed because of dirt problems. Settings outside 1 to 7 and N should be avoided.



When the thermostatic sensor has been installed, the presetting is protected against unintended regulation.

1. Factory setting
2. Presetting range
3. Reference mark

Ordering and Specifications

Type	Design	Connections		Max. work. press.	Max. diff. ¹⁾ press.	Test	Max. work. temp.	Code no.
		Inlet	Outlet					
		R _p	R	bar	bar	bar	°C	
RA-N 15	Angle	1/2	1/2	10	0.6	16	120	013G3963
	Straight	1/2	1/2	10	0.6	16	120	013G3964
RA-N 20	Angle	3/4	3/4	10	0.6	16	120	013G0015
	Straight	3/4	3/4	10	0.6	16	120	013G3966
RA-N 25	Angle	1	1	10	0.6	16	120	013G0037
	Straight	1	1	10	0.6	16	120	013G0038

Data and k_v-values in combination with RTW sensors

Type	Design	Pre-setting								
		kv _{max.} ²⁾ (m ³ /h at Δp = 1 bar)								k _{vs}
		1	2	3	4	5	6	7	N	
RA-N 15	Angle	0.04	0.08	0.14	0.21	0.31	0.37	0.47	0.53	1.00
	Straight	0.04	0.08	0.14	0.21	0.31	0.37	0.47	0.53	1.00
RA-N 20	Angle	0.09	0.14	0.17	0.25	0.31	0.40	0.51	0.71	1.40
	Straight	0.09	0.14	0.21	0.32	0.43	0.52	0.61	0.73	1.42
RA-N 25	Angle	0.09	0.14	0.17	0.25	0.31	0.40	0.51	0.71	1.40
	Straight	0.09	0.14	0.17	0.25	0.31	0.40	0.51	0.71	1.40

Data and k_v-values in combination with RA 2000 sensors

Type	Design	Pre-setting								
		$k_{v-max.}^{2)} \text{ (m}^3/\text{h at } \Delta p = 1 \text{ bar)}$								k_{vs}
		1	2	3	4	5	6	7	N	
RA-N 15	Angle	0.04	0.09	0.16	0.24	0.36	0.43	0.62	0.75	1.00
	Straight	0.04	0.09	0.16	0.24	0.36	0.43	0.62	0.75	1.00
RA-N 20	Angle	0.10	0.15	0.18	0.26	0.35	0.46	0.73	1.04	1.40
	Straight	0.10	0.15	0.22	0.37	0.52	0.68	0.83	1.14	1.42
RA-N 25	Angle	0.10	0.15	0.18	0.26	0.35	0.46	0.73	1.04	1.40
	Straight	0.10	0.15	0.18	0.26	0.35	0.46	0.73	1.04	1.40

¹⁾ Working pressure = static + differential pressure. The maximum differential pressure specified is the maximum pressure at which the valves give satisfactory regulation. As with any device which imposes a pressure drop in the system, noise may occur under certain flow/pressure conditions. To ensure quiet operation, maximum pressure drop should not exceed 30 to 35 kPa. The differential pressure can be reduced by the use of the Danfoss differential pressure regulators types AVD, AVDL, AVDS, IVD or ASV-P.

²⁾ The k_v-value indicates the water flow (Q) in m³/h at a pressure drop (Δp) across the valve of 1 bar;

$k_v = \frac{Q}{\sqrt{\Delta p}}$. At setting N the k_v-value is stated according to EN 215, at X_p = 2K i.e. the valve is closed at 2°C higher room temperature. At lower settings the X_p-value is reduced to 0.5K of the setting value. The k_{vs}-value states the flow Q at a maximum lift, i.e. at fully open valve at setting N.

Data Sheet

Radiator Valves Type RA-N with Integrated Presetting

Accessories

Product	Code no.
Gland seal, 10 pcs.	013G0290
Brass setting knob for manual adjustment of the valve (only for temporarily replacement of a thermostatic sensor)	013G3300
Demounting tool for changing valve inserts with system in operation	013G3085

Valve Sizing

Sizing example


Required heat:	0.7 kW
Cooling across radiator:	20°C
Flow through radiator:	$Q = \frac{0.7}{20 \times 1.16} = 0.03 \text{ m}^3/\text{h} = 30 \text{ l/h}$
Pressure drop across valve:	$\Delta p = 1 \text{ mwg}$
Valve setting:	RA-N 15 2
	RA-N 20 / 25 1

Alternatively the setting can be read in the table "Ordering and Specifications":


$$k_v = \frac{Q(\text{m}^3/\text{h})}{\sqrt{\Delta p (\text{bar})}}$$

Capacities


Valve capacities, RA-N 15 with RA 2000 thermostatic sensor




Valve capacities, RA-N 15 with RTW thermostatic sensor




Valve capacities, RA-N 20 angle / RA-N 25 with RA 2000 thermostatic sensor




Valve capacities, RA-N 20 angle / RA-N 25 with RTW thermostatic sensor




Valve capacities, RA-N 20 straight with RA 2000 thermostatic sensor



Valve capacities, RA-N 20 straight with RTW thermostatic sensor



Design




1. Gland seal (can be changed during operation, i.e. with water and pressure on the system)
2. O-Ring
3. Pressure pin
4. Seal
5. Regulation spring
6. Throttle bush
7. Valve body
8. k_v -nozzle

RA-N valve bodies are nickel-plated on the outside.


Valve body and other metal parts	Ms 58, brass
Throttle bush	PPS
O-ring	EPDM
Valve cone	NBR
Pressure pin and valve spring	Chrome steel
k_v -Nozzle* (only 013G0015, 013G0037 and 013G0038)	PP

Dimensions



Dimensions are for RA-N valves in combination with RTW thermostatic sensor.

Type	ISO 7-1		L ₁	L ₂	L ₃	L ₄	L ₅	L ₆	L ₇	Arc. flats	
	D	d ₂								S ₁	S ₂
RA-N 15	R _p 1/2	R 1/2	55	82	26	53	23	47	104	27	30
RA-N 20	R _p 3/4	R 3/4	65	98	30	63	26	52	109	32	37
RA-N 25	R _p 1	R 1	90	125	40	75	34	52	109	41	46



Dimensions are for RA-N valves in combination with RA2000 thermostatic sensor

Type	ISO 7-1			L ₁	L ₂	L ₃	L ₄	L ₅	L ₆	L ₇	Arc. flats	
	DN	D	d ₂								S ₁	S ₂
RA-N 15	15	R _p 1/2	R 1/2	55	82	26	53	23	47	96	27	30
RA-N 20	20	R _p 3/4	R 3/4	65	98	30	63	26	52	101	32	37
RA-N 25	20	R _p 1	R 1	90	125	40	75	34	52	101	41	46

Danfoss A/S
Heating Solutions
Haarupvaenget 11
8600 Silkeborg
Denmark
Phone: +45 7488 8000
Fax: +45 7488 8100
Email: heating.solutions@danfoss.com
www.heating.danfoss.com

Danfoss can accept no responsibility for possible errors in catalogues, brochures and other printed material. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alterations can be made without subsequential changes being necessary in specifications already agreed. All trademarks in this material are property of the respective companies. Danfoss Heating Solutions and the Danfoss Heating Solutions logotype are trademarks of Danfoss A/S. All rights reserved.
