



Data Sheet

Communication Software WebGPI™



Mobile Machine Management

Danfoss PC based WebGPI™ interface software provides serial communication to Danfoss microcontrollers containing supporting application software.

WebGPI™ utilizes Microsoft® Internet Explorer® operating environment to provide runtime controller operating data, access to application setup and tuning parameters.

When used in conjunction with a CAN based interface, support is provided for Danfoss PVED-CC actuators.

Product Highlights

Danfoss microcontrollers supported by WebGPI™ include: SX, MC200, MC210, MC300 and MC400.


Danfoss software application support includes: Dual Path, Automotive Control, Anti-Spin, Anti-Stall, Load Control, Rear Steer, Fan Drive, Joystick Shaping, and many Leader Follower and Positioning applications.

Features

WebGPI™ Standard Features


- Graphic software representation
- Control parameter access
- Runtime operation data
- Controller hardware information
- Data logging
- Controller error information
- Offline application interface
- Controller application file handling

Purchase and activate WebGPI™
Communication Software at:
www.danfoss.com

Main View


The ability to monitor and tune the operation of devices is provided by the Service Tool.

F101904

Data Logging View


Standard features include:

- Oscilloscope display for trending and tuning
- Data record
- Export feature

F101905

Specifications

System Requirements
Microsoft® Internet Explorer® version 6.0 or later
Microsoft® Windows Vista® 32 bit variants and Windows XP® Home and Professional
60 MB hard drive (including Internet Explorer® and Adobe® Acrobat® installations)

WebGPI™ is offered with a single user, pc locked license that is automatically activated upon purchase, download and installation. More details and the WebGPI™ Users Manual, **K28061** are on line at: www.Danfoss.com

Danfoss Power Solutions US Company
2800 East 13th Street
Ames, IA 50010, USA
Phone: +1 515 239 6000

Danfoss Power Solutions GmbH & Co. OHG
Krokamp 35
D-24539 Neumünster, Germany
Phone: +49 4321 871 0

Danfoss Power Solutions ApS
Nordborgvej 81
DK-6430 Nordborg, Denmark
Phone: +45 7488 2222

Danfoss Power Solutions (Shanghai) Co. Ltd.
Building #22, No. 1000 Jin Hai Rd
Jin Qiao, Pudong New District
Shanghai, China 201206
Phone: +86 21 3418 5200

Danfoss can accept no responsibility for possible errors in catalogues, brochures and other printed material. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alterations can be made without consequential changes being necessary in specifications already agreed. All trademarks in this material are property of the respective companies. Danfoss and the Danfoss logotype are trademarks of Danfoss A/S. All rights reserved.