



| NOZZLE DATA | SIZE |
|---|------|
| A1 FROM DRIVE | DN50 |
| A2 TO DRIVE | DN50 |
| B1 INLET CUSTOMER | DN50 |
| B2 OUTLET CUSTOMER | DN50 |
| E1 ELECTRICAL CONNECTION, Alternative 1 | MC25 |
| E2 ELECTRICAL CONNECTION, Alternative 2 | MC25 |

Delivery includes flange connections to primary (2 pcs) and secondary (2 pcs) circuits. The directions of connections can be chosen according the installation.

| REVISION HISTORY | | | | |
|------------------|-------------|------------|-----------|--------------|
| REV | DESCRIPTION | DATE | BY | APPROVED |
| a | Misc. | 31.08.2007 | A-M. Haka | J-P. Sampola |

*) NOTE:
See Retrofit assembly and dimensional drawing VL39-5003-07.
See Veda openings drawing VL39-5003-05.

| Part no. | Qty. | Part name, type and/or measures | Standard/Draw. no. | Material | Weight/pc |
|----------|------|--|--------------------|------------|-----------|
| 9 | 4 | Washer A8,4 | DIN 125 | Zn | - |
| 8 | 4 | Hex nut M8 | DIN 934 | 8 Zn | - |
| 7 | 4 | Hex-Head Bolt M8 x 18 | DIN 933 | 8.8 Zn | - |
| 6 | 4 | Fastener | - | - | - |
| 5 | 1 | Multigate MC25 | Mar-Con | - | - |
| 4 *) | - | Retrofit Master Flash#1, 1/2"-4", Aztec Nordic | RF101B | Black EPDM | - |
| 3 | 1 | System window 500x470x33, Rittal | FT 2735.520 | - | - |
| 2 | 1 | VEDA HXL Cubicle | VEDA | - | - |
| 1 | 1 | HXL120 | VL39-5023-05 | - | - |

| | | |
|--|--|--|
| | DRAWING NAME HXL 120 VEDA DRAWING TYPE Assembly drawing PROJECT NUMBER HXL-V-120-N-S | CUSTOMER VACON OYJ PROJECT NAME STD HX-unit CUSTOMER PROJECT NUMBER - |
| Runonide 7 FIN-40500 VAAJA, FINLAND Phone +358 (0)201 2121 | DRAWN A-M. Haka CHECKED U. Kähtävä APPR. J-P. Sampola | DATE 20.10.2006 SCALE 1:10 SIZE A1 |
| ISO 2768-c | | RIGID NO. VL39-5023-10a VL39-5023-10 REV. a |