




Legend

- 1 Compressor
- 2 Electric Expansion Valve
- 3 Micro Channel Heat Exchanger with axial fan
- 4 Refrigerant receiver with rotalock valve
- 5 Filter Drier
- 6 Sight Glass
- 7 Liquid Ball Valve
- 8 Suction Ball Valve
- B1 Condensing Pressure Transducer (P1)
- B2 Suction Pressure Transducer (P2)
- B3 High Pressure cartridge Switch (auto-reset)(PSH)
- B4 Low Pressure cartridge Switch (auto-reset) (PSL)
- R1 Ambient Temperature sensor (T4)
- R2 Discharge Temperature Sensor (T2)
- R3 Suction Temperature Sensor (T3)
- R8 Discharge Temperature Sensor (T1)
- /// Insulation

General Tolerances Table	Drawing Status :					
				Surface Area (m2)		
				Estimated Mass (Kg)		
				Projection	Scale	Size
						A3
Roughness (µm)			06-OCT-19			Material :
Revision	ECR Number	Date				Designation
Designer	KAMLESH					PID OPTYMA PLUS
Approval	RAJAN GORE			Confidential: Property of Danfoss Commercial Compressors. Not to be handed over to copied or used by third party. Two or three dimensional reproduction of contents to be authorized by Danfoss CC.		Sheet 1 of 1
						A.2 Dwg N° PID-OP_PLUS