


INTERNAL INTERFACE CABLES ARE HIDDEN IN THE DRAWING FOR BETTER CLARITY

CONTROL COMPARTMENT DOOR IS NOT SHOWN IN THE DRAWING FOR SHOWING INTERNAL COMPONENTS IN CONTROL COMPARTMENT ONLY CONTROL COMPARTMENT UNIT IS SHOWN FOR BETTER CLARITY



REFER NOTE 3

NOTE:
 1. BACK CHANNEL COOLING: BOTTOM IN TOP OUT
 2. CABLE FEED: BOTTOM ENTRY & BOTTOM OUT
 3. PLINTH HEIGHT CAN BE OF 100, 200, & 400mm HEIGHT

CRITICAL CHARACTERISTICS
 KEY CHARACTERISTICS
 INSPECTION
 MUST COMPLY TO ROHS DIRECTIVE 2011/65/EU

INTERPRET DIM. & TOL. PER ASME Y14.5M-1994		THIRD ANGLE PROJECTION	SCALE	SIZE	MATERIAL
ALL DIMENSIONS ARE IN MILLIMETERS			0.150	A1	
TOLERANCES UNLESS OTHERWISE SPECIFIED					FINISH
±0.10 ±0.50 ±1.0					DESCRIPTION
<p>— PDM CONTROLLED DRAWING — NOT VALID WITHOUT FROZEN DATE IN ID STAMP</p> <p>Danfoss MCAD-PLV-E6H-IP54-CONTACTOR</p>					
CHANGED	SABARISH	MAXY-29-19			
DESIGNED	Loufi	OCT-17-18			
CHECKED					
CONFIDENTIAL - PROPERTY OF DANFOSS A/S NORBORG, DENMARK. NOT TO BE HANDED OVER TO BE COPIED OR BE USED BY A THIRD PARTY. TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.					
DRAWING NUMBER				REV	
132R0279				002	
WORK				SHEET	1 OF 3
132R0279					

