



Preso di pressione  
7/16"UNF - 1/4"SAE  
SCHRADER con tappo  
(a richiesta del Cliente,  
montare il meccanismo  
di carica).

27 SET. 2002  
APPROVEND

Preso di pressione  
7/16"UNF - 1/4"SAE  
con tappo SW 14

CODICE	ODS	φi	φe	φp	A	B	C	D
6804500V01	3/8"	9.7	13	8.5	26	39	94	10
6804501V06	1/2"	12.95	16	11	29	42	97	14

MATERIAL : 11SMnPb37 UNI EN 10277-3

General Tolerances Table	Drawing Status :			PRODUCTION PRINT		
	Surface Area (m2)			Key characteristic Critical characteristic According to Danfoss standard 502Z0024	Material : See Notes	
Roughness (μm)	Estimated Mass (Kg)				Projection  Scale Size A3	Designation
	A	28-SEP-2016				<b>Sx Gauge port &amp; Dx in By-pass 38058 and 38059</b>
Revision	ECR Number	Date	Confidential: Property of Danfoss Commercial Compressors. Not to be handed over to copied or used by third party. Two or three dimensional reproduction of contents to be authorized by Danfoss CC.		Sheet 1 of 1	
Designer	KAMLESH				.0 Dwg N° SEE TABLE	
Approval	RAJAN GORE				A	