









Type	Value
Max Weight	38kg / 84lb
IP Class	IP21
UL Type	Type I



See page 2 for details




Position of connectors	
A	Line
B	Motor
C	Interface X0
D	Interface XI/X2

THIS DRAWING SHOWS THE MOST COMMON VERSION OF THIS PRODUCT VARIANT. SMALL DIFFERENCES MAY OCCUR DEPENDING ON THE FINAL PRODUCT CONFIGURATION.


CENTER OF GRAVITY: FOR REFERENCE ONLY, THE PRODUCT CONFIGURATION MAY INFLUENCE THE CG IN ALL THREE AXES.

UNLESS OTHERWISE SPECIFIED THE TOLERANCE IS ± 0.4 MM [0.4 INCH]. ALL DIMENSIONS ARE IN MILLIMETERS [INCH]		FIRST ANGLE PROJECTION	SCALE 1:10	DRAWING SIZE A3	MATERIAL -
					FINISH -
					DESCRIPTION
CHANGED					MCAD FK07 IP21 WITH DISCONNECT
DESIGNED	Kishore 2021-10-08				
CHECKED		PROPERTY OF DANFOSS A/S NORDBORG, DENMARK. TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.			DRAWING NUMBER: MCAD FK07 IP21 WITH DISCONNECT MODEL: MCAD FK07 IP21 WITH DISCONNECT REV: 1 OF 2



SECTION A-A
LINE TERMINALS




1:5



SECTION B-B
MOTOR TERMINALS



DETAIL C
SCALE 1:2



EARTHING INFORMATION

Position of connectors	
A	Line
B	Motor
C	Interface X0
D	Interface XI/X2

THIS DRAWING SHOWS THE MOST COMMON VERSION OF THIS PRODUCT VARIANT.
SMALL DIFFERENCES MAY OCCUR DEPENDING ON THE FINAL PRODUCT CONFIGURATION.

PROPERTY OF DANFOSS A/S NORDBORG, DENMARK. TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.

DRAWING NUMBER	REV
MCAD FK07 1P21 WITH DISCONNECT	
MODEL	SHEET
MCAD FK07 1P21 WITH DISCONNECT	2 OF 2