




Standard




Standard with Decoupling kits



Mounting-Base



Standard with Nema-Option



Standard with IP21-Option

THIS DRAWING SHOWS THE MOST COMMON VERSION OF THIS PRODUCT VARIANT.
SMALL DIFFERENCES MAY OCCUR DEPENDING ON THE FINAL PRODUCT CONFIGURATION.

CENTER OF GRAVITY:
FOR REFERENCE ONLY, THE PRODUCT CONFIGURATION MAY INFLUENCE THE CG IN ALL THREE AXES.

| | | | | | | | |
|---|------------------|---|-----------------|-----------------|----------|----------------|-----------------|
| UNLESS OTHERWISE SPECIFIED THE TOLERANCE IS ± 0.1MM (0.4 INCH). ALL DIMENSIONS ARE IN MILLIMETERS (INCH). | | FIRST ANGLE PROJECTION | SCALE 1:2 | DRAWING SIZE A1 | MATERIAL | - | |
| | | | | | FINISH | - | |
| | | | | | | DESCRIPTION | IC2-Micro MA02c |
| CHANGED | | | | | | DRAWING NUMBER | IC2-Micro MA02c |
| DESIGNED | DANFOSS 05/30/22 | MODEL | IC2-Micro MA02c | SHEET | 1 OF 1 | | |
| CHECKED | | PROPERTY OF DANFOSS A/S NORDBORG, DENMARK. TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S. | | | | | |