



# FRAME F3 AND F4 IP21/IP54/UL AND NEMA1/NEMA12



134.6 [5.30]  
0.0 [0.00]


## OPTIONS CABINET TERMINAL LOCATION



0.0 [0.00]  
75.3 [2.96]  
128.5 [5.06]  
150.3 [5.92]  
219.6 [8.65]  
294.6 [11.60]  
363.9 [14.33]  
369.5 [14.55]  
438.9 [17.28]

EARTH GROUND BAR

177G4467



004 Ø 12.0 [0.47]  
1031.4 [40.61]  
939.0 [36.97]

0.0 [0.00]  
44.4 [1.75]

244.4 [9.62]  
0.0 [0.00]  
76.4 [3.01]  
128.4 [5.05]  
119.0 [4.69]  
171.0 [6.73]

▽ CRITICAL CHARACTERISTICS  
▽ KEY CHARACTERISTICS  
○ INSPECTION  
MUST COMPLY TO ROHS DIRECTIVE 2011/65/EU

INTERPRET DIM. & TOL. PER ASME Y14.5M-1994 ALL DIMENSIONS ARE IN MILLIMETERS TOLERANCES UNLESS OTHERWISE SPECIFIED ±1.0 ±0.50 ±1.0		THIRD ANGLE PROJECTION	SCALE 0.200	SIZE A1	MATERIAL	
— PDM CONTROLLED DRAWING — NOT VALID WITHOUT FROZEN DATE IN ID STAMP				FINISH		
CHANGED	BC			05/07/18	DESCRIPTION	
DESIGNED	ML			06/28/07	DRW_REF_OPTIONS CAB_F3/F4	
CHECKED			DRAWING NUMBER 177R0036		REV 004	
CONFIDENTIAL - PROPERTY OF DANFOSS A/S NORBORG, DENMARK. NOT TO BE HANDED OVER TO BE COPIED OR BE USED BY A THIRD PARTY. TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.				SHEET 1 OF 3		

UNIT TYPE	DIMENSION FOR TERMINAL			
	A	B	C	D
450 kW (480V) 630/710 kW (690V)	34.9	86.9	122.2	174.2
500/560/630/710/800 kW (480V) 800/900/1M0 kW (690V)	46.2622	98.2622	119.013	171.013

FRAME F3 AND F4  
IP21/IP54/UL AND NEMA1/NEMA12

OPTIONS CABINET TERMINAL LOCATION WITH CIRCUIT BREAKER/MOLDED CASE SWITCH

