







114N3585		OP-HNXM0400UWK000N	
ITEM	PART NUMBER	DESCRIPTION	QTY
1	119-8211P03A	HOUSING J8 BACK PANEL ST G16 GRAY	1
2	119-8211P02B	HOUSING J8 LEFT PANEL ST G16 GRAY	1
3	119-8211P04A	HOUSING J8 TOP PANEL ST G16 GRAY	1
4	119-9319	EBOX 230V/1PH/60Hz Slim J8 MLZ026-030 LA	
5	119-8318P02A	HOUSING J8 ELECT PANEL COVER ST G16 GRAY	1
6	119-8216P01A	FAN SHROUD J8 ST G16 GRAY	1
7	021Z0644	MCHE Condenser 25.4x1.3x26 DF0041 I/24	1
8	119-8254	FAN MOTOR D450 230V-1F-50/60HZ	1
9	119-8186B	BASEPLATE G8/J8 ST G11 1204X420X35 GRAY	1
10	119-8381A	CONDENSER BRACKET J8 ST G12 GRAY	1
11	119-8216P02A	CONDENSER SUPPORT J8 ST G16 GRAY	1
12	119-8211P05A	HOUSING J8 FRONT PANEL ST G18 GRAY	1
13	121L8763	COMPRESSOR MLZ030T1LQ9A, M-PACK	1
14	119-9389	PIPE MCHE TO NRV 5/8" J8	1
15	119-9391	PIPE MCHE TO HEAD VALVE 5/8" J8	1
16	020B1018	NRV 16s Check valve SW M/24X4	2
17	119-9390	PIPE CONNec TEE TO NRV 5/8"	1
18	119-9392	PIPE NRV TO RECEIVER 1/2" J8	1
19	120Z5011	CRANKCASE HEATER 230V 70W - 70 FRAME	1
20	119-8193A	RECEIVER 8L 33B HJM32 - 64 UL	1
21	119-9429	PIPE L HEAD VALVE 5/8"	1
22	119-9416	Head Pressure Valve 5/8" LAC-5 180 PSI	1
23	119-9429	PIPE L HEAD VALVE 5/8"	1
24	119-9388	PIPE COMPRESSOR TO NRV 5/8" J8 -1	1
25	6804507V10	VALVE SERV. V10 1"-14R X 5/8"S	1
26	6804504V05	VALVE SERV. V05 1 1/4"-12R X 7/8"S	1
27	119-8224	Crankcase heater 72" (MLZ)	1
28	119-8188	(B) TUBE 7/8-7/8ODX7/8ID-2B-SW	1
29	6804501V06	VALVE SERV. V06 1"-14R X 1/2"S	1
30	023Z5044	Filter drier DML 164 M/12	1
31	119-8212A	(B) TUBE 7/8-7/8ODX7/8ID-2B-SW	1
32	061H3140	XGE Fan Speed Controller 4C	1
33	191U165525	(B) TUBE 1/2-1/2ODX1/2F-1B-FL	1
34	119-8382A	BRACKET FOR TUBE CLAMPING ST G14 GRAY	1
35	119-8211P06	HOUSING J8 LEFT COVER ST G16 GRAY	1
36	5501026P09AA	INSULATION PIPE 5/8 TYPE AC	1
37	5501026P09AA	INSULATION PIPE 5/8 TYPE AC	1
38	119-9154	INSULATION SHEET 48"x70"x1/2" roll	1
39	119-9154	INSULATION SHEET 48"x70"x1/2" roll	1
40	5501026P09AA	INSULATION PIPE 5/8 TYPE AC	1
41	5501026P09AA	INSULATION PIPE 5/8 TYPE AC	1
42	014L0173	SGP 12 N Sight Glass M/24x3	1
114N3586		OP-HNXM0400UWK000Q	
43	121L8765	COMPRESSOR MLZ030T2LQ9A, M-PACK	1
44	119-9320	EBOX 230V/3PH/60Hz Slim J8 MLZ026-030 LA	1

General Tolerances Table	Drawing Status : Production Print								
				Surface Area (m2)		N/A		▽ Key characteristic ⊙ Critical characteristic According to Danfoss standard 502Z0024	
	Unless Otherwise Spec.				Estimated Mass (Kg)		115		
				Projection		Scale	Size		
Units = mm Tol. = ± 7.0 Ang° = ± 1.0°						1:10	A3	Material : See Note 1	
Roughness (µm) N/A								Designation OP-HNXM0400UWK000N	
	Revision	ECR Number	Date						
	Designer	Patricio Treviño							
	Approval	Guillermo Magaña							
ISO 8015 ISO 1101	Confidential: Property of Danfoss Commercial Compressors. Not to be handed over to copied or used by third party. Two or three dimensional reproduction of contents to be authorized by Danfoss CC.							Sheet 2 of 2	AA
								Dwg N° 114N3585	