







114N3575		OP-HJZM0150UWK000N	
ITEM	PART NUMBER	DESCRIPTION	QTY
1	014L0100	SGP 10 I Sight Glass E&I 1/70	1
2	020B1012	NRV 12s Check valve SW M/24X4	2
3	MTZ18-1V1	COMPRESSOR VERSION EGALISATION I	1
4	6804507V10	VALVE SERV. V10 1"-14R X 5/8"S	1
5	6804501V06	VALVE SERV. V10 1"-14R X 5/8"S	1
6	021Z0642	MICROCHANNEL D8	1
7	023Z5040	FILTER DRIER DML 083	1
8	120Z0389	SSH 80W 230V Nelico (1 pack 8)	1
9	061H3140	COMPONENT, FEMALE FAN SPEED CONTROLLER	1
10	119-3754	VALVE SERV. CM 1"-14R X 3/8"S	1
11	191U165025	TUBE 3/8-3/80DX3/8F-2B-FL	1
12	119-8191	Receiver 3L CE BL UL	1
13	7303292P01A	CRANKCASE HEATER 59" lead	1
14	119-8209	Base D8 (D33/D43) 1104 X 340 X 35.5	1
15	119-8210	FAN SHROUD G8 ST G16 GRAY	1
16	119-8226	(B) TUBE 5/8-5/80DX5/8ID-3B-SW	1
17	119-8227	(B) TUBE ASSY. 3/8-4P-FL/FT	1
18	119-9315	EBOX 230V/1PH/60Hz Slim D8 MTZ018 LA	1
19	119-8253	FAN MOTOR D350 230V-1F-50/60HZ	1
20	119-8258	Clamp, 3/8" Cu Tube w/ Cushion	1
21	119-8260	Clamp, 5/8" Cu Tube w/ Cushion	1
22	119-8316P02A	HOUSING D8 ELECT PANEL COVER ST G16 GRAY	1
23	119-8382	BRACKET FOR TUBE CLAMPING ST G14 GRAY	1
24	119-8384	CONDENSER BRACKET D8/G8 ST G12 GRAY	1
25	119-8386	(B) TUBE 3/8-3/80DX1/4MF-1B-AS	1
26	119-9298	Head Pressure Control- Parker LAC	#903038P
27	119-9305	PIPE COMP NRV 1/2"	1
28	119-9306	PIPE NRV MCHE 1/2"	1
29	119-9307	PIPE COMP HEAD VALVE 1/2";	1
30	119-9308	PIPE MCHE HEAD VALVE 3/8"	1
31	119-9309	PIPE HEAD VALVE NRV 3/8"	1
32	119-9310	PIPE NRV RECEIVER 3/8"	1
33	119-9310	PIPE NRV RECEIVER 3/8"	1
34	119-8208P02	Housing Panels (D8-D43) LEFT SIDE PANEL	1
35	119-8208P03	Housing Panels (D8-D43) BACK SIDE PANEL	1
36	119-8208P04	Housing Panels (D8-D43) TOP SIDE PANEL	1
37	119-8208P05	Housing Panels (D8-D43) FRONT SIDE PANEL	1
39	5501026P09AA	INSULATION PIPE 5/8 TYPE C	1
40	5501026P09AA	INSULATION PIPE 5/8 TYPE C	1
41	5501026P09AA	INSULATION PIPE 5/8 TYPE C	1
42	5501026P09AA	INSULATION PIPE 5/8 TYPE C	1
43	119-9154	INSULATION SHEET 48" X 70'1/2" ROLL	1
44	119-9154	INSULATION SHEET 48" X 70'1/2" ROLL	1
114N3576		OP-HJZM0150UWK000Q	
45	MTZ18-3V1	COMPRESSOR OSG-EQUAL MULTIREF	1
46	119-9316	EBOX 230V/3PH/60Hz Slim D8 MTZ018 LA	1

General Tolerances Table		Drawing Status : Change in progress				▽ Key characteristic ⊗ Critical characteristic According to Danfoss standard 502Z0024		
Unless Otherwise Spec Units = mm Ang° = ±1.0° Tol. = ±7.0			Surface Area (m2)					
			Estimated Mass (Kg)					
			Projection 	Scale 1/8	Size A3			
Roughness (µm) N/A	AA	Initial Release	18-01-2023				Material : See Notes	
	Revision	ECR Number	Date					Designation OP-HJZM0150UWK000N
	Designer	Patricio Treviño						
• ISO 8015 ISO 1101	Approval	Jacobo Saynes		Confidential: Property of Danfoss Commercial Compressors. Not to be handed over to copied or used by third party. Two or three dimensional reproduction of contents to be authorized by Danfoss CC.		Sheet 2 of 2	AA	
								AA.3 Dwg N° 114N3575