








114N3592		OP-HNXM0750UWK000Q	
ITEM	PART NUMBER	DESCRIPTION	QTY
1	119-8202P03A	HOUSING Q8 TOP PANEL ST G16 GRAY	1
2	119-8202P04A	HOUSING Q8 FRONT PANEL ST G20 GRAY	1
3	119-8273P03A	FAN SHROUD LEFT COVER Q8 ST G20 GRAY	1
4	119-8273P01B	FAN SHROUD FRONT Q8 230V ST G20 GRAY	1
5	119-8202P01A	HOUSING Q8 RIGHT PANEL ST G16 GRAY	1
6	6804507V10	VALVE SERV. V10 1"-14R X 5/8"S	1
7	119-8273P02A	FAN SHROUD RIGHT COVER Q8 ST G20 GRAY	1
8	021Z0646	MCHE Condenser 25.4x1.3x26 DF0061 I/12	1
9	119-8181A	CONDENSER BRACKET Q8 ST G11 GRAY	2
10	121L8817	COMPRESSOR MLZ058T2LQ9A, M-PACK	1
11	119-9321	EBOX 230V/1PH/60Hz Slim N8 MLZ038-048 LA	1
12	119-8320P02A	HOUSING Q8 ELECT PANEL COVER ST G16 GRAY	1
13	119-8255	FAN MOTOR D600 230V-1F-50/60HZ	2
14	119-8195	Receiver 14L, ASME	1
15	120Z0138	ACC CRKCASE HTR NELICO/65W230V	1
16	119-8224	Crankcase heater 72" (MLZ)	1
17	119-9417	Head Pressure Valve 903033P 7/8" LAC-5 180 PSI	1
18	020B1054	NRV 19s Check valve SW M/28	2
19	119-8187A	BASEPLATE Q8 ST G11 1554X800X50 GRAY	1
20	119-9402	PIPE NRV TO RECEIVER 3/4"	1
21	191U161007	(B) TUBE 5/8-5/8ODX5/8ID-0B-SW	1
22	119-9399	PIPE MCHE TO HEAD VALVE 3/4"	1
23	119-9404	PIPE HEAD VALVE TO NRV 7/8"	1
24	119-9401	PIPE NRV TO HEAD VALVE 7/8"	1
25	119-9403	PIPE CONNec TEE TO NRV 7/8"	1
26	119-9400	PIPE COMPRESSOR NRV 7/8"	1
27	191U155927	B) TUBE 7/8-7/8ODX7/8OD-1B-NO	1
28	6804504V05	VALVE SERV. V05 1 1/4"-12R X 7/8"S	1
29	119-8146	(B) TUBE 7/8-7/8ODX7/8ID-2B-SW	1
30	119-8382A	BRACKET FOR TUBE CLAMPING ST G14 GRAY	3
31	6804506V02	VALVE SERV. V02 1 3/4"-12R X 1 1/8"S	1
32	014L0174	SGP 16 N Sight Glass M/36	1
33	119-8189	(B) TUBE 1 1/8-1 1/8ODX1 1/8ID-4B-SW	1
34	119-8206	(B) TUBE 5/8-5/8FX5/8ID-2B-ML	1
35	061H3140	XGE Fan Speed Controller 4C	1
36	023Z5045	Filter drier DML 165 M/12	1
37	191U165607	(B) TUBE 5/8-5/8ODX5/8F-3B-FL	1
38	5501026P09AA	INSULATION PIPE 5/8 TYPE AC	1
39	5501026P09AA	INSULATION PIPE 5/8 TYPE AC	1
40	5501026P05AA	INSULATION PIPE 7/8 TYPE AC	1
41	5501026P05AA	INSULATION PIPE 7/8 TYPE AC	1
42	5501026P05AA	INSULATION PIPE 7/8 TYPE AC	1
43	119-9154	INSULATION SHEET 48"X70"X1/2" ROLL	1
44	119-9154	INSULATION SHEET 48"X70"X1/2" ROLL	1
114N3593		OP-HRXM1000UWK000Q	
45	121L8835	COMPRESSOR MLZ076T2LQ9A, M-PACK	1

General Tolerances Table		Drawing Status : Production Print						
Unless Otherwise Spec. Units = mm Tol. = ± 7.0 Ang° = ± 1.0°				Surface Area (m2)		N/A		▽ Key characteristic ⊙ Critical characteristic According to Danfoss standard 502Z0024
				Estimated Mass (Kg)		N/A		
				Projection		Scale	Size	
						1:20	A3	
Roughness (µm) N/A	AA	New Release	10-oct-23				Designation OP-HNXM0750UWK000Q	
	Revision	ECR Number	Date					
	Designer	Patricio Treviño						
	Approval	Guillermo Magaña						
ISO 8015 ISO 1101	Confidential: Property of Danfoss Commercial Compressors. Not to be handed over to copied or used by third party. Two or three dimensional reproduction of contents to be authorized by Danfoss CC.						Sheet 2 of 2	AA
							Dwg N° 114N3592	