






- 1.MCHE product platform:C125(25.4S);
- 2.FPI=23;
- 3.Tube:25.4X1.3X26ports;
- 4.Tube material:9153;
- 5.Inlet and outlet tubes are copper;
- 6.Internal hold-up volume:2.79L;
- 7.PS:45bar,TS MIN/MAX:-40°C~121°C;
- 8.Need E-coating and UV top coating.

Distribution

IN	76
OUT	50

MRK	REVISION RECORD	DRN	DATE	Linear Tolerance Not Specified				Projection	Scale	Size	Angle Tolerance Not Specified	
				≤6	>6-30	>30-120	>120-400				0°/90°/180°	Other Angle
				±0.5	±1	±1.5	±2.5		1 : 5	A2	±3°	±3°
				>400-1000 >1000-2000 >2000-4000							Designation	
				±4	±6	±8	MCHE condenser D1800-C					
				DRN	H.JIN						Customer PN:	
				APP								
				DATE	2024.01.24							
				Confidential: Property of Danfoss A/S, Nordborg, Denmark. Not to be handed over to, copied or used by third party. Two- or three dimensional reproduction of contents to be authorized by Danfoss A/S.							NO. X0-DF0071E	REV.
											WT. 18.2Kg	00