


APPROVED

Name _____
Date _____



Technical requirements:

- 1.Product type:C125(25.4S);
- 2.FPI=23;
- 3.Tube:25.4X1.3X26 ports;
- 4.Tube material:9153;
- 5.Inlet and outlet tubes are copper;
- 6.Internal hold-up volume:3.49L;
- 7.PS:45bar,TS MIN/MAX: -40°C~121°C.

40 ± 5
[1.57 ± 0.2]

1274 ± 3
[50.16 ± 0.12]
(1242
[48.9])

UKCA label
UL label
PED label
GOST label

100
[3.94]
B(TYP)
68.8 ± 3
[2.71 ± 0.12]

817.6 ± 3
[32.19 ± 0.12]

134 ± 3
[5.28 ± 0.12]
100
[3.94]

68.8 ± 3
[2.71 ± 0.12]

263.7 ± 3
[10.38 ± 0.12]

238.2
[9.38]

238.2
[9.38]


238.2
[9.38]

16X 3.2
[0.126]

1352.9 ± 0.14 (Hole to hole)
[53.26 ± 0.55]

1362.9 ± 0.14 (Total height)
[53.66 ± 0.55]

1346.4 ± 4
[53.01 ± 0.16]



MRK
6A

REVISION RECORD

Change transitions to transition blocks and change tube material.

DRN
H.JIN

DATE
2024.02.05

Linear Tolerance Not Specified
≤6 >6-30 >30-120 >120-400
±0.5 ±1 ±1.5 ±2.5
>400-1000 >1000-2000 >2000-4000
±4 ±6 ±8

Projection
1:5

Scale
1:5

Size
A2

Angle Tolerance Not Specified
0°/90°/180° Other Angle
±3° ±3°

DRN
APP
DATE
2017.05.24

Designation
MCHC Condenser
D1900-C

Customer PN:
NO. X0-DF0101
WT. 20.082 kg
REV. 08

Confidential: Property of Danfoss A/S, Nordborg, Denmark.
Not to be handed over to, copied or used by third party. Two- or three
dimensional reproduction of contents to be authorized by Danfoss A/S.