






- ### ⚠️ Technical requirements:
- 1.Product type:C116(16S);
 - 2.FPI=23;
 - 3.Tube:16X1.3X16 ports;
 - 4.Tube material:9153;
 - 5.Inlet and outlet tubes are copper;
 - 6.Internal hold-up volume: 0.4L;
 - 7.PS:45bar, TS MIN/MAX:-40°C~121°C.



MRK	REVISION RECORD						DRN	DATE	Linear Tolerance Not Specified				Projection	Scale	Size	Angle Tolerance Not Specified		
A	Change tube material.						SQ.ZHANG	2024.03.04	≤6	>6-30	>30-120	>120-400		3: 7	A2	0°/90°/180°		Other Angle
									±0.5	±1	±1.5	±2.5				±3°		±3°
									>400-1000	>1000-2000	>2000-4000	Designation						
									±4	±6	±8	MCHC condenser D1300-C						
									DRN JB.LIU									
									APP									
									DATE 2021.01.04			Customer PN:						
Confidential: Property of Danfoss A/S, Nordborg, Denmark. Not to be handed over to, copied or used by third party. Two- or three dimensional reproduction of contents to be authorized by Danfoss A/S.									NO. X0-DF0141		REV. 09							
									WT. 2.153 kg									