






APPROVED

Name _____
Date _____



- Technical requirements:**
- 1.Product type:C116(16S);
 - 2.FPI=23;
 - 3.Tube:16X1.3X16 ports;
 - 4.Tube material:9153;
 - 5.Inlet and outlet tubes are copper;
 - 6.Internal hold-up volume: 0.9L;
 - 7.PS:45bar, TS MIN/MAX:-40°C~121°C.

Distribution	
IN	35
OUT	30

MRK	REVISION RECORD			DRN	DATE	Linear Tolerance Not Specified			Projection	Scale	Size	Angle Tolerance Not Specified					
A	Change transitions to transition blocks and change tube material.			SQ.ZHANG	2024.03.04	≤6	>6-30	>30-120	120-400		1 : 3	A2	0°/90°/180°	Other Angle			
						±0.5	±1	±1.5	±2.5				±3°	±3°			
						>400-1000	>1000-2000	>2000-4000	Designation								
						±4	±6	±8	MCHC condenser D1600-C								
						DRN		JB.LIU					Customer PN:				
						APP											
						DATE		2021.01.05									
						Confidential: Property of Danfoss A/S, Nordborg, Denmark. Not to be handed over to, copied or used by third party. Two- or three dimensional reproduction of contents to be authorized by Danfoss A/S.							NO.	X0-DF0161	REV. 07		
													WT.	5.977 kg			