






Type	Value
Max Weight	55 kg / 121 lb
IP Class	IP20
UL Type	Open







DETAIL C SCALE 1:5



200MM AIR SPACE FOR COOLING

200MM AIR SPACE FOR COOLING



Position of connectors	
A	Line
B	Motor
C	Brake / DC
D	Interface X0
E	Interface X1/X2

THIS DRAWING SHOWS THE MOST COMMON VERSION OF THIS PRODUCT VARIANT. SMALL DIFFERENCES MAY OCCUR DEPENDING ON THE FINAL PRODUCT CONFIGURATION.

● CENTER OF GRAVITY: FOR REFERENCE ONLY, THE PRODUCT CONFIGURATION MAY INFLUENCE THE CG IN ALL THREE AXES.

UNLESS OTHERWISE SPECIFIED THE TOLERANCE IS ± 1MM [0.4 INCH]. ALL DIMENSIONS ARE IN MILLIMETERS [INCH]		FIRST ANGLE PROJECTION	SCALE	DRAWING SIZE	MATERIAL
			1:10	A3	
		FINISH			
		DESCRIPTION			
		mca08_fa08_ip20			
CHANGED					
DESIGNED	Danfoss 2020-09-30				
CHECKED					
PROPERTY OF DANFOSS A/S NORDBORG, DENMARK. TWO OR THREE DIMENSIONAL REPRODUCTION OF CONCEPTS TO BE AUTHORIZED BY DANFOSS A/S.		DRAWING NUMBER	MCAD_FA08_IP20	REV	
		MODEL	MCAD_FA08_IP20	SHEET	1 OF 1