

Type	Value
Max Weight	208kg/458lb
IP Class	IP54
Frame	AAF 03

A


B

C







D

E

F



SEE DETAIL A



SCALE 1:20

Tolerances(mm)					
Dimension	<250	250>x>800	800	Parts in series	Folded parts
Tolerance	+/-1	+/-2.5	+/-4	+/-2.5	+/-2.5

THIS DRAWING SHOWS THE MOST COMMON VERSION OF THIS PRODUCT VARIANT.
SMALL DIFFERENCES MAY OCCUR DEPENDING ON THE FINAL PRODUCT CONFIGURATION.



CENTER OF GRAVITY:
FOR REFERENCE ONLY, THE PRODUCT CONFIGURATION MAY INFLUENCE THE CG IN ALL THREE AXES.

UNLESS OTHERWISE SPECIFIED THE TOLERANCE IS ±1MM [0.4 INCH].
ALL DIMENSIONS ARE IN MILLIMETERS [INCH]

FIRST ANGLE PROJECTION

SCALE
1:4

DRAWING
SIZE
A3

MATERIAL

FINISH

DESCRIPTION

MCAD-AAF-03-IP54

CHANGED		
DESIGNED	Danfoss	04/17/25
CHECKED		

Danfoss

PROPERTY OF DANFOSS A/S NORDBORG, DENMARK. TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.

DRAWING NUMBER
MCAD-AAF-03-IP54

MODEL

REV

SHEET

1 OF 1

A

B

C

D

E

F