

Type	Value
Max Weight	269kg/593lbs
IP Class	IP54
Frame	AAF 04

A


B

C






D

E

F



SEE DETAIL A



SCALE 1:25

Tolerances(mm)					
Dimension	<250	250>x>800	800	Parts in series	Folded parts
Tolerance	+/-1	+/-2.5	+/-4	+/-2.5	+/-2.5

THIS DRAWING SHOWS THE MOST COMMON VERSION OF THIS PRODUCT VARIANT.
SMALL DIFFERENCES MAY OCCUR DEPENDING ON THE FINAL PRODUCT CONFIGURATION.



CENTER OF GRAVITY:
FOR REFERENCE ONLY, THE PRODUCT CONFIGURATION MAY INFLUENCE THE CG IN ALL THREE AXES.

UNLESS OTHERWISE SPECIFIED THE TOLERANCE IS ±1MM [0.4 INCH]. ALL DIMENSIONS ARE IN MILLIMETERS [INCH]			FIRST ANGLE PROJECTION		SCALE 1:4	DRAWING SIZE A3	MATERIAL	
			FINISH					
							DESCRIPTION MCAD-AAF-04-IP54	
CHANGED			DESIGNED	Danfoss	07/15/25	CHECKED		
PROPERTY OF DANFOSS A/S NORDBORG, DENMARK. TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.								
DRAWING NUMBER							MCAD-AAF-04-IP54	REV
MODEL								SHEET 1 OF 1