








Type	Value
Max Weight	29kg / 64lb
IP Class	IP55
UL Type	Type 12




200MM AIR SPACE FOR COOLING

200MM AIR SPACE FOR COOLING



SCALE 3:20

Position of connectors	
A	Line
B	Motor
C	Brake/DC
D	Interface X0
E	Interface X1/X2 or X4




Product label

THIS DRAWING SHOWS THE MOST COMMON VERSION OF THIS PRODUCT VARIANT. SMALL DIFFERENCES MAY OCCUR DEPENDING ON THE FINAL PRODUCT CONFIGURATION.


CENTER OF GRAVITY: FOR REFERENCE ONLY, THE PRODUCT CONFIGURATION MAY INFLUENCE THE CG IN ALL THREE AXES.

UNLESS OTHERWISE SPECIFIED THE TOLERANCE IS ± 0.1 MM [0.4 INCH]. ALL DIMENSIONS ARE IN MILLIMETERS [INCH]			FIRST ANGLE PROJECTION	SCALE 1:10	DRAWING SIZE A3	MATERIAL			
						FINISH			
						DESCRIPTION			
						MCAD_FB06_IP55			
CHANGED			PROPERTY OF DANFOSS A/S NORDBORG, DENMARK. TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.			DRAWING NUMBER			
DESIGNED	Danfoss	2025-12-18				MCAD_FB06_IP55		REV	
CHECKED						MODEL		SHEET 1 OF 2	
						MCAD_FB06_IP55			





SECTION A-A
LINE TERMINALS



SECTION B-B
MOTOR TERMINAL



SECTION C-C
DC/BRAKE TERMINAL



Position of connectors	
A	Line
B	Motor
C	Brake/DC
D	Interface X0
E	Interface X1/X2 or X4

THIS DRAWING SHOWS THE MOST COMMON VERSION OF THIS PRODUCT VARIANT.
SMALL DIFFERENCES MAY OCCUR DEPENDING ON THE FINAL PRODUCT CONFIGURATION.

PROPERTY OF DANFOSS A/S NORDBORG, DENMARK. TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.

DRAWING NUMBER	REV
MCAD_FB06_IP55	
MODEL	SHEET
MCAD_FB06_IP55	2 OF 2