







NOTES:

1. THIS ENCLOSURE CONFIGURATION IS USED FOR ALL OPTION COMBINATIONS CONTAINING BYPASS WITH DV/DT FILTER OR LINE REACTOR OR CONTACT MOTOR SELECT OR DUAL MOTOR.
2. AT MINIMUM THE TWO OUTSIDE LIFTING POINTS ARE REQUIRED WHEN HANDLING THIS UNIT.

TIER 3 DIMENSIONS										
	A	B	C	D	E	F	G	H	J	K
D1 FRAME	1154.0 [45.4]	1209.9 [47.6]	1163.7 [45.8]	1175.6 [46.3]	847.5 [33.4]	200.0 [7.9]	805.0 [31.7]	285.0 [11.2]	232.5 [9.2]	52.5 [2.1]
D2 FRAME	1534.5 [60.4]	1588.2 [62.53]	1542.8 [60.7]	1272.1 [50.1]	859.5 [33.8]	271.0 [10.67]	808.0 [31.8]	374.0 [14.7]	327.0 [12.9]	47.0 [1.9]

D-FRAME MAX WEIGHTS	
	TIER 3
D1 FRAME	585 lbs [265 kg]
D2 FRAME	1070 lbs [486 kg]

TITLE			
INSTALLATION DRAWING, P650, D1 D2 TIER 2 / TIER 3			
SIZE	MODEL	REV	
D	P650-3_ASSY	005	
SCALE	DRAWING NO.	SHEET	
0.200	174N8666	2 OF 4	

D

C

B

A


D

C

B



A

AIR FLOW SPACING REQUIREMENTS



PEDESTAL MOUNTING PATTERN			
	A	B	C
D1 FRAME	289.8 [11.41]	328.9 [12.95]	750.4 [29.54]
D2 FRAME	384.8 [15.15]	423.9 [16.69]	845.4 [33.28]

DRIVE/PANEL CONFIGURATION	PEDESTAL KIT	QTY
D1 TIER2 (NEMA 1)	185B6017	1
D1 TIER2 (NEMA 12)	185B6018	1
D1 TIER3 (NEMA 1)	185B6019	1
D1 TIER3 (NEMA 12)	185B6020	1
D2 TIER2 (NEMA 1)	185B6021	1
D2 TIER2 (NEMA 12)	185B6022	1
D2 TIER3 (NEMA 1)	185B6023	1
D2 TIER3 (NEMA 12)	185B6024	1



TITLE			
INSTALLATION DRAWING, P650, D1 D2 TIER 2 / TIER 3			
SIZE	MODEL	REV	
D	P650-3_ASSY	005	
SCALE	DRAWING NO.	SHEET	
0.200	174N8666	3 OF 4	

