



Type	Value
Max Weight	35kg/77lb
IP Class	IP55
UL Type	Type 12




See page 2 for details





Company name


200MM AIR SPACE FOR COOLING



200MM AIR SPACE FOR COOLING



SCALE 1:10




Position of connectors	
A	Line
B	Motor
C	Brake/DC
D	Interface X0
E	Interface X1/X2 or X4

THIS DRAWING SHOWS THE MOST COMMON VERSION OF THIS PRODUCT VARIANT. SMALL DIFFERENCES MAY OCCUR DEPENDING ON THE FINAL PRODUCT CONFIGURATION.


CENTER OF GRAVITY: FOR REFERENCE ONLY, THE PRODUCT CONFIGURATION MAY INFLUENCE THE CG IN ALL THREE AXES.

UNLESS OTHERWISE SPECIFIED THE TOLERANCE IS $\pm 0.1$ MM [0.4 INCH]. ALL DIMENSIONS ARE IN MILLIMETERS [INCH]			FIRST ANGLE PROJECTION	SCALE 1:10	DRAWING SIZE A3	MATERIAL
						FINISH
						DESCRIPTION
CHANGED						MCAD_FB07_IP55
DESIGNED	Danfoss	2026-01-22				
CHECKED						
PROPERTY OF DANFOSS A/S NORDBORG, DENMARK. TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.						DRAWING NUMBER
						MCAD_FB07_IP55
						MODEL
						FB07_IP55_ASSY
						REV
						SHEET 1 OF 2





SECTION A-A  
LINE TERMINALS




SECTION B-B  
MOTOR TERMINALS



SECTION C-C  
DC/BRAKE TERMINAL



EARTHING INFORMATION



DETAIL C  
SCALE 2:5

Position of connectors	
A	Line
B	Motor
C	Brake/DC
D	Interface X0
E	Interface X1/X2 or X4

THIS DRAWING SHOWS THE MOST COMMON VERSION OF THIS PRODUCT VARIANT.  
SMALL DIFFERENCES MAY OCCUR DEPENDING ON THE FINAL PRODUCT CONFIGURATION.

PROPERTY OF DANFOSS A/S NORDBORG, DENMARK. TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.

DRAWING NUMBER	MCAD_FB07_IP55	REV
MODEL	FB07_IP55_ASSY	SHEET
		2 OF 2