


Type	Value
Max Weight	4.5kg/9.9lb
IP Class	IP20
UL Type	Open






DETAIL A
SCALE 1:1





DETAIL B
SCALE 1:1




100MM [3.9INCH] AIR SPACE FOR COOLING


100MM [3.9INCH] AIR SPACE FOR COOLING







Position of connectors	
A	Line
B	Motor
C	Brake / DC
D	Interface X0
E	Interface X1/X2 or X4



THIS DRAWING SHOWS THE MOST COMMON VERSION OF THIS PRODUCT VARIANT.
SMALL DIFFERENCES MAY OCCUR DEPENDING ON THE FINAL PRODUCT CONFIGURATION.

CENTER OF GRAVITY:
FOR REFERENCE ONLY, THE PRODUCT CONFIGURATION MAY INFLUENCE THE CG IN ALL THREE AXES.

UNLESS OTHERWISE SPECIFIED THE TOLERANCE IS ±1MM [0.4 INCH]. ALL DIMENSIONS ARE IN MILLIMETERS [INCH]	FIRST ANGLE PROJECTION	SCALE 1:5
DRAWING SIZE A3	MATERIAL	
	FINISH	

CHANGED		
DESIGNED	Danfoss	2026-07-29
CHECKED		

DESCRIPTION: MCAD-FA02a-IP20

PROPERTY OF DANFOSS A/S NORDBORG, DENMARK. TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.

DRAWING NUMBER	MCAD-FA02a-IP20
REV	001
MODEL	MCAD-FA02a-IP20
SHEET	1 OF 1