


Type	Value
Max Weight	14.1kg/31.1 lb
IP Class	IP20
UL Type	Open








DETAIL A
SCALE 1:1





DETAIL B
SCALE 1:1











Position of connectors	
A	Line
B	Motor
C	Brake / DC
D	Interface X0
E	Interface X1/X2 or X4

THIS DRAWING SHOWS THE MOST COMMON VERSION OF THIS PRODUCT VARIANT.
SMALL DIFFERENCES MAY OCCUR DEPENDING ON THE FINAL PRODUCT CONFIGURATION.

CENTER OF GRAVITY:
FOR REFERENCE ONLY, THE PRODUCT CONFIGURATION MAY INFLUENCE THE CG IN ALL THREE AXES.

UNLESS OTHERWISE SPECIFIED THE TOLERANCE IS ±1MM [0.4 INCH]. ALL DIMENSIONS ARE IN MILLIMETERS [INCH]	FIRST ANGLE PROJECTION	SCALE 1:5	DRAWING SIZE A3	MATERIAL	
				FINISH	
CHANGED			DESCRIPTION: MCAD-FA05b-IP20		
DESIGNED	Danfoss	2026-07-30			
CHECKED					
PROPERTY OF DANFOSS A/S NORDBORG, DENMARK. TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.			DRAWING NUMBER: MCAD-FA05b-IP20	REV: 001	
			MODEL: MCAD-FA05b-IP20	SHEET: 1 OF 1	