


Type	Value
Max Weight	60kg/132lb
IP Class	IP55
UL Type	Type 12








DETAIL A
SCALE 1:2




DETAIL B
SCALE 1:2










SCALE 2:25




Position of connectors	
A	LIne
B	Motor
C	Interface X0
D	Interface X1/X2 or X4


THIS DRAWING SHOWS THE MOST COMMON VERSION OF THIS PRODUCT VARIANT.
SMALL DIFFERENCES MAY OCCUR DEPENDING ON THE FINAL PRODUCT CONFIGURATION.

CENTER OF GRAVITY:
FOR REFERENCE ONLY, THE PRODUCT CONFIGURATION MAY INFLUENCE THE CG IN ALL THREE AXES.


UNLESS OTHERWISE SPECIFIED THE TOLERANCE IS ±1MM [0.4 INCH]. ALL DIMENSIONS ARE IN MILLIMETERS [INCH]	FIRST ANGLE PROJECTION	SCALE 1:10	DRAWING SIZE A3	MATERIAL		
				FINISH		
				DESCRIPTION: MCAD-FB08-IP55-WITH-DISCONNECT		
CHANGED						
DESIGNED	Danfoss	2026-08-12				
CHECKED						
PROPERTY OF DANFOSS A/S NORDBORG, DENMARK. TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.				DRAWING NUMBER: MCAD-FB08-IP55-WITH-DISCONNECT		REV
				MODEL: FB08		SHEET: 1 OF 2

SECTION A-A
LINE TERMINAL







SECTION B-B
MOTOR TERMINAL




INTERFACE X4





EARTHING INFORMATION



DETAIL C
SCALE 1:5

Position of connectors	
A	Line
B	Motor
C	Interface X0
D	Interface X1/X2 or X4

THIS DRAWING SHOWS THE MOST COMMON VERSION OF THIS PRODUCT VARIANT.
SMALL DIFFERENCES MAY OCCUR DEPENDING ON THE FINAL PRODUCT CONFIGURATION.

PROPERTY OF DANFOSS A/S NORDBORG, DENMARK. TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.

DRAWING NUMBER	REV
MCAD-FB08-IP55-WITH-DISCONNECT	
MODEL: FB08	SHEET: 2 OF 2