


Type	Value
Max Weight	11.6kg/25.5 lb
IP Class	IP20
UL Type	Open








DETAIL A
SCALE 1:1




DETAIL B
SCALE 1:1










Position of connectors	
A	Line
B	Motor
C	Brake / DC
D	Interface X0
E	Interface X1/X2 or X4



THIS DRAWING SHOWS THE MOST COMMON VERSION OF THIS PRODUCT VARIANT.
SMALL DIFFERENCES MAY OCCUR DEPENDING ON THE FINAL PRODUCT CONFIGURATION.

CENTER OF GRAVITY:
FOR REFERENCE ONLY, THE PRODUCT CONFIGURATION MAY INFLUENCE THE CG IN ALL THREE AXES.

UNLESS OTHERWISE SPECIFIED THE TOLERANCE IS ±1MM [0.4 INCH]. ALL DIMENSIONS ARE IN MILLIMETERS [INCH]	FIRST ANGLE PROJECTION	SCALE 1:5	DRAWING SIZE A3	MATERIAL	
				FINISH	

CHANGED			
DESIGNED	Danfoss	2026-07-30	
CHECKED			

DESCRIPTION: MCAD-FA04b-IP20

PROPERTY OF DANFOSS A/S NORDBORG, DENMARK. TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.

DRAWING NUMBER	MCAD-FA04b-IP20
REV	001
MODEL	MCAD-FA04b-IP20
SHEET	1 OF 1