


Type	Value
Max Weight	13.6kg/30.0 lb
IP Class	IP20
UL Type	Open








DETAIL A
SCALE 1:1





DETAIL B
SCALE 1:1











Position of connectors	
A	Line
B	Motor
C	Brake / DC
D	Interface X0
E	Interface X1/X2 or X4

THIS DRAWING SHOWS THE MOST COMMON VERSION OF THIS PRODUCT VARIANT.
SMALL DIFFERENCES MAY OCCUR DEPENDING ON THE FINAL PRODUCT CONFIGURATION.

CENTER OF GRAVITY:
FOR REFERENCE ONLY, THE PRODUCT CONFIGURATION MAY INFLUENCE THE CG IN ALL THREE AXES.

CHANGED		
DESIGNED	Danfoss	2026-07-30
CHECKED		

UNLESS OTHERWISE SPECIFIED THE TOLERANCE IS ±1MM [0.4 INCH].
ALL DIMENSIONS ARE IN MILLIMETERS [INCH]

FIRST ANGLE PROJECTION

SCALE 1:5

DRAWING SIZE A3

MATERIAL

FINISH

DESCRIPTION: MCAD-FA05a-IP20

PROPERTY OF DANFOSS A/S NORDBORG, DENMARK. TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.

DRAWING NUMBER: MCAD-FA05a-IP20 REV 001

MODEL: MCAD-FA05a-IP20 SHEET 1 OF 1