ENGINEERING TOMORROW

Danfoss

Data Sheet

Solenoid coils Type **BA**, **BD**, **BB**, **BE**, **BF**, **BG**, **BN**, **BO**, **BJ**, **BX**, **BY**, **BQ**, **AM**, **AZ**, **AS** and **AP**

Solenoid coils for A and B system



Danfoss solenoid valves and coils are usually ordered separately to allow maximum flexibility, enabling you to select a valve and coil combination to best suit your needs.

The Danfoss coil program consists of both the easy-to-handle Clip-On system and traditional coils with threaded fastener.

Danfoss offer a wide range of application specific coils for e.g. steam or hazardous areas. The coils are available with approvals such as EN60730-1, EEx/ATEX and UL.

Features

- Encapsulated coils with long operating life, even under extreme conditions
- Standard coils for AC or DC
- Standard coils from 12 V 400 V, 50, 60, 50 / 60 Hz or DC
- Standard coils available with:
 - Cable plugs
 - Industrial plugs
 - Terminal box
 - 3 core cable
 - Junction box
 - Conduit hub



1 Coil identification

Technical data is printed directly on the coil:

Figure 1: Identification label



- 1 Country of origin
- 2 Coil type
- 3 Spare part no. (code no.)
- 4 Ambient temperature: $(-40 40 \degree C = Ambient temperature range: -40 \degree C 40 \degree C)$
- 5 Supply voltage [V]
- 6 Frequency [Hz]
- 7 Power consumption [W]
- 8 Power consumption [VA]
- 9 CE marking
- 10 UL recognized coil
- **11** Raw coil number (F4501=Raw coil number 018F4501)
- **12** Point of contact



2 Product specification

2.1 BA, High performance coils

Figure 2: BA, High performance coils



Features

- Cable plug enclosure:
 - IP00 version with DIN 43650 A spade connectors
 - IP20 version with protective cap
- IP65/IP67 version with cable plug
- Nut and snap fastener included
- In accordance with:
- RoHS Directive 2011/65/EU
- Low Voltage Directive 2014/35/EU
 - EN60730-1
 - EN60730-2-8

Table 1: BA, High performance coils

Turne	Tambient	Supply voltage	Voltage variation Frequency [Hz]	Frequency	Power cor	sumption	Code no.
Туре	[°C]	[V]		[W]	[VA]	Code no.	
BA024A	-40 - 40	24	-15%, 10%	50	8.5	17	042N7508
BA048A	-40 - 40	48	-15%, 10%	50	9.5	18	042N7510
BA115A	-40 - 40	115	-15%, 10%	50	9	18	042N7512
BA230A	-40 - 40	220 – 230	-15%, 6%	50	12	22	042N7501
BA240A	-40 - 40	240	-15%, 10%	50	10	20	042N7502
BA400A	-40 - 40	380 - 400	-15%, 6%	50	12	22	042N7504
BA024B	-40 - 40	24	-15%, 10%	60	9.5	19	042N7520
BA115B	-40 - 40	115	-15%, 10%	60	12	23	042N7522
BA220B	-40 - 40	220	-15%, 10%	60	11	21	042N7523
BA012D	-40 - 40	12	±10%	DC	14	-	042N7550
BA024D	-40 - 40	24	±10%	DC	14	-	042N7551

Table 2: Technical data

Design	In accordance with VDE 0580
Insulation of coil windings	Class H according to IEC 85
Connection	Spade connector in accordance with DIN 43650 form A
Enclosure, IEC 529	IP00 with spade connector, IP20 with protective cap, IP65 with cable plug
Duty rating	Continuous
Plug type	Cable plug (042N1256)



2.1.1 Dimensions and weight

Figure 3: BA, High performance coils




Table 3: BA, High performance coils

Туре	L without cable plug	L with protective cap	L with cable plug	Weight
	[mm]	[mm]	[mm]	[kg]
BA	54	71	79	0.16

2.2 BD, High performance coils

Figure 4: BD, High performance coils



Features

- Cable plug enclosure:
- IP00 version with DIN 43650 A spade connectors
- IP20 version with protective cap
- IP65/IP67 version with cable plug
- Nut and snap fastener included
- In accordance with:
- RoHS Directive 2011/65/EU
- Low Voltage Directive 2014/35/EU
 - EN60730-1
 - EN60730-2-8

Table 4: BD, High performance coils

Turno	Tambient	Supply voltage	Voltage variation	Voltage variation Frequency		Power con	Code no.
Туре	[° C]	[V]		[Hz]	[W]	[VA]	coue no.
BD024A	-40 - 40	24	-15%, 10%	50	15	29	042N7597
BD230A	-40 - 40	230	-10%, 6%	50	14	28	042N7591

Table 5: Technical data

Design	In accordance with VDE 0580
Insulation of coil windings	Class H according to IEC 85
Connection	Spade connector in accordance with DIN 43650 form A
Enclosure, IEC 529	IP00 with spade connector, IP20 with protective cap, IP65 with cable plug
Duty rating	Continuous
Plug type	Cable plug (042N1256)



2.2.1 Dimensions and weight

Figure 5: BD, High performance coils





Table 6: BD, High performance coils

Туре	L without cable plug	L with protective cap	L with cable plug	Weight
	[mm]	[mm]	[mm]	[kg]
BD	54	71	79	0.16

2.3 BB, High performance coils





Features

- Enclosure:
- IP00 version with DIN 43650 A spade connectors
- IP20 version with protective cap
- IP65/IP67 version with mounted cable plug
- In accordance with:
- RoHS Directive 2011/65/EU
- Low Voltage Directive 2014/35/EU
 - EN60730-1
 - EN60730-2-8

Table 7: BB, High performance coils

Ture	Tambient	Supply voltage	e Voltage variation	Frequency	Power consumption		
Туре	[°C] [V] [Voltage variation [Hz]	[Hz]	[W]	[VA]	Code no.		
BB024AS	-40 - 80	24	-15%, 10%	50	11	19	018F7358
BB115AS	-40 - 80	115	-15%, 10%	50	11	19	018F7361
BB230AS	-40 - 80	220 – 230	-15%, 10%	50	11	19	018F7351
BB240AS	-40 - 80	240	-15%, 10%	50	11	19	018F7352
BB440CS	-40 – 50	380 - 400	-15%, 10%	50	14	24	018F7353
00-40C3	-40 - 30	440	-15%, 10%	60	15	24	01017333
BB024BS	-40 - 80	24	-15%, 10%	60	14	23	018F7365
BB110CS	-40 – 50	110	±10%	50	15	28	018F7360
5511005		110	±10%	60	13	22	01017500
BB230CS	-40 – 50	220 – 230	±10%	50	16	31	018F7363
5525005	-40 - 50	220 – 230	±10%	60	13	24	01017505
BB012DS	-40 - 50	12	±10%	DC	14	-	018F7396
BB024DS	-40 - 50	24	±10%	DC	16	-	018F7397



Table 8: Technical data	
Design	In accordance with VDE 0580
Insulation of coil windings	Class H according to IEC 85
Connection	Spade connector in accordance with DIN 43650 form A
Enclosure, IEC 529	IP00 with spade connector, IP20 with protective cap, IP65 with cable plug
Duty rating	Continuous
Plug type	Cable plug (042N1256)

2.3.1 Dimensions and weight

Figure 7: BB, High performance coils




Table 9: BB, High performance coils

Туре	L without cable plug	L with protective cap	L with cable plug	Weight
	[mm]	[mm]	[mm]	[kg]
BB	62	77	85	0.24

2.4 BE, High performance coils





Features

- Enclosure: IP67 for moist environments with terminal box
- In accordance with:
- RoHS Directive 2011/65/EU
- Low Voltage Directive 2014/35/EU
 - EN60730-1
 - EN60730-2-8

Table 10: BE, High performance coils

Turno	Tambient	Supply voltage	Voltage variation	Voltage variation Frequency		Power consumption		
Туре	[° C]	[V]	voltage variation	[Hz]	[W]	[VA]	Code no.	
BE024AS	-40 - 80	24	-15%, 10%	50	12	21	018F6707	
BE048AS	-40 - 80	48	-15%, 10%	50	11	20	018F6709	
BE115AS	-40 - 80	115	-15%, 10%	50	11	19	018F6711	
BE230AS	-40 - 80	220 – 230	-15%, 10%	50	12	22	018F6701	
BE240AS	-40 - 80	240	-15%, 10%	50	11	19	018F6702	



Solenoid coils, type BA, BD, BB, BE, BF, BG, BN, BO, BJ, BX, BY, BQ, AM, AS, AZ and AP

Turne	Tambient	Supply voltage	age Voltage variation	Frequency	Power con	Code no.	
туре	Type [°C]	[V] Voltage variation	[Hz]	[W]	[VA]	Code no.	
BE440CS	-40 – 80	380 - 400	-15%, 10%	50	13	23	018F6703
DE440C3	-40 - 80	440	-15%, 10%	60	14	24	01860703
BE024BS	-40 - 80	24	-15%, 10%	60	14	25	018F6715
BE115CS	-40 – 80	100	-15%, 10%	50	11	19	018F6710
DETISCS	-40 - 80	115	-15%, 10%	60	13	22	01860710
BE220BS	-40 - 80	220	-15%, 10%	60	13	23	018F6714
BE110CS	-40 - 50	110	±10%	50	15	28	018F6730
BETTOCS	-40 - 50	110	±10%	60	13	22	01860730
BE230CS	-40 – 50	220 – 230	±10%	50	17	31	018F6732
BE230C3	-40 - 50	220 – 230	±10%	60	14	24	01860732
BE012DS	-40 - 50	12	±10%	DC	15	-	018F6756
BE024DS	-40 - 50	24	±10%	DC	16	-	018F6757

Table 11: Technical data

Design	In accordance with VDE 0580
Insulation of coil windings	Class H according to IEC 85
Connection	1 m 3-core flying lead
Enclosure, IEC 529	IP67
Duty rating	Continuous

2.4.1 Dimensions and weight

Figure 9: BE, High performance coils




Table 12: BE, High performance coils

Туре	L with terminal box	L with 1m cable	Weight
	[mm]	[mm]	[kg]
BE	94	65	0.30

2.5 BF, High performance coils

Figure 10: BF, High performance coils



Features

- Enclosure: IP67 for moist environments with molded-in cable
- In accordance with:

Danfoss

- RoHS Directive 2011/65/EU
- Low Voltage Directive 2014/35/EU
 - EN60730-1
 - EN60730-2-8

Table 13: BF, High performance coils

Turne	Tambient	Supply voltage	Voltage variation	Frequency	Power cor	sumption	Code no.	
Туре	[°C]	[V]	voltage variation	[Hz]	[W]	[VA]	Code no.	
BF230AS	-40 - 80	220 – 230	-15%, 10%	50	12	22	018F6251	
BF240AS	-40 - 80	240	-15%, 10%	50	11	19	018F6252	
BF440CS	-40 – 80	380 - 400	-15%, 10%	50	14	24	018F6253	
BF440C3	-40 - 80	440	-15%, 10%	60	15	24	01860233	
BF024AS	-40 - 80	24	-15%, 10%	50	12	20	018F6257	
BF115CS	-40 – 80	100	-15%, 10%	50	11	19	018F6260	
BEIISCS	-40 - 80	-40 - 80	115	-15%, 10%	60	13	22	01860200
BF220BS	-40 - 80	220	-15%, 10%	60	14	23	018F6264	
BF024BS	-40 - 80	24	-15%, 10%	60	14	25	018F6265	
BF110CS	-40 – 50	110	±10%	50	15	29	018F6280	
BEITOCS	-40 - 50	110	±10%	60	13	23	01860280	
BF230CS	0.00	220 – 230	±10%	50	16	31	01956292	
DF230C3	-40 – 50	220 – 230	±10%	60	14	24	018F6282	

Table 14: Technical data

Design	In accordance with VDE 0580
Insulation of coil windings	Class H according to IEC 85
Connection	1 m 3-core flying lead
Enclosure, IEC 529	IP67
Duty rating	Continuous

2.5.1 Dimensions and weight

Figure 11: BF, High performance coils




Table 15: BF, High performance coils

Туре	L with 1m cable [mm]	Weight [kg]
BF	67	0.30



2.6 BG, High performance coils

Figure 12: BG, High performance coils



Features

- Enclosure: IP67 for moist environments with terminal box
- In accordance with:
- RoHS Directive 2011/65/EU
- Low Voltage Directive 2014/35/EU
 - EN60730-1
 - EN60730-2-8

Table 16: BG, High performance coils

Tupo	Tambient	Supply voltage	Voltage variation	Frequency	Power con	sumption	Code no.
Туре	[°C]	[V]	[Hz]		[W]	[VA]	Code no.
BG024AS	-40 - 80	24	-15%, 10%	50	11	21	018F6807
BG110AS	-40 - 80	110	-15%, 10%	50	13	25	018F6811
BG230AS	-40 - 80	220 – 230	-15%, 10%	50	15	28	018F6801
BG240AS	-40 - 80	240	-15%, 10%	50	13	25	018F6802
BG400AS	-40 - 80	380 - 400	-15%, 10%	50	15	29	018F6803
BG024BS	-40 - 80	24	-15%, 10%	60	15	29	018F6815
BG110BS	-40 - 80	110	-15%, 10%	60	16	29	018F6813
BG220BS	-40 - 80	220	-15%, 10%	60	16	29	018F6814
BG012DS	-40 - 50	12	±10%	DC	20	-	018F6856
BG024DS	-40 – 50	24	±10%	DC	20	-	018F6857

Table 17: Technical data

Design	In accordance with VDE 0580
Insulation of coil windings	Class H according to IEC 85
Connection	Terminal box
Enclosure, IEC 529	IP67
Duty rating	Continuous
Plug type	Terminal box

2.6.1 Dimensions and weight

Figure 13: BG, High performance coils






Table 18: BG, High performance coils

Туре	L with terminal box [mm]	Weight [kg]
BG	112	0.50

2.7 BN, High performance coils Hum-free

Figure 14: BN, High performance coils



Features

- Hum-free
- Enclosure: IP67 for moist environments with flying lead
- In accordance with:
- RoHS Directive 2011/65/EU
- Low Voltage Directive 2014/35/EU
 - EN60730-1
 - EN60730-2-8

Table 19: BN, High performance coils

Туре	Tambient	Supply voltage	Voltage variation		Power cons	sumption	Code no.
	[°C]	[V]		[Hz]	[W]	[VA]	
BN230CS	-40 - 50	220 – 230	±10%	50	22	24	018F7301
		220 – 230	±10%	60	22	24	

Table 20: Technical data

Design	In accordance with VDE 0580
Insulation of coil windings	Class H according to IEC 85
Connection	1 m 3-core flying lead
Enclosure, IEC 529	IP67
Duty rating	Continuous

2.7.1 Dimensions and weight

Figure 15: BN, High performance coils Hum-free






Table 21: BN, High performance coils

Туре	L with 1m cable [mm]	Weight [kg]
BN	112	0.60

2.8 BN, High performance coils Center boss

Figure 16: BN, High performance coils



Features

- Enclosure:
- Center boss for mounting IP65/IP67 cable plug in accordance with DIN43650 form A
- IP65/IP67 for moist environments with terminal box
- Used with EV215B, EV225B, and EV245B up to 160 °C low pressure steam and max. ambient temperature 40 °C (see additional information in the respective solenoid valve data sheets)
- In accordance with:
- RoHS Directive 2011/65/EU
- Low Voltage Directive 2014/35/EU
 - EN60730-1
 - EN60730-2-8
- Mounted with the solenoid valves EV210B, EV220B, EV215B and EV225B, the assembly is UL recognized

Table 22: BN, High performance coils Center boss

Turne	Tambient	Supply voltage	oltage Voltage varia- Frequency Power consumption		امتحدم	Code no.		
Туре	[°C]	[v]	tion	[Hz]	[W]	[VA]	Approval	code no.
BN024DS	-40 – 50	24	±10%	DC	20	-	c FN [®] us	018F6968

Table 23: Technical data

Design	In accordance with VDE 0580
Insulation of coil windings	Class H according to IEC 85
Connection	Cable plug in accordance with DIN43650 form A or terminal box
Enclosure, IEC 529	IP65, IP67
Duty rating	Continuous



2.8.1 Dimensions and weight






Table 24: BN, High performance coils Center boss

Туре	L [mm]	Weight [kg]
BN	64	0.47

2.9 BO, High performance coils

Figure 18: BO, High performance coils



Features

- ATEX Zone 1
- Enclosure: IP67 seal kit for moist environment included
- Approved in accordance with:
- ATEX 2014/34/EU
- Ex mb IIC T4 Gb
- ° ITS 09 ATEX 16835X
- Media temperature: Up to 90 °C

Table 25: BO, High performance coils

Turno	Tambient	Supply voltage	Voltage variation	Frequency	Power cor	nsumption	Code no.
Туре	[°C]	[V]	voltage variation	[Hz]	[W]	[VA]	Coue no.
BO024C	-40 - 60	24	±10%	50 / 60	10	21	018Z6595
BO110C	-40 - 60	110	±10%	50 / 60	10	21	018Z6593
BO230C	-40 - 60	230	±10%	50 / 60	10	21	018Z6592
BO240C	-40 - 60	240	±10%	50 / 60	10	21	018Z6591
BO024D	-40 – k60	24	±10%	DC	10	-	018Z6596

Table 26: Technical data

Insulation of coil windings	Class H according to IEC 85
Connection	5 m 3 x 0.75 mm ² flexible cord
Enclosure, IEC 529	IP67 including seal kit
Media temperature	-40 °C – 90 °C
Duty rating	Continuous



Solenoid coils, type BA, BD, BB, BE, BF, BG, BN, BO, BJ, BX, BY, BQ, AM, AS, AZ and AP

Humidity	0 – 100%
Pollution degree	3 (EN60730-1)
Impulse withstand voltage	2.5 kV (EN60730-1)

Table 27: Accessory

Description	Application	Code no.
Seal kit (included as standard)	Wet environment (pollution degree 3)	018Z0090

2.9.1 Dimensions and weight

Figure 19: BO, High performance coils




Table 28: BO, High performance coils

Туре	L [mm]	Weight [kg]
BO	125	0.60

2.10 BJ, High performance coils Junction box

Figure 20: BJ, High performance coils



Features

- Enclosure: IP30 / NEMA 2
- For UL listed valves (UL 429 and CSA)
- Ambient temperature: Up to 50 °C / 122 °F
- Media temperature: Up to 185 °C / 364 °F steam

Table 29: BJ, High performance coils

Valvetype Coiltype 5	Voltage toler-	Supply voltage [V]	Frequency [Hz]	Power con- sumption [W]	Wire length			
	ance				[in.]	[cm]	Code no.	
	BJ024CS	±10%	24	50 / 60	14	7	18	018F4100
EV220B 6-50 EV210B	BJ120CS	±10%	110	50 / 60	16	7	18	018F4110
EV215B	65120C3	5J120C5 ±10%	120	60	15			
EV225B EV250B	EV225B		208 - 240	60	14	7	10	01054120
EV250B BJ240CS	±10%	230	50	17	/	18	018F4120	

Table 30: Technical data

Design	In accordance with UL 429
Power consumption, cut in	49 VA
Insulation of coil windings	Class H according to IEC 85



Solenoid coils, type BA, BD, BB, BE, BF, BG, BN, BO, BJ, BX, BY, BQ, AM, AS, AZ and AP

Connection	Junction box
Enclosure, IEC 529	Junction box NEMA 2 ~ IP12 – 30
Ambient temperature	-40 – 50 °C / -40 – 122 °F

2.10.1 Dimensions and weight

Figure 21: BJ, High performance coils Junction box




Table 31: BJ, High performance coils Junction box

Туре	L [mm]	Weight [kg]
BJ	100	0.39

2.11 BX, High performance coils Conduit hub

Figure 22: BX, High performance coils



Features

- Enclosure: IP54 / NEMA 4
- For UL listed valves (UL 429 and CSA)
- Ambient temperature: Up to 50 °C / 122 °F
- Media temperature: Up to 185 °C / 364 °F steam

Table 32: BX, High performance coils

Valve type Coil type		Voltage toler- Supply	Supply voltage	Supply voltage Frequency	Power con-	Wire length											
	Coil type	ance	[V]	[Hz]	sumption [W]	[in.]	[cm]	Code no.									
	BX024CS	±10%	24	50 / 60	14	18	46	018F4102									
	BX024CS	±10%	24	50 / 60	14	71	180	018F4103									
EV220B 6-50	BX024CS	±10%	24	50 / 60	14	98	250	018F4104									
EV220B 6-50 EV210B	BX120CS	±10%				18	46	018F4112									
EV215B	BX120CS	±10%	110 120										50 / 60	16	36	91	018F4113
EV225B EV250B	BX120CS	±10%											120	120	120	120	120 60
EV250B	BX120CS	±10%						98	250	018F4115							
	BX240CS	±10%	208 - 240	60	14	18	46	018F4122									
	BX240CS	±10%	230	50	17	98	250	018F4123									



Table 33: Technical data	
Design	In accordance with UL 429
Power consumption, cut in	49 VA
Insulation of coil windings	Class H according to IEC 85
Connection	Conduit hub
Enclosure, IEC 529	Conduit hub NEMA 4 ~ IP54
Ambient temperature	-40 – 50 °C / -40 – 122 °F

2.11.1 Dimensions and weight

Figure 23: BX, High performance coils Conduit hub




Table 34: BX, High performance coils Conduit hub

Туре	L [mm]	Weight [kg]
ВХ	74	0.33

2.12 BY, High performance coils

Figure 24: BY, High performance coils



Features

- Enclosure:
- IP00 version with DIN 43650 A spade connectors
- IP20 version with protective cap
- \circ $\,$ IP65/IP67 version with mounted cable plug $\,$
- For UL recognised valves c Sus
- In accordance with:
- RoHS Directive 2011/65/EU
- Low Voltage Directive 2014/35/EU

Danfoss

- EN60730-1
- EN60730-2-8

Table 35: BY, High performance coils

Туре	Tambient	Supply voltage Voltage varia-	Voltage varia-	Frequency	Power consumption		Approval	Code no.
туре	[° C]	[v]	tion	[Hz]	[W]	[VA]		code no.
	10 50	24	±10%	50	14	26	c SL °us	018F7655
BY024CS	-40 – 50	24	±10%	60	12	21		
		230	±10%	50	16	32		
BY240CS	BY240CS -40 – 50	208 - 240	±10%	60	14	28	c FL us	018F7658
		110	±10%	50	14	27		
BY120BS	-40 – 50	-40 – 50 110 – 120	±10%	60	14	27	c 🐴 us	018F7663

Table 36: Technical data

Design	In accordance with VDE 0580
Insulation of coil windings	Class H according to IEC 85
Connection	Spade connector in accordance with DIN 43650 form A
Enclosure, IEC 529	Up to IP65 / NEMA 4
Plug type	Cable plug (042N1256)

2.12.1 Dimensions and weight

Figure 25: BY, High performance coils




Table 37: BY, High performance coils

Туре	L without cable plug [mm]	L with protective cap [mm]	L with cable plug [mm]	Weight [kg]
BY	62	77	85	0.24

2.13 BQ, High performance coils

Figure 26: BQ, High performance coils



Features

Enclosure:



- IP00 version with DIN 43650 A spade connectors
- IP20 version with protective cap
- IP65/IP67 version with mounted cable plug
- Max. media temperature: 185 °C steam
- For UL recognised valves c UL recognised
- In accordance with:
 - RoHS Directive 2011/65/EU
 - Low Voltage Directive 2014/35/EU
 - EN60730-1
 - EN60730-2-8

Table 38: BQ, High performance coils

Туре	Tambient	Supply voltage [V]	Voltage varia-	Frequency	Power consumption		Approval	Code no.
туре	[° C]		tion	[Hz]	[W]	[VA]		code no.
		24	-15%, 10%	50	10	17	c FN [®] us	018F4517
BQ024CS	-40 – 40	24	-15%, 10%	60	9	16		
BQ120BS	-40 - 40	110/120	-15%, 6%	60	13.5	19	c SN [®] us	018F4519
		230	-15%, 6%	50	10	17	c SV [®] us	018F4511
BQ240CS	-40 - 40	208 / 240	-6%, 6%	60	9.5	16		
BQ220BS	-40 - 40	220	-15%, 6%	60	12	19		018F4520

Table 39: Technical data

Design	In accordance with VDE 0580
Insulation of coil windings	Class H according to IEC 85
Connection	Spade connector in accordance with DIN 43650 form A
Enclosure, IEC 529	Up to IP65 / NEMA 4
Plug type	Cable plug (042N1256)

2.13.1 Dimensions and weight

Figure 27: BQ, High performance coils




Table 40: BQ, High performance coils

Туре	L without cable plug	L with protective cap	L with cable plug	Weight
	[mm]	[mm]	[mm]	[kg]
BY	62	77	85	0.24



<u>2.14 AM coil</u>

Figure 28: AM coi



Features

- Cable plug enclosure:
 - IP00 version with DIN 43650 A spade connectors
- IP20 version with protective cap
- IP65/IP67 version with cable plug
- In accordance with:
 - RoHS Directive 2011/65/EU
 - Low Voltage Directive 2014/35/EU
 - EN60730-1
 - EN60730-2-8

Table 41: AM coil

Turne	Tambient	Tambient Supply voltage		oltage variation Frequency	Power con	Code no.	
Туре	[°C]	[V]	voltage variation	[Hz]	[W]	[VA]	Coue no.
AM024C	-40 – 50	24	±10%	60	5.5	11	042N0842
AIWI024C	-40 - 50	24	±10%	50	7.5	14	042110842
AM110C	-40 – 50	110	±10%	60	5.5	11	042N0845
AMITTOC	-40 - 30	110	±10%	50	7.5	14	042100845
AM230C	-40 – 50	230	±10%	60	6.5	13	042N0840
AM250C	-40 - 50	230	±10%	50	9.5	18	042110840
AM240C	-40 – 50	240	±10%	60	5.5	11	042N0841
AM240C	AM240C -40 - 50	240	±10%	50	7.5	15	042100841
AM012D	-40 - 50	12	±10%	DC	8.5	-	042N0848
AM024D	-40 - 50	24	±10%	DC	9	-	042N0843

Table 42: Technical data

Design	In accordance with VDE 0580
Power consumption, cut in	22.5 VA AC coils only
Insulation of coil windings	Class H according to IEC 85
Connection	Spade connector in accordance with DIN 43650 form A
Enclosure, IEC 529	IP00 with spade connector, IP65 with cable plug
Duty rating	Continuous
Plug type	Cable plug (042N1256)



2.14.1 Dimensions and weight

Figure 29: AM coil




Table 43: AM coil

Туре	L without cable plug	L with cable plug	L with protective cap	Weight
	[mm]	[mm]	[mm]	[kg]
AM	48	72	64	0.10

2.15 AP, Compact UL recognised coils

Figure 30: AP Coil



Features

- Cable plug enclosure:
 - IP00 version with DIN 43650 A spade connectors
- IP20 version with protective cap
- IP65/IP67 version with cable plug
- For UL recognised valves
- Ambient temperature: Up to 50 °C / 122 °F
- In accordance with:
- RoHS Directive 2011/65/EU
- Low Voltage Directive 2014/35/EU
 - EN60730-1
 - EN60730-2-8

Table 44: AP, Compact UL recognised coils

Туре	Tambient	Supply voltage	Voltage varia-		Power consumption		Approval	Code no.
туре	[°C / °F]	[V]	tion		[W]	[VA]		coue no.
	-40 – 50 / -40 –	208 – 240	±10%	60	5.5	11		042N4291
AP240C	122	230		50	7.5	15	c FL us	
AP120B	-40 – 50 / -40 – 122	110 – 120	±10%	60	5	11	c FL [®] us	042N4292
AP024B	-40 – 50 / -40 – 122	24	±10%	60	5	11		042N4293

Table 45: Technical data

Design	In accordance with VDE 0580
Insulation of coil windings	Class H according to IEC 85
Connection	Spade connector in accordance with DIN 43650 form A
Enclosure, IEC 529	IP00 with spade connector, IP65 / NEMA 2 with cable plug
Duty rating	Continuous
Plug type	Cable plug (042N1256)

2.15.1 Dimensions and weight

Figure 31: AP, Compact UL recognised coils






Table 46: AP, Compact UL recognised coils

Туре	L without cable plug	L with cable plug	L with protective cap	Weight
	[mm]	[mm]	[mm]	[kg]
AP	48	72	64	0.10

2.16 AS/AZ, Compact UL recognised clip-on coils

Figure 32: AS/AZ Coil



Features

- Cable plug enclosure:
- IP00 version with DIN 43650 A spade connectors
- IP20 version with protective cap
- IP65/IP67 version with cable plug
- Ambient temperature: Up to 50 °C / 122 °F
- In accordance with:
 - RoHS Directive 2011/65/EU
 - Low Voltage Directive 2014/35/EU
 - EN60730-1
 - EN60730-2-8
- UL recognized CNUs

Table 47: AS/AZ, Compact UL recognised clip-on coils

Туре	Tambient	Supply voltage	Voltage varia-	Frequency	Power cor	sumption	Approval	Code no.
туре	[°C / °F]	[V]	[V] tion [H:	[Hz]	[W]	[VA]	Approvai	code no.
1000100	-40 - 50 / -40 -	24		50	9.5	18		0.0017400
AS024CS	122	24	-10%, +6%	60	7.0	14	c FL us	042N7608
	-40 - 50 / -40 -	230	-10%, +6%	50	8.0	16	~~\	
AS230CS	122	208 - 240	±6%	60	7.0	14	c FL us	042N7601
AZ012DS	-40 – 50 / -40 – 122	12	-10%, +6%	DC	6.0	-	c FN [®] us	042N7616
AZ024DS	-40 – 50 / -40 – 122	24	-10%, +6%	DC	6.5	-	c FN [®] us	042N7617

Table 48: Technical data

Design	In accordance with UL 429
Insulation of coil windings	Class H according to IEC 85
Connection	Spade connector in accordance with DIN 43650 form A
Enclosure, IEC 529	IP00 with spade connector, IP65 / IP67 with cable plug
Duty rating	Continuous
Plug type	Cable plug (042N1256)



2.16.1 Dimensions and weight




Table 49: AS/AZ, Compact UL recognised clip-on coils

Туре	L without cable plug	L with cable plug	L with protective cap	Weight
	[mm]	[mm]	[mm]	[kg]
AS/AZ	48	72	64	0.10

2.17 Cable plug

Figure 34: Cable plug



Features

- Enclosure: IP67 / NEMA 4X
- For use with Danfoss coils type AL, AM, AS, AZ, BA, BB, BD, BN (Center boss), BQ, and BY
- AC / DC all voltages up to 250 V
- In accordance with:
- RoHS 2011/65/EU
- LVD 2014/35/EU




- Design according to:
- Flammability
 - UL94 V0
 - IEC 60695-11-5

Table 50: DIN 18

Cable plug size	Description	Code no.
DIN 18	Cable plug IP67	042N1256

Figure 35: Pin





Solenoid coils, type BA, BD, BB, BE, BF, BG, BN, BO, BJ, BX, BY, BQ, AM, AS, AZ and AP

Table 51: Technical data			
Туре	Cable plug with Danfoss logo		
Design	EN 175301-803 Form A		
Cable gland	Ext. thread diameter range 4-9 mm		
Poles	2+1 (Earth)		
Max. voltage	250 V AC / DC		
Enclosure	IP67 (IEC 60529)		
Max. operating current	16 A		
Contact resistance	≤ 15 mΩ		
Cable diameter	Ø 4 - 9 mm		
Wire cross section	Max. 1.5 mm ²		
Ambient temperature	-40 - 125 °C / -40 - 257 °F		
	Housing	PA66 GF (Polymide)	
Materials	Terminal block	PA66 GF (Polymide)	
	Profiled gasket	Silicone	

2.17.1 Dimensions and weight

Figure 36: Cable plug




Table 52: Cable plug

Туре	Weight [kg / lbs]
Cable plug	0.026 / 0.057

2.18 Cable plug

Figure 37: Cable plug



Features

- Enclosure: IP65 / NEMA 4
- For use with Danfoss coils type AL, AM, AS, AZ, BA, BB, BD, BN (Center boss), BQ, and BY
- AC / DC all voltages up to 250 V
- In accordance with:
- RoHS 2011/65/EU
- LVD 2014/35/EU



- Design according to:
- Flammability



- UL94 V0
- IEC 60695-11-5

Table 53: DIN 18

Table 53: DIN 18		
Cable plug size	Description	Code no.
DIN 18	Cable plug IP65	042N1278
Figure 38: Pin		
•(
Table 54: Technical data		
Туре	Cable plug with Danfoss logo	
Design	EN 175301-803 Form A	
Cable gland	PC 0	

Design	EN 175301-803 Form A		
Cable gland	PG 9		
Poles	2+1 (Earth)		
Max. voltage	250 V AC / DC		
Enclosure	IP65 (IEC 60529)		
Max. operating current	16 A		
Contact resistance	≤ 15 mΩ		
Cable diameter	Ø 6 - 8 mm		
Wire cross section	Max. 1.5 mm ²		
Ambient temperature	-40 - 90°C / -40 - 194°F		
	Housing	PA66 GF (Polymide)	
Materials	Terminal block	PA66 GF (Polymide)	
	Profiled gasket	NBR	

2.18.1 Dimensions and weight




Table 55: Cable plug

Туре	Weight [kg / lbs]
Cable plug	0.031 / 0.067

2.19 Industrial plug

Figure 40: Industrial plug



Features

- Enclosure: Up to IP65
- For use with Danfoss coils type AB and AC
- AC / DC all voltages up to 250 V
- Approved in accordance with:



• CSA

Table 56: DIN 11

Industrial plug size	Description	Suitable for coil types	Code no.
DIN 11	Cable plug for 6.3 x 0.8 mm spade con- nectors	AB, AC	042N0139

Figure 41: Pin




Table 57: Technical data

Туре	GM 209 J (Black)		
Design	DIN 43650-B		
Cable gland	PG 9		
Poles	2 + PE		
Max. voltage	250 V AC / DC		
Enclosure	IP65 (IEC 60529)		
Max. operating current	16 A		
Contact resistance	< 10m Ω		
Cable diameter	Ø4.5 – 7 mm		
Wire cross section	Max. 1.5 mm ²		
Ambient temperature	-30 – 90 °C / -22 – 194 °F		
	Contacts:	CuSn (Tin plated)	
Materials	Terminal block:	PA 6 GF	
Materials	Flat gasket:	NBR	
	Housing:	PA 6 GF	



2.19.1 Dimensions and weight

Figure 42: Industrial plug




Table 58: Industrial plug

Туре	Weight [kg / lbs]
Industrial plug	0.023 / 0.050

2.20 Cable plug (LED + Varistor)

Figure 43: Cable plug



Features

- Enclosure: Up to IP65
- For use with Danfoss coils type AM, AK, AL, AS, AZ, BA, BD, BB, and BY
- 24 V AC / DC and 230 V AC version
- DIN 18
- Approved in accordance with: CSA
- In accordance with:
- RoHS 2011/65/EU
- LVD 2014/35/EU

Table 59: DIN 18

Industrial plug	Volt	Voltage		Suitable for coil	LED colour	Built-in VDR ⁽¹⁾ re-	Code no.
size	[V AC]	[V DC]	Voltage variation	types		sistor	Coue no.
DIN 18	24	24	±10%	AM, AL, AS, AZ, BA, BB, BD, BY	Red	Yes	042N0263
DIN 18	230	-	±10%	AM, AL, AS, AZ, BA, BB, BD, BY	Red	Yes	042N0265

⁽¹⁾ Protects against voltage peaks

Danfoss

Figure 44:




Table 60: Technical data

Design	EN 175301-803 A		
Power consumption	Max. 5 mA		
Approval	CSA		
Enclosure	IP65 (IEC 60529)		
Max. operating current	1.5 A clamping contact		
Contact resistance	$\leq 4m \Omega$		
Protection against wrong polarity	Yes		
Cable diameter	6 – 8 mm and 8 – 10 mm		
Wire cross section	Max. 1.5 mm ²		
Ambient temperature	-25 – 60 °C / -13 – 140 °F		
	Contacts:	CuZn, Cu/Sn-plated	
	Terminal block:	PA6 + 30% FG, black	
Materials	Flat gasket:	NBR LABS-fre	
	Housing:	PA6	
	Wire holder:	PA6.6 + 50% FG P7,5 black	

2.20.1 Dimensions and weight

Figure 45: Cable plug (LED + Varistor)




Table 61: Cable plug (LED + Varistor)

Туре	Weight [kg / lbs]
Cable plug (LED + Varistor)	0.027 / 0.059

2.21 Industrial plug (LED + Varistor)

Figure 46: Industrial plug



Features

- Enclosure: Up to IP65
- For use with Danfoss coils type AB and AC
- 24 V AC
- Approved in accordance with: CSA
- In accordance with:
- ° RoHS 2011/65/EU
- ° LVD 2014/35/EU

Table 62: DIN 11

Industrial plug size	Volt	tage	Suitable for coil	LED colour	Built-in VDR ⁽¹⁾ resis-	Code no.
industrial plug size	[V AC]	[V DC]	types		tor Code no.	
DIN 11	24	24	AB, AC	Red	Yes	042N0267

⁽¹⁾ Protects against voltage peaks.

Figure 47:




Table 63: Technical data

Design	Industrial form		
Supply voltage variation	±10%		
Power consumption	Max. 5 mA		
Approval	CSA		
Enclosure	IP65 (IEC 60529)		
Max. operating current	1.5 A clamping contact		
Contact resistance	$\leq 4m \Omega$		
Protection against wrong polarity	Yes		
Cable diameter	5 – 6 mm and 6 – 9 mm		
Wire cross section	Max. 1 mm ²		
Ambient temperature	-25 – 60 °C / -13 – 140 °F		
	Contacts:	CuZn, Cu/Sn-plated	
	Terminal block:	PA6 + 30% FG, black	
Materials	Flat gasket:	NBR LABS-fre	
	Housing:	PA6	
	Wire holder:	PA6.6 + 50% FG P7,5 black	



2.21.1 Dimensions and weight

Figure 48: Industrial plug (LED + Varistor)




Table 64: Industrial plug (LED + Varistor)

Туре	Weight [kg / lbs]	
Industrial plug (LED + Varistor)	0.027 / 0.059	

2.22 Universal electronic multi-timer Type ET 20 M

Figure 49: ET 20 M



Features

- Outside adjustments
- Light weight and small size
- External adjustable timing from 1 minute to 45 minutes with 1 to 15 seconds drain open
- One solid state timer fits all coil voltages from 24 240 V AC
- Light diodes for indication
- All in one unit
- Manual override (test button)

Table 65: BA024A

Туре	Voltage [V]	Suitable for coil types	Code no.
BA024A	24 – 240	AL, AM, AS, AZ, BA, BD, BB	042N0185



Solenoid coils, type BA, BD, BB, BE, BF, BG, BN, BO, BJ, BX, BY, BQ, AM, AS, AZ and AP

Table 66: Technical data

Туре	ET 20 M
Voltage	24 – 240 V AC / 50 – 60 Hz
Power rating	Max. 20 W
Enclosure	IP00, IP65 with cable plug
Electrical connection	DIN connector (DIN 43650-A)
Ambient operating temperature range	-10 – 50 °C
Function	Start with pulse
Interval timer	0 – 45 min.
"On" timer	0 – 15 sec.

2.22.1 Dimensions and weight




Figure 50: Universal electronic multi-timer Type ET 20 M

3 Online support

Danfoss offers a wide range of support along with our products, including digital product information, software, mobile apps, and expert guidance. See the possibilities below.

The Danfoss Product Store



The Danfoss Product Store is your one-stop shop for everything product related—no matter where you are in the world or what area of the cooling industry you work in. Get quick access to essential information like product specs, code numbers, technical documentation, certifications, accessories, and more.

Start browsing at store.danfoss.com.

Find technical documentation



Find the technical documentation you need to get your project up and running. Get direct access to our official collection of data sheets, certificates and declarations, manuals and guides, 3D models and drawings, case stories, brochures, and much more.

Start searching now at www.danfoss.com/en/service-and-support/documentation.

Danfoss Learning



Danfoss Learning is a free online learning platform. It features courses and materials specifically designed to help engineers, installers, service technicians, and wholesalers better understand the products, applications, industry topics, and trends that will help you do your job better.

Create your Danfoss Learning account for free at www.danfoss.com/en/service-and-support/learning.

Get local information and support



Local Danfoss websites are the main sources for help and information about our company and products. Find product availability, get the latest regional news, or connect with a nearby expert—all in your own language.

Find your local Danfoss website here: www.danfoss.com/en/choose-region.

Spare Parts



Get access to the Danfoss spare parts and service kit catalog right from your smartphone. The app contains a wide range of components for air conditioning and refrigeration applications, such as valves, strainers, pressure switches, and sensors.

Download the Spare Parts app for free at www.danfoss.com/en/service-and-support/downloads.

Danfoss A/S

Climate Solutions • danfoss.com • +45 7488 2222

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues descriptions, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the product. All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.

Danfoss

ENGINEERING TOMORROW