



Sports Field Heating

Application manual



Index

1. Sports field heating	4
2. System Description	5
3. System Design	8
4. Installation	11
5. Cases References	15
6. Cases	16

Our quality management system **certifications and compliances**

- ✓ ISO 9001
- ✓ TS 16949
- ✓ ISO 14001

Along with full compliance with EU directives and product approvals

Let DEVI do the work

DEVI - an abbreviation of Dansk El-Varme Industri - was established in Copenhagen, Denmark, in 1942. As from January 1st 2003 DEVI has become a part of the Danfoss Group - Denmark's largest industrial Group. Danfoss is one of the world's leading companies within heating, cooling and air-conditioning. The Danfoss Group has more than 23.000 employees and serves customers in more than 100 countries.

DEVI is Europe's leading brand of electrical cable heating systems and electric pipe heating systems with over 70 years of experience. The production of heating cables takes place in France and Poland while the head office is situated in Denmark.

Natural grass lawns

This design guide presents DEVI's recommendations for design and installation of ice and snow melting systems for sport field heating application. It provides guidance for heating cable positioning, electrical data and system configurations.

Following DEVI's recommendations will ensure energy efficient, reliable and maintenance free solution for constant wattage heating cables with 20 year warranty.



1. Sports field heating

For professional and international stadiums a very high standard of playing surface is required. Under these circumstances it is important to eliminate risks of poor playing conditions or cancellation, particularly associated with poor weather conditions, e.g. heavy rainfalls or ice and snow.

According to the FIFA's Technical recommendations and requirements, 5th edition (paragraph 4.2): "(...) In cold climates, the playing field should be equipped with an underground heating system to prevent it from freezing in extreme winter conditions. (...)"

In some leagues, the undersoil heating is already a standard, e.g. in the first and second Bundesliga (DFB) in Germany.

Benefits

- **Keeps the pitch frost free** – prolonging pitch usage during the autumn season
- **Defreeze the pitch after a winter break** – increasing pitch quality and making it playable earlier
- **Reducing financial risks** – caused by postponing games due to poor weather conditions
- **Increasing safety** – helps to reduce injuries
- **Increasing usage** – helps to recover natural grass after heavy usage faster
- **International standards** – DEVI heating system is bringing football pitch in line with FIFA's Technical recommendations and requirements
- **Affordable solution** - initial investment of 50% below cost of hydronic systems
- **Quick Installation time** of 4 weeks (or less), to make pitch playable again – all games meet the schedule and no need to close a stadium for long renovation
- **Maintenance free** – no need to change anything during the warranty period, vs. Glycol in hydronic systems which has to be replaced after 2 years (app. 8000 liters; depending on the field size)
- **Reliable system** – 20 years of warranty on DEVI heating cables for natural grass pitches
- **Experienced supplier** – DEVI has been involved in football field heating since 1995. DEVI electric heating solutions installed in football fields, golf courses, cricket fields both under Natural. Within the past 20 years our systems have been installed in over 40 playing fields.


2. System Description

Pitch heating is keeping the ground temperature at appropriate level and helps to maintain good quality of pitch during the whole season.

DEVI offers a wide variety of heating cables and thermostats for installation in football fields, golf courses, cricket fields, and other play grounds where any kind of sport activities takes place.

Installation of DEVI heating cables in natural turf ensures grass growth and helps to prolong pitch usage by several months.

For bigger stadiums the appropriate power needed to operate cables can be easily achieved. Normally the night light systems are operated only when the field is in use. It is simple to modify the wiring to provide the desired power for heating cables at the moment when the night light system is switched off.



Steady state at -5 °C ambient air temperature:

- +3 °C is evenly distributed in turf
- 89% of heat is going up
- Cable temperature is approx. 20 °C

Benefits


- For new construction and renovation of pitches
- Approx. 2 weeks from installation start to make the pitch playable again
- Keeps the pitch frost free during winter
- Defreezes the pitch after a winter break
- Stimulates grass growth in cold weather conditions

2.1 Frost heave prevention system

The heating elements installed just below the grass root zone together with temperature sensors must be controlled by a thermostat. The root zone's temperature should be maintained in the range of 10...18 °C (in each case the temperature level should be determined by an agricultural engineer of the sport field in question).

Temperature maintenance of the soil around the grass roots ensures grass growth and prolongs the field usage by 3-4 months per year. In spring the pitch will be ready up to two months earlier than usual. Furthermore, the playing season can be prolonged in autumn when the period, until the grass stops growing, can be extended by means of roots heating regardless the geographic location.

DEVI heating cables can be installed both when the grass is placed and when the grass is renewed. The latter takes place by laying heating cables directly in the ground. The grass area must be levelled and appropriate drainage is ensured.



2.2 Product Selection

Heating cables

DEVIsport™ for natural grass field. Robust cable and resistive heating cable can be also used for plough installations. DEVI provides 20 year warranty. Manufactured in EU.

The DEVIsport™ single conductor heating cable of high mechanical strength against both pulling and deformation (1500 N) making it ideal for installation with specialized cable ploughs.

The DEVIsport™ can be customized to any specific project, with regards to the pitch size, voltage level, required output and length of cold leads.

For a new pitch construction the heating system may include the following resistive heating cables:

- Single conductor DEVIbasic™ 20S, DEVIbasic™ on drum,
- Twin conductor DEVIsnow™ 20T.



Thermostats

Regulation can be provided by means of DEVIreg™ 330 (5...45 °C) thermostats with an external sensor installed in the ground at the same depth as the heating element and as close to grass roots as possible.

Regulation can also be provided "on-site" by means of already existing temperature measuring devices.

DEVIreg™ 330 (5...45 °C) thermostats have a full set of functions to control any heating system for natural grass, and allow for attachment of external sensors for ground temperature measuring.

Accessories:

DEVIfast™ Metal - galvanized metal band for cable.



Products - general overview of Sport fields heating

Product	Options	Description
Resistive heating cable DEVIsport™	DEVIsport™ on drum 400 V, 0,04-8 Ohm/m	Single conductor, screen, black. Max. 30 W/m, max. 400 V. IEC60800:1992 M2, NF-C 32-330.
Resistive heating cable DEVIbasic™ 20S	DEVIbasic™ 20S, 230 V DEVIbasic™ 20S, 400 V	Single conductor, wire screen. 20 W/m (230 V/400 V). DIN IEC 60800:1992 C
Resistive heating cable DEVIbasic™	DEVIbasic™ on drum; 0,0134-34,1 Ohm/m	Single conductor, wire screen. Max 20 W/m; max. 400 V. DIN IEC 60800:1992 C
Constant wattage cable DEVIsnow™	DEVIsnow™ 20T 230V & 400V program	Twin conductor, 100% screen, UV stabilized, black. 20 W/m, (230 V/400 V), DIN IEC 60800: 2009 M2
DEVIreg™ Thermostat	DEVIreg™ 330 (5...45 °C)	5...45 °C, 16 A, IP20, DIN rail
Temperature sensor	10 m, PVC	Wire sensor, Ø8 mm, IP65, NTC 15 kOhm @25 °C
Fixing	DEVIfast™ Metal	25 m pack; galvanized metal, fixings every 2,5 cm. 100 pcs pack;

For details please refer to the DEVI Catalogue.

3. System Design

Considerations prior to design of a heating system

- Field type – Natural
- Project type – new construction or renovation
- Power supply availability – new or existing power supply from power transformers of the stadium lighting system
- Supply power – max. kW for heating and calculated max. output. W/m²
- Operating strategy – climatic conditions and possibility of operation during periods with low tariffs
- Drainage – no underground heating without drainage, as less water means less heating
- Size of the field – maximum size of grass areas
- Area conditions – permanently shadowed areas and a required number of zones
- Timing for installation – time available for installation
- Testing

Installed output

Normally the recommended installed output for heating natural grass fields is 80-100 W/m² with maximum limit of 120 W/m² depending on the geographic location.

In most cases for sport field heating it is used the power supply from existing transformers of the stadium lighting system. Maximum possible output of transformers of the lighting system is typically 400-800 kW and should be used as a limit for calculation of the field heating system.

For example, the transformers power of the lighting system is 600 kW. The football field size is 70 x 100 m or

7000 m². The max. possible output of the cable heating system per m² can be determined as follows:
 $600 \text{ kW} / 7000 \text{ m}^2 = 85 \text{ W/m}^2$.

Additionally for natural grass the maximum possible temperature of the root zone should be taken into account. Max. cable linear output and/or maximum heating system output can cause burning of grass roots. One of the alternative solution to avoid this problem is to install cable below the root zone, e.g. at a 30-35 cm depth.

Based on the above the recommended maximum output for the cable is 25 W/m and system output is up to 80-100 W/m².

Note. Output for sport field heating systems should be designed in accordance with the recommended values where possible.

Possible minimum working temperature

One of the main tasks of sport field heating systems is to defreeze the pitch just for an individual football game or support min +1 °C on the surface. When calculating rated output the lowest ambient air temperature at which the heating system ensures +1 °C on the surface shall be taken into account.

All in all for medium weather conditions in order to heat a 1 m² surface outside up to 1 °C approx. power of 23 Watt (see e.g. "Asphalt application. Ice and Snow Melting" Application manual) is needed. Otherwise the heat exchange coefficient - approx. 23 W/(m²·K) should be used for calculation.


The possible temperature difference between the surface and the air e.g. for installed 100 W/m² can be determined as follows:
 $100 \text{ W/m}^2 / 23 \text{ W/(m}^2 \cdot \text{K)} \approx 4 \text{ }^\circ\text{C}$.

To summarize - 100 W/m² ensures defreezing the pitch

surface under conditions of minimum air temperature up to minus 3 degrees: +1 °C - (+4 °C) = -3 °C.

Heating zones

The heating system and the field should be split in zones. Size and direction of the field areas which are permanently shadowed during winter are determined the required number of zones.



Minimum 4 zones are recommended. Application of more zones simplifies system design and control.

For each zone minimum one thermostat with a temperature sensor shall be used.

Depth of cable installation

According to the FIFA's Technical recommendations and requirements, 5th edition (paragraph 4.3) the installation depth of heating cables should be not less than 250 mm.

The heating cables should be installed 25-30 cm (up till 35 cm) below the surface to avoid cable damage due to the use of e. g. javelins.



The above output values ensure 6...10 °C temperature in the root zone, approx. 10 cm below the surface

In order to keep the soil warm and moist the area should be covered

with plastic or a similar material when it is not in use.

Local requirements for installation depth and possible mechanical protection for cold leads should be observed.

Insertion depth of objects like lawn aerators, vertidrain, spades, javelins, pegs, anchor bolts etc. should be taken into account.

Cable output and C-C distance

The heating cables with 15-25 W/m output, 230/400 V should be used for applications in grass areas.

The distance between the cables (C-C distance) naturally depends on the output per meter and the desired output per m², and is typically 15-25 cm.

Additionally to avoid cold gaps between heating cables the C-C distance should be equal or less than the cable installation depth.

Two formulas can be used for the C-C distance calculation:

or

The easiest way to calculate/evaluate the system output W/m² (heat density) is to multiply cable linear output by the number of cable lines per m².

For example if C-C distance is 21 cm and the cable output is 20 W/m the

$$C - C [cm] = \frac{Area [m^2]}{Cable length [m]} \cdot 100 \quad (1)$$

heating system output is determined

$$C - C [cm] = \frac{Cable output [W/m]}{Heat density [W/m^2]} \cdot 100 \quad (2)$$

as follows:

$$20 W/m \cdot (100 cm / 21 cm) \approx 95 W/m^2.$$

The table shows the C-C distances and corresponding outputs per m²:

C-C, cm	Cable linear output, W/m				
	16	18	20	22	24
15	107	120	133	147	160
16	100	113	125	138	150
17	94	106	118	129	141
18	89	100	111	122	133
19	84	95	105	116	126
20	80	90	100	110	120
21	76	86	95	105	114
22	73	82	91	100	109
23	70	78	87	96	104
24	67	75	83	92	100
25	64	72	80	88	96
26	62	69	77	85	92
27	59	67	74	81	89
28	57	64	71	79	86
29	55	62	69	76	83
30	53	60	67	73	80

Note. The recommended output range is 80-120 W/m² (black values in the table).

Cable length

For cable length calculation the position of an electrical connection box and the location of cable channel(s) – either along or across the field should be evaluated.

The DEVI sport™ heating cable on drum can be supplied with a specific Ohm/m value with regards to the pitch size, voltage, desired output, number of cable lines and length of cold leads.

Accurate calculation of the cable length is required to supply cable cold lead(s) to the end on the same side of the field and to optimize the electrical connection. Hence the number of lines of each cable should be even.

Most usual installation is 4 cable lines for each heating cable.

For example, if cables are supposed to be installed in 4 lines along the short side of 70 x 110 m football field, then the cable length should be 4 · 70 = 280 m. In case of cable installation along the long side of the field the cable length is 4 · 110 = 440 m. Please note

that the designed cable length shall provide the required Ohm/m value. If it is not possible - 2 cable lines should be chosen.

Sensor place

The sensor should be installed at the same level with the grass roots (in case of natural grass field) to ensure appropriate temperature.


It is recommended to use 2 sensors or 1 additional sensor for measuring average top soil temperature.

Cable trench

A special cable trench shall be designed.

Cold leads in a cable trench shall be designed with installation in 1 layer only (no bundling, no pipes).

It is recommended connection of cold leads and sensors in sealed junction boxes or cable wells, max. 20 m from each zone.



Start of heating

The heating system for Natural grass should be operated during 3-6 weeks before the start of the field use in spring.

This is required to ensure that the grass starts growing before the first match or training takes place. Failure to do so will result in fast destruction of the playing surface.

Calculation of cables on drum

A single conductor DEVI sport™ and DEVI basic™ heating cables are available on drums. In this case heating cables can be selected and calculated with any linear output (W/m), but not exceeding the max. value. As a result the length of a separate heating cable can be calculated based on the field size.

For example, standard Ohm/m values that are used for cables on drum for football fields are as follows:

DEVI sport™ - 0,04, 0,06, 0,085, 0,1, 0,15, 0,177 Ohm/m;

DEVI basic™ - 0,032, 0,05, 0,07, 0,1, 0,15, 0,187, 0,21 Ohm/m.

For details concerning Ohm/m values for cables on drum please refer to the DEVI Catalogue.

One more advantage is that the accurate length of heating cables can be ensured during installation. But it should be noted that cold tail joints and terminal connections should be performed by qualified personnel only. Ensure that proper type and size of cold tail and joints are selected.

For calculation of heating cables on drums the following formulas can be used:

$$L = U / \sqrt{p \cdot r}, \quad (3)$$

$$p = U^2 / (L^2 \cdot r), \quad (4)$$

$$r = U^2 / (L^2 \cdot p), \quad (5)$$

where

L – length of heating cable (m);

U – supply voltage (V);

p – linear output (W/m);

r – linear resistance (Ohm/m).

Example 1.

Calculation cable on drum

Football field size: 70 x 110 m, power supply: 380 V, max. power of the lighting system transformers: 800 kW. Field renovation with cable installation by plough.



Max. heating system output is $800 \text{ kW} / (70 \cdot 110) \text{ m}^2 = 103 \text{ W/m}^2$.

The cable trench is supposed to be arranged along the long side of the pitch and cable lines along the short side accordingly. Area for cable installation is e.g. 69,4 x 109,4 m (without 30 cm indents from the edges). A single conductor cable is supposed to be installed – in 4 lines with the C-C distance of 20 cm, the preliminary cable output is 20 W/m and the heating system output is $100/20 \cdot 20 \text{ W/m} = 100 \text{ W/m}^2$.

Cable length is $69,4 \text{ m} \cdot 4 = 277,6 \text{ m}$.

DEVI sport™ on drum is considered and an appropriate Ohm/m value should be chosen. According to formula (5) the calculated Ohm/m is determined as follows: $r = U^2 / (L^2 \cdot p) = 380^2 / (277,6^2 \cdot 20) = 0,094 \text{ Ohm/m}$.

According to the calculated 0,094 Ohm/m DEVI sport™ with 0,085 Ohm/m should be chosen (see DEVI sport™ data in the DEVI Catalogue).

Cable linear output in W/m should be checked with max. values for the chosen 0,085 Ohm/m.

Cable linear output according to formula (4) is determined as:

$$p = U^2 / (L^2 \cdot r) = 380^2 / (277,6^2 \cdot 0,085) = 22 \text{ W/m}.$$

Maximum W/m for DEVI sport™ is 30 W/m. So the chosen 277,6 m cable with 0,085 Ohm/m and 22 W/m output is correct.

For specified 100 W/m² C-C distance should be (formula (2)):

$$\text{C-C} = (22 \text{ W/m} / 100 \text{ W/m}^2) \cdot 100 \text{ cm} = 22 \text{ cm}$$

Cable with 22 W/m is correct for possible maximum of 104 W/m².

Number of heating cables:

$$109,4 \text{ m} / (0,22 \text{ m} \cdot 4) = 124 \text{ pcs.}$$

Cable output:

$$109,4 \text{ m} \cdot 22 \text{ W/m} = 5552 \text{ W}.$$

The calculation results are as follows:

- DEVI sport™ heating cable on drum;
- 277,6 m;
- 0,085 Ohm/m;
- 22 W/m;
- 124 pcs.;
- 100 W/m²;
- system output 688,5 kW;
- installation with 4 lines per cable;
- installation along the short side of the field.

4. Installation

Heating cables can be laid during the construction of a new or remodeling of an existing grass surface. Distance between the wires depends on the required heating power per square meter, and typically is about 15-25 cm.

DEVI is recommending installation on the depth of 25-30 cm (up to 35 cm), which protects the cable from damage by equipment used for reclamation of turf, posts and other.

Measure, verify and record element and insulation resistances during installation.

- After unpacking
- After fastening the elements
- After the installation is finalized.

4.1 Plowing in cables under natural grass

There is also the possibility of laying heating cables in the existing playing surface (turf). The installation is done using a special plough, on which there is a drum with a cable, which simultaneously cuts furrow and places in the heating cable at a required depth. Using the pitch is possible after about 10-12 days of laying the heating cable when the new grass cover traces of the passing plow.

For plough installation special heating cable with high level of pulling strength has to be used. DEVI sport™ is the only possibly choice for plowing in cables under natural grass.


Before installation of cable, field opposite edges are marked with paint showing distance between cable lines. After that a cord serving driver a checkpoint is pulled and fixed between marking.

A cable drum is placed on handling device. Cold lead (supply cord provided with the heating cable) unwinded manually from the drum, while heating cable is led to guiding mechanism. Tractor starts moving from the edge of the field simultaneously lowering handling device and mechanism of cable installation. When reaching the field's opposite side, the handling device rises, tractor turns around and process is repeated. While tractor's turning around, it's necessary to unwind cable from drum manually and rewind it on drum after the maneuver is performed.

After the ploughing prepare, cultivate the grass and make soil restoration with a road roller.

Time required for installation of one cable's 4 coils - 20 minutes. Thus, it will take approximately 2 weeks to install all the cables, for a standard size football field (disregarding days of bad, rainy weather).

Remained on the surface heating cable which wasn't embedded with handling device is placed into the necessary depth together with cold tails, manually.




After the ploughing prepare, cultivate the grass and make soil restoration with a road roller.




4.2 Electrical connection

To control the heating system recommended thermostats are DEVIreg™ 330 (5...45 °C) cooperating with the temperature sensor placed in the rooting zone of grass, about 25 cm below the surface.

It is recommended to divide the playing surface into several zones controlled by separate thermostats and sensors. It gives a possibility for division of connected power and optimizes the energy consumption, since the grass field is often subject to varied weather conditions like sun and cold temperature.



Example of installation of heating cables across a football field



4.3 Note when installing cables

Please refer to the installation manual for outdoor heating applications to comply with the relevant rules and regulations.

It is not recommended to install heating elements at temperatures below -5 °C. At low temperatures, heating elements can become rigid.

For safety reasons:

- Heating system should always be turned off, when the field is in use;
- Heating systems for sports fields must be made using screened electrical cables, and must have a power supply protected by a differential switch / residual current device (RCD) connected at all times.
- The screen of all heating elements must be grounded in accordance with applicable regulations.
- Max. tyre pressure on the surface not more than 1 kg/cm². If you have any doubts or questions regarding the installation or use of the application please contact DEVI for further information.

Notes

This image shows a single sheet of white paper with horizontal blue ruling lines. The lines are evenly spaced and run across the width of the page. There are no vertical margin lines or other markings present. The paper appears to be a standard sheet of notebook paper.

5. Cases References

Lokomotiv, Nizhniy Novgorod, Russia, 1996

Metalurg, Kryvyi Rig, Ukraine, 1999

Locomotive, Donetsk, Ukraine, 2003

FC "Vitebsk", Vitebsk, Belorussia, 2006

AC "Steaua Bucuresti", Ghencea, Romania mania, 2007



Stadion Most, Czech Republic, 2007

Amica Wronki, Poland, 2007



LKS, Łódź, Poland, 2007

Widzew Łódź, Poland, 2007

Odra Wodzisław Slaski, Poland, 2007

Ioan Moina, Romania, 2008

Municipal Stadium, Romania, 2008

Tehelné Pole Stadion, Slovakia, 2008

Stadion in Bratislava, Slovakia, 2008

Training pitch FC "Werder Bremen", Bremen, Germany, 2009

Constant Vanden Stock, Anderlecht, Belgium, 2009

Rhein Energie Stadion, Köln, Germany, 2010



Helsingin Olympiastadion, Helsinki, Finland, 2010

Silkeborg, Denmark, 2011

Otelul Stadium, Galati, Romania, 2011

Municipal Stadium "Gaz Metan", Medias, Romania, 2011

Ilie Oana Stadium, Ploiesti, Romania, 2011

Farum Park, Denmark, 2012

Zhetisu, Kazakhstan, 2012

Tineretului Stadium, Brasov, Romania, 2012

Municipal Stadium, Vaslui, Romania, 2012

Nicolae Dobrin Stadium, Pitesti, Romania, 2012

Marin Anastasovici Stadium, Giurgiu, Romania, 2012

Bilino polje Zenica, Bosnia and Hercegovina, 2012

Stavanger Gjesdal, Norway, 2013

Debrecen, Hungary, 2013

Telki, Hungary, 2013

Dacia Stadium, Mioveni, Romania, 2014

Municipal Stadium Botasani, Botosani, Romania, 2014

Ústí nad Labem, Czech Republic, 2014

Atatürk Stadium, Konya, Turkey, 2014



Fredrikstad Stadium, Norway, 2015

Atatürk Olympic Stadium, Istanbul, Turkey, 2015

6. Cases

RSCA ANDERLECHT STADIUM, Brussels, Belgium

Seed Beed Heating becomes mandatory in 2010 for stadiums in the Belgian First Division.

The RSC Anderlecht pitch is a semi synthetic field constructed in 2007. It is based on 90% sand and reinforced with 40 million PE fibers. The investment at that time for RSCA was already about 500 k€ so making a whole new pitch was not an option.

The electrical system was chosen as

- The cables could be installed retrofit with a special machine without damaging more than 3% of the PE fibers and the field was playable after 4 weeks.
- The power supply was already available, thus saving the cost, approval and operation of a 720 kW gasfired boiler.
- The control of the heating cables was included in the existing PLC control SMART EYE for irrigation and draining.

