ENGINEERING TOMORROW



**Data Sheet** 

# Pilot-operated servo valve Type **ICS**

65 bar/52 bar valves for controlling pressure, temperature and ON/OFF in refrigeration systems



ICS pilot-operated servo valves belong to the ICV (Industrial Control Valve) family.

The valve comprises three main components: valve body, function module and top cover.

ICS pilot-operated servo valves are pilot operated valves for regulating pressure, temperature and ON/OFF function in refrigeration systems. ICS valves are designed for low and high-pressure refrigerants.

The small sizes are designed for MWP of 65 bar, while large sizes have MWP of 52 bar.

ICS valves can be used on the high and lowpressure sides, in wet and dry suction lines and in liquid lines without phase change (i.e. where no expansion takes place in the valve).

The function of ICS valves is dependent on the pilot pressure applied from either a pilot valve or external pilot pressure source.

ICS 1 pilot has one pilot pressure connection and ICS 3 pilot has three pilot pressure connections.



#### **Features**

- Designed for industrial refrigeration applications for a maximum working pressure (MWP) of:
- ICS DN25 to DN65 (80): 65 bar / 943 psig.
  - **NOTE:** Operating valve MWP is dependent on MWP of installed pilots.
- $^{\circ}~$  ICS DN 100 to DN 150: 52 bar / 754 psig.
- Applicable to HCFC, HFC, R717 (Ammonia) and R744 (CO<sub>2</sub>).
- Direct coupled connections.
- Connection types include butt weld, socket weld, solder and threaded connections.
- Low temperature steel body.
- · Low weight and compact design.
- V-port regulating cone ensures optimum regulating accuracy particularly at part load.
- Function module has a QPQ surface treated insert and a steel piston ring ensuring precise control accuracy.
- ICV 4 in., 5 in. and 6 in. ANSI with NPT threaded pressure outlet in the outlet of the valve.
- Replaceable Teflon valve seat for ICS 25-80.
- Maintenance spare part kit available for ICS 100-150.
- Modular Concept:
- Each valve body is available with several different connection types and sizes.
- Valve overhaul on ICS 25-80 is done by replacing the function module.
- Possible to convert ICS pilot-operated servo valve to ICM motor operated valve.
- Manual opening.
- The ICS valve is a multifunction valve where several pilot valves can be mounted into the pilot ports.
- The standard range of pilot valves can be used on all sizes of ICS valves. Pilot valves can be either screwed directly into the ICS valve, thus eliminating the need for solder/weld connections or external pilot lines.
- Pressure gauge connection port to measure valve inlet pressure.
- The top cover can be rotated into any possible position without affecting the operation of the valve.
- To get an updated list of certification on the products please contact your local Danfoss Sales Company.



### **Functions**

Figure 1: ICS 1 Pilot





Figure 2: ICS 3 Pilots



### **ICS 1 Pilot and ICS 3 Pilot**

1	Body	3a	Cylinder
1a	Pilot channel to inlet side	3b	Piston
1b	Circular gap between house and module	3с	Valve plate
2	Top cover	3d	Spring
2a	Pilot channels in top cover	3e	Cone
2b	Pilot insertion hole	3f	Equalisation orifice
2c	Pressure gauge connection	3g	Piston rod
2d	Piston top inlet channel	p <sub>1</sub>	Inlet pressure
2e	Cross channel SI to SII	p <sub>2</sub>	Pressure on piston
2f	Inlet channel	p <sub>3</sub>	Pressure underneath piston
2g	Circular groove	p <sub>4</sub>	Outlet pressure
3	Function module	8	Manual operating spindle

The ICS main valve is a pilot operated valve. The types of pilot valves used determine the function. The ICS main valve with pilot valve(s) controls refrigerant flow by modulation or on/off in accordance with the pilot valve and main valve status. The manual spindle can be used to open the valve plate.

The opening degree of the main valve is determined by the pressure difference (differential pressure) between pressure  $p_2$ , which acts on top of the servo piston (3b), and pressure  $p_3$ , which acts on the underside of the servo piston.

If this pressure difference is 0, the main valve will be fully closed.



If the pressure difference is 0.2 bar (3 psi) or greater, the main valve will be fully open. At pressure differences ( $p_2$ - $p_3$ ) between 0.07 bar (1 psi) and 0.2 bar (3 psi), the degree of opening will be correspondingly proportional.

The port of the throttle cone (3e) is V-shaped, which provide good regulation characteristic to pilot operated main valves even at low loads.  $P_3$  pressure is equal to the valve outlet pressure ( $P_4$ ), due to a clearance between the piston rod (3g) and the function module. The opening degree of the ICS valve is therefore controlled by the application of  $P_2$  pressure acting on top of the servo piston, which is equal to or greater than valve outlet pressure ( $P_4$ ).

 $p_2 = p_4 \sim closed$   $p_2 = p_4 + 0.2$  bar (3 psi)~ fully open  $p_4 \le p_2 \le p_4 + 0.2$  bar (3 psi) ~ proportional degree of opening.

The maximum pressure ( $p_2$ ) can act on the top of the servo piston (3b).  $p_2$  normally corresponds to the pressure,  $p_1$  - ICS main valve inlet pressure. Inlet pressure  $p_1$  is led, via the drilled channels (1a, 1b, 2f, 2b (pilot), 2a, 2d) in the valve body (1) and cover (2) through the individual pilot valves and onto the top of the servo piston (3b).

The degree of opening of the individual pilot valves determines the magnitude of pressure  $p_2$  and thus the degree of opening of the main valve. The equalisation hole (3f) in the servo piston (3b) ensures that pressure  $p_2$  is balanced in accordance with the degree of opening of the pilot valve.

#### NOTE:

When ICS valves with 3 pilot ports are used with external pressure connector (Figure 2: ICS 3 Pilots, pos. 61), the valve port inlet pressure will be isolated.

The ICS can be fitted with just a single screwed-in pilot valve or external pilot connection. The degree of opening of the main valve will be in accordance with the control status of the pilot valve or external pilot flow control.

ICS main valve with one pilot connection is fully closed when the pilot valve is fully closed and fully open when the pilot valve is fully open. Otherwise the degree of opening of the main valve is proportional to the degree of opening of the pilot valve.

The ICS 3 pilot version can be fitted with one, two, or three pilot valves so that up to three regulating functions are possible. If the external pilot connection is used, more functions can be added.

In the ICS three pilot version, the pilot ports are related as follows:

- The pilot valves fitted in ports SI and SII are connected in series.
- The ICS 3 pilot operated main valve will be fully closed if just one of the series-connected pilot valves is closed. The main valve can only open if both pilot valves are open at the same time.
- The pilot valve fitted in port P is connected in parallel to the pilot valves in ports SI and SII.

The ICS valve will be fully open if the pilot valve in P is fully open, irrespective of the degree of opening of pilot valves SI and SII.

The ICS valve will be fully closed if the pilot valve in P is fully closed and at least one of the valves in SI or SII is fully closed at the same time. The relation between the pilot valves in ports SI, SII and P is shown in the table on the next page.

If the ICS is not fitted with three pilot valves, the unused port(s) must be sealed with a blanking plug. If the blanking plug is fitted as an assembled unit, A + B, the channels from the specific port will be closed. (See illustration below)

If only the top part, A, of the plug is fitted, the channels from the ports in question will be open. If the degree of opening of the ICS main valve is not to be a function of the main valve inlet pressure, or if more than three regulating functions are required, ports SI, SII or P can be fitted with a nipple for the connection of external pilot pressure. This applies to all ICS versions.

The pressure to which the external pilot line is connected will then determine pressure p2 on top of the servo piston. The pilot valves fitted in that external pilot line will determine the main valve function. Pilot valves installed in external lines must be mounted in a type CVH housing.

Depending on the function of the pilot valves, the ICS regulating characteristic becomes:



- · on/off
- proportional
- integral or
- cascade.

ICS main valves are therefore especially suitable for all forms of temperature and pressure regulating systems.

An overview of the types of pilot valves available can be found in the literature "Pilot valves for operated main valves" (Al248786497190).


On the following pages, a number of configuration examples can be found. These are only for explanatory purpose. However, by using the literature regarding pilot valves these examples are easier to comprehend.


Table 1: Pilot valve port

	Pilot valve port				
SI	SII	P	ICS valve		
Open	Open	Closed	Open		
Open	Open	Open	Open		
Open	Closed	Closed	Closed		
Open	Closed	Open	Open		
Closed	Open	Closed	Closed		
Closed	Open	Open	Open		
Closed	Closed	Closed	Closed		
Closed	Closed	Open	Open		

Figure 3: Blanking plug A + B Figure 4: Blanking plug A Figure 5: Example (ICS with 3 pilot









### Media

### **Refrigerants**

Applicable to HCFC, HFC, R717(Ammonia) and R744 (CO<sub>2</sub>). Use with flammable hydrocarbons cannot be recommended; please contact Danfoss.

### **New refrigerants**

Danfoss products are continually evaluated for use with new refrigerants depending on market requirements.

When a refrigerant is approved for use by Danfoss, it is added to the relevant portfolio, and the R number of the refrigerant (e.g. R513A) will be added to the technical data of the code number. Therefore, products for specific refrigerants are best checked at store.danfoss.com/en/, or by contacting your local Danfoss representative.



### **Product specification**

### **Design**

ICS valves are designed as pilot operated valves requiring minimal pressure differential to open. If the pressure difference is 0 bar /0 psi, the ICS valve will be closed. If the pressure difference is 0.2 bar /3 psi or more, the ICS valve will be fully open. At pressure differences between 0.07 bar /1 psi and 0.2 bar /3 psi, the opening degree will be correspondingly proportional.

The ICS is available for use with either one or three pilot valves.

Two of the three pilot pressure connections (S1 and S2) are connected in series whilst the third (P) is connected in parallel to S1 and S2. This allows different combinations of pilot valves to be used, thus providing numerous variations in control functions.

Valve body and top cover material Low temperature steel

### Pressure and temperature range

#### **Temperature range**

-60 °C /+120 °C (-76 °F /+248 °F).

#### **Pressure range**

The valve is designed for a Max. working pressure:

- Size DN 25 to DN 65 (80): 65 bar (943 psig) (1)
- Size DN 100 to DN 150: 52 bar (754 psig)

#### **Surface protection**

The external surface is zinc-chromated for the storage, transport and installation. The external surface of the valve must be protected against corrosion with a suitable top coating after installation involving welding and consequent assembly.

#### **Opening differential pressure**

Fully open: Min. 0.2 bar (min. 3 psig); Max. Opening Pressure Differential (MOPD), solenoid valves only - at nominal conditions.

- 10 W a.c. up to 21 bar (305 psi)
- 20 W a.c. up to 40 bar (580 psi)

<sup>1</sup> MWP of the system main valve + pilots is defined by lowest MWP of the single pilot (not all pilots are designed for MWP of 65 bar).




### **The ICS Concept**

The ICS concept is developed around a modular principle. This gives the possibility of combining function modules and top covers with special valve body size that is available in a variety of connection possibilities.

There are eight valve bodies available.

Figure 6: Valve bodies






Valve bodies in the sizes ICV 20-ICV65 are available with a range of undersizes through oversized connection sizes and types.

ICV 100 - ICV 150 are available in butt-weld DIN and butt-weld ANSI nominal sizes

Figure 7: Valve body in sizes



Each valve body may be fitted with a 1 pilot or 3 pilot top cover.



Figure 8: 1 pilot top cover






Figure 9: 3 pilot top cover



In ICS, multiple inserts (function modules) are available to give different capacities.

Figure 10: ICS function modules



Туре	Valve body size	K <sub>v</sub> (m³/h)	C <sub>v</sub> (US <sub>gal/min</sub> )
ICS 25-5		1.7	2.0
ICS 25-10		3.5	4.1
ICS 25-15	25	6.0	7.0
ICS 25-20		8	9.3
ICS 25-25		11.5	13.3
ICS 32	32	17	20
ICS 40	40	27	31
ICS 50	50	44	51
ICS 65	65	70	81
ICS 80	80	85	98
ICS 100	100	142	165
ICS 125	125	207	240
ICS 150	150	354	410



### **Connections**

There is a very wide range of connection types available with ICS valves:

- D: Butt weld, DIN (2448)
- A: Butt weld, ANSI (B 36.10)
- J: Butt weld, JIS (B S 602)
- SOC: Socket weld, ANSI (B 16.11)
- SD: Solder connection, DIN (2856)
- SA: Solder connection, ANSI (B 16.22)
- FPT: Female pipe thread (ANSI/ASME B 1.20.1)

Figure 11: D: Butt-weld





Table 2: Butt-weld DIN

Size	Size	OD	Т	OD	Т
mm	in.	mm	mm	in.	in.
20	(3/4)	26.9	2.3	1.059	0.091
25	(1)	33.7	2.6	1.327	0.103
32	(11/4)	42.4	2.6	1.669	0.102
40	(1½)	48.3	2.6	1.902	0.103
50	(2)	60.3	2.9	2.37	0.11
65	(21/2)	76.1	2.9	3	0.11
80	(3)	88.9	3.2	3.50	0.13
100	(4)	114.3	3.6	4.5	0.14
125	(5)	140.7	4	5.5	0.16
150	(6)	168.3	6.3	6.6	0.25

Figure 12: A: Butt-weld ANSI (B 36.10)



**Table 3: Butt-weld ANSI** 

Size mm	Size in.	OD mm	T mm	OD in.	T in.	Schedule
(20)	3/4	26.9	4.0	1.059	0.158	80
(25)	1	33.7	4.6	1.327	0.181	80
(32)	11⁄4	42.4	4.9	1.669	0.193	80
(40)	11/2	48.3	5.1	1.902	0.201	80
(50)	2	60.3	3.9	2.37	0.15	40
(65)	21/2	73.0	5.2	2.87	0.20	40
(80)	3	88.9	5.5	3.50	0.22	40
(100)	4	114.3	6	4.5	0.24	
(125)	5	140.7	6.5	5.5	0.26	
(150)	6	168.3	7.1	6.6	0.28	



Figure 13: J: Butt-weld JIS





Table 4: Butt-weld JIS

Size	Size	OD	Т	OD	Т
mm	in.	mm	mm	in.	in.
(20)	3/4	26.9	4.0	1.059	0.158
(25)	1	33.7	4.6	1.327	0.181
(32)	11⁄4	42.4	4.9	1.669	0.193
(40)	1½	48.3	5.1	1.902	0.201
(50)	2	60.3	3.9	2.37	0.15
(65)	21/2	76.3	5.2	3.0	0.20

Figure 14: SOC: Socket welding ANSI (B 16.11)



**Table 5: Socket welding ANSI** 

Size mm	Size in.	OD mm	T mm	OD in.	T in.	L mm	L in.
(20)	3/4	27.2	4.6	1.071	0.181	13	0.51
(25)	1	33.9	7.2	1.335	0.284	13	0.51
(32)	11⁄4	42.7	6.1	1.743	0.240	13	0.51
(40)	11/2	48.8	6.6	1.921	0.260	13	0.51
(50)	2	61.2	6.2	2.41	0.24	16	0.63
(65)	21/2	74	8.8	2.91	0.344	16	0.63

Figure 15: SD: Soldering (DIN 2856)




Table 6: SD: Soldering DIN

Size	ID	L
mm	mm	mm
22	22.08	16.5
28	28.08	26
35	35.07	25



Size	ID	L
mm	mm	mm
42	42.07	28
54	54.09	33
76	76.1	33

Figure 16: SA: Soldering (ANSI B 16.22)





Table 7: Socket welding ANSI

Size in.	OD in.	L in.
7∕8	0.875	0.650
11/8	1.125	1.024
13/8	1.375	1.024
15⁄8	1.625	1.102
21/8	2.125	1.300
25/8	2.625	1.300

Figure 17: FPT: Female pipe thread, (ANSI/ASME B 1.20.1)



**Table 8: Socket welding ANSI** 

Size mm	Size in.	Inside pipe thread
(20)	3/4	(¾×14 NPT)
(25)	1	(1 × 11.5 NPT)
(32)	11⁄4	(1¼ × 11.5 NPT)



# **Material specification**

Figure 18: ICS 25, 32, 40, 50, 65




Table 9: Type and size of Bolt (pos. 5)

Туре	Screw
ICS 25	M12 × 30 A2-70 DIN 933
ICS 32	M14 × 35 A2-70 DIN 933
ICS 40	M14 × 40 A2-70 DIN 933
ICS 50	M16 × 40 A2-70 DIN 933
ICS 65	M16 × 50 A2-70 DIN 933

Table 10: Material and parts list (ICS 25, 32, 40, 50, 65)

No.	Part	Material	EN	ASTM	JIS
1	Body	Low temperature steel	G20Mn5QT, EN 10213-3	LCC A352	SCPL1 G5151
2	Top cover	Low temperature steel	G20Mn5QT, EN 10213-3 P285QH+QT 10222-4	LCC A352 LF2, A350	SCPL1 G5151
3	Function module (assembled)				
3a	o-ring	Cloroprene (Neoprene)			
3b	o-ring	Cloroprene (Neoprene)			
3c	Washer plate	Steel			
Α	Cylinder	Steel			
В	Piston	Steel			
C	Valve plate	PTFE			
D	Spring	Steel			
E	Cone	Steel			
4	Gasket	Fiber, non-asbestos			
5	Bolts	Stainless steel	A2-70, EN 1515-1	Grade B8 A320	A2-70, B 1054
6	Plug	Steel			
7	Gasket	Aluminium			
8	Manual operating spindle	Steel			
9	Plug	Steel			
10	Gasket	Aluminium			



Figure 19: ICS 100, 125, 150




Table 11: Type and size of Bolt (pos. 5)

**	
Туре	Screw
ICS 100	M20 × 60 A2-70 DIN 933
ICS 125	M20 × 60 A2-70 DIN 933
ICS 150	M20 × 70 A2-70 DIN 933


Table 12: Material and parts list (ICS 100, 125, 150)

	iateriai aria parts list (i				
No.	Part	Material	EN	ASTM	JIS
1	Body	Low temperature steel	G20Mn5QT, EN 10213-3	LCC A352	SCPL1 G5151
2	Top cover	Low temperature steel	G20Mn5QT, EN 10213-3	LCC A352	SCPL1 G5151
3	Function module (assembled)				
3a	Piston/rod	Stainless steel / steel			
3b	Piston ring	Steel			
3c	Insert	Steel			
3d	Spring	Steel			
3e	Cone	Stainless steel / steel			
3f	Teflon plate	Teflon unfilled			
3g	Washer plate	PTFE			
3h	O-ring	Cloroprene (Neoprene)			
4	Gasket	Fiber, non-asbestos			
5	Bolts	Stainless steel	A2-70, EN 1515-1	Grade B8 A320	A2-70, B 1054
6	Plug	Steel			
7	Eye bolt	Galvanized steel			
8	Manual operating spindle	Steel			



### **Configuration examples**

Table 13: Example no. 1









Table 14: Example no. 2





#### Example no. 2-5 **Products** External control pressure with electrical shut off combined with constant pres-1 × ICS 3 Pilots $1 \times \text{Nipple}$ for external sure regulation control pressure - -0.66 bar to 7 bar (19.5 in. Hg to 102 1 × CVP-L $1 \times \text{EVM}$ psig) CVP $1 \times \text{Coil}$ ICS3 Example no. 2-6 Products Constant pressure regulation with ex-1 × ICS 3 Pilots ternal control pressure combined with 1 × Nipple for external electrical wide open control pressure CVP 1 × CVP-L • -0.66 bar to 7 bar (19.5 in. Hg to 102 $1 \times EVM$ $1 \times \text{Coil}$ ÉVŇ ICS3 Example no. 2-7 **Products** 1 × ICS 3 Pilots Constant pressure regulation with electrical shut off combined with external $1 \times Nipple$ for external control pressure control pressure $1 \times \text{CVP-L}$ • -0.66 bar to 7 bar (19.5 in. Hg to 102 $1 \times EVM$ psig) $1 \times Coil$ Ext. Example no. 2-8 **Products** Solenoid valve with external control $1 \times ICS 3$ $1 \times Blanking plug (A + B)$ pressure for small pressure drops $1 \times Nipple$ for external control pressure <u> ∏ P</u> $1 \times EVM$ $1 \times \text{Coil}$ (A)+(B) ICS3 Example no. 2-9 **Products** Differential pressure regulation com- $1 \times ICS 3$ bined with electrical shut off $1 \times Blanking plug (A + B)$ 1 × CVPP-L • CVPP-L (0.66 bar to 7 bar ) (19.5 in. $1 \times EVM$ Hg to 102 psig) <del>-</del>π₽ $1 \times \text{Coil}$ **(A)+(B)** ICS3 Example no. 2-10 Products Differential pressure regulation com-1 × ICS 3 Pilots bined with electrical wide open $1 \times Blanking plug (A)$ • CVPP-L (0.66 bar to 7 bar) (19.5 in. $1 \times \text{CVPP-L}$ $1 \times \text{EVM}$ Hg to 102 psig) $1 \times Coil$ ÉVŇ ICS3




#### Example no. 2-11 **Products** Differential pressure regulation com-1 × ICS 3 Pilots SII significant bined with electrical wide open and $1 \times \text{CVPP-L}$ shut off $2 \times EVM$ **CVPP** • CVPP-L (0.66 bar to 7 bar) (19.5 in. 2 × Coils Hg to 102 psig) ÉVŇ ICS3 Example no. 2-12 **Products** Constant pressure regulation combined 1 × ICS 3 Pilots with electrical shut off $1 \times Blanking plug (A + B)$ 1 × CVP-L/M/H • CVP-L (-0.66 bar to 7 bar) (19.5 in. Hg $1 \times EVM$ to 102 psig) <u>√IIIP</u> • CVP-M (4 bar to 28 bar) (58 to 406 $1 \times \text{Coil}$ • CVP-H (25 bar to 52 bar) (363 to 754 ICS3 Example no. 2-13 **Products** 1 × ICS 3 Pilots Constant pressure regulation combined with electrical wide open 1 × Blanking plug (A) • CVP-L (-0.66 bar to 7 bar) (19.5 in. Hg $1 \times \text{CVP-L/M/H}$ $1 \times \text{EVM}$ to 102 psig) • CVP-M (4 bar to 28 bar) (58 to 406 1 x Coil psig) • CVP-H (25 bar to 52 bar) (363 to 754 psig) Example no. 2-14 **Products** Constant pressure regulation combined 1 × ICS 3 Pilots SII with electrical shut off and wide open $1 \times \text{CVP-L/M/H}$ • CVP-L (-0.66 bar to 7 bar) (19.5 in. Hg $2 \times EVM$ CVP to 102 psig) $2 \times Coils$ • CVP-M (4 bar to 28 bar) (58 to 406 • CVP-H (25 bar to 52 bar) (363 to 754 psig) ICS3 Example no. 2-15 **Products** Constant pressure regulation with 1 × ICS 3 Pilots change-over between two preset evap-2 × CVP-L/M/H orating pressures $1 \times EVM$ CVP • CVP-L (-0.66 bar to 7 bar) (19.5 in. Hg $1 \times Coil$ to 102 psig) • CVP-M (4 bar to 28 bar) (58 to 406 • CVP-H (25 bar to 52 bar) (363 to 754 ICS3 psig) Example no. 2-16 **Products** Differential pressure regulation com-1 × ICS 3 Pilots bined with electrical shut off $1 \times Blanking plug (A + B)$ • CVPP-L (-0.66 bar to 7 bar) (19.5 in. $1 \times \text{CVPP-L/M}$ CVPP $1 \times \text{EVM}$ Hg to 102 psig) CVPP-M (4 bar to 28 bar) (58 to 406 $1 \times Coil$ psig) (A)+(B) ICS3




#### Example no. 2-17 **Products** Differential pressure regulation com-1 × ICS 3 Pilots SII bined with electrical wide open 1 × Blanking plug (A) • CVPP-L (-0.66 bar to 7 bar) (19.5 in. $1 \times \text{CVPP-L/M}$ Hg to 102 psig) $1 \times EVM$ CVPP-M (4 bar to 28 bar) (58 to 406 $1 \times \text{Coil}$ psig) ICS3 Example no. 2-18 Products 1 × ICS 3 Pilots Differential pressure regulation com-<u></u>S∥ bined with electrical wide open and $1 \times \text{CVPP-L/M}$ shut off 2 × EVM CVPP ÉVM • CVPP-L (-0.66 bar to 7 bar) (19.5 in. $2 \times Coils$ Hg to 102 psig) CVPP-M (4 bar to 28 bar) (58 to 406 psig) ICS3 Example no. 2-19 **Products** 1 × ICS 3 Pilots Constant pressure regulation combined with electrical wide open and shut off $1 \times \text{CVP-L/M/H}$ • CVP-L (-0.66 bar to 7 bar) (19.5 in. Hg $1 \times \text{EVM}$ 1 × EVM-NO (12 W coil) to 102 psig) • CVP-M (4 bar to 28 bar) (58 to 406 2 × Coils psig) EVM-NO • CVP-H (25 bar to 52 bar) (363 to 754 psig) Example no. 2-20 **Products** Crankcase pressure regulation (max. $1 \times ICS$ 3 Pilots suction pressure regulation) combined $1 \times Blanking plug (A + B)$ with shut off $1 \times \text{CVC-L}$ • -0.45 bar to 7 bar (13.3 in. Hg to 102 $1 \times \text{EVM}$ <del>∏</del>P $1 \times \text{Coil}$ psig) (A)+(B) ICS3 Example no. 2-21 **Products** Crankcase pressure regulation (max. 1 × ICS 3 Pilots suction pressure regulation) combined $1 \times Blanking plug (A + B)$ with evaporating pressure regulation $1 \times \text{CVC-L/M}$ CVP CVC • -0.66 bar to 28 bar (19.5 in. Hg to $1 \times \text{CVP-L/M}$ <u>∭</u>Ρ 406 psig). (A)+(B) ICS3 Example no. 2-22 **Products** Crankcase pressure regulation (max. 1 × ICS 3 Pilots suction pressure regulation) at low $1 \times Blanking plug (A + B)$ pressure drops across the valve $1 \times \text{Nipple for external}$ CVC control pressure • -0.45 bar to 7 bar (13.3 in. Hg to 102 1 × CVC-L psig) **(A)** + **(B)** ICS3









## Valve selection based on capacity calculation


As for extended capacity calculations and valve selection based on capacities and refrigerants, please refer to Coolselector®2. Rated and extended capacities are calculated with the Coolselector®2 calculation engine to ARI standards with the ASEREP equations based on laboratory measurements of selected valves.

Download Coolselector®2 for free at coolselector.danfoss.com.

### **Dimensions and weights**

### ICS 25-5 to ICS 25-25

Figure 20: Dimensions and weights - ICS 25-5 to ICS 25-25





**Table 15: Connection type and Weight** 

		p										
Connection		H <sub>1</sub>	H <sub>2</sub>	Н <sub>3</sub>	H <sub>4</sub>	L	L,	L <sub>2</sub>	В,	B <sub>2</sub>	Weight ICS 1 Pilot	Weight ICS 3 Pi- lots
20 D (¾ in.)	mm	37	145	86	60	135	42	15	42	87	3 kg	3.6 kg
	in.	1.46	5.71	3.39	2.36	5.31	1.65	0.59	1.65	3.43	6.6 lb.	7.92 lb.
25 D (1 in.)	mm	37	145	86	60	135	42	15	42	87	3 kg	3.6 kg
	in.	1.46	5.71	3.39	2.36	5.31	1.65	0.59	1.65	3.43	6.6 lb.	7.92 lb.
32 D (1¼ in.)	mm	37	145	86	60	135	42	15	42	87	3 kg	3.6 kg
	in.	1.46	5.71	3.39	2.36	5.31	1.65	0.59	1.65	3.43	6.6 lb.	7.92 lb.
40 D (1½ in.)	mm	37	145	86	60	135	42	15	42	87	3 kg	3.6 kg
	in.	1.46	5.71	3.39	2.36	5.31	1.65	0.59	1.65	3.43	6.6 lb.	7.92 lb.
20 A (¾ in.)	mm	37	145	86	60	135	42	15	42	87	3 kg	3.6 kg
	in.	1.46	5.71	3.39	2.36	5.31	1.65	0.59	1.65	3.43	6.6 lb.	7.92 lb.
25 A (1 in.)	mm	37	145	86	60	135	42	15	42	87	3 kg	3.6 kg
	in.	1.46	5.71	3.39	2.36	5.31	1.65	0.59	1.65	3.43	6.6 lb.	7.92 lb.
32 A (1¼ in.)	mm	37	145	86	60	135	42	15	42	87	3 kg	3.6 kg
	in.	1.46	5.71	3.39	2.36	5.31	1.65	0.59	1.65	3.43	6.6 lb.	7.92 lb.
20 SOC (¾ in.)	mm	37	145	86	60	135	42	15	42	87	3 kg	3.6 kg
	in.	1.46	5.71	3.39	2.36	5.31	1.65	0.59	1.65	3.43	6.6 lb.	7.92 lb.
25 SOC (1 in.)	mm	37	145	86	60	147	42	15	42	87	3 kg	3.6 kg
	in.	1.46	5.71	3.39	2.36	5.79	1.65	0.59	1.65	3.43	6.6 lb.	7.92 lb.
22 SD (¾ in.)	mm	37	145	86	60	135	42	15	42	87	3 kg	3.6 kg
	in.	1.46	5.71	3.39	2.36	5.31	1.65	0.59	1.65	3.43	6.6 lb.	7.92 lb.
28 SD (1½ in.)	mm	37	145	86	60	147	42	15	42	87	3 kg	3.6 kg
	in.	1.46	5.71	3.39	2.36	5.78	1.65	0.59	1.65	3.43	6.6 lb.	7.92 lb.
22 SA (1/8 in.)	mm	37	145	86	60	135	42	15	42	87	3 kg	3.6 kg
	in.	1.46	5.71	3.39	2.36	5.31	1.65	0.59	1.65	3.43	6.6 lb.	7.92 lb.
28 SA (1½ in.)	mm	37	145	86	60	147	42	15	42	87	3 kg	3.6 kg
	in.	1.46	5.71	3.39	2.36	5.78	1.65	0.59	1.65	3.43	6.6 lb.	7.92 lb.
35 SA (1% in.)	mm	37	145	86	60	147	42	15	42	87	3 kg	3.6 kg
	in.	1.46	5.71	3.39	2.36	5.78	1.65	0.59	1.65	3.43	6.6 lb.	7.92 lb.
20 FPT (¾ in.)	mm	37	145	86	60	135	42	15	42	87	3 kg	3.6 kg
	in.	1.46	5.71	3.39	2.36	5.31	1.65	0.59	1.65	3.43	6.6 lb.	7.92 lb.
25 FPT (1 in.)	mm	37	145	86	60	135	42	15	42	87	3 kg	3.6 kg
	in.	1.46	5.71	3.39	2.36	5.31	1.65	0.59	1.65	3.43	6.6 lb.	7.92 lb.

### NOTE:

Specified weights are approximate values only.

**D** = Butt-weld DIN

**A** = Butt-weld ANSI

 $\mathbf{J} = \text{Butt-weld JIS}$ 


**SOC** = Socket weld ANSI

**SD** = Solder DIN

**SA** = Solder ANSI



Figure 21: ICS 32, Dimensions and weights



**Table 16: Connection type and Weight** 

Table 10. Connec		pe ana i	· c.g									
Connection		Н,	H <sub>2</sub>	H <sub>3</sub>	H₄	L	L,	L <sub>2</sub>	В <sub>1</sub>	B <sub>2</sub>	Weight ICS 1 Pilot	Weight ICS 3 Pi- lots
32 D (1¼ in.)	mm	40	160	100	74	145	51	15	51	87	4.5 kg	5 kg
	in.	1.57	6.30	3.93	2.91	5.71	2.00	0.59	2.00	3.43	9.9 lb.	11 lb.
40 D (1½ in.)	mm	40	160	100	74	145	51	15	51	87	4.5 kg	5 kg
	in.	1.57	6.30	3.93	2.91	5.71	2.00	0.59	2.00	3.43	9.9 lb.	11 lb.
32 A (1¼ in.)	mm	40	160	100	74	145	51	15	51	87	4.5 kg	5 kg
	in.	1.57	6.30	3.93	2.91	5.71	2.00	0.59	2.00	3.43	9.9 lb.	11 lb.
40 A (1½ in.)	mm	40	160	100	74	145	51	15	51	87	4.5 kg	5 kg
	in.	1.57	6.30	3.93	2.91	5.71	2.00	0.59	2.00	3.43	9.9 lb.	11 lb.
32 SOC (11/4 in.)	mm	40	160	100	74	145	51	15	51	87	4.5 kg	5 kg
	in.	1.57	6.30	3.93	2.91	5.71	2.00	0.59	2.00	3.43	9.9 lb.	11 lb.
35 SD (1% in. SA)	mm	40	160	100	74	145	51	15	51	87	4.5 kg	5 kg
	in.	1.57	6.30	3.93	2.91	5.71	2.00	0.59	2.00	3.43	9.9 lb.	11 lb.
42 SD (15% in.)	mm	40	160	100	74	145	51	15	51	87	4.5 kg	5 kg
	in.	1.57	6.30	3.93	2.91	5.71	2.00	0.59	2.00	3.43	9.9 lb.	11 lb.
42 SA (1% in.)	mm	40	160	100	74	145	51	15	51	87	4.5 kg	5 kg
	in.	1.57	6.30	3.93	2.91	5.71	2.00	0.59	2.00	3.43	9.9 lb.	11 lb.

#### NOTE:

Specified weights are approximate values only.

**D** = Butt-weld DIN

**A** = Butt-weld ANSI

 $\mathbf{J} = \text{Butt-weld JIS}$ 


**SOC** = Socket weld ANSI

**SD** = Solder DIN

**SA** = Solder ANSI



Figure 22: ICS 40, Dimensions and weights



**Table 17: Connection type and Weight** 

	-,	<b>P</b> C 1										
Connection		H <sub>1</sub>	H <sub>2</sub>	H <sub>3</sub>	H <sub>4</sub>	L	L,	L <sub>2</sub>	B <sub>1</sub>	B <sub>2</sub>	Weight ICS 1 Pilot	Weight ICS 3 Pi- lots
40 D (1½ in.)	mm	49	166	105	78	160	51	15	54	87	5.9 kg	6.3 kg
	in.	1.93	6.54	4.13	3.07	6.30	2.00	0.59	2.13	3.43	13.0 lb.	13.9 lb.
50 D (2 in.)	mm	49	166	105	78	180	51	15	54	87	5.9 kg	6.3 kg
	in.	1.93	6.54	4.13	3.07	7.09	2.00	0.59	2.13	3.43	13.0 lb.	13.9 lb.
40 A (1½ in.)	mm	49	166	105	78	160	51	15	54	87	5.9 kg	6.3 kg
	in.	1.93	6.54	4.13	3.07	6.30	2.00	0.59	2.13	3.43	13.0 lb.	13.9 lb.
50 A (2 in.)	mm	49	166	105	78	180	51	15	54	87	5.9 kg	6.3 kg
	in.	1.93	6.54	4.13	3.07	7.09	2.00	0.59	2.13	3.43	13.0 lb.	13.9 lb.
40 SOC (1½ in.)	mm	49	166	105	78	180	51	15	54	87	5.9 kg	6.3 kg
	in.	1.93	6.54	4.13	3.07	7.09	2.00	0.59	2.13	3.43	13.0 lb.	13.9 lb.
42 SD (1% in.)	mm	49	166	105	78	180	51	15	54	87	5.9 kg	6.3 kg
	in.	1.93	6.54	4.13	3.07	7.09	2.00	0.59	2.13	3.43	13.0 lb.	13.9 lb.
42 SA (15% in.)	mm	49	166	105	78	180	51	15	54	87	5.9 kg	6.3 kg
	in.	1.93	6.54	4.13	3.07	7.09	2.00	0.59	2.13	3.43	13.0 lb.	13.9 lb.

### • NOTE:

Specified weights are approximate values only.

 $\mathbf{D} = \text{Butt-weld DIN}$ 

**A** = Butt-weld ANSI

**J** = Butt-weld JIS


**SOC** = Socket weld ANSI

**SD** = Solder DIN

**SA** = Solder ANSI



Figure 23: ICS 50, Dimensions and weights



**Table 18: Connection type and Weight** 

Connection		Н	H <sub>2</sub>	H <sub>3</sub>	H <sub>4</sub>	L	L,	L <sub>2</sub>	В <sub>1</sub>	B <sub>2</sub>	Weight ICS 1 Pilot	Weight ICS 3 Pi- lots
50 D (2 in.)	mm	59	181	120	93	200	51	15	63	91	8.9 kg	9.2 kg
	in.	2.32	7.13	4.72	3.66	7.87	2.00	0.59	2.48	3.58	19.6 lb.	20.2 lb.
65 D (2½ in.)	mm	59	181	120	93	210	51	15	63	91	8.9 kg	9.2 kg
	in.	2.32	7.13	4.72	3.66	8.27	2.00	0.59	2.48	3.58	19.6 lb.	20.2 lb.
50 A (2 in.)	mm	59	181	120	93	200	51	15	63	91	8.9 kg	9.2 kg
	in.	2.32	7.13	4.72	3.66	7.87	2.00	0.59	2.48	3.58	19.6 lb.	20.2 lb.
65 A (2½ in.)	mm	59	181	120	93	210	51	15	63	91	8.9 kg	9.2 kg
	in.	2.32	7.13	4.72	3.66	8.27	2.00	0.59	2.48	3.58	19.6 lb.	20.2 lb.
50 SOC (2 in.)	mm	59	181	120	93	216	51	15	63	91	8.9 kg	9.2 kg
	in.	2.32	7.13	4.72	3.66	8.50	2.00	0.59	2.48	3.58	19.6 lb.	20.2 lb.
54 SD (2½ in. SA)	mm	59	181	120	93	216	51	15	63	91	8.9 kg	9.2 kg
	in.	2.32	7.13	4.72	3.66	8.50	2.00	0.59	2.48	3.58	19.6 lb.	20.2 lb.

#### NOTE:

Specified weights are approximate values only.

**D** = Butt-weld DIN

A = Butt-weld ANSI

**J** = Butt-weld JIS

**SOC** = Socket weld ANSI


 $\mathbf{SD} = \text{Solder DIN}$ 

**SA** = Solder ANSI



### ICS 65/ ICS 80

Figure 24: ICS 65 / ICS 80, Dimensions and weights



**Table 19: Connection type and Weight** 

Table 15. Connection type and weight												
Connection		Н,	H <sub>2</sub>	H <sub>3</sub>	H <sub>4</sub>	L	L,	L <sub>2</sub>	B <sub>1</sub>	B <sub>2</sub>	Weight ICS 1 Pilot	Weight ICS 3 Pi- lots
65 D (2½ in.)	mm	65	202	140	115	230	51	15	70	91	13.4 kg	13.5 kg
	in.	2.56	7.95	5.51	4.53	9.06	2.00	0.59	2.76	3.58	29.48 lb.	29.7 lb.
80 D (3 in.)	mm	65	202	140	115	245	51	15	70	91	13.4 kg	13.5 kg
	in.	2.56	7.95	5.51	4.53	9.65	2.00	0.59	2.76	3.58	29.48 lb.	29.7 lb.
65 A (2½ in.)	mm	65	202	140	115	230	51	15	70	91	13.4 kg	13.5 kg
	in.	2.56	7.95	5.51	4.53	9.06	2.00	0.59	2.76	3.58	29.48 lb.	29.7 lb.
80 A (3 in.)	mm	65	202	140	115	245	51	15	70	91	13.4 kg	13.5 kg
	in.	2.56	7.95	5.51	4.53	9.65	2.00	0.59	2.76	3.58	29.48 lb.	29.7 lb.
65 J (2½ in.)	mm	65	202	140	115	230	51	15	70	91	13.4 kg	13.5 kg
	in.	2.56	7.95	5.51	4.53	9.06	2.00	0.59	2.76	3.58	29.48 lb.	29.7 lb.
65 SOC (2½ in.)	mm	65	202	140	115	230	51	15	70	91	13.4 kg	13.5 kg
	in.	2.56	7.95	5.51	4.53	9.06	2.00	0.59	2.76	3.58	29.48 lb.	29.7 lb.
76 SD (3 in.)	mm	65	202	140	115	245	51	15	70	91	13.4 kg	13.5 kg
	in.	2.56	7.95	5.51	4.53	9.65	2.00	0.59	2.76	3.58	29.48 lb.	29.7 lb.
67 SA (25% in.)	mm	65	202	140	115	245	51	15	70	91	13.4 kg	13.5 kg
	in.	2.56	7.95	5.51	4.53	9.65	2.00	0.59	2.76	3.58	29.48 lb.	29.7 lb.

#### NOTE:

Specified weights are approximate values only.

**D** = Butt-weld DIN

**A** = Butt-weld ANSI


 $\mathbf{J} = \text{Butt-weld JIS}$ 

**SOC** = Socket weld ANSI

**SD** = Solder DIN

**SA** = Solder ANSI





**Table 20: Connection type and Weight** 


Connection		H <sub>1</sub>	H <sub>2</sub>	H <sub>3</sub>	H <sub>4</sub>	L	L <sub>1</sub>	L <sub>2</sub>	L <sub>3</sub>	B <sub>1</sub>	B <sub>2</sub>	B <sub>3</sub>	B <sub>4</sub>	Weight
100 D or A (4 in )	mm	109	372	237	196	295	60	51	50	109	38	52	33	45 kg
100 D or A (4 in.)	in.	4.3	14.7	9.3	7.7	11.6	2.4	2.0	2.0	4.3	1.5	2.1	1.3	99.2 lb.

### NOTE:

Specified weights are approximate values only.

**D** = Butt-weld DIN ; **A** = Butt-weld ANSI






**Table 21: Connection type and Weight** 

Connection		H <sub>1</sub>	H <sub>2</sub>	H <sub>3</sub>	H <sub>4</sub>	L	L,	L <sub>2</sub>	L <sub>3</sub>	L <sub>4</sub>	B <sub>1</sub>	B <sub>2</sub>	B <sub>3</sub>	B <sub>4</sub>	Weight
125 D or A /E in )	mm	139	386	246	212	350	84	56	55	85	130	45	50	47	68 kg
125 D or A (5 in.)	in.	5.5	15.2	9.7	8.4	13.8	3.3	2.2	2.2	3.4	5.1	1.8	2.0	1.9	149.9 lb.

Specified weights are approximate values only.

**D** = Butt-weld DIN; **A** = Butt-weld ANSI





**Table 22: Connection type and Weight** 

Connection		H <sub>1</sub>	H <sub>2</sub>	H <sub>3</sub>	H <sub>4</sub>	L	L,	L <sub>2</sub>	L <sub>3</sub>	L <sub>4</sub>	B <sub>1</sub>	B <sub>2</sub>	B <sub>3</sub>	B <sub>4</sub>	Weight
150 D or A (6 in.)	mm	168	425	297	256	445	107	58	69	96	150	48	52	50	115 kg
150 D OF A (6 III.)	in.	6.6	16.7	11.7	10.1	17.5	4.2	2.3	2.7	3.8	5.9	1.9	2.1	2.0	253.5 lb.

Specified weights are approximate values only.

**D** = Butt-weld DIN; **A** = Butt-weld ANSI



### **Ordering**

### **ICS 25**

### Ordering from the parts programme

Figure 28: Example (select from table ICV 25 valve body w/different connections, table ICS 25 function module and table ICS 25 top cover)




Figure 29: ICV 25 valve body



Table 23: ICV 25 valve body w/different connections

Table 25. ICV 25 valve body W/amerent connections	
Connection	Code Number
20 D (3/4 in.)	027H2128
25 D (1 in.)	027H2120
32 D (11/4 in.)	027H2129
40 D (11/2 in.)	027H2135
35 SD (13/8 in. SA)	027H2134
28 SA (11/8 in.)	027H2126
22 SA (7/8 in.)	027H2125
28 SD (11/8 in.)	027H2124
22 SD (7/8 in.)	027H2123
20 A (3/4 in.)	027H2131
25 A (1 in.)	027H2121
32 A (11/4 in.)	027H2130
20 SOC (3/4 in.)	027H2132
25 SOC (1 in.)	027H2122
20 FPT (½ in.)	027H2133
25 FPT (1 in.)	027H2127

**D** = Butt-weld DIN

**A** = Butt-weld ANSI

**J** = Butt-weld JIS

**SOC** = Socket weld ANSI

**SD** = Solder DIN

**SA** = Solder ANSI



Figure 30: ICS 25 function module




Table 24: ICS 25 function module

Description	Code Number
ICS 25-5	027H2201 <sup>(1)</sup>
ICS 25-10	027H2202 <sup>(1)</sup>
ICS 25-15	027H2203 <sup>(1)</sup>
ICS 25-20	027H2204 <sup>(1)</sup>
ICS 25-25	027H2200 <sup>(1)</sup>

<sup>(1)</sup> Including gasket and O-rings

Figure 31: ICS 1




Figure 32: ICS 3




Table 25: ICS 25 top cover

Description	Code Number
Top cover 1 Pilot	027H2172 <sup>(2)</sup>
Top cover 3 Pilots	027H2173 <sup>(3)</sup>

<sup>(2)</sup> Including bolts

### Ordering complete factory assembled valve

(body, function module and top cover)

<sup>(3)</sup> including bolts and one blanking plug



Figure 33: 1 pilot





Figure 34: 3 pilots



**Table 26: Connections** 

		Available connections							
		20 D (¾ in.)	25 D (1 in.)	32 D (1¼ in.)	40 D (1½ in.)	35 SD (1¾ in. SA)	28 SA (1½ in.)	22 SA (½ in.)	28 SD (1½ in.)
ICS 25-5	1 Pilot	027H2028	027H2020	*	*	*	027H2026	027H2025	027H2024
103 23-3	3 Pilots <sup>(4)</sup>	027H2078	027H2070	*	*	*	027H2076	027H2075	027H2074
ICS 25-10	1 Pilot	027H2038	027H2030	*	*	*	027H2036	027H2035	027H2034
	3 Pilots(4)	027H2088	027H2080	*	*	*	027H2086	027H2085	027H2084
ICS 25-15	1 Pilot	027H2048	027H2040	*	*	*	027H2046	027H2045	027H2044
	3 Pilots(4)	027H2098	027H2090	*	*	*	027H2096	027H2095	027H2094
ICS 25-20	1 Pilot	027H2058	027H2050	*	*	*	027H2056	027H2055	027H2054
	3 Pilots <sup>(4)</sup>	027H2108	027H2100	*	*	*	027H2106	027H2105	027H2104
ICS 25-25	1 Pilot	027H2068	027H2060	*	*	*	027H2066	027H2065	027H2064
	3 Pilots <sup>(4)</sup>	027H2118	027H2110	*	*	*	027H2116	027H2115	027H2114

<sup>(4)</sup> Including one blanking plug (A+B)

**Table 27: Connections** 

			Available connections						
		22 SD (¾ in.)	20 A (¾ in.)	25 A (1 in.)	32 A (1¼ in.)	20 SOC (¾ in.)	25 SOC (1 in.)	20 FPT (½ in.)	25 FPT (1 in. )
ICS 25-5	1 Pilot	027H2023	027H2029	027H2021	*	027H2140	*	*	*
IC3 25-5	3 Pilots <sup>(4)</sup>	027H2073	027H2079	027H2071	*	027H2145	*	*	*
ICS 25-10	1 Pilot	027H2033	027H2039	027H2031	*	*	*	*	*
	3 Pilots <sup>(4)</sup>	027H2083	027H2089	027H2081	*	027H2146	*	*	*
ICS 25-15	1 Pilot	027H2043	027H2049	027H2041	*	027H2142	*	*	*
	3 Pilots <sup>(4)</sup>	027H2093	027H2099	027H2091	*	*	*	*	*
ICS 25-20	1 Pilot	027H2053	027H2059	027H2051	*	027H2143	*	*	*
	3 Pilots <sup>(4)</sup>	027H2103	027H2109	027H2101	*	027H2148	*	*	*
ICS 25-25	1 Pilot	027H2063	*	027H2061	*	*	027H2062	*	*
	3 Pilots <sup>(4)</sup>	027H2113	*	027H2111	*	*	027H2112	*	*

<sup>\*</sup> Select from parts programme

<sup>\*</sup> Select from parts programme



### Ordering from the parts programme

Figure 35: Example (select from table ICV 32 valve body w/different connections, table ICS 32 function module and table ICS 32 top cover)




Figure 36: ICV 32 valve body w/different connections



Table 28: ICV 32 valve body w/different connections

Code Number
027H3120
027H3125
027H3127
027H3128
027H3123
027H3121
027H3122
027H3126

 $\mathbf{D} = \text{Butt-weld DIN}$ 

**A** = Butt-weld ANSI

J = Butt-weld JIS


**SOC** = Socket weld ANSI

SD = Solder DIN

**SA** = Solder ANSI



Figure 37: function module



### Table 29: ICS 32 function module

Description	Code Number
ICS 32	027H3200 <sup>(1)</sup>

<sup>(1)</sup> Including gasket and O-rings

Figure 38: ICS 1




Figure 39: ICS 3




Table 30: ICS 32 top cover

Description	Code Number
Top cover 1 Pilot	027H3172 <sup>(2)</sup>
Top cover 3 Pilots	027H3173 <sup>(3)</sup>

<sup>(2)</sup> Including bolts

### Ordering complete factory assembled valve

(body, function module and top cover)

<sup>(3)</sup> Including bolts and one blanking plug



Figure 40: 1 pilot





Figure 41: 3 pilots



**Table 31: Connections** 

		Available connections							
		32 D (1¼ in.)	40 D (1½ in.)	42 SA (1 <sup>5</sup> / <sub>8</sub> in.)	42 SD (15% in.)	35 SD (1¾ in. SA)	32 A (1¼ in.)	32 SOC (1¼ in.)	40 A (1½ in.)
ICS 32	1 Pilot	027H3020	*	*	*	027H3023	027H3021	027H3022	*
1C3 32	3 Pilots <sup>(4)</sup>	027H3030	*	*	*	027H3033	027H3031	027H3032	*

<sup>(4)</sup> Including one blanking plug (A+B)

<sup>\*</sup> Select from parts programme



### Ordering from the parts programme

Figure 42: Example (select from table ICV 40 valve body w/different connections, table ICS 40 function module and table ICS 40 top cover)




Figure 43: ICV 40 valve body w/different connections



Table 32: ICV 40 valve body w/different connections

indice = i i i i i i i i i i i i i i i i i i	
Connections	Code Number
40 D (1½ in.)	027H4120
50 D (2 in.)	027H4126
42 SA (1% in.)	027H4124
42 SD (1% in.)	027H4123
40 A (1½ in.)	027H4121
40 SOC (1½ in.)	027H4122
50 A (2 in.)	027H4127

**D** = Butt-weld DIN

**A** = Butt-weld ANSI

**J** = Butt-weld JIS

**SOC** = Socket weld ANSI

**SD** = Solder DIN

**SA** = Solder ANSI

Figure 44: function module







Table 33: ICS 40 function module

Description	Code Number
ICS 40	027H4200 <sup>(1)</sup>

<sup>(1)</sup> Including gasket and O-rings

Figure 45: ICS 1







Table 34: ICS 40 top cover

Description	Code Number
Top cover 1 Pilot	027H4172 <sup>(2)</sup>
Top cover 3 Pilots	027H4173 <sup>(3)</sup>

## Ordering complete factory assembled valve

(body, function module and top cover)

Figure 47: 1 pilot






Figure 48: 3 pilots

**Table 35: Connections** 

		Available connections						
		40 D (1½ in.)	50 D (2 in.)	42 SA (15% in.)	42 SD (1% in.)	40 A (1½ in.)	40 SOC (1½ in.)	50 A (2 in.)
ICS 40	1 Pilot	027H4020	*	027H4024	027H4023	027H4021	027H4022	*
103 40	3 Pilots <sup>(4)</sup>	027H4030	*	027H4034	027H4033	027H4031	027H4032	*

<sup>(4)</sup> Including one blanking plug (A+B)

<sup>(2)</sup> Including bolts
(3) Including bolts and one blanking plug


<sup>\*</sup> Select from parts programme




## **ICS 50**

# Ordering from the parts programme

Figure 49: Example (select from table ICV 50 valve body w/different connections, table ICS 50 function module and table ICS 50 top cover)



### Figure 50: ICV 50 valve body w/different connections



#### Table 36: ICV 50 valve body w/different connections

······································						
Connections	Code Number					
50 D (2 in.)	027H5120					
65 D (2½ in.)	027H5124					
54 SD (21/8 in. SA)	027H5123					
50 A (2 in.)	027H5121					
50 SOC (2 in.)	027H5122					
65 A (2½ in.)	027H5125					

**D** = Butt-weld DIN

**A** = Butt-weld ANSI

**J** = Butt-weld JIS

**SOC** = Socket weld ANSI

**SD** = Solder DIN

**SA** = Solder ANSI

**FPT** = Female Pipe Thread

## Figure 51: function module







Table 37: ICS 50 function module

Description	Code Number
ICS 50	027H5200 <sup>(1)</sup>

<sup>(1)</sup> Including gasket and O-rings

Figure 52: ICS 1







Table 38: ICS 50 top cover


Description	Code Number
Top cover 1 Pilot	027H5172 <sup>(2)</sup>
Top cover 3 Pilots	027H5173 <sup>(3)</sup>

## Ordering complete factory assembled valve

(body, function module and top cover)

Figure 54: 1 pilot





**Table 39: Connections** 

		Available connections						
		50 D (2 in.)	65 D (2½ in.)	54 SD (2½ in. SA)	65 A (2½ in.)	50 A (2 in.)	50 SOC (2 in.)	
ICS 50	1 Pilot	027H5020	*	027H5023	*	027H5021	027H5022	
103 30	3 Pilots <sup>(4)</sup>	027H5030	*	027H5033	*	027H5031	027H5032	

<sup>(4)</sup> Including one blanking plug (A+B)

<sup>(2)</sup> Including bolts
(3) Including bolts and one blanking plug

<sup>\*</sup> Select from parts programme



## **ICS 65 and ICS 80**

## Ordering from the parts programme

Figure 56: Example (select from table ICV 65 valve body w/different connections, table ICS 65 and ICS 80 function module and table ICS 65/80 top cover)




Figure 57: ICV 65 valve body w/different connections




Table 40: ICV 65 valve body w/different connections

Connections	Code Number
65 D (2½ in.)	027H6120
65 A (2½ in.)	027H6121
65 J (2½ in.)	027H6122
80 D (3 in.)	027H6126
80 A (3 in.)	027H6127
67 SA (2 % in.)	027H6125
76 SD (3 in.)	027H6124
65 SOC (2½ in.)	027H6123

**D** = Butt-weld DIN

**A** = Butt-weld ANSI

**J** = Butt-weld JIS

**SOC** = Socket weld ANSI

**SD** = Solder DIN

**SA** = Solder ANSI

**FPT** = Female Pipe Thread



Figure 58: function module




Table 41: ICS 65 and ICS 80 function module

Description	Code Number
ICS 65	027H6200 <sup>(1)</sup>
ICS 80	027H8200 <sup>(1)</sup>

<sup>(1)</sup> Including gasket and O-rings

Figure 59: ICS 1




Figure 60: ICS 3




Table 42: ICS 65/80 top cover

Description	Code Number
Top cover 1 Pilot (65)	027H6172 <sup>(2)</sup>
Top cover 3 Pilots (65)	027H6173 <sup>(3)</sup>
Top cover 1 Pilot (80)	027H8192 <sup>(2)</sup>
Top cover 3 Pilots (80)	027H8193 <sup>(3)</sup>

## Ordering complete factory assembled valve

(body, function module and top cover)

<sup>(2)</sup> Including bolts
(3) Including bolts and one blanking plug



Figure 61: 1 pilot





Figure 62: 3 pilots



**Table 43: Connections** 

Table 43. Connections									
			Available connections						
		65 D (2½ in.)	65 A (2½ in.)	65 SOC (2½ in.)	80 D (3 in.)	80 A (3 in.)	67 SA (2 <sup>5</sup> % in.)	76 SD (3 in.)	65 J (2½ in.)
ICS 65	1 Pilot	027H6020	027H6021	027H6023	*	*	027H6025	027H6024	*
103 03	3 Pilots <sup>(4)</sup>	027H6030	027H6021	027H6033	*	*	027H6035	027H6034	*
ICS 80	1 Pilot	*	*	*	027H8020	027H8021	*	*	*
103 80	3 Pilots <sup>(4)</sup>	*	*	*	027H8030	027H8031	*	*	*

<sup>(4)</sup> Including one blanking plug (A+B)

### • NOTE:

The capacity of the ICS 80 module can only be achieved when using the valve body with 80 D or A (3 in) connections.


If any other ICV 65 valve body is used the capacity of the complete valve will be reduced by approximately 6%.

## ICS 100 - 150

## Ordering complete factory assembled valve

(body, function module and top cover)

Figure 63: ICS 100



**Table 44: Connections** 


	Connections				
	100 D (4 in.) 100 A (4 in.) 100 A (4 in.) 100 A (4 in.) with % in. NPT pres				
ICS 100 <sup>(1)</sup>	027H7120	027H7121	027H7122		

<sup>(1)</sup> Including two blanking plugs (A) and one sealing plug (B)

<sup>\*</sup> Select from parts programme




Figure 64: ICS 125



**Table 45: Connections** 

	Connections		
	125 D (5 in.)	125 A (5 in.)	125 A (5 in.) with % in. NPT pressure outlet
ICS 125 <sup>(1)</sup>	027H7140	027H7141	027H7142

Figure 65: ICS 150



**Table 46: Connections** 

	Connections		
	150 D (6 in.)	150 A (6 in.) with $\%$ in. NPT pressure outlet	
ICS 150 <sup>(1)</sup>	027H7160	027H7161	027H7162

**Spare parts:**Please see Al245486497115

# **Accessories**

Figure 66: Top cover







Table 47: Top covers

Top covers				
Consist of: Top cover complete with manuel spindle, and gasket	Size	Code number		
	ICS 100	027H7123		
	ICS 125	027H7143		
	ICS 150	027H7163		

#### **ICV PM flanged valve housings**

ICV PM flanged valve housings can replace the PM valves on already installed refrigeration systems.

Figure 67: ICV PM flanged valve housing



### **Pressure range**

The ICV PM valve housing is designed for a max. working pressure of 28 bar (406 psig) and therefore a suitable replacement for PM valves in the service market. They also offer the same drop-in dimensions as the PM valves.


Table 48: Top covers

Description	Code no.
ICV 25 PM Valve housing	027H2119 <sup>(1)</sup>
ICV 32 PM Valve housing	027H3129 <sup>(1)</sup>
ICV 40 PM Valve housing	027H4128 <sup>(1)</sup>
ICV 50 PM Valve housing	027H5127 <sup>(2)</sup>
ICV 65 PM Valve housing	027H6128 <sup>(2)</sup>

<sup>(1)</sup> Includes ICV PM valve housing, flange gaskets and flange bolts.

Function modules and top covers must be ordered separately (see the section "Ordering").

Figure 68: ICV PM



### ICV (H)A4A flanged valve housings

ICV (H)A4A flanged valve housings can replace the (H)A4A valves on already installed refrigeration systems.

<sup>(2)</sup> Includes ICV PM valve housing, flange gaskets, flange bolts and flange nuts.



Figure 69: ICV (H)A4A flanged valve housing



### **Pressure range**

The ICV (H)A4A valve housing is designed for a max. working pressure of 28 bar (406 psig) and therefore a suitable replacement for (H)A4A valves in the service market. They also offer the same drop-in dimensions as the (H)A4A valves.

Table 49: ICV Valve housing

·······	
Description	Code no.
ICV 25 (H)A4A Valve housing	027H2304 <sup>(3)</sup>
ICV 32 A4A Valve housing	027H3130
ICV 32 HA4A Valve housing	027H3131
ICV 40 (H)A4A Valve housing	027H4129
ICV 50 (H)A4A Valve housing	027H5128
ICV 65 (H)A4A Valve housing	027H6129

<sup>(3)</sup> Includes ICV (H)A4A valve housing, flange gaskets, flange bolts and flange nuts.

Function modules and top covers must be ordered separately (see the section "Ordering").

Figure 70: ICV (H)A4A



# Pressure gauge connection (weld / solder)

Figure 71: Pressure gauge connection (weld / solder).




Table 50: Pressure gauge connection (weld / solder).

Description	Code no.
∅ 6.5 mm / ∅ 10 mm (∅ 0.26 in. / ∅ 0.39 in.) weld / solder	027B2035



Figure 72: Pressure gauge connection (weld / solder)




Table 51: Pressure gauge connection (weld / solder)


Accessories	size	L	L,	B <sub>1</sub>	B <sub>2</sub>	B <sub>3</sub>	B <sub>4</sub>	B <sub>5</sub>
	mm in.	66 2.60	54 2.13	AF 19	AF 22	G ¼ A	G % A	Ø6.5 / Ø10

# Pressure gauge connection, ¼ in. flare (self-closing)

Pressure gauge connection, ¼ in. flare (self-closing) Must not be used in R 717 plant.

Figure 73: ¼ in. flare (self-

closing)



**Table 52: Connection** 

Description	Code no.
¼ in. flare	027B2041

Figure 74: 1/4 in. flare (self-

closing)





Table 53: Pressure gauge connection, 1/4 in. flare (self-closing)

Accessories	В	B <sub>1</sub>	B <sub>2</sub>
¼ in. flare	G 1/4 A	AF 19	¼ in. flare



# Pressure gauge connection (cutting ring)


Figure 75: Pressure gauge connection (cutting ring).



**Table 54: Cutting ring connection** 

Description	Code no.
Cutting ring connection, 6 mm	027B2063
Cutting ring connection, 10 mm	027B2064

Figure 76: Cutting ring connection



**Table 55: Pressure gauge connection (cutting ring)** 

	<i>5 5</i>					
Accessories		L	L1	В	B1	B2
6 mm	mm in.	27 1.06	39 1.54	G ¼ A	AF 19	AF 14
10 mm	mm in.	29 1.14	40 1.57	G 1/4 A	AF 19	AF 14

## Multi-function tool

Table 56: Multi-function tool

Description	Code no.	
Multi-function tool for ICS 25-65	027H0180 / 027H0181	

Figure 77: Multi-function tool



The multi-funktion tool can be used for:

- Removing the ICS function module
- Operating the manual spindle

For further information please see the instruction PIHU0A.



# Pressure gauge connection

Figure 78: Connection




Table 57: Pressure gauge connection

Description	Code no.	
¼ FPT	027B2062	

Figure 79: Pressure gauge connection





Table 58: Pressure gauge connection

Accessories		L	L <sub>1</sub>	В	B <sub>1</sub>	B <sub>2</sub>
	mm in.	23 0.91	35.5 1.40	G ¼ A	AF 22	1/4 FPT

# External pilot connection


Figure 80: Connection



**Table 59: ICS connections** 

ICS	Description	Code no.
5 - 80	External pilot connection (incl. damping orifice, D: 1.0 mm)	027F1048
5 - 150	Accessory bag with seal and O-ring for pilot valve	027F0666
100 - 150	External pilot connection (incl. damping orifice, D: 1.8 mm)	027F1049

Figure 81: External pilot connection






## Table 60: External pilot connection

Accessories		н	Н,	OD	В	B <sub>1</sub>	B <sub>2</sub>
	mm in.	90 3.54	66 2.60	18 0.71	AF 32	AF 32	M 24 × 1.5

# Blanking plug for pilot valves

Figure 82:







Table 61: Blanking plug

Description	Code no.
Blanking plug	027F1046

Figure 84: FIA Straightway



**Table 62: Recommended filters** 

Recommended filters					Filter element for liquid line		Filter element for suction line		
						150 mesh	100 mesh	72 mesh	38 mesh
Filter Type	Size	D	А	FPT	soc	100 my	150 my	250 my	500 my
FIA Straightway	20 (¾ in.)	148B5343	148B5347	148B5349	148B5348	148H3122	148H3124	148H3126	148H3128
FIA Straightway	25 (1 in.)	148B5443	148B5447	148B5449	148B5448	148H3123	148H3125	148H3127	148H3129
FIA Straightway	32 (1¼ in.)	148B5544	148B5552	148B5549	148B5548	148H3123	148H3125	148H3127	148H3129
FIA Straightway	40 (1½ in.)	148B5625	148B5644		148B5645	148H3123	148H3125	148H3127	148H3129
FIA Straightway	50 (2 in.)	148B5713	148B5716		148B5717	148H3157	148H3130	148H3138	148H3144
FIA Straightway	65 (2½ in.)	148B5813	148B5815				148H3131	148H3139	148H3145
FIA Straightway	80 (3 in.)	148B5906	148B5908				148H3119	148H3120	148H3121
FIA Straightway	100 (4 in.)	148B6007	148B6009				148H3132	148H3140	148H3146
FIA Straightway	125 (5 in.)	148B6106	148B6108				148H3133	148H3141	148H3147
FIA Straightway	150 (6 in.)	148B6203	148B6205				148H3134	148H3142	148H3148



## Certificates, declarations, and approvals

The list contains all certificates, declarations, and approvals for the product. Individual code number may have some or all of these approvals, and certain local approvals may not appear on the list.

Some approvals may change over time. You can check the most current status at danfoss.com or contact your local Danfoss representative if you have any questions.

### Table 63: The ICV valve approvals



The ICV valve concept is designed to fulfill global refrigeration requirements.

For specific approval information, please contact Danfoss.

The ICS valves are approved in accordance with the European standard specified in the Pressure Equipment Directive and are CE marked.

### Table 64: ICS valves

ICS valves						
Nominal bore	DN≤ 25 (1 in.)	DN 32-65 (1¼ - 2½ in.)	DN 80-125 (3 - 5 in.)			
Classified for	Fluid group I					
Category	Article 3, paragraph 3	II	III			

#### **Table 65: Certificates and declarations**

File name	Document type	Document topic	Approval authority
RU Д-DK.БЛ08.В.00191_18	EAC Declaration	Machinery & Equipment	EAC
0045 202 1204 Z 00354 19 D 001(00)	Pressure - Safety Certificate	-	TÜV
RU Д-DK.БЛ08.В.00189_18	EAC Declaration	EMC	EAC
RU Д-DK.PA01.B.72054_20	EAC Declaration	PED	EAC
RU C-DK.БЛ08.B.01093_20	Pressure - Safety Certificate	PED	EAC
033F0685.AK	EU Declaration	EMCD/PED	Danfoss
033F0691.AE	Manufacturers Declaration	RoHS	Danfoss
0045 202 1204 Z 00355 19 D 001(00)	Pressure - Safety Certificate	-	TÜV
19.10325.266	Marine - Safety Certificate	-	RMRS



## Online support

Danfoss offers a wide range of support along with our products, including digital product information, software, mobile apps, and expert guidance. See the possibilities below.

#### **The Danfoss Product Store**



The Danfoss Product Store is your one-stop shop for everything product related—no matter where you are in the world or what area of the cooling industry you work in. Get quick access to essential information like product specs, code numbers, technical documentation, certifications, accessories, and more.

Start browsing at store.danfoss.com.

### **Find technical documentation**



Find the technical documentation you need to get your project up and running. Get direct access to our official collection of data sheets, certificates and declarations, manuals and guides, 3D models and drawings, case stories, brochures, and much more.

Start searching now at www.danfoss.com/en/service-and-support/documentation.

#### **Danfoss Learning**



Danfoss Learning is a free online learning platform. It features courses and materials specifically designed to help engineers, installers, service technicians, and wholesalers better understand the products, applications, industry topics, and trends that will help you do your job better.

Create your Danfoss Learning account for free at www.danfoss.com/en/service-and-support/learning.

#### Get local information and support



Local Danfoss websites are the main sources for help and information about our company and products. Find product availability, get the latest regional news, or connect with a nearby expert—all in your own language.

Find your local Danfoss website here: www.danfoss.com/en/choose-region.

#### **Spare Parts**



Get access to the Danfoss spare parts and service kit catalog right from your smartphone. The app contains a wide range of components for air conditioning and refrigeration applications, such as valves, strainers, pressure switches, and sensors.

Download the Spare Parts app for free at www.danfoss.com/en/service-and-support/downloads.

## Coolselector®2 - find the best components for you HVAC/R system



Coolselector®2 makes it easy for engineers, consultants, and designers to find and order the best components for refrigeration and air conditioning systems. Run calculations based on your operating conditions and then choose the best setup for your system design.

Download Coolselector®2 for free at coolselector.danfoss.com.

#### Danfoss A/S

Climate Solutions • danfoss.com • +45 7488 2222

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues descriptions, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or further that the sending Dantoss reserves the right to after its produce miniocities and the product.

All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.