ENGINEERING TOMORROW



Data Sheet

Shut-off ball valve Type **GBC (90 bar)** and **GBCT (140 bar)**

For CO₂ application





Danfoss shut-off ball valves, type GBC (90 bar), GBCT (140 bar) are manually operated shut-off valves for CO₂ refrigeration systems, in order to open and to shut off inner flow path by operating the valve spindle.

The valves are specifically designed for intrinsic standstill security, meaning that the valves can withstand pressures normally arising when the refrigeration system is shut off, i.e. during serving or during unexpected power failure.

The valve structure and materials are designed and tested specifically for use with CO₂ refrigerant.

GBC (90 bar) valves are designed to use in subcritical CO₂ refrigeration systems. GBCT (140 bar) valves are approved for use in transcritical CO₂ systems.



Features

Features of GBC (90 bar)

- Maximum working pressure: 90 bar / 1305 psig
- Applicable for subcritical CO₂ refrigeration systems
- Bidirectional flow
- Bleed hole design to prevent liquid entrapment when the valve is closed
- Able to isolate both directions during service
- Sealing material especially for CO₂ to ensure long term product reliability
- Stainless steel body with Cu-plated stainless steel tube easy and fast brazing for systems with copper piping
- · Available of access port version for all sizes
- Meet demand for lead-free and full RoHS compliance
- UL/cUL Listed, complies with Pressure Equipment Directive 2014/68/EU

Features of GBCT (140 bar)

- Maximum working pressure: 140 bar / 2031 psig
- Applicable for transcritical CO₂ refrigeration systems
- · Bidirectional flow
- Bleed hole design to prevent liquid entrapment when the valve is closed
- Sealing material especially for CO₂ to ensure long term product reliability
- Version with reinforced copper-iron tube extensions to allow easy torch-brazing installation for systems with K65 piping
- Version with stainless-steel butt welding connections, suitable for systems with stainless-steel piping
- Available of access port version for all sizes
- UL/cUL Listed, complies with Pressure Equipment Directive 2014/68/EU



Applications


Typical applications for CO₂ ball valves are:

- Display cases
- Cold rooms
- Rack/Pack units

Danfoss CO₂ ball valves are designed for the following refrigerant cycles:

- GBC with PS = 90 bar, Cu-plated stainless steel connections equipped, for subcritical systems
- GBCT with PS = 140 bar, copper (K65) / stainless steel connections equipped, for transcritical systems

Figure 1: Application



HP High Pressure (120-140 bar) HP Receiver Pressure (60-90 bar) LP Suction Pressure MT (35-55 bar) LP Suction Pressure LT (25-30 bar)



Media

Table 1: Media

Refrigerants	R 744 (CO ₂)
Refrigerant oil	POE,PVE,PAG(Not compatible for Mineral oil and PAO)

• NOTE:

For the application use with R744 as part of a secondary loop or cascade:

- 1. The design pressure of the refrigerant containing component is not less than the design pressure of the associated components.
- 2. The component is not provided with any pressure relief or pressure regulating relief valve and that a sufficient number of valves having capacity deemed adequate shall be field installed on the refrigeration system.
- 3. When the refrigeration system is de-energized, venting of R744 may occur through the pressure regulating relief valves, and may need to be recharged, but the valve should not be defeated or bypassed.
- 4. A sufficient number of pressure relief and pressure regulating valves may need to be provided based upon system capacity and located such that no stop valve is provided between the relief valve and the parts or section of the system being protected.



Product specification

Technical data

Table 2: Technical data

Technical data	GBC	GBCT					
Max. working pressure	90 bar / 1305 psig	140 bar / 2031 psig					
Media temperature range	-40 °C – 100 °C / -40 °F – 212 °F	-40 °C – 149 °C / -40 °F – 300 °F					
Flow direction	Bi flow	Bi flow					
Isolation orientation during service	Bi-directional	Uni-directional (following GBCT instruction)					
Environmental transport/storage temperature and humidity	-40 – 65 °C /-40 – 150 °F. Air humidity: RH≤95%.						

Mounting of GBCT:

Danfoss recommends that GBCT valves are installed so that the HP side is oriented towards the highest pressure side of the system when the valve is in the closed position. The ball valve will only internally seal in closed position when flow direction is from HP to LP.


Figure 2: Marking of GBCT



Table 3: Marking of GBCT

3	
Inscription	Explanation
	Indicates where the bleed hole of ball is located and Danfoss recommends the HP side is oriented towards the highest pressure side of system when valve is in closed position.
"LP"	Indicates the side without bleed hole and shall be oriented towards to the low pressure side of system when valve is in closed position.

Figure 3: Flow direction for GBCT






GBCT CAUTION - RISK OF HIGH PRESSURE

Do not close with CO2 liquid temperature below ambient. This component shall be installed along with a pressure relief valve set to discharge at no higher than the rated pressure of this component. This component is intended for systems in which the critical pressure of the refrigerant will be exceeded. The relief valve shall comply with the requirements of ASME Section VIII, be marked "UV" and sized based on the refrigeration system capacity. An orange Hanging tag is added on all valves as per requirement of UL certificate.

Figure 4: Hanging tag of GBCT



Identification

Relevant product data is available on the product and box label. An example of a box label and product label are shown, including an explanation of the content.

Figure 5: Box label



Figure 6: Product label




Table 4: Product and label text

Position	Inscription	Explanation
Box label; Product label	Shut-off ball valve	Product name
Box label; Product label	GBC 42s H	Product type
Box label; Product label	009L5569	Code number for ordering
Box label	Bi-flow	Flow type
Box label	Straightway	Direction
Box label	R744	Refrigerant
Box label	42 mm ODF	Connection size and type
Box label; Product label	PS 90 bar/MWP 1305 psig	Max. working pressure in bar and psig
Box label; Product label	BE0522A	Code for production place and time (BE = Wuqing, week 05, year 2022, weekday A = Monday)
Box label; Product label	MADE IN CHINA	Manufacturing site acc. to EN standards
Box label	EAN code	Barcode for individual code no. identification according to EAN standard
Product label	TS -40/+100°C -40/+212°F	Media temperature range
Box label; Product label	Additional information: Relevant approval authority logos	-

Design and materials

Direct flow gives maximum through-flow with minimum pressure drop across valve. The combination of laserwelded valve body (2) and valve tail (4), ball seat/seal (3), double O-ring seal in spindle (6), and cap seal (7) provides the best tightness.



Figure 7: GBC with Cu-plated stainless steel tube




Figure 8: GBCT with copper tube




Figure 9: GBCT with stainless steel tube




Table 5: Design and materials

D '4'	Possibility	Mat	erial
Position	Description	GBC	GBCT
1	Connection tube	Cu-plated stainless steel	Copper/Stainless steel
2	Valve body	Stainless steel	Brass
3	Ball seat	PTFE	PTFE
4	Valve tail	Stainless steel	Brass
5	Ball	Stainless steel	Stainless steel
6	Double O-ring seal in spindle	EPDM	FKM
7	Cap seal	PTFE	PTFE
8	Seal cap	Aluminum	Brass
9	Spindle	Stainless steel	Stainless steel/Brass
10	Pin	Stainless steel	Stainless steel
11	Guide ring	PTFE	PTFE
12	Schrader valve	Brass	Brass
13	Bleed hole	-	-

Dimensions

We have chosen to show dimensions of the major versions.

You will find downloadable dimension drawings for individual code numbers on Danfoss store as part of the Visuals tab for individual code numbers.



Weights also differ depending on the design of the individual code numbers. Weights are available as part of the technical data for individual code numbers on Danfoss store.

GBC solder ODF/ODF, Cu plated stainless steel connections

Figure 10: GBC solder ODF/ODF, Cu plated stainless steel connections




Table 6: GBC solder ODF/ODF, Cu plated stainless steel connections

		Connec- tion	Connection tol- erance	Н	H1	L	L1	L2	L3	D	d	Weight	Code	e no.
Туре	Size	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[kg]	without access port	with access port
GBC 6s H	1/4 in.	6.35		43	12	139	7	72.4	31	11	1.5	0.13	009L5415	009L5581
GDC 0311	6 mm	6		43	12	139	,	72.4	31	11	1.5	0.13	009L5395	009L5580
GBC 10s H	3/8 in.	9.52		43	12	139	9	72.4	31	11	1.5	0.13	009L5416	009L5582
GDC 105 H	10 mm	10		43	12	139	9	72.4	31	11	1.5	0.13	009L5396	009L5583
CDC 12: 11	½ in.	12.7	+0.065/+0.155	42	12	161	9	83.4	31	11	1.5	0.14	009L5417	009L5585
GBC 12s H	12 mm	12	+0.005/+0.155	43	12	101	9	83.4	31	11	1.5	0.14	009L5397	009L5584
GBC 16s H	5⁄8 in.	16		50	147	161	12	02.6	21	1.4	1.5	0.22	0001 5410	0001 5500
	16 mm	10		50 14.7 161 12 83.6	31	14	1.5	0.22	009L5418	009L5586				
GBC 18s H	3/4 in.	19.05		58	18.8	105	12	95.8	37	19	1.5	0.4	009L5419	009L5588
(1)	18 mm	18		36	10.0	100	12	93.0	3/	19	1.5	0.4	009L5399	009L5587
GBC 22s H ⁽¹⁾	7⁄8 in. 22 mm	22.22		58	18.8	185	17	95.8	37	19	1.5	0.4	009L5420	009L5589
	1 in.	25.4											009L5400	009L5590
GBC 25s H ⁽¹⁾	25 mm	25	+0.075/+0.185	80	25	208	20	111	44	25.5	2	0.85	-	-
	1 1/8 in.	28.58											009L5526	009L5565
GBC 28s H ⁽¹⁾	28 mm	28		80	25	208	20	111	44	25.5	2	0.85	009L5406	009L5566
	1 3/8 in.		0.00/.000											
GBC 35s H ⁽¹⁾	35 mm	35		0.004.0.00	89	30	251	20	132	44	32	2	1.3	009L5410
CDC 42 1177	1 5/8 in.	41.28	+0.09/+0.23	446	25	204	20						009L5529	009L5568
GBC 42s H ⁽¹⁾	42 mm	42		110	35	281	29	149	56	38	2	2.2	009L5411	009L5569

⁽¹⁾ GBC 18s H~42s H will be available in June, 2024



GBCT solder ODF/ODF, copper connections

Figure 11: GBCT solder ODF/ODF, copper connections




Table 7: GBCT solder ODF/ODF, copper connections

Tuno	Size	Con- nec- tion	Connection tolerance	н	H1	L	L1	L3	L4	L5	М	D	Weight	Code	e no.
Туре		[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[kg]	without access port	with ac- cess port
GBCT 6s	½ in.	6.35		57	14	127	7	69	22	N/A	M4 × 0.7	13	0.2	009L6415	-
			57	14	127	7	55	N/A	44	N/A	13	0.3	-	009L6581	
GBCT 10s	³⁄8 in.	9.52		57	14	132	9	72	22	N/A	M4 × 0.7	13	0.2	009L6416	-
				57	14	132	9	58	N/A	46	N/A	13	0.3	-	009L6582
GBCT 12s	¹⁄2 in.	12.70	+0.051/+0.155	57	14	139	10	75	22	N/A	M4 × 0.7	13	0.2	009L6417	-
				57	14	139	10	61	N/A	50	N/A	13	0.3	-	009L6585
GBCT 16s	5⁄8 in.	15.88		57	14	148	13	80	22	N/A	M4 × 0.7	13	0.2	009L6418	-
				57	14	148	13	66	N/A	54	N/A	13	0.3	-	009L6586
GBCT 18s	3/4 in.	19.05		87	32	148	17	78	N/A	30	N/A	19	0.7	009L6419	009L6588
GBCT 22s	7/8 in.	22.22		87	32	185	20	96	N/A	40	N/A	19	0.7	009L6420	009L6589
GBCT 28s	1 1/8 in.	28.58	+0.075/+0.185	102	37	185	24	95	N/A	40	N/A	25	1.3	009L6406	009L6451
GBCT 35s	1 3/8 in.	34.93	+0.0/5/+0.185	103	35	205	25	102	N/A	44	N/A	32	2.0	009L6410	009L6453
GBCT 42s	1 5⁄8 in.	41.28	+0.075/+0.203	113	40	240	28	120	N/A	50	N/A	38	2.9	009L6411	009L6454
GBCT 54s	2 1/8 in.	53.98	TU.U/ 3/ TU.203	144	52	275	35	138	N/A	56	N/A	51	6.1	009L6412	009L6456



GBCT butt weld, stainless steel connections

Figure 12: GBCT butt weld, stainless steel connections




Table 8: GBCT (ODE)

	ODE	Н	H1	L	L3	L4	L5	М	D	Weight	Code no.
Туре	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[kg]	with access port
GBCT 10 D	10.20	57	14	132	57	22	29	M4 x 0.7	13	0.27	009L6701
GBCT 13 D	13.50	57	14	139	61	22	32	M4 x 0.7	13	0.28	009L6702
GBCT 17 D	17.20	57	14	148	66	22	36	M4 x 0.7	13	0.29	009L6703
GBCT 21 D	21.30	72	20	185	86	30	58	M4 x 0.7	19	0.54	009L6704
GBCT 27 D	26.90	92	28	185	84	38	53	M4 x 0.7	25	1.08	009L6705
GBCT 34 D	33.70	103	35	205	94	48	61	M6 x 1.0	32	2.08	009L6706
GBCT 42 D	42.40	113	40	240	114	55	72	M6 x 1.0	38	3.13	009L6707
GBCT 48 D	48.30	144	52	275	132	74	81	M6 x 1.0	51	6.23	009L6708
GBCT 60 D	60.30	144	52	275	132	74	81	M6 x 1.0	51	6.51	009L6709

ODE = Outside Diameter External

Table 9: GBCT (NPS)

Table 3. Gi	Table 9. dec 1 (141 5)											
	NPS	Н	H1	L	L3	L4	L5	М	D	Weight	Code no.	
Туре	[in.]	[in.]	[in.]	[in.]	[in.]	[in.]	[in.]	[in.]	[in.]	[lbs]	with acess port	
GBCT 10 D	1/8	2.2	0.6	5.2	2.2	0.9	1.1	M4 x 0.7	0.5	0.60	009L6701	
GBCT 13 D	1/4	2.2	0.6	5.5	2.4	0.9	1.3	M4 x 0.7	0.5	0.62	009L6702	
GBCT 17 D	3/8	2.2	0.6	5.8	2.6	0.9	1.4	M4 x 0.7	0.5	0.64	009L6703	
GBCT 21 D	1/2	2.8	0.8	7.3	3.4	1.2	2.3	M4 x 0.7	0.7	1.19	009L6704	
GBCT 27 D	3/4	3.6	1.1	7.3	3.3	1.5	2.1	M4 x 0.7	1.0	2.38	009L6705	
GBCT 34 D	1	4.1	1.4	8.1	3.7	1.9	2.4	M6 x 1.0	1.3	4.59	009L6706	
GBCT 42 D	1 1/4	4.4	1.6	9.4	4.5	2.2	2.8	M6 x 1.0	1.5	6.90	009L6707	
GBCT 48 D	1 ½	5.7	2.1	10.8	5.2	2.9	3.2	M6 x 1.0	2.0	13.7	009L6708	
GBCT 60 D	2	5.7	2.1	10.8	5.2	2.9	3.2	M6 x 1.0	2.0	14.4	009L6709	

NPS = National Pipe Size



Connection Diagrams

Connection diagrams of GBC (90 bar)

Туре	Connection type	Connection Size					
		6 mm	1⁄4 in.				
		10 mm	3⁄8 in.				
		12 mm	½ in.				
		16 mm	5⁄8 in.				
GBC (90bar)	Solder ODF	18 mm	³⁄₄ in.				
GBC (90bar)	Solder ODF	22 mm	₹/8 in.				
		-	1 in.				
		28 mm	1 ½ in.				
		35 mm	1 3⁄8 in.				
		42 mm	1 5⁄8 in.				

Connection diagrams of GBCT (140 bar)


Туре	Connection type	Connection Size					
			¼ in.				
			3/8 in.				
			½ in.				
			5/8 in.				
	Solder ODF	_	¾ in.				
	Solder ODF	-	⁷ ⁄8 in.				
			1 ½ in.				
			1 3/8 in.				
			1 5⁄8 in.				
GBCT (140bar)			2 1/8 in.				
		10.2 mm	1⁄8 in.				
		13.5 mm	¼ in.				
		17.2 mm	3⁄8 in.				
		21.3 mm	½ in.				
	Butt weld	26.9 mm	¾ in.				
		33.7 mm	1 in.				
		42.4 mm	1 ¼ in.				
		48.3 mm	1 ½ in.				
		60.3 mm	2 in.				



Ordering

GBC solder ODF/ODF, Cu plated stainless steel connections

Figure 13: GBC without access port, solder ODF






Table 10: GBC solder ODF/ODF, Cu-plated stainless steel connections

	Code no.		Conn	Connection		Cv ⁽¹⁾	Multi pack	PED catego- ry	Max. work- ing pressure	Media tem-
Туре	without ac- cess port	with access port	[in.]	[mm]	[m³/h]	[gal/min]	Qty/ pack	[Fluid Group 2]	PS/MWP	perature range
GBC 6s H	009L5415	009L5581	1/4	-	1.78	2.06	30			
GDC 03 II	009L5395	009L5580	-	6	1.78	2.06	30		90 bar / 1305 psig	
GBC 10s H	009L5416	009L5582	3/8	-	7.00	8.09	30			
GDC 105 FI	009L5396	009L5583	-	10	7.00	8.09	30			-40 °C ~ +100 °C / -40 °F ~ +212 °F
GBC 12s H	009L5417	009L5585	1/2	-	8.00	9.25	30			
GDC 125 FI	009L5397	009L5584	-	12	8.00	9.25	30			
GBC 16s H	009L5418	009L5586	5/8	16	12.40	14.33	25	Art. 4.3		
GBC 18s H (2)	009L5419	009L5588	3/4	-	31.00	35.84	25	A11. 4.5		
GDC 105 H	009L5399	009L5587	-	18	31.00	35.84	25			
GBC 22s H ⁽²⁾	009L5420	009L5589	7/8	22	25.47	29.44	25			
GBC 25s H ⁽²⁾	009L5400	009L5590	1	-	55.93	64.66	5			
GBC 28s H ⁽²⁾	009L5526	009L5565	1 1/8	-	65.85	76.12	5			
GDC 203 П'-'	009L5406	009L5566	-	28	65.85	76.12	5			
GBC 35s H ⁽²⁾	009L5410	009L5567	1 3/8	35	103.05	119.13	5			
GBC 42s H ⁽²⁾	009L5529	009L5568	1 5/8	-	175.41	202.78	4	Cat. I		
GDC 425 FI(2)	009L5411	009L5569	-	42	175.41	202.78	4	Cdt. I		

⁽¹⁾ Calculated based on fluid dynamic equations

Solder connection reference standard ISO 2016 (≈EN 1254-1)

⁽²⁾ GBC 18s H~42s H will be available in June, 2024



GBCT solder ODF/ODF, copper connections

Figure 15: GBCT without access port, solder ODF



Figure 16: GBCT with access port, solder ODF



Table 11: GBCT solder ODF/ODF, copper connections

Type	Code no		Connection		Kv	Cv	Multi pack	Max work- ing pressure	Media tem-	PED catego- ry
	without ac- cess port	with access port	[in.]	[mm]	[m3/h]	[gal/min]	qty/pack	PS/MWP	perature range	[Fluid Group 2]
GBCT 6s	009L6415	009L6581	1/4	-	0.9	1.0	30		-40 °C − 149 °C / -40 °F − 300 °F	Art. 4.3
GBCT 10s	009L6416	009L6582	3/8	-	3.7	4.3	30			
GBCT 12s	009L6417	009L6585	1/2	-	5.4	6.2	30			
GBCT 16s	009L6418	009L6586	5/8	-	10.4	12.1	30			
GBCT 18s	009L6419	009L6588	3/4	-	16.4	19.0	18	140 bar /		
GBCT 22s	009L6420	009L6589	7/8	-	23.7	27.5	18	2031 psig		
GBCT 28s	009L6406	009L6451	1 1/8	-	42.3	48.9	4			
GBCT 35s	009L6410	009L6453	1 3/8	-	67.1	77.6	4			
GBCT 42s	009L6411	009L6454	1 5/8	-	83.1	96.1	4			Cat. I
GBCT 54s	009L6412	009L6456	2 1/8	-	171.3	198.0	2			

GBCT butt weld, stainless steel connections

Figure 17: GBCT butt weld, stainless steel connections



Туре –	Code no		Connection		Kv	Cv	Multi pack	Max. work- ing pressure		PED catego- ry
	without ac- cess port	with access port	NPS [in.]	ODE [mm]	[m3/h]	[gal/min]	qty/pack	PS/MWP	range	[Fluid Group 2]
GBCT 10 D	-	009L6701	/	10.3	3.5	4	30		-40 °C – 149 °C / -40 °F – 300 °F	Art. 4.3 Cat. I
GBCT 13 D	-	009L6702	/	13.5	4.2	4.9	30			
GBCT 17 D	-	009L6703	/	17.2	8.9	10.3	30			
GBCT 21 D	-	009L6704	/	21.3	18	21	16	4401 /		
GBCT 27 D	-	009L6705	/	26.9	36	42	4	140 bar / 2031 psig		
GBCT 34 D	-	009L6706	1	33.7	64	74	4			
GBCT 42 D	-	009L6707	1.25	42.4	96	111	4			
GBCT 48 D	-	009L6708	1.5	48.3	169	196	2			
GBCT 60 D	-	009L6709	2	60.3	202	234	2			



NPS = National Pipe Size

ODE = Outside Diameter External

Butt-weld connection reference standard EN 10220

Spare parts

Figure 18: Seal cap kit



Table 12: Seal cap kit

Tuno	Valve conn	ection size	Industrial pack [pcs]	Code no.	
Туре	[inch]	[mm]	iliuustiiai pack [pcs]		
GBC 6s H - 12s H	1/4 -/	6 – 22	4	009L5209	
GBC 16s H - 22s H	5/8 – 7/8	16 – 22	4	009L5210	
GBC 25s H - 35s H	1 - 1 ³ /8	25 - 35	2	009L5211	
GBC 42s H	1 5/8	42	2	009L5212	

Figure 19: Schrader valve



Туре	Industrial pack [pcs.]	Code no.
GBC 6s H - 42s H	10	009L5213

• NOTE:

The spare parts are only for GBC. For GBCT spare parts, please consult Danfoss



Certificates, declarations, and approvals

The list contains all certificates, declarations, and approvals for this product type. Individual code number may have some or all of these approvals, and certain local approvals may not appear on the list.

Some approvals may change over time. You can check the most current status at danfoss.com or contact your local Danfoss representative if you have any questions.





Туре	File name	Document type	Document topic	Approval authority
GBCT	EAC RU Д-DK.PA01.B.02567_19	EAC Declaration	EAC	EAC RU
GBC	033F4001	Manufacturers Declaration	PED RoHS	Danfoss
GBC	033F4002	EU Declaration UK Declaration	PED UKCA	Danfoss
GBCT	033F4003	Manufacturers Declaration	PED	Danfoss
GBC	033F4006	Manufacturers Declaration	China RoHS	Danfoss
GBCT	033F4013	EU Declaration	PED	Danfoss
GBC	UA.TR.089.1015.04-22	Pressure - Safety Certificate	UA	LLC CDC EURO TYSK
GBC, GBCT	UL SA7200	Mechanical - Safety Certificate	UL 207	UL
GBCT	033F4052	UK Declaration	UKCA	Danfoss



Online support

Danfoss offers a wide range of support along with our products, including digital product information, software, mobile apps, and expert guidance. See the possibilities below.

The Danfoss Product Store



The Danfoss Product Store is your one-stop shop for everything product related—no matter where you are in the world or what area of the cooling industry you work in. Get quick access to essential information like product specs, code numbers, technical documentation, certifications, accessories,

Start browsing at store.danfoss.com.

Find technical documentation



Find the technical documentation you need to get your project up and running. Get direct access to our official collection of data sheets, certificates and declarations, manuals and guides, 3D models and drawings, case stories, brochures, and much more.

Start searching now at www.danfoss.com/en/service-and-support/documentation.

Danfoss Learning



Danfoss Learning is a free online learning platform. It features courses and materials specifically designed to help engineers, installers, service technicians, and wholesalers better understand the products, applications, industry topics, and trends that will help you do your job better.

Create your Danfoss Learning account for free at www.danfoss.com/en/service-and-support/learning.

Get local information and support



Local Danfoss websites are the main sources for help and information about our company and products. Find product availability, get the latest regional news, or connect with a nearby expert—all in your own language.

Find your local Danfoss website here: www.danfoss.com/en/choose-region.

Danfoss A/S

Climate Solutions • danfoss.com • +45 7488 2222

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues descriptions, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or further that the sending