ENGINEERING TOMORROW



**Data Sheet** 

# Hand operated regulating valve Type **REG-SA** and **REG-SB 10-65**

Assures favorable flow characteristics and accurate linear characteristics



REG-SA and REG-SB are angleway and straightway hand operated regulating valves, which act as normal shut-off valves in closed position.

The valves are available in two different versions – REG-SA and REG-SB designed for regulation purposes in liquid and expansion lines.

The valves are designed to meet the strict quality requirements on refrigerating installations specified by the international classification societies and are carefully designed to present favourable flow conditions and accurate linear characteristics.

REG-SA and REG-SB are equipped with vented cap and internal backseating enables replacement of the spindle seal whilst the valve is active, i.e. under pressure.



### **Features**

- Applicable to HCFC, HFC, R717 (Ammonia), R744 (CO<sub>2</sub>), Propane, Butane, Iso-Butane and Ethane.
- R717 Heat Pump and Propylene applications with replaced O-ring.
- · Modular Concept:
- Each valve housing is available with several different connection types and sizes.
- Possible to convert REG-SA or REG-SB to any other product in the FlexlineTM SVL family (shut-off valve, check & stop valve, check valve or strainer) just by replacing the complete top part.
- Fast and easy valve overhaul service. It is easy to replace the top part and no welding is needed.
- Designed to ensure perfect regulation
- · Internal backseating enables replacement of the spindle seal whilst the valve is active, i.e. under pressure.
- Easy to disassemble for inspection and possible repair.
- Long neck versions (DN 15 to DN 40) for insulated systems available from parts programme.
- Max. operating pressure: 52 bar (754 psig)
- Temperature range: -60 °C to +150 °C (-76 °F to +302 °F)
- Acts as a normal shut-off valve in closed position.
- Housing and bonnet material is low temperature steel according to requirements of the Pressure Equipment Directive and other international classification authorities.
- Exact capacity and setting of the valve can be calculated for all refrigerants by means of Coolselector®2 (Danfoss calculation and selection software).
- Classification: DNV, CRN, BV, EAC etc. To get an updated list of certification on the products please contact your local Danfoss Sales Company.



### Media

# **Refrigerants**

Applicable to HCFC, HFC, R717 (Ammonia), R744 (CO<sub>2</sub>), Propane, Butane, Iso-Butane and Ethane.

R717 Heat Pump and Propylene applications with replaced O-ring.

# **New refrigerants**

Danfoss products are continually evaluated for use with new refrigerants depending on market requirements.

When a refrigerant is approved for use by Danfoss, it is added to the relevant portfolio, and the R number of the refrigerant (e.g. R513A) will be added to the technical data of the code number. Therefore, products for specific refrigerants are best checked at store.danfoss.com/en/, or by contacting your local Danfoss representative.



# **Product specification**

# **Design**

#### Housing

Housing is Standard SVA angleway or straightway housing allowing other inserts from the SVL platform to be installed.

Material is special, cold resistant steel

#### The cone

The valves are available in two different versions – REG-SA with an A cone and REG-SB with a B cone. The A cone is designed for expansion lines, while the B cone is designed for regulating purposes e.g. liquid lines.

The valve cone is designed to ensure perfect regulation and provide an extensive regulating area. Irrespective of the refrigerant used, it is easy to obtain the correct capacity. A cone seal ring provides perfect sealing at a minimum closing momentum.

The valve cone can be turned on the spindle, thus there will be no friction between the cone and the seat when the valve is opened and closed.

#### **Spindle**

The spindle is made of polished stainless steel, which is ideal for O-ring sealing.

#### Packing gland - REG-SA and REG-SB

The "full temperature range" packing gland ensures perfect tightness in the whole range: -60 °C/+150 °C (-76 °F / +302 °F). The packing glands are equipped with a scraper ring to prevent penetration of dirt and ice.

For special and/or high demanding applications/conditions which run with high constant temperatures, it is recommended to replace the packing gland with "HL Packing Gland" as spare part. For more information, please, contact your local Danfoss sales representative.


#### Installation

Install the valve with the spindle up or in horizontal position. The flow must be directed towards the cone.

The valve is designed to withstand high internal pressure. However, the piping system in general should be designed to avoid liquid traps and reduce the risk of hydraulic pressure caused by thermal expansion.

For further information refer to product instruction for REG-SA and REG-SB.

Figure 1: Example of marking ring, REG-SA





# Pressure and temperature data

Table 1: Temperature and pressure

Description	Values
Temperature range	-60 °C /+150 °C (-76 °F /+302 °F)
Max working pressure	52 bar (754 psi g)

#### Flow coefficients

Flow coefficients for fully opened valves from  $k_y = 0.15$  to 80 m<sup>3</sup>/h ( $C_y = 0.17$  to 92.5 USgal/min).

# **Connections**

Available with the following connections:

- Butt-weld DIN (EN 10220) DN 10 65 (3/8 21/2 in.)
- Butt-weld ANSI (B 36.10 Schedule 80) DN 10 40 (% 1½ in.)
- Butt-weld ANSI (B 36.10 Schedule 40) DN 50 65 (2 21/2 in.)
- Butt-weld GOST, (8734-75 and 8732-78) DN 10 65 (  $^{3\!\!/}_{8}$   $21\!\!/_{2}$  in.)
- Socket weld (ANSI B 16.11) DN 15 40 (1/2 11/2 in.)
- FPT inside pipe thread, NPT (ANSI/ASME B 1.20.1) DN 15 32 (1/2 11/4 in.)

Figure 2: DIN




Table 2: Butt-weld DIN (EN 10220)

	Size mm	Size in.	OD mm	T mm	OD in.	T in.	Cone
REG-SA / SB	10	3/8	17.2	2.3	0.677	0.091	A and B
REG-SA / SB	15 20	1/2 3/4	21.3 26.9	2.3 2.3	0.839 1.059	0.091 0.091	A and B
REG-SA / SB	25 32 40	1 1¼ 1½	33.7 42.4 48.3	2.6 2.6 2.6	1.327 1.669 1.902	0.103 0.102 0.103	A and B
REG-SB	50	2	60.3	2.9	2.37	0.11	В
REG-SB	65	21/2	76.1	2.9	3	0.11	В

Figure 3: ANSI




Table 3: Butt-weld ANSI (B 36.10 Schedule 80)

	Size mm	Size in.	OD mm	T mm	OD in.	T in.	Cone
REG-SA / SB	10	3/8	17.2	3.2	0.677	0.126	A and B
REG-SA / SB	15 20	1/ <sub>2</sub> 3/ <sub>4</sub>	21.3 26.9	3.7 4.0	0.839 1.059	0.146 0.158	A and B
REG-SA / SB	25 32 40	1 1¼ 1½	33.7 42.4 48.3	4.6 4.9 5.1	1.327 1.669 1.902	0.181 0.193 0.201	A and B



Table 4: Butt-weld ANSI (B 36.10 Schedule 40)

	Size mm	Size in.	OD mm	T mm	OD in.	T in.	Cone
REG-SB	50	2	60.3	3.9	2.37	0.15	В
REG-SB	65	21/2	73.0	5.2	2.87	0.20	В

Figure 4: GOST




Table 5: Butt-weld GOST (8734-75 and 8732-78)

	Size mm	Size in.	OD mm	T mm	OD in.	T in.	Cone
REG-SA / SB	10	3/8	14	2	0.551	0.079	A and B
REG-SA / SB	15 20	1/2 3/4	18 25	2 2.5	0.709 0.984	0.079 0.098	A and B
REG-SA / SB	25 32 40	1 1½ 1½	32 38 45	3 3 3	1.260 1.496 1.772	0.118 0.118 0.118	A and B
REG-SB	50	2	57	3.5	2.244	0.138	В
REG-SB	65	21/2	76.1	2.9	3	0.11	В

Figure 5: SOC




Table 6: Socket welding ANSI (B 16.11)

			,						
	Size mm	Size in.	OD mm	T mm	OD in.	T in.	L mm	L in.	Cone
REG-SA / SB	15 20	1/ <sub>2</sub> 3/ <sub>4</sub>	21.8 27.2	6.0 7.6	0.858 1.071	0.235 0.299	10 13	0.39 0.51	A and B
REG-SA / SB	25 32 40	1 1¼ 1½	33.9 42.7 48.8	7.2 6.1 6.6	1.335 1.743 1.921	0.284 0.240 0.260	13 13 13	0.51 0.51 0.51	A and B
REG-SB	50	2	61.2	6.2	2.41	0.24	16	0.63	В

Figure 6: FPT






Table 7: FPT inside pipe thread, NPT (ANSI/ASME B 1.20.1)

	Size mm	Size in.	Inside pipe thread	Cone
REG-SA / SB	15 20	½ ¾	(½ × 14 NPT) (¾ × 14 NPT)	A and B
REG-SA / SB	25 32	1 11⁄4	(1 × 11.5 NPT) (1¼ × 11.5 NPT)	A and B

# **Computation and selection**

#### Introduction

In refrigeration plants, hand operated regulating valves are primarily used in liquid lines in order to regulate the flow of refrigerant. The valves can, however, also be used as expansion valves. From a calculation point of view the two fields of application are very different.


Normal flow is the term used to describe the general case where the flow through the valve is proportional to the square root of the pressure drop across it and inversely proportional to the density of the refrigerant (Bernouillis equation).

This relationship between mass flow, pressure drop and density satisfies the majority of all valve applications with refrigerants and brines.

Normal flow is characterised by turbulent flow through the valve without any phase change. The following capacity curves are based on the above mentioned assumption.

Application of the hand operated regulating valves outside the normal flow area will reduce the capacity of the valve considerably. In such cases it is recommended to use Coolselector®2 (Danfoss calculation and selection software).

Figure 7: Location of valve in system (marked with grey)



Sizing hand operated regulating valve for liquid flow

Liquid refrigerants: Use the liquid tables, Figure 13, Figure 14, Figure 15, Figure 16, Figure 17. For other refrigerants and brines, "Normal flow" (Turbulent flow); see below and use the flow coefficient tables (Figure 8, Figure 9, Figure 10, Figure 11, Figure 12).

#### SI-units

Mass flow:

$$k_V = \frac{G}{\sqrt{\rho \times 1000 \times \Delta p}} = G \times C_A [m^3/h]$$

Volume flow:



$$k_{v} = \frac{V}{\sqrt{\frac{1000 \times \Delta p}{\rho}}} \ [m^{3}/h]$$

k <sub>v</sub>	[m³/h]	Quantity [m <sup>3</sup> /h] of water flowing through a valve at a pressure loss of 1 bar (according to VDE/VDI Norm 2173).
P <sub>1</sub>	[bar]	Pressure before the valve (upstream).
P <sub>2</sub>	[bar]	Pressure after the valve (downstream).
Δр	[bar]	Actual pressure loss across the valve $(P_1-P_2)$ .
G	[kg/h]	Mass flow through the valve.
V	[m³/h]	Volume flow through the valve.
ρ	[kg/m³]	Density of the refrigerant before the valve.
C <sub>A</sub>		Calculation factor (See Figure 18).

# **Imperial units**

Mass flow:


$$C_{\text{v}} = \frac{0.95 \times \text{G}}{\sqrt{\rho \times \Delta p}} = 31.6 \times \text{G} \times \text{C}_{\text{A}} \text{ [USgal/min.]}$$

Volume flow:


$$C_{v} = \frac{0.127 \times \bigvee}{\sqrt{\frac{\Delta p}{\rho}}} [USgal/min.]$$


$C_v$	[US gal/min]	Quantity [US gal/min] of water flowing through a valve at a pressure loss of 1 psi.
P <sub>1</sub>	[psi]	Pressure before the valve (upstream).
P <sub>2</sub>	[psi]	Pressure after the valve (downstream).
Δр	[psi]	Actual pressure loss across the valve $(P_1 - P_2)$ .
G	[lb/min]	Mass flow through the valve.
V	[US gal/min]	Volume flow through the valve.
ρ	[lb/ft³]	Density of the refrigerant before the valve.
C <sub>A</sub>		Calculation factor (See Figure 18).

#### Figure 8: REG-SA 10 and REG-SB 10











# Figure 10: REG-SA 25-40 and REG-SB 25-40











Figure 12: REG-SB 65



Liquid R 717, density: 670 kg/m<sup>3</sup> [42 lb/ft<sup>3</sup>]











Figure 14: REG-SA 15-20 and REG-SB 15-20











### Figure 16: REG-SB 50











Figure 18: Calculation factor C



#### • NOTE:

For choice of valve size and connection see "".

# **Computation and selection Example 1**

Refrigerant: R 717


Refrigerant flow: 2200 kg/h Pressure drop:  $\Delta p = 0.5$  bar



The above mentioned example is illustrated on the following flow rate diagram and shows that REG-SB 15 and 20 with cone B can be used. The main rule is that nominal regulation range should be below 85% opening degree. If the arrowline is crossing 2 cone curves, the smaller cone should be selected if opening degree < 85%.

The example is only correct if the density of the refrigerant is approx. 670 (kg/m³), and there must be no build-up of flash gas in the valve.

Figure 19: Flow rate diagram



# **Computation and selection Example 2**

Brine, density  $\rho$ : 1150 [kg/m<sup>3</sup>] Brine flow G: 2,700 [kg/h] Pressure drop Δp: 0.5 [bar]

In this example it is not possible to use the selection diagrams (Figure 13, Figure 14, Figure 15, Figure 16, Figure 17) as the refrigerant in question is not included.

Use the curves of the k<sub>x</sub>-values instead (Figure 8, Figure 9, Figure 10, Figure 11, Figure 12) and calculate the required k, by means of the formulas in the "Introduction" passage at the beginning of this chapter. Alternatively calculate the  $k_v$ -values by means of the calculation factor  $C_A$  (Figure 20) and the flow rate diagram (in this example: Figure 21) as per the following calculation example.

Required k, -value  $C_{\Delta} = 0.00132$  (from Figure 20)  $k_v = C_A \times G$  $k_{y} = 0.00132 \times 2,700 \text{ [kg/h]}$ = 3.56 [m<sup>3</sup>/h]

Calculation example:









Figure 21: Flow rate diagram



REG-SB 15 and REG-SB 20 with cone B can be used.



# **Material specification**

Figure 22: REG-SA and REG-SB 10 - 65




Table 8: Material and part list

No.	Part	Material	EN	ISO	ASTM
1	Housing	Steel	G20Mn5QT, 10213-3 P285QH+QT, 10222-4		LCC, A352 LF2, A350
2	DN 15 - 40 (½ - 1½ in.) - Bonnet, Flange	Steel	P275 NL EN10028-3		A A662
3A	DN 10 - 40 (% - 1½ in.) - Bonnet, Insert	Steel	11SMn30 10087	Type 2, R 683-9	1213 SAE J403
3B	DN 50 - 65 (2 - 2½ in.) - Bonnet, Flange	Steel	P285QH+QT 10222-4		LF2 A350
4	Spindle DN 10 - 65 (¼ - 2½ in.)	Stainless steel	X8CrNiS 18-9, 17440	Type 17, 683/13	AISI 303
5	Cone	Steel			
7	Packing washer	Aluminium			
8	Packing gland	Stainless Steel	X8CrNiS 18-9, 10088	Type 17, 683/13	AISI 303
9	O-ring	Cloroprene (Neoprene)			
10	Spring loaded Teflon ring	PTFE			
11	O-ring	Cloroprene (Neoprene)			
12	Bolts	Stainless steel	A2-70	A2-70	Type 308
13	Gasket	Fiber, non asbestos			
14	Bottom insert	Steel			
17	Seal cap	Aluminium			
18	Gasket f. seal cap	Nylon			
19	Locking nut	Steel			
20	Screw	Steel			
21	Disk spring	Steel			



# **Dimensions and weights**

Figure 23: REG-SA and REG-SB 10 - 65 in angleway version




Table 9: REG-SA and REG-SB 10 - 65 in angleway version

Tubic 7. ILC 3/Luin	a ned 30	io os ili aligicway	VCISIOII			
Valve size		С	G	ØD	Øн	Weight
REG-SA/SB 10	mm	139	30	30	36	0.8 kg
REG-SA/SB (%)	in.	5.47	1.18	1.18	1.42	1.8 lb
REG-SA/SB 15-20	mm	182	45	38	60	1.4 kg
REG-SA/SB (½-¾)	in.	7.17	1.77	1.50	2.36	3.1 lb
REG-SA/SB 25-40	mm	237	55	50	70	2.4 kg
REG-SA/SB (1-11/2)	in.	9.33	2.17	1.97	2.76	5.3 lb
REG-SB 50	mm	315	60	50	77	3.2 kg
REG-SB (2 in.)	in.	12.4	2.36	1.97	3.03	7.1 lb
REG-SB 65	mm	335	70	50	90	4.8 kg
REG-SB (2½ in.)	in.	13.19	2.76	1.97	3.54	10.6 lb
REG-SA/SB 32 SOC	mm	275	62	50	70	2.9 kg
REG-SA/SB (1¼ in.) SOC	in.	10.83	2.44	1.97	2.76	6.4 lb
REG-SA/SB 40 SOC	mm	275	62	50	70	2.9 kg
REG-SA/SB (1½ in.) SOC	in.	10.83	2.44	1.97	2.76	6.4 lb
REG-SB 50 SOC	mm	320	65	50	77	4.1 kg
REG-SB (2 in.) SOC	in.	12.60	2.56	1.97	3.03	9.0 lb



Specified weights are approximate values only.

Figure 24: REG-SA and REG-SB 10 - 65 in straightway version




Table 10: REG-SA and REG-SB 10 - 65 in straightway version

Table To. NEG .	table 10. Ned 3A and Ned 3b 10 03 in straightway version										
Valve size		С	В	E	G	ØD	Øн	Weight			
REG-SA/SB 10	mm	110	120	13	70	30	36	0.8 kg			
REG-SA/SB (3/8)	in.	4.33	4.72	0.51	2.76	1.18	1.42	1.8 lb			
REG-SA/SB 15-20	mm	145	155	20	120	38	60	2.0 kg			
REG-SA/SB (1/2-3/4)	in.	5.71	6.10	0.79	4.72	1.50	2.36	4.4 lb			
REG-SA/SB 25-40	mm	200	215	26	155	50	70	3.0 kg			
REG-SA/SB (1-1½)	in.	7.87	8.46	1.02	6.10	1.97	2.76	6.6 lb			
REG-SB 50	mm	257	250	32	148	50	77	4.2 kg			



# Hand operated regulating valve, type REG-SA and REG-SB 10-65

Valve size		С	В	E	G	ØD	ØН	Weight
REG-SB (2 in.)	in.	10.12	10.20	1.26	5.83	1.97	3.03	9.3 lb
REG-SB 65	mm	280	284	40	176	50	90	6.3 kg
REG-SB (2½ in.)	in.	11.02	11.18	1.57	6.93	1.97	3.54	13.9 lb
REG 32 SOC	mm	209	222	27.4	155	50	70	3.0 kg
REG (11/4 in.) SOC	in.	8.23	8.74	1.08	6.10	1.97	2.76	6.6 lb
REG 40 SOC	mm	213	222	31.0	155	50	70	3.0 kg
REG (1½ in.) SOC	in.	8.39	8.74	1.22	6.10	1.97	2.76	6.6 lb
REG-SB 50 SOC	mm	261	266	37	162	50	77	5.1 kg
REG-SB (2 in.) SOC	in.	10.28	10.47	1.26	6.38	6.38	3.03	11.2 lb

# • NOTE:

Specified weights are approximate values only.



# Ordering

#### How to order

The table below is used to indentify the valve required.

Please note that the type codes only serve to identify the valves, some of which may not form part of the standard product range. For further information please contact your local Danfoss Sales Company.

Table 11: Type codes

Valve type	REG	Hand operated regulating valves									
				Ava	ailable connection typ	oes					
			Α	D	G	SOC	FPT				
	10	DN 10	x	x	x						
Nominal size in	15	DN 15	x	x	x	x	х				
mm	20	DN 20	x	x	х	х	x				
(Valve size meas- ured on	22	DN 22									
the connection di-	25	DN 25	x	х	х	x	x				
ameter)	32	DN 32	х	х	х	x	x				
	40	DN 40	х	х	х	x					
	50	DN 50	x	x	x	x					
	65	DN 65	х	х							
	Α			e 80, 15 - 40 (½ - 1½ ir e 40, 50 - 65 (2 - 2½ in							
	D	Welding branches: 8	N 10220								
Connections	G	Welding branches: 0	GOST (8734-75 and 8	732-78)							
	SOC	Socket weld: ANSI B 16.11									
	FPT	NPT inside pipe thread: ANSI/ASME B1.20.1									
Valve housing	ANG	Angle flow									
valve flousing	STR	Straight flow									
	Size:	Flow area [mm²]									
	DN 10	3.02									
	DN 15	36.5									
Cone A	DN 20	36.5									
	DN 25	178	178								
	DN 32	178									
	DN 40	178									
	Size:	Flow area [mm <sup>2</sup> ]									
	DN 10	16									
	DN 15	115									
	DN 20	115									
Cone B	DN 25	531									
	DN 32	531									
	DN 40	531									
	DN 50	822									
	DN 65	1978									

Table 12: Available combination between valve size, cone type and valve connection

Size	DN (¾		DN (1/2	15 2")		20 4")		22 ś")	DN (1	25 ")	DN (13		DN (13		DN (2	50 !")	DN (21	65 /2")
Cone type	A	В	A	В	A	В	А	В	A	В	A	В	A	В	A	В	A	В
DIN	×	×	×	×	×	×			×	×	×	×	×	×		×		×
ANSI	×	×	×	×	×	×			×	×	×	×	×	×		×		×
GOST	×	×	×	×	×	×			×	×	×	×	×	×		×		
SOC			×	×	×	×			×	×	×	×	×	×		×		
FPT			×	×	×	×			×	×	×	×						

 $\times$  = available



# **Complete REG-SA (Cone type A)**

#### **Example:**

REG-SA (Cone A) 15 DIN angleway = 148B5226

#### **•** IMPORTANT:

Where products need to be certified according to specific certification societies or where higher pressures are required, the relevant information should be included at the time of order.

Table 13: Butt-weld DIN (EN 10220)

Si	ze	Туре	Code no.	
mm	in.	Туре		
<b>Angleway</b> - REG-SA with cone type A				
10	3/8	REG-SA 10 D ANG	148B5102	
15	1/2	REG-SA 15 D ANG	148B5226	
20	3/4	REG-SA 20 D ANG	148B5326	
25	1	REG-SA 25 D ANG	148B5426	
32	11⁄4	REG-SA 32 D ANG	148B5527	
40	1½	REG-SA 40 D ANG	148B5627	

Table 14: Butt-weld DIN (EN 10220)

Si	ze	Туре	Code no.	
mm	in.	Туре		
<b>Straightway</b> - REG-SA with cone type A				
10	3/8	REG-SA 10 D STR	148B5104	
15	1/2	REG-SA 15 D STR	148B5228	
20	3/4	REG-SA 20 D STR	148B5328	
25	1	REG-SA 25 D STR	148B5428	
32	11⁄4	REG-SA 32 D STR	148B5528	
40	11/2	REG-SA 40 D STR	148B5629	

Table 15: Butt-weld ANSI (B 36.10 Schedule 80)

Si	ze	Type	Code no.	
mm	in.	Туре		
<b>Angleway</b> - REG-SA with cone type A				
10	3/8	REG-SA 10 A ANG	148B5106	
15	1/2	REG-SA 15 A ANG	148B5202	
20	3/4	REG-SA 20 A ANG	148B5302	
25	1	REG-SA 25 A ANG	148B5402	
32	11⁄4	REG-SA 32 A ANG	148B5502	
40	1½	REG-SA 40 A ANG	148B5602	

Table 16: Butt-weld ANSI (B 36.10 Schedule 80)

in.	Туре	Code no.	
in			
	, , , , , , , , , , , , , , , , , , ,	code no.	
3/8	REG-SA 10 A STR	148B5116	
1/2	REG-SA 15 A STR	148B5212	
3/4	REG-SA 20 A STR	148B5312	
1	REG-SA 25 A STR	148B5412	
1¼	REG-SA 32 A STR	148B5512	
1½	REG-SA 40 A STR	148B5612	
	% 1/2 3/4 1 1/4	% REG-SA 10 A STR  ½ REG-SA 15 A STR  ¾ REG-SA 20 A STR  1 REG-SA 25 A STR  1¼ REG-SA 32 A STR	

Table 17: Socket welding ANSI (B 16.11)

Si	ze	Туре	Code no.
mm	in.	туре	Code no.
<b>Angleway</b> - REG-SA with cone type A			
15	1/2	REG-SA 15 SOC ANG	148B5204
20	3/4	REG-SA 20 SOC ANG	148B5304



Si	ze	Туре	Code no.	
mm	in.	туре		
25	1	REG-SA 25 SOC ANG	148B5404	
32	1¼	REG-SA 32 SOC ANG	148B5504	
40	1½	REG-SA 40 SOC ANG	148B5604	

Table 18: Socket welding ANSI (B 16.11)

Si	ze	Туре	Code no.	
mm	in.	туре		
Straightway  - REG-SA with cone type A				
15	1/2	REG-SA 15 SOC STR	148B5214	
20	3/4	REG-SA 20 SOC STR	148B5314	
25	1	REG-SA 25 SOC STR	148B5414	
32	1¼	REG-SA 32 SOC STR	148B5514	
40	1½	REG-SA 40 SOC STR	148B5614	

Table 19: FPT inside pipe thread, NPT (ANSI/ASME B 1.20.1)

Si	ze	Туре	Code no.	
mm	in.	туре	Code no.	
Angleway - REG-SA with cone type A				
15	1/2	REG-SA 15 FTP ANG	148B5206	
20	3/4	REG-SA 20 FTP ANG	148B5306	
25	1	REG-SA 25 FTP ANG	148B5406	
32	11⁄4	REG-SA 32 FTP ANG	148B5506	

Table 20: FPT inside pipe thread, NPT (ANSI/ASME B 1.20.1)

	, ,			
Si	ze	Туре	Code no.	
mm	in.	Туре		
Straightway  - REG-SA with cone type A				
15	1/2	REG-SA 15 FTP STR	148B5216	
20	3/4	REG-SA 20 FTP STR	148B5316	
25	1	REG-SA 25 FTP STR	148B5416	
32	11⁄4	REG-SA 32 FTP STR	148B5516	

**D** = Butt-weld DIN

**A** = Butt-weld ANSI

**SOC** = Socket weld

**FPT** = Inside pipe thread

**ANG** = Angleway

**STR** = Straightway

# **Complete REG-SB (Cone type B)**

#### **Example:**

REG-SB (Cone B) 15 DIN angleway = **148B5227** 

# • IMPORTANT:

Where products need to be certified according to specific certification societies or where higher pressures are required, the relevant information should be included at the time of order.

Table 21: Butt-weld DIN (EN 10220)

Size		Tuna	Code no.
mm	in.	- Туре	Code no.
<b>Angleway</b> - REG-SB with cone type B			
10	3∕8	REG-SB 10 D ANG	148B5103
15	1/2	REG-SB 15 D ANG	148B5227
20	3/4	REG-SB 20 D ANG	148B5327
25	1	REG-SB 25 D ANG	148B5427
32	11⁄4	REG-SB 32 D ANG	148B5526



Size		Tuno	Code no.
mm	in.	Туре	Code no.
40	1½	REG-SB 40 D ANG	148B5626
50	2	REG-SB 50 D ANG	148B5726
65	2½	REG-SB 65 D ANG	148B5826

### Table 22: Butt-weld DIN (EN 10220)

Size		Tuno	Code no.
mm	in.	- Туре	Code IIo.
<b>Straightway</b> - REG-SB with cone type B			
10	3/8	REG-SB 10 D STR	148B5105
15	1/2	REG-SB 15 D STR	148B5229
20	3/4	REG-SB 20 D STR	148B5329
25	1	REG-SB 25 D STR	148B5429
32	11⁄4	REG-SB 32 D STR	148B5529
40	1½	REG-SB 40 D STR	148B5628

### Table 23: Butt-weld ANSI (B 36.10 Schedule 80)

Size		- Type	Code no.
mm	in.	Туре	Code no.
<b>Angleway</b> - REG-SB with cone type B			
10	3/8	REG-SB 10 A ANG	148B5107
15	1/2	REG-SB 15 A ANG	148B5203
20	3/4	REG-SB 20 A ANG	148B5303
25	1	REG-SB 25 A ANG	148B5403
32	11⁄4	REG-SB 32 A ANG	148B5503
40	1½	REG-SB 40 A ANG	148B5603

### Table 24: Butt-weld ANSI (B 36.10 Schedule 80)

Size		Type	Code no.
mm	in.	Туре	Code no.
<b>Straightway</b> - REG-SB with cone type B			
10	3/8	REG-SB 10 A STR	148B5117
15	1/2	REG-SB 15 A STR	148B5213
20	3/4	REG-SB 20 A STR	148B5313
25	1	REG-SB 25 A STR	148B5413
32	11⁄4	REG-SB 32 A STR	148B5513
40	1½	REG-SB 40 A STR	148B5613

# Table 25: Butt-weld ANSI (B 36.10 Schedule 40)

Size		Time	Code no.
mm	in.	Туре	Code no.
<b>Angleway</b> - REG-SB with cone type B			
50	2	REG-SB 50 A ANG	148B5706
65	2½	REG-SB 65 A ANG	148B5806

# Table 26: Butt-weld ANSI (B 36.10 Schedule 40)

Size		Tuna	Code no.
mm	in.	Туре	Code no.
<b>Angleway</b> - REG-SB with cone type B			
50	2	REG-SB 50 A STR	148B5724
65	2½	REG-SB 65 A STR	148B5809

# Table 27: Socket welding ANSI (B 16.11)

Size		- Type	Code no.
mm	in.	туре	Code no.
Angleway - REG-SB with cone type B			
15	1/2	REG-SB 15 SOC ANG	148B5205
20	3/4	REG-SB 20 SOC ANG	148B5305
25	1	REG-SB 25 SOC ANG	148B5405

# Hand operated regulating valve, type REG-SA and REG-SB 10-65

Size		Tuna	Code no.
mm	in.	Туре	Code no.
32	1¼	REG-SB 32 SOC ANG	148B5505
40	1½	REG-SB 40 SOC ANG	148B5605
50	2	REG-SB 50 SOC ANG	148B5727

# Table 28: Socket welding ANSI (B 16.11)

Size		Time	Code no.
mm	in.	Туре	code no.
<b>Angleway</b> - REG-SB with cone type B			
15	1/2	REG-SB 15 SOC STR	148B5215
20	3/4	REG-SB 20 SOC STR	148B5315
25	1	REG-SB 25 SOC STR	148B5415
32	1¼	REG-SB 32 SOC STR	148B5515
40	1½	REG-SB 40 SOC STR	148B5615
50	2	REG-SB 50 SOC STR	148B5725

### Table 29: FPT inside pipe thread, NPT (ANSI/ASME B 1.20.1)

Size		- Type	Code no.
mm	in.	Туре	code no.
Angleway - REG-SB with cone type B			
15	1/2	REG-SB 15 FTP ANG	148B5207
20	3/4	REG-SB 20 FTP ANG	148B5307
25	1	REG-SB 25 FTP ANG	148B5407
32	1¼	REG-SB 32 FTP ANG	148B5507

### Table 30: FPT inside pipe thread, NPT (ANSI/ASME B 1.20.1)

Size		- Type	Code no.	
mm	in.	туре	Code no.	
<b>Straightway</b> - REG-SB with cone type B	Straightway - REG-SB with cone type B			
15	1/2	REG-SB 15 FTP STR	148B5217	
20	3/4	REG-SB 20 FTP STR	148B5317	
25	1	REG-SB 25 FTP STR	148B5417	
32	11⁄4	REG-SB 32 FTP STR	148B5517	

 $\mathbf{D} = \text{Butt-weld DIN}$ 

**A** = Butt-weld ANSI

**SOC** = Socket weld

**FPT** = Inside pipe thread

**ANG** = Angleway

STR = Straightway



# Ordering REG-SA/SB from the parts programme

Figure 25: Example (select from table 31: SVL valve housings w/different connections and table 32: REG complete top part including gaskets and bolts)




Figure 26: DN 10 mm (3/8 in.)




Figure 27: DN 15-65 mm (1/2 - 21/2 in.)






Table 31: SVL valve housings w/different connections

Sizes [DN]		Valve Housing SVL										
		DIN-Butt weld		ANSI-Butt weld		GOST-Butt-weld		soc		FPT		Т
mm	in.	ANG	STR	ANG	STR	ANG	STR	ANG	STR	ANG	STR	ANG
10	3/8	148B5122	148B5123	148B5124	148B5125	148B5134	148B5135					
15	1/2	148B5252	148B5253	148B5254	148B5255	148B5391	148B5392	148B5256	148B5257	148B5258	148B5259	
20	3/4	148B5352	148B5353	148B5354	148B5355	148B5393	148B5394	148B5356	148B5357	148B5358	148B5359	
25	1	148B5452	148B5453	148B5454	148B5455	148B5498	148B5499	148B5456	148B5457	148B5458	148B5459	
32	11⁄4	148B5576	148B5577	148B5578	148B5579	148B5593	148B5594	148B5580	148B5581	148B5582	148B5583	
40	11/2	148B5652	148B5653	148B5654	148B5655	148B5681	148B5682	148B5656	148B5657			
50	2	148B5741	148B5742	148B5743	148B5744	148B5759	148B5760	148B5745	148B5746			
65	21/2	148B5816	148B5817	148B5818	148B5819	148B5816	148B5817	148B5816	148B5817			

Figure 28: REG-SA/SB 10 Figure 29: REG-SA/SB 15-65 Figure 30: REG-LA/LB 15-40










Table 32: REG complete top part including gaskets and bolts

Sizes [DN]		Complete top part					
mm	in.	REG-SA	REG-SB	REG-LA	REG-LB		
10	3/8	148B5112	148B5113				
15	1/2	148B5280	148B5281	148B6401	148B6402		
20	3/4	14003200	14003201				
25	1						
32	11⁄4	148B5480	148B5481	148B6403	148B6404		
40	11/2						
50	2		148B5734				
65	21/2		148B5824				

Replacement kit (O-ring replacement) for R717 Ammonia Heat Pump<sup>(1)</sup> and Propylene applications (including ID tag)

Table 33: O-ring kit

Size	(DN)	O-ring kit for		
mm	in.	R717 Heat pump	R1270 Propylene	
10	3/8	148B6084	148B6085	
15	1/2	148B6070	148B6077	
20	3/4	14000070	1460077	
25	1			
32	11⁄4	148B6096	148B6097	
40	11/2			

<sup>&</sup>lt;sup>1</sup> Replacement kits for R717 Ammonia Heat Pump is applicable for continuous operating temperature between 100 °C to 150 °C (212 °F to 302 °F)



# Certificates, declarations, and approvals

The list contains all certificates, declarations, and approvals for this product type. Individual code number may have some or all of these approvals, and certain local approvals may not appear on the list.

Some approvals may change over time. You can check the most current status at danfoss.com or contact your local Danfoss representative if you have any questions.

#### **Table 34: Pressure Equipment Directive (PED)**



REG valves are approved according to the European standard specified in the Pressure Equipment Directive and are CE marked.

#### Table 35: REG-SA and REG-SB valves

REG-SA and REG-SB valves						
Nominal bore	DN = < 25 mm (1 in.)	DN32-80 mm (1¼ - 3 in.)	DN100 - 125 mm (4 - 5 in.)			
Classified for	Fluid group I					
Category	Article 3, paragraph 3	II	III			

#### **Table 36: Certificates and declarations**

File name	Document type	Document topic	Approval authority
BV 03709-F0 BV	Marine - Safety Certificate	-	BV
TAP0000002 Rev. 2	Marine - Safety Certificate	-	DNV GL
033F0685.AK	EU Declaration	EMCD/PED	Danfoss
033F0691.AE	Manufacturers Declaration	RoHS	Danfoss
RMRS 19.10048.266	Marine - Safety Certificate	-	RMRS



# Online support

Danfoss offers a wide range of support along with our products, including digital product information, software, mobile apps, and expert guidance. See the possibilities below.

#### **The Danfoss Product Store**



The Danfoss Product Store is your one-stop shop for everything product related—no matter where you are in the world or what area of the cooling industry you work in. Get quick access to essential information like product specs, code numbers, technical documentation, certifications, accessories, and more.

Start browsing at store.danfoss.com.

#### **Find technical documentation**



Find the technical documentation you need to get your project up and running. Get direct access to our official collection of data sheets, certificates and declarations, manuals and guides, 3D models and drawings, case stories, brochures, and much more.

Start searching now at www.danfoss.com/en/service-and-support/documentation.

#### **Danfoss Learning**



Danfoss Learning is a free online learning platform. It features courses and materials specifically designed to help engineers, installers, service technicians, and wholesalers better understand the products, applications, industry topics, and trends that will help you do your job better.

Create your Danfoss Learning account for free at www.danfoss.com/en/service-and-support/learning.

#### Get local information and support



Local Danfoss websites are the main sources for help and information about our company and products. Find product availability, get the latest regional news, or connect with a nearby expert—all in your own language.

Find your local Danfoss website here: www.danfoss.com/en/choose-region.

#### **Spare Parts**



Get access to the Danfoss spare parts and service kit catalog right from your smartphone. The app contains a wide range of components for air conditioning and refrigeration applications, such as valves, strainers, pressure switches, and sensors.

Download the Spare Parts app for free at www.danfoss.com/en/service-and-support/downloads.

#### Coolselector®2 - find the best components for you HVAC/R system



Coolselector®2 makes it easy for engineers, consultants, and designers to find and order the best components for refrigeration and air conditioning systems. Run calculations based on your operating conditions and then choose the best setup for your system design.

Download Coolselector®2 for free at coolselector.danfoss.com.

#### Danfoss A/S

Climate Solutions • danfoss.com • +45 7488 2222

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues descriptions, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or further that the sending