



Technical Information

Series 45 G Frame

Contents**Frame G**

Design	4
Specifications	5
Performance G74B	6
Performance G90C	7
Order code.....	8
Controls.....	10
Pressure compensated control (PC).....	10
Remote PC control (RP).....	10
Load sensing control (LS).....	11
Load sensing control with internal bleed orifice (LB).....	11
Input shafts	12
Auxiliary mounting pads.....	13
SAE-A auxiliary mounting pad	13
SAE-B auxiliary mounting pad	13
Displacement limiter.....	14
SAE-C auxiliary mounting pad	14
Installation drawings	15
Running cover	15
Adjustable displacement limiter	15
Axial ported endcap	16
Radial ported endcap	18

This information was removed from:

Series 45 Axial Piston Open Circuit Pumps Technical Information Manual **520L0519**

Rev E November 2006


For more information regarding the Series 45 product line refer to the current version of **520L0519**.

Design

Series 45 Frame G pumps have a dual servo piston design with a cradle-type swashplate set in polymer-coated journal bearings. The bias piston increases swashplate angle. The displacement piston decreases swashplate angle. At equal pressure, the larger diameter displacement piston overpowers the bias piston. Nine reciprocating pistons displace fluid from the pump inlet to the pump outlet as the cylinder block rotates on the pump input shaft. The block spring holds the piston slippers to the swashplate via the slipper retainer. The cylinder block rides on a bi-metal valve plate optimized for high volumetric efficiency and low noise. Tapered roller bearings support the input shaft and a viton lip-seal protects against shaft leaks.

An adjustable one spool (PC only, not shown) or two spool (LS) control senses system pressure and load pressure (LS controls). The control ports system pressure to the displacement piston to control pump output flow.

Frame G cross section



P104 002E

Technical Information

Series 45 G Frame Pumps

Specifications

For general operating parameters, including fluid viscosity, temperature, and inlet and case pressures, [see page 13](#). For system design parameters, including installation, filtration, reservoir, and line velocities, [see page 15](#).

Features and options

		Model	
Feature	Unit	G74B	G90C
Maximum Displacement	cm ³ [in ³]	74 [4.52]	90 [5.49]
Flow at rated speed (theoretical)	l/min [US gal/min]	177.6 [46.9]	198 [52.3]
Input torque at maximum displacement (theoretical)	N•m/bar [lbf•in/1000 psi]	1.178 [719]	1.432 [874]
Mass moment of inertia of internal rotating components	kg•m ² [slug•ft ²]	0.00630 [0.00465]	0.00650 [0.00480]
Weight	Axial ports	29 [63]	
	Radial ports	36 [80]	
Rotation		Clockwise, Counterclockwise	
Mounting		SAE-C	
Auxiliary mounting (See page 74)		SAE-A, SAE-B, SAE-BB, SAE-C	
System ports (type)		4-bolt split flange	
System ports (location)		Axial, Radial	
Control types (See page 71)		PC, Remote PC, LS, LS with internal bleed	
Shafts (See page 73)	Splined	14 tooth, 17 tooth	
	Straight	Ø 31.75 mm [1.25 in]	
Displacement limiters (See page 75)		Optional, adjustable	

For definitions of pressure and speed ratings, [see page 14](#). For more information on external shaft loads, [see page 16](#); mounting flange loads, [see page 17](#).

Ratings

		Model	
Rating	Units	G74B	G90C
Input speed ¹	minimum	500	500
	continuous	2400	2200
	maximum	2800	2600
Working pressure	continuous	310 [4495]	260 [3770]
	maximum	400 [5800]	350 [5075]
External shaft loads	External moment (M _e)	300 [2655]	
	Thrust in (T _{in}), out (T _{out})	2900 [650]	
Bearing life	at 140 bar [2030 psi]	B ₁₀ hours	41 383
	at 210 bar [3045 psi]		9048
	at 260 bar [3770 psi]		4339
	at 310 bar [4495 psi]		1948
Mounting flange load moments	Vibratory (continuous)	1580 [14 000]	
	Shock (max)	5650 [50 000]	

1. Input speeds are valid at 1 bar absolute [0 in Hg vac] inlet pressure. See [Inlet pressure vs. speed](#) charts.

Sound levels²

For more information on noise levels, [see page 19](#).


dB(A)	210 bar [3045 psi]		260 bar [3770 psi]		310 bar [4495 psi]	
Model	1800 min ⁻¹ (rpm)	Rated speed	1800 min ⁻¹ (rpm)	Rated speed	1800 min ⁻¹ (rpm)	Rated speed
G74B	75	78	74	76	75	77
C90C	74	76	75	77	—	—

2. Sound data was collected in a *semi-anechoic* chamber. Values have been adjusted (-3 dB) to reflect *anechoic* levels.


**Performance
G74B**

Flow and power data valid at 49°C [120°F] and viscosity of 17.8 mm²/sec [88 SUS].


Flow vs. speed



Input power vs. speed



Inlet pressure vs. speed




The chart on the right shows allowable inlet pressure and speed at various displacements. Greater speeds and lower inlet pressures are possible at reduced displacement. Operating outside of acceptable limits reduces pump life.


Performance
G90C

Flow and power data valid at
49°C [120°F] and viscosity of
17.8 mm²/sec [88 SUS].


Flow vs. speed



Input power vs. speed



Inlet pressure vs. speed



The chart on the right shows allowable inlet pressure and speed at various displacements. Greater speeds and lower inlet pressures are possible at reduced displacement. Operating outside of acceptable limits reduces pump life.

Technical Information

Series 45 G Frame Pumps

Order Code

R S P C D E F G H J K L M N
1 2 3 1 2 3

R Product

GR	G Frame, variable displacement open circuit pump
-----------	--

S Rotation

L	Left hand (counterclockwise)
R	Right hand (clockwise)

P Displacement and pressure rating

074B	074 cm ³ /rev [4.52 in ³ /rev], 310 bar [4495 psi] continuous working pressure
090C	090 cm ³ /rev [5.49 in ³ /rev], 260 bar [3770 psi] continuous working pressure

C Control type

PC	Pressure compensated control 100-280 bar [1450-4060 psi]
BC	Pressure compensated control 290-310 bar [4205-4495 psi]
RP	Remote pressure compensated control 100-280 bar [1450-4060 psi]
BP	Remote pressure compensated control 290-310 bar [4205-4495 psi]
LS	Load sensing / pressure compensating control 100-280 bar [1450-4060 psi]
BS	Load sensing / pressure compensating control 290-310 bar [4205-4495 psi]
LB	Load sensing / pressure compensating control with internal bleed orifice 100-280 bar [1450-4060 psi]
BB	Load sensing / pressure compensating control with internal bleed orifice 290-310 bar [4205-4495 psi]

D PC setting (2 digit code, 10 bar increments)

Example	10 = 100 bar
10-31	100 to 310 bar [1450 to 4495 psi] (074B)
10-26	100 to 260 bar [1450 to 3770 psi] (090C)

E Load sensing setting (2 digit code, 1 bar increments)

Example	20 = 20 bar
10-30	10 to 40 bar [145 to 435 psi]
NN	Not applicable (use with PC controls)

F Not used

NN	Not applicable
-----------	----------------

Technical Information

Series 45 G Frame Pumps

Order Code (continued)

R S P C D E F G H J K L M N
1 2 3 1 2 3

G *Pilot orifice*

N	Standard
----------	----------

H *Gain orifice*

3	Standard
----------	----------

J1 *Input shaft*

S1	14 tooth, 12/24 pitch (ANSI B92.1 1970 - Class 5)
S2	17 tooth, 12/24 pitch (ANSI B92.1 1970 - Class 5)
K4	Ø 31.75 mm [1.25 in], straight keyed

J2 *Auxiliary mounting flange*

N	None
A	SAE-A, 9-tooth coupling
T	SAE-A, 11-tooth coupling
B	SAE-B, 13-tooth coupling
V	SAE-BB, 15-tooth coupling
C	SAE-C, 14-tooth coupling

J3 *System port size and location*

Code	Location	Port type	Inlet size	Outlet size
2	Radial	4-bolt split-flange	2 in.	1 in.
4	Axial	4-bolt split-flange	2 in.	1 in.

K1 *Shaft seal*

A	Single lip seal, viton
----------	------------------------

K2 *Mounting flange and housing port style*

1	SAE-C 4-bolt, SAE O-ring boss housing ports
----------	---

K3 *Not used*

N	Not applicable
----------	----------------

L *Displacement limiter*

NNN	None
AAA	Adjustable, factory set at max angle (074B)
CAA	Adjustable, factory set at max angle (090C)

M *Special hardware*

NNN	None
------------	------

N *Special features*

NNN	None
------------	------


Controls
Specifications
Pressure compensated control (PC)
PC control setting range

Model	bar	psi
G74B	100–310	1450–4495
G90C	100–260	1450–3770

*Response/recovery times**

(ms)	Response	Recovery
G74B	35	130
G90C	40	140

* For definitions, [see page 9](#).

Schematic diagram
PC schematic

Legend

B = Outlet
 S = Inlet
 L1, L2 = Case drain
 M2 = System pressure gauge port
 M4 = Servo pressure gauge port


Specifications
Remote PC control (RP)
PC control setting range

Model	bar	psi
G74B	100–310	1450–4495
G90C	100–260	1450–3770

*Response/recovery times**

(ms)	Response	Recovery
G74B	35	130
G90C	40	140

* For definitions, [see page 10](#).

Schematic diagram
Remote PC schematic

Legend

B = Outlet
 S = Inlet
 L1, L2 = Case drain
 M2 = System pressure gauge port
 M4 = Servo pressure gauge port
 X = Remote PC port


Controls (continued)
Specifications
Load sensing control (LS)
PC setting range

Model	bar	psi
G74B	100–310	1450–4495
G90C	100–260	1450–3770

*Response/recovery times**

(ms)	Response	Recovery
G74B	35	100
G90C	40	130

* For definitions, [see page 11](#)

Schematic diagram
LS Schematic

LS setting range

Model	bar	psi
All	10–30	145–435

Legend

- B = Outlet
- S = Inlet
- L1, L2 = Case drain
- M2 = System pressure gauge port
- M4 = Servo pressure gauge port
- X = LS signal port


Load sensing control with internal bleed orifice (LB)
Specifications
PC setting range

Model	bar	psi
G74B	100–310	1450–4495
G90C	100–260	1450–3770

*Response/recovery times**

(ms)	Response	Recovery
G74B	35	100
G90C	40	130

* For definitions, [see page 11](#).

Schematic diagram
LB Schematic

LS setting range

Model	bar	psi
All	10–30	145–435

Legend

- B = Outlet
- S = Inlet
- L1, L2 = Case drain
- M2 = System pressure gauge port
- M4 = Servo pressure gauge port
- X = LS signal port

Input Shafts
Shaft data

Code	Description	Maximum torque rating ¹ N·m [lbf·in]	Drawing
S1	14 tooth spline 12/24 pitch (ANSI B92.1 1970 - Class 5)	734 [6500]	
S2	17 tooth spline 12/24 pitch (ANSI B92.1 1970 - Class 5)	1017 [9000]	
K4	Ø 31.75 mm [1.25 in] Straight keyed	734 [6495]	


1. See [Input shaft torque ratings](#), page 18 for an explanation of maximum torque.

Auxiliary Mounting Pads

SAE-A auxiliary mounting pad

Dimensions

See page 18 for mating pump pilot and spline dimensions.




Specifications

Coupling	9-tooth	11-tooth
Spline minimum engagement	13.5 mm [0.53 in]	15 mm [0.59 in]
Maximum torque	107 N·m [950 lbf·in]	147 N·m [1300 lbf·in]
Dimension A	21.1 mm [0.83 in]	16.1 mm [0.63 in]

SAE-B auxiliary mounting pad

Dimensions

See page 18 for mating pump pilot and spline dimensions.




Specifications

Coupling	13-tooth	15-tooth
Spline minimum engagement	14.2 mm [0.56 in]	18.9 mm [0.74 in]
Maximum torque	249 N·m [2200 lbf·in]	339 N·m [3000 lbf·in]
Dimension A	20.7 mm [0.81 in]	12.7 mm [0.5 in]

**Auxiliary Mounting Pads
(continued)**

**SAE-C auxiliary mounting pad
Dimensions**

See page 18 for mating pump pilot and spline dimensions.



Specifications

Coupling	14-tooth
Spline minimum engagement	18.3 mm [0.72 in]
Maximum torque	339 N·m [3000 lbf·in]


Displacement limiter

G Frame open circuit pumps are available with an optional adjustable displacement limiter. This adjustable stop limits the pump's maximum displacement.

Displacement limiter cross-section

Setting range


G74B	56 to 74 cm ³ [3.39 to 4.52 in ³]
G90C	68 to 90 cm ³ [4.12 to 5.49 in ³]




1. See [Input shaft torque ratings](#), page 19 for definitions of continuous and maximum torque.

Installation Drawings

Running cover
Dimensions







Adjustable displacement limiter
Dimensions



Installation Drawings
(continued)

Axial ported endcap




P106 174E



Installation Drawings
(continued)

Axial ported endcap (continued)






P104 074e



Installation Drawings
(continued)

Radial ported endcap




P106 175E



Installation Drawings
(continued)

Radial ported endcap (continued)



P104 075E





Products we offer:

- Bent Axis Motors
- Closed Circuit Axial Piston Pumps and Motors
- Displays
- Electrohydraulic Power Steering
- Electrohydraulics
- Hydraulic Power Steering
- Integrated Systems
- Joysticks and Control Handles
- Microcontrollers and Software
- Open Circuit Axial Piston Pumps
- Orbital Motors
- PLUS+1® GUIDE
- Proportional Valves
- Sensors
- Steering
- Transit Mixer Drives

Danfoss Power Solutions is a global manufacturer and supplier of high-quality hydraulic and electronic components. We specialize in providing state-of-the-art technology and solutions that excel in the harsh operating conditions of the mobile off-highway market. Building on our extensive applications expertise, we work closely with our customers to ensure exceptional performance for a broad range of off-highway vehicles.

We help OEMs around the world speed up system development, reduce costs and bring vehicles to market faster.

Danfoss – Your Strongest Partner in Mobile Hydraulics.

Go to www.powersolutions.danfoss.com for further product information.

Wherever off-highway vehicles are at work, so is Danfoss.

We offer expert worldwide support for our customers, ensuring the best possible solutions for outstanding performance. And with an extensive network of Global Service Partners, we also provide comprehensive global service for all of our components.

Please contact the Danfoss Power Solution representative nearest you.

Comatrol

www.comatrol.com

Schwarz Müller-Inverter

www.schwarzmueller-inverter.com

Turolla

www.turollaocg.com

Valmova

www.valmova.com

Hydro-Gear

www.hydro-gear.com

Daikin-Sauer-Danfoss

www.daikin-sauer-danfoss.com

Local address:

Danfoss Power Solutions US Company

2800 East 13th Street
Ames, IA 50010, USA
Phone: +1 515 239 6000

Danfoss Power Solutions GmbH & Co. OHG

Krokamp 35
D-24539 Neumünster, Germany
Phone: +49 4321 871 0

Danfoss Power Solutions ApS

Nordborgvej 81
DK-6430 Nordborg, Denmark
Phone: +45 7488 2222

Danfoss Power Solutions

22F, Block C, Yishan Rd
Shanghai 200233, China
Phone: +86 21 3418 5200

Danfoss can accept no responsibility for possible errors in catalogues, brochures and other printed material. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alterations can be made without subsequential changes being necessary in specifications already agreed. All trademarks in this material are property of the respective companies. Danfoss and the Danfoss logotype are trademarks of Danfoss A/S. All rights reserved.