

ENGINEERING
TOMORROW

Danfoss

Catalog

Optyma™ condensing units



Easy

installation, easy
service and reliable
performance

www.danfoss.us/aftermarket

Catalog	Content
	Optyma™ condensing unit features..... 4 Optyma™ Indoor Condensing Units..... 5 Optyma™ condensing unit R134a - MBP 6 Optyma™ condensing unit R404A/R507 - MBP 10 Optyma™ condensing unit R448A/R449A - H/MBP 14 Optyma™ condensing unit R448A/R449A - MBP 16 Optyma™ condensing unit R452A - MBP 18 Optyma™ condensing unit R404A/R507 - LBP 20 Optyma™ condensing unit R290 – L/MBP..... 24 Optyma™ condensing unit R290 – L/MBP..... 26 Spare parts 28 Spare parts & accessories list..... 31 Electrical wiring diagrams 33 Dimensions 40 Optyma™ Slim Outdoor Condensing Units 45 Optyma™ Slim condensing unit R448A/R449A - MBP..... 46 Optyma™ Slim condensing unit R134a - MBP..... 50 Optyma™ Slim condensing unit R404A/R507 - MBP 54 Optyma™ Slim condensing unit R452A - MBP 58 Optyma™ Slim condensing unit R454C/R455A - MBP..... 62 Optyma™ Slim condensing unit R448A/R449A - LBP 66 Optyma™ Slim condensing unit R404A/R507 - LBP..... 68 Optyma™ Slim condensing unit R452A - LBP..... 70 Optyma™ Slim condensing unit R454C/R455A - LBP 72 Optyma™ Slim Spare parts & accessories - MBP 74 Optyma™ Slim Spare parts & accessories - LBP 75 Optyma™ Slim Spare parts & accessories - WK (MBP) & WL (LBP) 76 Electrical wiring diagrams 77 Dimensions 83

Optyma™ condensing unit nomenclature / model no.

	Application	Design	Refrigerant	Condenser size	HP rating	Certification	Version	Electrical code
	H	N	X	M	0300	U	WG000	Q
Application:	Electrical code:							
L: Low	B: Compressor & fan(s), 115V, 1ph, 60 Hz							
H: High or Medium / High	N: Compressor & fan(s), 230V, 1ph, 60 Hz							
M: Medium or Low/Medium	Q: Compressor 208-230V, 3ph, 60 Hz							
U: Universal Low / Medium / High	Fan(s) 230V, 1ph, 60 Hz							
Design:	R: Compressor 460V, 3ph, 60 Hz							
C: Air cooled condenser, Single fan, Recip	Fan(s) 460V, 1ph, 60 Hz							
J: Air cooled condenser, Slim Design, Recip	Version:							
G: Air cooled condenser, Twin fan, Recip	DF: Plastic baseplate							
N: Air cooled condenser, Slim Design, Scroll	WA: Power cord							
R: Air cooled condenser, Twin fan, Scroll	WB: Power cord, Receiver							
Refrigerant:	WC: Electrical box, Receiver							
G: R134a	WD: Electrical box, Receiver, Low pressure control							
H: R404A/R507/R452A	WE: Electrical box, Receiver, Dual pressure control, Fan cycling control, larger than 3HP dual fan units use KPU fan cycling control							
M: R22 Replacement	WF: WE + Filter drier, Sight glass, Solenoid valve with coil							
N: R290	WG: BX, Receiver, Dual pressure control, Fan speed controller or Fan cycling, Defrost Timer, Outdoor enclosure (MBP)							
J: R454C/R455A/R134a*/R404A/R448A/R449A	WH: Electrical box, Receiver, Dual pressure control, Fan speed controller or Fan cycling, Defrost timer, Outdoor enclosure, Suction Accumulator (LBP)							
Z: R404A/R507A/R134a*/R448A/R449A/R452A	WJ: Electrical box, Receiver, Dual pressure control, Fan cycling control, Filter drier, Sight glass							
X: R448A/R449A/R404A/R507A/R134a/R452A	WK: WG + Low Ambient Temperature							
Y: R448A/R449A/R404A/R507A/R452A	WL: WH + Low Ambient Temperature							
S: R410A/R454B								
Condenser size:								
C: Fin and Tube condenser size 110F ambient								
M: Microchannel Condenser size 115F ambient								
HP rating:								
HP rating in hundredths of HP, i.e.: 0033=1/3 HP, 1000 = 10 HP								
Certification:								
R: UL Recognized								
U: UL Listed								

* R134a is only available in MBP units without low-ambient kit

Rating Conditions (ARI)

Application	LBP	MBP/HBP
Ambient Temp	90°F	90°F
Return Gas	40°F	65°F
SubCooling	5°F	5°F

OPTYMA

MADE IN USA

Model

HCGC0033RWB000B

Danfoss Code

114N2022

Serial Number

012345AU0116

Compressor: 115V-60Hz-1Ph LRA43.1A RLA8.9A

Fan Motor: 115V FLA 0.45 A

MCA: 11.6 A

Max. Fuse/HACR breaker: 20.0

Design Pressure: Low/High side 87/185psi

Refrigerant: R134a

Oil Type: Polyolester

Wiring diagram: 119-3987

HCGC0033RWB000B (Model no.)

114N2022 (Code no.)

Date Code: XXXXXXXAU0116
7 digits = serial #
AU = Assembled in US
01 = Week of Manufacture
16 = Year of Manufacture

OPTYMA

ASSEMBLED IN MEXICO

Model

HCGC0033RWB000B

Danfoss Code

114N2022

Serial Number

012345AM0116

Compressor: 115V-60Hz-1Ph LRA43.1A RLA8.9A

Fan Motor: 115V FLA 0.45 A

MCA: 11.6 A

Max. Fuse/HACR breaker: 20.0

Design Pressure: Low/High side 87/185psi

Refrigerant: R134a


Oil Type: Polyolester

Wiring diagram: 119-3987

HCGC0033RWB000B (Model no.)

114N2022 (Code no.)

Date Code: XXXXXXXAM0116
7 digits = serial #
AM = Assembled in Mexico
01 = Week of Manufacture
16 = Year of Manufacture



Fan	Model no	Version	Electrical code	Code no	Compressor model	Amb. temp.	Capacity range in (btu/hr) at evaporating temperature										Power consumption [W] at evap. temp. 20 °F
						°F	0	5	10	15	20	25	30	35	40	45	
Single fan	UCGC0020R	WA	B	114N2017	NF6.1FX.2	90	1050	1200	1350	1500	1700	1850	2050	2250	2450	2700	250
						95	1000	1150	1300	1450	1600	1800	2000	2200	2400	2600	
						100	950	1100	1250	1400	1550	1750	1900	2100	2300	2500	
						110	900	1000	1150	1300	1450	1600	1800	1950	2150	2350	
	UCGC0025R	WB	B	114N2019	NF7.3FX.2	90	1250	1400	1600	1750	1950	2150	2400	2600	2850	3100	350
						95	1200	1350	1550	1700	1900	2100	2300	2500	2750	3000	
						100	1150	1300	1450	1650	1800	2000	2200	2450	2650	2900	
						110	1050	1200	1350	1550	1700	1900	2050	2250	2450	2700	
	HCGC0033R	WB	B	114N2022	NF11FX	90	-	2050	2300	2550	2850	3100	3450	3750	4100	4450	450
						95	-	1950	2200	2450	2750	3000	3300	3650	3950	4300	
						100	-	1900	2100	2350	2600	2900	3200	3500	3800	4150	
						110	-	1750	1950	2200	2450	2700	2950	3250	3550	3850	
	UCGC0050R	WB	B	114N2023	SC18G	90	2350	2700	3050	3450	3800	4250	4700	5150	5650	6150	700
						95	2300	2600	2950	3300	3700	4100	4500	4950	5400	5900	
						100	2200	2500	2800	3200	3550	3950	4350	4750	5200	5650	
						110	2000	2300	2600	2900	3250	3600	4000	4400	4800	5200	
	HCGC0055R	WB	B	114N2025	NT6215Z	90	-	2900	3300	3800	4300	4850	5450	6100	6700	7350	700
						95	-	2800	3200	3650	4150	4650	5250	5850	6450	7050	
						100	-	2650	3050	3500	3950	4500	5050	5600	6150	6750	
						110	-	-	-	3250	3700	4150	4700	-	-	-	
	HCGC0075R	WB	B	114N2027	NJ6220Z	90	-	4350	4850	5550	6250	7150	8050	9100	10100	11200	1000
						95	-	4100	4700	5350	6100	6950	7850	8800	9800	10850	
	HCGC0075U	WC	N	114N2028		100	-	3900	4500	5150	5900	6750	7600	8550	9500	10450	
						110	-	-	-	4850	5600	6400	7250	8100	-	-	
	HCGC0100U	WD	N	114N2029	NJ6226Z	90	-	6800	7450	8200	9050	9950	10950	12000	13050	14200	1200
						95	-	6300	7000	7750	8550	9450	10400	11450	12450	13550	
						100	-	-	6550	7300	8100	8950	9900	10900	11850	12900	
						110	-	-	-	6500	7250	8100	9000	-	-	-	
	MCGB0045R	60	B	114N0006	SC15G	90	1858	2118	2394	2687	2995	3319	3658	4011	4377	4755	602
						95	1762	2018	2290	2576	2877	3193	3524	3868	4224	4592	
						100	1561	1810	2072	2348	2636	2938	3253	3580	3917	-	
						110	1457	1701	1960	2230	2514	2809	-	-	-	-	
	MCGB0050R	60	B	114N0007	SC18G	90	2175	2479	2805	3152	3519	3906	4311	4733	5168	5615	668
						95	2085	2384	2703	3041	3399	3773	4165	4570	4988	5416	
						100	2003	2295	2605	2933	3278	3639	4015	4403	4801	5208	
						110	1854	2127	2413	2716	3032	3360	-	-	-	-	

Test condition

 Return gas temperature 65°F
 Subcooling 5°F

Electrical code
B: Compressor & fan(s) 115V, 1 ph, 60 Hz
N: Compressor & fan(s) 230V, 1 ph, 60 Hz

Version
WA: Power cord
WB: Power cord, Receiver
WC: Electrical box, Receiver
WD: Electrical box, Receiver, Low pressure control

 HP rating in hundredths of HP, i.e.: 033=1/3hp, (UCGC0100U:0100=1hp)
 Power consumption referred at 90°F ambient temperature

Catalog

Optyma™ condensing unit R134a - MBP

Model no	Condenser fan	Receiver lbs @ 90%	Dimensions (in) ⁽¹⁾						Weight (lbs)	MCA (A)	Oil Type / Charge (oz)	Wiring diagram code ⁽²⁾
	Fan blade Ø (in)		Figure	Height H (in)	Width W (in)	Depth D (in)	Suction line	Liquid line	Gross			
UCGC0020R	8	---	2	9.0	11	14	3/8" F	1/4" F	32	6.1	POE / 10.8	119-3987
UCGC0025R	8	2.16	2	9.1	13.5	17	3/8" F	1/4" F	45	6.4	POE / 10.8	119-3987
HCGC0033R	9	2.16	2	10.3	13.5	17	3/8" F	1/4" F	47	11.7	POE / 10.8	119-3987
UCGC0050R	10	2.16	3	11.8	13.5	17	1/2" F	1/4" F	57	13.7	POE / 20.3	119-3983
HCGC0055R	10	4	4	11.9	14	18	3/8" F	1/4" F	67	15	POE / 19.6	119-3988
HCGC0075R	12	4	4	13.2	16.9	19	1/2" F	1/4" F	100	16	POE / 30.1	119-3983
HCGC0075U		4	4							10.5		119-3985
HCGC0100U	12	4	4	16.1	21.1	20.8	1/2" F	1/4" F	113	11.2	POE / 30.1	119-3990
MCGB0045R	9	-	17a	10.2	13	17	5/16" S	1/4" S	50	11.2	POE / 16.9	119-3993
MCGB0050R	9	-	17a	10.2	13.5	17	3/8" S	1/4" S	53	13.1	POE / 18.6	119-3992

⁽¹⁾ Dimensions (in) available on page 40

⁽²⁾ Wiring diagram available on page 33

For spare parts, see pages 28

Fan	Model no	Version	Electrical code	Code no	Compressor model	Amb. temp.	Capacity range in (btu/hr) at evaporating temperature								Power consumption [W] at evap. temp. 25°F	Power consumption [W] at evap. temp. 20°F	AWEF
						°F	15	20	25	30	35	40	45	50			
Single fan	HCZC0150U	WJ	N	114N3601	MTZ18	90	5500	6305	7192	8163	9216	10350	11560	12840	1220	1167	7.17
			Q	114N3602		95	5194	5975	6835	7775	8794	9889	11060	12290			
			R	114N3603		100	4889	5645	6477	7386	8369	9426	10550	11740			
						105	4585	5315	6118	6994	7942	8960	10040	11190			
						110	4282	4985	5758	6601	7513	8491	9532	10630			
	HCZC0200U	WJ	N	114N3604	MTZ22	90	7245	8343	9529	10800	12160	13590	15090	16660	1460	1387	7.35
			Q	114N3605		95	6921	7981	9123	10350	11650	13020	14460	15960			
			R	114N3606		100	6592	7611	8708	9881	11130	12440	13820	15250			
						105	6255	7232	8283	9404	10590	11850	13160	14530			
						110	5912	6845	7847	8916	10050	11240	12490	13790			
	HCZC0250U	WJ	N	114N3607	MTZ28	90	9583	10990	12480	14040	15680	17380	19140	20960	1834	1730	7.35
			Q	114N3608		95	9147	10520	11960	13470	15060	16700	18400	20140			
			R	114N3609		100	8704	10030	11430	12900	14420	16000	17640	19310			
						105	8257	9544	10900	12310	13780	15300	16860	18470			
						110	7804	9049	10350	11710	13130	14580	16080	17610			
	HCZC0275U	WJ	N	114N3610	MTZ36	90	12470	14150	15930	17820	19800	21880	24030	26270	2400	2253	7.32
			Q	114N3611		95	11890	13520	15260	17090	19010	21010	23090	25240			
			R	114N3612		100	11320	12900	14580	16350	18210	20140	22140	24210			
						105	10740	12280	13910	15620	17400	19260	21190	23170			
						110	10170	11660	13230	14880	16590	18380	20220	22110			
	HCZC0300U	WJ	N	114N3614	MTZ40	90	14490	16220	18070	20050	22140	24350	26680	29110	2640	2469	7.6
			Q	114N3615		95	13690	15400	17230	19170	21230	23410	25690	28080			
			R	114N3616		100	12910	14600	16410	18320	20350	22490	24730	27070			
						105	12160	13830	15610	17500	19500	21600	23800	26090			
						110	11440	13090	14850	16710	18670	20740	22890	25130			
Two fan	HGZC0400U	WJ	N	114N3617	MTZ50	90	16350	19020	21910	25000	28280	31760	35410	39220	3093	2950	7.13
			Q	114N3618		95	15700	18300	21100	24090	27260	30610	34130	37800			
			R	114N3619		100	15010	17540	20240	23130	26200	29430	32810	36340			
						105	14290	16730	19350	22140	25090	28200	31460	34840			
						110	13530	15900	18430	21120	23960	26940	30060	33310			
	HGZC0500U	WJ	N	114N3621	MTZ64	90	20950	24290	27860	31650	35630	39800	44130	48600	3778	3574	7.69
			Q	114N3622		95	20080	23320	26780	30440	34290	38310	42470	46770			
			R	114N3623		100	19170	22320	25660	29200	32910	36780	40780	44910			
						105	18220	21270	24510	27930	31500	35220	39070	43020			
						110	17240	20200	23330	26620	30060	33630	37320	41110			
	HGZC0700U	WJ	Q	114N3626	MTZ80	90	27750	31880	36300	41010	46000	51260	56750	62480	4690	4429	8.07
			R	114N3627		95	26630	30630	34920	39480	44300	49370	54680	60200			
						100	25500	29380	33530	37930	42590	47480	52590	57900			
						105	24350	28110	32120	36370	40860	45570	50490	55590			
						110	23200	26830	30700	34800	39120	43650	48370	53270			
	HGZC0900U	WJ	Q	114N3628	MTZ100	90	32220	37130	42390	48000	53940	60200	66750	73590	6376	6065	7.33
			R	114N3629		95	30500	35270	40360	45790	51530	57560	63880	70460			
						100	28780	33400	38330	43560	49090	54900	60980	67300			
						105	27070	31530	36280	41320	46640	52220	58060	64120			
						110	25360	29660	34230	39070	44180	49530	55110	60910			
	HGZC1000U	WJ	Q	114N3631	MTZ125	90	40340	46370	52830	59690	66930	74540	82480	90720	7203	6815	7.9
			R	114N3632		95	38310	44150	50390	57010	63980	71300	78920	86820			
						100	36290	41930	47940	54300	61000	68020	75320	82880			
						105	34280	39710	45480	51580	58000	64700	71680	78890			
						110	32270	37480	43000	48840	54960	61350	68000	74860			
	HGZC1200U	WJ	Q	114N3633	MTZ144	90	52460	59230	66410	73990	81940	90260	98920	107900	9064	8635	7.77
			R	114N3634		95	50300	56870	63830	71160	78840	86860	95190	103800			
						100	48100	54470	61200	68270	75670	83390	91400	99680			
						105	45860	52020	58510	65320	72440	79850	87530	95470			
						110	43590	49530	55780	62320	69150	76250	83590	91170			
	HGZC1350U	WJ	Q	114N3636	MTZ160	90	58110	65480	73290	81500	90100	99080	108400	118000	9819	9306	7.8
			R	114N3637		95	55650	62820	70390	78350	86670	95340	104300	113600			
						100	53150	60110	67450	75140	83180	91540	100200	109100			
						105	50600	57350	64440	71880	79630	87670	96000	104600			
						110	48010	54540	61390	68550	76010	83750	91730	99950			

Test condition

 Return gas temperature 65°F
 Subcooling 5°F

Electrical code
Q: Compressor 208-230V, 3ph, 60 Hz / Fan(s) 230V, 1ph, 60 Hz
R: Compressor 460V, 3ph, 60 Hz / Fan(s) 460V, 1ph, 60 Hz

Version
WJ: Electrical box, Receiver, Dual pressure control, Fan cycling control, Filter drier, Sight glass

 HP rating in hundredths of HP, ie.: 033=1/3hp, (UCGC0100U:0100=1hp)
 Power consumption referred at 90°F ambient temperature

Catalog

Optyma™ condensing unit R134a - MBP

Model no	Condenser fan	Receiver lbs @ 90%	Dimensions (in) ⁽¹⁾						Weight (lbs)	MCA (A)	Oil Type / Charge (oz)	Wiring diagram code ⁽²⁾
	Fan blade Ø (in)		Figure	Height H (in)	Width W (in)	Depth D (in)	Suction line	Liquid line	Gross			
HCZC0150U	14	7	6a	16.3	20.1	25	½" S	¾" S	130	N: 14 Q: 9 R: 6	POE/29	119-6401 119-6403 119-6406
HCZC0200U	14	7	6a	16.3	20.1	25	½" S	¾" S	130	N: 17 Q: 11 R: 6	POE/29	119-6401 119-6403 119-6406
HCZC0250U	14	7	6a	17.4	27.6	19.7	⅝" S	¾" S	140	N: 24 Q: 16 R: 8	POE/29	119-6401 119-6403 119-6406
HCZC0275U	14	7	6a	17.4	27.6	19.7	⅝" S	¾" S	150	N: 28 Q: 17 R: 9	POE/29	119-6401 119-6403 119-6406
HCZC0300U	18	7	6a	21.4	31.5	24	⅝" S	¾" S	150	N: 40 Q: 23 R: 12	POE/29	119-6401 119-6403 119-6406
HGZC0400U	14	15	8a	21.8	39.4	27.6	⅞" S	½" S	210	N: 36 Q: 24 R: 12	POE/63	119-6402 119-6404 119-6405
HGZC0500U	18	18.5	8a	26.6	47.2	31.5	⅞" S	½" S	300	N: 52 Q: 32 R: 16	POE/63	119-6402 119-6404 119-6405
HGZC0700U	18	28	8a	26.6	47.2	31.5	1 ⅛" S	½" S	300	Q: 40 R: 17	POE/63	119-6404 119-6405
HGZC0900U	22	33	9a	34.4	34.3	59.1	1 ⅞" S	½" S	500	Q: 50 R: 26	POE/132	119-6404 119-6405
HGZC1000U	22	33	9a	34.4	34.3	59.1	1 ⅞" S	½" S	500	Q: 60 R: 30	POE/132	119-6404 119-6405
HGZC1200U	22	33	9a	34.4	34.3	59.1	1 ⅞" S	½" S	510	Q: 69 R: 33	POE/132	119-6404 119-6405
HGZC1350U	22	40	9a	34.4	34.3	59.1	1 ⅞" S	½" S	540	Q: 75 R: 38	POE/132	119-6404 119-6405

⁽¹⁾ Dimensions (in) available on page 40

⁽²⁾ Wiring diagram available on page 33
For spare parts, see pages 28

Fan	Model no	Version	Electrical code	Code no	Compressor model	Amb. temp.	Capacity range in (btu/hr) at evaporating temperature										Power consumption [W] at evap. temp. 20° F	
						°F	0	5	10	15	20	25	30	35	40	45		
Single fan	UCHC0020R	WA	B	114N2316	TF4CLX	90	1000	1100	1250	1400	1500	1650	1800	2000	2150	2300	300	
						95	950	1050	1200	1300	1450	1600	1750	1900	2050	2200		
						100	900	1000	1100	1250	1350	1500	1650	1800	-	-		
						110	800	900	1000	1150	1250	1400	1500	-	-	-		
	UCHC0025R	WB	B	114N2318	NF5.5CLX	90	1650	1850	2050	2250	2450	2650	2900	3150	3400	3650	450	
						95	1600	1750	1950	2150	2350	2550	2800	3000	3250	3500		
						100	1500	1650	1850	2050	2250	2450	2650	2900	3100	3350		
						110	1350	1550	1700	1850	2050	2250	-	-	-	-		
	UCHC0033R	WB	B	114N2321	NF7CLX	90	2050	2250	2500	2750	3000	3250	3550	3850	4100	4450	550	
						95	1950	2150	2400	2600	2850	3100	3400	3650	3950	4250		
						100	1850	2050	2250	2500	2700	2950	3200	3500	3750	4050		
						110	1650	1850	2050	-	-	-	-	-	-	-		
	UCHC0050R	WB	B	114N2324	SC10CL	90	2450	2750	3100	3400	3750	4100	4500	4900	5250	5700	700	
						95	2300	2600	2900	3200	3550	3850	4250	4600	4950	5350		
	UCHC0050U	WC	N	114N2325		100	2100	2400	2700	3000	3300	3600	3950	4300	4650	5000		
						110	1850	2100	2350	2600	2850	3150	-	-	-	-		
	HCHC0060U	WC	B	114N2328	SC12MLX	90	3400	3750	4200	4600	5050	5550	6050	6600	7100	7700	900	
						95	3200	3550	3950	4350	4800	5250	5750	6250	6750	7300		
						100	3000	3350	3700	4100	4500	4950	5400	5900	6400	6900		
						110	2650	2950	3300	3700	4050	4450	4900	-	-	-		
	HCHC0075R	WB	B	114N2330	SC18MLX	90	4400	4950	5500	6150	6800	7500	8250	9000	9800	10650	1000	
						95	4150	4700	5250	5850	6500	7200	7900	8650	9400	10250		
	HCHC0075U	WC	N	114N2331		NT6220GK	100	3900	4450	5000	5600	6200	6850	7550	8300	9050		9850
							110	3500	4000	4550	5100	5700	6350	7000	-	-		-
	HCHC0100U	WD	N	114N2332	NT6222GK	90	-	5900	6650	7450	8200	9000	9850	10650	11450	12300	1300	
						95	-	5600	6350	7100	7800	8600	9350	10150	10950	11750		
						100	-	-	6000	6700	7400	8150	8900	9650	10400	11150		
						110	-	-	-	6100	6750	7400	8100	8800	-	-		

Test condition

Return gas temperature 65°F
Subcooling 5°F

Electrical code

B: Compressor & fan(s) 115V, 1 ph, 60 Hz
N: Compressor & fan(s) 230V, 1 ph, 60 Hz

Version

WA: Power cord
WB: Power cord, Receiver
WC: Electrical box, Receiver
WD: Electrical box, Receiver, Low pressure control

HP rating in hundredths of HP, ie.: 033=1/3hp, (UCGC0100U:0100=1hp)
Power consumption referred at 90°F ambient temperature

Catalog

Optyma™ condensing unit R404A/R507 - MBP

Model no	Condenser fan	Receiver lbs @ 90%	Dimensions (in) ⁽¹⁾						Weight (lbs)	MCA (A)	Oil Type / Charge (oz)	Wiring diagram code ⁽²⁾
	Fan blade Ø (in)		Figure	Height H (in)	Width W (in)	Depth D (in)	Suction line	Liquid line	Gross			
UCHC0020R	9	-	1	10.2	12.3	14	3/8" F	1/4" F	39	5.2	POE / 9	119-3987
UCHC0025R	9	2.16	2	10.3	13.5	17	3/8" F	1/4" F	50	6.2	POE / 11	119-3987
UCHC0033R	9	2.16	2	10.3	13.5	17	3/8" F	1/4" F	49	7.6	POE / 11	119-3987
UCHC0050R	10	2.16	3	11.8	13.5	17	3/8" F	1/4" F	60	11.8	POE / 19	119-3993
UCHC0050U							1/2" F			4.3		119-3995
HCHC0060U	12	4	3	14	16.3	19	3/8" F	1/4" F	70	14.1	POE / 20	119-3983
										7.1		119-3995
HCHC0075R	12	4	3	13.3	17	19	1/2" S	1/4" F	78	22.2	POE / 20	119-3992
HCHC0075U			4						91	9.4		119-3990
HCHC0100U	12	4	4	13.3	16.9	19	1/2" S	1/4" F	91	10.8	POE / 20	119-3990

⁽¹⁾Dimensions (in) available on page 40

⁽²⁾Wiring diagram available on page 33
For spare parts, see pages 28

Fan	Model no	Version	Electrical code	Code no	Compressor model	Amb. temp.	Capacity range in (btu/hr) at evaporating temperature								Power consumption [W] at evap. temp. 25°F	Power consumption [W] at evap. temp. 20°F	AWEF
						°F	15	20	25	30	35	40	45	50			
Single fan	HCZC0150U	WJ	N	114N3601	MTZ18	90	9989	11300	12670	14100	15590	17120	18700	20310	2066	1996	7.07
			Q	114N3602		95	9438	10690	12000	13370	14780	16240	17750	19280			
			R	114N3603		100	8879	10080	11320	12620	13970	15360	16790	18250			
						105	8313	9451	10640	11870	13150	14470	15820	17200			
						110	7742	8822	9949	11120	12330	13580	-	-			
	HCZC0200U	WJ	N	114N3604	MTZ22	90	13320	14880	16510	18210	19960	21750	23590	25460	2365	2259	7.93
			Q	114N3605		95	12660	14140	15690	17290	18950	20650	22380	24150			
			R	114N3606		100	11970	13380	14840	16360	17920	19520	21160	22820			
						105	11260	12590	13970	15400	16870	18380	19910	21470			
						110	10530	11780	13080	14420	15800	17210	-	-			
	HCZC0250U	WJ	N	114N3607	MTZ28	90	16910	18680	20500	22380	24310	26270	28260	30270	3056	2914	7.7
			Q	114N3608		95	16110	17790	19520	21310	23130	24980	26870	28760			
			R	114N3609		100	15290	16880	18530	20210	21930	23680	25450	27240			
						105	14450	15960	17510	19100	20720	22370	24030	25700			
						110	13600	15020	16480	17970	19490	21040	-	-			
	HCZC0275U	WJ	N	114N3610	MTZ36	90	20820	23050	25350	27690	30080	32500	34930	37360	3824	3599	7.69
			Q	114N3611		95	19740	21860	24050	26280	28540	30830	33130	35420			
			R	114N3612		100	18660	20680	22750	24860	27000	29160	31330	33490			
						105	17580	19490	21450	23440	25460	27500	29540	31560			
						110	16500	18310	20150	22030	23930	25850	-	-			
	HCZC0300U	WJ	N	114N3614	MTZ40	90	23390	25810	28300	30830	33380	35950	38520	41060	4281	4026	7.51
			Q	114N3615		95	22180	24490	26850	29240	31660	34090	36510	38910			
			R	114N3616		100	20980	23170	25400	27660	29940	32230	34510	36770			
						105	19780	21850	23950	26080	28230	30390	32530	34640			
						110	18590	20530	22510	24520	26540	28550	-	-			
Two fan	HGZC0400U	WJ	N	114N3617	MTZ50	90	31480	35020	38720	42580	46590	50730	54980	59340	5051	4839	8.68
			Q	114N3618		95	29880	33270	36820	40510	44330	48280	52330	56480			
			R	114N3619		100	28260	31490	34880	38390	42040	45790	49650	53580			
						105	26600	29690	32910	36260	39720	43280	46940	50670			
						110	24930	27860	30920	34100	37380	40760	-	-			
	HGZC0500U	WJ	N	114N3621	MTZ64	90	38340	42410	46630	50980	55440	59980	64600	69260	6437	6127	8.23
			Q	114N3622		95	36310	40200	44210	48350	52580	56900	61280	65700			
			R	114N3623		100	34270	37970	41780	45700	49720	53810	57960	62130			
						105	32220	35720	39340	43050	46850	50710	54630	58570			
						110	30170	33480	36890	40390	43980	47620	-	-			
	HGZC0700U	WJ	Q	114N3626	MTZ80	90	49600	54670	59940	65380	70990	76730	82580	88530	8635	8206	8.03
			R	114N3627		95	47120	51940	56950	62120	67440	72890	78440	84070			
						100	44610	49190	53940	58840	63880	69030	74280	79600			
						105	42090	46420	50900	55530	60290	65160	70110	75130			
						110	39550	43630	47860	52220	56700	61280	-	-			
	HGZC0900U	WJ	Q	114N3628	MTZ100	90	60260	67010	74070	81430	89080	97000	105200	113500	10100	9728	8.59
			R	114N3629		95	57030	63470	70210	77230	84520	92050	99810	107800			
						100	53800	59940	66350	73030	79950	87110	94470	102000			
						105	50570	56400	62490	68820	75380	82160	89130	96270			
						110	47350	52870	58630	64620	70820	77230	-	-			
	HGZC1000U	WJ	Q	114N3631	MTZ125	90	75520	83250	91320	99710	108400	117400	126600	136000	12880	12330	8.32
			R	114N3632		95	71710	79080	86780	94770	103000	111600	120300	129300			
						100	67860	74880	82210	89800	97660	105700	114000	122500			
						105	63980	70660	77610	84810	92250	99910	107700	115700			
						110	60090	66410	72990	79800	86830	94050	-	-			
	HGZC1200U	WJ	Q	114N3633	MTZ144	90	87530	96260	105400	114800	124500	134500	144800	155200	14670	14000	8.04
			R	114N3634		95	83140	91470	100100	109100	118400	127900	137600	147500			
						100	78710	86630	94860	103400	112200	121200	130400	139800			
						105	74230	81750	89550	97630	106000	114500	123200	132000			
						110	69730	76830	84210	91840	99690	107700	-	-			
	HGZC1350U	WJ	Q	114N3636	MTZ160	90	94170	103400	112900	122900	133100	143600	154300	165200	16660	15820	7.9
			R	114N3637		95	89460	98240	107400	116800	126500	136500	146700	157000			
						100	84750	93100	101800	110800	120000	129500	139100	148900			
						105	80020	87960	96190	104700	113400	122400	131500	140700			
						110	75300	82810	90600	98630	106900	115300	-	-			

Test condition

Return gas temperature 65°F
Subcooling 5°F

Electrical code

N: Compressor & fan(s) 230V, 1 ph, 60 Hz
Q: Compressor 208-230V, 3ph, 60 Hz / Fan(s) 230V, 1ph, 60 Hz
R: Compressor 460V, 3ph, 60 Hz / Fan(s) 460V, 1ph, 60 Hz

Version

WJ: Electrical box, Receiver, Dual pressure control, Fan cycling control, Filter drier, Sight glass

HP rating in hundredths of HP, i.e.: 033=1/3hp, (UCGC0100U:0100=1hp)
Power consumption referred at 90°F ambient temperature

Catalog

Optyma™ condensing unit R404A/R507 - MBP

Model no	Condenser fan	Receiver lbs @ 90%	Dimensions (in) ⁽¹⁾						Weight (lbs)	MCA (A)	Oil Type / Charge (oz)	Wiring diagram code ⁽²⁾
	Fan blade Ø (in)		Figure	Height H (in)	Width W (in)	Depth D (in)	Suction line	Liquid line	Gross			
HCZC0150U	14	7	6a	16.3	20.1	25	½" S	¾" S	130	N: 14 Q: 9 R: 6	POE/29	119-6401 119-6403 119-6406
HCZC0200U	14	7	6a	16.3	20.1	25	½" S	¾" S	130	N: 17 Q: 11 R: 6	POE/29	119-6401 119-6403 119-6406
HCZC0250U	14	7	6a	17.4	27.6	19.7	⅝" S	¾" S	140	N: 24 Q: 16 R: 8	POE/29	119-6401 119-6403 119-6406
HCZC0275U	14	7	6a	17.4	27.6	19.7	⅝" S	¾" S	150	N: 28 Q: 17 R: 9	POE/29	119-6401 119-6403 119-6406
HCZC0300U	18	7	6a	21.4	31.5	24	⅝" S	¾" S	150	N: 40 Q: 23 R: 12	POE/29	119-6401 119-6403 119-6406
HGZC0400U	14	15	8a	21.8	39.4	27.6	⅞" S	½" S	210	N: 36 Q: 24 R: 12	POE/63	119-6402 119-6404 119-6405
HGZC0500U	18	18.5	8a	26.6	47.2	31.5	⅞" S	½" S	300	N: 52 Q: 32 R: 16	POE/63	119-6402 119-6404 119-6405
HGZC0700U	18	28	8a	26.6	47.2	31.5	1 ⅛" S	½" S	300	Q: 40 R: 17	POE/63	119-6404 119-6405
HGZC0900U	22	33	9a	34.4	34.3	59.1	1 ⅛" S	½" S	500	Q: 50 R: 26	POE/132	119-6404 119-6405
HGZC1000U	22	33	9a	34.4	34.3	59.1	1 ⅛" S	½" S	500	Q: 60 R: 30	POE/132	119-6404 119-6405
HGZC1200U	22	33	9a	34.4	34.3	59.1	1 ⅛" S	½" S	510	Q: 69 R: 33	POE/132	119-6404 119-6405
HGZC1350U	22	40	9a	34.4	34.3	59.1	1 ⅛" S	½" S	540	Q: 75 R: 38	POE/132	119-6404 119-6405

⁽¹⁾ Dimensions (in) available on page 40

⁽²⁾ Wiring diagram available on page 33
For spare parts, see pages 28

Fan	Model no	Version	Electrical code	Code no	Compressor model	Amb. temp.	Capacity range in (btu/hr) at evaporating temperature													Power consumption [W] at evap. temp. 20°F
						°F	-10	-5	0	5	10	15	20	25	30	35	40	45	50	
Single fan	HCYC0075R	C0001 C0002	N	114N2088 114N2107	MPT14RF	90				3050	3407	3779	4166	4567	4982	5409	5849	6302	6770	1027
						95				2907	3242	3594	3962	4345	4742	5153	5578	6018	6474	
						100				2764	3077	3409	3757	4122	4502	4897	5308	-	-	
						105				-	2913	3224	3553	3899	4262	4641	-	-	-	
						110						3039	3349	3676	4022					
	HCYC0100R	C0001 C0002	N	114N2089 114N2108	MX18TGa	90	2430	2786	3158	3543	3941	4351	4772	5204	5647	6101	6566	7044	7537	1202
						95	2279	2609	2955	3316	3691	4078		4891	5315	5751	6200	6663	-	
						100	-	2432	2752	3089	3440	3806	4185	4577	4982	5400	5833	-	-	
						105	-	-	2549	2861	3189	3532	3890	4262	4648	-	-	-	-	
						110				2633	2938	3258	3595	3947						
	HCYC0075R	C0001 C0002	B	114N2102 114N2109	MPT14RD	90				3148	3517	3892	4270	4652	5036	5421	5807	6193	6579	1077
						95				3004	3347	3696	4050	4408	4770	5134	5500	5868	6236	
						100				2860	3176	3500	3829	4165	4504	4848	5194	-	-	
						105				-	3005	3303	3609	3921	4238	4561	-	-	-	
						110						3106	3389	3677	3972					

Test condition

Return gas temperature 65°F
Subcooling 5°F

Electrical code

B: Compressor & fan(s) 115V, 1 ph, 60 Hz
N: Compressor & fan(s) 230V, 1 ph, 60 Hz

Version

C0001: Multi Pack
C0002: Single Pack

HP rating in hundredths of HP, ie.: 033=1/3hp, (UCGC0100U:0100=1hp)
Power consumption referred at 90°F ambient temperature

Catalog

Optyma™ condensing unit R448A/R449A - H/MBP

Model no	Condenser fan	Receiver lbs @ 90%	Dimensions (in) ⁽¹⁾						Weight (lbs)	MCA (A)	Oil Type / Charge (oz)	Wiring diagram code ⁽²⁾
	Fan blade Ø (in)		Figure	Height H (in)	Width W (in)	Depth D (in)	Suction line	Liquid line	Gross			
HCYC0075R	10	3.15	10	11.73	15.98	19.02	3/8" SAE M FL	1/4" ID S	30.78	8.11	POE / 14.1	119-9231
HCYC0100R	10	3.15	11	11.73	15.98	19.02	3/8" SAE M FL	1/4" ID S	38.34	8.6	POE / 17.6	119-9231
HCYC0075R	10	3.15	10	11.73	15.98	19.02	3/8" SAE M FL	1/4" ID S	38.56	18.2	POE / 14.1	119-9233

⁽¹⁾Dimensions (in) available on page 40

⁽²⁾Wiring diagram available on page 33
For spare parts, see pages 28

Fan	Model no	Version	Electrical code	Code no	Compressor model	Amb. temp.	Capacity range in (btu/hr) at evaporating temperature								Power consumption [W] at evap. temp. 25°F	Power consumption [W] at evap. temp. 20°F	AWEF
						°F	15	20	25	30	35	40	45	50			
Single fan	HCZC0150U	WJ	N	114N3601	MTZ18	90	8586	9756	10990	12280	13620	15020	16460	17960	1782	1700	7.58
			Q	114N3602		95	8110	9234	10420	11650	12950	14290	15680	17110			
			R	114N3603		100	7644	8723	9857	11040	12280	13570	14900	16270			
						105	7188	8222	9308	10440	11630	12860	14130	15450			
						110	6744	7732	8770	9857	10990	12160	13380	14630			
	HCZC0200U	WJ	N	114N3604	MTZ22	90	11590	12990	14490	16080	17750	19500	21320	23210	2142	2034	8.16
			Q	114N3605		95	11060	12390	13820	15330	16930	18600	20330	22130			
			R	114N3606		100	10530	11800	13160	14590	16110	17700	19350	21060			
						105	10010	11210	12500	13860	15300	16810	18380	20000			
						110	9488	10630	11850	13140	14500	15930	17410	18950			
	HCZC0250U	WJ	N	114N3607	MTZ28	90	14170	15860	17660	19550	21540	23610	25750	27960	2619	2479	8.2
			Q	114N3608		95	13520	15130	16830	18640	20530	22500	24540	26650			
			R	114N3609		100	12880	14400	16020	17730	19530	21400	23350	25350			
						105	12240	13680	15220	16840	18540	20320	22160	24060			
						110	11600	12970	14420	15950	17560	19240	20980	22780			
	HCZC0275U	WJ	N	114N3610	MTZ36	90	18050	20130	22290	24530	26830	29190	31570	33990	3486	3273	7.7
			Q	114N3611		95	17220	19200	21270	23400	25590	27830	30100	32390			
			R	114N3612		100	16390	18270	20240	22270	24350	26470	28630	30800			
						105	15560	17350	19210	21130	23110	25120	27160	29220			
						110	14720	16420	18180	20000	21870	23770	25700	27640			
	HCZC0300U	WJ	N	114N3614	MTZ40	90	20390	22700	25090	27560	30080	32640	35230	37820	3929	3679	7.69
			Q	114N3615		95	19430	21630	23920	26260	28660	31090	33550	36020			
			R	114N3616		100	18470	20570	22740	24970	27240	29550	31880	34210			
						105	17520	19510	21560	23670	25830	28010	30210	32420			
						110	16570	18450	20390	22380	24410	26480	28550	30630			
Two fan	HGZC0400U	WJ	N	114N3617	MTZ50	90	26130	29570	33220	37070	41100	45300	49670	54170	4562	4309	8.86
			Q	114N3618		95	24900	28200	31690	35380	39240	43270	47450	51770			
			R	114N3619		100	23660	26820	30160	33690	37390	41240	45240	49370			
						105	22410	25430	28630	31990	35520	39210	43020	46970			
						110	21160	24040	27090	30300	33660	37170	40810	44570			
	HGZC0500U	WJ	N	114N3621	MTZ64	90	32200	36160	40310	44650	49160	53810	58600	63500	5610	5288	8.49
			Q	114N3622		95	30610	34410	38400	42570	46890	51360	55960	60660			
			R	114N3623		100	29040	32680	36510	40500	44640	48920	53320	57820			
						105	27480	30970	34620	38440	42410	46500	50710	55010			
						110	25940	29270	32760	36400	40180	44090	48110	52210			
	HGZC0700U	WJ	Q	114N3626	MTZ80	90	43870	48970	54330	59930	65750	71780	77980	84330	7519	7090	8.55
			R	114N3627		95	41900	46800	51930	57300	62880	68650	74590	80670			
						100	39930	44610	49530	54660	60000	65520	71190	77000			
						105	37940	42420	47120	52020	57120	62380	67800	73340			
						110	35950	40220	44700	49380	54230	59250	64410	69690			
	HGZC0900U	WJ	Q	114N3628	MTZ100	90	52540	59390	66680	74390	82510	91020	99900	109100	9131	8701	8.74
			R	114N3629		95	49960	56530	63520	70920	78720	86890	95410	104300			
						100	47410	53700	60400	67490	74960	82790	90960	99450			
						105	44890	50900	57310	64090	71240	78730	86550	94680			
						110	42410	48140	54250	60720	67550	74710	82180	89940			
	HGZC1000U	WJ	Q	114N3631	MTZ125	90	66450	74950	83960	93470	103400	113900	124700	135900	11540	10950	8.73
			R	114N3632		95	63170	71330	79980	89100	98690	108700	119100	129900			
						100	59930	67740	76030	84770	93960	103600	113500	123900			
						105	56720	64190	72110	80480	89270	98470	108000	117900			
						110	53550	60670	68240	76230	84630	93410	102600	112000			
	HGZC1200U	WJ	Q	114N3633	MTZ144	90	78110	86970	96280	106000	116200	126700	137500	148700	13150	12470	8.61
			R	114N3634		95	74470	82980	91920	101300	111000	121100	131600	142300			
						100	70870	79040	87620	96590	105900	115600	125600	135900			
						105	67330	75150	83370	91970	100900	110200	119800	129600			
						110	63850	71320	79180	87400	95950	104800	114000	123400			
	HGZC1350U	WJ	Q	114N3636	MTZ160	90	83580	92920	102700	112900	123500	134500	145800	157300	14990	14190	8.12
			R	114N3637		95	79660	88630	98030	107800	118000	128500	139300	150400			
						100	75790	84400	93410	102800	112600	122600	133000	143600			
						105	71990	80220	88850	97840	107200	116800	126700	136800			
						110	68240	76110	84350	92930	101800	111000	120500	130100			

Test condition

Return gas temperature 65°F
Subcooling 5°F

Electrical code

Q: Compressor 208-230V, 3ph, 60 Hz / Fan(s) 230V, 1ph, 60 Hz
R: Compressor 460V, 3ph, 60 Hz / Fan(s) 460V, 1ph, 60 Hz

Version

WJ: Electrical box, Receiver, Dual pressure control, Fan cycling control, Filter drier, Sight glass

HP rating in hundredths of HP, i.e.: 033=1/3hp, (UCGC0100U:0100=1hp)
Power consumption referred at 90°F ambient temperature

Catalog
Optyma™ condensing unit R448A/R449A - MBP

Model no	Condenser fan	Receiver lbs @ 90%	Dimensions (in) ⁽¹⁾						Weight (lbs)	MCA (A)	Oil Type / Charge (oz)	Wiring diagram code ⁽²⁾
	Fan blade Ø (in)		Figure	Height H (in)	Width W (in)	Depth D (in)	Suction line	Liquid line	Gross			
HCZC0150U	14	7	6a	16.3	20.1	25	½" S	¾" S	130	N: 14 Q: 9 R: 6	POE/29	119-6401 119-6403 119-6406
HCZC0200U	14	7	6a	16.3	20.1	25	½" S	¾" S	130	N: 17 Q: 11 R: 6	POE/29	119-6401 119-6403 119-6406
HCZC0250U	14	7	6a	17.4	27.6	19.7	⅝" S	¾" S	140	N: 24 Q: 16 R: 8	POE/29	119-6401 119-6403 119-6406
HCZC0275U	14	7	6a	17.4	27.6	19.7	⅝" S	¾" S	150	N: 28 Q: 17 R: 9	POE/29	119-6401 119-6403 119-6406
HCZC0300U	18	7	6a	21.4	31.5	24	⅝" S	¾" S	150	N: 40 Q: 23 R: 12	POE/29	119-6401 119-6403 119-6406
HGZC0400U	14	15	8a	21.8	39.4	27.6	⅞" S	½" S	210	N: 36 Q: 24 R: 12	POE/63	119-6402 119-6404 119-6405
HGZC0500U	18	18.5	8a	26.6	47.2	31.5	⅞" S	½" S	300	N: 52 Q: 32 R: 16	POE/63	119-6402 119-6404 119-6405
HGZC0700U	18	28	8a	26.6	47.2	31.5	1 ⅛" S	½" S	300	Q: 40 R: 17	POE/63	119-6404 119-6405
HGZC0900U	22	33	9a	34.4	34.3	59.1	1 ⅞" S	½" S	500	Q: 50 R: 26	POE/132	119-6404 119-6405
HGZC1000U	22	33	9a	34.4	34.3	59.1	1 ⅞" S	½" S	500	Q: 60 R: 30	POE/132	119-6404 119-6405
HGZC1200U	22	33	9a	34.4	34.3	59.1	1 ⅞" S	½" S	510	Q: 69 R: 33	POE/132	119-6404 119-6405
HGZC1350U	22	40	9a	34.4	34.3	59.1	1 ⅞" S	½" S	540	Q: 75 R: 38	POE/132	119-6404 119-6405

⁽¹⁾ Dimensions (in) available on page 40

⁽²⁾ Wiring diagram available on page 33
For spare parts, see pages 28

Fan	Model no	Version	Electrical code	Code no	Compressor model	Amb. temp.	Capacity range in (btu/hr) at evaporating temperature								Power consumption [W] at evap. temp. 25°F	Power consumption [W] at evap. temp. 20°F	AWEF
						°F	15	20	25	30	35	40	45	50			
Single fan	HCZC0150U	WJ	N	114N3601	MTZ18	90	9663	10850	12100	13400	14760	16170	17630	19120	1945	1869	7.64
			Q	114N3602		95	9109	10240	11430	12670	13970	15310	16690	18120			
			R	114N3603		100	8558	9636	10770	11950	13180	14450	15770	17120			
						105	8010	9034	10110	11230	12400	13600	14850	16130			
						110	7466	8436	9453	10510	11620	12760	13940	15160			
	HCZC0200U	WJ	N	114N3604	MTZ22	90	12930	14340	15820	17360	18950	20580	22260	23970	2311	2207	8.24
			Q	114N3605		95	12260	13610	15010	16480	17990	19540	21140	22760			
			R	114N3606		100	11590	12880	14210	15600	17040	18510	20030	21570			
						105	10930	12150	13420	14740	16100	17490	18920	20380			
						110	10280	11440	12640	13880	15160	16480	17830	19200			
	HCZC0250U	WJ	N	114N3607	MTZ28	90	15430	17050	18780	20610	22540	24540	26620	28760	2810	2676	8.16
			Q	114N3608		95	14650	16180	17810	19540	21350	23240	25210	27230			
			R	114N3609		100	13860	15300	16830	18450	20160	21940	23790	25700			
						105	13070	14410	15840	17360	18960	20630	22370	24170			
						110	12260	13510	14850	16260	17760	19330	20960	22640			
	HCZC0275U	WJ	N	114N3610	MTZ36	90	19170	21110	23130	25230	27390	29600	31850	34130	3606	3415	7.71
			Q	114N3611		95	18200	20030	21940	23920	25960	28040	30160	32310			
			R	114N3612		100	17220	18940	20740	22600	24510	26470	28470	30490			
						105	16220	17840	19520	21260	23060	24900	26770	28670			
						110	15210	16720	18290	19920	21600	23320	25070	26850			
	HCZC0300U	WJ	N	114N3614	MTZ40	90	22110	24310	26590	28930	31320	33740	36180	38630	4146	3918	7.71
			Q	114N3615		95	20990	23060	25200	27390	29640	31910	34200	36490			
			R	114N3616		100	19840	21780	23790	25840	27940	30070	32210	34350			
						105	18680	20490	22360	24270	26230	28210	30210	32210			
						110	17490	19180	20910	22690	24510	26350	28210	30080			
Two fan	HGZC0400U	WJ	N	114N3617	MTZ50	90	29010	32460	36070	39840	43760	47800	51950	56200	4794	4572	8.27
			Q	114N3618		95	27590	30880	34320	37910	41630	45480	49430	53470			
			R	114N3619		100	26140	29270	32540	35950	39480	43130	46880	50710			
						105	24670	27630	30730	33960	37310	40760	44310	47940			
						110	23170	25970	28900	31960	35120	38380	41730	45160			
	HGZC0500U	WJ	N	114N3621	MTZ64	90	35840	39770	43850	48080	52420	56870	61400	65990	5965	5675	8.19
			Q	114N3622		95	34010	37750	41640	45660	49800	54030	58340	62710			
			R	114N3623		100	32160	35730	39430	43240	47170	51180	55270	59410			
						105	30320	33690	37200	40820	44530	48330	52200	56120			
						110	28460	31660	34970	38390	41900	45490	49140	52830			
	HGZC0700U	WJ	Q	114N3626	MTZ80	90	45880	50630	55570	60700	65990	71430	76990	82650	7642	7280	8.01
			R	114N3627		95	43730	48250	52960	57840	62870	68030	73310	78680			
						100	41550	45840	50310	54930	59700	64600	69590	74670			
						105	39330	43390	47620	52000	56500	61130	65850	70640			
						110	37070	40910	44900	49030	53280	57640	62080	66600			
	HGZC0900U	WJ	Q	114N3628	MTZ100	90	58530	65320	72470	79950	87760	95870	104200	112900	9691	9295	8.8
			R	114N3629		95	55620	62090	68900	76030	83460	91170	99140	107300			
						100	52700	58850	65320	72100	79150	86470	94040	101800			
						105	49770	55610	61740	68160	74850	81780	88940	96310			
						110	46820	52360	58160	64230	70550	77100	83870	90820			
	HGZC1000U	WJ	Q	114N3631	MTZ125	90	72590	80820	89440	98420	107700	117400	127300	137400	12250	11720	8.75
			R	114N3632		95	68910	76760	84970	93530	102400	111600	121000	130600			
						100	65210	72680	80490	88630	97060	105800	114700	123800			
						105	61510	68590	76000	83710	91700	99950	108400	117100			
						110	57790	64490	71500	78800	86350	94150	102200	110300			
	HGZC1200U	WJ	Q	114N3633	MTZ144	90	81990	90110	98610	107500	116600	126100	135800	145800	14100	13510	8.51
			R	114N3634		95	77940	85700	93810	102300	111000	120100	129400	138900			
						100	73890	81280	89010	97060	105400	114000	122900	132000			
						105	69850	76870	84210	91860	99800	108000	116400	125000			
						110	65810	72470	79430	86680	94210	102000	110000	118200			
	HGZC1350U	WJ	Q	114N3636	MTZ160	90	91250	100200	109400	119000	129000	139200	149600	160300	15950	15210	8.19
			R	114N3637		95	86730	95220	104100	113200	122700	132400	142400	152500			
						100	82200	90280	98690	107400	116400	125600	135100	144700			
						105	77670	85340	93320	101600	110100	118900	127800	136900			
						110	73140	80400	87960	95790	103900	112100	120600	129200			

Test condition

Return gas temperature 65°F
Subcooling 5°F

Electrical code

Q: Compressor 208-230V, 3ph, 60 Hz / Fan(s) 230V, 1ph, 60 Hz
R: Compressor 460V, 3ph, 60 Hz / Fan(s) 460V, 1ph, 60 Hz

Version

WJ: Electrical box, Receiver, Dual pressure control, Fan cycling control, Filter drier, Sight glass

HP rating in hundredths of HP, i.e.: 033=1/3hp, (UCGC0100U:0100=1hp)
Power consumption referred at 90°F ambient temperature

Catalog
Optyma™ condensing unit R452A - MBP

Model no	Condenser fan	Receiver lbs @ 90%	Dimensions (in) ⁽¹⁾						Weight (lbs)	MCA (A)	Oil Type / Charge (oz)	Wiring diagram code ⁽²⁾
	Fan blade Ø (in)		Figure	Height H (in)	Width W (in)	Depth D (in)	Suction line	Liquid line	Gross			
HCZC0150U	14	7	6a	16.3	20.1	25	½" S	¾" S	130	N: 14 Q: 9 R: 6	POE/29	119-6401 119-6403 119-6406
HCZC0200U	14	7	6a	16.3	20.1	25	½" S	¾" S	130	N: 17 Q: 11 R: 6	POE/29	119-6401 119-6403 119-6406
HCZC0250U	14	7	6a	17.4	27.6	19.7	⅝" S	¾" S	140	N: 24 Q: 16 R: 8	POE/29	119-6401 119-6403 119-6406
HCZC0275U	14	7	6a	17.4	27.6	19.7	⅝" S	¾" S	150	N: 28 Q: 17 R: 9	POE/29	119-6401 119-6403 119-6406
HCZC0300U	18	7	6a	21.4	31.5	24	⅝" S	¾" S	150	N: 40 Q: 23 R: 12	POE/29	119-6401 119-6403 119-6406
HGZC0400U	14	15	8a	21.8	39.4	27.6	⅞" S	½" S	210	N: 36 Q: 24 R: 12	POE/63	119-6402 119-6404 119-6405
HGZC0500U	18	18.5	8a	26.6	47.2	31.5	⅞" S	½" S	300	N: 52 Q: 32 R: 16	POE/63	119-6402 119-6404 119-6405
HGZC0700U	18	28	8a	26.6	47.2	31.5	1 ⅛" S	½" S	300	Q: 40 R: 17	POE/63	119-6404 119-6405
HGZC0900U	22	33	9a	34.4	34.3	59.1	1 ⅞" S	½" S	500	Q: 50 R: 26	POE/132	119-6404 119-6405
HGZC1000U	22	33	9a	34.4	34.3	59.1	1 ⅞" S	½" S	500	Q: 60 R: 30	POE/132	119-6404 119-6405
HGZC1200U	22	33	9a	34.4	34.3	59.1	1 ⅞" S	½" S	510	Q: 69 R: 33	POE/132	119-6404 119-6405
HGZC1350U	22	40	9a	34.4	34.3	59.1	1 ⅞" S	½" S	540	Q: 75 R: 38	POE/132	119-6404 119-6405

⁽¹⁾ Dimensions (in) available on page 40

⁽²⁾ Wiring diagram available on page 33
For spare parts, see pages 28

Fan	Model no	Version	Electrical code	Code no	Compressor model	Amb. temp.	Capacity range in (btu/hr) at evaporating temperature										Power consumption [W] at evap. temp. -10 F	
						°F	-40	-35	-30	-25	-20	-15	-10	-5	0	5		10
Single fan	UCHC0020R	WA	B	114N2316	TF4CLX	90	350	400	450	550	600	700	800	900	1000	1100	1250	200
						95	300	350	450	500	550	650	750	850	950	1050	1200	
						100	300	350	400	450	550	600	700	800	900	1000	1100	
						110	250	300	350	400	500	550	650	700	800	900	-	
	UCHC0025R	WB	B	114N2318	NF5.5CLX	90	600	700	800	900	1050	1200	1350	1500	1650	1850	2050	300
						95	550	650	750	900	1000	1150	1250	1400	1600	1750	1950	
						100	550	600	700	850	950	1050	1200	1350	1500	1650	1850	
						110	450	550	650	750	850	950	1100	1250	1350	1550	1700	
	UCHC0033R	WB	B	114N2321	NF7CLX	90	750	850	1000	1100	1300	1450	1650	1800	2050	2250	2500	400
						95	700	800	950	1050	1200	1400	1550	1750	1950	2150	2400	
						100	650	750	850	1000	1150	1300	1450	1650	1850	2050	2250	
						110	550	650	750	900	1000	1150	1350	1500	-	-	-	
	UCHC0050R	WB	B	114N2324	SC10CL	90	-	-	1100	1300	1500	1700	1900	2150	2400	2700	2950	500
						95	-	-	1000	1200	1400	1600	1850	2050	2300	2550	2850	
	UCHC0050U	WC	N	114N2325		100	-	-	900	1100	1300	1500	1750	1950	2200	2450	2700	
						110	-	-	750	950	1150	1350	1550	1750	2000	2250	2500	
	LCHC0050R	WB	B	114N2389	SC12CLX2	90	1050	1250	1450	1700	1950	2200	2500	2800	3150	3450	3850	650
						95	950	1150	1350	1600	1850	2100	2400	2650	3000	3300	3650	
						100	850	1050	1250	1500	1700	2000	2250	2500	2800	3150	3450	
						110	700	900	1100	1300	1500	1750	2000	2300	2550	2850	3150	
	LCHC0060R	WB	B	114N2335	SC15CLX.2	90	1350	1550	1850	2100	2400	2700	3050	3400	3800	4200	4600	700
						95	1250	1450	1700	1950	2250	2550	2900	3200	3600	3950	4350	
						100	1150	1350	1600	1850	2100	2400	2700	3050	3400	3750	4100	
						110	950	1150	1400	1600	1850	2150	2400	2700	3050	3350	-	
LCHC0075R	WB	B	114N2337	NT2178GK	90	1450	1800	2150	2550	2950	3400	3900	4400	4950	5550	6200	850	
					95	1400	1750	2100	2450	2900	3350	3800	4300	4850	5450	6100		
					100	-	1650	2000	2400	2800	3250	3750	4250	4800	5350	6000		
					110	-	-	-	-	-	3100	3600	4100	4650	5200	-		
LCHC0100U	WD	N	114N2339	NJ2192GK	90	1700	2250	2800	3400	4000	4650	5350	6000	6800	7550	8400	1150	
					95	1550	2100	2650	3200	3850	4500	5150	5850	6600	7400	8250		
					100	-	1900	2500	3050	3650	4300	5000	5700	6450	7250	8100		
					110	-	-	-	-	-	4000	4700	5400	6150	7000	-		

Test condition

Return gas temperature 65°F
Subcooling 5°F

Electrical code

B: Compressor & fan(s) 115V, 1 ph, 60 Hz
N: Compressor & fan(s) 230V, 1 ph, 60 Hz

Version

WA: Power cord
WB: Power cord, Receiver
WC: Electrical box, Receiver
WD: Electrical box, Receiver, Low pressure control

HP rating in hundredths of HP, ie.: 033=1/3hp, (UCGC0100U:0100=1hp)
Power consumption referred at 90°F ambient temperature

Catalog

Optyma™ condensing unit R404A/R507 - LBP

Model no	Condenser fan	Receiver lbs @ 90%	Dimensions (in) ⁽¹⁾						Weight (lbs)	MCA (A)	Oil Type / Charge (oz)	Wiring diagram code ⁽²⁾
	Fan blade Ø (in)		Figure	Height H (in)	Width W (in)	Depth D (in)	Suction line	Liquid line	Gross			
UCHC0020R	9	-	1	10.2	12.3	14	⅜" F	¼" F	39	5.2	POE / 9.5	119-3987
UCHC0025R	9	2.16	2	10.3	13.5	17	⅜" F	¼" F	50	6.2	POE / 10.8	119-3987
UCHC0033R	9	2.16	2	10.3	13.5	17	⅜" F	¼" F	49	7.6	POE / 10.8	119-3987
UCHC0050R	10	2.16	3	11.8	13.5	17	⅜" F	¼" F	60	11.8	POE / 18.6	119-3993
UCHC0050U									58	4.3		119-3995
LCHC0050R	10	2.16	3	11.9	13.5	17.3	½" F	¼" F	58	11.8	POE / 18.6	119-3993
LCHC0060R	10	2.16	3	11.8	13.5	17	⅜" F	¼" F	58	14.2	POE / 18.6	119-3983
LCHC0060U										6.3		119-3990
LCHC0075R	10	4	4	11.9	13.3	18	½" F	¼" F	76	12.2	POE / 19.6	119-3992
LCHC0075U							⅝" F			5.5		119-3990
LHC0100U	12	4	4	13.4	17.5	19	½" F	½" F	105	8	POE / 30.1	119-3990

⁽¹⁾ Dimensions (in) available on page 40

⁽²⁾ Wiring diagram available on page 33

For spare parts, see pages 28

Fan	Model no	Version	Electrical code	Code no	Compressor model	Amb. temp.	Capacity range in (btu/hr) at evaporating temperature								Power consumption [W] at evap. temp. -10 °F	AWEF
						°F	-40	-35	-30	-25	-20	-15	-10	-5		
Single fan	LCHC0151U	WF	N Q	114N6725 114N6726	NTZ048A	90	2911	3625	4394	5214	6082	6993	7944	8929	1901	6.81 6.63
						95	2657	3342	4076	4858	5683	6547	7447	8378		
						100	2405	3060	3761	4504	5286	6104	6954	7831		
						105	-	2781	3448	4153	4893	5664	6464	7288		
						110	-	-	3138	3805	4503	5228	5979	6750		
	LCHC0201U	WF	N Q R	114N6729 114N6730 114N6731	NTZ068A	90	4571	5324	6147	7041	8004	9036	10130	11290	2679	3.61 3.5 3.51
						95	4227	4943	5724	6572	7486	8465	9505	10600		
						100	3898	4579	5320	6122	6987	7913	8898	9938		
						105	-	4230	4932	5690	6507	7381	8310	9292		
						110	-	-	4559	5275	6044	6866	7741	8665		
	LCHC0301U	WF	N Q	114N6733 114N6734	NTZ108A	90	5850	7248	8720	10240	11800	13360	14910	16420	4146	3.19
						95	5375	6708	8104	9544	11010	12470	13920	15320		
						100	4889	6158	7480	8837	10210	11580	12920	14220		
						105	-	5601	6849	8124	9406	10680	11920	13120		
						110	-	-	6213	7406	8600	9777	10920	12020		
Two fan	LGHC0401U	WF	N Q R	114N6737 114N6738 114N6739	NTZ136A	90	9106	11160	13370	15740	18250	20910	23700	26610	5644	3.29
						95	8364	10340	12470	14740	17150	19690	22350	25120		
						100	7626	9529	11570	13750	16050	18470	21000	23640		
						105	-	8723	10680	12750	14950	17250	19660	22150		
						110	-	-	9791	11770	13850	16040	18320	20670		
	LGHC0601U	WF	Q R	114N6741 114N6742	NTZ215A	90	14890	17940	21250	24820	28630	32690	36990	41500	7858	3.66 3.63
						95	13630	16570	19760	23180	26830	30700	34800	39090		
						100	12340	15170	18230	21500	24980	28670	32560	36640		
						105	-	13750	16670	19790	23110	26610	30300	34160		
						110	-	-	15100	18060	21210	24530	28020	31660		
	LGHC0751U	WF	Q R	114N6744 114N6745	NTZ271A	90	20210	24010	28100	32460	37070	41920	46960	52180	10250	3.47 3.45
						95	18820	22450	26350	30500	34880	39470	44230	49160		
						100	17400	20870	24580	28520	32660	36990	41480	46110		
						105	-	19280	22800	26520	30430	34500	38710	43050		
						110	-	-	21010	24510	28180	31990	35930	39980		

Test condition

 Return gas temperature 40°F
 Subcooling 5°F

Electrical code
N: Compressor & fan(s) 230V, 1 ph, 60 Hz
Q: Compressor 208-230V, 3ph, 60 Hz / Fan(s) 230V, 1ph, 60 Hz
R: Compressor 460V, 3ph, 60 Hz / Fan(s) 460V, 1ph, 60 Hz

Version
WF: WE + Filter drier, Sight glass, Solenoid valve with coil

 HP rating in hundredths of HP, ie.: 033=1/3hp, (UCGC0100U:0100=1hp)
 Power consumption referred at 90°F ambient temperature

Catalog

Optyma™ condensing unit R404A/R507 - LBP

Model no	Condenser fan	Receiver lbs @ 90%	Dimensions (in) ⁽¹⁾						Weight (lbs)	MCA (A)	Oil Type / Charge (oz)	Wiring diagram code ⁽²⁾
	Fan blade Ø (in)		Figure	Height H (in)	Width W (in)	Depth D (in)	Suction line	Liquid line	Gross			
LCHC0151U	14	10	6a	16.3	20.1	25	½" S	¾" S	130	N: 18 Q: 11 R: 5	POE / 29	119-6401 119-6403 119-6406
LCHC0201U	14	10	6a	16.3	20.1	25	⅝" S	¾" S	130	N: 24 Q: 19 R: 6	POE / 29	119-6401 119-6403 119-6406
LCHC0301U	14	10	7a	17.4	27.5	27	⅞" S	½" S	150	N: 32 Q: 21 R: 10	POE / 63	119-6401 119-6403 119-6406
LGHC0401U	14	17.5	8a	21.8	39.4	27.6	⅞" S	½" S	210	N: 36 Q: 78 R: 12	POE / 63	119-6402 119-6404 119-6405
LGHC0601U	18	26	9a	26.4	47.2	31.5	1 ⅞" S	½" S	300	Q: 43 R: 17	POE / 132	119-6404 119-6405
LGHC0751U	18	26	9a	26.4	47.2	31.5	1 ⅞" S	½" S	300	Q: 53 R: 22	POE / 132	119-6404 119-6405

⁽¹⁾ Dimensions (in) available on page 40

⁽²⁾ Wiring diagram available on page 33
For spare parts, see pages 28

Fan	Model no	Version	Electrical code	Code no	Compressor model	Amb. temp.	Capacity range in (btu/hr) at evaporating temperature									Power consumption [W] at evap. temp. -10 °F	Power Consumption [W] at evap. Temp. 20°F	
						°F	-30	-20	-10	0	10	20	30	40	50			
Single fan	MCNC0015R	DF600 DF602	B	114N2090 114N2117	NBC30NR	90	346	477	627	795	979	1179	1393	1622		114	152	
						95	329	453	597	757	935	1128	1337	1559				
						100	313	430	566	720	891	1078	1280					
						105	297	406	535	683	847							
	MCNC0020R	DF600 DF602	B	114N2092 114N2119	NUT55LRb	90	704	912	1139	1383	1642	1916	2202	2500		201	277	
						95	671	869	1086	1321	1572	1837	2115	2405				
						100	638	826	1034	1259	1501	1758	2028					
						105	604	783	981	1198	1431							
	MCNC0033R	WA000 WA002	B	114N2097 114N2123	DLE6.5CN	90	792	1022	1276	1563	1887	2253	2663	3120		268	361	
						95	758	981	1227	1504	1818	2173	2572	3016				
						100	724	941	1179	1447	1751	2094	2482					
						105	691	901	1132	1391	1684							
	MCNC0050R	DF600 DF602	B	114N2094 114N2121	NLY12NRb	90	1195	1606	2055	2541	3059	3607	4183	4784		417	596	
						95	1148	1540	1971	2438	2939	3470	4030	4617				
						100	1102	1474	1887	2336	2819	3334	3878					
						105	1056	1409	1802	2234	2700							
	MCNC0050R	WA000 WA002	B	114N2091 114N2118	NLY12NRb	90	1228	1666	2150	2680	3251	3863	4512	5198		412	583	
						95	1181	1599	2064	2574	3128	3721	4353	5022				
						100	1134	1532	1978	2469	3004	3579	4194					
						105	1088	1465	1891	2364	2880							
	MCNC0075R	DF600 DF602	B	114N2095 114N2122	NPT14ND	90	1497	1964	2496	3086	3728	4416	5146	5912		546	789	
						95	1435	1880	2390	2959	3581	4250	4961	5711				
						100	1373	1795	2284	2832	3434	4084	4778					
						105	1312	1711	2178	2706	3288							
	LCNC0075R	DF600	B	114N2104	NPT16LR	90	1565	1981	2444	2944	3473					637	N/A	
						95		1887	2331	2813								
						100		1793	2217	2681								
						105												
	MCNC0075R	WA000 WA002	B	114N2098 114N2124	NPT14 ND	90	1497	1964	2496	3086	3728	4416	5146	5912		546	789	
						95	1435	1880	2390	2959	3581	4250	4961	5711				
						100	1373	1795	2284	2832	3434	4084	4778					
						105	1312	1711	2178	2706	3288							
	MCNC0075R	WA000 WA002	N	114N2099 114N2125	SCE15MNX	90					4142	4859	5596	6355	7140	N/A	718	
						95					3978	4660	5359	6079	6825			
						100					3799	4444	5104	5786				
						105					3600	4208	4831					
MCNC0100R	WA000 WA002	B	114N2100 114N2126	SCE18MNX	90					5039	5942	6874	7828	8796	N/A	850		
					95					4849	5715	6607	7518	8442				
					100					4654	5488	6343	7214					
					105					4456	5261	6083						
MCNC0100R	WA000 WA002	N	114N2101 114N2127	NPT16NF	90	1775	2352	2993	3693	4446	5247	6093	6980		652	938		
					95	1700	2247	2860	3532	4260	5036	5859	6724					
					100	1624	2141	2726	3372	4073	4826	5626						
					105	1549	2036	2592	3211	3887								

Test condition

Return gas temperature 65°F
Subcooling 5°F

Electrical code

B: Compressor & fan(s) 115V, 1 ph, 60 Hz
N: Compressor & fan(s) 230V, 1 ph, 60 Hz

Version

DF000: Multi pack plastic baseplate
DF002: Single pack plastic baseplate
WA000: Multi pack metal baseplate
WA002: Single pack metal baseplate

HP rating in hundredths of HP, ie.: 033=1/3hp, (UCGC0100U:0100=1hp)
Power consumption referred at 90°F ambient temperature

Catalog

Optyma™ condensing unit R290 – L/MBP

Model no	Condenser fan	Receiver lbs @ 90%	Dimensions (in) ⁽¹⁾						Weight (lbs)	MCA (A)	Oil Type / Charge (oz)	Wiring diagram code ⁽²⁾
	Fan blade Ø (in)		Figure	Height H (in)	Width W (in)	Depth D (in)	Suction line	Liquid line	Gross			
MCNC0015R	4.75	-	12a	8.50	8.27	17.20	1/4" S	2.8 mm S	30.78	2.19	POE / 4.2	119-9261
MCNC0020R	4.75	-	12a	8.50	8.27	17.20	1/4" S	2.8 mm S	38.34	3.07	POE / 7	119-9262
MCNC0033R	8	-	13a	8.98	11.26	13.78	1/4" S	1/4" S	35.75	5.65	POE / 7.8	119-3993
MCNC0050R	10	-	14a	12.44	13.11	17.01	5/16" S	2.8 mm S	49.25	7.39	POE / 13.9	119-9262
MCNC0050R	10	-	14a	11.89	13.23	17.01	5/16" S	2.8 mm S	48.46	7.39	POE / 13.9	119-9262
MCNC0075R	10	-	14a	12.44	12.99	17.01	5/16" S	1/4" S	58.01	7.7	POE / 14.1	119-9262
LCNC0075R	8	-	15a	9.84	10.55	20.08	5/16" S	1/4" S	59.62	7.27	POE / 14.1	119-9262
MCNC0075R	10	-	14a	11.89	13.23	17.01	5/16" S	1/4" S	60.21	7.7	POE / 14.1	119-9262
MCNC0075R	10	-	14a	11.89	13.23	17.01	3/8" S	1/4" S	64.5	5.21	POE / 19.4	119-3990
MCNC0100R	12	-	16a	13.94	15.98	19.02	3/8" S	1/4" S	64.5	11.93	POE / 19.4	119-3992
MCNC0100R	12	-	16a	13.94	15.98	19.02	5/16" S	1/4" S	59.91	4.39	POE / 15.8	119-9263

⁽¹⁾ Dimensions (in) available on page 40

⁽²⁾ Wiring diagram available on page 33
For spare parts, see pages 28

Fan	Model No	Version	Electrical Code	Code No	Compressor Model	Ambient Temperature	Capacity range in (btu/hr) at evaporating temperature								Power Consumption [W] at evap. Temp. -10°F	Power Consumption [W] at evap. Temp. 20°F		
						°F	-40	-30	-20	-10	0	10	20	30			40	
Two fan	LGNM0100R	WA000	N	114N2201	NST26NG	80		2320	3404	4629	5985	7463	9055	10750		857	1281	
						90		1979	2993	4148	5433	6842	8364	9992				
						95			2788	3907	5158	6532	8019	9611				
						100			2583	3667	4883	6222	7674	9231				
						105			2378	3427	4609	5912	7330	8851				
	LGNM0120R	WA000	N	114N2203	NST30NG	80		3067	4200	5489	6923	8493	10190	12010		1065	1502	
						90		2768	3809	5008	6354	7837	9450	11180				
						95			3615	4768	6070	7510	9079	10770				
						100			3420	4529	5786	7183	8709	10360				
	LGNM0140R	WA000	N	114N2205	NST34NG	105			3225	4289	5503	6856	8339	9944		1335	1904	
						80	2528	3815	5214	6715	8308	9984	11740	13560				
						90	2346	3505	4780	6161	7638	9202	10840	12560				
						95		3350	4563	5885	7304	8811	10400	12060				
						100		3195	4347	5609	6970	8421	9954	11560				
	LGNM0150R	WA000	N	114N2207	NST38NG	105			3041	4131	5333	6636	8032	9510	11060		1349	2016
						80	2754	4095	5609	7278	9084	11010	13050	15180				
						90	2547	3729	5091	6613	8277	10070	11970	13970				
						95	2443	3547	4832	6281	7874	9596	11430	13370				
						100	2339	3365	4574	5949	7471	9124	10890	12760				

Test condition

Return gas temperature 40°F
Subcooling 5°F

Electrical code
N: Compressor & fan(s) 230V, 1 ph, 60 Hz

These models are in Single Pack

HP rating in hundredths of HP, ie.: 033=1/3hp, (UCGC0100U:0100=1hp)

Power consumption referred at 90°F ambient temperature

Model No	Condenser Fan	Receiver lbs @90%	Dimensions (in)						Weight (lbs)	MCA (A)	Oil Type / Charge (oz)	Wiring Diagram code
	Fan Blade (in)		Figure	Height H (in)	Width W (in)	Depth D (in)	Suction line	Liquid Line	Gross			
LGNM0100R	10	-	Figure 18a	11.9	28.1	13.8	1/2" IDS	3/8" IDS	85.0	7.60	POE / 23.7	119-9599
LGNM0120R	10	-	Figure 18a	11.9	28.1	13.8	1/2" IDS	3/8" IDS	86.0	9.04	POE / 23.7	119-9599
LGNM0140R	10	-	Figure 18a	11.9	28.1	13.8	1/2" IDS	3/8" IDS	88.5	11.76	POE / 23.7	119-9599
LGNM0150R	10	-	Figure 18a	11.9	28.1	13.8	1/2" IDS	3/8" IDS	88.5	12.80	POE / 23.7	119-9599

⁽¹⁾ Dimensions (in) available on page 40

⁽²⁾ Wiring diagram available on page 33

For spare parts, see pages 28

Optyma™ condensing unit - MBP

Unit	N	Q	R	Compressor					Contactor	Service valve		
				4	Code number	Start capacitor	Run Capacitor	Start Relay		Suction	Discharge	Receiver valve
HCZC0150	114N3601	114N3602	114N3603	MTZ18-1 MTZ18-3 MTZ18-4	N: MTZ18-1VI Q: MTZ18-3VI R: MTZ18-4VI	N: 119-5637	N: 119-5617	N: 119-5616	N: 119-8784 Q,R: 119-5640	119-4545	119-4545	119-8785
HCZC0200	114N3604	114N3605	114N3606	MTZ22-1 MTZ22-3 MTZ22-4	MTZ22-1VI MTZ22-3VI MTZ22-4VI	N: 119-5637	N: 119-5618	N: 119-5616	N: 119-8784 Q,R: 119-5640	N: 119-4546 Q, R: 119-4545	119-4545	119-8785
HCZC0250	114N3607	114N3608	114N3609	MTZ28-1 MTZ28-3 MTZ28-4	MTZ28-1VI MTZ28-3VI MTZ28-4VI	N: 119-5636	N: 119-5619	N: 119-5616	N: 119-8784 Q,R: 119-5640	N: 119-4546 Q, R: 119-4545	119-4545	119-8785
HCZC0275	114N3610	114N3611	114N3612	MTZ36-1 MTZ36-3 MTZ36-4	MTZ36-1VI MTZ36-3VI MTZ36-4VI	N: 119-5637	N: 119-5618	N: 119-5616	N: 119-8784 Q,R: 119-5640	119-4546	119-4545	119-8785
HCZC0300	114N3614	114N3615	114N3616	MTZ40-1 MTZ40-3 MTZ40-4	MTZ40-1VI MTZ40-3VI MTZ40-4VI	N: 119-5637	N: 119-5620	N: 119-5616	N: 119-8784 Q,R: 119-5640	119-4546	119-4545	119-8785
HGZC0400	114N3617	114N3618	114N3619	MTZ50-1 MTZ50-3 MTZ50-4	MTZ50-1VI MTZ50-3VI MTZ50-4VI	N: 119-5636	N: 119-5618	N: 119-5616	N: 119-4652 Q: 119-5639 R: 119-5640	119-4549	119-4546	119-4545
HGZC0500	114N3621	114N3622	114N3623	MTZ64-1 MTZ64-3 MTZ64-4	MTZ64-1VI MTZ64-3VI MTZ64-4VI	N: 119-5635	N: 119-5620	N: 119-5616	N: 119-4652 Q: 119-5639 R: 119-5640	119-4549	119-4547	119-4545
HGZC0700		114N3626	114N3627	MTZ80-3 MTZ80-4	MTZ80-3VI MTZ80-4VI	---	---	---	Q: 119-4652 R: 119-5640	119-4549	119-4547	119-4545
HGZC0900		114N3628	114N3629	MTZ100-3 MTZ100-4	MTZ100-3VI MTZ100-4VI	---	---	---	Q: 119-4652 R: 119-5639	119-4550	119-4548	119-4545
HGZC1000		114N3631	114N3632	MTZ125-3 MTZ125-4	MTZ125-3VI MTZ125-4VI	---	---	---	Q: 119-4652 R: 119-5639	119-4550	119-4548	119-4545
HGZC1200		114N3633	114N3634	MTZ144-3 MTZ144-4	MTZ144-3VI MTZ144-4VI	---	---	---	Q: 119-4652 R: 119-5639	119-4550	119-4548	119-4545
HGZC1350		114N3636	114N3637	MTZ160-3 MTZ160-4	MTZ160-3VI MTZ160-4VI	---	---	---	Q: 119-4652 R: 119-5639	119-4550	119-4548	119-4545

Unit	Oil	Condenser kit	Low pressure switch	Fan kit	Fan cycling	Filter drier	Receiver	Sight glass	Transformer
HCZC0150	120Z0638	119-8720	060-5253	N,Q: 119-9561 R: 119-8718	060-5241	023Z5058	119-8733	014L0182	R: 119-8687
HCZC0200	120Z0638	119-8720	060-5253	N,Q: 119-9561 R: 119-8718	060-5241	023Z5058	119-8733	014L0182	R: 119-8687
HCZC0250	120Z0638	119-8726	060-5253	N,Q: 119-9561 R: 119-8718	060-5241	023Z5064	119-8733	014L0182	R: 119-8687
HCZC0275	120Z0638	119-8726	060-5253	N,Q: 119-9561 R: 119-8718	060-5241	023Z5064	119-8733	014L0182	R: 119-8687
HCZC0300	120Z0638	119-8727	060-5253	N,Q: 119-8254E R: 119-9660	060-5241	023Z5064	119-8733	014L0182	R: 119-8687
HGZC0400	120Z0638	119-8721	060-5253	N,Q: 119-9561 R: 119-8718	060-5241	023Z5067	119-8731	014L0203	R: 119-8687
HGZC0500	120Z0638	119-8722	060-5253	N,Q: 119-8254E R: 119-9660	060-5241	023Z5067	119-8732	014L0203	R: 119-8687
HGZC0700	120Z0638	119-8724	060-5253	Q: 119-8254E R: 119-9660	060-5241	023Z5067	119-8728	014L0203	R: 119-8687
HGZC0900	120Z0638	119-8725	060-5253	Q: 119-9650 R: 119-9651	060-5241	023Z5067	119-8729	014L0203	R: 119-8687
HGZC1000	120Z0638	119-8725	060-5253	Q: 119-9650 R: 119-9651	060-5241	023Z5067	119-8729	014L0203	R: 119-8687
HGZC1200	120Z0638	119-8725	060-5253	Q: 119-9650 R: 119-9651	060-5241	023Z5067	119-8729	014L0203	R: 119-8687
HGZC1350	120Z0638	119-8725	060-5253	Q: 119-9650 R: 119-9651	060-5241	023Z5067	119-8730	014L0203	R: 119-8687

Optyma™ condensing unit R404A/R507 - LBP

Unit	N	Q	R	Compressor					Contactor	Service valve		
				Model no	Code number	Start capacitor	Run Capacitor	Start Relay		Suction	Discharge	Receiver valve
LCHC0151	114N6725	114N6726		N: NTZ048A1 Q: NTZ048A3	N: 120F0293 Q: 120F0279	N: 119-5637	N: 119-5618	N: 119-5616	N: 119-8784 Q: 119-5640	119-4546	119-4545	119-8785
LCHC0201	114N6729	114N6730	114N6731	N: NTZ068A1 Q: NTZ068A3 R: NTZ068A4	N: 120F0294 Q: 120F0280 R: 120F0230	N: 119-5636	N: 119-5619	N: 119-5616	N: 119-8784 Q,R: 119-5640	119-4546	119-4545	119-8785
LCHC0301	114N6733	114N6734		N: NTZ108A1 Q: NTZ108A3	N: 120F0296 Q: 120F0282	N: 119-5636	N: 119-5618	N: 119-5616	N: 119-8784 Q: 119-5640	119-4549	119-4546	119-8785
LGHC0401	114N6737	114N6738	114N6739	N: NTZ136A1 Q: NTZ136A3 R: NTZ136A4	N: 120F0297 Q: 120F0283 R: 120F0236	N: 119-5636	N: 119-5618	N: 119-5616	N: 119-4652 Q: 119-5639 R: 119-5640	119-4549	119-4546	119-4545
LGHC0601		114N6741	114N6742	Q: NTZ215A1 R: NTZ215A3	N: 120F0284 Q: 120F0240	---	---	---	Q: 119-4652 R: 119-5639	119-4550	119-4547	119-4545
LGHC0751		114N6744	114N6745	Q: NTZ271A1 R: NTZ271A3	N: 120F0285 Q: 120F0242	---	---	---	Q: 119-4652 R: 119-5639	119-4550	119-4547	119-4545

Unit	Oil	Condenser kit	pressure switch	Fan kit	Fan cycling	Filter drier	Receiver	Sight glass	Transformer
LCHC0151	120Z0638	119-8720	060-5249	N,Q: 119-9561	060-5241	023Z5058	119-8733	014L0182	---
LCHC0201	120Z0638	119-8720	060-5249	N,Q: 119-9561 R: 119-8718	060-5241	023Z5058	119-8733	014L0182	R: 119-8687
LCHC0301	120Z0638	119-8726	060-5249	N,Q: 119-9561	060-5241	023Z5064	119-8733	014L0182	---
LGHC0401	120Z0638	119-8721	060-5249	N,Q: 119-9561 R: 119-8718	060-5241	023Z5067	119-8731	014L0203	R: 119-8687
LGHC0601	120Z0638	119-8723	060-5249	Q: 119-8254E R: 119-9660	060-5241	023Z5067	119-8728	014L0203	R: 119-8687
LGHC0751	120Z0638	119-8723	060-5249	Q: 119-8254E R: 119-9660	060-5241	023Z5067	119-8728	014L0203	R: 119-8687

Optyma™ condensing unit R448A / R449A – H/MBP

Code no	Compressor			Fan Motor	Fan Blade	Condenser	Low Pressure Switch	Fan Cycling	Start Capacitor	Run Capacitor	Relay	LP Hose	HP Hose FC Hose	Motor Protector
	Model No	Model	Code No											
114N2088 114N2107	HCYC0075RC0001N HCYC0075RC0002N	MPT14RF	123B2543	119-5665	119-5672	119-9260	N/A	N/A	123B9302	123B9231	123B9196	N/A	N/A	123B9585
114N2089 114N2108	HCYC0100RC0001N HCYC0100RC0002N	MX18TGa	123B2541	119-5665	119-5672	119-9260	N/A	N/A	123B9321	123B9231	123B9159	N/A	N/A	123B9586
114N2102 114N2109	HCYC0075RC0001B HCYC0075RC0002B	MPT14RD	123B2544	119-5663	119-5672	119-9260	N/A	N/A	123B9756* 123B9756*	123B9756*	N/A	N/A	N/A	123B9577

NOTE: 123B9756 it is a connecting box include run and start capacitor

Optyma™ condensing unit R290 – L/MBP

Code no	Compressor			Fan Motor	Fan Blade	Condenser	Low Pressure Switch	Fan Cycling	Start Capacitor	Run Capacitor	Relay	LP Hose	HP Hose FC Hose	Motor Protector
	Model No	Model	Code No											
114N2090	MCNC0015RDF600B	NBC30NR	123B8311	119-9246	N/A	119-9240	N/A	N/A	123B9323	N/A	123B9182	N/A	N/A	123B9567
114N2117	MCNC0015RDF602B													
114N2092	MCNC0020RDF600B	NUT55LRb	125B3165	119-9246	N/A	119-9240	N/A	N/A	123B9328	123B9216	123B9189	N/A	N/A	123B9579
114N2119	MCNC0020RDF602B													
114N2097	MCNC0033RWA000B	DLE6.5CN	119-9349	119-9344	119-9252	119-9242	N/A	N/A	119-7769	N/A	119-9357	N/A	N/A	N/A
114N2123	MCNC0033RWA002B													
114N2094	MCNC0050RDF600B	NLY12NRb	123B3304	119-9247	119-5672	119-8703	N/A	N/A	123B9314	123B9216	123B9187	N/A	N/A	123B9527
114N2121	MCNC0050RDF602B													
114N2091	MCNC0050RWA000B	NLY12NRb	123B3304	119-9247	119-5672	119-8703	N/A	N/A	123B9314	123B9216	123B9187	N/A	N/A	123B9527
114N2118	MCNC0050RWA002B													
114N2095	MCNC0075RDF600B	NPT14ND	123B3328	119-9247	119-5672	119-8703	N/A	N/A	123B9328	123B9227	123B9143	N/A	N/A	123B9496
114N2122	MCNC0075RDF602B													
114N2098	MCNC0075RWA000B	NPT14ND	123B3328	119-9247	119-5672	119-8703	N/A	N/A	123B9328	123B9227	123B9143	N/A	N/A	123B9496
114N2124	MCNC0075RWA002B													
114N2099	MCNC0075RWA000N	SCE15MNX	119-9347	119-9247	119-5672	119-8703	N/A	N/A	119-9348	N/A	119-9348	N/A	N/A	N/A
114N2125	MCNC0075RWA002N													
114N2100	MCNC0100RWA000B	SCE18MNX	119-9345	119-9247	119-9363	119-5642	N/A	N/A	119-9346	N/A	119-9346	N/A	N/A	N/A
114N2126	MCNC0100RWA002B													
114N2101	MCNC0100RWA000N	NPT16NF	123B3326	119-9247	119-9363	119-5642	N/A	N/A	123B9302	123B9222	123B9160	N/A	N/A	123B9582
114N2127	MCNC0100RWA002N													
114N2104	LCNC0075RDF600B	NPT16LR	123B3165	119-9248	119-5670	119-5626	N/A	N/A	123B9329	123B9221	123B9143	N/A	N/A	123B9494

NOTE: 119-9348 and 119-9346 included all electrical kit service

Code no	Compressor			Assy Fan Motor	Fan Blade	Condenser	Low Pressure Switch	Fan Cycling	Start Capacitor	Run Capacitor	Relay	LP Hose	HP Hose FC Hose	Motor Protector	Electrical kit service
	Model No	Model	Code No												
114N2201	LGNM0100RWA000N	NST26NG	123B3333	119-9597	N/A	119-9598	N/A	N/A	123B9304	123B9205	123B9147	N/A	N/A	123B9550	123B9724
114N2203	LGNM0120RWA000N	NST30NG	123B3325	119-9597	N/A	119-9598	N/A	N/A	123B9327	123B9208	123B9146	N/A	N/A	123B9529	123B9758
114N2205	LGNM0140RWA000N	NST34NG	123B3334	119-9597	N/A	119-9598	N/A	N/A	123B9304	123B9238	123B9156	N/A	N/A	123B9594	123B9731
114N2207	LGNM0150RWA000N	NST38NG	123B3335	119-9597	N/A	119-9598	N/A	N/A	123B9304	123B9208	123B9146	N/A	N/A	123B9594	123B9759

NOTE:

Assy Fan Motor include: motor, guard and blade.

Condenser include: condenser MCHE and Fan Shroud.

Electrical kit service include: relay, start and run capacitors


Catalog
Spare parts & accessories list

Spare Part Number	Raw material	Spare Part Description
119-8786	101Z0203	Service Kit BD50F 12/24VDC - R134a
119-8787	104L2853	Service Kit SC15CL 220V
119-8788	105G5954	Service Kit NF11FX2 115V
119-8789	191U196000	Service Kit NT6217Z 115V R134a
119-8027	191U197900	Service Kit NT6215Z 115V R134a
119-8028	191U196300	Service Kit NJ6220Z 115V R134a
119-8029	191U196400	Service Kit NJ6220Z 208-230V R134a
119-8030	191U197400	Service Kit NJ6226Z 208-230V R134a
119-8031	191U196700	Service Kit NT2178GK 115V R404A
119-8032	191U196800	Service Kit NT2178GK 208-230V R404A
119-8033	191U197300	NJ2192GK 208-230V/60Hz/1PH R404A
119-8034	191U197000	NT6220GK 208-230V/60Hz/1PH R404A
119-8035	191U197200	NT6222GKV 208-230V/60Hz/1PH R404A
195B0059	104G8820	SC18G Universal R134A 220-240V 50/60Hz
195B0061	104L1603	SC12CL LBP R404A/R507 115V 60Hz
195B0099	104G7550	SC15G Universal R134A 115V 60Hz
195B0147	104L1503	KIT SC10CLX 115V R404A/R507 60HZ LBP/MBP
195B0237	104L1853	SERVICE-Kit SC15CLX.2 115V 60HZ R404A
195B0276	104G7800	Kit SC18G 115V 60HZ R134A
195B0306	104L2105	SERVICE-Kit SC18MLX 115V 60Hz R404A
195B0348	105F1612	SERVICE-Kit NF 5.5 CLX 115 V
195B0491	104L1696	SERVICE-Kit SC12CLX2 115V/60Hz
195B0510	104L1606	SERVICE-Kit SC12MLX 115V 60Hz R404A
195B0671	104L2536	SERVICE-Kit SC10CLX 208-230
195B0304	105F1727	NF7CLX 115V steel connectors
195B0388	105G5958	SERVICE-Kit NF 11 FX
195B0411	105G6665	NL6.1 MF 50/60Hz steel connectors
195B0468	102U2122	KIT TF4CLX COMPRESSOR 115V/60Hz
195B0560	105G5639	SERVICE-Kit NF6.1FX2 115V - P-T#6.5/S#
195B0586	105G5737	SERVICE-Kit NF 7.3 FX2 115 V
195B0672	105F1728	NF7CLX 115V steel connectors
119-5622	119-3158A	SP - CONDENSER AC 026T/3R/3/8"S 07FPI
119-5626	119-3169	SP - CONDENSER AC 024T/3R/5/16"R 07FPI
119-5629	119-3170	SP - CONDENSER AC 026T/3R/5/16"R 07FPI
119-5642	119-3175	SP - CONDENSER AC 052T/4R/5/16"R 09FPI
119-5643	119-3176	SP - CONDENSER AC 016T/2R/5/16"R 07FPI
119-5644	119-3177	SP - CONDENSER AC 032T/3R/5/16"R 07FPI
119-5645	119-3181	SP - CONDENSER AC 048T/4R/3/8"C 10FPI
119-5647	119-3182A	SP - CONDENSER AC 060T/4R/3/8"S 10FPI
119-5648	119-8127	SP - Condenser AC 20T/2R/ 5/16"OD 12FPI
119-8702	119-3171	SP - CONDENSER AC 036T/4R/5/16"R 07FPI
119-8703	119-3172	SP - CONDENSER AC 044T/4R/5/16"R 07FPI
119-5669	119-3303	SP - FAN BLADE AL 9"x22°x5 - CCW
119-5670	119-3306	SP - FAN BLADE AL 8"x30°x5 - CCW
119-5671	119-3309	SP - FAN BLADE AL 8"x22°x5 - CCW
119-5672	119-3311	SP - FAN BLADE AL 10"x34°x5 - CCW
119-5674	191U139700	SP - FAN BLADE AL 12"x24°x5 - CCW
119-5679	119-3624	SP - FAN GUARD 9" SQR BLK
119-5680	119-3625	SP - FAN GUARD 8" SQR BLK
119-5682	119-3637	SP - FAN GUARD 10" SQR BLK
119-5683	119-3639	SP - FAN GUARD 12" RND BLK
119-5684	191U138110	SP - FAN GUARD 12" RND BLK
119-5659	7605518	SP - FAN MOTOR 1/15HP 208-230V/50-60Hz
119-5660	7605521	SP - FAN MOTOR 1/15HP 115V/50-60Hz
119-5661	119-3250	SP - FAN MOTOR 5W 115V/60Hz
119-5662	119-3256	SP - FAN MOTOR 9W 115V/60Hz
119-5663	119-3257	SP - FAN MOTOR 16W 115V/60Hz
119-5664	119-3258	SP - FAN MOTOR 9W 230V/60Hz
119-5665	119-3260	SP - FAN MOTOR 16W 230V/60Hz
119-5649	119-8128	SP - Fan Motor 24VDC 5214NH 127x38mm

Catalog
Spare parts & accessories list


Spare Part Number	Raw material	Spare Part Description
023Z5013	023Z5013	Filter drier DCL 032S M/32
023Z8128	023Z8128	Filter drier DCL 032SX2/3mm I/28
023Z8129	023Z8129	Filter drier DML 032SX2/2S I/28
023Z8252	023Z8252	Filter drier DCL 1.525XL/2.8mm I/36
119-8544	119-8308	SP - Capillary Hose .6 mts Red
119-8543	119-8200	SP - Capillary Hose .6 mts Blue
032F5043	032F5043	EVU2 Valve ODF-ODF 1/4-1/4in I-pack 40
042N4233	042N4233	Coil AY120C 110-120V 50/60Hz Ext. Frame
068-2010	068-2010	Orifice No 01 for T/TE 2
068Z3400	068Z3400	T 2 Therm. exp. valve Flare/Flare
119-5650	101N0213	SP - Electronic Module 2G - BD35/50F
119-5651	119-5400	SP - Crankcase Heater 120V (belly band)
060-117191	060-117191	KP5 Pressure Switch M/36
060-5231	060-5231	KPU1 Pressure Switch M/14
060-5249	060-5249	KPU15B Pressure Switch M/14
061F6050	061F6050	ACB Cartridge Switch 2UB215W I/100
061F7506	061F7506	ACB Cartridge Switch 2UB506W I/20
061F7520	061F7520	ACB Cartridge Switch 2UA520W I/20
061F8490	061F8490	ACB Cartridge Switch 2UA392W I/20
119-5652	119-3322	SP - Liquid Receiver 0.028 ft ³ (UL)
119-5654	119-3323	SP - Liquid Receiver 0.038 ft ³ (UL)
119-5655	119-3324	SP - Liquid Receiver 0.056 ft ³ (UL)
119-5657	119-3643	SP - Receiver 0.4 L UL BK 2.5"ODx5"
119-5658	119-3670	SP - Receiver UL BK 2.5" OD x 5"
119-5666	119-3671A	SP - Receiver UL BK 3"ODx9"
119-7757	117-7441	SP - STARTING RELAY SC 115V/60Hz
119-7758	117U4061	SP - STARTING RELAY NL/FF 115V/60Hz
119-7759	117U4123	SP - STARTING RELAY NF 115V/60Hz
119-7760	117U4127	SP - STARTING RELAY NF 115V/60Hz
119-7761	117U4129	SP - STARTING RELAY NF 115V/60Hz
119-7762	117U4148	SP - STARTING RELAY TF 115V/60Hz
119-7764	117U6005	SP - STARTING RELAY SC 220V/50Hz
119-7766	117U6020	SP - STARTING RELAY SC 115V/60Hz
119-5667	117U4151	SP - STARTING RELAY NF 115V/60Hz
119-5675	117U6015	SP - Starting Relay FR
119-5676	117U6019	SP - Starting Relay SC 50/60 Hz
119-5677	119-8131	SP - Solid State Relay 3.5-32VDC 3A
119-7772	117-7114	SP - RUN CAPACITOR 23.5 MFD 190 VAC
014L0181	014L0181	SGP 6s N Sight Glass M/25x4
119-7767	117U5019	SP - ST. CAPACITOR 80 MFD 330 VAC
119-7768	117U5022	SP - ST. CAPACITOR 320 MFD 125 VAC
119-7769	117U5023	SP - ST. CAPACITOR 240 MFD 125 VAC
119-7770	117U5025	SP - ST. CAPACITOR 280 MFD 125 VAC
119-7771	117U5028	SP - ST. CAPACITOR 410 MFD 125 VAC
119-5678	117U5015	SP - START CAPACITOR 80 mfd
119-5685	119-3609A	SP - VALVE BM 1/4"xF 1/4"x5/16"
119-5686	119-3610A	SP - VALVE BM F 1/4"xF 3/8"x5/16"
119-5687	119-3978B	SP - VALVE BM F 1/2"xF 1/4"x3/8"
119-8790	119-7079	SP - FAN MOTOR 9W 115V/60Hz

Wiring Diagram 119-3375




* Heater not shown
Use 14AWG black wire for connections **Ver 2**

Wiring Diagram 119-3983




* Heater not shown
Ver 6

Wiring Diagram 119-3985




* Heater not shown
Ver 6

Wiring Diagram 119-3987




*Power cord optional

Wiring Diagram 119-3988




Ver 5

Wiring Diagram 119-3989




Ver 7

Wiring Diagram 119-3990



Ver 7

Wiring Diagram 119-3992



Ver 7

Ver 5


Ver 5

35

Wiring Diagram 119-6403

230V/THREE PHASE/60Hz - 230V/3Ph/60Hz


230V 3PH 60Hz
FIELD WIRING



Wiring Diagram 119-6404

230V/THREE PHASE/60Hz - 230V/3Ph/60Hz


230V 3PH 60Hz
FIELD WIRING



Wiring Diagram 119-6405

460V/THREE PHASE/60Hz - 460V/3Ph/60Hz


460V 3PH 60Hz
FIELD WIRING




Wiring Diagram 119-6406

460V/THREE PHASE/60Hz - 460V/3 Phase/ 60Hz

460V/3Phases/60Hz - 460V/3 Ph/60Hz
FIELD WIRING




Wiring Diagram 119-9231




REV. AA

Wiring Diagram 119-9233




REV. AB

Wiring Diagram 119-9261




REV. AB

Wiring Diagram 119-9262



REV. AB


Wiring Diagram 119-9263



REV. AB

Wiring Diagram 119-3990


Wiring Diagram for SC/NJ compressor 220V



-Power cord optional
-Run Capacitor optional

Wiring Diagram 119-3992

Wiring Diagram for SC/NT/NJ compressor 115V




-Power cord optional
-Run Capacitor optional
-HP/LP cartridges could replace KP15B

S: Start
C: Common
R: Run
MP: Motor Protector

Wiring Diagram 119-3993

Wiring diagram for TL/SC compressors 115V



*Power cord optional




Figure 1




Figure 2




Figure 3




Figure 4




Figure 5




Figure 6a




Figure 7a




Figure 8a




Figure 9a




Figure 10a




Figure 11a




Figure 12a




Figure 13a




Figure 14a




Figure 15a




Figure 16a




Figure 17a







Figure 18a





Easy to clean, durable microchannel coil

Fan	Model no	Version	Electrical code	Code no	Compressor model	Amb. Temp.	Capacity range in (btu/hr) at evaporating temperature							Power consumption [W] at evap. Temp. 25 °F	Power consumption [W] at evap. Temp. 20 °F	AWEF*
						°F	10	15	20	25	30	35	40			
Single fan	HJJM0150	WG	N	114N6100	MTZ18	90	7668	8819	10040	11330	12680	14100	15590	1705	1629	8.19
			Q	114N6101		95	7224	8330	9503	10740	12040	13410	14830			
		WK	N	114N6150		100	6791	7852	8978	10170	11420	12720	14090			
			Q	114N6151		110	-	6929	7960	9049	10190	11390	12640			
						115	-	6484	7469	8508	9599	10740	11930			
	HNJM0200	WG	N	114N6102	MLZ15	90	12910	14400	15990	17690	19490	21400	23430	2408	2357	8.44 8.77
			Q	114N6103		95	12460	13900	15430	17070	18810	20650	22610			
		WK	N	114N6152		100	12010	13390	14870	16450	18120	19900	21780			
			Q	114N6153		110	-	12370	13730	15190	16730	18370	20110			
						115	-	11850	13160	14550	16030	17600	19270			
	HNJM0250	WG	N	114N6104	MLZ19	90	16790	18660	20650	22770	25020	27390	29900	3013	2944	8.79 9.19
			Q	114N6105		95	16240	18040	19960	22000	24170	26460	28870			
		WK	N	114N6154		100	15690	17420	19260	21230	23310	25510	27830			
			Q	114N6155		110	-	16140	17840	19640	21560	23580	25730			
						115	-	15480	17110	18840	20670	22610	24660			
	HNJM0300	WG	N	114N6106	MLZ21	90	17760	19770	21910	24180	26580	29120	31800	3174	3097	8.92 9.24
			Q	114N6107		95	17130	19070	21130	23320	25630	28080	30660			
		WK	N	114N6156		100	16490	18360	20340	22440	24670	27030	29510			
			Q	114N6157		110	-	16900	18730	20660	22710	24880	27170			
						115	-	16160	17900	19750	21710	23790	25980			
	HNJM0350	WG	N	114N6108	MLZ26	90	22170	24600	27190	29960	32890	35990	39270	3826	3730	9.22 9.87
			Q	114N6109		95	21400	23740	26230	28890	31700	34690	37840			
		WK	N	114N6158		100	20620	22860	25250	27800	30500	33360	36390			
			Q	114N6159		110	-	21060	23240	25560	28030	30650	33420			
						115	-	20140	22210	24420	26770	29260	31900			
	HNJM0400	WG	N	114N6110	MLZ30	90	26300	29140	32180	35420	38860	42510	46370	4455	4336	9.4 9.8
			Q	114N6111		95	25260	28000	30920	34040	37360	40890	44610			
		WK	N	114N6160		100	24200	26830	29640	32640	35830	39220	42810			
			Q	114N6161		110	-	24410	26980	29730	32670	35800	39110			
						115	-	23180	25620	28240	31040	34030	37210			

Test condition

Return gas temperature 65°F
Subcooling 5°F
(MBP)

Electrical code

N: Compressor & fan(s) 230V, 1 ph, 60 Hz
Q: Compressor 208-230V, 3ph, 60 Hz

Fan(s) 230V, 1ph, 60 Hz

Version

WG: Electrical box, Receiver, Dual pressure control, Fan speed controller or Fan cycling, Defrost Timer, Outdoor enclosure

WK: WG + Low Ambient Kit

HP rating in hundredths of HP, ie.: 033=1/3hp, (UCGC0100U:0100=1hp)

Power consumption referred at 90°F ambient temperature

*This refrigeration system is designed and certified for use in walk-in cooler applications

R448A and R449A performance data are nearly identical

Performance data is based on fan full speed

All Optyma Slim Condensing units are UL Listed

Model no	Condenser coil			Con- denser fan	Receiver volume [Lbs]	Dimensions (in) ⁽¹⁾						Weight (lbs)		MCA (A)	Wiring diagram code ⁽²⁾
	Type	Air flow [CFM]	Int. volume [lbs]	Fan blade Ø (in)		Figure	Height H (in)	Width W (in)	Depth D (in)	Suction line	Liquid line	Gross	Net		
HJMJ0150	D8	1410	0.9	14	6.5	1	19.5	43.5	13.4	5/8"	3/8"	176	156	12.6	119-9800
														9.04	119-9801
															119-9802 119-9803
HNJM0200	G8	2825	1.1	18	13	1	22.4	47.4	16.5	7/8"	1/2"	253	227	19.2	119-9800
														14.3	119-9804
															119-9805 119-9806
HNJM0250	G8	2825	1.1	18	13	1	22.4	47.4	16.5	7/8"	1/2"	253	227	26.8	119-9800
														18.6	119-9804
															119-9805 119-9806
HNJM0300	G8	2825	1.1	18	13	1	22.4	47.4	16.5	7/8"	1/2"	253	227	28.7	119-9800
														19	119-9804
															119-9805 119-9806
HNJM0350	J8	3700	2.8	18	17.5	1	28.2	47.4	16.5	7/8"	1/2"	300	271	35.5	119-9800
														22.7	119-9804
															119-9805 119-9806
HNJM0400	J8	3700	2.8	18	17.5	1	28.2	47.4	16.5	7/8"	1/2"	300	271	41.8	119-9800
														26.6	119-9804
															119-9805 119-9806

⁽¹⁾ Dimensions (in) available on page 83

⁽²⁾ Dimensions (in) available on page 77
For spare parts, see pages 74

Fan	Model no	Version	Electrical code	Code no	Compressor model	Amb. Temp.	Capacity range in (btu/hr) at evaporating temperature							Power consumption [W] at evap. Temp. 25 °F	Power consumption [W] at evap. Temp. 20 °F	AWEF*
						°F	10	15	20	25	30	35	40			
Two fan	HRJM0500	WG	N	114N6112	MLZ38	90	31640	35200	39050	43210	47670	52450	57540	5406	5301	9.06 9.58
				114N6113		95	30560	33980	37700	41710	46020	50630	55560			
		WK	N	114N6162		100	29480	32760	36330	40180	44340	48790	53550			
				114N6163		110	-	30290	33550	37090	40920	45040	49460			
							115	-	29050	32150	35530	39190	43140			
	HRJM0600	WG	Q	114N6114	MLZ45	90	38490	42850	47520	52510	57830	63480	69460	6504	6351	9.64
				95		37070	41280	45790	50610	55760	61220	67020				
				100		35650	39700	44050	48710	53670	58950	64550				
				110		-	36520	40550	44850	49450	54360	59570				
				115		-	34920	38780	42910	47320	52040	57060				
		WK	Q	114N6164	MLZ45	90	38120	42410	46990	51880	57090	62610	68440	6337	6174	9.88
				95		36710	40840	45270	49990	55020	60350	66000				
				100		35280	39260	43530	48080	52930	58080	63540				
				110		-	36080	40020	44220	48710	53490	58560				
				115		-	34470	38240	42270	46580	51170	56040				
	HRJM0700	WG	Q	114N6116	MLZ48	90	42340	47050	52070	57410	63070	69060	75370	6907	6749	9.83
				95		40720	45260	50110	55260	60720	66490	72580				
				100		39070	43440	48100	53060	58320	63880	69750				
				110		-	39700	43980	48540	53380	58510	63930				
				115		-	37770	41860	46210	50840	55760	60960				
		WK	Q	114N6166	MLZ48	90	41800	46410	51310	56510	62000	67800	73900	6791	6622	10
				95		40180	44620	49340	54340	59640	65230	71100				
				100		38520	42780	47320	52130	57230	62600	68260				
				110		-	39010	43170	47580	52260	57210	62420				
				115		-	37070	41040	45250	49710	54440	59430				
	HRJM0750	WG	Q	114N6118	MLZ58	90	51070	56740	62810	69310	76240	83610	91420	7665	7493	10.28
				95		49310	54780	60640	66910	73590	80710	88260				
				100		47530	52790	58430	64470	70910	77770	85060				
				110		-	48720	53920	59480	65420	71770	78510				
				115		-	46650	51620	56940	62630	68700	75180				
		WK	Q	114N6168	MLZ58	90	50680	56260	62240	68620	75410	82630	90260	7953	7771	9.87
				95		48910	54300	60060	66210	72760	79730	87100				
				100		47120	52300	57840	63760	70080	76780	83900				
				110		-	48230	53320	58770	64580	70770	77340				
				115		-	46150	51010	56220	61780	67700	74000				
	HRJM1000	WG	Q	114N6120	MLZ76	90	62370	69580	77310	85550	94330	103600	113500	9991	9768	9.88
				95		59830	66820	74300	82280	90790	99810	109400				
				100		57230	63980	71210	78930	87150	95890	105200				
				110		-	58100	64800	71980	79630	87770	96420				
				115		-	55060	61490	68380	75740	83580	91920				
		WK	Q	114N6170	MLZ76	90	61710	68800	76380	84460	93040	102100	111700	10350	10120	9.51
				95		59160	66020	73360	81170	89480	98290	107600				
				100		56540	63170	70250	77800	85830	94350	103400				
				110		-	57250	63810	70810	78270	86190	94580				
				115		-	54190	60470	67190	74360	81970	90060				

Test condition

Return gas temperature 65°F
Subcooling 5°F

Electrical code

N: Compressor & fan(s) 230V, 1 ph, 60 Hz
Q: Compressor 208-230V, 3ph, 60 Hz & Fan(s) 230V, 1ph, 60 Hz
R: Compressor 420-460V, 3ph, 60 Hz & Fan(s) 460V, 1ph, 60 Hz

Version

WG: Electrical box, Receiver, Dual pressure control, Fan speed controller or Fan cycling, Defrost Timer, Outdoor enclosure (MBP)
WK: WG + Low Ambient Kit

HP rating in hundredths of HP, ie.: 033=1/3hp, (UCGC0100U:0100=1hp)

Power consumption referred at 90°F ambient temperature

*This refrigeration system is designed and certified for use in walk-in cooler applications

R448A and R449A performance data are nearly identical

Performance data is based on fan full speed

All Optyma Slim Condensing units are UL Listed

Catalog

Optyma™ Slim condensing unit R448A/R449A - MBP

Model no	Condenser coil			Condens- er fan	Receiver volume [Lbs]	Dimensions (in) ⁽¹⁾						Weight (lbs)		MCA (A)	Wiring diagram code ⁽²⁾
	Type	Air flow [CFM]	Int. volume [lbs]	Fan blade Ø (in)		Figure	Height H (in)	Width W (in)	Depth D (in)	Suction line	Liquid line	Gross	Net		
HRJM0500	N8	5180	3.7	18	22	2	28.8	49.4	31.5	7/8"	1/2"	400	367	50.4	119-9800
														33.3	119-9804
HRJM0600	N8	5180	3.7	18	22	2	28.8	49.4	31.5	7/8"	1/2"	400	367	39.2	119-9805
														15	119-9806
															119-9809
HRJM0700	N8	5180	3.7	18	22	2	28.8	49.4	31.5	7/8"	1/2"	400	367	42.2	119-9804
														16	119-9806
															119-9809
HRJM0750	Q8	8230	5.4	24	30	2	39.1	61.2	31.5	1 1/8"	5/8"	630	594	50.7	119-9804
														20	119-9806
															119-9809
HRJM1000	Q8	8230	5.4	24	30	2	39.1	61.2	31.5	1 1/8"	5/8"	630	594	65.1	119-9804
														28	119-9806
															119-9809

⁽¹⁾ Dimensions (in) available on page 83

⁽²⁾ Dimensions (in) available on page 77

For spare parts, see pages 74

Fan	Model no	Version	Electrical code	Code no	Compressor model	Amb. Temp.	Capacity range in (btu/hr) at evaporating temperature							Power consumption	Power consumption	AWEF*
						°F	10	15	20	25	30	35	40	[W] at evap. Temp. 25 °F	[W] at evap. Temp. 20 °F	
Single fan	HJJM0150	WG	N Q	114N6100 114N6101	MTZ18	90	4842	5722	6684	7725	8847	10050	11330	1150	1107	7.76 7.93
						95	4571	5415	6336	7334	8408	9558	10780			
						100	4297	5106	5987	6941	7968	9067	10240			
						110	-	4486	5288	6156	7088	8086	9147			
						115	-	4176	4940	5765	6651	7598	8606			
	HNJM0200	WG	N Q	114N6102 114N6103	MLZ15	90	8480	9651	10900	12220	13630	15140	16730	1577	1555	8.01 8.78
						95	8207	9349	10570	11860	13240	14710	16280			
						100	7932	9041	10230	11490	12840	14270	15800			
						110	-	8422	9532	10720	12000	13360	14810			
						115	-	8113	9183	10330	11560	12880	14290			
	HNJM0250	WG	N Q	114N6104 114N6105	MLZ19	90	10900	12380	13960	15640	17440	19350	21380	2053	2019	8 9.19
						95	10530	11980	13520	15170	16930	18800	20770			
						100	10160	11570	13070	14680	16400	18220	20150			
						110	-	10750	12170	13690	15310	17030	18850			
						115	-	10350	11720	13180	14750	16420	18180			
	HNJM0300	WG	N Q	114N6106 114N6107	MLZ21	90	11600	13160	14830	16600	18480	20480	22600	2124	2090	8.21 9.42
						95	11220	12740	14370	16100	17940	19890	21960			
						100	10830	12310	13890	15580	17370	19280	21300			
						110	-	11430	12910	14500	16190	18000	19920			
						115	-	10980	12420	13950	15590	17340	19200			
	HNJM0350	WG	N Q	114N6108 114N6109	MLZ26	90	14440	16380	18460	20690	23060	25580	28260	2611	2570	8.38 10.17
						95	13970	15870	17900	20070	22390	24860	27480			
						100	13500	15340	17320	19440	21700	24110	26660			
						110	-	14270	16130	18120	20250	22530	24950			
						115	-	13740	15520	17440	19500	21710	24050			
	HNJM0400	WG	N Q	114N6110 114N6111	MLZ30	90	17090	19430	21920	24550	27340	30300	33440	2940	2883	8.87 10.2
						95	16540	18820	21230	23800	26530	29420	32490			
						100	15980	18190	20540	23040	25690	28510	31500			
						110	-	16940	19130	21470	23960	26610	29430			
						115	-	16320	18420	20670	23070	25630	28360			

Test condition

Return gas temperature 65°F
Subcooling 5°F
(MBP)

Electrical code

N: Compressor & fan(s) 230V, 1 ph, 60 Hz
Q: Compressor 208-230V, 3ph, 60 Hz
Fan(s) 230V, 1ph, 60 Hz

Version

WG: Electrical box, Receiver, Dual pressure control, Fan speed controller or Fan cycling, Defrost Timer, Outdoor enclosure

HP rating in hundredths of HP, i.e.: 033=1/3hp, (UCGC0100U:0100=1hp)

Power consumption referred at 90°F ambient temperature

*This refrigeration system is designed and certified for use in walk-in cooler applications

Performance data is based on fan full speed

All Optyma Slim Condensing units are UL Listed

Model no	Condenser coil			Con- denser fan	Receiver volume [Lbs]	Dimensions (in) ⁽¹⁾						Weight (lbs)		MCA (A)	Wiring diagram code ⁽²⁾
	Type	Air flow [CFM]	Int. volume [lbs]	Fan blade Ø (in)		Figure	Height H (in)	Width W (in)	Depth D (in)	Suction line	Liquid line	Gross	Net		
HJJM0150	D8	1410	0.9	14	6.5	1	19.5	43.5	13.4	5/8"	3/8"	176	156	12.6	119-9800
														9.04	119-9801
HNJM0200	G8	2825	1.1	18	13	1	22.4	47.4	16.5	7/8"	1/2"	253	227	19.2	119-9800
														14.3	119-9804
HNJM0250	G8	2825	1.1	18	13	1	22.4	47.4	16.5	7/8"	1/2"	253	227	26.8	119-9800
														18.6	119-9804
HNJM0300	G8	2825	1.1	18	13	1	22.4	47.4	16.5	7/8"	1/2"	253	227	28.7	119-9800
														19	119-9804
HNJM0350	J8	3700	2.8	18	17.5	1	28.2	47.4	16.5	7/8"	1/2"	300	271	35.5	119-9800
														22.7	119-9804
HNJM0400	J8	3700	2.8	18	17.5	1	28.2	47.4	16.5	7/8"	1/2"	300	271	41.8	119-9800
														26.6	119-9804

⁽¹⁾ Dimensions (in) available on page 83

⁽²⁾ Dimensions (in) available on page 77

For spare parts, see pages 74

Fan	Model no	Version	Electrical code	Code no	Compressor model	Amb. Temp.	Capacity range in (btu/hr) at evaporating temperature							Power consumption [W] at evap. Temp. 25 °F	Power consumption [W] at evap. Temp. 20 °F	AWEF*
						°F	10	15	20	25	30	35	40			
Two fan	HRJM0500	WG	N Q	114N6112 114N6113	MLZ38	90	20530	23340	26340	29530	32930	36540	40390	3582	3530	8.44 9.33
						95	19880	22620	25540	28660	31990	35530	39300			
						100	19210	21880	24730	27770	31020	34480	38170			
						110	-	20370	23050	25920	29000	32280	35790			
						115	-	19620	22200	24980	27950	31140	34540			
	HRJM0600	WG	Q	114N6114	MLZ45	90	25440	28790	32430	36360	40560	45040	49790	4095	4030	9.73
						95	24570	27840	31390	35210	39310	43680	48300			
						100	23680	26860	30310	34040	38030	42280	46770			
						110	-	24830	28090	31610	35380	39390	43630			
						115	-	23800	26960	30370	34020	37910	42030			
	HRJM0700	WG	R	114N6115	MLZ45	90	25360	28690	32310	36220	40400	44840	49550	3666	3601	10.43
						95	24490	27740	31270	35070	39140	43470	48060			
						100	23590	26760	30190	33890	37860	42070	46530			
						110	-	24730	27970	31460	35200	39180	43390			
						115	-	23700	26840	30220	33850	37700	41780			
	HRJM0750	WG	Q	114N6116	MLZ48	90	26930	30440	34250	38340	42720	47380	52310	4157	4082	9.76
						95	26040	29450	33160	37150	41410	45950	50750			
						100	25120	28440	32050	35930	40070	44490	49160			
						110	-	26370	29750	33410	37320	41480	45880			
						115	-	25310	28590	32120	35910	39940	44210			
	HRJM0750	WG	R	114N6117	MLZ48	90	26850	30340	34120	38190	42540	47160	52050	3902	3825	10.42
						95	25950	29350	33030	37000	41230	45730	50490			
						100	25030	28340	31920	35770	39890	44270	48900			
						110	-	26260	29620	33250	37130	41260	45620			
						115	-	25200	28460	31970	35720	39720	43950			
	HRJM0750	WG	Q	114N6118	MLZ58	90	32660	36870	41410	46290	51500	57050	62950	5031	4935	9.66
						95	31670	35770	40190	44940	50020	55440	61200			
						100	30690	34660	38950	43570	48520	53800	59400			
						110	-	32410	36430	40770	45430	50410	55700			
						115	-	31280	35150	39340	43850	48670	53800			
	HRJM0750	WG	R	114N6119	MLZ58	90	32600	36800	41330	46190	51380	56910	62790	5222	5125	9.31
						95	31620	35700	40110	44840	49910	55300	61030			
						100	30630	34590	38870	43470	48400	53650	59240			
						110	-	32350	36350	40670	45310	50260	55530			
						115	-	31210	35070	39240	43730	48520	53630			
	HRJM1000	WG	Q	114N6120	MLZ76	90	41830	47000	52650	58760	65320	72310	79710	6361	6222	9.8
						95	40540	45600	51120	57090	63490	70290	77490			
						100	39210	44160	49550	55380	61610	68230	75220			
						110	-	41150	46280	51800	57700	63950	70540			
						115	-	39580	44580	49950	55680	61750	68130			
	HRJM1000	WG	R	114N6121	MLZ76	90	41740	46890	52510	58600	65130	72080	79430	6565	6423	9.49
						95	40450	45490	50990	56930	63290	70060	77210			
						100	39120	44040	49410	55210	61410	67990	74940			
						110	-	41020	46130	51630	57500	63710	70250			
						115	-	39450	44430	49780	55470	61500	67840			

Test condition

 Return gas temperature 65°F
 Subcooling 5°F

Electrical code
N: Compressor & fan(s) 230V, 1 ph, 60 Hz
Q: Compressor 208-230V, 3ph, 60 Hz & Fan(s) 230V, 1ph, 60 Hz
R: Compressor 420-460V, 3ph, 60 Hz & Fan(s) 460V, 1ph, 60Hz

Version
WG: Electrical box, Receiver, Dual pressure control, Fan speed controller or Fan cycling, Defrost Timer, Outdoor enclosure (MBP)

HP rating in hundredths of HP, ie.: 033=1/3hp, (UCGC0100U:0100=1hp)

Power consumption referred at 90°F ambient temperature

*This refrigeration system is designed and certified for use in walk-in cooler applications

Performance data is based on fan full speed

All Optyma Slim Condensing units are UL Listed

Catalog

Optyma™ Slim condensing unit R134a - MBP

Model no	Condenser coil			Con- denser fan Fan blade Ø (in)	Re- ceiver volume [Lbs]	Dimensions (in) ⁽¹⁾						Weight (lbs)		MCA (A)	Wiring diagram code ⁽²⁾
	Type	Air flow [CFM]	Int. volume [lbs]			Figure	Height H (in)	Width W (in)	Depth D (in)	Suction line	Liquid line	Gross	Net		
HRJM0500	N8	5180	3.7	18	22	2	28.8	49.4	31.5	7/8"	1/2"	400	367	50.4	119-9800
														33.3	119-9804
HRJM0600	N8	5180	3.7	18	22	2	28.8	49.4	31.5	7/8"	1/2"	400	367	39.2	119-9804
														15	119-9809
HRJM0700	N8	5180	3.7	18	22	2	28.8	49.4	31.5	7/8"	1/2"	400	367	42.2	119-9804
														16	119-9809
HRJM0750	Q8	8230	5.4	24	30	2	39.1	61.2	31.5	1 1/8"	5/8"	630	594	50.7	119-9804
														20	119-9809
HRJM1000	Q8	8230	5.4	24	30	2	39.1	61.2	31.5	1 1/8"	5/8"	630	594	65.1	119-9804
														28	119-9809

⁽¹⁾ Dimensions (in) available on page 83

⁽²⁾ Dimensions (in) available on page 77
For spare parts, see pages 74

Fan	Model no	Version	Electrical code	Code no	Compressor model	Amb. Temp.	Capacity range in (btu/hr) at evaporating temperature							Power consumption [W] at evap. Temp. 25 °F	Power consumption [W] at evap. Temp. 20 °F	AWEF
						°F	10	15	20	25	30	35	40			
Single fan	HJJM0150	WG	N	114N6100	MTZ18	90	9048	10350	11676	13124	14644	16232	17847	2002	1935	7.85
			Q	114N6101		95	8504	9749	11017	12399	13848	15363	16904			
		WK	N	114N6150		100	7957	9146	10355	11672	13052	14492	15960			
			Q	114N6151		110	-	8138	9249	10458	11723	13042	14388			
						115	-	7532	8585	9730	10927	12175	13449			
	HNJM0200	WG	N	114N6102	MLZ15	90	14640	16250	17950	19740	21590	23520	25490	2359	2337	10.06 10.04
			Q	114N6103		95	13970	15520	17150	18870	20650	22490	24380			
		WK	N	114N6152		100	13290	14780	16340	17990	19700	21460	23260			
			Q	114N6153		110	-	13240	14680	16180	17750	19350	20990			
						115	-	12440	13820	15260	16750	18280	19850			
	HNJM0250	WG	N	114N6104	MLZ19	90	19080	20970	22970	25090	27320	29670	32130	2973	2933	10.04 10.3
			Q	114N6105		95	18290	20100	22020	24040	26180	28430	30800			
		WK	N	114N6154		100	17490	19210	21040	22980	25030	27180	29450			
			Q	114N6155		110	-	17390	19050	20810	22670	24640	26710			
						115	-	16450	18020	19690	21470	23340	25320			
	HNJM0300	WG	N	114N6106	MLZ21	90	20150	22110	24190	26400	28730	31190	33790	3187	3136	9.92 10.27
			Q	114N6107		95	19300	21180	23180	25290	27530	29890	32390			
		WK	N	114N6156		100	18420	20220	22140	24160	26310	28580	30970			
			Q	114N6157		110	-	18230	19980	21840	23800	25890	28090			
						115	-	17190	18860	20630	22510	24510	26630			
	HNJM0350	WG	N	114N6108	MLZ26	90	25330	27850	30510	33300	36230	39270	42440	3829	3774	10.33 10.58
			Q	114N6109		95	24270	26680	29230	31910	34720	37640	40680			
		WK	N	114N6158		100	23170	25480	27930	30490	33180	35980	38900			
			Q	114N6159		110	-	22980	25210	27560	30020	32580	35250			
						115	-	21670	23800	26040	28390	30840	33400			
	HNJM0400	WG	N	114N6110	MLZ30	90	28880	31820	34900	38120	41480	44960	48570	4596	4507	9.62 10.51
			Q	114N6111		95	27590	30400	33360	36450	39660	43010	46470			
		WK	N	114N6160		100	26270	28960	31790	34740	37820	41020	44340			
			Q	114N6161		110	-	25990	28570	31250	34060	36970	40000			
						115	-	24470	26910	29470	32140	34920	37800			

Test condition

Return gas temperature 65°F
Subcooling 5°F
(MBP)

Electrical code

N: Compressor & fan(s) 230V, 1 ph, 60 Hz
Q: Compressor 208-230V, 3ph, 60 Hz
Fan(s) 230V, 1ph, 60 Hz

Version

WG: Electrical box, Receiver, Dual pressure control, Fan speed controller or Fan cycling, Defrost Timer, Outdoor enclosure
WK: WG + Low Ambient Kit

HP rating in hundredths of HP, i.e.: 033=1/3hp, (UCGC0100U:0100=1hp)

Power consumption referred at 90°F ambient temperature

*This refrigeration system is designed and certified for use in walk-in cooler applications

Performance data is based on fan full speed

All Optyma Slim Condensing units are UL Listed

Catalog

Optyma™ Slim condensing unit R404A/R507 - MBP

Model no	Condenser coil			Condenser fan	Receiver volume [Lbs]	Dimensions (in) ⁽¹⁾						Weight (lbs)		MCA (A)	Wiring diagram code ⁽²⁾
	Type	Air flow [CFM]	Int. volume [lbs]	Fan blade Ø (in)		Figure	Height H (in)	Width W (in)	Depth D (in)	Suction line	Liquid line	Gross	Net		
HJJM0150	D8	1410	0.9	14	6.5	1	19.5	43.5	13.4	58"	38"	176	156	12.6	119-9800
														119-9802	
														9.04	119-9801
HNJM0200	G8	2825	1.1	18	13	1	22.4	47.4	16.5	7/8"	1/2"	253	227	19.2	119-9800
														119-9805	
														14.3	119-9804
HNJM0250	G8	2825	1.1	18	13	1	22.4	47.4	16.5	7/8"	1/2"	253	227	26.8	119-9800
														119-9805	
														18.6	119-9804
HNJM0300	G8	2825	1.1	18	13	1	22.4	47.4	16.5	7/8"	1/2"	253	227	28.7	119-9800
														119-9805	
														19	119-9804
HNJM0350	J8	3700	2.8	18	17.5	1	28.2	47.4	16.5	7/8"	1/2"	300	271	35.5	119-9800
														119-9805	
														22.7	119-9804
HNJM0400	J8	3700	2.8	18	17.5	1	28.2	47.4	16.5	7/8"	1/2"	300	271	41.8	119-9800
														119-9805	
														26.6	119-9804

⁽¹⁾ Dimensions (in) available on page 83

⁽²⁾ Dimensions (in) available on page 77

For spare parts, see pages 74

Fan	Model no	Version	Electrical code	Code no	Compressor model	Amb. Temp.	Capacity range in (btu/hr) at evaporating temperature							Power consumption [W] at evap. Temp. 25 °F	Power consumption [W] at evap. Temp. 20 °F	AWEF*	
						°F	10	15	20	25	30	35	40				
Two fan	HRJM0500	WG	N	114N6112	MLZ38	90	35730	39530	43530	47720	52110	56690	61440	5430	5336	9.64 10.48	
				114N6113		95	34120	37770	41630	45690	49930	54360	58960				
		WK	N	114N6162		100	32480	35990	39700	43610	47700	51970	56420				
				114N6163		110	-	32350	35750	39340	43110	47060	51190				
	HRJM0600	WG	Q	114N6114	MLZ45	115	-	30520	33750	37170	40770	44560	48510	6264	6181	10.57	
				90		43050	47300	51790	56540	61520	66740	72210					
				95		41250	45320	49630	54180	58960	63980	69220					
				100		39410	43310	47430	51780	56360	61170	66200					
		WK	Q	114N6164	110	-	39140	42890	46860	51040	55430	60040					
				115	-	36980	40550	44320	48310	52500	56900						
				WG	R	114N6115	90	42760	46970	51400	56080	60990	66130	71500			
						95	40970	44990	49240	53720	58430	63360	68520				
		100	39130			42970	47040	51330	55830	60560	65500						
		110	-			38790	42490	46400	50510	54830	59350						
		HRJM0700	WG	Q	114N6116	MLZ48	115	-	36630	40150	43860	47780	51900	56220	6912	6798	10.45
					90		46560	51140	55980	61060	66380	71930	77700				
	95				44590		48980	53610	58470	63570	68890	74420					
	100				42570		46760	51180	55830	60700	65790	71080					
	WK		Q	114N6166	110	-	42140	46150	50360	54790	59420	64250					
				115	-	39740	43540	47540	51750	56160	60760						
				WG	R	114N6117	90	46220	50750	55520	60520	65760	71210	76870			
						95	44250	48580	53140	57930	62940	68160	73590				
	100		42230			46360	50710	55290	60070	65070	70260						
	110		-			41730	45670	49820	54170	58710	63440						
	HRJM0750		WG	Q	114N6118	MLZ58	115	-	39320	43060	47000	51120	55450	59960	8089	7948	10.66
					90		56950	63010	69380	76050	83030	90340	97970				
		95			54160		59960	66040	72410	79070	86030	93300					
		100			51290		56830	62620	68670	75010	81620	88520					
		WK	Q	114N6168	110	-	50310	55510	60940	66610	72520	78690					
				115	-	46940	51840	56950	62280	67840	73640						
				WG	R	114N6119	90	56660	62700	69070	75750	82720	89980	97500			
						95	53860	59640	65720	72100	78750	85670	92850				
		100	50980			56480	62270	68340	74680	81260	88090						
		110	-			49920	55110	60560	66240	72140	78260						
		HRJM1000	WG	Q	114N6120	MLZ76	115	-	46510	51400	56530	61880	67440	73210	10580	10380	10.3
					90		72760	79770	87190	95020	103300	111900	120900				
95	69610				76280		83330	90760	98580	106800	115400						
100	66390				72700		79370	86410	93800	101600	109700						
WK	Q		114N6170	110	-	65300	71210	77440	84000	90890	98100						
			115	-	61460	67000	72830	78970	85420	92190							
			WG	R	114N6121	90	72440	79400	86750	94500	102600	111200	120100				
					95	69300	75900	82880	90230	97960	106100	114500					
100	66070				72330	78930	85880	93190	100900	108900							
110	-				64910	70760	76920	83390	90190	97300							
115	-		61080	66550	72310	78370	84730	91400									

Test condition

 Return gas temperature 65°F
 Subcooling 5°F

Electrical code
N: Compressor & fan(s) 230V, 1 ph, 60 Hz
Q: Compressor 208-230V, 3ph, 60 Hz & Fan(s) 230V, 1ph, 60 Hz
R: Compressor 420-460V, 3ph, 60 Hz & Fan(s) 460V, 1ph, 60Hz

Version
WG: Electrical box, Receiver, Dual pressure control, Fan speed controller or Fan cycling, Defrost Timer, Outdoor enclosure (MBP)
WK: WG + Low Ambient Kit

HP rating in hundredths of HP, ie.: 033=1/3hp, (UCGC0100U:0100=1hp)

Power consumption referred at 90°F ambient temperature

*This refrigeration system is designed and certified for use in walk-in cooler applications

Performance data is based on fan full speed

All Optyma Slim Condensing units are UL Listed

Catalog

Optyma™ Slim condensing unit R404A/R507 - MBP

Model no	Condenser coil			Con- denser fan	Receiver volume [Lbs]	Dimensions (in) ⁽¹⁾						Weight (lbs)		MCA (A)	Wiring diagram code ⁽²⁾
	Type	Air flow [CFM]	Int. volume [lbs]	Fan blade Ø (in)		Figure	Height H (in)	Width W (in)	Depth D (in)	Suction line	Liquid line	Gross	Net		
HRJM0500	N8	5180	3.7	18	22	2	28.8	49.4	31.5	7/8"	1/2"	400	367	50.4	119-9800
														119-9804	
														33.3	119-9805
														119-9806	
HRJM0600	N8	5180	3.7	18	22	2	28.8	49.4	31.5	7/8"	1/2"	400	367	39.2	119-9804
														15	119-9806
														119-9809	
														42.2	119-9804
HRJM0700	N8	5180	3.7	18	22	2	28.8	49.4	31.5	7/8"	1/2"	400	367	16	119-9806
														119-9809	
HRJM0750	Q8	8230	5.4	24	30	2	39.1	61.2	31.5	1 1/8"	5/8"	630	594	50.7	119-9804
														20	119-9806
														119-9809	
														65.1	119-9804
HRJM1000	Q8	8230	5.4	24	30	2	39.1	61.2	31.5	1 1/8"	5/8"	630	594	28	119-9806
														119-9809	

⁽¹⁾ Dimensions (in) available on page 83

⁽²⁾ Dimensions (in) available on page 77

For spare parts, see pages 74

Fan	Model no	Version	Electrical code	Code no	Compressor model	Amb. Temp.	Capacity range in (btu/hr) at evaporating temperature							Power consumption [W] at evap. Temp. 25 °F	Power consumption [W] at evap. Temp. 20 °F	AWEF*
						°F	10	15	20	25	30	35	40			
Single fan	HJMJ0150	WG	N Q	114N6100 114N6101	MTZ18	90	8675	9829	11050	12340	13690	15100	16570	1875	1801	8.09
						95	8167	9269	10440	11660	12950	14290	15690			
						100	7662	8712	9822	10990	12210	13490	14820			
						110	-	7606	8606	9658	10760	11910	13100			
						115	-	7059	8005	8999	10040	11120	12250			
	HNJM0200	WG	N Q	114N6102 114N6103	MLZ15	90	14020	15500	17070	18730	20490	22340	24290	2481	2442	8.69 8.98
						95	13490	14900	16400	18000	19680	21450	23310			
						100	12930	14280	15720	17240	18850	20540	22320			
						110	-	13000	14300	15670	17120	18660	20270			
						115	-	12340	13560	14860	16240	17690	19230			
	HNJM0250	WG	N Q	114N6104 114N6105	MLZ19	90	17940	19830	21830	23940	26150	28470	30900	3087	3032	9.06 9.23
						95	17220	19030	20940	22960	25080	27300	29620			
						100	16470	18210	20030	21960	23980	26100	28320			
						110	-	16500	18150	19890	21720	23640	25650			
						115	-	15620	17190	18830	20560	22380	24290			
	HNJM0300	WG	N Q	114N6106 114N6107	MLZ21	90	18820	20800	22890	25100	27430	29870	32420	3237	3177	9.06 9.28
						95	18050	19940	21940	24060	26280	28620	31070			
						100	17250	19060	20970	22990	25110	27340	29680			
						110	-	17220	18940	20770	22690	24710	26840			
						115	-	16270	17900	19620	21450	23360	25380			
	HNJM0350	WG	N Q	114N6108 114N6109	MLZ26	90	23480	25980	28640	31450	34410	37530	40790	3855	3779	9.56 9.76
						95	22490	24900	27450	30150	32990	35980	39120			
						100	21490	23800	26240	28830	31550	34420	37430			
						110	-	21530	23760	26110	28600	31230	33980			
						115	-	20360	22480	24730	27100	29600	32240			
	HNJM0400	WG	N Q	114N6110 114N6111	MLZ30	90	27420	30250	33240	36400	39720	43200	46830	4572	4466	9.35 9.8
						95	26330	29040	31900	34920	38100	41430	44910			
						100	25210	27800	30530	33410	36440	39620	42950			
						110	-	25210	27670	30280	33020	35910	38940			
						115	-	23870	26200	28670	31270	34010	36890			

Test condition

Return gas temperature 65°F
Subcooling 5°F

Electrical code

N: Compressor & fan(s) 230V, 1 ph, 60 Hz
Q: Compressor 208-230V, 3ph, 60 Hz & Fan(s) 230V, 1ph, 60 Hz

Version

WG: Electrical box, Receiver, Dual pressure control, Fan speed controller or Fan cycling, Defrost Timer, Outdoor enclosure (MBP)
WK: WG + Low Ambient Kit

HP rating in hundredths of HP, ie.: 033=1/3hp, (UCGC0100U:0100=1hp)

Power consumption referred at 90°F ambient temperature

*This refrigeration system is designed and certified for use in walk-in cooler applications

Performance data is based on fan full speed

All Optyma Slim Condensing units are UL Listed

Model no	Condenser coil			Con- denser fan Fan blade Ø (in)	Receiver volume [Lbs]	Dimensions (in) ⁽¹⁾						Weight (lbs)		MCA (A)	Wiring diagram code ⁽²⁾
	Type	Air flow [CFM]	Int. volume [lbs]			Figure	Height H (in)	Width W (in)	Depth D (in)	Suction line	Liquid line	Gross	Net		
HJJM0150	D8	1410	0.9	14	6.5	1	19.5	43.5	13.4	5/8"	3/8"	176	156	12.6 9.04	119-9800 119-9801
HNJM0200	G8	2825	1.1	18	13	1	22.4	47.4	16.5	7/8"	1/2"	253	227	19.2 14.3	119-9800 119-9804
HNJM0250	G8	2825	1.1	18	13	1	22.4	47.4	16.5	7/8"	1/2"	253	227	26.8 18.6	119-9800 119-9804
HNJM0300	G8	2825	1.1	18	13	1	22.4	47.4	16.5	7/8"	1/2"	253	227	28.7 19	119-9800 119-9804
HNJM0350	J8	3700	2.8	18	17.5	1	28.2	47.4	16.5	7/8"	1/2"	300	271	35.5 22.7	119-9800 119-9804
HNJM0400	J8	3700	2.8	18	17.5	1	28.2	47.4	16.5	7/8"	1/2"	300	271	41.8 26.6	119-9800 119-9804

⁽¹⁾ Dimensions (in) available on page 83

⁽²⁾ Dimensions (in) available on page 77
For spare parts, see pages 74

Fan	Model no	Version	Electrical code	Code no	Compres- sor model	Amb. Temp.	Capacity range in (btu/hr) at evaporating temperature							Power con- sumption [W] at evap. Temp. 25 °F	Power con- sumption [W] at evap. Temp. 20 °F	AWEF*
						°F	10	15	20	25	30	35	40			
Single fan	HRJM0500	WG	N Q	114N6112 114N6113	MLZ38	90	33490	37040	40820	44840	49100	53590	58330	5617	5514	9.14 9.71
						95	32190	35580	39210	43050	47130	51440	55980			
						100	30850	34100	37560	41230	45130	49240	53580			
						110	-	31020	34150	37470	41000	44740	48690			
						115	-	29440	32390	35540	38890	42440	46190			
	HRJM0600	WG	Q	114N6114	MLZ45	90	40810	44950	49360	54040	58980	64190	69670	6647	6484	9.53
						95	39180	43130	47340	51800	56510	61490	66730			
						100	37520	41280	45270	49520	54010	58750	63750			
						110	-	37480	41060	44860	48890	53170	57680			
						115	-	35540	38900	42480	46290	50330	54610			
		WG	R	114N6115	MLZ45	90	40670	44780	49150	53780	58670	63820	69230	6411	6246	9.89
						95	39040	42950	47120	51540	56200	61120	66290			
						100	37380	41100	45060	49260	53700	58380	63310			
						110	-	37290	40830	44580	48560	52770	57220			
						115	-	35340	38660	42190	45940	49910	54110			
	HRJM0700	WG	Q	114N6116	MLZ48	90	44500	49090	53970	59130	64580	70310	76320	7246	7086	9.81
						95	42630	47020	51680	56620	61830	67320	73080			
						100	40720	44900	49350	54050	59030	64270	69780			
						110	-	40550	44550	48790	53280	58030	63050			
						115	-	38330	42090	46100	50350	54860	59620			
		WG	R	114N6117	MLZ48	90	44160	48690	53480	58560	63900	69510	75390	7060	6892	10.07
						95	42290	46610	51190	56040	61150	66520	72150			
						100	40380	44490	48850	53470	58340	63470	68850			
						110	-	40130	44040	48180	52570	57200	62070			
						115	-	37880	41560	45470	49610	53990	58610			
	HRJM0750	WG	Q	114N6118	MLZ58	90	53900	59650	65770	72280	79180	86470	94150	8415	8255	10.3
						95	51680	57210	63090	69350	75980	82990	90380			
						100	49420	54710	60350	66340	72700	79430	86520			
						110	-	49540	54670	60140	65940	72090	78600			
						115	-	46880	51750	56940	62470	68330	74550			
		WG	R	114N6119	MLZ58	90	53730	59450	65540	72000	78850	86080	93690	8241	8080	10
						95	51520	57010	62860	69070	75640	82590	89920			
						100	49250	54510	60110	66060	72370	79030	86060			
						110	-	49340	54430	59840	65590	71680	78110			
						115	-	46660	51490	56630	62100	67890	74030			
	HRJM1000	WG	Q	114N6120	MLZ76	90	67150	74200	81650	89500	97760	106400	115500	10420	10220	9.95
						95	64380	71130	78270	85800	93710	102000	110700			
						100	61540	68000	74820	82020	89590	97530	105800			
						110	-	61520	67700	74220	81090	88310	95890			
						115	-	58180	64040	70220	76740	83600	90810			
		WG	R	114N6121	MLZ76	90	66860	73850	81230	89000	97170	105700	114600	10680	10470	9.69
						95	64080	70780	77850	85300	93120	101300	109900			
						100	61240	67640	74400	81510	88990	96820	105000			
						110	-	61140	67250	73680	80460	87560	95010			
						115	-	57790	63560	69650	76070	82810	89880			

Test condition

Return gas temperature 65°F
Subcooling 5°F

Electrical code

N: Compressor & fan(s) 230V, 1 ph, 60 Hz
Q: Compressor 208-230V, 3ph, 60 Hz & Fan(s) 230V, 1ph, 60 Hz
R: Compressor 420-460V, 3ph, 60 Hz & Fan(s) 460V, 1ph, 60Hz

Version

WG: Electrical box, Receiver, Dual pressure control, Fan speed controller or Fan cycling, Defrost Timer, Outdoor enclosure (MBP)

HP rating in hundredths of HP, i.e.: 033=1/3hp, (UCGC0100U:0100=1hp)

Power consumption referred at 90°F ambient temperature

*This refrigeration system is designed and certified for use in walk-in cooler applications

Performance data is based on fan full speed

All Optyma Slim Condensing units are UL Listed

Model no	Condenser coil			Condenser fan	Re-ceiver volume [Lbs]	Dimensions (in) ⁽¹⁾						Weight (lbs)		MCA (A)	Wiring diagram code ⁽²⁾
	Type	Air flow [CFM]	Int. volume [lbs]	Fan blade Ø (in)		Figure	Height H (in)	Width W (in)	Depth D (in)	Suction line	Liquid line	Gross	Net		
HRJM0500	N8	5180	3.7	18	22	2	28.8	49.4	31.5	7/8"	1/2"	400	367	50.4 33.3	119-9800 119-9804
HRJM0600	N8	5180	3.7	18	22	2	28.8	49.4	31.5	7/8"	1/2"	400	367	39.2 15	119-9804 119-9809
HRJM0700	N8	5180	3.7	18	22	2	28.8	49.4	31.5	7/8"	1/2"	400	367	42.2 16	119-9804 119-9809
HRJM0750	Q8	8230	5.4	24	30	2	39.1	61.2	31.5	1 1/8"	5/8"	630	594	50.7 20	119-9804 119-9809
HRJM1000	Q8	8230	5.4	24	30	2	39.1	61.2	31.5	1 1/8"	5/8"	630	594	65.1 28	119-9804 119-9809

⁽¹⁾ Dimensions (in) available on page 83

⁽²⁾ Dimensions (in) available on page 77
For spare parts, see pages 74

Fan	Model no	Version	Electrical code	Code no	Compressor model	Amb. Temp.	Capacity range in (btu/hr) at evaporating temperature							Power consumption [W] at evap. Temp. 25 °F	Power consumption [W] at evap. Temp. 20 °F	AWEF*
						°F	10	15	20	25	30	35	40			
Single fan	HJJM0150	WG	N	114N6100	MTZ18	90	7007	8166	9412	10748	12171	13683	15280	1569	1483	7.6
			Q	114N6101		95	6560	7678	8882	10179	11557	13018	14557			
		WK	N	114N6150		100	6114	7198	8362	9609	10939	12346	13834			
			Q	114N6151		110	-	6245	7331	8493	9730	11038	12409			
						115	-	5776	6824	7941	9131	10388	11705			
	HNJM0200	WG	N	114N6102	MLZ15	90	11519	12911	14409	16026	17740	19567	21513	2462	2427	7.6
			Q	114N6103		95	11128	12477	13929	15488	17150	18925	20796			
		WK	N	114N6152		100	10733	12040	13446	14958	16563	18272	20078			
			Q	114N6153		110	-	11158	12469	13873	15368	16954	18627			
						115	-	11188	11975	13326	14760	16290	17891			
	HNJM0250	WG	N	114N6104	MLZ19	90	14751	16446	18269	20219	22301	24505	26931	3038	2981	7.6
			Q	114N6105		95	14266	15904	17662	19541	21544	23665	26078			
		WK	N	114N6154		100	13782	15361	17055	18865	20791	22830	25160			
			Q	114N6155		110	-	14276	15839	17507	19283	21272	23319			
						115	-	13733	15230	16826	18521	20466	22396			
	HNJM0300	WG	N	114N6106	MLZ21	90	15547	17358	19298	21377	23589	25933	28611	3167	3109	7.6
			Q	114N6107		95	14996	16746	18625	20633	22767	25092	27626			
		WK	N	114N6156		100	14439	16128	17945	19882	21943	24285	26635			
			Q	114N6157		110	-	14889	16570	18368	20265	22472	24624			
						115	-	14877	15877	17597	19461	21546	23610			
	HNJM0350	WG	N	114N6108	MLZ26	90	29195	31654	34299	37160	40158	43378	46780	3849	3767	7.6
			Q	114N6109		95	29017	31418	34002	36765	39711	42839	46146			
		WK	N	114N6158		100	28863	31206	33722	36299	39284	42325	45534			
			Q	114N6159		110	-	30862	33247	35796	38504	41371	44385			
						115	-	30729	33052	35531	38153	40934	43851			
	HNJM0400	WG	N	114N6110	MLZ30	90	23532	26147	28956	31964	35166	38555	42132	4521	4422	7.6
			Q	114N6111		95	22605	25135	27850	30752	33851	37121	40561			
		WK	N	114N6160		100	21682	24122	26742	29541	32515	35661	38957			
			Q	114N6161		110	-	22053	24475	27060	29807	32701	35732			
						115	-	21718	23327	25803	28434	31190	34089			

Test condition

Return gas temperature 40°F
Subcooling 5°F

Electrical code

N: Compressor & fan(s) 230V, 1 ph, 60 Hz
Q: Compressor 208-230V, 3ph, 60 Hz & Fan(s) 230V, 1ph, 60 Hz
R: Compressor 420-460V, 3ph, 60 Hz & Fan(s) 460V, 1ph, 60Hz

Version

WH: Electrical box, Receiver, Dual pressure control, Fan speed controller or Fan cycling, Defrost Timer, Outdoor enclosure, Suction Accumulator (LBP)
WL: WH+Low Ambient Kit

HP rating in hundredths of HP, ie.: 033=1/3hp, (UCGC0100U:0100=1hp)
Power consumption referred at 90°F ambient temperature
Performance data is based on fan full speed

All Optyma Slim Condensing units are UL Listed

Catalog

Optyma™ Slim condensing unit R454C/R455A - MBP

Model no	Condenser coil			Con- denser fan	Re- ceiver volume [Lbs]	Dimensions (in) ⁽¹⁾						Weight (lbs)		MCA (A)	Wiring diagram code ⁽²⁾
	Type	Air flow [CFM]	Int. volume [lbs]	Fan blade Ø (in)		Fig- ure	Height H (in)	Width W (in)	Depth D (in)	Suction line	Liquid line	Gross	Net		
HJJM0150	D8	1410	0.9	14	6.5	1	19.5	43.5	13.4	5/8"	3/8"	176	156	12.6	119-9800 119-9801
														9.04	119-9802 119-9803
HNJM0200	G8	2825	1.1	18	13	1	22.4	47.4	16.5	7/8"	1/2"	253	227	19.2	119-9800 119-9804
														14.3	119-9805 119-9806
HNJM0250	G8	2825	1.1	18	13	1	22.4	47.4	16.5	7/8"	1/2"	253	227	26.8	119-9800 119-9804
														18.6	119-9805 119-9806
HNJM0300	G8	2825	1.1	18	13	1	22.4	47.4	16.5	7/8"	1/2"	253	227	28.7	119-9800 119-9804
														19	119-9805 119-9806
HNJM0350	J8	3700	2.8	18	17.5	1	28.2	47.4	16.5	7/8"	1/2"	300	271	35.5	119-9800 119-9804
														22.7	119-9805 119-9806
HNJM0400	J8	3700	2.8	18	17.5	1	28.2	47.4	16.5	7/8"	1/2"	300	271	41.8	119-9800 119-9804
														26.6	119-9805 119-9806

⁽¹⁾ Dimensions (in) available on page 83

⁽²⁾ Dimensions (in) available on page 77

For spare parts, see pages 74

Fan	Model no	Version	Electrical code	Code no	Compressor model	Amb. Temp.	Capacity range in (btu/hr) at evaporating temperature							Power consumption [W] at evap. Temp. 25 °F	Power consumption [W] at evap. Temp. 20 °F	AWEF*
						°F	10	15	20	25	30	35	40			
Two fan	HRJM0500	WG	N	114N6112	MLZ38	90	28142	31442	35025	38901	43079	47553	52325	5053	4983	7.6
				114N6113		95	27202	30399	33867	37620	41651	45987	50592			
		WK	N	114N6162		100	26258	29350	32703	36331	40236	44413	48861			
				114N6163		110	-	27238	30354	33720	37354	41227	45329			
						115	-	27199	29177	32415	35893	39608	43555			
	HRJM0600	WG	Q	114N6114	MLZ45	90	34721	38545	42677	47116	51869	56830	62292	6041	5945	7.6
						95	33527	37211	41175	45446	50026	54875	60026			
		WK	Q	114N6164		100	32327	35855	39677	43774	48163	52826	57743			
						110	-	33161	36648	40400	43592	48664	53143			
						115	-	31803	35129	38702	42523	46578	50844			
		WG	R	114N6115	MLZ45	90	34721	38545	42677	47116	51869	56830	62292	5902	5806	7.6
						95	33527	37211	41175	45446	50026	54875	60026			
						100	32327	35855	39677	43774	48163	52826	57743			
						110	-	33161	36648	40400	43592	48664	53143			
						115	-	31803	35129	38702	42523	46578	50844			
	HRJM0700	WG	Q	114N6116	MLZ48	90	37644	41879	46440	51349	56590	62169	68066	6388	6388	7.6
						95	36312	40389	44794	49528	54590	59952	65630			
		WK	Q	114N6166		100	34963	38893	43127	47677	52556	57730	63167			
						110	-	35886	39797	43988	48591	53190	58186			
						115	-	34381	38115	42123	46407	50928	55678			
		WG	R	114N6117	MLZ48	90	37644	41879	46440	51349	56590	62169	68066	6396	6249	7.6
						95	36312	40389	44794	49528	54590	59952	65630			
						100	34963	38893	43127	47677	52556	57730	63167			
						110	-	35886	39797	43988	48591	53190	58186			
						115	-	34381	38115	42123	46407	50928	55678			
	HRJM0750	WG	Q	114N6118	MLZ58	90	44593	49853	55506	61570	68081	75016	82360	7143	7056	7.6
						95	43055	48150	53627	59506	65801	72490	79598			
		WK	Q	114N6168		100	41491	46420	51714	57398	63474	69931	76784			
						110	-	42874	47794	53092	58688	64683	71003			
						115	-	41064	45798	50860	56262	61962	68019			
		WG	R	114N6119	MLZ58	90	44593	49853	55520	61570	68081	75016	82360	7231	7144	7.6
						95	43055	48150	53627	59506	65801	72490	79598			
						100	41491	46420	51714	57398	63474	69931	76784			
						110	-	42874	47794	53092	58688	64683	71003			
						115	-	41064	45798	50860	56262	61962	68019			
	HRJM1000	WG	Q	114N6120	MLZ76	90	57356	64141	71434	79267	87573	96402	105740	9463	9298	7.6
						95	55198	61776	68830	76392	84450	92997	101998			
		WK	Q	114N6170		100	53006	59373	66203	73503	81275	89523	98198			
						110	-	54470	60824	67615	74824	82445	92093			
						115	-	51976	58089	64607	71524	78823	86502			
		WG	R	114N6121	MLZ76	90	57271	64053	71332	79138	87462	96286	105619	9549	9384	7.6
						95	55114	61691	68748	76296	84348	92890	101881			
						100	52933	59291	66113	73409	81188	89447	98084			
						110	-	54394	60741	67525	74743	82331	90341			
						115	-	51902	58006	64523	71438	78729	86396			

Catalog

Optyma™ Slim condensing unit R454C/R455A - MBP

Model no	Condenser coil			Con- denser fan	Re- ceiver volume [Lbs]	Dimensions (in) ⁽¹⁾						Weight (lbs)		MCA (A)	Wiring diagram code ⁽²⁾
	Type	Air flow [CFM]	Int. volume [lbs]	Fan blade Ø (in)		Figure	Height H (in)	Width W (in)	Depth D (in)	Suction line	Liquid line	Gross	Net		
HRJM0500	N8	5180	3.7	18	22	2	28.8	49.4	31.5	7/8"	1/2"	400	367	50.4 33.3	119-9800 119-9804 119-9805 119-9806
HRJM0600	N8	5180	3.7	18	22	2	28.8	49.4	31.5	7/8"	1/2"	400	367	39.2 15	119-9804 119-9806 119-9809
HRJM0700	N8	5180	3.7	18	22	2	28.8	49.4	31.5	7/8"	1/2"	400	367	42.2 16	119-9804 119-9806 119-9809
HRJM0750	Q8	8230	5.4	24	30	2	39.1	61.2	31.5	1 1/8"	5/8"	630	594	50.7 20	119-9804 119-9806 119-9809
HRJM1000	Q8	8230	5.4	24	30	2	39.1	61.2	31.5	1 1/8"	5/8"	630	594	65.1 28	119-9804 119-9806 119-9809

⁽¹⁾ Dimensions (in) available on page 83

⁽²⁾ Dimensions (in) available on page 77

For spare parts, see pages 74

Fan	Model no	Version	Electrical code	Code no	Compressor model	Amb. Temp.	Capacity range in (btu/hr) at evaporating temperature							Power consumption [W] at evap. Temp. -20 °F	Power consumption [W] at evap. Temp. -10 °F	AWEF*	
						°F	-25	-20	-15	-10	-5	0	5				10
Single fan	LNJM0400	WH WL	Q Q	114N6134 114N6184	LLZ013	90	11030	12470	14030	15720	17550	19500	21590	23820	3268	3563	3.41
						95	-	12090	13590	15220	16970	18850	20850	22980			
						100	-	-	13140	14700	16380	18180	20100	22140			
						105	-	-	-	14170	15770	17490	19330	21270			
						110	-	-	-	-	15150	16790	18540	20400			
	LNJM0500	WH WL	Q Q	114N6136 114N6186	LLZ015	90	13550	15280	17170	19210	21420	23800	26350	29070	3981	4297	3.48
						95	-	14850	16660	18620	20730	23000	25430	28020			
						100	-	-	16140	18010	20020	22180	24500	26960			
						105	-	-	-	17380	19300	21350	23550	25890			
						110	-	-	-	-	18550	20500	22580	24790			
	LNJM0600	WH WL	Q Q	114N6138 114N6188	LLZ018	90	15080	17030	19150	21440	23920	26570	29400	32420	4954	5385	3.26
						95	-	16410	18440	20630	22990	25520	28220	31090			
						100	-	-	17700	19780	22030	24440	27010	29740			
						105	-	-	-	18900	21030	23320	25750	28340			
						110	-	-	-	-	19990	22150	24450	26890			
Two fan	LNJM0800	WH WL	Q Q	114N6140 114N6190	LLZ024	90	20000	22510	25230	28170	31330	34730	38350	42200	5683	6222	3.39
						95	-	21860	24480	27310	30340	33590	37060	40750			
						100	-	-	23700	26410	29320	32430	35750	39270			
						105	-	-	-	25470	28250	31220	34390	37750			
						110	-	-	-	-	27140	29970	32980	36180			

Test condition

Return gas temperature 40°F
Subcooling 5°F

Electrical code

N: Compressor & fan(s) 230V, 1 ph, 60 Hz
Q: Compressor 208-230V, 3ph, 60 Hz & Fan(s) 230V, 1ph, 60 Hz
R: Compressor 420-460V, 3ph, 60 Hz & Fan(s) 460V, 1ph, 60Hz

Version

WH: Electrical box, Receiver, Dual pressure control, Fan speed controller or Fan cycling, Defrost Timer, Outdoor enclosure, Suction Accumulator (LBP)
WL: WH+Low Ambient Kit

HP rating in hundredths of HP, i.e.: 033=1/3hp, (UCGC0100U:0100=1hp)
Power consumption referred at 90°F ambient temperature
Performance data is based on fan full speed

All Optyma Slim Condensing units are UL Listed

Model no	Condenser coil			Con- denser fan Fan blade Ø (in)	Receiver volume [Lbs]	Dimensions (in) ⁽¹⁾						Weight (lbs)		MCA (A)	Wiring diagram code ⁽²⁾
	Type	Air flow [CFM]	Int. volume [lbs]			Figure	Height H (in)	Width W (in)	Depth D (in)	Suction line	Liquid line	Gross	Net		
LNJM0400	J8	3590	2.8	18	17.5	1	28.2	47.4	16.5	7/8"	1/2"	295	266	24.3	119-9807 119-9808
LNJM0500	J8	3590	2.8	18	17.5	1	28.2	47.4	16.5	7/8"	1/2"	295	266	25.1	119-9807 119-9808
LNJM0600	J8	3590	2.8	18	17.5	1	28.2	47.4	16.5	7/8"	1/2"	295	266	28.9	119-9807 119-9808
LRJM0800	N8	5026	3.7	18	22	2	28.8	49.4	31.5	1 1/8"	1/2"	442	409	35.9	119-9807 119-9808

⁽¹⁾ Dimensions (in) available on page 83

⁽²⁾ Dimensions (in) available on page 77
For spare parts, see pages 74

Fan	Model no	Version	Electrical code	Code no	Compressor model	Amb. Temp.	Capacity range in (btu/hr) at evaporating temperature								Power consumption [W] at evap. Temp. -20 °F	Power consumption [W] at evap. Temp. -10 °F	AWEF*
						°F	-25	-20	-15	-10	-5	0	5	10			
Single fan	LJJM0150	WH	N Q	114N6130 114N6131	NTZ048	90	5545	6509	7537	8627	9776	10980	12240	13550	1552	1840	3.87 3.65
						95	-	6092	7069	8104	9193	10340	11530	12770			
						100	-	5676	6603	7582	8612	9691	10820	11990			
						105	-	-	6138	7063	8034	9050	10110	11210			
						110	-	-	-	6547	7460	8413	9404	10430			
	LJJM0200	WH	N Q	114N6132 114N6133	NTZ068	90	7671	8785	9994	11300	12700	14190	15770	17430	2234	2588	4.1 3.91
						95	-	8211	9358	10600	11930	13350	14850	16430			
						100	-	7661	8746	9920	11180	12530	13950	15460			
						105	-	-	8159	9267	10460	11730	13090	14510			
						110	-	-	-	8638	9761	10960	12240	13590			
	LNJM0400	WH WL	Q Q	114N6134 114N6184	LLZ013	90	13650	15330	17130	19030	21050	23190	25440	27810	3405	3672	3.81
						95	-	14750	16460	18280	20200	22230	24370	26610			
						100	-	-	15780	17510	19330	21250	23270	25390			
						105	-	-	-	16720	18440	20250	22160	24150			
						110	-	-	-	-	17530	19230	21020	22880			
	LNJM0500	WH	Q	114N6136 114N6186	LLZ015	90	16480	18500	20670	23000	25500	28160	30980	33960	4082	4462	3.77
						95	-	17780	19850	22070	24440	26970	29650	32480			
						100	-	-	19010	21120	23370	25760	28300	30980			
						105	-	-	-	20150	22280	24540	26930	29460			
						110	-	-	-	-	21160	23290	25540	27920			
	LNJM0600	WH	Q	114N6138 114N6188	LLZ018	90	19340	21670	24170	26840	29690	32710	35890	39240	5064	5513	3.53
						95	-	20810	23190	25730	28440	31300	34320	37490			
						100	-	-	22200	24600	27160	29870	32720	35720			
						105	-	-	-	23450	25860	28410	31100	33920			
						115	-	-	-	-	24540	26930	29450	32100			
Two fan	LRJM0800	WH WL	Q Q	114N6140 114N6190	LLZ024	90	24780	27840	31150	34720	38560	42650	47010	51640	5852	6360	3.76
						95	-	26780	29940	33350	37000	40890	45040	49440			
						100	-	-	28710	31950	35410	39110	43040	47210			
						105	-	-	-	30510	33800	37300	41020	44960			
						110	-	-	-	-	32150	35450	38960	42670			
		WH WL	R R	114N6141 114N6191	LLZ024	90	24600	27620	30880	34380	38130	42140	46070	50120	5644	6163	3.86
						95	-	26560	29670	33000	36580	40380	44320	48320			
						100	-	-	28430	31600	34990	38600	42490	46490			
						110	-	-	-	-	31730	34940	38420	41960			
						115	-	-	-	-	-	33060	36690	40360			

Test condition

Return gas temperature 40°F
Subcooling 5°F

Electrical code

N: Compressor & fan(s) 230V, 1 ph, 60 Hz
Q: Compressor 208-230V, 3ph, 60 Hz & Fan(s) 230V, 1ph, 60 Hz
R: Compressor 420-460V, 3ph, 60 Hz & Fan(s) 460V, 1ph, 60Hz

Version

WH: BX, Receiver, Dual pressure control, Fan speed controller or Fan cycling, Defrost Timer, Outdoor enclosure, Suction Accumulator (LBP)
WL: WH+Low Ambient Kit

HP rating in hundredths of HP, ie.: 033=1/3hp, (UCGC0100U:0100=1hp)
Power consumption referred at 90°F ambient temperature
Performance data is based on fan full speed

All Optyma Slim Condensing units are UL Listed

Model no	Condenser coil			Con- denser fan	Receiver volume [Lbs]	Dimensions (in) ⁽¹⁾						Weight (lbs)		MCA (A)	Wiring diagram code ⁽²⁾
	Type	Air flow [CFM]	Int. volume [lbs]	Fan blade Ø (in)		Figure	Height H (in)	Width W (in)	Depth D (in)	Suction line	Liquid line	Gross	Net		
LJJM0150	D8	1410	0.9	14	6.5	1	19.5	43.5	13.4	5/8"	3/8"	187	167	12.8 10	119-9800 119-9801
LJJM0200	D8	1410	0.9	14	6.5	1	19.5	43.5	13.4	5/8"	3/8"	187	167	19.8 14.2	119-9800 119-9801
LNJM0400	J8	3590	2.8	18	17.5	1	28.2	47.4	16.5	7/8"	1/2"	295	266	24.3	119-9807 119-9808
LNJM0500	J8	3590	2.8	18	17.5	1	28.2	47.4	16.5	7/8"	1/2"	295	266	25.1	119-9807 119-9808
LNJM0600	J8	3590	2.8	18	17.5	1	28.2	47.4	16.5	7/8"	1/2"	295	266	28.9	119-9807 119-9808
LRJM0800	N8	5026	3.7	18	22	2	28.8	49.4	31.5	1 1/8"	1/2"	442	409	35.9	119-9807 119-9808
		5180												40	119-9810 119-9811

⁽¹⁾ Dimensions (in) available on page 83

⁽²⁾ Dimensions (in) available on page 77
For spare parts, see pages 74

Fan	Model no	Version	Electrical code	Code no	Compressor model	Amb. Temp.	Capacity range in (btu/hr) at evaporating temperature						Power consumption [W] at evap. Temp. -20 °F	Power consumption [W] at evap. Temp. -10 °F	AWEF*
						°F	-25	-20	-15	-10	-5	0			
Single fan	LJJM0150	WH	N Q	114N6130 114N6131	NTZ048	90	-	6103	7084	8152	9300	10520	1569	1847	3.71 3.7
						95	-	-	6653	7663	8750	9906			
						100	-	-	-	7174	8199	9290			
						110	-	-	-	-	7098	8058			
						115	-	-	-	-	-	7445			
	LJJM0200	WH	N Q	114N6132 114N6133	NTZ068	90	-	8460	9798	11200	12640	14120	2341	2668	3.29 3.58
						95	-	-	9220	10550	11920	13320			
						100	-	-	-	9905	11200	12520			
						110	-	-	-	-	9758	10920			
						115	-	-	-	-	-	10120			
	LNJM0400	WH	Q	114N6134	LLZ013	90	-	13370	15000	16750	18620	20620	3426	3736	3.52
						95	-	-	14400	16080	17870	19780			
						100	-	-	-	15400	17110	18940			
						110	-	-	-	-	15550	17200			
						115	-	-	-	-	-	16320			
	LNJM0500	WH	Q	114N6136	LLZ015	90	-	16540	18510	20630	22900	25320	4070	4464	3.67
						95	-	-	17760	19790	21960	24290			
						100	-	-	-	18940	21020	23240			
						110	-	-	-	-	19090	21100			
						115	-	-	-	-	-	20020			
	LNJM0600	WH	Q	114N6138	LLZ018	90	-	19180	21420	23820	26370	29090	5069	5572	3.33
						95	-	-	20570	22860	25300	27890			
						100	-	-	-	21880	24200	26670			
						110	-	-	-	-	21960	24170			
						115	-	-	-	-	-	22900			
Two fan	LRJM0800	WH	Q	114N6140	LLZ024	90	-	24510	27440	30580	33940	37510	5893	6499	3.48
						95	-	-	26400	29400	32610	36020			
						100	-	-	-	28200	31250	34490			
						110	-	-	-	-	28430	31340			
						115	-	-	-	-	-	29710			
		WH	R	114N6141	LLZ024	90	-	24300	27180	30260	33540	37030	8722	8386	3.58
						95	-	-	26140	29070	32200	35520			
						100	-	-	-	27860	30830	33980			
						110	-	-	-	-	27980	30790			
						115	-	-	-	-	-	29140			

Test condition

Return gas temperature 40°F
Subcooling 5°F

Electrical code

N: Compressor & fan(s) 230V, 1 ph, 60 Hz
Q: Compressor 208-230V, 3ph, 60 Hz & Fan(s) 230V, 1ph, 60 Hz
R: Compressor 420-460V, 3ph, 60 Hz & Fan(s) 460V, 1ph, 60Hz

Version

WH: Electrical box, Receiver, Dual pressure control, Fan speed controller or Fan cycling, Defrost Timer, Outdoor enclosure, Suction Accumulator (LBP)

HP rating in hundredths of HP, i.e.: 033=1/3hp, (UCGC0100U:0100=1hp)
Power consumption referred at 90°F ambient temperature
Performance data is based on fan full speed

All Optyma Slim Condensing units are UL Listed

Model no	Condenser coil			Con- denser fan	Receiver volume [Lbs]	Dimensions (in) ⁽¹⁾						Weight (lbs)		MCA (A)	Wiring diagram code ⁽²⁾
	Type	Air flow [CFM]	Int. volume [lbs]	Fan blade Ø (in)		Figure	Height H (in)	Width W (in)	Depth D (in)	Suction line	Liquid line	Gross	Net		
LJJM0150	D8	1410	0.9	14	6.5	1	19.5	43.5	13.4	5/8"	3/8"	187	167	12.8 10	119-9800 119-9801
LJJM0200	D8	1410	0.9	14	6.5	1	19.5	43.5	13.4	5/8"	3/8"	187	167	19.8 14.2	119-9800 119-9801
LNJM0400	J8	3700	2.8	18	17.5	1	28.2	47.4	16.5	7/8"	1/2"	295	266	24.3	119-9807
LNJM0500	J8	3590	2.8	18	17.5	1	28.2	47.4	16.5	7/8"	1/2"	295	266	25.1	119-9807
LNJM0600	J8	3590	2.8	18	17.5	1	28.2	47.4	16.5	7/8"	1/2"	295	266	28.9	119-9807
LRJM0800	N8	5026 5180	3.7	18	22	2	28.8	49.4	31.5	1 1/8"	1/2"	442	409	35.9 40	119-9807 119-9810

⁽¹⁾ Dimensions (in) available on page 83

⁽²⁾ Dimensions (in) available on page 77

For spare parts, see pages 74

Fan	Model no	Version	Electrical code	Code no	Compressor model	Amb. Temp.	Capacity range in (btu/hr) at evaporating temperature								"Power consumption [W] at evap. Temp. -20 °F"	"Power consumption [W] at evap. Temp. -10 °F"	AWEF*
						°F	-25	-20	-15	-10	-5	0	5	10			
Single fan	LJJM0150	WH	N Q	114N6130 114N6131	NTZ048	90	3188	4054	5029	6121	7333	8674	10144	11751	996	1289	3.15
						95	-	3689	4627	5678	6848	8145	9571	11130			
						100	-	3320	4217	5227	6353	7606	8984	10496			
						105	-	-	3801	4767	5848	7049	8380	9837			
						110	-	-	-	4303	5333	6486	7763	9168			
	LJJM0200	WH	N Q	114N6132 114N6133	NTZ068	90	5309	6473	7780	9254	10912	12775	14867	17207	1612	1997	3.15
						95	-	6033	7288	8698	10284	12069	14068	16307			
						100	-	5596	6797	8145	9660	11359	13270	15409			
						105	-	-	6302	7589	9032	10656	12475	14512			
						110	-	-	-	7036	8411	9953	11683	13625			
	LNJM0400	WH WL	Q Q	114N6134 114N6184	LLZ013	90	9609	10932	12396	14014	15798	17764	19920	22285	2713	2876	3.15
						95	-	10578	11980	13536	15249	17136	19207	21479			
						100	-	10213	11560	13048	14689	16498	18487	20667			
						105	-	-	11134	12557	14126	15853	17757	19842			
						110	-	-	-	12059	13553	15201	17016	19009			
	LNJM0500	WH WL	Q Q	114N6136 114N6186	LLZ015	90	11782	13386	15181	17177	19398	21862	24588	27594	3199	3379	3.15
						95	-	12956	14665	16566	18681	21029	23626	26492			
						100	-	12519	14140	15948	17955	20183	22650	25376			
						105	-	-	13608	15317	17218	19326	21664	24250			
						110	-	-	-	14679	16470	18463	20671	23114			
	LNJM0600	WH WL	Q Q	114N6138 114N6188	LLZ018	90	14338	16290	18460	20872	23544	26499	29754	33337	3741	3987	3.15
						95	-	15788	17866	20173	22728	25557	28676	32108			
						100	-	15276	17265	19466	21909	24608	27591	30870			
						105	-	-	16651	18750	21073	23646	26488	29617			
						115	-	-	-	18020	20227	22674	25373	28351			
Two fan	LRJM0800	WH WL	Q R Q R	114N6140 114N6141 114N6190 114N6191	LLZ024	90	17313	19620	22175	24997	28116	31549	35316	39444	4556	4885	3.15
						95	-	19030	21486	24195	27188	30484	34104	38079			
						100	-	18432	20787	23383	26253	29409	32879	36681			
						105	-	-	20070	22558	25298	28317	31637	35282			
						110	-	-	-	21715	24329	27212	30382	33862			

Test condition

 Return gas temperature 40°F
 Subcooling 5°F

Electrical code
N: Compressor & fan(s) 230V, 1 ph, 60 Hz
Q: Compressor 208-230V, 3ph, 60 Hz & Fan(s) 230V, 1ph, 60 Hz
R: Compressor 420-460V, 3ph, 60 Hz & Fan(s) 460V, 1ph, 60Hz

Version
WH: Electrical box, Receiver, Dual pressure control, Fan speed controller or Fan cycling, Defrost Timer, Outdoor enclosure, Suction Accumulator (LBP)

HP rating in hundredths of HP, ie.: 033=1/3hp, (UCGC0100U:0100=1hp)

Power consumption referred at 90°F ambient temperature

Performance data is based on fan full speed

All Optyma Slim Condensing units are UL Listed

Model no	Condenser coil			Con- denser fan	Re- ceiver volume [Lbs]	Dimensions (in) ⁽¹⁾						Weight (lbs)		MCA (A)	Wiring diagram code ⁽²⁾
	Type	Air flow [CFM]	Int. volume [lbs]	Fan blade Ø (in)		Figure	Height H (in)	Width W (in)	Depth D (in)	Suction line	Liquid line	Gross	Net		
LJJM0150	D8	1410	0.9	14	6.5	1	19.5	43.5	13.4	5/8"	3/8"	187	167	12.8 10	119-9800 119-9801
LJJM0200	D8	1410	0.9	14	6.5	1	19.5	43.5	13.4	5/8"	3/8"	187	167	19.8 14.2	119-9800 119-9801
LNJM0400	J8	3590	2.8	18	17.5	1	28.2	47.4	16.5	7/8"	1/2"	295	266	24.3	119-9807 119-9808
LNJM0500	J8	3590	2.8	18	17.5	1	28.2	47.4	16.5	7/8"	1/2"	295	266	25.1	119-9807 119-9808
LNJM0600	J8	3590	2.8	18	17.5	1	28.2	47.4	16.5	7/8"	1/2"	295	266	28.9	119-9807 119-9808
LRJM0800	N8	5026 5180	3.7	18	22	2	28.8	49.4	31.5	1 1/8"	1/2"	442	409	35.9	119-9807 119-9810
														40	119-9808 119-9811

⁽¹⁾ Dimensions (in) available on page 83

⁽²⁾ Dimensions (in) available on page 77

For spare parts, see pages 74

Spare Parts

Unit	N	Q	R	Compressor					Contactor	Service valve			Oil
				Model no	Code number	Start capacitor	Run capacitor	Start relay		Suction	Dis-charge	Receiver valve	
HJJM0150	114N6100 114N6150	114N6101 114N6151		MTZ18-1 MTZ18-3	MTZ18-1VI MTZ18-3VI	N: 119-4654	N: 119-5617	N: 119-5616	119-5640	119-4551	119-4545	119-4544	120Z0638
HNJM0200	114N6102 114N6152	114N6103 114N6153		MLZ15T1 MLZ15T2	121L8987 121L9011	N: 119-8775	N: 119-5618	N: 119-8780	119-5640	119-4548	119-4545	119-4545	120Z0648
HNJM0250	114N6104 114N6154	114N6105 114N6155		MLZ19T1 MLZ19T2	121L8991 121L9015	N: 119-8775	N: 119-5618	N: 119-8780	119-5640	119-4548	119-4545	119-4545	120Z0648
HNJM0300	114N6106 114N6156	114N6107 114N6157		MLZ21T1 MLZ21T2	121L8995 121L9019	N: 119-8775	N: 119-5618	N: 119-8780	119-5640	119-4548	119-4545	119-4545	120Z0648
HNJM0350	114N6108 114N6158	114N6109 114N6159		MLZ26T1 MLZ26T2	121L8999 121L9023	N: 119-4654	N: 119-8777	N: 119-8781	119-5639	119-4548	119-4551	119-4545	120Z0648
HNJM0400	114N6110 114N6160	114N6111 114N6161		MLZ30T1 MLZ30T2	121L9003 121L9027	N: 119-8776	N: 119-8778	N: 119-8781	N: 119-5639 Q: 119-5640	119-4548	119-4551	119-4545	120Z0648
HRJM0500	114N6112 114N6162	114N6113 114N6163		MLZ38T1 MLZ38T2	121L9007 121L9031	N: 119-4654	N: 119-8779	N: 119-8782	N: 119-4652 Q: 119-5639	119-4548	119-4551	119-4545	120Z0648
HRJM0600	----	114N6114 114N6164	114N6115	MLZ45T2 MLZ45T4	121L9035 121L8978	----	----	----	Q: 119-5639 R: 119-5640	119-4548	119-4551	119-4545	120Z0648
HRJM0700	----	114N6116 114N6166	114N6117	MLZ48T2 MLZ48T4	121L9039 121L8980	----	----	----	Q: 119-5639 R: 119-5640	119-4548	119-4546	119-4545	120Z0648
HRJM0750	----	114N6118 114N6168	114N6119	MLZ58T2 MLZ58T4	121L9043 121L8982	----	----	----	Q: 119-4652 R: 119-5639	119-4550	119-4548	119-4551	120Z0648
HRJM1000	----	114N6120 114N6170	114N6121	MLZ76T2 MLZ76T4	121L9051 121L8984	----	----	----	Q: 119-4652 R: 119-5639	119-4550	119-4548	119-4551	120Z0648

Unit	Crankcase Heater	Acoustic hood	Condenser kit	Defrost Timer	Dual pressure switch	Fan kit	Fan speed controller	Filter drier	Receiver	Sight glass	Sequence phase relay	Transformer
HJJM0150	120Z0459	120Z0575	119-4536	119-9438	060-5253	119-8772E	061H3246	023Z5040	119-4531	014L0022	----	----
HNJM0200	120Z5040	120Z5083	119-4537	119-9438	060-5253	119-8773E	061H3246	023Z5041	119-4532	014L0022	119-4567	----
HNJM0250	120Z5040	120Z5083	119-4537	119-9438	060-5253	119-8773E	061H3246	023Z5041	119-4532	014L0025	119-4567	----
HNJM0300	120Z5040	120Z5083	119-4537	119-9438	060-5253	119-8773E	061H3246	023Z5041	119-4532	014L0025	119-4567	----
HNJM0350	120Z5040	120Z5083	119-4538	119-9438	060-5253	119-8773E	061H3246	023Z5044	119-4533	014L0025	119-4567	----
HNJM0400	120Z5040	120Z5084	119-4538	119-9438	060-5253	119-8773E	061H3246	023Z5044	119-4533	014L0025	119-4567	----
HRJM0500	120Z5040	120Z5084	119-4539	119-9438	060-5253	119-8773E	061H3246	023Z5044	119-4534	014L0025	119-4567	----
HRJM0600	Q:120Z5040 R:120Z5041	120Z5084	119-4539	119-9438	060-5253	Q: 119-8773E R: 119-9660	061H3246	023Z5044	119-4534	014L0025	119-4567	119-8687
HRJM0700	Q:120Z5040 R:120Z5041	120Z5084	119-4539	119-9438	060-5253	Q: 119-8773E R: 119-9660	061H3246	023Z5044	119-4534	014L0025	119-4567	119-8687
HRJM0750	Q:120Z5040 R:120Z5041	120Z5085	119-9652	119-9438	060-5253	Q: 119-9650 R: 119-9651	061H3246	023Z5045	119-4535	014L0026	119-4567	119-8687
HRJM1000	Q:120Z5040 R:120Z5041	120Z5085	119-9652	119-9438	060-5253	Q: 119-9650 R: 119-9651	061H3246	023Z5045	119-4535	014L0026	119-4567	119-8687

Spare Parts

Unit	N	Q	R	Compressor					Contactor	Service valve			Oil
				Model no	Code number	Start capacitor	Run capacitor	Start relay		Suction	Dis-charge	Receiver valve	
LJYM0150	114N6130	114N6131	----	NTZ048-1 NTZ048-3	N: 120F0293 Q: 120F0279	N:119-4654	N:119-5617	N:119-5616	119-5640	119-4546	119-4545	119-4544	120Z0638
LJYM0200	114N6132	114N6133	----	NTZ068-1 NTZ068-3	N: 120F0294 Q: 120F0280	N:119-5636	N:119-8783	N:119-5616	119-5640	119-4546	119-4545	119-4544	120Z0638
LNJM0400	----	114N6134 114N6184	----	LLZ013T2	121L9053	----	----	----	119-5640	119-4548	119-4551	119-4545	120Z0648
LNJM0500	----	114N6136 114N6186	----	LLZ015T2	121L9055	----	----	----	119-5640	119-4548	119-4551	119-4545	120Z0648
LNJM0600	----	114N6138	----	LLZ018T2	121L9057	----	----	----	119-5639	119-4548	119-4551	119-4545	120Z0648
LRJM0800	----	114N6140 114N6190	114N6141 114N6191	LLZ024T2 LLZ024T4	Q: 121L9059 R: 121L8461	----	----	----	Q: 119-5639 R: 119-5639	119-4550	119-4546	119-4551	120Z0648

Unit	Filter drier	Receiver	Sight glass	Liquid Injection Valve	Liquid Injection Coil	Sequence phase relay	Transformer
LJYM0150	023Z5040	119-4531	014L0022	----	----	----	----
LJYM0200	023Z5040	119-4531	014L0022	----	----	----	----
LNJM0400	023Z5044	119-4533	014L0025	068F5211	018F4135	119-4567	----
LNJM0500	023Z5044	119-4533	014L0025	068F5211	018F4135	119-4567	----
LNJM0600	023Z5045	119-4533	014L0025	068F5211	018F4135	119-4567	----
LRJM0800	023Z5045	119-4535	014L0025	068F5212	018F4135	119-4567	119-8687

Unit	Crankcase heater	Acoustic hood	Condenser kit	Defrost Timer	Dual pressure switch	Fan kit	Fan speed controller
LJYM0150	120Z0459	120Z0575	119-4536	119-9438	060-5253	119-8772E	061H3246
LJYM0200	120Z0459	120Z0575	119-4536	119-9438	060-5253	119-8773E	061H3246
LNJM0400	120Z5040	120Z5052	119-4538	119-9438	060-5253	119-8773E	061H3246
LNJM0500	120Z5040	120Z5052	119-4538	119-9438	060-5253	119-8773E	061H3246
LNJM0600	120Z5040	120Z5052	119-4538	119-9438	060-5253	119-8773E	061H3246
LRJM0800	Q: 120Z5040 R: 120Z5041	120Z5053 120Z5053	119-4539	119-9438	060-5253	Q: 119-8773E R: 119-9660	061H3246


**Spare Parts WK Low Ambient
Kit MBP**

Unit	N	Q	R	Crankcase Heater Receiver	KPU Pressure switch (High)	KPU Pressure switch (Low)	Valve Head Pressure	Timer	Thermostat
HJMJ0150	114N6150	114N6151	----	120Z0389	060-5243	060-5231	119-9439	119-9437	119-9436
HNJM0200	114N6152	114N6153	----	120Z5040	060-5243	060-5231	119-9439	119-9437	119-9436
HNJM0250	114N6154	114N6155	----	120Z5040	060-5243	060-5231	119-9439	119-9437	119-9436
HNJM0300	114N6156	114N6157	----	120Z5040	060-5243	060-5231	119-9439	119-9437	119-9436
HNJM0350	114N6158	114N6159	----	120Z5011	060-5243	060-5231	119-9440	119-9437	119-9436
HNJM0400	114N6160	114N6161	----	120Z5011	060-5243	060-5231	119-9440	119-9437	119-9436
HRJM0500	114N6162	114N6163	----	120Z0138	060-5243	060-5231	119-9440	119-9437	119-9436
HRJM0600	----	114N6164	----	120Z0138	060-5243	060-5231	119-9440	119-9437	119-9436
HRJM0700	----	114N6166	----	120Z0138	060-5243	060-5231	119-9440	119-9437	119-9436
HRJM0750	----	114N6168	----	120Z0138	060-5243	060-5231	119-9441	119-9437	119-9436
HRJM1000	----	114N6170	----	120Z0138	060-5243	060-5231	119-9441	119-9437	119-9436


**Spare Parts WL Low Ambient
Kit LBP**

Unit	N	Q	R	Crankcase Heater Receiver	"KPU Pressure switch (High)"	"KPU Pressure switch (Low)"	Valve Head Pressure	Timer	Thermostat
LNJM0400	----	114N6184	----	120Z5011	060-5243	060-5231	119-9439	119-9437	119-9436
LNJM0500	----	114N6186	----	120Z5011	060-5243	060-5231	119-9439	119-9437	119-9436
LNJM0600	----	114N6188	----	120Z5011	060-5243	060-5231	119-9439	119-9437	119-9436
LRJM0800	----	114N6190	----	120Z0138	060-5243	060-5231	119-9440	119-9437	119-9436
LRJM0800	----	----	114N6191	119-9444	060-5243	060-5231	119-9440	119-9437	119-9436


Wiring Diagram 119-9800




Wiring Diagram 119-9801




Wiring Diagram 119-9802




Wiring Diagram 119-9803




Wiring Diagram 119-9804




Wiring Diagram 119-9805




Wiring Diagram 119-9808



Wiring Diagram 119-9809



Wiring Diagram 119-9810



Wiring Diagram 119-9811




Figure 1





Figure 2



Danfoss Commercial Compressors

is a worldwide manufacturer of compressors and condensing units for refrigeration and HVAC applications. With a wide range of high quality and innovative products we help your company to find the best possible energy efficient solution that respects the environment and reduces total life cycle costs.

We have 40 years of experience within the development of hermetic compressors which has brought us amongst the global leaders in our business, and positioned us as distinct variable speed technology specialists. Today we operate from engineering and manufacturing facilities spanning across three continents.



Danfoss Scrolls



Danfoss Inverter Scrolls



Danfoss Turbocor Compressors



Danfoss Light Commercial Refrigeration Compressors



Danfoss Maneurop Reciprocating Compressors



Danfoss Optyma Condensing Units

Our products can be found in a variety of applications such as rooftops, chillers, residential air conditioners, heatpumps, coldrooms, supermarkets, milk tank cooling and industrial cooling processes.

Danfoss A/S

Climate Solutions • danfoss.us • +1 888 326 3677 • baltimore@danfoss.com

member of:



www.asercom.org

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues descriptions, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the product.

All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.