




Flat Stations

EvoFlat 4.0F

Domestic hot water and direct heating

Description

Danfoss EvoFlat 4.0 station is particularly suitable for multi family buildings with central heat generation or district heating. The innovative unit sets new standard. It consists of functional blocks made of a specially reinforced PPS composite material. This makes the station extremely lightweight and limits internal heat emission. The smooth surface reduces the risks of scaling and clogging.

All components are assembled with newly designed click-fit connections. Compared to conventional substations with pipes and screw connections, this new connection technology does not require retightening during installation and commissioning.

Primary side (DH)

The flat station is equipped with two differential pressure controller and a central strainer. A summer bypass keeps the supply line warm during standstill. This ensures a fast response time for DHW during the summer. The bypass is thermostatically controlled.

Heating (HE)

The flat station supplies the radiator heating circuits with the flow temperature provided by the supply. The differential pressure regulator integrated as standard creates optimal operating conditions for the heating. A zone valve is integrated in the return side. Time dependent temperature control can be carried out using an optional actuator and room thermostat using an optional high-temperature connection set.

Domestic hot water (DHW)

Four sizes of heat exchanger are available to cover all requirements from 37 kW up to 70 kW. The EvoFlat 4.0 M is equipped with an intelligent controller that regulates the supply side flow based on the domestic hot water temperature and the volume of water drawn. The station features an integrated differential pressure controller on the supply side of the domestic hot water heating system. This eliminates the need for hydraulic balancing of the station. If necessary, the station can be expanded with a hot water circulation set.

Features & benefits

- Light weight
- Easy installation, maintenance and operation
- Durable composite material
- Minimum space required for installation
- Minimal heat loss thanks to EPP insulation cover
- Prepared for build-in heat meter
- Prepared for build-in water meter
- Compatible with various heat sources, such as district heating, heat pumps, biomass etc.

Ordering

Product code numbers


Product code numbers standard stations

Flat station	Brazing (HEX) copper	Brazing (HEX) Stainless steel
EvoFlat 4.0 F (HEX size 1)	183B1000	183B1500
EvoFlat 4.0 F (Hex size 2)	183B1001	183B1501
EvoFlat 4.0 F (HEX size 3)	183B1002	183B1502
EvoFlat 4.0 F (HEX size 4)	183B1003	183B1503

Product code numbers stations with water hammer arrestor

Flat station	Brazing (HEX) copper	Brazing (HEX) Stainless steel
EvoFlat 4.0 F WHA (HEX size 1)	183B1012	183B1512
EvoFlat 4.0 F WHA (Hex size 2)	183B1013	183B1513
EvoFlat 4.0 F WHA (HEX size 3)	183B1014	183B1514
EvoFlat 4.0 F WHA (HEX size 4)	183B1015	183B1515

Danfoss offers flat stations where water hammer arrestor is built in from the factory




The water hammer resistor is placed at the domestic hot water supply.



Accessories code numbers

Domestic hot water circulation



If required a set with pump and safety valve (10 bar) can be ordered for easy connection to the flat station. This increases the width of the recess box to at least 690 mm.

Code number	
183B0500	Circulation set EvoFlat 4.0
183B0547	Circulation set EvoFlat 4.0 with insulation shell for circulation pump



White steel cover

If the station is to be installed on a wall and a large recess box is not desired, Danfoss offers a steel cover to conceal the station, allowing it to blend seamlessly with a white wall. The cover is simply pressed into place over the EPP.

Code number	Description
004U8578	White steel cover for station RAL 9016




Recess box

Is made of galvanized sheet steel metal, with frame and door powder-coated on both sides in RAL 9016. Appropriate mounting bolts are provided on the rear wall for quick and easy installation of the flat station and distribution unit. The box is closed all around, open at the bottom, and features mounting feet that are height-adjustable by up to 120 mm. A mounting rail with seven ball valves (supplied loose) is included. The box can be mounted in a wall or on a wall

Reces boxes				
Code number		Wide	Height	Depth
183U6028	Recess box w/mounting rail and loose ball valves	610	910	150
145H4901	Door + frame for Recess box 183U6028			
183U6029	Recess box w/mounting rail and loose ball valves	690	910	150
145H4903	Door + frame for Recess box 183U6029			
183U6033*	Feet set for recess box			
183L5142*	Ball valve set ¾" 7 connections			

*Spare parts

On wall panels for recess boxes				
Code number		Wide	High	Depth
183U6012	On wall panels	610	910	150
183U6014	On wall panels	690	910	150



The distribution units fits on the back plate of the recess boxes but can also be mounted on the wall.

Recess boxes for built-in variants are available in two sizes:

Standard station: Recess box W 610 / H 910 / D 150 mm


Station with DHW circulation

Recess box W 690 / H 910 / D 150 mm

Product details

General data


Circuit diagram



2	DHW plate heat exchanger
4	Differential pressure controller
5	Strainer
7	Ball valve*
9	DHW circulation pump*
12	Safety valve
23	Sensor pocket
24	Fitting piece for energy meter 3/4" x 110 mm
33	Connection DHW circulation38) Hot water controller
40	Summer bypass
52	Zone valve*
52A	TWA Q-NO 230 V for zone valve*
59	Fitting piece for water meter 3/4" x 110 mm

*Optional

Connections:



1	Domestic cold water (DCW) inlet
2	Domestic hot water (DHW) supply
3	Domestic cold water (DCW) outlet
4	Heating source (DH) supply
5	Heating source (DH) return
6	Room heating (HE) supply
7	Room heating (HE) return

Technical data:

Domestic hot water controller	Flow compensated temperature controller
Nominal pressure	PN10
Max. supply temperature (DH)	95 °C
DCW static cold water	P = 1.5 bar min
Brazing (HEX)	Copper or stainless steel
Weight excl. cover	7.7 – 9.3 kg
Insulation	EPP λ 0.039
Electrical supply	230 V AC
Connection sizes	G ¾" internal thread
Pressure nominal primary	10 bar
Pressure nominal secondary	10 bar
Weight without accessories - Type 1 HEX	9.7 kg
Weight without accessories - Type 2 HEX	10.1 kg
Weight without accessories - Type 3 HEX	10.6 kg
Weight without accessories - Type 4 HEX	11.4 kg

Capacity

DHW capacity examples

Unit type HEX	DHW capacity [kW]	Temperature DHS/DHR [°C]	Flow rate primary [l/h]	Pressure loss Primary* [kPa]	Tap load 50 °C [l/min]
Type 1	37	65/15	637	25	13.3
	45	65/17	820	31	16.2
Type 2	45	65/15	770	29	16.2
	50	65/17	896	33	18.0
Type 3	55	65/16	978	39	19.8
	40	53/24	1205	57	14.4
Type 4	60	65/16	1056	38	21.6
	70	65/14	1197	57	25.2
	45	53/23	1310	63	16.2

*Energy meter not included

Heating capacity examples


Heating capacity [kW]	Heating circuit ΔT [°C]	Total pressure loss primary* [kPa]	Flow rate supply [l/h]
10	20	12	430
10	25	8	344
10	30	6	287
10	35	5	246
10	40	4	215
17.5	30	20	500**

*Energy meter and DHW heating not included


**Max. flow

Flowrate type 1 HEX


Pressure loss supply side (primary heating water)




Pressure loss drinking water side (secondary)




Flow rate supply side at different supply temperatures
DHW heating from 10°C to 45°C




Return temperature supply side at different supply temperatures
DHW heating from 10°C to 45°C




Flow rate supply side at different supply temperatures
DHW heating from 10°C to 50°C




Return temperature supply side at different supply temperatures
DHW heating from 10°C to 50°C



Flow rate supply side at different supply temperatures
DHW heating from 10°C to 60°C




Return temperature supply side at different supply temperatures
DHW heating from 10°C to 60°C




Flowrate type 2 HEX


Pressure loss supply side (primary heating water)




Pressure loss drinking water side (secondary)




Flow rate supply side at different supply temperatures
DHW heating from 10°C to 45°C




Return temperature supply side at different supply temperatures
DHW heating from 10°C to 45°C




Flow rate supply side at different supply temperatures
DHW heating from 10°C to 50°C




Return temperature supply side at different supply temperatures
DHW heating from 10°C to 50°C



Flow rate supply side at different supply temperatures
DHW heating from 10°C to 60°C











Return temperature supply side at different supply temperatures
DHW heating from 10°C to 60°C






Flowrate type 3 HEX










Flowrate type 4 HEX

Pressure loss supply side (primary heating water)



Pressure loss drinking water side (secondary)

Flow rate supply side at different supply temperatures
DHW heating from 10°C to 45°CReturn temperature supply side at different supply temperatures
DHW heating from 10°C to 45°CFlow rate supply side at different supply temperatures
DHW heating from 10°C to 50°CReturn temperature supply side at different supply temperatures
DHW heating from 10°C to 50°CFlow rate supply side at different supply temperatures
DHW heating from 10°C to 60°CReturn temperature supply side at different supply temperatures
DHW heating from 10°C to 60°C

Guidelines for water quality

Danfoss has prepared this guideline for the water quality of tap water and district heating water used in plate heat exchangers of stainless steel (EN 1.4404 ~ AISI 316L) brazed with pure Copper (Cu), CoResist (Cn) or Stainless Steel (StS). It is important to point out that the water specification is not a guarantee against corrosion, but it must be considered as a tool to avoid the most critical water applications.

Parameter	Unit	Value or concentration	Plate	Brazing material		
			AISI 316L W. Nr. 1.4404	Cu	CoResist	StS
pH		< 0.6	o	-	-	o
		6.0 – 7.5	+	o/-	o	+
		7.5 – 10.5	+	+	+	+
		> 10.5	+	o	o	+
Conductivity	µS/cm	< 10	+	+	+	+
		10 – 500	+	+	+	+
		500 – 1000	+	o	+	+
		> 1000	+	-	o	+
Free Chlorine	mg/l	< 0.5	+	+	+	+
		0.5 – 1	o	+	+	+
		1 – 5	-	o	o	o
		> 5	-	-	-	-
Ammonia (NH ₃ , NH ₄ ⁺)	mg/l	< 2	+	+	+	+
		2 – 20	+	o	o	+
		> 20	+	-	-	+
Alkalinity (HCO ₃ ⁻)	mg/l	< 60	+	+	+	+
		60 – 300	+	+	+	+
		> 300	+	o	+	+
Sulphate (SO ₄ ²⁻)	mg/l	< 100	+	+	+	+
		100 – 300	+	o/-	o	+
		> 300	+	-	-	+
HCO ₃ ⁻ / SO ₄ ²⁻	mg/l	< 1.5	+	+	+	+
		> 1.5	+	o/-	o	+
Nitrate (NO ₃)	mg/l	< 100	+	+	+	+
		> 100	+	o	+	+
Manganese (Mn)	mg/l	< 0.1	+	+	+	+
		> 0.1	+	o	o	+
Iron (Fe)	mg/l	< 0.2	+	+	+	+
		> 0.2	+	o	+	+
* Hardness ratio [Ca ²⁺ , Mg ²⁺]/[HCO ₃ ⁻]		0 – 0.3	+	-	-	+
		0.3 – 0.5	+	o/-	+	+
		> 0.5	+	+	+	+

+	Good corrosion resistance
o	**Corrosion could happen when more parameters are evaluated with o
o/-	Risk of corrosion
-	Use is not recommended


* Hardness ratio limits defined per experience and internal tests in Danfoss laboratory

** In case of three or more parameters evaluated with o consultancy is needed with Consultant for Corrosion & Microbiology or BU HHE Representative

Recommended Chloride concentration to avoid Stress Corrosion Cracking (SCC) in the stainless-steel plates:

Application temperature	Chloride concentration
at $T \leq 20\text{ }^{\circ}\text{C}$	max 1000 mg/l
at $T \leq 50\text{ }^{\circ}\text{C}$	max 400 mg/l
at $T \leq 80\text{ }^{\circ}\text{C}$	max 200 mg/l
at $T \geq 100\text{ }^{\circ}\text{C}$	max 100 mg/l

Spare part code numbers:



Pos.	Code number	Description
1100	183B0503	Service kit type 1 heat exchanger in copper
1100	183B0504	Service kit type 2 heat exchanger in copper
1100	183B0505	Service kit type 3 heat exchanger in copper
1100	183B0506	Service kit type 4 heat exchanger in copper
1100	183B0507	Service kit type 1 heat exchanger in stainless steel
1100	183B0508	Service kit type 2 heat exchanger in stainless steel
1100	183B0509	Service kit type 3 heat exchanger in stainless steel
1100	183B0510	Service kit type 4 heat exchanger in stainless steel
2000	183B0563	Dp regulator DHW EvoFlat 4.0 SAC
2010	183B0564	Dp regulator HE EvoFlat 4.0 SAC
2030	183B0511	DHW control valve set EvoFlat 4.0 SAC
2040	183B0512	DHW control thermostat set EvoFlat 4.0 SAC
2050	183B0513	Air vent set Danfoss EvoFlat 4.0
2060	183B0514	Flow activator with screws and gaskets
2070	183B0515	Strainer set EvoFlat 4.0
2080		FJVR thermostate
2090	183B0517	Bypass valve thermostatic EvoFlat 4.0 SAC
2130	183B0521	EPP cover set Danfoss EvoFlat 4.0
2170	183B0529	Zone valve set EvoFlat 4.0 SAC
3000	183B0552	Bracket kit for EvoFlat 4.0
3010	183B0553	Plast screw 15x25
3020	183B0554	Block for bypass EvoFlat 4.0
3030	183B0555	Pipe Ø18 - 171 mm
3040	183B0556	Pipe Ø18 - 223 mm
3050	183B0557	Bushing w/nuts 3/4" x 3/4" x 32 mm
3060	183B0558	Fitting piece 3/4" x 110 mm - DHW
3070	183B0559	Pipe Ø18 - 77 mm
3110	183B0565	Fitting piece 3/4" x 110 mm - HE
3120	183B0566	Mounting rail with symbols for EvoFlat 4.0
3130	183B0560	Clips, O-rings & washers for EvoFlat 4.0
4000	082F1601	Zone valve, TWA-Q-NO
	183B0533	Flushing Tool EvoFlat 4.0 HEX

Certificates, declarations and approvals

The list contains all certificates, declarations, and approvals for this product type. Individual code number may have some or all of these approvals, and certain local approvals may not appear on the list.

When you click on the link you will be directed to the latest version of the 'Declaration of Conformity'. Products developed and sold before this date of issue conform to the directives/standards in force at the time of their sale.

Approval type	Title	Certification body	Approval topic
Hygienic Certificate	CARSO 25 ACC LY 385	CARSO - Laboratoire Santé Environnement Hygiène de Lyon	Drinking Water
Manufacturer's Declaration	Danfoss MD DHEUMD101.B	Danfoss	PED, Pressure
Export Control Declaration	Export Control Declaration - Small stations	Danfoss	
Hygienic Certificate	Eurofins Certificate No 014-01	eurofin - eurofin Product Service GmbH	Drinking Water

Tender text

Copper HEX

Design

Danfoss EvoFlat™ flat station for direct heating and hygienic safe hot water provision with a control valve without auxiliary energy in the continuous flow system. Mounted on a heat-insulated base plate including EPP heat insulation hood, for flush or surface mounting.

Domestic hot water (DHW)

Tap water is heated by means of heat exchangers based on the continuous flow principle. The tap water temperature is regulated by the self-acting controller. These controllers ensure outstanding ease of use. The flow-controlled part allows primary and secondary flow through the heat exchanger only during hot water tapping. The flow is blocked immediately after completion of hot water tapping.

The thermostat part in turn regulates the hot water temperature.

Thanks to the fast-acting control valve, limescale deposits and bacteria growth are largely avoided.

The controller in combination with the differential pressure controller ensures a constant DHW temperature even with varying flow temperatures and differential pressures.

The primary line is kept warm by a thermostatically controlled bypass valve (summer bypass).

The flat station is equipped with a connection for domestic hot water circulation. The circulation kit is available as an option.

Heating (HE)

To enable programming of time-dependent temperature control, the station can optionally be equipped with an actuator (TWA Q-NO) for the zone valve integrated in the heating block as well as a room thermostat. The heating circuit is equipped with a second differential pressure controller.

Supply-side equipment

Temperature and pressure regulators, two differential pressure regulators, zone valve, strainer and ventilation

Mark: Danfoss

Fitting piece for heat meter G $\frac{3}{4}$ "x110mm in return flow, sensor holder as direct immersion sensor M10x1mm

Heat exchanger

Sealless stainless steel plate heat exchanger, brazed with stainless steel braze under vacuum to form a compact unit. New Micro Plate™ heat exchanger technology with unique plate structure for more effective heat transfer, lower pressure losses and longer service life. Corrosion resistant design.

Calculation and materials according to AD data sheets. Manufactured in accordance with DIN ISO 9001, CE tested in accordance with Pressure Equipment Directive 97/23/EC (PED).

Mark: Danfoss Type: XB05H

Tap-water-side equipment

Fitting piece for cold water meter G $\frac{3}{4}$ "x110 mm (CW inlet)

Technical data

Heating	
max. capacity [kW]:	17.5
at max. volume flow [m ³ /h]:	0.5 (supply side) / 1.29 (consumer side)

Tap water heating	
max. capacity [kW]:	45 @ VL65°C (Type 1 HEX)
at max. tapping capacity [l/min]:	13.2
max. capacity [kW]:	53 @ VL65°C (Type 2 HEX)
at max. tapping capacity [l/min]:	15.4
max. capacity [kW]:	60 @ VL65°C (Type 3 HEX)
at max. tapping capacity [l/min]:	17.4
max. capacity [kW]:	80 @ VL65°C (Type 4 HEX)
at max. tapping capacity [l/min]:	28.3
Pressure level (tap water side):	PN10
Pressure level (supply side):	PN10
DH network, max. differential pressure [bar]:	4
CW network, min. static pressure [bar]:	1.5
DH network, max. flow temperature [°C]:	95
Nominal connection size:	G¾" (union, 7x)
Electrical connection:	230V AC
Dimensions H/W/D [mm]:	613/530/150
Weight [kg]:	7.7 (Type 1 HEX)
	8.1 (Type 2 HEX)
	8.8 (Type 3 HEX)
	9.3 (Type 4 HEX)

Copper HEX

Design

Danfoss EvoFlat™ flat station for direct heating and hygienic safe hot water provision with a control valve without auxiliary energy in the continuous flow system. Mounted on a heat-insulated base plate including EPP heat insulation hood, for flush or surface mounting.

Domestic hot water (DHW)

Tap water is heated by means of heat exchangers based on the continuous flow principle. The tap water temperature is regulated by the self-acting controller. These controllers ensure outstanding ease of use. The flow-controlled part allows primary and secondary flow through the heat exchanger only during hot water tapping. The flow is blocked immediately after completion of hot water tapping.

The thermostat part in turn regulates the hot water temperature.

Thanks to the fast-acting control valve, limescale deposits and bacteria growth are largely avoided.

The controller in combination with the differential pressure controller ensures a constant DHW temperature even with varying flow temperatures and differential pressures.

The primary line is kept warm by a thermostatically controlled bypass valve (summer bypass).

The flat station is equipped with a connection for domestic hot water circulation. The circulation kit is available as an option.

Heating (HE)

To enable programming of time-dependent temperature control, the station can optionally be equipped with an actuator (TWA Q-NO) for the zone valve integrated in the heating block as well as a room thermo-stat. The heating circuit is equipped with a second differential pressure controller.

Supply-side equipment

Temperature and pressure regulators, two differential pressure regulators, zone valve, strainer and ventilation

Mark: Danfoss

Fitting piece for heat meter G $\frac{3}{4}$ "x110mm in return flow, sensor holder as direct immersion sensor M10x1mm

Heat exchanger

Sealless stainless steel plate heat exchanger, brazed with stainless steel braze under vacuum to form a compact unit. New Micro Plate™ heat exchanger technology with unique plate structure for more effective heat transfer, lower pressure losses and longer service life. Corrosion resistant design.

Calculation and materials according to AD data sheets. Manufactured in accordance with DIN ISO 9001, CE tested in accordance with Pressure Equipment Directive 97/23/EC (PED).

Mark: Danfoss Type: XB05H


Tap-water-side equipment

Fitting piece for cold water meter G $\frac{3}{4}$ "x110mm (CW inlet)

Heating	
max. capacity [kW]:	17.5
at max. volume flow [m ³ /h]:	0.5 (supply side) / 1.29 (consumer side)


Tap water heating	
max. capacity [kW]:	45 @ VL65°C (Type 1 HEX)
at max. tapping capacity [l/min]:	13.2
max. capacity [kW]:	53 @ VL65°C (Type 2 HEX)
at max. tapping capacity [l/min]:	15.4
max. capacity [kW]:	60 @ VL65°C (Type 3 HEX)
at max. tapping capacity [l/min]:	17.4
max. capacity [kW]:	80 @ VL65°C (Type 4 HEX)
at max. tapping capacity [l/min]:	28.3
Pressure level (tap water side):	PN10
Pressure level (supply side):	PN10
DH network, max. differential pressure [bar]:	4
CW network, min. static pressure [bar]:	1.5
DH network, max. flow temperature [°C]:	95
Nominal connection size:	G ³ / ₄ " (union, 7x)
Electrical connection:	230V AC
Dimensions H/W/D [mm]:	613/530/150
Weight [kg]:	7.7 (Type 1 HEX)
	8.1 (Type 2 HEX)
	8.8 (Type 3 HEX)
	9.3 (Type 4 HEX)

Other stations in this portfolio




EvoFlat 4.0 M

Flat station for domestic hot water and floor heating.



EvoFlat 4.0 W

Flat station for domestic hot water.



EvoFlat 4.0 Four pipe

Flat station for domestic hot water and floor heating.
Especially made for heat pumps.

Contact details

Online support

Danfoss offers a wide range of support along with our products, including digital information, software, mobile apps and expert guidance. See the possibilities below.



The Danfoss Design center

Discover the Design Center, our advanced digital platform that streamlines product selection. With integrated tools and enhanced type pages, it's simpler than ever to access product information and documentation, and to select the right products. Check the availability of Danfoss products at partner locations and enjoy seamless transitions from selection to purchase with our basket-to-basket functionality. Whether you're buying from our distributors or directly from the Product Store, the Design Center simplifies your experience. Learn more at: designcenter.danfoss.com.



The Danfoss product store

The Danfoss Product Store is a one-stop shop available 24/7 for our customers, no matter where you are in the world or what area of industry you work in. Browse our catalog, check product details and documentation, view your prices and product availability, and quickly finalize your purchase. Start browsing at: store.danfoss.com.



Danfoss Partner Portal/Product Data tool

Designed to support you with easy access to product data extracts, essential resources, tools, and information. The Partner Portal provides a centralized hub for product documentation, training materials, marketing assets, and technical support, ensuring you have everything you need to succeed and grow your business with Danfoss. The Partner Portal is available 24/7 at: partner.danfoss.com and is ready to support your business.



Find technical documentation

Find technical documentation you need to get your project up running. Get direct access to our official collection of data sheets, certificates and declarations, manuals and guides, 3D models and drawings, case stories, brochures, and much more. Start searching now at: documentation.danfoss.com.



Danfoss Learning

Danfoss Learning is a free online learning platform. It features courses and materials specifically designed to help engineers, installers, service technicians, and wholesalers better understand the products, applications industry topics, and trends that will help you do your job better. Find your local Danfoss website here: learning.danfoss.com.



Get local information and support

Local Danfoss websites are the main sources for help and information about our company and products. Find product availability, get the latest regional news, or connect with a nearby expert - all in your own language. Find your local Danfoss website here: danfoss.com.

Danfoss A/S

Climate Solutions . danfoss.com . +45 7488 2222

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues description, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the products. All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.
