

European Catalogue

Optyma™ Bare condensing units

R290, R452A, R134a/R513A, R448A, R449A, R407A, R407C, R407F, R404A/R507



Danfoss Optyma™ bare condensing units	4
Optyma™ Range and feature overview	5
Performance data	7
Optyma™ Light Commercial R290 LBP	7
Optyma™ Light Commercial R452A LBP	8
Optyma™ Commercial R452A LBP	9
Optyma™ Light Commercial R404A/R507 LBP	11
Optyma™ Commercial R404A/R507 LBP	13
Optyma™ Light Commercial R290 MBP	15
Optyma™ Light Commercial R134a MBP	16
Optyma™ Commercial R134a MBP	18
Optyma™ Light Commercial R513A MBP	21
Optyma™ Commercial R513A MBP	23
Optyma™ Commercial R513A MBP	25
Optyma™ Commercial R448A MBP	26
Optyma™ Commercial R449A MBP	29
Optyma™ Commercial R452A MBP	32
Optyma™ Commercial R407A MBP	35
Optyma™ Commercial R407F MBP	38
Optyma™ Commercial R407C MBP	41
Optyma™ Light Commercial R404A/R507 MBP	44
Optyma™ Commercial R404A/R507 MBP	45
Technical data	48
Optyma™ Light Commercial	48
Optyma™ Commercial	50
Spare parts & accessories	51
Optyma™ Light Commercial LBP - R290	51
Optyma™ Light Commercial LBP - R452A - R404A/R507	52
Optyma™ Light Commercial MBP - R290	53
Optyma™ Light Commercial MBP - R134a, R513A, R404A/R507	54
Optyma™ Commercial LBP	55
Optyma™ Commercial MBP	57
Spare parts & accessories list	59
Optyma™ Light Commercial	59
Optyma™ Commercial	61
Dimensions	62
Optyma™ Light Commercial - Dimensions	62
Optyma™ Commercial - Dimensions	63
Electrical wiring diagrams	66
Optyma™ Light Commercial	66
Optyma™ Commercial	69

Danfoss Optyma™ bare condensing units

Robust, efficient and reliable condensing units, saving on service and maintenance costs and reducing energy consumption.



Benefits for the contractor

- Broad working envelop
- Multiple lower-GWP refrigerants
- Commercial range with microchannel condenser reducing the refrigerant charge and Light commercial range with fine & tube condenser
- Some of the most reliable hermetic reciprocating compressor on the market
- Economical €/kW value



Benefits for the end-user

- Reliable solution
- Low energy consumption under changing working conditions
- Easy & simple condenser maintenance

Optyma™ Light Commercial up to ~1.5 kW

Complete line featuring a higher efficiency and a reduced footprint, available also with R290 making it the perfect choice for a greener installation. This solution is ideal for OEMs or end-users looking for compact products to fit in small systems, and optimal cooling performance and capacity.



Optyma™ Commercial from ~1.5 kW and up

Highly efficient new line with microchannel condenser, multiple lower-GWP refrigerants, and working up to 46°C ambient temperature. Easy to install and service. Quieter by up to 3 dB(A) thanks to 6 pole fan motor instead of 4 pole fan.



MBP and LBP applications



- ✓ Industrial Processes
- ✓ Milk-Cooling
- ✓ Cold rooms in fisheries, florists, etc.
- ✓ Commercial fridge and freezers, display cases, bottle coolers, serving tables

Designation

OP - LCQN 048 MT A14 E

OP = Optyma

1 2 3 4 5 6 7 8

1	Application: M = Medium Back Pressure ; L = Low Back Pressure
2	Platform: C : Air cooled condensing unit with single fan G : Air cooled condensing unit with dual fan
3	Refrigerant: R : R134a, R404A/R507, R407C, R407A, R407F, R448A, R449A, R452A; G : R134a, R513A; H : R404A/R507; Q : R452A, R404A/R507; N : R290
4	Condenser design: C : Fin & Tube condenser, ambient temperature up to 43°C N : Microchannel condenser, ambient temperature up to 46°C
5	Compressor displacement: Example 048 = 48 cm³
6	Reciprocating compressor platform: FR = FR, NF = NF, SC = SC, GS = GS, NX = NX, NB = NBC, NS = NS, NY = NLY, NP = NPT, MP = MPT, MY = MLY, MX = MX, NT = NTZ, MT = MTZ, TL = TL, NL = NL
7	Version: A00, A01, A14, A04, A09, A10, A11. See table Feature overview, for features within each version.
8	Electrical code: G : Compressor 230V/1P/50Hz, fan 230V/1P/50Hz E : Compressor 400V/3P/50Hz, fan 230V/1P/50Hz

Feature overview:

	Light Commercial			Light Commercial R290			Commercial
	A00	A01	A04	A09	A10	A11	A02 & A14
Ambient temperature	Up to 43°C			Up to 43°C			Up to 46°C
Hermetic reciprocating compressor	MPT, MLY, NL, SC, GS, FR, TL, NF			NLY, NBC, NPT, NS, NX			MTZ, NTZ
Unit base	Rails or base plate						Base plate
Condenser type	Fin & Tube (painted)						Microchannel
Fan	AC/EC	AC/EC	AC/EC	EC	EC	EC	AC 6 pole
Bracket & tube for pressostat mounting	-	yes	yes	yes	-	-	-
Dual pressure switch - KP 17 WB	-	-	yes	-	-	-	yes
Schrader valve	-	-	-	yes	yes	yes	-
Wired electrical box	yes	yes	yes	yes	yes	yes	yes
Mini HP/LP pressostat	-	-	-	-	yes	-	-
Power cord	-	-	yes	-	yes	-	-
Receiver	-	yes	yes	-	Combo drier + receiver	-	yes
Net weight in kg	14 chassis: Lighter: 14 Bigger: 44			4 chassis: Lighter: 14 Bigger: 41			5 chassis: Lighter single fan: 53 Bigger single fan: 179 Lighter dual fan: 110 Bigger dual fan: 211
Dimensions in mm (height x width x depth)	14 chassis: Smaller: 205 x 289 x 424 Larger: 350 x 445 x 613			4 chassis: Smaller: 226 x 286 x 513 Larger: 350 x 442 x 480			5 chassis: Smaller single fan: 545 x 630 x 650 Larger single fan: 836.5 x 1200 x 800 Smaller dual fan: 693.5 x 1500 x 870 Larger dual fan: 836.5 x 1500 x 870


Overview by range and refrigerant:

Min / Max cooling capacity (kW)	Light Commercial	Commercial
Medium temperature (MBP)		
R290	0.2 - 1.4	
R448A		2 - 20.5
R449A		2 - 20.5
R134a	0.1 - 1.6	1.3 - 13.1
R513A	0.1 - 1.6	1.3 - 14.0
R452A		2.2 - 20.6
R407A		1.9 - 19.1
R407C		1.8 - 19.1
R407F		2 - 20.1
R404A/507	0.3 - 17	2.2 - 21.7
Low temperature (LBP)		
R290	0.1 - 0.7	
R452A	0.1 - 0.3	0.8 - 6.1
R404A/507	0.1 - 0.9	0.9 - 6.6

Rating conditions EN 13215 (dew point):

MBP: Ambient temp = 32°C, Evap temp = -10°C, Superheat = 10K, Subcooling = 0K

LBP: Ambient temp = 32°C, Evap temp = -35°C, Superheat = 10K, Subcooling = 0K



Optyma™ Light Commercial – up to ~1.5 kW

Specially designed for key commercial applications such as glass door merchandisers, bottle coolers, chilled food or ice cream cabinets. To meet the latest guidelines while satisfying tomorrow's consumer needs, Danfoss compressors use the environmentally friendly R290 propane as a refrigerant.



Faster and safer installation and maintenance

Schrader valve for easy charging of refrigerant, pre-wired e-box, ACB mini pressostat and ATEX class N fan motor for enhanced safety.



Serviceability and compactness

Combo of drier and receiver in one piece making it the ideal fit for compact systems and providing higher serviceability.



R290 natural refrigerant

The major environmental benefits are obtained combining the use of the R290 with the design criteria of highly efficient compressors and EC fan motor.



Universal

Most of units are designed with rail concept allowing easy condensed water evacuation, high airflow, and reduced height to fit display cabinets. Suited for high ambient temperatures thanks to EC fan ATEX class N.



R290 unit



Energy efficient, environmentally friendly and safe hydrocarbons

Hydrocarbons such as propane R290 have excellent thermodynamic properties, and in this respect they are as good as or better than HFC or HCFC refrigerants in most applications. When they are used responsibly and relevant norms are followed, hydrocarbons can be employed in a variety of refrigeration and air conditioning applications. Hydrocarbons can deliver high energy efficiency and have zero Ozone Depletion Potential (ODP) and negligible Global Warming Potential (GWP).



Relevant norms & standards when working with hydrocarbon refrigerants:

ATEX 94/9/EC Directive

Specifies the requirements for equipment intended for use in potentially explosive atmospheres (both electrical and mechanical). Organizations in EU must follow the directive to protect employees from explosion risk in areas with an explosive atmosphere.

Pressure Equipment Directive 97/23/EC (PED)

The directive provides a legislative framework for pressurized equipment and assemblies.

EN378 1-4

EN378 defines "best practice" for design, operation and maintenance. It is a harmonised standard, which ensures that all essential requirements in the PED are fulfilled.

ISO 5149 1-4

The international safety standard, defines "best practices" very similarly to EN378, but without referring to EU law.

IEC 60335: International Standard

Specifies all requirements for small hermetically sealed household appliances (supports the EU Low Voltage Directive (2006/95/EC)). It deals with the safety of electrical appliances for household and similar purposes.

Model	Code	Version	Compressor	Electrical code (1)	Tamb [°C]	Cooling capacity Q [kW] (2)							EcoDesign (3)			
						Te [°C]							Q [kW]	P [kW]	COP	SEPR
						-40°C	-35°C	-30°C	-25°C	-20°C	-15°C	-10°C				
OP-LCNC004	114F0202 114F0203 114F0201	A09 A10 A11	NLY45LAb	G	27	0.095	0.128	0.166	0.209	0.256	0.307	0.363				
					32	0.086	0.116	0.152	0.192	0.236	0.284	0.337	0.124	0.119	1.04	
					38	0.075	0.103	0.134	0.171	0.212	0.257	0.307				
					43	0.067	0.091	0.120	0.154	0.192	0.235	0.282				
OP-LCNC006	114F0205 114F0206 114F0204	A09 A10 A11	NLY60LAb	G	27	0.120	0.163	0.211	0.265	0.323	0.386	0.453				
					32	0.110	0.148	0.193	0.242	0.296	0.356	0.419	0.159	0.149	1.06	
					38	0.097	0.131	0.170	0.215	0.265	0.320	0.379				
					43	0.087	0.116	0.152	0.193	0.239	0.290	0.346				
OP-LCNC008	114F0308 114F0309 114F0307	A09 A10 A11	NLY80LAb	G	27	0.162	0.219	0.284	0.356	0.436	0.523	0.616				
					32	0.148	0.199	0.258	0.325	0.400	0.482	0.571	0.212	0.196	1.08	
					38	0.131	0.175	0.228	0.289	0.357	0.433	0.517				
					43	0.117	0.156	0.203	0.259	0.322	0.393	0.472				
OP-LCNC011	114F0411 114F0412 114F0410	A09 A10 A11	NPY12LAb	G	27	0.258	0.342	0.440	0.550	0.671	0.805	0.950				
					32	0.235	0.312	0.402	0.505	0.619	0.746	0.884	0.333	0.290	1.15	
					38	0.208	0.276	0.357	0.451	0.557	0.675	0.805				
					43	0.185	0.246	0.320	0.406	0.505	0.616	0.740				
OP-LCNC016	114F0414 114F0415 114F0413	A09 A10 A11	NPT16LA	G	27	0.344	0.460	0.590	0.731	0.883	1.045	1.218				
					32	0.315	0.421	0.539	0.670	0.812	0.965	1.129	0.451	0.391	1.15	
					38	0.282	0.374	0.480	0.598	0.728	0.869	1.022				
					43	0.254	0.335	0.430	0.538	0.658	0.790	0.933				
OP-LCNC023	114F0417 114F0418 114F0416	A09 A10 A11	NX23FBa	G	27	0.421	0.570	0.731	0.903	1.086	1.280	1.484				
					32	0.382	0.518	0.667	0.827	0.999	1.182	1.375	0.556	0.538	1.03	
					38	0.335	0.456	0.590	0.737	0.895	1.065	1.245				
					43	0.296	0.405	0.527	0.662	0.809	0.967	1.137				
OP-LCNC034	114F0620 114F0621 114F0619	A09 A10 A11	NS34FB	G	27	0.557	0.784	1.042	1.326	1.636	1.967	2.317				
					32	0.484	0.692	0.931	1.197	1.488	1.801	2.135	0.739	0.626	1.18	
					38	0.399	0.584	0.800	1.043	1.312	1.604	1.916				
					43	0.329	0.495	0.691	0.916	1.166	1.440	1.734				

LBP
(1) E - 400V-3ph-50Hz Compressor & 230V-1ph-50Hz Fan

G - 230V-1ph-50Hz Compressor & 230V-1ph-50Hz Fan

(2) Nominal conditions (EN13215), Evaporating temperatures at dew point, Superheat 10K, Subcooling 0K

(3) Rated conditions (EN13215), Evaporating temperature Midpoint -35°C, Ambient air temperature +32°C, Return Gas Temperature 20°C, Subcooling 0K

COP: Coefficient Of Performance link to EN13215 and ErP (Energy related Products) 2009/125/CE

SEPR: Seasonal Energy Performance Ratio link to EN13215 and ErP (Energy Related Products) 2009/125/CE

Tamb [°C]: Ambient Temperature

Te [°C]: Evaporating Temperature

Q [kW]: Cooling Capacity in Kilo Watt

P [kW]: Power Input in Kilo Watt

Version

A09: Tube for KP pressostat + Wired Ebox + Schrader valve

A10: HP and LP Mini pressure switch + Wired Ebox + Combo Filter drier + Schrader valve

A11: Wired Ebox + Schrader valve


For regular updates and detailed capacities, please refer to **Coolselector®2** software


Model	Code	Version	Compressor	Electrical code (1)	Tamb [°C]	Cooling capacity Q [kW] (2)						EcoDesign (3)			
						Te [°C]						Q [kW]	P [kW]	COP	SEPR
						-40°C	-35°C	-30°C	-25°C	-20°C	-15°C				
OP-LCQC004	114X1221	A01	MLY45LAb	G	27	0.111	0.152	0.197	0.246	0.299	0.357	0.109	0.136	0.80	
					32	0.099	0.135	0.176	0.221	0.271	0.325				
					38	0.084	0.115	0.152	0.192	0.237	0.286				
					43	0.072	0.099	0.131	0.168	0.209	0.254				
OP-LCQC006	114X1337	A01	MLY60LAb	G	27	0.140	0.164	0.205	0.264	0.340	0.436	0.140	0.167	0.84	
					32	0.126	0.152	0.194	0.253	0.331	0.428				
					38	0.110	0.136	0.180	0.240	0.319	0.417				
					43	0.096	0.124	0.167	0.228	0.308	0.406				
OP-LCQC008	114X1341	A01	MLY80LAb	G	27	0.210	0.276	0.346	0.418	0.493	0.571	0.208	0.235	0.88	
					32	0.186	0.246	0.309	0.375	0.444	0.516				
					38	0.158	0.210	0.265	0.323	0.385	0.450				
					43	0.135	0.180	0.228	0.280	0.336	0.395				
OP-LCQC012	114X1449	A01	MLY12LAb	G	27	0.309	0.400	0.500	0.607	0.721	0.843	0.307	0.321	0.96	
					32	0.276	0.359	0.450	0.549	0.656	0.771				
					38	0.237	0.309	0.391	0.480	0.578	0.684				
					43	0.204	0.269	0.342	0.423	0.513	0.611				
OP-LCQC012	114X1569	A01	MPT12LA	G	27	0.368	0.470	0.581	0.698	0.823	0.955	0.365	0.371	0.98	
					32	0.328	0.421	0.521	0.630	0.746	0.869				
					38	0.281	0.361	0.450	0.548	-	-				
					43	0.242	0.312	0.392	0.480	-	-				
OP-LCQC014	114X1573	A01	MPT14LA	G	27	0.415	0.525	0.642	0.765	0.894	1.028	0.415	0.436	0.95	
					32	0.372	0.472	0.578	0.692	0.811	0.936				
					38	0.322	0.409	0.503	0.604	-	-				
					43	0.280	0.357	0.441	0.532	-	-				

LBP

(1) E - 400V-3ph-50Hz Compressor & 230V-1ph-50Hz Fan

G - 230V-1ph-50Hz Compressor & 230V-1ph-50Hz Fan

(2) Nominal conditions (EN13215), Evaporating temperatures at dew point, Superheat 10K, Subcooling 0K

(3) Rated conditions (EN13215), Evaporating temperature Midpoint -35°C, Ambient air temperature +32°C, Return Gas Temperature 20°C, Subcooling 0K

COP: Coefficient Of Performance link to EN13215 and ErP (Energy related Products) 2009/125/CE

SEPR: Seasonal Energy Performance Ratio link to EN13215 and ErP (Energy Related Products) 2009/125/CE

Tamb [°C]: Ambient Temperature

Te [°C]: Evaporating Temperature

Q [kW]: Cooling Capacity in Kilo Watt

P [kW]: Power Input in Kilo Watt

Version

A00: Without valves and receiver for capillary tubes

A01: With receiver, 2 stop valves, brackets and copper pipes for KP

A04: A01 + KP17 WB + FSA-kit + power cord



For regular updates and detailed capacities, please refer to **Coolselector®2** software



Model	Code	Version	Compressor	Electrical code (1)	Tamb [°C]	Cooling capacity Q [kW] (2)						EcoDesign (3)				Sound power level dB(A)	Sound pressure level 10 m dB(A)
						Te [°C]						Q [kW]	P [kW]	COP	SEPR		
						-35°C	-30°C	-25°C	-20°C	-15°C	-10°C						
OP-LCQN048	114X5758	A02	NTZ048	E	27	0.990	1.299	1.648	2.031	2.439	2.864	0.977	0.945	1.03		73	42
					32	0.873	1.152	1.467	1.814	2.185	2.571						
					38	0.742	0.985	1.261	1.564	1.889	2.228						
					43	-	0.854	1.097	1.364	1.649	-						
					46	-	-	-	-	-	-						
OP-LCQN048	114X5759	A02	NTZ048	G	27	0.996	1.331	1.709	2.123	2.563	3.019	0.969	0.909	1.07		73	42
					32	0.867	1.174	1.520	1.898	2.300	2.716						
					38	0.723	0.995	1.302	1.637	1.992	2.359						
					43	-	0.854	1.128	1.426	1.741	-						
					46	-	-	-	-	-	-						
OP-LCQN068	114X5761 114X5784	A02 A14	NTZ068	E	27	1.638	2.137	2.683	3.258	3.861	4.479	1.792	1.470	1.22		71	40
					32	1.440	1.893	2.387	2.904	3.458	4.004						
					38	1.212	1.599	2.029	2.495	2.980	3.443						
					43	-	1.373	1.754	2.166	2.590	-						
					46	-	1.240	1.593	1.972	2.361	-						
OP-LCQN068	114X5762 114X5783	A02 A14	NTZ068	G	27	1.666	2.135	2.663	3.245	3.867	4.492	1.815	1.718	1.06		71	40
					32	1.450	1.883	2.369	2.902	3.468	4.028						
					38	1.201	1.590	2.025	2.500	3.000	3.491						
					43	-	1.355	1.748	2.175	2.620	-						
					46	-	1.219	1.587	1.985	2.397	-						
OP-LCQN096	114X5764	A02	NTZ096	E	27	1.977	2.582	3.260	3.994	4.766	5.560	1.942	1.859	1.04		82	51
					32	1.733	2.280	2.895	3.561	4.263	4.983						
					38	1.450	1.927	2.464	3.048	3.664	4.295						
					43	-	1.641	2.114	2.628	3.170	-						
					46	-	-	-	-	-	-						
OP-LGQN096	114X5766 114X5785	A02 A14	NTZ096	E	27	2.296	3.118	4.130	5.345	6.777	8.429	2.430	1.939	1.25	1.77	82	51
					32	2.030	2.790	3.730	4.864	6.205	7.759						
					38	1.710	2.384	3.228	4.256	5.481	6.909						
					43	-	2.045	2.801	3.733	4.852	-						
					46	-	1.843	2.544	3.414	4.468	-						

LBP
(1) E - 400V-3ph-50Hz Compressor & 230V-1ph-50Hz Fan

G - 230V-1ph-50Hz Compressor & 230V-1ph-50Hz Fan

(2) Nominal conditions (EN13215), Evaporating temperatures at dew point, Superheat 10K, Subcooling 0K

(3) Rated conditions (EN13215), Evaporating temperature Midpoint -35°C, Ambient air temperature +32°C, Return Gas Temperature 20°C, Subcooling 0K

COP: Coefficient Of Performance link to EN13215 and ErP (Energy related Products) 2009/125/CE

SEPR: Seasonal Energy Performance Ratio link to EN13215 and ErP (Energy Related Products) 2009/125/CE

Tamb [°C]: Ambient Temperature

Te [°C]: Evaporating Temperature

Q [kW]: Cooling Capacity in Kilo Watt

P [kW]: Power Input in Kilo Watt

Version

A02: Receiver + Stop valves + KP17WB pressure switch + Electrical box

A14: Filter drier + Sight glass + Receiver + Stop valves + KP17WB pressure switch + Electrical box

This table continues on the next page


For regular updates and detailed capacities, please refer to **Coolselector®2** software


Model	Code	Version	Compressor	Electrical code (1)	Tamb [°C]	Cooling capacity Q [kW] (2)						EcoDesign (3)				Sound power level dB(A)	Sound pressure level 10 m dB(A)
						Te [°C]						Q [kW]	P [kW]	COP	SEPR		
						-35°C	-30°C	-25°C	-20°C	-15°C	-10°C						
OP-LCQN108	114X5768 114X5786	A02 A14	NTZ108	E	27	2.865	3.834	4.978	6.313	7.854	9.609	3.053	2.373	1.29	1.79	78	47
					32	2.534	3.441	4.499	5.725	7.136	8.738						
					38	2.115	2.954	3.914	5.015	6.274	7.698						
					43	-	2.533	3.416	4.418	5.556	-						
					46	-	2.273	3.112	4.057	5.125	-						
OP-LGQN108	114X5769	A02	NTZ108	E	27	3.003	3.991	5.173	6.554	8.138	9.923	2.946	2.158	1.37	1.95	78	47
					32	2.662	3.556	4.631	5.894	7.349	8.997						
					38	2.280	3.065	4.013	5.134	6.435	7.919						
					43	-	2.679	3.523	4.527	5.700	-						
					46	-	-	-	-	-	-						
OP-LGQN136	114X5771	A02	NTZ136	E	27	3.703	4.896	6.312	7.953	9.818	11.898	3.643	2.902	1.26	1.69	78	47
					32	3.284	4.364	5.650	7.149	8.859	10.777						
					38	2.814	3.760	4.893	6.221	7.745	9.467						
					43	-	3.284	4.291	5.477	6.847	-						
					46	-	-	-	-	-	-						
OP-LCQN136	114X5772 114X5787	A02 A14	NTZ136	E	27	3.534	4.714	6.084	7.648	9.405	11.350	3.774	2.972	1.27	1.80	78	47
					32	3.108	4.198	5.460	6.898	8.514	10.300						
					38	2.612	3.592	4.722	6.009	7.455	9.055						
					43	-	3.100	4.119	5.279	6.581	-						
					46	-	2.811	3.763	4.846	6.061	-						
OP-LGQN215	114X5774 114X5788	A02 A14	NTZ215	E	27	5.326	7.065	9.119	11.500	14.22	17.260	5.669	4.838	1.17	1.73	86	55
					32	4.707	6.310	8.202	10.400	12.92	15.750						
					38	3.988	5.422	7.117	9.092	11.36	13.930						
					43	-	4.702	6.227	8.009	10.06	-						
					46	-	4.278	5.700	7.363	9.285	-						
OP-LGQN271	114X5776	A02	NTZ271	E	27	7.015	9.190	11.708	14.576	17.793	21.352	6.812	5.818	1.17	1.66	86	55
					32	6.136	8.154	10.487	13.146	16.132	19.444						
					38	5.112	6.940	9.052	11.459	14.169	17.182						
					43	-	5.955	7.881	10.079	12.557	-						
					46	-	-	-	-	-	-						

LBP

(1) **E** - 400V-3ph-50Hz Compressor & 230V-1ph-50Hz Fan

G - 230V-1ph-50Hz Compressor & 230V-1ph-50Hz Fan

(2) Nominal conditions (EN13215), Evaporating temperatures at dew point, Superheat 10K, Subcooling 0K

(3) Rated conditions (EN13215), Evaporating temperature Midpoint -35°C, Ambient air temperature +32°C, Return Gas Temperature 20°C, Subcooling 0K

COP: Coefficient Of Performance link to EN13215 and ErP (Energy related Products) 2009/125/CE

SEPR: Seasonal Energy Performance Ratio link to EN13215 and ErP (Energy Related Products) 2009/125/CE

Tamb [°C]: Ambient Temperature

Te [°C]: Evaporating Temperature

Q [kW]: Cooling Capacity in Kilo Watt

P [kW]: Power Input in Kilo Watt

Version

A02: Receiver + Stop valves + KP17WB pressure switch + Electrical box

A14: Filter drier + Sight glass + Receiver + Stop valves + KP17WB pressure switch + Electrical box



For regular updates and detailed capacities, please refer to **Coolselector®2** software



Model	Code	Version	Compressor	Electrical code (1)	Tamb [°C]	Cooling capacity Q [kW] (2)								EcoDesign (3)			
						Te [°C]								Q [kW]	P [kW]	COP	SEPR
						-45°C	-40°C	-35°C	-30°C	-25°C	-20°C	-15°C	-10°C				
OP-LCHC004	114X1208 114X1209 114X1211	A00 A01 A04	TL4CL	G	27	0.051	0.074	0.101	0.133	0.169	0.211	0.259	0.312	0.105	0.131	0.80	
					32	0.052	0.070	0.093	0.120	0.152	0.190	0.233	0.283				
					38	0.047	0.061	0.079	0.101	0.129	0.162	0.202	0.248				
					43	0.040	0.050	0.065	0.084	0.109	0.139	0.175	0.219				
OP-LCQC004	114X1221	A01	MLY45LAb	G	27	-	-	0.136	0.182	0.233	0.288	0.347	0.409	0.139	0.154	0.89	
					32	-	-	0.120	0.163	0.209	0.259	0.313	0.372				
					38	-	-	0.071	0.139	0.180	0.224	0.273	0.326				
					43	-	-	0.061	0.119	0.155	0.196	0.240	0.289				
OP-LCHC006	114X1216 114X1217 114X1219	A00 A01 A04	FR6CL	G	27	0.080	0.118	0.163	0.216	0.277	0.347	0.427	0.515	0.169	0.212	0.80	
					32	0.076	0.109	0.149	0.196	0.250	0.313	0.384	0.463				
					38	0.068	0.096	0.129	0.169	0.215	0.269	0.330	0.400				
					43	0.059	0.083	0.112	0.146	0.186	0.232	-	-				
OP-LCQC006	114X1337	A01	MLY60LAb	G	27	-	-	0.196	0.256	0.320	0.387	0.458	0.532	0.196	0.217	0.90	
					32	-	-	0.173	0.227	0.285	0.347	0.412	0.481				
					38	-	-	0.146	0.193	0.244	0.298	0.357	0.420				
					43	-	-	0.124	0.165	0.209	0.259	0.312	0.370				
OP-LCHC007	114X1328 114X1329 114X1331	A00 A01 A04	NL7CLX	G	27	0.112	0.157	0.211	0.274	0.345	0.425	0.513	0.607	0.217	0.244	0.89	
					32	0.101	0.142	0.191	0.247	0.312	0.385	0.464	0.550				
					38	0.087	0.122	0.165	0.214	0.271	0.335	0.405	0.481				
					43	0.074	0.105	0.142	0.185	0.236	0.292	0.354	0.422				
OP-LCQC008	114X1341	A01	MLY80LAb	G	27	-	-	0.226	0.299	0.376	0.458	0.543	0.632	0.228	0.257	0.89	
					32	-	-	0.200	0.265	0.335	0.410	0.488	0.571				
					38	-	-	0.169	0.225	0.286	0.352	0.423	0.497				
					43	-	-	0.144	0.193	0.246	0.305	0.368	0.436				
OP-LCHC008	114X1304 114X1301 114X1302	A00 A01 A04	NL8.4CLX	G	27	0.121	0.169	0.227	0.293	0.369	0.452	0.543	0.640	0.233	0.268	0.87	
					32	0.109	0.153	0.204	0.265	0.333	0.408	0.491	0.579				
					38	0.094	0.131	0.176	0.229	0.288	0.354	0.427	0.504				
					43	0.079	0.112	0.151	0.197	0.249	0.308	0.372	0.441				
OP-LCHC012	114X1440 114X1441 114X1443	A00 A01 A04	SC12CLX	G	27	-	0.243	0.333	0.439	0.563	0.704	0.862	1.037	0.318	0.380	0.84	
					32	-	0.198	0.282	0.381	0.496	0.626	0.773	0.936				
					38	-	0.146	0.221	0.311	0.414	0.533	0.666	0.814				
					43	-	-	0.172	0.253	0.347	0.454	0.576	0.711				
OP-LCHC012	114X1444	A00	SC12CLX.2	G	27	0.190	0.260	0.346	0.446	0.563	0.695	0.844	1.009	0.345	0.417	0.83	
					32	0.160	0.226	0.305	0.398	0.506	0.628	0.766	0.919				
					38	-	0.184	0.256	0.339	0.436	0.547	0.672	0.810				
					43	-	-	0.215	0.290	0.378	0.478	0.591	0.718				

LBP
(1) E - 400V-3ph-50Hz Compressor & 230V-1ph-50Hz Fan

G - 230V-1ph-50Hz Compressor & 230V-1ph-50Hz Fan

(2) Nominal conditions (EN13215), Evaporating temperatures at dew point, Superheat 10K, Subcooling 0K

(3) Rated conditions (EN13215), Evaporating temperature Midpoint -35°C, Ambient air temperature +32°C, Return Gas Temperature 20°C, Subcooling 0K

COP: Coefficient Of Performance link to EN13215 and ErP (Energy related Products) 2009/125/CE

SEPR: Seasonal Energy Performance Ratio link to EN13215 and ErP (Energy Related Products) 2009/125/CE

Tamb [°C]: Ambient Temperature

Te [°C]: Evaporating Temperature

Q [kW]: Cooling Capacity in Kilo Watt

P [kW]: Power Input in Kilo Watt

Version

A00: Without valves and receiver for capillary tubes

A01: With receiver, 2 stop valves, brackets and copper pipes for KP

A04: A01 + KP17 WB + FSA-kit + power cord

This table continues on the next page


For regular updates and detailed capacities, please refer to **Coolselector®2** software


Model	Code	Version	Compressor	Electrical code (1)	Tamb [°C]	Cooling capacity Q [kW] (2)								EcoDesign (3)			
						Te [°C]								Q [kW]	P [kW]	COP	SEPR
						-45°C	-40°C	-35°C	-30°C	-25°C	-20°C	-15°C	-10°C				
OP-LCQC012	114X1449	A01	MLY12LAB	G	27	-	-	0.334	0.436	0.548	0.670	0.802	0.943				
					32	-	-	0.297	0.390	0.493	0.606	0.729	0.862	0.336	0.351	0.96	
					38	-	-	0.254	0.335	0.427	0.529	0.642	0.765				
					43	-	-	0.219	0.290	0.372	0.465	0.569	0.683				
OP-LCHC015	114X1548 114X1549 114X1551	A00 A01 A04	SC15CL	G	27	-	-	0.285	0.389	0.507	0.639	0.788	0.951	1.130			
					32	-	-	0.233	0.335	0.449	0.576	0.716	0.870	1.038	0.379	0.468	0.81
					38	-	-	0.265	0.375	0.496	0.627	0.771	0.926				
					43	-	-	-	0.311	0.426	0.551	0.686	0.832				
OP-LCQC012	114X1569	A01	MPT12LA	G	27	-	-	0.398	0.512	0.635	0.769	0.912	1.065				
					32	-	-	0.354	0.456	0.569	0.692	0.825	0.968	0.401	0.405	0.99	
					38	-	-	0.302	0.390	0.490	0.600	0.722	-				
					43	-	-	0.258	0.336	0.425	0.525	-	-				
OP-LCQC014	114X1573	A01	MPT14LA	G	27	-	-	0.448	0.569	0.700	0.840	0.988	1.144				
					32	-	-	0.401	0.511	0.630	0.758	0.896	1.041	0.456	0.478	0.95	
					38	-	-	0.345	0.441	0.546	0.661	0.785	-				
					43	-	-	0.299	0.383	0.477	0.580	-	-				
OP-LCHC018	114X1556 114X1557 114X1559	A00 A01 A04	SC18CLX	G	27	0.260	0.362	0.486	0.632	0.801	0.991	1.203	1.435				
					32	0.215	0.310	0.423	0.557	0.712	0.886	1.082	1.296	0.478	0.501	0.95	
					38	-	0.250	0.351	0.470	0.608	0.764	0.939	1.132				
					43	-	-	0.294	0.400	0.524	0.664	0.822	0.998				
OP-LCHC021	114X1600 114X1601 114X1602	A00 A01 A04	SC21CL	G	27	-	0.397	0.537	0.695	0.868	1.057	1.262	1.484				
					32	-	0.347	0.469	0.608	0.764	0.937	1.127	1.336	0.328	0.354	0.92	
					38	-	0.282	0.383	0.503	0.641	0.797	0.972	1.168				
					43	-	0.230	0.316	0.422	0.546	0.690	0.854	1.040				
OP-LCHC026	114X1673	A01	GS26CLX	G	27	0.390	0.542	0.724	0.934	1.172	1.436	1.725	2.035				
					32	0.324	0.464	0.631	0.824	1.043	1.286	1.553	1.840	0.716	0.754	0.95	
					38	0.249	0.375	0.524	0.697	0.892	1.110	1.350	1.609				
					43	0.192	0.306	0.440	0.594	0.770	0.967	1.184	1.420				
OP-LCHC034	114X1781 114X1783	A01 A04	GS34CLX	G	27	-	0.756	0.998	1.278	1.598	1.956	2.349	2.773				
					32	-	0.663	0.886	1.146	1.441	1.772	2.136	2.531	1.009	1.010	1.00	
					38	-	0.553	0.754	0.987	1.253	1.551	1.880	2.238				
					43	-	0.464	0.645	0.856	1.096	1.366	1.665	1.992				

LBP
(1) E - 400V-3ph-50Hz Compressor & 230V-1ph-50Hz Fan

G - 230V-1ph-50Hz Compressor & 230V-1ph-50Hz Fan

(2) Nominal conditions (EN13215), Evaporating temperatures at dew point, Superheat 10K, Subcooling 0K

(3) Rated conditions (EN13215), Evaporating temperature Midpoint -35°C, Ambient air temperature +32°C, Return Gas Temperature 20°C, Subcooling 0K

COP: Coefficient Of Performance link to EN13215 and ErP (Energy related Products) 2009/125/CE

SEPR: Seasonal Energy Performance Ratio link to EN13215 and ErP (Energy Related Products) 2009/125/CE

Tamb [°C]: Ambient Temperature

Te [°C]: Evaporating Temperature

Q [kW]: Cooling Capacity in Kilo Watt

P [kW]: Power Input in Kilo Watt

Version

A00: Without valves and receiver for capillary tubes

A01: With receiver, 2 stop valves, brackets and copper pipes for KP

A04: A01 + KP17 WB + FSA-kit + power cord


For regular updates and detailed capacities, please refer to **Coolselector®2** software


Model	Code	Version	Compressor	Electrical code (1)	Tamb [°C]	Cooling capacity Q [kW] (2)							EcoDesign (3)				Sound power level dB(A)	Sound pressure level 10 m dB(A)
						Te [°C]							Q [kW]	P [kW]	COP	SEPR		
						-40°C	-35°C	-30°C	-25°C	-20°C	-15°C	-10°C						
OP-LCQN048	114X5758	A02	NTZ048	E	27	0.732	1.054	1.425	1.841	2.298	2.791	3.314					73	42
					32	0.625	0.920	1.258	1.636	2.051	2.497	2.972	1.040	0.951	1.09			
					38	0.498	0.761	1.060	1.393	1.757	2.148	2.565						
					43	-	0.632	0.899	1.194	1.516	1.862	-						
					46	-	0.557	0.804	1.076	1.373	1.692	-						
OP-LCQN048	114X5759	A02	NTZ048	G	27	0.717	1.036	1.413	1.844	2.323	2.842	3.393					73	42
					32	0.598	0.892	1.237	1.631	2.068	2.543	3.047	1.008	1.060	0.96			
					38	0.457	0.720	1.027	1.377	1.764	2.184	2.631						
					43	-	0.580	0.855	1.167	1.512	1.887	-						
					46	-	0.499	0.754	1.042	1.362	1.709	-						
OP-LCQN068	114X5761 114X5784	A02 A14	NTZ068	E	27	1.274	1.718	2.223	2.788	3.402	4.055	4.738					71	40
					32	1.103	1.509	1.969	2.481	3.040	3.634	4.256	1.824	1.671	1.09			
					38	0.914	1.275	1.682	2.131	2.620	3.142	3.687						
					43	-	1.093	1.455	1.852	2.281	2.742	-						
					46	-	0.988	1.323	1.688	2.082	2.504	-						
OP-LCQN068	114X5762 114X5783	A02 A14	NTZ068	G	27	1.272	1.686	2.17	2.718	3.322	3.969	4.642					71	40
					32	1.134	1.509	1.945	2.436	2.977	3.555	4.153	1.814	1.787	1.02			
					38	0.970	1.299	1.677	2.102	2.568	3.063	3.572						
					43	-	1.124	1.456	1.826	2.23	2.657	-						
					46	-	1.019	1.324	1.662	2.028	2.413	-						
OP-LCQN096	114X5764	A02	NTZ096	E	27	1.458	1.984	2.613	3.337	4.144	5.017	5.937					82	51
					32	1.242	1.720	2.290	2.947	3.680	4.475	5.313	1.954	1.946	1.00			
					38	0.986	1.404	1.904	2.481	3.126	3.827	4.567						
					43	-	1.148	1.588	2.098	2.669	3.292	-						
					46	-	0.998	1.402	1.871	2.398	2.973	-						
OP-LGQN096	114X5766 114X5785	A02 A14	NTZ096	E	27	1.69	2.353	3.188	4.213	5.446	6.904	8.604					82	51
					32	1.457	2.067	2.837	3.783	4.924	6.276	7.857	2.388	1.939	1.23	1.64		
					38	1.172	1.713	2.399	3.246	4.272	5.494	6.929						
					43	-	1.417	2.029	2.79	3.717	4.827	-						
					46	-	1.243	1.809	2.517	3.383	4.424	-						

LBP
(1) E - 400V-3ph-50Hz Compressor & 230V-1ph-50Hz Fan

G - 230V-1ph-50Hz Compressor & 230V-1ph-50Hz Fan

(2) Nominal conditions (EN13215), Evaporating temperatures at dew point, Superheat 10K, Subcooling 0K

(3) Rated conditions (EN13215), Evaporating temperature Midpoint -35°C, Ambient air temperature +32°C, Return Gas Temperature 20°C, Subcooling 0K

COP: Coefficient Of Performance link to EN13215 and ErP (Energy related Products) 2009/125/CE

SEPR: Seasonal Energy Performance Ratio link to EN13215 and ErP (Energy Related Products) 2009/125/CE

Tamb [°C]: Ambient Temperature

Te [°C]: Evaporating Temperature

Q [kW]: Cooling Capacity in Kilo Watt

P [kW]: Power Input in Kilo Watt

Version

A02: Receiver + Stop valves + KP17WB pressure switch + Electrical box

A14: Filter drier + Sight glass + Receiver + Stop valves + KP17WB pressure switch + Electrical box

This table continues on the next page


For regular updates and detailed capacities, please refer to **Coolselector®2** software


Model	Code	Version	Compressor	Electrical code (1)	Tamb [°C]	Cooling capacity Q [kW] (2)							EcoDesign (3)				Sound power level dB(A)	Sound pressure level 10 m dB(A)
						Te [°C]							Q [kW]	P [kW]	COP	SEPR		
						-40°C	-35°C	-30°C	-25°C	-20°C	-15°C	-10°C						
OP-LCQN108	114X5768 114X5786	A02 A14	NTZ108	E	27	1.999	2.792	3.759	4.905	6.231	7.737	9.418					78	47
					32	1.718	2.449	3.336	4.387	5.602	6.984	8.530	2.852	2.331	1.22	1.70		
					38	1.385	2.040	2.831	3.766	4.848	6.08	7.463						
					43	-	1.706	2.415	3.252	4.222	5.329	-						
					46	-	1.510	2.168	2.947	3.849	4.880	-						
OP-LGQN108	114X5769	A02	NTZ108	E	27	2.029	2.841	3.834	5.016	6.391	7.961	9.725					78	47
					32	1.744	2.495	3.409	4.495	5.759	7.204	8.832	2.805	2.247	1.25	1.74		
					38	1.407	2.082	2.900	3.869	4.999	6.294	7.757						
					43	-	1.744	2.479	3.351	4.367	5.535	-						
					46	-	1.544	2.230	3.042	3.990	5.081	-						
OP-LGQN136	114X5771	A02	NTZ136	E	27	2.601	3.556	4.713	6.081	7.671	9.486	11.528					78	47
					32	2.263	3.144	4.208	5.469	6.935	8.613	10.506	3.544	3.060	1.16	1.70		
					38	1.865	2.655	3.607	4.736	6.053	7.564	9.277						
					43	-	2.254	3.112	4.129	5.319	6.690	-						
					46	-	2.019	2.817	3.767	4.880	6.166	-						
OP-LCQN136	114X5772 114X5787	A02 A14	NTZ136	E	27	2.559	3.489	4.609	5.926	7.446	9.170	11.090					78	47
					32	2.224	3.080	4.108	5.317	6.714	8.301	10.070	3.611	3.149	1.15	1.68		
					38	1.831	2.596	3.512	4.589	5.837	7.257	8.848						
					43	-	2.201	3.022	3.989	5.109	6.388	-						
					46	-	1.970	2.733	3.632	4.675	5.867	-						
OP-LGQN215	114X5774 114X5788	A02 A14	NTZ215	E	27	4.041	5.532	7.302	9.371	11.750	14.460	17.50					86	55
					32	3.469	4.867	6.519	8.446	10.660	13.180	16.010	5.682	4.930	1.15	1.66		
					38	2.771	4.042	5.540	7.284	9.291	11.570	14.140						
					43	-	3.349	4.707	6.288	8.109	10.180	-						
					46	-	2.936	4.205	5.684	7.389	9.3340	-						
OP-LGQN271	114X5776	A02	NTZ271	E	27	5.409	7.353	9.644	12.288	15.286	18.632	22.315					86	55
					32	4.751	6.549	8.661	11.098	13.862	16.951	20.360	7.403	6.344	1.17	1.62		
					38	3.956	5.568	7.459	9.639	12.116	14.893	17.967						
					43	3.299	4.748	6.446	8.406	10.638	13.148	-						
					46	-	4.258	5.837	7.662	9.744	12.090	-						

LBP
(1) E - 400V-3ph-50Hz Compressor & 230V-1ph-50Hz Fan

G - 230V-1ph-50Hz Compressor & 230V-1ph-50Hz Fan

(2) Nominal conditions (EN13215), Evaporating temperatures at dew point, Superheat 10K, Subcooling 0K

(3) Rated conditions (EN13215), Evaporating temperature Midpoint -35°C, Ambient air temperature +32°C, Return Gas Temperature 20°C, Subcooling 0K

COP: Coefficient Of Performance link to EN13215 and ErP (Energy related Products) 2009/125/CE

SEPR: Seasonal Energy Performance Ratio link to EN13215 and ErP (Energy Related Products) 2009/125/CE

Tamb [°C]: Ambient Temperature

Te [°C]: Evaporating Temperature

Q [kW]: Cooling Capacity in Kilo Watt

P [kW]: Power Input in Kilo Watt

Version

A02: Receiver + Stop valves + KP17WB pressure switch + Electrical box

A14: Filter drier + Sight glass + Receiver + Stop valves + KP17WB pressure switch + Electrical box


For regular updates and detailed capacities, please refer to **Coolselector®2** software


Model	Code	Version	Compressor	Electrical code (1)	Tamb [°C]	Cooling capacity Q [kW] (2)								EcoDesign (3)			
						Te [°C]								Q [kW]	P [kW]	COP	SEPR
						-25°C	-20°C	-15°C	-10°C	-5°C	0°C	5°C	10°C				
OP-MCNC003	114F1202	A09	NBC30RA	G	27	0.141	0.177	0.218	0.264	0.316	0.372	0.433	0.498	0.251	0.134	1.88	
	114F1203	A10			32	0.129	0.162	0.200	0.244	0.292	0.346	0.404	0.467				
	114F1201	A11			38	0.116	0.145	0.180	0.220	0.265	0.315	0.370	-				
					43	0.105	0.131	0.163	0.199	0.242	0.289	-	-				
OP-MCNC004	114F1205	A09	NLY45RAb	G	27	0.203	0.254	0.311	0.373	0.439	0.510	0.586	0.666	0.354	0.187	1.88	
	114F1206	A10			32	0.186	0.233	0.286	0.343	0.406	0.474	0.546	0.623				
	114F1204	A11			38	0.166	0.208	0.256	0.309	0.367	0.430	0.498	-				
					43	0.149	0.187	0.231	0.280	0.334	0.394	-	-				
OP-MCNC006	114F1308	A09	NLY60RAb	G	27	0.274	0.341	0.416	0.500	0.590	0.689	0.794	0.906	0.477	0.245	1.95	
	114F1309	A10			32	0.254	0.315	0.385	0.463	0.549	0.642	0.743	0.852				
	114F1307	A11			38	0.230	0.284	0.347	0.419	0.499	0.586	0.682	-				
					43	0.210	0.258	0.316	0.382	0.457	0.540	-	-				
OP-MCNC008	114F1411	A09	NLY80RAb	G	27	0.354	0.454	0.566	0.691	0.828	0.977	1.138	1.310	0.657	0.324	2.03	
	114F1412	A10			32	0.328	0.418	0.522	0.639	0.768	0.910	1.063	1.228				
	114F1410	A11			38	0.296	0.376	0.469	0.576	0.696	0.829	0.974	-				
					43	0.269	0.341	0.426	0.524	0.636	0.761	-	-				
OP-MCNC009	114F1414	A09	NLY90RAb	G	27	0.408	0.518	0.641	0.776	0.924	1.084	1.255	1.437	0.739	0.365	2.02	
	114F1415	A10			32	0.378	0.478	0.592	0.719	0.858	1.009	1.173	1.348				
	114F1413	A11			38	0.342	0.431	0.533	0.649	0.778	0.920	1.075	-				
					43	0.312	0.391	0.485	0.592	0.712	0.846	-	-				
OP-MCNC011	114F1417	A09	NLY12RAb	G	27	0.474	0.603	0.743	0.894	1.056	1.228	1.409	1.601	0.859	0.445	1.93	
	114F1418	A10			32	0.442	0.561	0.691	0.833	0.986	1.149	1.324	1.508				
	114F1416	A11			38	0.404	0.511	0.630	0.760	0.902	1.056	1.221	-				
					43	0.372	0.469	0.578	0.699	0.833	0.978	-	-				
OP-MCNC014	114F1420	A09	NPT14RA	G	27	0.687	0.746	0.851	1.003	1.200	1.441	1.728	2.061	0.983	0.590	1.66	
	114F1421	A10			32	0.652	0.705	0.805	0.950	1.141	1.378	1.660	1.990				
	114F1419	A11			38	0.609	0.656	0.748	0.887	1.071	1.302	1.579	-				
					43	0.573	0.614	0.701	0.834	1.013	1.238	-	-				
OP-MCNC016	114F1623	A09	NPT16RA	G	27	0.786	0.859	0.987	1.168	1.402	1.688	2.027	2.418	1.141	0.637	1.79	
	114F1624	A10			32	0.746	0.813	0.934	1.108	1.335	1.615	1.948	2.335				
	114F1622	A11			38	0.698	0.757	0.870	1.036	1.255	1.527	1.854	-				
					43	0.658	0.710	0.816	0.975	1.188	1.454	-	-				
OP-MCNC018	114F1626	A09	NX18TBa	G	27	0.740	0.936	1.160	1.410	1.686	1.985	2.308	2.653	1.335	0.726	1.84	
	114F1627	A10			32	0.675	0.854	1.062	1.296	1.556	1.841	2.150	2.483				
	114F1625	A11			38	0.597	0.756	0.944	1.159	1.401	1.669	1.962	-				
					43	0.533	0.675	0.847	1.046	1.272	1.525	-	-				
OP-MCNC020	114F1629	A09	NX21TBa	G	27	0.826	1.032	1.260	1.510	1.780	2.067	2.372	2.693	1.423	0.844	1.69	
	114F1630	A10			32	0.752	0.937	1.147	1.379	1.631	1.903	2.192	2.500				
	114F1628	A11			38	0.663	0.825	1.011	1.221	1.453	1.705	1.977	-				
					43	0.590	0.731	0.899	1.091	1.305	1.541	-	-				

MBP
(1) E - 400V-3ph-50Hz Compressor & 230V-1ph-50Hz Fan

G - 230V-1ph-50Hz Compressor & 230V-1ph-50Hz Fan

(2) Nominal conditions (EN13215), Evaporating temperatures at dew point, Superheat 10K, Subcooling 0K

(3) Rated conditions (EN13215), Evaporating temperature Midpoint -10°C, Ambient air temperature +32°C, Return Gas Temperature 20°C, Subcooling 0K

COP: Coefficient Of Performance link to EN13215 and ErP (Energy related Products) 2009/125/CE

SEPR: Seasonal Energy Performance Ratio link to EN13215 and ErP (Energy Related Products) 2009/125/CE

Tamb [°C]: Ambient Temperature

Te [°C]: Evaporating Temperature

Q [kW]: Cooling Capacity in Kilo Watt

P [kW]: Power Input in Kilo Watt

Version

A09: Tube for KP pressostat + Wired Ebox + Schrader valve

A10: HP and LP Mini pressure switch + Wired Ebox + Combo Filter drier + Schrader valve

A11: Wired Ebox + Schrader valve


For regular updates and detailed capacities, please refer to **Coolselector®2** software


Model	Code	Version	Compressor	Electrical code (1)	Tamb [°C]	Cooling capacity Q [kW] (2)								EcoDesign (3)				
						Te [°C]								Q [kW]	P [kW]	COP	SEPR	
						-30°C	-25°C	-20°C	-15°C	-10°C	-5°C	0°C	5°C					10°C
OP-MCGC003	114X0104	A00	TL3G	G	27	0.050	0.066	0.086	0.110	0.137	0.167	0.200	0.236	0.273				
	114X0105	A01			32	0.045	0.060	0.079	0.101	0.126	0.154	0.184	0.217	0.251	0.13	0.12	1.08	
	114X0107	A04			38	0.038	0.052	0.070	0.090	0.112	0.138	0.165	0.194	0.225				
					43	0.032	0.045	0.061	0.080	0.101	0.123	0.148	0.175	0.202				
OP-MCGC004	114X0108	A00	TL4G	G	27	0.050	0.077	0.106	0.137	0.170	0.205	0.242	0.284	0.329				
	114X0109	A01			32	0.048	0.071	0.096	0.124	0.154	0.187	0.224	0.264	0.310	0.159	0.159	1.00	
	114X0111	A04			38	0.042	0.062	0.084	0.109	0.136	0.168	0.204	0.245	-				
					43	0.037	0.054	0.074	0.097	0.124	0.155	0.190	-	-				
OP-MCGC005	114X0112	A00	TL5G	G	27	0.079	0.102	0.130	0.162	0.198	0.238	0.281	0.328	0.376				
	114X0113	A01			32	0.071	0.094	0.120	0.150	0.184	0.222	0.263	0.306	0.352	0.19	0.171	1.11	
	114X0115	A04			38	0.063	0.084	0.108	0.136	0.168	0.203	0.241	0.281	0.323				
					43	0.056	0.076	0.099	0.125	0.155	0.187	0.222	0.260	0.321				
OP-MCGC006	114X0200	A00	FR6G	G	27	0.110	0.146	0.188	0.238	0.296	0.364	0.441	0.527	0.623				
	114X0201	A01			32	0.097	0.131	0.172	0.219	0.275	0.340	0.413	0.496	0.588	0.283	0.187	1.51	
	114X0203	A04			38	0.080	0.113	0.152	0.197	0.250	0.311	0.380	0.458	0.544				
					43	0.067	0.099	0.136	0.179	0.229	0.287	0.352	0.426	0.508				
OP-MCGC006	114X0228	A00	NL6.1MF	G	27	-	-	0.197	0.252	0.316	0.388	0.470	0.560	0.657				
					32	-	-	0.181	0.233	0.293	0.361	0.438	0.522	0.614	0.301	0.202	1.49	
					38	-	-	0.162	0.210	0.265	0.328	0.399	0.477	0.562				
					43	-	-	0.146	0.191	0.242	0.301	0.366	0.439	0.519				
OP-MCGC007	114X0216	A00	FR7.5G	G	27	0.118	0.156	0.202	0.256	0.319	0.392	0.474	0.567	0.669				
	114X0217	A01			32	0.103	0.140	0.184	0.236	0.296	0.366	0.444	0.532	0.630	0.305	0.213	1.43	
	114X0219	A04			38	0.087	0.122	0.164	0.213	0.269	0.335	0.408	0.491	0.583				
					43	0.074	0.108	0.148	0.194	0.248	0.309	0.379	0.457	0.543				
OP-MCGC008	114X0224	A00	FR8.5G	G	27	0.139	0.184	0.239	0.302	0.376	0.458	0.551	0.653	0.765				
	114X0225	A01			32	0.129	0.171	0.222	0.281	0.350	0.428	0.516	0.613	0.720	0.36	0.248	1.45	
	114X0227	A04			38	0.112	0.151	0.198	0.253	0.317	0.389	0.472	0.564	0.666				
					43	0.097	0.133	0.177	0.229	0.289	0.358	0.436	0.525	0.623				
OP-MCGC007	114X0244	A00	NL7.3MF	G	27	-	-	0.237	0.301	0.374	0.457	0.548	0.648	0.757				
					32	-	-	0.218	0.278	0.347	0.424	0.511	0.605	0.708	0.357	0.241	1.48	
					38	-	-	0.196	0.251	0.314	0.386	0.466	0.554	0.649				
					43	-	-	0.178	0.229	0.288	0.355	0.429	0.511	0.600				
OP-MCGC008	114X0204	A00	NL8.4MF	G	27	-	-	0.269	0.339	0.418	0.508	0.606	0.714	0.828				
	114X0205	A01			32	-	-	0.248	0.314	0.388	0.472	0.565	0.666	0.775	0.4	0.256	1.56	
					38	-	-	0.224	0.284	0.353	0.431	0.516	0.610	0.711				
					43	-	-	0.205	0.261	0.325	0.397	0.477	0.564	0.659				

MBP
(1) E - 400V-3ph-50Hz Compressor & 230V-1ph-50Hz Fan

G - 230V-1ph-50Hz Compressor & 230V-1ph-50Hz Fan

(2) Nominal conditions (EN13215), Evaporating temperatures at dew point, Superheat 10K, Subcooling 0K

(3) Rated conditions (EN13215), Evaporating temperature Midpoint -10°C, Ambient air temperature +32°C, Return Gas Temperature 20°C, Subcooling 0K

COP: Coefficient Of Performance link to EN13215 and ErP (Energy related Products) 2009/125/CE

SEPR: Seasonal Energy Performance Ratio link to EN13215 and ErP (Energy Related Products) 2009/125/CE

Tamb [°C]: Ambient Temperature

Te [°C]: Evaporating Temperature

Q [kW]: Cooling Capacity in Kilo Watt

P [kW]: Power Input in Kilo Watt

Version

A00: Without valves and receiver for capillary tubes

A01: With receiver, 2 stop valves, brackets and copper pipes for KP

A04: A01 + KP17 WB + FSA-kit + power cord

This table continues on the next page


For regular updates and detailed capacities, please refer to **Coolselector®2** software


Model	Code	Version	Compressor	Electrical code (1)	Tamb [°C]	Cooling capacity Q [kW] (2)									EcoDesign (3)			
						Te [°C]									Q [kW]	P [kW]	COP	SEPR
						-30°C	-25°C	-20°C	-15°C	-10°C	-5°C	0°C	5°C	10°C				
OP-MCGC010	114X0223	A04	SC10G	G	27	0.148	0.212	0.284	0.365	0.454	0.551	0.656	0.771	0.896	0.426	0.303	1.41	
					32	0.128	0.186	0.252	0.328	0.413	0.507	0.611	0.725	0.853				
					38	0.102	0.153	0.214	0.286	0.367	0.459	0.563	0.679	0.811				
					43	0.080	0.127	0.185	0.254	0.334	0.425	0.530	0.650	-				
OP-MCGC008	114X0352	A00	NL8.4MF	G	27	-	-	0.278	0.352	0.437	0.533	0.641	0.760	0.889	0.417	0.281	1.48	
					32	-	-	0.256	0.325	0.405	0.496	0.598	0.710	0.832				
					38	-	-	0.232	0.295	0.369	0.453	0.547	0.651	0.765				
					43	-	-	0.212	0.271	0.339	0.417	0.505	0.603	0.710				
OP-MCGC011	114X0336	A00	FR11G	G	27	0.163	0.241	0.322	0.406	0.499	0.600	0.715	0.844	-	0.473	0.337	1.41	
	114X0337	A01			32	0.153	0.223	0.296	0.374	0.460	0.557	0.666	0.793	-				
	114X0339	A04			38	0.136	0.198	0.263	0.334	0.414	0.505	0.611	0.734	-				
					43	0.121	0.177	0.236	0.302	0.377	0.465	0.568	0.690	-				
OP-MCGC012	114X0340	A00	SC12G	G	27	0.213	0.281	0.362	0.457	0.566	0.688	0.824	0.972	1.133	0.535	0.378	1.41	
	114X0341	A01			32	0.185	0.249	0.326	0.416	0.519	0.635	0.764	0.906	1.060				
	114X0343	A04			38	0.153	0.213	0.284	0.368	0.464	0.572	0.694	0.828	0.974				
					43	0.129	0.185	0.251	0.329	0.419	0.522	0.637	0.764	-				
OP-MCGC015	114X0448	A00	SC15G	G	27	-	0.323	0.427	0.552	0.694	0.854	1.029	1.218	1.418	0.67	0.463	1.45	
	114X0449	A01			32	-	0.294	0.397	0.515	0.650	0.800	0.963	1.138	1.323				
	114X0451	A04			38	-	0.252	0.353	0.466	0.592	0.730	0.879	1.039	1.207				
					43	-	0.213	0.312	0.421	0.540	0.669	0.807	0.954	1.109				
OP-MCGC018	114X0556	A00	SC18G	G	27	-	0.400	0.515	0.649	0.803	0.978	1.173	1.389	1.624	0.77	0.552	1.40	
	114X0557	A01			32	-	0.351	0.465	0.596	0.746	0.915	1.104	1.310	1.532				
	114X0559	A04			38	-	0.307	0.417	0.543	0.685	0.844	1.019	1.211	1.415				
					43	-	0.280	0.384	0.502	0.635	0.783	0.946	1.122	-				
OP-MCGC021	114X0568	A00	SC21MF	G	27	-	-	0.623	0.773	0.945	1.137	1.350	1.583	1.833	0.91	0.647	1.41	
					32	-	-	0.578	0.720	0.881	1.063	1.264	1.483	1.720				
					38	-	-	0.524	0.655	0.804	0.972	1.159	1.364	1.585				
					43	-	-	0.480	0.601	0.740	0.897	1.072	1.263	-				
OP-MCGC021	114X0564	A00	SC21G	G	27	-	0.463	0.601	0.758	0.933	1.125	1.331	1.551	1.783	0.89	0.631	1.41	
	114X0565	A01			32	-	0.421	0.550	0.698	0.862	1.042	1.235	1.441	1.658				
	114X0567	A04			38	-	0.375	0.491	0.624	0.773	0.936	1.112	1.300	1.499				
					43	-	0.337	0.440	0.559	0.694	0.842	1.003	1.176	1.359				
OP-MCGC026	114X0773	A01	GS26MFX	G	27	-	-	0.873	1.125	1.416	1.745	2.113	2.519	-	1.352	0.766	1.77	
					32	-	-	0.809	1.045	1.317	1.625	1.970	2.350	-				
					38	-	-	0.736	0.953	1.202	1.485	1.801	2.151	-				
					43	-	-	0.675	0.877	1.108	1.369	1.662	1.986	-				
OP-MCGC034	114X0781	A01	GS34MFX	G	27	-	-	1.138	1.432	1.772	2.158	2.592	3.072	-	1.699	0.982	1.73	
					32	-	-	1.051	1.330	1.652	2.018	2.429	2.886	-				
					38	-	-	0.946	1.207	1.507	1.848	2.232	2.660	-				
					43	-	-	0.858	1.103	1.385	1.706	2.067	2.470	-				

MBP
(1) E - 400V-3ph-50Hz Compressor & 230V-1ph-50Hz Fan

G - 230V-1ph-50Hz Compressor & 230V-1ph-50Hz Fan

(2) Nominal conditions (EN13215), Evaporating temperatures at dew point, Superheat 10K, Subcooling 0K

(3) Rated conditions (EN13215), Evaporating temperature Midpoint -10°C, Ambient air temperature +32°C, Return Gas Temperature 20°C, Subcooling 0K

COP: Coefficient Of Performance link to EN13215 and ErP (Energy related Products) 2009/125/CE

SEPR: Seasonal Energy Performance Ratio link to EN13215 and ErP (Energy Related Products) 2009/125/CE

Tamb [°C]: Ambient Temperature

Te [°C]: Evaporating Temperature

Q [kW]: Cooling Capacity in Kilo Watt

P [kW]: Power Input in Kilo Watt

Version

A00: Without valves and receiver for capillary tubes

A01: With receiver, 2 stop valves, brackets and copper pipes for KP

A04: A01 + KP17 WB + FSA-kit + power cord


For regular updates and detailed capacities, please refer to **Coolselector®2** software


Model	Code	Version	Compressor	Electrical code (1)	Tamb [°C]	Cooling capacity Q [kW] (2)								EcoDesign (3)				Sound power level dB(A)	Sound pressure level 10 m dB(A)
						Te [°C]								Q [kW]	P [kW]	COP	SEPR		
						-20°C	-15°C	-10°C	-5°C	0°C	5°C	10°C	15°C						
OP-MCRN030	114X5721	A02	MTZ018	E	27	0.739	1.058	1.445	1.902	2.433	3.036	3.710	4.453					76	45
					32	0.616	0.923	1.292	1.726	2.226	2.793	3.426	4.123	1.322	0.727	1.82			
					38	0.490	0.779	1.122	1.523	1.984	2.504	3.085	-						
					43	0.405	0.675	0.993	1.363	1.787	2.267	2.800	-						
					46	0.363	0.620	0.921	1.272	1.673	2.126	2.630	-						
OP-MCRN030	114X5722	A02	MTZ018	G	27	0.739	1.058	1.445	1.902	2.433	3.036	3.710	4.453					76	45
					32	0.616	0.923	1.292	1.726	2.226	2.793	3.426	4.123	1.322	0.727	1.82			
					38	0.490	0.779	1.122	1.523	1.984	2.504	3.085	-						
					43	0.405	0.675	0.993	1.363	1.787	2.267	2.800	-						
					46	0.363	0.620	0.921	1.272	1.673	2.126	2.630	-						
OP-MCRN038	114X5724 114X5790	A02 A14	MTZ022	E	27	0.947	1.325	1.789	2.343	2.989	3.726	4.552	5.460					74	43
					32	0.815	1.179	1.620	2.145	2.754	3.447	4.223	5.076	1.659	0.856	1.94			
					38	0.676	1.017	1.427	1.912	2.473	3.111	3.824	-						
					43	0.578	0.896	1.276	1.725	2.243	2.832	3.491	-						
					46	0.528	0.830	1.192	1.616	2.108	2.666	3.292	-						
OP-MCRN038	114X5723 114X5789	A02 A14	MTZ022	G	27	0.947	1.325	1.789	2.343	2.989	3.726	4.552	5.460					74	43
					32	0.815	1.179	1.620	2.145	2.754	3.447	4.223	5.076	1.659	0.856	1.94			
					38	0.676	1.017	1.427	1.912	2.473	3.111	3.824	-						
					43	0.578	0.896	1.276	1.725	2.243	2.832	3.491	-						
					46	0.528	0.830	1.192	1.616	2.108	2.666	3.292	-						
OP-MCRN048	114X5726 114X5792	A02 A14	MTZ028	E	27	1.226	1.653	2.200	2.879	3.697	4.660	5.767	7.016					74	43
					32	1.085	1.494	2.014	2.656	3.429	4.337	5.382	6.559	2.062	1.114	1.85			
					38	0.942	1.323	1.804	2.397	3.110	3.948	4.913	-						
					43	0.848	1.199	1.643	2.189	2.848	3.623	4.517	-						
					46	0.802	1.134	1.552	2.069	2.693	3.429	4.279	-						
OP-MCRN048	114X5728 114X5791	A02 A14	MTZ028	G	27	1.226	1.653	2.200	2.879	3.697	4.660	5.767	7.016					74	43
					32	1.085	1.494	2.014	2.656	3.429	4.337	5.382	6.559	2.062	1.114	1.85			
					38	0.942	1.323	1.804	2.397	3.110	3.948	4.913	-						
					43	0.848	1.199	1.643	2.189	2.848	3.623	4.517	-						
					46	0.802	1.134	1.552	2.069	2.693	3.429	4.279	-						
OP-MCRN054	114X5729	A02	MTZ032	E	27	1.409	1.919	2.558	3.337	4.261	5.334	6.554	7.916					74	43
					32	1.243	1.732	2.341	3.079	3.952	4.965	6.116	7.400	2.398	1.353	1.77			
					38	1.064	1.523	2.088	2.772	3.580	4.516	5.581	-						
					43	0.935	1.362	1.887	2.521	3.270	4.139	5.128	-						
					46	0.867	1.273	1.772	2.373	3.086	3.913	4.855	-						
OP-MCRN054	114X5731	A02	MTZ032	G	27	1.409	1.919	2.558	3.337	4.261	5.334	6.554	7.916					74	43
					32	1.243	1.732	2.341	3.079	3.952	4.965	6.116	7.400	2.398	1.353	1.77			
					38	1.064	1.523	2.088	2.772	3.580	4.516	5.581	-						
					43	0.935	1.362	1.887	2.521	3.270	4.139	5.128	-						
					46	0.867	1.273	1.772	2.373	3.086	3.913	4.855	-						

MBP
(1) E - 400V-3ph-50Hz Compressor & 230V-1ph-50Hz Fan

G - 230V-1ph-50Hz Compressor & 230V-1ph-50Hz Fan

(2) Nominal conditions (EN13215), Evaporating temperatures at dew point, Superheat 10K, Subcooling 0K

(3) Rated conditions (EN13215), Evaporating temperature Midpoint -10°C, Ambient air temperature +32°C, Return Gas Temperature 20°C, Subcooling 0K

COP: Coefficient Of Performance link to EN13215 and ErP (Energy related Products) 2009/125/CE

SEPR: Seasonal Energy Performance Ratio link to EN13215 and ErP (Energy Related Products) 2009/125/CE

Tamb [°C]: Ambient Temperature

Te [°C]: Evaporating Temperature

Q [kW]: Cooling Capacity in Kilo Watt

P [kW]: Power Input in Kilo Watt

Version

A02: Receiver + Stop valves + KP17WB pressure switch + Electrical box

A14: Filter drier + Sight glass + Receiver + Stop valves + KP17WB pressure switch + Electrical box

This table continues on the next page


For regular updates and detailed capacities, please refer to **Coolselector®2** software


Model	Code	Version	Compressor	Electrical code (1)	Tamb [°C]	Cooling capacity Q [kW] (2)								EcoDesign (3)				Sound power level dB(A)	Sound pressure level 10 m dB(A)
						Te [°C]								Q [kW]	P [kW]	COP	SEPR		
						-20°C	-15°C	-10°C	-5°C	0°C	5°C	10°C	15°C						
OP-MCRN060	114X5732 114X5794	A02 A14	MTZ036	E	27	1.929	2.522	3.237	4.079	5.052	6.154	7.382	8.729					74	43
					32	1.758	2.330	3.014	3.815	4.736	5.778	6.937	8.207	3.092	1.607	1.92			
					38	1.564	2.105	2.745	3.491	4.347	5.312	6.385	-						
					43	1.413	1.921	2.521	3.217	4.014	4.913	5.911	-						
					46	1.326	1.814	2.387	3.051	3.811	4.668	5.620	-						
OP-MCRN060	114X5734 114X5793	A02 A14	MTZ036	G	27	1.929	2.522	3.237	4.079	5.052	6.154	7.382	8.729					74	43
					32	1.758	2.330	3.014	3.815	4.736	5.778	6.937	8.207	3.092	1.607	1.92			
					38	1.564	2.105	2.745	3.491	4.347	5.312	6.385	-						
					43	1.413	1.921	2.521	3.217	4.014	4.913	5.911	-						
					46	1.326	1.814	2.387	3.051	3.811	4.668	5.620	-						
OP-MCRN068	114X5735	A02	MTZ040	E	27	2.276	2.905	3.641	4.489	5.451	6.528	7.718	9.016					76	45
					32	2.115	2.724	3.432	4.244	5.161	6.185	7.313	8.542	3.522	1.739	2.02			
					38	1.921	2.501	3.170	3.933	4.792	5.747	6.798	-						
					43	1.757	2.308	2.941	3.659	4.466	5.362	6.345	-						
					46	1.657	2.189	2.798	3.488	4.262	5.120	6.063	-						
OP-MCRN086	114X5737 114X5795	A02 A14	MTZ050	E	27	2.412	3.323	4.446	5.796	7.388	9.226	11.31	13.650					84	53
					32	2.127	2.980	4.028	5.288	6.776	8.499	10.46	12.670	4.162	1.943	2.14			
					38	1.807	2.597	3.561	4.719	6.086	7.675	9.492	-						
					43	1.551	2.296	3.196	4.274	5.546	7.025	8.723	-						
					46	1.402	2.121	2.985	4.017	5.234	6.65	8.277	-						
OP-MCRN096	114X5739 114X5796	A02 A14	MTZ056	E	27	2.292	3.28	4.501	5.973	7.708	9.718	12.010	14.58					83	52
					32	2.001	2.93	4.079	5.466	7.107	9.011	11.180	13.63	4.215	2.051	2.06			
					38	1.683	2.538	3.599	4.884	6.408	8.183	10.220	-						
					43	1.446	2.238	3.224	4.421	5.847	7.514	9.429	-						
					46	1.317	2.071	3.011	4.155	5.522	7.122	8.966	-						
OP-MCRN108	114X5740 114X5797	A02 A14	MTZ064	E	27	2.589	3.739	5.142	6.811	8.751	10.960	13.440	16.180					83	52
					32	2.278	3.376	4.707	6.286	8.119	10.210	12.550	15.140	4.870	2.308	2.11			
					38	1.912	2.949	4.195	5.666	7.372	9.3170	11.500	-						
					43	1.615	2.601	3.778	5.161	6.761	8.585	10.630	-						
					46	1.441	2.398	3.533	4.862	6.399	8.151	10.120	-						
OP-MGRN108	114X5743	A02	MTZ064	E	27	2.591	3.749	5.162	6.842	8.796	11.023	13.518	16.273					83	52
					32	2.278	3.385	4.727	6.319	8.167	10.273	12.635	15.245	4.84	2.242	2.16			
					38	1.910	2.956	4.214	5.700	7.422	9.385	11.587	-						
					43	1.611	2.607	3.796	5.194	6.812	8.654	10.724	-						
					46	1.435	2.402	3.550	4.895	6.450	8.221	10.211	-						

MBP
(1) E - 400V-3ph-50Hz Compressor & 230V-1ph-50Hz Fan

G - 230V-1ph-50Hz Compressor & 230V-1ph-50Hz Fan

(2) Nominal conditions (EN13215), Evaporating temperatures at dew point, Superheat 10K, Subcooling 0K

(3) Rated conditions (EN13215), Evaporating temperature Midpoint -10°C, Ambient air temperature +32°C, Return Gas Temperature 20°C, Subcooling 0K

COP: Coefficient Of Performance link to EN13215 and ErP (Energy related Products) 2009/125/CE

SEPR: Seasonal Energy Performance Ratio link to EN13215 and ErP (Energy Related Products) 2009/125/CE

Tamb [°C]: Ambient Temperature

Te [°C]: Evaporating Temperature

Q [kW]: Cooling Capacity in Kilo Watt

P [kW]: Power Input in Kilo Watt

Version

A02: Receiver + Stop valves + KP17WB pressure switch + Electrical box

A14: Filter drier + Sight glass + Receiver + Stop valves + KP17WB pressure switch + Electrical box

This table continues on the next page


For regular updates and detailed capacities, please refer to **Coolselector®2** software


Model	Code	Version	Compressor	Electrical code (1)	Tamb [°C]	Cooling capacity Q [kW] (2)								EcoDesign (3)				Sound power level dB(A)	Sound pressure level 10 m dB(A)
						Te [°C]								Q [kW]	P [kW]	COP	SEPR		
						-20°C	-15°C	-10°C	-5°C	0°C	5°C	10°C	15°C						
OP-MCRN121	114X5744	A02	MTZ072	E	27	2.984	4.234	5.762	7.582	9.704	12.130	14.854	17.865						
					32	2.667	3.873	5.334	7.069	9.087	11.390	13.976	16.835						
					38	2.280	3.427	4.805	6.434	8.323	10.477	12.896	-	5.466	2.625	2.08	2.71	82	51
					43	1.958	3.052	4.357	5.894	7.673	9.701	11.978	-						
					46	1.768	2.828	4.088	5.567	7.279	9.230	11.422	-						
OP-MGRN121	114X5746	A02	MTZ072	E	27	2.984	4.234	5.762	7.582	9.704	12.130	14.854	17.865						
					32	2.667	3.873	5.334	7.069	9.087	11.390	13.976	16.835	5.466	2.555	2.14	2.80	82	51
					38	2.280	3.427	4.805	6.434	8.323	10.477	12.896	-						
					43	1.958	3.052	4.357	5.894	7.673	9.701	11.978	-						
					46	1.768	2.828	4.088	5.567	7.279	9.230	11.422	-						
OP-MCRN136	114X5747	A02	MTZ080	E	27	4.068	5.496	7.259	9.393	11.929	14.891	18.299	22.163						
					32	3.693	5.062	6.742	8.770	11.178	13.990	17.227	20.903	6.897	2.991	2.31	2.55	82	51
					38	3.238	4.533	6.111	8.008	10.259	12.890	15.921	-						
					43	2.858	4.089	5.579	7.366	9.484	11.961	14.820	-						
					46	2.632	3.823	5.259	6.979	9.016	11.401	14.155	-						
OP-MGRN136	114X5749	A02	MTZ080	E	27	3.895	5.241	6.877	8.822	11.086	13.670	16.567	19.764						
					32	3.530	4.817	6.373	8.216	10.359	12.805	15.548	18.578	6.535	2.976	2.20	2.55	82	51
					38	3.087	4.303	5.760	7.480	9.476	11.755	14.314	-						
					43	2.720	3.873	5.246	6.862	8.736	10.875	13.281	-						
					46	2.501	3.616	4.939	6.491	8.291	10.346	12.659	-						
OP-MGRN171	114X5750	A02	MTZ100	E	27	4.814	6.493	8.569	11.082	14.059	17.523	21.488	25.959						
					32	4.209	5.830	7.821	10.219	13.054	16.346	20.112	24.356	8.004	4.202	1.90	2.68	87	56
					38	3.572	5.105	6.974	9.217	11.862	14.933	18.444	-						
					43	3.124	4.566	6.317	8.414	10.887	13.759	17.045	-						
					46	2.893	4.273	5.946	7.949	10.312	13.059	16.205	-						
OP-MGRN215	114X5753	A02	MTZ125	E	27	6.141	8.185	10.674	13.642	17.113	21.104	25.620	30.657						
					32	5.365	7.344	9.736	12.574	15.884	19.681	23.972	28.754	9.969	4.796	2.08	2.91	86	55
					38	4.513	6.393	8.648	11.311	14.409	17.957	21.962	-						
					43	3.872	5.651	7.775	10.277	13.183	16.509	20.265	-						
					46	3.520	5.231	7.269	9.667	12.450	15.638	19.238	-						
OP-MGRN242	114X5754	A02	MTZ144	E	27	7.721	10.141	13.051	16.481	20.447	24.955	29.996	35.552						
					32	6.930	9.267	12.058	15.330	19.102	23.380	28.156	33.416	12.36	5.939	2.08	2.76	85	54
					38	6.038	8.254	10.879	13.943	17.464	21.449	25.895	-						
					43	5.352	7.446	9.916	12.789	16.086	19.814	23.973	-						
					46	4.968	6.981	9.349	12.101	15.256	18.825	22.807	-						
OP-MGRN271	114X5757	A02	MTZ160	E	27	8.459	11.058	14.200	17.910	22.199	27.060	32.471	38.394						
					32	7.616	10.124	13.129	16.658	20.720	25.311	30.411	35.988	13.465	6.393	2.11	2.79	84	53
					38	6.709	9.074	11.884	15.165	18.928	23.171	27.879	-						
					43	6.033	8.253	10.874	13.924	17.416	21.351	25.716	-						
					46	5.661	7.781	10.278	13.180	16.500	20.242	24.394	-						

MBP
(1) E - 400V-3ph-50Hz Compressor & 230V-1ph-50Hz Fan

G - 230V-1ph-50Hz Compressor & 230V-1ph-50Hz Fan

(2) Nominal conditions (EN13215), Evaporating temperatures at dew point, Superheat 10K, Subcooling 0K

(3) Rated conditions (EN13215), Evaporating temperature Midpoint -10°C, Ambient air temperature +32°C, Return Gas Temperature 20°C, Subcooling 0K

COP: Coefficient Of Performance link to EN13215 and ErP (Energy related Products) 2009/125/CE

SEPR: Seasonal Energy Performance Ratio link to EN13215 and ErP (Energy Related Products) 2009/125/CE

Tamb [°C]: Ambient Temperature

Te [°C]: Evaporating Temperature

Q [kW]: Cooling Capacity in Kilo Watt

P [kW]: Power Input in Kilo Watt

Version

A02: Receiver + Stop valves + KP17WB pressure switch + Electrical box


For regular updates and detailed capacities, please refer to **Coolselector®2** software


Model	Code	Version	Compressor	Electrical code (1)	Tamb [°C]	Cooling capacity Q [kW] (2)									EcoDesign (3)			
						Te [°C]									Q [kW]	P [kW]	COP	SEPR
						-30°C	-25°C	-20°C	-15°C	-10°C	-5°C	0°C	5°C	10°C				
OP-MCGC003	114X0104	A00	TL3G	G	27	0.052	0.069	0.089	0.113	0.140	0.170	0.203	0.238	0.274	0.134	0.128	1.05	
	114X0105	A01			32	0.046	0.062	0.081	0.103	0.128	0.156	0.186	0.218	0.252				
	114X0107	A04			38	0.039	0.054	0.071	0.091	0.114	0.138	0.165	0.194	0.224				
		43			0.032	0.046	0.062	0.080	0.101	0.123	0.148	0.173	0.200					
OP-MCGC004	114X0108	A00	TL4G	G	27	0.066	0.086	0.110	0.137	0.169	0.204	0.242	0.284	0.329	0.163	0.149	1.09	
	114X0109	A01			32	0.058	0.077	0.099	0.125	0.155	0.188	0.224	0.264	0.306				
	114X0111	A04			38	0.050	0.067	0.087	0.111	0.138	0.169	0.202	0.239	0.278				
		43			0.043	0.059	0.078	0.100	0.125	0.153	0.184	0.219	-					
OP-MCGC005	114X0112	A00	TL5G	G	27	0.080	0.103	0.130	0.161	0.196	0.233	0.273	0.315	0.358	0.191	0.186	1.03	
	114X0113	A01			32	0.072	0.094	0.120	0.149	0.181	0.216	0.253	0.292	0.332				
	114X0115	A04			38	0.063	0.083	0.107	0.134	0.163	0.195	0.229	0.264	-				
		43			0.056	0.075	0.097	0.121	0.148	0.177	0.208	-	-					
OP-MCGC006	114X0200	A00	FR6G	G	27	0.116	0.152	0.196	0.247	0.307	0.376	0.454	0.542	0.640	0.296	0.201	1.48	
	114X0201	A01			32	0.101	0.136	0.178	0.227	0.284	0.350	0.424	0.508	0.601				
	114X0203	A04			38	0.083	0.117	0.157	0.203	0.256	0.318	0.387	0.466	0.553				
		43			0.069	0.101	0.139	0.183	0.233	0.291	0.357	0.430	0.512					
OP-MCGC006	114X0228	A00	NL6.1MF	G	27	-	0.153	0.201	0.259	0.326	0.403	0.491	0.588	0.695	0.316	0.206	1.53	
		32			-	0.140	0.185	0.240	0.303	0.376	0.459	0.551	0.652					
		38			-	0.124	0.166	0.216	0.275	0.343	0.419	0.505	0.599					
		43			-	0.110	0.150	0.197	0.251	0.314	0.386	0.466	0.555					
OP-MCGC007	114X0216	A00	FR7.5G	G	27	0.126	0.165	0.213	0.269	0.334	0.410	0.495	0.590	0.696	0.323	0.228	1.42	
	114X0217	A01			32	0.109	0.148	0.193	0.247	0.309	0.381	0.462	0.553	0.653				
	114X0219	A04			38	0.091	0.127	0.171	0.221	0.280	0.346	0.422	0.507	0.601				
		43			0.077	0.112	0.153	0.200	0.255	0.318	0.389	0.469	0.558					
OP-MCGC008	114X0224	A00	FR8.5G	G	27	0.146	0.193	0.249	0.314	0.388	0.472	0.566	0.669	0.782	0.376	0.267	1.41	
	114X0225	A01			32	0.134	0.178	0.229	0.290	0.359	0.438	0.527	0.624	0.732				
	114X0227	A04			38	0.115	0.155	0.203	0.258	0.323	0.396	0.478	0.570	0.672				
		43			0.099	0.136	0.180	0.232	0.292	0.361	0.439	0.527	0.625					
OP-MCGC007	114X0244	A00	NL7.3MF	G	27	-	0.193	0.251	0.320	0.400	0.491	0.592	0.704	0.826	0.388	0.258	1.51	
		32			-	0.177	0.231	0.296	0.371	0.457	0.553	0.659	0.775					
		38			-	0.157	0.208	0.268	0.337	0.416	0.506	0.605	0.714					
		43			-	0.142	0.189	0.244	0.309	0.383	0.467	0.560	0.663					
OP-MCGC008	114X0204	A00	NL8.4MF	G	27	-	0.222	0.284	0.356	0.439	0.531	0.634	0.745	0.864	0.424	0.276	1.54	
	114X0205	A01			32	-	0.203	0.260	0.328	0.405	0.492	0.588	0.693	0.806				
		38			-	0.181	0.234	0.295	0.366	0.446	0.535	0.631	0.736					
		43			-	0.163	0.212	0.269	0.334	0.408	0.490	0.581	0.678					

MBP
(1) E - 400V-3ph-50Hz Compressor & 230V-1ph-50Hz Fan

G - 230V-1ph-50Hz Compressor & 230V-1ph-50Hz Fan

(2) Nominal conditions (EN13215), Evaporating temperatures at dew point, Superheat 10K, Subcooling 0K

(3) Rated conditions (EN13215), Evaporating temperature Midpoint -10°C, Ambient air temperature +32°C, Return Gas Temperature 20°C, Subcooling 0K

COP: Coefficient Of Performance link to EN13215 and ErP (Energy related Products) 2009/125/CE

SEPR: Seasonal Energy Performance Ratio link to EN13215 and ErP (Energy Related Products) 2009/125/CE

Tamb [°C]: Ambient Temperature

Te [°C]: Evaporating Temperature

Q [kW]: Cooling Capacity in Kilo Watt

P [kW]: Power Input in Kilo Watt

Version

A00: Without valves and receiver for capillary tubes

A01: With receiver, 2 stop valves, brackets and copper pipes for KP

A04: A01 + KP17 WB + FSA-kit + power cord

This table continues on the next page


For regular updates and detailed capacities, please refer to **Coolselector®2** software


Model	Code	Version	Compressor	Electrical code (1)	Tamb [°C]	Cooling capacity Q [kW] (2)									EcoDesign (3)			
						Te [°C]									Q [kW]	P [kW]	COP	SEPR
						-30°C	-25°C	-20°C	-15°C	-10°C	-5°C	0°C	5°C	10°C				
OP-MCGC010	114X0223	A04	SC10G	G	27	0.157	0.224	0.300	0.385	0.477	0.578	0.687	0.804	0.931	0.453	0.324	1.40	
					32	0.135	0.196	0.266	0.345	0.433	0.530	0.636	0.752	0.879				
					38	0.106	0.160	0.224	0.298	0.382	0.476	0.580	0.696	0.826				
					43	0.083	0.132	0.192	0.263	0.344	0.436	0.540	0.658	0.794				
OP-MCGC008	114X0352	A00	NL8.4MF	G	27	-	0.228	0.293	0.369	0.457	0.557	0.669	0.792	0.925	0.442	0.301	1.47	
					32	-	0.208	0.269	0.340	0.423	0.517	0.622	0.737	0.863				
					38	-	0.186	0.241	0.307	0.382	0.469	0.566	0.673	0.790				
					43	-	0.168	0.219	0.280	0.350	0.430	0.520	0.620	0.730				
OP-MCGC011	114X0336	A00	FR11G	G	27	0.173	0.255	0.340	0.429	0.526	0.634	0.754	0.890	1.044	0.505	0.360	1.41	
	114X0337	A01			32	0.161	0.235	0.311	0.393	0.484	0.585	0.700	0.831	0.982				
	114X0339	A04			38	0.142	0.206	0.274	0.349	0.432	0.527	0.636	0.763	0.912				
					43	0.124	0.182	0.244	0.313	0.391	0.481	0.587	0.711	0.859				
OP-MCGC012	114X0340	A00	SC12G	G	27	0.227	0.299	0.385	0.485	0.599	0.727	0.869	1.026	1.195	0.572	0.405	1.41	
	114X0341	A01			32	0.196	0.264	0.345	0.439	0.547	0.668	0.804	0.953	1.115				
	114X0343	A04			38	0.161	0.224	0.298	0.385	0.486	0.599	0.726	0.866	1.019				
					43	0.135	0.192	0.262	0.343	0.436	0.543	0.662	0.794	0.940				
OP-MCGC015	114X0448	A00	SC15G	G	27	0.251	0.341	0.449	0.577	0.724	0.889	1.069	1.264	1.471	0.707	0.496	1.43	
	114X0449	A01			32	0.219	0.309	0.415	0.538	0.676	0.830	0.997	1.178	1.370				
	114X0451	A04			38	0.174	0.265	0.368	0.484	0.612	0.754	0.907	1.071	1.245				
					43	0.132	0.223	0.323	0.434	0.556	0.687	0.828	0.979	1.139				
OP-MCGC018	114X0556	A00	SC18G	G	27	0.325	0.430	0.551	0.692	0.853	1.035	1.240	1.467	1.715	0.824	0.589	1.40	
	114X0557	A01			32	0.270	0.374	0.493	0.631	0.788	0.964	1.162	1.379	1.616				
	114X0559	A04			38	0.223	0.323	0.437	0.569	0.717	0.884	1.068	1.271	1.491				
					43	0.196	0.291	0.399	0.522	0.661	0.816	0.988	1.176	1.379				
OP-MCGC021	114X0568	A00	SC21MF	G	27	-	0.514	0.650	0.810	0.994	1.202	1.434	1.688	1.966	0.975	0.689	1.42	
					32	-	0.474	0.603	0.754	0.928	1.124	1.344	1.586	1.851				
					38	-	0.427	0.547	0.687	0.848	1.030	1.235	1.462	1.712				
					43	-	0.389	0.500	0.630	0.781	0.952	1.144	1.358	-				
OP-MCGC021	114X0564	A00	SC21G	G	27	-	0.490	0.634	0.798	0.980	1.179	1.395	1.625	1.869	0.946	0.677	1.40	
	114X0565	A01			32	-	0.442	0.578	0.731	0.902	1.089	1.291	1.507	1.736				
	114X0567	A04			38	-	0.391	0.512	0.650	0.805	0.975	1.159	1.357	1.567				
					43	-	0.348	0.455	0.580	0.719	0.874	1.042	1.224	1.418				
OP-MCGC026	114X0773	A01	GS26MFX	G	27	-	0.680	0.898	1.151	1.442	1.769	2.133	2.531	2.961	1.390	0.824	1.69	
					32	-	0.623	0.827	1.063	1.333	1.638	1.976	2.348	2.750				
					38	-	0.558	0.744	0.960	1.206	1.483	1.792	2.131	2.500				
					43	-	0.503	0.676	0.875	1.101	1.355	1.639	1.951	2.291				
OP-MCGC034	114X0781	A01	GS34MFX	G	27	-	0.913	1.166	1.460	1.797	2.178	2.603	3.071	3.578	1.739	1.059	1.64	
					32	-	0.830	1.069	1.346	1.664	2.023	2.424	2.866	3.346				
					38	-	0.730	0.952	1.209	1.503	1.835	2.207	2.617	3.065				
					43	-	0.647	0.855	1.095	1.368	1.677	2.024	2.407	2.827				

MBP
(1) E - 400V-3ph-50Hz Compressor & 230V-1ph-50Hz Fan

G - 230V-1ph-50Hz Compressor & 230V-1ph-50Hz Fan

(2) Nominal conditions (EN13215), Evaporating temperatures at dew point, Superheat 10K, Subcooling 0K

(3) Rated conditions (EN13215), Evaporating temperature Midpoint -10°C, Ambient air temperature +32°C, Return Gas Temperature 20°C, Subcooling 0K

COP: Coefficient Of Performance link to EN13215 and ErP (Energy related Products) 2009/125/CE

SEPR: Seasonal Energy Performance Ratio link to EN13215 and ErP (Energy Related Products) 2009/125/CE

Tamb [°C]: Ambient Temperature

Te [°C]: Evaporating Temperature

Q [kW]: Cooling Capacity in Kilo Watt

P [kW]: Power Input in Kilo Watt

Version

A00: Without valves and receiver for capillary tubes

A01: With receiver, 2 stop valves, brackets and copper pipes for KP

A04: A01 + KP17 WB + FSA-kit + power cord


For regular updates and detailed capacities, please refer to **Coolselector®2** software


Model	Code	Version	Compressor	Electrical code (1)	Tamb [°C]	Cooling capacity Q [kW] (2)								EcoDesign (3)				Sound power level dB(A)	Sound pressure level 10 m dB(A)
						Te [°C]								Q [kW]	P [kW]	COP	SEPR		
						-20°C	-15°C	-10°C	-5°C	0°C	5°C	10°C	15°C						
OP-MCRN030	114X5721	A02	MTZ018	E	27	0.806	1.119	1.498	1.945	2.464	3.054	3.714	4.443					76	45
					32	0.726	1.018	1.371	1.787	2.269	2.819	3.436	4.118	1.425	0.786	1.81			
					38	0.632	0.901	1.223	1.604	2.044	2.547	3.112	3.740						
					43	0.552	0.804	1.103	1.455	1.862	2.326	2.850	3.433						
					46	0.504	0.746	1.032	1.367	1.754	2.197	2.696	3.252						
OP-MCRN030	114X5722	A02	MTZ018	G	27	0.811	1.126	1.511	1.970	2.504	3.117	3.806	4.570					76	45
					32	0.728	1.020	1.377	1.804	2.302	2.874	3.520	4.238	1.432	0.797	1.80			
					38	0.634	0.899	1.223	1.611	2.066	2.590	3.184	3.847						
					43	0.559	0.803	1.100	1.455	1.874	2.358	2.909	3.527						
					46	0.516	0.746	1.027	1.364	1.761	2.221	2.747	3.337						
OP-MCRN038	114X5724 114X5790	A02 A14	MTZ022	E	27	1.093	1.481	1.946	2.489	3.113	3.816	4.600	5.464					74	43
					32	0.984	1.344	1.775	2.282	2.864	3.524	4.261	5.075	1.879	0.921	2.04			
					38	0.863	1.189	1.581	2.044	2.578	3.185	3.867	-						
					43	0.772	1.069	1.429	1.854	2.348	2.912	3.548	-						
					46	0.721	1.001	1.341	1.744	2.214	2.753	3.362	-						
OP-MCRN038	114X5723 114X5789	A02 A14	MTZ022	G	27	1.066	1.453	1.918	2.465	3.092	3.800	4.586	5.446					74	43
					32	0.956	1.313	1.744	2.253	2.840	3.504	4.243	5.056	1.828	0.928	1.97			
					38	0.836	1.156	1.545	2.007	2.544	3.155	3.838	4.591						
					43	0.749	1.035	1.388	1.811	2.305	2.869	3.505	4.209						
					46	0.702	0.968	1.299	1.697	2.164	2.701	3.308	3.982						
OP-MCRN048	114X5726 114X5792	A02 A14	MTZ028	E	27	1.353	1.840	2.433	3.133	3.943	4.863	5.893	7.028					74	43
					32	1.233	1.687	2.238	2.890	3.645	4.506	5.470	6.538	2.354	1.224	1.92			
					38	1.097	1.510	2.011	2.604	3.294	4.082	4.969	-						
					43	0.992	1.370	1.829	2.373	3.007	3.734	4.556	-						
					46	0.932	1.290	1.722	2.237	2.838	3.528	4.310	-						
OP-MCRN048	114X5728 114X5791	A02 A14	MTZ028	G	27	1.342	1.831	2.416	3.103	3.897	4.800	5.817	6.948					74	43
					32	1.203	1.659	2.207	2.851	3.598	4.451	5.414	6.491	2.327	1.288	1.81			
					38	1.048	1.463	1.963	2.554	3.243	4.034	4.932	-						
					43	0.929	1.309	1.768	2.313	2.952	3.690	4.534	-						
					46	0.864	1.221	1.654	2.172	2.780	3.486	4.297	-						
OP-MCRN054	114X5729	A02	MTZ032	E	27	1.667	2.231	2.895	3.664	4.539	5.521	6.608	7.796					74	43
					32	1.498	2.025	2.647	3.368	4.189	5.111	6.133	7.254	2.754	1.379	2.00			
					38	1.305	1.788	2.357	3.017	3.771	4.621	5.566	6.603						
					43	1.155	1.598	2.122	2.731	3.429	4.217	5.095	6.063						
					46	1.070	1.489	1.985	2.563	3.226	3.976	4.815	5.740						
OP-MCRN054	114X5731	A02	MTZ032	G	27	1.516	2.068	2.722	3.483	4.351	5.328	6.412	7.598					74	43
					32	1.360	1.877	2.491	3.205	4.022	4.942	5.964	7.084	2.591	1.423	1.82			
					38	1.183	1.657	2.219	2.875	3.628	4.478	5.424	6.466						
					43	1.047	1.482	1.999	2.605	3.303	4.093	4.976	5.949						
					46	0.971	1.381	1.871	2.446	3.109	3.863	4.707	5.640						

MBP
(1) E - 400V-3ph-50Hz Compressor & 230V-1ph-50Hz Fan

G - 230V-1ph-50Hz Compressor & 230V-1ph-50Hz Fan

(2) Nominal conditions (EN13215), Evaporating temperatures at dew point, Superheat 10K, Subcooling 0K

(3) Rated conditions (EN13215), Evaporating temperature Midpoint -10°C, Ambient air temperature +32°C, Return Gas Temperature 20°C, Subcooling 0K

COP: Coefficient Of Performance link to EN13215 and ErP (Energy related Products) 2009/125/CE

SEPR: Seasonal Energy Performance Ratio link to EN13215 and ErP (Energy Related Products) 2009/125/CE

Tamb [°C]: Ambient Temperature

Te [°C]: Evaporating Temperature

Q [kW]: Cooling Capacity in Kilo Watt

P [kW]: Power Input in Kilo Watt

Version

A02: Receiver + Stop valves + KP17WB pressure switch + Electrical box

A14: Filter drier + Sight glass + Receiver + Stop valves + KP17WB pressure switch + Electrical box

This table continues on the next page


For regular updates and detailed capacities, please refer to **Coolselector®2** software


Model	Code	Version	Compressor	Electrical code (1)	Tamb [°C]	Cooling capacity Q [kW] (2)								EcoDesign (3)				Sound power level dB(A)	Sound pressure level 10 m dB(A)
						Te [°C]								Q [kW]	P [kW]	COP	SEPR		
						-20°C	-15°C	-10°C	-5°C	0°C	5°C	10°C	15°C						
OP-MCRN060	114X5732 114X5794	A02 A14	MTZ036	E	27	1.827	2.443	3.176	4.033	5.018	6.154	7.449	8.907					74	43
					32	1.671	2.259	2.953	3.763	4.690	5.768	7.008	8.414	3.105	1.613	1.92			
					38	1.468	2.018	2.663	3.412	4.269	5.275	6.449	-						
					43	1.288	1.803	2.405	3.101	3.897	4.842	5.96	-						
					46	1.176	1.669	2.243	2.907	3.666	4.573	5.658	-						
OP-MCRN060	114X5734 114X5793	A02 A14	MTZ036	G	27	1.800	2.449	3.215	4.103	5.117	6.259	7.533	8.939					74	43
					32	1.625	2.238	2.962	3.802	4.766	5.855	7.075	8.429	3.132	1.677	1.87			
					38	1.424	1.992	2.665	3.449	4.352	-	-	-						
					43	1.268	1.797	2.425	3.162	-	-	-	-						
					46	1.181	1.685	-	-	-	-	-	-						
OP-MCRN068	114X5735	A02	MTZ040	E	27	2.276	3.009	3.875	4.876	6.014	7.289	8.696	10.230					76	45
					32	2.061	2.746	3.556	4.494	5.563	6.762	8.088	9.536	3.702	1.924	1.92			
					38	1.818	2.443	3.183	4.043	5.025	6.131	7.359	8.703						
					43	1.631	2.203	2.882	3.674	4.583	5.610	6.753	8.009						
					46	1.526	2.065	2.707	3.457	4.321	5.299	6.391	7.594						
OP-MCRN086	114X5737 114X5795	A02 A14	MTZ050	E	27	2.698	3.599	4.698	6.013	7.556	9.337	11.380	13.690					84	53
					32	2.444	3.280	4.301	5.523	6.962	8.628	10.530	12.700	4.489	1.983	2.26			
					38	2.155	2.916	3.843	4.957	6.272	7.800	9.552	-						
					43	1.926	2.625	3.477	4.501	5.714	7.129	8.757	-						
					46	1.793	2.456	3.263	4.234	5.387	6.734	8.289	-						
OP-MCRN096	114X5739 114X5796	A02 A14	MTZ056	E	27	2.774	3.807	5.055	6.529	8.236	10.182	12.369	14.797					83	52
					32	2.470	3.425	4.585	5.962	7.564	9.396	11.462	13.762	4.762	2.157	2.21			
					38	2.144	3.002	4.054	5.311	6.783	8.476	10.394	12.538						
					43	1.908	2.683	3.641	4.796	6.157	7.732	9.524	11.537						
					46	1.784	2.507	3.407	4.500	5.793	7.296	9.012	10.944						
OP-MCRN108	114X5740 114X5797	A02 A14	MTZ064	E	27	3.214	4.351	5.718	7.328	9.191	10.18	12.420	14.91					83	52
					32	2.875	3.933	5.209	6.717	8.466	9.396	11.490	13.870	5.413	2.434	2.22	3.18		
					38	2.495	3.456	4.620	6.003	7.614	8.476	10.390	-						
					43	2.203	3.081	4.150	5.426	6.920	7.732	9.524	-						
					46	2.039	2.866	3.878	5.089	6.511	7.296	9.012	-						
OP-MGRN108	114X5743	A02	MTZ064	E	27	3.214	4.351	5.718	7.328	9.191	11.310	13.710	16.410					83	52
					32	2.875	3.933	5.209	6.717	8.466	10.460	12.710	15.270	5.443	2.431	2.24	3.23		
					38	2.495	3.456	4.620	6.003	7.614	9.461	11.550	-						
					43	2.203	3.081	4.150	5.426	6.920	8.640	10.590	-						
					46	2.039	2.866	3.878	5.089	6.511	8.155	10.030	-						

MBP

(1) E - 400V-3ph-50Hz Compressor & 230V-1ph-50Hz Fan
G - 230V-1ph-50Hz Compressor & 230V-1ph-50Hz Fan

(2) Nominal conditions (EN13215), Evaporating temperatures at dew point, Superheat 10K, Subcooling 0K

(3) Rated conditions (EN13215), Evaporating temperature Midpoint -10°C, Ambient air temperature +32°C, Return Gas Temperature 20°C, Subcooling 0K

COP: Coefficient Of Performance link to EN13215 and ErP (Energy related Products) 2009/125/CE

SEPR: Seasonal Energy Performance Ratio link to EN13215 and ErP (Energy Related Products) 2009/125/CE

Tamb [°C]: Ambient Temperature

Te [°C]: Evaporating Temperature

Q [kW]: Cooling Capacity in Kilo Watt

P [kW]: Power Input in Kilo Watt

Version

A02: Receiver + Stop valves + KP17WB pressure switch + Electrical box

A14: Filter drier + Sight glass + Receiver + Stop valves + KP17WB pressure switch + Electrical box

This table continues on the next page



For regular updates and detailed capacities, please refer to **Coolselector®2** software



Model	Code	Version	Compressor	Electrical code (1)	Tamb [°C]	Cooling capacity Q [kW] (2)								EcoDesign (3)				Sound power level dB(A)	Sound pressure level 10 m dB(A)
						Te [°C]								Q [kW]	P [kW]	COP	SEPR		
						-20°C	-15°C	-10°C	-5°C	0°C	5°C	10°C	15°C						
OP-MCRN121	114X5744	A02	MTZ072	E	27	3.638	4.859	6.329	8.062	10.069	12.353	14.918	17.759					82	51
					32	3.287	4.425	5.799	7.425	9.311	11.466	13.891	16.585	6.031	2.795	2.16	2.96		
					38	2.890	3.925	5.180	6.673	8.413	10.409	12.664	15.177						
					43	2.581	3.527	4.681	6.059	7.674	9.535	11.646	14.008						
					46	2.407	3.297	4.388	5.697	7.236	9.015	11.038	13.308						
OP-MGRN121	114X5746	A02	MTZ072	E	27	3.638	4.859	6.329	8.062	10.069	12.353	14.918	17.759					82	51
					32	3.287	4.425	5.799	7.425	9.311	11.466	13.891	16.585	6.031	2.725	2.21	3.05		
					38	2.890	3.925	5.180	6.673	8.413	10.409	12.664	15.177						
					43	2.581	3.527	4.681	6.059	7.674	9.535	11.646	14.008						
					46	2.407	3.297	4.388	5.697	7.236	9.015	11.038	13.308						
OP-MCRN136	114X5747	A02	MTZ080	E	27	4.092	5.479	7.139	9.079	11.304	13.811	16.596	19.648					82	51
					32	3.672	4.959	6.507	8.324	10.415	12.779	15.412	18.307	6.770	3.181	2.13	2.97		
					38	3.211	4.371	5.778	7.441	9.367	11.555	14.003	16.704						
					43	2.867	3.916	5.200	6.730	8.513	10.550	12.840	15.376						
					46	2.680	3.659	4.867	6.315	8.010	9.955	12.149	14.584						
OP-MGRN136	114X5749	A02	MTZ080	E	27	4.092	5.479	7.139	9.079	11.304	13.811	16.596	19.648					82	51
					32	3.672	4.959	6.507	8.324	10.415	12.779	15.412	18.307	6.770	3.111	2.18	3.04		
					38	3.211	4.371	5.778	7.441	9.367	11.555	14.003	16.704						
					43	2.867	3.916	5.200	6.730	8.513	10.550	12.840	15.376						
					46	2.680	3.659	4.867	6.315	8.010	9.955	12.149	14.584						
OP-MGRN171	114X5750	A02	MTZ100	E	27	5.253	7.016	9.167	11.739	14.760	18.250	22.220	26.678					87	56
					32	4.783	6.433	8.439	10.838	13.659	16.925	20.651	24.846	8.765	4.429	1.98	2.74		
					38	4.224	5.744	7.582	9.778	12.363	15.364	18.799	22.679						
					43	3.758	5.174	6.877	8.907	11.300	14.083	17.278	20.899						
					46	3.477	4.832	6.456	8.389	10.668	13.322	16.374	19.839						
OP-MGRN215	114X5753	A02	MTZ125	E	27	6.924	9.080	11.714	14.868	18.575	22.853	27.709	33.140					86	55
					32	6.420	8.444	10.905	13.850	17.312	21.314	25.868	30.973	11.340	5.286	2.15	2.84		
					38	5.798	7.666	9.922	12.616	15.785	19.458	23.649	28.365						
					43	5.263	7.003	9.090	11.575	14.502	17.901	21.792	26.183						
					46	4.934	6.598	8.583	10.945	13.727	16.963	20.673	24.870						
OP-MGRN242	114X5754	A02	MTZ144	E	27	8.113	10.628	13.620	17.111	21.113	25.634	30.672	36.221					85	54
					32	7.369	9.716	12.516	15.791	19.559	23.825	28.592	33.853	13.020	6.110	2.13	2.84		
					38	6.531	8.666	11.226	14.236	17.713	21.667	26.102	31.013						
					43	5.885	7.836	10.189	12.969	16.197	19.885	24.036	28.650						
					46	5.523	7.359	9.584	12.224	15.300	18.824	22.803	27.236						
OP-MGRN271	114X5757	A02	MTZ160	E	27	9.259	12.001	15.239	18.994	23.277	28.091	33.431	39.282					84	53
					32	8.407	10.973	14.008	17.534	21.566	26.108	31.156	36.700	14.580	6.925	2.11	2.76		
					38	7.427	9.772	12.555	15.799	19.522	23.730	28.424	33.594						
					43	6.650	8.805	11.370	14.373	17.832	21.756	26.149	31.003						
					46	6.204	8.240	10.672	13.527	16.825	20.577	24.786	29.448						

MBP
(1) E - 400V-3ph-50Hz Compressor & 230V-1ph-50Hz Fan

G - 230V-1ph-50Hz Compressor & 230V-1ph-50Hz Fan

(2) Nominal conditions (EN13215), Evaporating temperatures at dew point, Superheat 10K, Subcooling 0K

(3) Rated conditions (EN13215), Evaporating temperature Midpoint -10°C, Ambient air temperature +32°C, Return Gas Temperature 20°C, Subcooling 0K

COP: Coefficient Of Performance link to EN13215 and ErP (Energy related Products) 2009/125/CE

SEPR: Seasonal Energy Performance Ratio link to EN13215 and ErP (Energy Related Products) 2009/125/CE

Tamb [°C]: Ambient Temperature

Te [°C]: Evaporating Temperature

Q [kW]: Cooling Capacity in Kilo Watt

P [kW]: Power Input in Kilo Watt

Version

A02: Receiver + Stop valves + KP17WB pressure switch + Electrical box


For regular updates and detailed capacities, please refer to **Coolselector®2** software


Model	Code	Version	Compressor	Electrical code (1)	Tamb [°C]	Cooling capacity Q [kW] (2)								EcoDesign (3)				Sound power level dB(A)	Sound pressure level 10 m dB(A)
						Te [°C]								Q [kW]	P [kW]	COP	SEPR		
						-25°C	-20°C	-15°C	-10°C	-5°C	0°C	5°C	10°C						
OP-MCRN030	114X5721	A02	MTZ018	E	27	0.918	1.309	1.764	2.282	2.863	3.506	4.206	4.962					76	45
					32	0.786	1.151	1.575	2.060	2.603	3.205	3.862	4.573	2.094	1.084	1.93			
					38	0.639	0.973	1.361	1.804	2.302	2.855	3.461	4.117						
					43	-	0.834	1.192	1.601	2.061	2.573	-	-						
					46	-	0.755	1.095	1.483	1.921	2.408	-	-						
OP-MCRN030	114X5722	A02	MTZ018	G	27	0.921	1.338	1.826	2.386	3.018	3.719	4.488	5.318					76	45
					32	0.790	1.185	1.646	2.174	2.768	3.428	4.151	4.933	2.212	1.139	1.94			
					38	0.626	0.994	1.422	1.910	2.460	3.071	3.740	4.464						
					43	-	0.831	1.230	1.686	2.198	2.767	-	-						
					46	-	0.732	1.114	1.549	2.039	2.584	-	-						
OP-MCRN038	114X5724 114X5790	A02 A14	MTZ022	E	27	1.399	1.814	2.309	2.886	3.546	4.286	5.100	5.984					74	43
					32	1.282	1.666	2.121	2.651	3.257	3.937	4.688	5.509	2.985	1.465	2.04			
					38	1.143	1.490	1.898	2.372	2.914	3.524	4.201	4.946						
					43	-	1.344	1.715	2.143	2.633	3.184	-	-						
					46	-	1.257	1.605	2.007	2.465	2.982	-	-						
OP-MCRN038	114X5723 114X5789	A02 A14	MTZ022	G	27	1.226	1.768	2.392	3.095	3.87	4.711	5.610	6.563					74	43
					32	1.050	1.561	2.147	2.806	3.532	4.319	5.163	6.055	3.207	1.537	2.09			
					38	0.834	1.309	1.850	2.457	3.125	3.849	4.625	5.444						
					43	-	1.097	1.602	2.166	2.786	3.459	-	-						
					46	-	0.970	1.453	1.992	2.584	3.225	-	-						
OP-MCRN048	114X5726 114X5792	A02 A14	MTZ028	E	27	1.804	2.362	3.044	3.862	4.823	5.929	7.182	8.581					74	43
					32	1.654	2.170	2.798	3.549	4.433	5.455	6.617	7.920	3.989	1.790	2.23			
					38	1.478	1.946	2.510	3.185	3.980	4.901	5.955	7.144						
					43	-	1.761	2.275	2.888	3.610	4.450	-	-						
					46	-	1.650	2.135	2.712	3.391	4.182	-	-						
OP-MCRN048	114X5728 114X5791	A02 A14	MTZ028	G	27	1.905	2.578	3.362	4.262	5.279	6.415	7.664	9.025					74	43
					32	1.719	2.355	3.094	3.940	4.895	5.960	7.135	8.417	4.425	1.926	2.30			
					38	1.497	2.088	2.771	3.551	4.431	5.413	6.496	7.682						
					43	-	1.865	2.501	3.225	4.042	4.953	-	-						
					46	-	1.732	2.339	3.029	3.807	4.675	-	-						
OP-MCRN054	114X5729	A02	MTZ032	E	27	2.119	2.753	3.517	4.419	5.467	6.663	8.004	9.486					74	43
					32	1.923	2.515	3.224	4.062	5.035	6.147	7.397	8.780	4.130	1.938	2.13			
					38	1.681	2.222	2.866	3.626	4.509	5.521	6.662	7.929						
					43	-	1.974	2.564	3.259	4.067	4.996	-	-						
					46	-	1.825	2.382	3.037	3.801	4.679	-	-						
OP-MCRN054	114X5731	A02	MTZ032	G	27	1.998	2.664	3.432	4.308	5.296	6.397	7.611	8.935					74	43
					32	1.796	2.435	3.166	3.996	4.930	5.968	7.113	8.363	4.065	2.042	1.99			
					38	1.543	2.147	2.832	3.606	4.474	5.438	6.500	7.660						
					43	-	1.898	2.545	3.271	4.083	4.985	-	-						
					46	-	1.746	2.369	3.066	3.845	4.709	-	-						

MBP
(1) E - 400V-3ph-50Hz Compressor & 230V-1ph-50Hz Fan

G - 230V-1ph-50Hz Compressor & 230V-1ph-50Hz Fan

(2) Nominal conditions (EN13215), Evaporating temperatures at dew point, Superheat 10K, Subcooling 0K

(3) Rated conditions (EN13215), Evaporating temperature Midpoint -10°C, Ambient air temperature +32°C, Return Gas Temperature 20°C, Subcooling 0K

COP: Coefficient Of Performance link to EN13215 and ErP (Energy related Products) 2009/125/CE

SEPR: Seasonal Energy Performance Ratio link to EN13215 and ErP (Energy Related Products) 2009/125/CE

Tamb [°C]: Ambient Temperature

Te [°C]: Evaporating Temperature

Q [kW]: Cooling Capacity in Kilo Watt

P [kW]: Power Input in Kilo Watt

Version

A02: Receiver + Stop valves + KP17WB pressure switch + Electrical box

A14: Filter drier + Sight glass + Receiver + Stop valves + KP17WB pressure switch + Electrical box

This table continues on the next page


For regular updates and detailed capacities, please refer to **Coolselector®2** software


Model	Code	Version	Compressor	Electrical code (1)	Tamb [°C]	Cooling capacity Q [kW] (2)								EcoDesign (3)				Sound power level dB(A)	Sound pressure level 10 m dB(A)
						Te [°C]								Q [kW]	P [kW]	COP	SEPR		
						-25°C	-20°C	-15°C	-10°C	-5°C	0°C	5°C	10°C						
OP-MCRN060	114X5732 114X5794	A02 A14	MTZ036	E	27	2.256	3.004	3.889	4.914	6.078	7.379	8.806	10.34					74	43
					32	2.059	2.756	3.579	4.531	5.612	6.820	8.146	9.574	5.098	2.458	2.07	2.93		
					38	1.824	2.458	3.204	4.066	5.045	6.140	7.344	8.644						
					43	-	2.211	2.893	3.679	4.573	5.575	-	-						
					46	-	2.064	2.707	3.449	4.292	5.239	-	-						
OP-MCRN060	114X5734 114X5793	A02 A14	MTZ036	G	27	2.274	3.022	3.881	4.856	5.948	7.158	8.479	9.906					74	43
					32	2.040	2.754	3.569	4.491	5.521	6.661	7.905	9.245	5.034	2.486	2.02	2.81		
					38	1.751	2.422	3.183	4.039	4.995	6.050	7.200	8.436						
					43	-	2.138	2.852	3.653	4.545	5.529	-	-						
					46	-	1.966	2.652	3.419	4.272	5.211	-	-						
OP-MCRN068	114X5735	A02	MTZ040	E	27	2.599	3.482	4.523	5.725	7.083	8.594	10.248	12.035					76	45
					32	2.362	3.185	4.155	5.274	6.540	7.951	9.497	11.170	5.368	2.740	1.96	2.79		
					38	2.087	2.834	3.716	4.734	5.888	7.176	8.592	10.126						
					43	-	2.548	3.354	4.286	5.346	6.530	-	-						
					46	-	2.380	3.139	4.019	5.020	6.143	-	-						
OP-MCRN086	114X5737 114X5795	A02 A14	MTZ050	E	27	2.891	3.974	5.276	6.805	8.567	10.560	12.770	15.210					84	53
					32	2.607	3.622	4.837	6.263	7.904	9.759	11.830	14.110	7.087	3.080	2.30	3.43		
					38	2.255	3.188	4.299	5.601	7.098	8.793	10.690	12.780						
					43	-	2.819	3.843	5.041	6.419	7.981	-	-						
					46	-	2.596	3.567	4.702	6.009	7.491	-	-						
OP-MCRN096	114X5739 114X5796	A02 A14	MTZ056	E	27	3.185	4.371	5.792	7.454	9.358	11.500	13.870	16.460					83	52
					32	2.871	3.983	5.308	6.856	8.628	10.620	12.830	15.250	7.761	3.392	2.29	3.40		
					38	2.483	3.505	4.715	6.126	7.741	9.558	11.570	13.790						
					43	-	3.098	4.214	5.511	6.995	8.666	-	-						
					46	-	2.852	3.910	5.139	6.545	8.129	-	-						
OP-MCRN108	114X5740 114X5797	A02 A14	MTZ064	E	27	3.816	5.141	6.695	8.481	10.500	12.740	15.190	17.830					83	52
					32	3.396	4.630	6.079	7.747	9.634	11.730	14.040	16.530	8.758	3.892	2.25	3.27		
					38	2.916	4.041	5.362	6.887	8.616	10.550	12.670	14.960						
					43	-	3.569	4.784	6.187	7.782	9.565	-	-						
					46	-	3.295	4.445	5.775	7.288	8.980	-	-						

MBP
(1) E - 400V-3ph-50Hz Compressor & 230V-1ph-50Hz Fan

G - 230V-1ph-50Hz Compressor & 230V-1ph-50Hz Fan

(2) Nominal conditions (EN13215), Evaporating temperatures at dew point, Superheat 10K, Subcooling 0K

(3) Rated conditions (EN13215), Evaporating temperature Midpoint -10°C, Ambient air temperature +32°C, Return Gas Temperature 20°C, Subcooling 0K

COP: Coefficient Of Performance link to EN13215 and ErP (Energy related Products) 2009/125/CE

SEPR: Seasonal Energy Performance Ratio link to EN13215 and ErP (Energy Related Products) 2009/125/CE

Tamb [°C]: Ambient Temperature

Te [°C]: Evaporating Temperature

Q [kW]: Cooling Capacity in Kilo Watt

P [kW]: Power Input in Kilo Watt

Version

A02: Receiver + Stop valves + KP17WB pressure switch + Electrical box

A14: Filter drier + Sight glass + Receiver + Stop valves + KP17WB pressure switch + Electrical box

This table continues on the next page


For regular updates and detailed capacities, please refer to **Coolselector®2** software


Model	Code	Version	Compressor	Electrical code (1)	Tamb [°C]	Cooling capacity Q [kW] (2)								EcoDesign (3)				Sound power level dB(A)	Sound pressure level 10 m dB(A)
						Te [°C]								Q [kW]	P [kW]	COP	SEPR		
						-25°C	-20°C	-15°C	-10°C	-5°C	0°C	5°C	10°C						
OP-MCRN121	114X5744	A02	MTZ072	E	27	4.353	5.852	7.600	9.594	11.823	14.275	16.932	19.771					82	51
					32	3.875	5.274	6.906	8.768	10.855	13.153	15.647	18.317	8.939	4.364	2.05	2.89		
					38	3.324	4.602	6.092	7.795	9.708	11.820	14.117	16.583						
					43	-	4.061	5.431	7.000	8.766	10.721	-	-						
					46	-	3.745	5.042	6.530	8.207	10.067	-	-						
OP-MGRN121	114X5746	A02	MTZ072	E	27	4.353	5.852	7.600	9.594	11.823	14.275	16.932	19.771					82	51
					32	3.875	5.274	6.906	8.768	10.855	13.153	15.647	18.317	8.939	4.294	2.08	3.08		
					38	3.324	4.602	6.092	7.795	9.708	11.820	14.117	16.583						
					43	-	4.061	5.431	7.000	8.766	10.721	-	-						
					46	-	3.745	5.042	6.530	8.207	10.067	-	-						
OP-MCRN136	114X5747	A02	MTZ080	E	27	5.265	6.880	8.748	10.863	13.211	15.773	18.522	21.432					82	51
					32	4.779	6.290	8.034	10.007	12.198	14.589	17.159	19.882	10.221	5.194	1.97	2.95		
					38	4.198	5.580	7.173	8.974	10.974	13.161	15.515	18.013						
					43	-	4.991	6.454	8.109	9.950	11.965	-	-						
					46	-	4.639	6.024	7.590	9.334	11.246	-	-						
OP-MGRN136	114X5749	A02	MTZ080	E	27	5.265	6.880	8.748	10.863	13.211	15.773	18.522	21.432					82	51
					32	4.779	6.290	8.034	10.007	12.198	14.589	17.159	19.882	10.221	5.124	2.00	2.78		
					38	4.198	5.580	7.173	8.974	10.974	13.161	15.515	18.013						
					43	-	4.991	6.454	8.109	9.950	11.965	-	-						
					46	-	4.639	6.024	7.590	9.334	11.246	-	-						
OP-MGRN171	114X5750	A02	MTZ100	E	27	6.111	8.292	10.912	13.990	17.536	21.552	26.030	30.956					87	56
					32	5.463	7.486	9.918	12.781	16.087	19.841	24.039	28.670	12.988	6.306	2.06	3.01		
					38	4.717	6.555	8.764	11.370	14.390	17.831	21.693	25.970						
					43	-	5.806	7.832	10.226	13.008	16.189	-	-						
					46	-	5.369	7.285	9.553	12.193	15.218	-	-						
OP-MGRN215	114X5753	A02	MTZ125	E	27	8.003	10.804	14.133	17.999	22.397	27.312	32.717	38.581					86	55
					32	7.154	9.756	12.850	16.450	20.555	25.153	30.224	35.738	16.750	8.020	2.09	2.99		
					38	6.176	8.538	11.351	14.630	18.382	22.600	27.268	32.362						
					43	-	7.557	10.134	13.147	16.604	20.504	-	-						
					46	-	6.983	9.419	12.271	15.551	19.261	-	-						
OP-MGRN242	114X5754	A02	MTZ144	E	27	9.911	12.849	16.247	20.108	24.420	29.164	34.312	39.831					85	54
					32	8.913	11.656	14.827	18.433	22.467	26.914	31.751	36.945	18.790	9.244	2.03	2.86		
					38	7.769	10.282	13.183	16.484	20.185	24.275	28.734	33.538						
					43	-	9.180	11.859	14.908	18.331	22.123	-	-						
					46	-	8.535	11.083	13.982	17.239	20.851	-	-						
OP-MGRN271	114X5757	A02	MTZ160	E	27	11.163	14.432	18.191	22.434	27.139	32.278	37.811	43.693					84	53
					32	10.041	13.095	16.602	20.563	24.962	29.774	34.965	40.493	20.980	10.582	1.98	2.74		
					38	8.751	11.551	14.762	18.387	22.418	26.837	31.615	36.716						
					43	-	10.309	13.277	16.625	20.352	24.443	-	-						
					46	-	9.581	12.405	15.589	19.133	23.028	-	-						

MBP
(1) E - 400V-3ph-50Hz Compressor & 230V-1ph-50Hz Fan

G - 230V-1ph-50Hz Compressor & 230V-1ph-50Hz Fan

(2) Nominal conditions (EN13215), Evaporating temperatures at dew point, Superheat 10K, Subcooling 0K

(3) Rated conditions (EN13215), Evaporating temperature Midpoint -10°C, Ambient air temperature +32°C, Return Gas Temperature 20°C, Subcooling 0K

COP: Coefficient Of Performance link to EN13215 and ErP (Energy related Products) 2009/125/CE

SEPR: Seasonal Energy Performance Ratio link to EN13215 and ErP (Energy Related Products) 2009/125/CE

Tamb [°C]: Ambient Temperature

Te [°C]: Evaporating Temperature

Q [kW]: Cooling Capacity in Kilo Watt

P [kW]: Power Input in Kilo Watt

Version

A02: Receiver + Stop valves + KP17WB pressure switch + Electrical box


For regular updates and detailed capacities, please refer to **Coolselector®2** software


Model	Code	Version	Compressor	Electrical code (1)	Tamb [°C]	Cooling capacity Q [kW] (2)								EcoDesign (3)				Sound power level dB(A)	Sound pressure level 10 m dB(A)
						Te [°C]								Q [kW]	P [kW]	COP	SEPR		
						-25°C	-20°C	-15°C	-10°C	-5°C	0°C	5°C	10°C						
OP-MCRN030	114X5721	A02	MTZ018	E	27	0.918	1.309	1.764	2.282	2.863	3.506	4.206	4.962					76	45
					32	0.786	1.151	1.575	2.060	2.603	3.205	3.862	4.573	2.097	1.084	1.94			
					38	0.639	0.973	1.361	1.804	2.302	2.855	3.461	4.117						
					43	-	0.834	1.192	1.601	2.061	2.573	-	-						
					46	-	0.755	1.095	1.483	1.921	2.408	-	-						
OP-MCRN030	114X5722	A02	MTZ018	G	27	0.921	1.338	1.826	2.386	3.018	3.719	4.488	5.318					76	45
					32	0.790	1.185	1.646	2.174	2.768	3.428	4.151	4.933	2.215	1.139	1.95			
					38	0.626	0.994	1.422	1.910	2.460	3.071	3.740	4.464						
					43	-	0.831	1.230	1.686	2.198	2.767	-	-						
					46	-	0.732	1.114	1.549	2.039	2.584	-	-						
OP-MCRN038	114X5724 114X5790	A02 A14	MTZ022	E	27	1.398	1.812	2.307	2.883	3.544	4.283	5.094	5.973					74	43
					32	1.281	1.664	2.118	2.647	3.251	3.933	4.683	5.497	2.969	1.462	2.03			
					38	1.142	1.488	1.896	2.369	2.909	3.521	4.197	4.932						
					43	-	1.343	1.712	2.139	2.627	3.183	-	-						
					46	-	1.255	1.602	2.002	2.459	2.982	-	-						
OP-MCRN038	114X5723 114X5789	A02 A14	MTZ022	G	27	1.225	1.766	2.389	3.091	3.864	4.703	5.601	6.551					74	43
					32	1.049	1.559	2.144	2.801	3.526	4.312	5.152	6.042	3.187	1.533	2.08			
					38	0.833	1.306	1.847	2.452	3.118	3.841	4.614	5.43						
					43	-	1.095	1.599	2.161	2.780	3.450	-	-						
					46	-	0.968	1.450	1.987	2.578	3.216	-	-						
OP-MCRN048	114X5726 114X5792	A02 A14	MTZ028	E	27	1.803	2.361	3.042	3.862	4.823	5.929	7.179	8.574					74	43
					32	1.654	2.169	2.796	3.546	4.432	5.454	6.613	7.912	3.966	1.786	2.22			
					38	1.477	1.944	2.508	3.182	3.976	4.899	5.951	7.134						
					43	-	1.760	2.273	2.885	3.606	4.448	-	-						
					46	-	1.649	2.133	2.709	3.387	4.181	-	-						
OP-MCRN048	114X5728 114X5791	A02 A14	MTZ028	G	27	1.904	2.576	3.36	4.260	5.279	6.415	7.664	9.022					74	43
					32	1.718	2.354	3.092	3.937	4.893	5.960	7.133	8.410	4.400	1.922	2.29			
					38	1.496	2.086	2.769	3.548	4.426	5.409	6.491	7.672						
					43	-	1.864	2.499	3.222	4.037	4.946	-	-						
					46	-	1.730	2.336	3.026	3.802	4.668	-	-						
OP-MCRN054	114X5729	A02	MTZ032	E	27	2.119	2.753	3.517	4.419	5.467	6.663	8.004	9.486					74	43
					32	1.923	2.515	3.224	4.062	5.035	6.147	7.397	8.780	4.136	1.938	2.13			
					38	1.681	2.222	2.866	3.626	4.509	5.521	6.662	7.929						
					43	-	1.974	2.564	3.259	4.067	4.996	-	-						
					46	-	1.825	2.382	3.037	3.801	4.679	-	-						
OP-MCRN054	114X5731	A02	MTZ032	G	27	1.998	2.664	3.432	4.308	5.296	6.397	7.611	8.935					74	43
					32	1.796	2.435	3.166	3.996	4.930	5.968	7.113	8.363	4.071	2.042	1.99			
					38	1.543	2.147	2.832	3.606	4.474	5.438	6.500	7.660						
					43	-	1.898	2.545	3.271	4.083	4.985	-	-						
					46	-	1.746	2.369	3.066	3.845	4.709	-	-						

MBP
(1) E - 400V-3ph-50Hz Compressor & 230V-1ph-50Hz Fan

G - 230V-1ph-50Hz Compressor & 230V-1ph-50Hz Fan

(2) Nominal conditions (EN13215), Evaporating temperatures at dew point, Superheat 10K, Subcooling 0K

(3) Rated conditions (EN13215), Evaporating temperature Midpoint -10°C, Ambient air temperature +32°C, Return Gas Temperature 20°C, Subcooling 0K

COP: Coefficient Of Performance link to EN13215 and ErP (Energy related Products) 2009/125/CE

SEPR: Seasonal Energy Performance Ratio link to EN13215 and ErP (Energy Related Products) 2009/125/CE

Tamb [°C]: Ambient Temperature

Te [°C]: Evaporating Temperature

Q [kW]: Cooling Capacity in Kilo Watt

P [kW]: Power Input in Kilo Watt

Version

A02: Receiver + Stop valves + KP17WB pressure switch + Electrical box

A14: Filter drier + Sight glass + Receiver + Stop valves + KP17WB pressure switch + Electrical box

This table continues on the next page


For regular updates and detailed capacities, please refer to **Coolselector®2** software


Model	Code	Version	Compressor	Electrical code (1)	Tamb [°C]	Cooling capacity Q [kW] (2)								EcoDesign (3)				Sound power level dB(A)	Sound pressure level 10 m dB(A)
						Te [°C]								Q [kW]	P [kW]	COP	SEPR		
						-25°C	-20°C	-15°C	-10°C	-5°C	0°C	5°C	10°C						
OP-MCRN060	114X5732 114X5794	A02 A14	MTZ036	E	27	2.255	3.002	3.889	4.914	6.075	7.371	8.796	10.330					74	43
					32	2.058	2.754	3.576	4.526	5.606	6.812	8.135	9.559	5.069	2.452	2.07	2.93		
					38	1.822	2.456	3.201	4.062	5.042	6.134	7.333	8.631						
					43	-	2.209	2.889	3.676	4.572	5.573	-	-						
					46	-	2.062	2.703	3.445	4.291	5.237	-	-						
OP-MCRN060	114X5734 114X5793	A02 A14	MTZ036	G	27	2.273	3.02	3.878	4.852	5.946	7.155	8.477	9.906					74	43
					32	2.039	2.752	3.566	4.486	5.517	6.656	7.900	9.245	5.007	2.481	2.02	2.80		
					38	1.749	2.419	3.179	4.034	4.989	6.042	7.192	8.436						
					43	-	2.135	2.848	3.648	4.538	5.520	-	-						
					46	-	1.963	2.647	3.413	4.264	5.202	-	-						
OP-MCRN068	114X5735	A02	MTZ040	E	27	2.599	3.482	4.523	5.725	7.083	8.594	10.248	12.035					76	45
					32	2.362	3.185	4.155	5.274	6.540	7.951	9.497	11.170	5.376	2.740	1.96	2.79		
					38	2.087	2.834	3.716	4.734	5.888	7.176	8.592	10.126						
					43	-	2.548	3.354	4.286	5.346	6.530	-	-						
					46	-	2.380	3.139	4.019	5.020	6.143	-	-						
OP-MCRN086	114X5737 114X5795	A02 A14	MTZ050	E	27	2.891	3.974	5.276	6.805	8.567	10.56	12.77	15.200					84	53
					32	2.605	3.619	4.834	6.259	7.901	9.759	11.83	14.100	7.043	3.072	2.29	3.43		
					38	2.253	3.185	4.295	5.595	7.092	8.790	10.69	12.770						
					43	-	2.816	3.838	5.034	6.411	7.977	-	-						
					46	-	2.592	3.562	4.695	6.001	7.487	-	-						
OP-MCRN096	114X5739 114X5796	A02 A14	MTZ056	E	27	3.183	4.369	5.789	7.451	9.355	11.500	13.860	16.450					83	52
					32	2.869	3.979	5.303	6.849	8.619	10.610	12.820	15.230	7.714	3.383	2.28	3.39		
					38	2.481	3.501	4.710	6.119	7.731	9.545	11.560	13.770						
					43	-	3.095	4.208	5.503	6.984	8.652	-	-						
					46	-	2.848	3.904	5.130	6.533	8.115	-	-						
OP-MCRN108	114X5740 114X5797	A02 A14	MTZ064	E	27	3.813	5.139	6.692	8.473	10.49	12.720	15.170	17.810					83	52
					32	3.392	4.628	6.076	7.738	9.621	11.720	14.020	16.510	8.707	3.882	2.24	3.26		
					38	2.912	4.036	5.355	6.877	8.603	10.530	12.650	14.930						
					43	-	3.564	4.777	6.177	7.768	9.547	-	-						
					46	-	3.290	4.438	5.764	7.273	8.960	-	-						
OP-MGRN108	114X5743	A02	MTZ064	E	27	3.849	5.190	6.762	8.566	10.599	12.851	15.312	17.964					83	52
					32	3.427	4.679	6.147	7.834	9.737	11.850	14.162	16.659	7.990	3.684	2.17	3.08		
					38	2.941	4.084	5.425	6.970	8.716	10.660	12.793	15.101						
					43	-	3.605	4.839	6.263	7.877	9.678	-	-						
					46	-	3.326	4.494	5.845	7.379	9.094	-	-						

MBP

(1) E - 400V-3ph-50Hz Compressor & 230V-1ph-50Hz Fan
G - 230V-1ph-50Hz Compressor & 230V-1ph-50Hz Fan

(2) Nominal conditions (EN13215), Evaporating temperatures at dew point, Superheat 10K, Subcooling 0K

(3) Rated conditions (EN13215), Evaporating temperature Midpoint -10°C, Ambient air temperature +32°C, Return Gas Temperature 20°C, Subcooling 0K

COP: Coefficient Of Performance link to EN13215 and ErP (Energy related Products) 2009/125/CE

SEPR: Seasonal Energy Performance Ratio link to EN13215 and ErP (Energy Related Products) 2009/125/CE

Tamb [°C]: Ambient Temperature

Te [°C]: Evaporating Temperature

Q [kW]: Cooling Capacity in Kilo Watt

P [kW]: Power Input in Kilo Watt

Version

A02: Receiver + Stop valves + KP17WB pressure switch + Electrical box

A14: Filter drier + Sight glass + Receiver + Stop valves + KP17WB pressure switch + Electrical box

This table continues on the next page



For regular updates and detailed capacities, please refer to **Coolselector®2** software



Model	Code	Version	Compressor	Electrical code (1)	Tamb [°C]	Cooling capacity Q [kW] (2)								EcoDesign (3)				Sound power level dB(A)	Sound pressure level 10 m dB(A)
						Te [°C]								Q [kW]	P [kW]	COP	SEPR		
						-25°C	-20°C	-15°C	-10°C	-5°C	0°C	5°C	10°C						
OP-MCRN121	114X5744	A02	MTZ072	E	27	4.353	5.852	7.600	9.594	11.823	14.275	16.932	19.771					82	51
					32	3.875	5.274	6.906	8.768	10.855	13.153	15.647	18.317	8.952	4.364	2.05	2.89		
					38	3.324	4.602	6.092	7.795	9.708	11.820	14.117	16.583						
					43	-	4.061	5.431	7.000	8.766	10.721	-	-						
					46	-	3.745	5.042	6.530	8.207	10.067	-	-						
OP-MGRN121	114X5746	A02	MTZ072	E	27	4.353	5.852	7.600	9.594	11.823	14.275	16.932	19.771					82	51
					32	3.875	5.274	6.906	8.768	10.855	13.153	15.647	18.317	8.952	4.294	2.08	2.95		
					38	3.324	4.602	6.092	7.795	9.708	11.820	14.117	16.583						
					43	-	4.061	5.431	7.000	8.766	10.721	-	-						
					46	-	3.745	5.042	6.530	8.207	10.067	-	-						
OP-MCRN136	114X5747	A02	MTZ080	E	27	5.265	6.880	8.748	10.863	13.211	15.773	18.522	21.432					82	51
					32	4.779	6.290	8.034	10.007	12.198	14.589	17.159	19.882	10.240	5.194	1.97	2.74		
					38	4.198	5.580	7.173	8.974	10.974	13.161	15.515	18.013						
					43	-	4.991	6.454	8.109	9.950	11.965	-	-						
					46	-	4.639	6.024	7.590	9.334	11.246	-	-						
OP-MGRN136	114X5749	A02	MTZ080	E	27	5.265	6.880	8.748	10.863	13.211	15.773	18.522	21.432					82	51
					32	4.779	6.290	8.034	10.007	12.198	14.589	17.159	19.882	10.240	5.124	2.00	2.79		
					38	4.198	5.580	7.173	8.974	10.974	13.161	15.515	18.013						
					43	-	4.991	6.454	8.109	9.950	11.965	-	-						
					46	-	4.639	6.024	7.590	9.334	11.246	-	-						
OP-MGRN171	114X5750	A02	MTZ100	E	27	6.111	8.292	10.912	13.990	17.536	21.552	26.030	30.956					87	56
					32	5.463	7.486	9.918	12.781	16.087	19.841	24.039	28.670	13.010	6.306	2.06	3.01		
					38	4.717	6.555	8.764	11.370	14.390	17.831	21.693	25.970						
					43	-	5.806	7.832	10.226	13.008	16.189	-	-						
					46	-	5.369	7.285	9.553	12.193	15.218	-	-						
OP-MGRN215	114X5753	A02	MTZ125	E	27	8.003	10.804	14.133	17.999	22.397	27.312	32.717	38.581					86	55
					32	7.154	9.756	12.850	16.450	20.555	25.153	30.224	35.738	16.770	8.021	2.09	2.99		
					38	6.176	8.538	11.351	14.630	18.382	22.600	27.268	32.362						
					43	-	7.557	10.134	13.147	16.604	20.504	-	-						
					46	-	6.983	9.419	12.271	15.551	19.261	-	-						
OP-MGRN242	114X5754	A02	MTZ144	E	27	9.911	12.849	16.247	20.108	24.420	29.164	34.312	39.831					85	54
					32	8.913	11.656	14.827	18.433	22.467	26.914	31.751	36.945	18.810	9.244	2.04	2.86		
					38	7.769	10.282	13.183	16.484	20.185	24.275	28.734	33.538						
					43	-	9.180	11.859	14.908	18.331	22.123	-	-						
					46	-	8.535	11.083	13.982	17.239	20.851	-	-						
OP-MGRN271	114X5757	A02	MTZ160	E	27	11.163	14.432	18.191	22.434	27.139	32.278	37.811	43.693					84	53
					32	10.041	13.095	16.602	20.563	24.962	29.774	34.965	40.493	21.010	10.580	1.99	2.74		
					38	8.751	11.551	14.762	18.387	22.418	26.837	31.615	36.716						
					43	-	10.309	13.277	16.625	20.352	24.443	-	-						
					46	-	9.581	12.405	15.589	19.133	23.028	-	-						

MBP
(1) E - 400V-3ph-50Hz Compressor & 230V-1ph-50Hz Fan

G - 230V-1ph-50Hz Compressor & 230V-1ph-50Hz Fan

(2) Nominal conditions (EN13215), Evaporating temperatures at dew point, Superheat 10K, Subcooling 0K

(3) Rated conditions (EN13215), Evaporating temperature Midpoint -10°C, Ambient air temperature +32°C, Return Gas Temperature 20°C, Subcooling 0K

COP: Coefficient Of Performance link to EN13215 and ErP (Energy related Products) 2009/125/CE

SEPR: Seasonal Energy Performance Ratio link to EN13215 and ErP (Energy Related Products) 2009/125/CE

Tamb [°C]: Ambient Temperature

Te [°C]: Evaporating Temperature

Q [kW]: Cooling Capacity in Kilo Watt

P [kW]: Power Input in Kilo Watt

Version

A02: Receiver + Stop valves + KP17WB pressure switch + Electrical box


For regular updates and detailed capacities, please refer to **Coolselector®2** software


Model	Code	Version	Compressor	Electrical code (1)	Tamb [°C]	Cooling capacity Q [kW] (2)								EcoDesign (3)				Sound power level dB(A)	Sound pressure level 10 m dB(A)
						Te [°C]								Q [kW]	P [kW]	COP	SEPR		
						-25°C	-20°C	-15°C	-10°C	-5°C	0°C	5°C	10°C						
OP-MCRN030	114X5721	A02	MTZ018	E	27	1.122	1.519	1.987	2.526	3.139	3.821	4.572	5.387					76	45
					32	0.977	1.346	1.778	2.278	2.844	3.477	4.174	4.932	2.377	1.188	2.00			
					38	0.806	1.140	1.531	1.981	2.493	3.066	3.699	4.390						
					43	0.666	0.972	1.327	1.737	2.203	2.726	-	-						
					46	0.584	0.872	1.207	1.592	2.031	2.523	-	-						
OP-MCRN030	114X5722	A02	MTZ018	G	27	1.038	1.467	1.967	2.538	3.179	3.888	4.659	5.488					76	45
					32	0.900	1.303	1.771	2.303	2.900	3.559	4.277	5.050	2.404	1.166	2.06			
					38	0.730	1.101	1.528	2.013	2.555	3.155	3.809	4.514						
					43	0.588	0.929	1.321	1.766	2.263	2.812	-	-						
					46	0.503	0.827	1.197	1.616	2.086	2.605	-	-						
OP-MCRN038	114X5724 114X5790	A02 A14	MTZ022	E	27	1.599	2.077	2.626	3.247	3.939	4.697	5.514	6.385					74	43
					32	1.423	1.866	2.372	2.940	3.578	4.278	5.033	5.84	3.313	1.577	2.10			
					38	1.218	1.617	2.072	2.580	3.152	3.781	4.462	5.190						
					43	1.054	1.416	1.828	2.288	2.802	3.372	-	-						
					46	0.959	1.299	1.686	2.118	2.595	3.128	-	-						
OP-MCRN038	114X5723 114X5789	A02 A14	MTZ022	G	27	1.275	1.783	2.370	3.036	3.779	4.595	5.473	6.394					74	43
					32	1.104	1.580	2.126	2.742	3.429	4.181	4.991	5.840	3.110	1.487	2.09			
					38	0.896	1.332	1.827	2.384	3.002	3.680	4.409	5.182						
					43	0.724	1.124	1.577	2.084	2.646	3.262	-	-						
					46	0.622	1.001	1.428	1.905	2.434	3.012	-	-						
OP-MCRN048	114X5726 114X5792	A02 A14	MTZ028	E	27	2.048	2.573	3.221	4.007	4.942	6.031	7.284	8.735					74	43
					32	1.883	2.368	2.963	3.683	4.536	5.533	6.68	8.003	4.102	1.923	2.13			
					38	1.676	2.108	2.636	3.274	4.030	4.919	5.949	7.115						
					43	1.496	1.883	2.354	2.921	3.597	4.397	-	-						
					46	1.387	1.746	2.181	2.708	3.335	4.078	-	-						
OP-MCRN048	114X5728 114X5791	A02 A14	MTZ028	G	27	1.714	2.384	3.175	4.094	5.144	6.326	7.634	9.052					74	43
					32	1.475	2.111	2.856	3.715	4.694	5.792	7.005	8.318	4.178	1.900	2.20			
					38	1.188	1.781	2.466	3.250	4.138	5.133	6.230	7.417						
					43	0.953	1.505	2.137	2.856	3.667	4.574	-	-						
					46	0.815	1.342	1.94	2.619	3.383	4.236	-	-						
OP-MCRN054	114X5729	A02	MTZ032	E	27	2.274	2.951	3.751	4.680	5.739	6.927	8.240	9.671					74	43
					32	2.040	2.669	3.411	4.270	5.250	6.349	7.565	8.893	4.459	2.118	2.10			
					38	1.752	2.323	2.992	3.766	4.648	5.640	6.740	7.944						
					43	1.510	2.029	2.636	3.337	4.138	5.039	-	-						
					46	1.365	1.852	2.420	3.077	3.828	4.675	-	-						
OP-MCRN054	114X5731	A02	MTZ032	G	27	1.973	2.720	3.589	4.587	5.715	6.974	8.361	9.872					74	43
					32	1.680	2.381	3.196	4.132	5.190	6.373	7.678	9.101	4.310	2.085	2.07			
					38	1.339	1.983	2.731	3.590	4.563	5.651	6.856	8.172						
					43	1.067	1.661	2.351	3.143	4.043	5.052	-	-						
					46	0.910	1.473	2.127	2.879	3.734	4.694	-	-						

MBP
(1) E - 400V-3ph-50Hz Compressor & 230V-1ph-50Hz Fan

G - 230V-1ph-50Hz Compressor & 230V-1ph-50Hz Fan

(2) Nominal conditions (EN13215), Evaporating temperatures at dew point, Superheat 10K, Subcooling 0K

(3) Rated conditions (EN13215), Evaporating temperature Midpoint -10°C, Ambient air temperature +32°C, Return Gas Temperature 20°C, Subcooling 0K

COP: Coefficient Of Performance link to EN13215 and ErP (Energy related Products) 2009/125/CE

SEPR: Seasonal Energy Performance Ratio link to EN13215 and ErP (Energy Related Products) 2009/125/CE

Tamb [°C]: Ambient Temperature

Te [°C]: Evaporating Temperature

Q [kW]: Cooling Capacity in Kilo Watt

P [kW]: Power Input in Kilo Watt

Version

A02: Receiver + Stop valves + KP17WB pressure switch + Electrical box

A14: Filter drier + Sight glass + Receiver + Stop valves + KP17WB pressure switch + Electrical box

This table continues on the next page


For regular updates and detailed capacities, please refer to **Coolselector®2** software


Model	Code	Version	Compressor	Electrical code (1)	Tamb [°C]	Cooling capacity Q [kW] (2)								EcoDesign (3)				Sound power level dB(A)	Sound pressure level 10 m dB(A)
						Te [°C]								Q [kW]	P [kW]	COP	SEPR		
						-25°C	-20°C	-15°C	-10°C	-5°C	0°C	5°C	10°C						
OP-MCRN060	114X5732 114X5794	A02 A14	MTZ036	E	27	2.556	3.252	4.084	5.058	6.174	7.434	8.841	10.410					74	43
					32	2.335	2.986	3.758	4.655	5.680	6.831	8.109	9.520	5.206	2.637	1.97	2.75		
					38	2.054	2.640	3.331	4.132	5.043	6.067	7.215	8.474						
					43	1.812	2.338	2.959	3.678	4.496	5.419								
					46	1.664	2.154	2.733	3.404	4.171	5.033	-	-						
OP-MCRN060	114X5734 114X5793	A02 A14	MTZ036	G	27	2.253	3.153	4.197	5.388	6.721	8.192	9.784	11.470					74	43
					32	1.955	2.797	3.768	4.871	6.105	7.463	8.934	10.490	5.514	2.634	2.09	2.90		
					38	1.591	2.361	3.243	4.241	5.353	6.578	7.904	9.3170						
					43	1.287	1.996	2.803	3.712	4.724	5.839	-	-						
					46	1.107	1.778	2.539	3.395	4.348	5.397	-	-						
OP-MCRN068	114X5735	A02	MTZ040	E	27	2.989	3.839	4.857	6.051	7.422	8.968	10.681	12.549					76	45
					32	2.751	3.542	4.484	5.584	6.847	8.270	9.848	11.571	5.839	2.995	1.95	2.75		
					38	2.440	3.155	4.001	4.986	6.115	7.390	8.806	10.356						
					43	2.163	2.811	3.573	4.459	5.475	6.625	-	-						
					46	1.992	2.597	3.307	4.132	5.080	6.153	-	-						
OP-MCRN086	114X5737 114X5795	A02 A14	MTZ050	E	27	3.355	4.500	5.868	7.454	9.256	11.270	13.51	16.000					84	53
					32	3.020	4.092	5.367	6.841	8.512	10.380	12.46	14.760	7.662	3.290	2.33	3.03		
					38	2.602	3.579	4.736	6.069	7.578	9.269	11.15	13.230						
					43	2.243	3.137	4.191	5.404	6.776	8.315	-	-						
					46	2.025	2.868	3.859	4.998	6.287	7.732	-	-						
OP-MCRN096	114X5739 114X5796	A02 A14	MTZ056	E	27	3.692	4.950	6.445	8.173	10.13	12.300	14.690	17.350					83	52
					32	3.323	4.499	5.890	7.492	9.298	11.300	13.520	15.980	8.407	3.619	2.32	3.05		
					38	2.862	3.932	5.193	6.639	8.266	10.070	12.070	14.290						
					43	2.466	3.445	4.592	5.905	7.381	9.017	-	-						
					46	2.224	3.148	4.226	5.458	6.844	8.380	-	-						
OP-MCRN108	114X5740 114X5797	A02 A14	MTZ064	E	27	4.432	5.820	7.445	9.292	11.360	13.630	16.110	18.830					83	52
					32	3.947	5.238	6.743	8.457	10.370	12.480	14.790	17.330	9.505	4.141	2.30	3.01		
					38	3.374	4.544	5.908	7.456	9.187	11.100	13.190	15.510						
					43	2.905	3.978	5.219	6.627	8.201	9.939	-	-						
					46	2.632	3.644	4.809	6.132	7.611	9.244	-	-						
OP-MGRN108	114X5743	A02	MTZ064	E	27	4.474	5.874	7.501	9.357	11.436	13.731	16.227	18.907					83	52
					32	3.988	5.295	6.809	8.533	10.466	12.601	14.926	17.426	8.923	4.012	2.22	2.90		
					38	3.415	4.603	5.975	7.537	9.289	11.227	13.343	15.624						
					43	2.946	4.029	5.279	6.701	8.298	10.069	-	-						
					46	2.669	3.687	4.861	6.197	7.700	9.369	-	-						

MBP
(1) E - 400V-3ph-50Hz Compressor & 230V-1ph-50Hz Fan

G - 230V-1ph-50Hz Compressor & 230V-1ph-50Hz Fan

(2) Nominal conditions (EN13215), Evaporating temperatures at dew point, Superheat 10K, Subcooling 0K

(3) Rated conditions (EN13215), Evaporating temperature Midpoint -10°C, Ambient air temperature +32°C, Return Gas Temperature 20°C, Subcooling 0K

COP: Coefficient Of Performance link to EN13215 and ErP (Energy related Products) 2009/125/CE

SEPR: Seasonal Energy Performance Ratio link to EN13215 and ErP (Energy Related Products) 2009/125/CE

Tamb [°C]: Ambient Temperature

Te [°C]: Evaporating Temperature

Q [kW]: Cooling Capacity in Kilo Watt

P [kW]: Power Input in Kilo Watt

Version

A02: Receiver + Stop valves + KP17WB pressure switch + Electrical box

A14: Filter drier + Sight glass + Receiver + Stop valves + KP17WB pressure switch + Electrical box

This table continues on the next page


For regular updates and detailed capacities, please refer to **Coolselector®2** software


Model	Code	Version	Compressor	Electrical code (1)	Tamb [°C]	Cooling capacity Q [kW] (2)								EcoDesign (3)				Sound power level dB(A)	Sound pressure level 10 m dB(A)
						Te [°C]								Q [kW]	P [kW]	COP	SEPR		
						-25°C	-20°C	-15°C	-10°C	-5°C	0°C	5°C	10°C						
OP-MCRN121	114X5744	A02	MTZ072	E	27	5.061	6.629	8.441	10.492	12.775	15.274	17.970	20.840					82	51
					32	4.507	9.740	7.653	9.557	11.676	13.996	16.503	19.175	10.010	4.746	2.11	2.77		
					38	3.855	5.182	6.705	8.426	10.343	12.445	14.720	17.151						
					43	3.323	4.531	5.915	7.479	9.221	11.138	-	-						
					46	3.009	4.143	5.441	6.908	8.545	10.347	-	-						
OP-MGRN121	114X5746	A02	MTZ072	E	27	5.061	6.629	8.441	10.492	12.775	15.274	17.970	20.840					82	51
					32	4.507	5.969	7.653	9.557	11.676	13.996	16.503	19.175	10.010	4.676	2.14	2.81		
					38	3.855	5.182	6.705	8.426	10.343	12.445	14.720	17.151						
					43	3.323	4.531	5.915	7.479	9.221	11.138	-	-						
					46	3.009	4.143	5.441	6.908	8.545	10.347	-	-						
OP-MCRN136	114X5747	A02	MTZ080	E	27	5.656	7.221	9.034	11.094	13.396	15.927	18.670	21.602					82	51
					32	5.133	6.596	8.282	10.195	12.330	14.677	17.221	19.943	10.680	5.378	1.99	2.58		
					38	4.492	5.823	7.350	9.078	11.006	13.127	15.430	17.899						
					43	3.947	5.161	6.549	8.118	9.869	11.798	-	-						
					46	3.617	4.757	6.059	7.529	9.172	10.984	-	-						
OP-MGRN136	114X5749	A02	MTZ080	E	27	5.599	7.138	8.913	10.923	13.157	15.601	18.235	21.033					82	51
					32	5.078	6.515	8.165	10.027	12.095	14.358	16.796	19.390	10.520	5.348	1.97	2.57		
					38	4.439	5.745	7.236	8.915	10.779	12.819	15.021	17.368						
					43	3.898	5.086	6.439	7.960	9.649	11.501	-	-						
					46	3.569	4.685	5.952	7.376	8.958	10.694	-	-						
OP-MGRN171	114X5750	A02	MTZ100	E	27	7.193	9.480	12.193	15.348	18.949	22.995	27.472	32.361					87	56
					32	6.450	8.580	11.096	14.016	17.351	21.100	25.257	29.806	14.630	6.795	2.15	3.10		
					38	5.553	7.494	9.773	12.412	15.425	18.818	22.590	26.730						
					43	4.797	6.582	8.663	11.067	13.812	16.908	-	-						
					46	4.340	6.030	7.992	10.255	12.840	15.759	-	-						
OP-MGRN215	114X5753	A02	MTZ125	E	27	9.170	12.040	15.402	19.263	23.908	28.437	33.704	39.377					86	55
					32	8.199	10.872	13.992	17.570	21.603	26.077	30.970	36.252	18.370	8.683	2.12	3.10		
					38	7.035	9.464	12.287	15.520	19.166	23.218	27.661	32.470						
					43	6.066	8.286	10.856	13.797	17.117	20.814	-	-						
					46	5.486	7.578	9.994	12.758	15.880	19.364	-	-						
OP-MGRN242	114X5754	A02	MTZ144	E	27	11.122	13.934	17.174	20.852	24.963	29.495	34.425	39.723					85	54
					32	9.989	12.605	15.615	19.032	22.856	27.079	31.684	36.646	19.920	10.070	1.98	3.01		
					38	8.658	11.029	13.754	16.848	20.319	24.165	28.373	32.924						
					43	7.570	9.730	12.209	15.028	18.199	21.723	-	-						
					46	6.926	8.956	11.285	13.936	16.924	20.253	-	-						
OP-MGRN271	114X5757	A02	MTZ160	E	27	12.150	15.195	18.675	22.594	26.941	31.696	36.826	42.289					84	53
					32	10.903	13.738	16.969	20.603	24.637	29.053	33.823	38.914	21.600	11.450	1.89	2.71		
					38	9.430	12.004	14.928	18.213	21.862	25.864	30.198	34.835						
					43	8.218	10.569	13.230	16.218	19.541	23.192	-	-						
					46	7.497	9.711	12.211	15.019	18.143	21.582	-	-						

MBP
(1) E - 400V-3ph-50Hz Compressor & 230V-1ph-50Hz Fan

G - 230V-1ph-50Hz Compressor & 230V-1ph-50Hz Fan

(2) Nominal conditions (EN13215), Evaporating temperatures at dew point, Superheat 10K, Subcooling 0K

(3) Rated conditions (EN13215), Evaporating temperature Midpoint -10°C, Ambient air temperature +32°C, Return Gas Temperature 20°C, Subcooling 0K

COP: Coefficient Of Performance link to EN13215 and ErP (Energy related Products) 2009/125/CE

SEPR: Seasonal Energy Performance Ratio link to EN13215 and ErP (Energy Related Products) 2009/125/CE

Tamb [°C]: Ambient Temperature

Te [°C]: Evaporating Temperature

Q [kW]: Cooling Capacity in Kilo Watt

P [kW]: Power Input in Kilo Watt

Version

A02: Receiver + Stop valves + KP17WB pressure switch + Electrical box


For regular updates and detailed capacities, please refer to **Coolselector®2** software


Model	Code	Version	Compressor	Electrical code (1)	Tamb [°C]	Cooling capacity Q [kW] (2)								EcoDesign (3)				Sound power level dB(A)	Sound pressure level 10 m dB(A)
						Te [°C]								Q [kW]	P [kW]	COP	SEPR		
						-25°C	-20°C	-15°C	-10°C	-5°C	0°C	5°C	10°C						
OP-MCRN030	114X5721	A02	MTZ018	E	27	0.780	1.152	1.600	2.127	2.729	3.405	4.149	4.956					76	45
					32	0.691	1.036	1.453	1.941	2.501	3.130	3.823	4.577	1.976	1.073	1.84			
					38	0.584	0.898	1.275	1.718	2.226	2.799	3.433	4.123						
					43	-	-	1.128	1.533	1.998	2.524	-	-						
					46	-	-	1.041	1.422	1.862	-	-	-						
OP-MCRN030	114X5722	A02	MTZ018	G	27	0.779	1.150	1.598	2.123	2.725	3.399	4.141	4.946					76	45
					32	0.690	1.035	1.450	1.938	2.496	3.123	3.815	4.567	1.973	1.113	1.77			
					38	0.583	0.896	1.273	1.714	2.221	2.792	3.424	4.112						
					43	-	-	1.125	1.529	1.993	2.517	-	-						
					46	-	-	1.038	1.419	1.857	-	-	-						
OP-MCRN038	114X5724 114X5790	A02 A14	MTZ022	E	27	1.445	1.939	2.525	3.202	3.965	4.806	5.719	6.695					74	43
					32	1.270	1.721	2.256	2.876	3.575	4.348	5.189	6.09	3.138	1.517	2.07			
					38	1.068	1.467	1.939	2.488	3.110	3.801	4.554	5.364						
					43	-	1.262	1.681	2.169	2.726	3.346	-	-						
					46	-	1.142	1.530	1.980	2.496	3.075	-	-						
OP-MCRN038	114X5723 114X5789	A02 A14	MTZ022	G	27	1.445	1.939	2.525	3.202	3.965	4.806	5.719	6.695					74	43
					32	1.270	1.721	2.256	2.876	3.575	4.348	5.189	6.090	3.138	1.517	2.07			
					38	1.068	1.467	1.939	2.488	3.110	3.801	4.554	5.364						
					43	-	1.262	1.681	2.169	2.726	3.346	-	-						
					46	-	1.142	1.530	1.980	2.496	3.075	-	-						
OP-MCRN048	114X5726 114X5792	A02 A14	MTZ028	E	27	1.996	2.687	3.494	4.423	5.473	6.645	7.937	9.345					74	43
					32	1.736	2.375	3.124	3.985	4.960	6.049	7.252	8.565	4.300	2.028	2.12			
					38	1.440	2.017	2.693	3.470	4.353	5.341	6.435	7.633						
					43	-	1.731	2.344	3.051	3.855	4.758	-	-						
					46	-	1.566	2.139	2.803	3.560	4.411	-	-						
OP-MCRN048	114X5728 114X5791	A02 A14	MTZ028	G	27	1.996	2.687	3.494	4.423	5.473	6.645	7.937	9.345					74	43
					32	1.736	2.375	3.124	3.985	4.960	6.049	7.252	8.565	4.300	2.028	2.12			
					38	1.440	2.017	2.693	3.470	4.353	5.341	6.435	7.633						
					43	-	1.731	2.344	3.051	3.855	4.758	-	-						
					46	-	1.566	2.139	2.803	3.56	4.411	-	-						
OP-MCRN054	114X5729	A02	MTZ032	E	27	1.873	2.589	3.434	4.409	5.516	6.752	8.112	9.589					74	43
					32	1.664	2.340	3.133	4.048	5.087	6.246	7.523	8.910	4.121	1.934	2.13			
					38	1.408	2.032	2.763	3.605	4.560	5.627	6.803	8.084						
					43	-	-	2.451	3.230	4.114	5.103	-	-						
					46	-	-	2.263	3.004	3.846	-	-	-						
OP-MCRN054	114X5731	A02	MTZ032	G	27	1.871	2.586	3.429	4.403	5.508	6.742	8.099	9.573					74	43
					32	1.662	2.336	3.129	4.042	5.078	6.235	7.509	8.893	4.116	2.006	2.05			
					38	1.405	2.029	2.758	3.598	4.551	5.615	6.788	8.065						
					43	-	-	2.446	3.223	4.105	5.092	-	-						
					46	-	-	2.258	2.997	3.836	-	-	-						

MBP
(1) E - 400V-3ph-50Hz Compressor & 230V-1ph-50Hz Fan

G - 230V-1ph-50Hz Compressor & 230V-1ph-50Hz Fan

(2) Nominal conditions (EN13215), Evaporating temperatures at dew point, Superheat 10K, Subcooling 0K

(3) Rated conditions (EN13215), Evaporating temperature Midpoint -10°C, Ambient air temperature +32°C, Return Gas Temperature 20°C, Subcooling 0K

COP: Coefficient Of Performance link to EN13215 and ErP (Energy related Products) 2009/125/CE

SEPR: Seasonal Energy Performance Ratio link to EN13215 and ErP (Energy Related Products) 2009/125/CE

Tamb [°C]: Ambient Temperature

Te [°C]: Evaporating Temperature

Q [kW]: Cooling Capacity in Kilo Watt

P [kW]: Power Input in Kilo Watt

Version

A02: Receiver + Stop valves + KP17WB pressure switch + Electrical box

A14: Filter drier + Sight glass + Receiver + Stop valves + KP17WB pressure switch + Electrical box

This table continues on the next page


For regular updates and detailed capacities, please refer to **Coolselector®2** software


Model	Code	Version	Compressor	Electrical code (1)	Tamb [°C]	Cooling capacity Q [kW] (2)								EcoDesign (3)				Sound power level dB(A)	Sound pressure level 10 m dB(A)
						Te [°C]								Q [kW]	P [kW]	COP	SEPR		
						-25°C	-20°C	-15°C	-10°C	-5°C	0°C	5°C	10°C						
OP-MCRN060	114X5732 114X5794	A02 A14	MTZ036	E	27	2.714	3.555	4.528	5.628	6.852	8.192	9.639	11.180					74	43
					32	2.426	3.205	4.100	5.112	6.236	7.466	8.795	10.210	5.552	2.701	2.06	2.92		
					38	2.079	2.783	3.586	4.490	5.493	6.591	7.778	9.0470						
					43	-	2.430	3.155	3.969	4.871	5.858	-	-						
					46	-	2.218	2.896	3.656	4.497	5.417	-	-						
OP-MCRN060	114X5734 114X5793	A02 A14	MTZ036	G	27	2.714	3.555	4.528	5.628	6.852	8.192	9.639	11.180					74	43
					32	2.426	3.205	4.100	5.112	6.236	7.466	8.795	10.210	5.552	2.701	2.06	2.92		
					38	2.079	2.783	3.586	4.49	5.493	6.591	7.778	9.047						
					43	-	2.430	3.155	3.969	4.871	5.858	-	-						
					46	-	2.218	2.896	3.656	4.497	5.417	-	-						
OP-MCRN068	114X5735	A02	MTZ040	E	27	2.555	3.467	4.515	5.702	7.026	8.483	10.066	11.765					76	45
					32	2.307	3.174	4.163	5.278	6.517	7.879	9.357	10.942	5.379	2.649	2.03	2.57		
					38	1.996	2.808	3.725	4.751	5.888	7.134	8.485	9.934						
					43	-	-	3.349	4.300	5.351	6.499	-	-						
					46	-	-	3.121	4.027	5.024	-	-	-						
OP-MCRN086	114X5737 114X5795	A02 A14	MTZ050	E	27	3.756	4.986	6.444	8.138	10.07	12.240	14.630	17.250					84	53
					32	3.313	4.439	5.776	7.331	9.108	11.110	13.330	15.760	7.889	3.281	2.40	3.42		
					38	2.813	3.815	5.004	6.392	7.984	9.783	11.790	13.990						
					43	-	3.318	4.386	5.633	7.070	8.699	-	-						
					46	-	3.03	4.023	5.187	6.530	8.057	-	-						
OP-MCRN096	114X5739 114X5796	A02 A14	MTZ056	E	27	3.896	5.205	6.760	8.570	10.640	12.960	15.530	18.330					83	52
					32	3.437	4.641	6.072	7.738	9.646	11.790	14.180	16.790	8.349	3.576	2.34	3.21		
					38	2.923	3.999	5.279	6.773	8.489	10.430	12.590	14.960						
					43	-	3.489	4.644	5.993	7.547	9.311	-	-						
					46	-	3.192	4.271	5.534	6.991	8.649	-	-						
OP-MCRN108	114X5740 114X5797	A02 A14	MTZ064	E	27	4.661	6.123	7.856	9.867	12.160	14.730	17.560	20.650					83	52
					32	4.133	5.484	7.081	8.935	11.050	13.420	16.050	18.910	9.689	4.283	2.26	3.15		
					38	3.514	4.727	6.159	7.822	9.723	11.860	14.240	16.840						
					43	-	4.106	5.397	6.899	8.620	10.560	-	-						
					46	-	3.738	4.944	6.347	7.959	9.784	-	-						
OP-MGRN108	114X5743	A02	MTZ064	E	27	3.662	5.024	6.637	8.507	10.633	13.005	15.611	18.432					83	52
					32	3.246	4.525	6.038	7.791	9.785	12.013	14.465	17.123	7.943	3.660	2.17	2.87		
					38	2.741	3.918	5.308	6.920	8.755	10.810	13.076	15.540						
					43	-	-	4.698	6.190	7.891	9.802	-	-						
					46	-	-	4.334	5.753	7.374	-	-	-						

MBP
(1) E - 400V-3ph-50Hz Compressor & 230V-1ph-50Hz Fan

G - 230V-1ph-50Hz Compressor & 230V-1ph-50Hz Fan

(2) Nominal conditions (EN13215), Evaporating temperatures at dew point, Superheat 10K, Subcooling 0K

(3) Rated conditions (EN13215), Evaporating temperature Midpoint -10°C, Ambient air temperature +32°C, Return Gas Temperature 20°C, Subcooling 0K

COP: Coefficient Of Performance link to EN13215 and ErP (Energy related Products) 2009/125/CE

SEPR: Seasonal Energy Performance Ratio link to EN13215 and ErP (Energy Related Products) 2009/125/CE

Tamb [°C]: Ambient Temperature

Te [°C]: Evaporating Temperature

Q [kW]: Cooling Capacity in Kilo Watt

P [kW]: Power Input in Kilo Watt

Version

A02: Receiver + Stop valves + KP17WB pressure switch + Electrical box

A14: Filter drier + Sight glass + Receiver + Stop valves + KP17WB pressure switch + Electrical box

This table continues on the next page


For regular updates and detailed capacities, please refer to **Coolselector®2** software


Model	Code	Version	Compressor	Electrical code (1)	Tamb [°C]	Cooling capacity Q [kW] (2)								EcoDesign (3)				Sound power level dB(A)	Sound pressure level 10 m dB(A)
						Te [°C]								Q [kW]	P [kW]	COP	SEPR		
						-25°C	-20°C	-15°C	-10°C	-5°C	0°C	5°C	10°C						
OP-MCRN121	114X5744	A02	MTZ072	E	27	4.129	5.614	7.350	9.336	11.567	14.033	16.717	19.600					82	51
					32	3.642	5.035	6.663	8.528	10.628	12.951	15.484	18.209	8.702	4.156	2.09	2.76		
					38	3.076	4.355	5.852	7.571	9.509	11.660	14.011	16.546						
					43	-	-	5.193	6.787	8.589	10.595	-	-						
					46	-	-	4.805	6.324	8.044	-	-	-						
OP-MGRN121	114X5746	A02	MTZ072	E	27	4.129	5.614	7.350	9.336	11.567	14.033	16.717	19.600					82	51
					32	3.642	5.035	6.663	8.528	10.628	12.951	15.484	18.209	8.702	4.086	2.13	2.82		
					38	3.076	4.355	5.852	7.571	9.509	11.660	14.011	16.546						
					43	-	-	5.193	6.787	8.589	10.595	-	-						
					46	-	-	4.805	6.324	8.044	-	-	-						
OP-MCRN136	114X5747	A02	MTZ080	E	27	4.838	6.488	8.377	10.501	12.846	15.396	18.128	21.018					82	51
					32	4.313	5.872	7.649	9.643	11.844	14.238	16.804	19.520	9.855	4.972	1.98	2.64		
					38	3.685	5.132	6.774	8.611	10.638	12.843	15.208	17.716						
					43	-	-	6.047	7.753	9.634	11.680	-	-						
					46	-	-	5.615	7.241	9.033	-	-	-						
OP-MGRN136	114X5749	A02	MTZ080	E	27	4.838	6.488	8.377	10.501	12.846	15.396	18.128	21.018					82	51
					32	4.313	5.872	7.649	9.643	11.844	14.238	16.804	19.520	9.855	4.902	2.01	2.64		
					38	3.685	5.132	6.774	8.611	10.638	12.843	15.208	17.716						
					43	-	-	6.047	7.753	9.634	11.680	-	-						
					46	-	-	5.615	7.241	9.033	-	-	-						
OP-MGRN171	114X5750	A02	MTZ100	E	27	5.722	7.951	10.592	13.658	17.151	21.065	25.388	30.098					87	56
					32	5.134	7.239	9.720	12.592	15.859	19.521	23.567	27.981	12.810	6.257	2.05	2.83		
					38	4.389	6.343	8.631	11.270	14.268	17.628	21.343	25.403						
					43	-	-	7.696	10.140	12.913	16.022	-	-						
					46	-	-	7.126	9.452	12.091	-	-	-						
OP-MGRN215	114X5753	A02	MTZ125	E	27	7.559	10.266	13.446	17.108	21.251	25.867	30.937	36.433					86	55
					32	6.687	9.225	12.205	15.641	19.533	23.876	28.654	33.844	15.93x	7.758	2.05	2.83		
					38	5.669	7.999	10.737	13.897	17.486	21.500	25.926	30.745						
					43	-	-	9.539	12.467	15.799	19.536	-	-						
					46	-	-	8.834	11.621	14.798	-	-	-						
OP-MGRN242	114X5754	A02	MTZ144	E	27	8.818	11.861	15.388	19.399	23.882	28.814	34.160	39.879					85	54
					32	7.889	10.760	14.074	17.836	22.036	26.656	31.666	37.030	18.190	8.951	2.03	2.74		
					38	6.751	9.410	12.465	15.923	19.782	24.027	28.635	33.574						
					43	-	-	11.109	14.312	17.883	21.814	-	-						
					46	-	-	10.295	13.342	16.740	-	-	-						
OP-MGRN271	114X5757	A02	MTZ160	E	27	9.535	12.804	16.576	20.846	25.595	30.788	36.383	42.325					84	53
					32	8.538	11.627	15.177	19.185	23.637	28.505	33.750	39.325	19.590	10.100	1.94	2.58		
					38	7.319	10.186	13.463	17.154	21.249	25.726	30.552	35.686						
					43	-	-	12.020	15.443	19.238	23.386	-	-						
					46	-	-	11.153	14.413	18.025	-	-	-						

MBP
(1) E - 400V-3ph-50Hz Compressor & 230V-1ph-50Hz Fan

G - 230V-1ph-50Hz Compressor & 230V-1ph-50Hz Fan

(2) Nominal conditions (EN13215), Evaporating temperatures at dew point, Superheat 10K, Subcooling 0K

(3) Rated conditions (EN13215), Evaporating temperature Midpoint -10°C, Ambient air temperature +32°C, Return Gas Temperature 20°C, Subcooling 0K

COP: Coefficient Of Performance link to EN13215 and ErP (Energy related Products) 2009/125/CE

SEPR: Seasonal Energy Performance Ratio link to EN13215 and ErP (Energy Related Products) 2009/125/CE

Tamb [°C]: Ambient Temperature

Te [°C]: Evaporating Temperature

Q [kW]: Cooling Capacity in Kilo Watt

P [kW]: Power Input in Kilo Watt

Version

A02: Receiver + Stop valves + KP17WB pressure switch + Electrical box


For regular updates and detailed capacities, please refer to **Coolselector®2** software


Model	Code	Version	Compressor	Electrical code (1)	Tamb [°C]	Cooling capacity Q [kW] (2)								EcoDesign (3)				Sound power level dB(A)	Sound pressure level 10 m dB(A)
						Te [°C]								Q [kW]	P [kW]	COP	SEPR		
						-25°C	-20°C	-15°C	-10°C	-5°C	0°C	5°C	10°C						
OP-MCRN030	114X5721	A02	MTZ018	E	27	0.827	1.228	1.705	2.257	2.882	3.579	4.343	5.170	2.060	1.132	1.82		76	45
					32	0.715	1.086	1.529	2.043	2.628	3.282	4.000	4.780						
					38	-	0.939	1.342	1.812	2.349	2.951	3.615	4.339						
					43	-	-	1.206	1.640	2.137	2.696	-	-						
					46	-	-	1.132	1.545	2.018	-	-	-						
OP-MCRN030	114X5722	A02	MTZ018	G	27	0.826	1.226	1.701	2.252	2.877	3.572	4.334	5.159	2.056	1.175	1.75		76	45
					32	0.713	1.084	1.526	2.039	2.623	3.275	3.992	4.769						
					38	-	0.937	1.339	1.808	2.344	2.944	3.606	4.327						
					43	-	-	1.204	1.637	2.132	2.689	-	-						
					46	-	-	1.130	1.542	2.014	-	-	-						
OP-MCRN038	114X5724 114X5790	A02 A14	MTZ022	E	27	1.217	1.710	2.287	2.948	3.689	4.507	5.398	6.355	2.694	1.389	1.94		74	43
					32	1.049	1.508	2.047	2.667	3.367	4.142	4.988	5.900						
					38	-	1.297	1.794	2.367	3.016	3.740	4.533	5.391						
					43	-	-	1.608	2.144	2.754	3.435	-	-						
					46	-	-	1.508	2.022	2.608	3.264	-	-						
OP-MCRN038	114X5723 114X5789	A02 A14	MTZ022	G	27	1.214	1.706	2.282	2.941	3.680	4.496	5.384	6.338	2.688	1.442	1.86		74	43
					32	1.047	1.505	2.043	2.661	3.358	4.131	4.974	5.883						
					38	-	1.294	1.789	2.361	3.008	3.729	4.519	5.374						
					43	-	-	1.604	2.139	2.746	3.424	-	-						
					46	-	-	1.504	2.017	2.601	-	-	-						
OP-MCRN048	114X5726 114X5792	A02 A14	MTZ028	E	27	1.723	2.426	3.243	4.179	5.238	6.420	7.727	9.157	3.791	1.850	2.05		74	43
					32	1.463	2.118	2.883	3.763	4.763	5.883	7.126	8.492						
					38	-	1.803	2.512	3.330	4.262	5.312	6.482	7.772						
					43	-	-	2.247	3.018	3.899	4.894	-	-						
					46	-	-	2.105	2.851	3.704	-	-	-						
OP-MCRN048	114X5728 114X5791	A02 A14	MTZ028	G	27	1.670	2.268	3.000	3.875	4.899	6.074	7.396	8.861	3.600	1.810	1.99		74	43
					32	1.525	2.084	2.763	3.574	4.523	5.614	6.845	8.213						
					38	-	1.868	2.487	3.223	4.085	5.076	6.200	7.452						
					43	-	-	2.260	2.936	3.727	4.638	-	-						
					46	-	-	2.123	2.765	3.514	-	-	-						
OP-MCRN054	114X5729	A02	MTZ032	E	27	2.029	2.798	3.689	4.706	5.850	7.120	8.515	10.031	4.299	2.037	2.11		74	43
					32	1.755	2.474	3.309	4.265	5.343	6.546	7.870	9.315						
					38	-	2.135	2.909	3.796	4.801	5.925	7.168	8.528						
					43	-	-	2.618	3.453	4.400	5.461	-	-						
					46	-	-	2.460	3.266	4.180	-	-	-						
OP-MCRN054	114X5731	A02	MTZ032	G	27	2.026	2.794	3.683	4.698	5.840	7.108	8.500	10.012	4.292	2.114	2.03		74	43
					32	1.752	2.470	3.303	4.257	5.334	6.534	7.855	9.297						
					38	-	2.132	2.904	3.790	4.792	5.913	7.153	8.510						
					43	-	-	2.614	3.447	4.392	5.451	-	-						
					46	-	-	2.456	3.260	4.172	-	-	-						

MBP
(1) E - 400V-3ph-50Hz Compressor & 230V-1ph-50Hz Fan

G - 230V-1ph-50Hz Compressor & 230V-1ph-50Hz Fan

(2) Nominal conditions (EN13215), Evaporating temperatures at dew point, Superheat 10K, Subcooling 0K

(3) Rated conditions (EN13215), Evaporating temperature Midpoint -10°C, Ambient air temperature +32°C, Return Gas Temperature 20°C, Subcooling 0K

COP: Coefficient Of Performance link to EN13215 and ErP (Energy related Products) 2009/125/CE

SEPR: Seasonal Energy Performance Ratio link to EN13215 and ErP (Energy Related Products) 2009/125/CE

Tamb [°C]: Ambient Temperature

Te [°C]: Evaporating Temperature

Q [kW]: Cooling Capacity in Kilo Watt

P [kW]: Power Input in Kilo Watt

Version

A02: Receiver + Stop valves + KP17WB pressure switch + Electrical box

A14: Filter drier + Sight glass + Receiver + Stop valves + KP17WB pressure switch + Electrical box

This table continues on the next page


For regular updates and detailed capacities, please refer to **Coolselector®2** software


Model	Code	Version	Compressor	Electrical code (1)	Tamb [°C]	Cooling capacity Q [kW] (2)								EcoDesign (3)				Sound power level dB(A)	Sound pressure level 10 m dB(A)
						Te [°C]								Q [kW]	P [kW]	COP	SEPR		
						-25°C	-20°C	-15°C	-10°C	-5°C	0°C	5°C	10°C						
OP-MCRN060	114X5732 114X5794	A02 A14	MTZ036	E	27	2.327	3.190	4.181	5.299	4.917	7.902	9.378	10.961						
					32	2.042	2.854	3.785	4.837	6.007	7.294	8.691	10.193	4.881	2.473	1.97			
					38	-	2.503	3.371	4.350	5.440	6.640	7.946	9.353					74	43
					43	-	-	3.067	3.993	5.021	6.153	-	-						
					46	-	-	2.900	3.796	4.791	-	-	-						
OP-MCRN060	114X5734 114X5793	A02 A14	MTZ036	G	27	2.323	3.185	4.174	5.289	6.528	7.886	9.358	10.937						
					32	2.039	2.849	3.779	4.828	5.995	7.278	8.672	10.169	4.872	2.565	1.90			
					38	-	2.498	3.365	4.342	5.429	6.625	7.927	9.330					74	43
					43	-	-	3.062	3.985	5.011	6.140	-	-						
					46	-	-	2.894	3.789	4.781	-	-	-						
OP-MCRN068	114X5735	A02	MTZ040	E	27	2.726	3.692	4.795	6.035	7.411	8.919	10.552	12.305						
					32	2.413	3.324	4.363	5.531	6.827	8.251	9.796	11.457	5.580	2.789	2.00	2.80		
					38	-	2.937	3.908	4.996	6.204	7.530	8.972	10.524					76	45
					43	-	-	3.572	4.602	5.742	6.992	-	-						
					46	-	-	3.385	4.384	5.486	-	-	-						
OP-MCRN086	114X5737 114X5795	A02 A14	MTZ050	E	27	3.174	4.390	5.814	7.451	9.299	11.357	13.619	16.078						
					32	2.745	3.870	5.194	6.723	8.459	10.402	12.547	14.890	6.776	3.016	2.25	3.27		
					38	-	3.344	4.559	5.967	7.576	9.384	11.393	13.597					84	53
					43	-	-	4.111	5.429	6.938	8.641	-	-						
					46	-	-	3.874	5.142	6.595	-	-	-						
OP-MCRN096	114X5739 114X5796	A02 A14	MTZ056	E	27	3.287	4.576	6.089	7.831	9.805	12.010	14.441	17.094						
					32	2.844	4.043	5.456	7.093	8.958	11.051	13.370	15.911	7.153	3.289	2.17	3.16		
					38	-	3.507	4.814	6.335	8.076	10.040	12.229	14.638					83	52
					43	-	-	4.365	5.799	7.445	9.310	11.394	13.697						
					46	-	-	4.126	5.515	7.109	8.917	10.941	13.183						
OP-MCRN108	114X5740 114X5797	A02 A14	MTZ064	E	27	3.910	5.351	7.036	8.972	11.159	13.597	16.280	19.200						
					32	3.411	4.761	6.344	8.171	10.245	12.566	15.132	17.936	8.250	3.937	2.10	2.99		
					38	-	4.144	5.616	7.321	9.265	11.452	13.879	16.544					83	52
					43	-	-	5.083	6.695	8.538	10.617	12.933	15.484						
					46	-	-	4.790	6.351	8.137	10.155	12.406	14.889						
OP-MGRN108	114X5743	A02	MTZ064	E	27	3.910	5.351	7.036	8.972	11.159	13.597	16.280	19.200						
					32	3.411	4.761	6.344	8.171	10.245	12.566	15.132	17.936	8.250	3.867	2.13	3.05		
					38	-	4.144	5.616	7.321	9.265	11.452	13.879	16.544					83	52
					43	-	-	5.083	6.695	8.538	10.617	12.933	15.484						
					46	-	-	4.790	6.351	8.137	10.155	12.406	14.889						

MBP
(1) E - 400V-3ph-50Hz Compressor & 230V-1ph-50Hz Fan

G - 230V-1ph-50Hz Compressor & 230V-1ph-50Hz Fan

(2) Nominal conditions (EN13215), Evaporating temperatures at dew point, Superheat 10K, Subcooling 0K

(3) Rated conditions (EN13215), Evaporating temperature Midpoint -10°C, Ambient air temperature +32°C, Return Gas Temperature 20°C, Subcooling 0K

COP: Coefficient Of Performance link to EN13215 and ErP (Energy related Products) 2009/125/CE

SEPR: Seasonal Energy Performance Ratio link to EN13215 and ErP (Energy Related Products) 2009/125/CE

Tamb [°C]: Ambient Temperature

Te [°C]: Evaporating Temperature

Q [kW]: Cooling Capacity in Kilo Watt

P [kW]: Power Input in Kilo Watt

Version

A02: Receiver + Stop valves + KP17WB pressure switch + Electrical box

A14: Filter drier + Sight glass + Receiver + Stop valves + KP17WB pressure switch + Electrical box

This table continues on the next page


For regular updates and detailed capacities, please refer to **Coolselector®2** software


Model	Code	Version	Compressor	Electrical code (1)	Tamb [°C]	Cooling capacity Q [kW] (2)								EcoDesign (3)				Sound power level dB(A)	Sound pressure level 10 m dB(A)
						Te [°C]								Q [kW]	P [kW]	COP	SEPR		
						-25°C	-20°C	-15°C	-10°C	-5°C	0°C	5°C	10°C						
OP-MCRN121	114X5744	A02	MTZ072	E	27	4.362	5.932	7.743	9.797	12.096	14.636	17.413	20.420					82	51
					32	3.804	5.275	6.981	8.929	11.120	13.554	16.226	19.132	9.024	4.391	2.06	2.87		
					38	-	4.608	6.202	8.030	10.099	12.409	14.960	17.747						
					43	-	-	5.652	7.392	9.366	11.580	14.034	16.725						
					46	-	-	5.361	7.052	8.975	11.134	13.533	16.169						
OP-MGRN121	114X5746	A02	MTZ072	E	27	4.362	5.932	7.743	9.797	12.096	14.636	17.413	20.420					82	51
					32	3.804	5.275	6.981	8.929	11.120	13.554	16.226	19.132	9.024	4.321	2.09	2.92		
					38	-	4.608	6.202	8.030	10.099	12.409	14.960	17.747						
					43	-	-	5.652	7.392	9.366	11.580	14.034	16.725						
					46	-	-	5.361	7.052	8.975	11.134	13.533	16.169						
OP-MCRN136	114X5747	A02	MTZ080	E	27	5.095	6.828	8.793	10.988	13.410	16.051	18.904	21.958					82	51
					32	4.502	6.146	8.014	10.108	12.426	14.963	17.713	20.666	10.230	5.269	1.94	2.67		
					38	-	5.443	7.209	9.193	11.395	13.814	16.445	19.280						
					43	-	-	6.630	8.534	10.650	12.978	15.515	18.256						
					46	-	-	6.314	8.178	10.248	12.525	15.010	17.697						
OP-MGRN136	114X5749	A02	MTZ080	E	27	5.095	6.828	8.793	10.988	13.410	16.051	18.904	21.958					82	51
					32	4.502	6.146	8.014	10.108	12.426	14.963	17.713	20.666	10.232	5.199	1.97	2.71		
					38	-	5.443	7.209	9.193	11.395	13.814	16.445	19.280						
					43	-	-	6.630	8.534	10.650	12.978	15.515	18.256						
					46	-	-	6.314	8.178	10.248	12.525	15.010	17.697						
OP-MGRN171	114X5750	A02	MTZ100	E	27	6.109	8.512	11.331	14.571	18.228	22.294	26.754	31.591					87	56
					32	5.361	7.605	10.233	13.255	16.673	20.484	24.678	29.239	13.350	6.576	2.03	3.13		
					38	-	6.661	9.091	11.878	15.031	18.551	22.436	26.674						
					43	-	-	8.253	10.869	13.822	17.118	20.758	24.736						
					46	-	-	7.785	10.312	13.156	16.326	19.825	23.652						
OP-MGRN215	114X5753	A02	MTZ125	E	27	8.048	10.935	14.279	18.089	22.370	27.118	32.326	37.984					86	55
					32	7.006	9.693	12.821	16.405	20.453	24.966	29.940	35.365	16.550	8.164	2.03	2.99		
					38	-	8.442	11.338	14.672	18.457	22.700	27.401	32.554						
					43	-	-	10.302	13.449	17.033	21.065	25.550	30.484						
					46	-	-	9.758	12.804	16.276	20.190	24.550	29.359						
OP-MGRN242	114X5754	A02	MTZ144	E	27	9.395	12.618	16.301	20.448	25.056	30.115	35.609	41.521					85	54
					32	8.274	11.307	14.779	18.699	23.069	27.884	33.130	38.793	18.890	9.430	2.00	2.86		
					38	-	9.947	13.191	16.861	20.962	25.495	30.453	35.821						
					43	-	-	12.043	15.525	19.420	23.732	28.458	33.588						
					46	-	-	11.420	14.800	18.579	22.766	27.359	32.350						
OP-MGRN271	114X5757	A02	MTZ160	E	27	10.130	13.582	17.510	21.916	26.794	32.131	37.908	44.101					84	53
					32	8.945	12.206	15.925	20.109	24.757	29.859	35.401	41.360	20.330	10.650	1.91	2.67		
					38	-	10.781	14.276	18.215	22.603	27.436	32.702	38.385						
					43	-	-	13.085	16.842	21.030	25.652	30.700	36.160						
					46	-	-	12.437	16.096	20.175	24.678	29.600	34.930						

MBP
(1) E - 400V-3ph-50Hz Compressor & 230V-1ph-50Hz Fan

G - 230V-1ph-50Hz Compressor & 230V-1ph-50Hz Fan

(2) Nominal conditions (EN13215), Evaporating temperatures at dew point, Superheat 10K, Subcooling 0K

(3) Rated conditions (EN13215), Evaporating temperature Midpoint -10°C, Ambient air temperature +32°C, Return Gas Temperature 20°C, Subcooling 0K

COP: Coefficient Of Performance link to EN13215 and ErP (Energy related Products) 2009/125/CE

SEPR: Seasonal Energy Performance Ratio link to EN13215 and ErP (Energy Related Products) 2009/125/CE

Tamb [°C]: Ambient Temperature

Te [°C]: Evaporating Temperature

Q [kW]: Cooling Capacity in Kilo Watt

P [kW]: Power Input in Kilo Watt

Version

A02: Receiver + Stop valves + KP17WB pressure switch + Electrical box


For regular updates and detailed capacities, please refer to **Coolselector®2** software


Model	Code	Version	Compressor	Electrical code (1)	Tamb [°C]	Cooling capacity Q [kW] (2)							EcoDesign (3)				Sound power level dB(A)	Sound pressure level 10 m dB(A)
						Te [°C]							Q [kW]	P [kW]	COP	SEPR		
						-15°C	-10°C	-5°C	0°C	5°C	10°C	15°C						
OP-MCRN030	114X5721	A02	MTZ018	E	27	1.512	2.049	2.663	3.350	4.104	4.918	5.785						
					32	1.337	1.843	2.421	3.066	3.774	4.539	5.353	1.863	0.984	1.89			
					38	-	1.608	2.143	2.738	3.391	4.097	-					76	45
					43	-	1.422	1.921	2.476	3.083	3.738	-						
					46	-	-	1.793	2.323	2.902	3.528	-						
OP-MCRN030	114X5722	A02	MTZ018	G	27	1.434	1.970	2.595	3.305	4.088	4.937	5.839						
					32	1.320	1.821	2.402	3.058	3.784	4.569	5.407	1.841	0.996	1.85			
					38	-	1.645	2.179	2.776	3.435	4.148	-					76	45
					43	-	1.494	1.993	2.547	3.153	3.807	-						
					46	-	-	1.879	2.409	2.985	3.606	-						
OP-MCRN038	114X5724 114X5790	A02 A14	MTZ022	E	27	2.064	2.688	3.388	4.157	4.987	5.868	6.790						
					32	1.855	2.444	3.101	3.821	4.597	5.420	6.281	2.475	1.300	1.90			
					38	-	2.154	2.760	3.422	4.133	4.886	-					74	43
					43	-	1.919	2.482	3.094	3.751	4.445	-						
					46	-	-	2.318	2.900	3.524	4.183	-						
OP-MCRN038	114X5723 114X5789	A02 A14	MTZ022	G	27	1.985	2.618	3.338	4.136	5.004	5.931	6.907						
					32	1.786	2.380	3.053	3.800	4.612	5.479	6.392	2.410	1.301	1.85			
					38	-	2.101	2.720	3.404	4.148	4.943	-					74	43
					43	-	1.877	2.449	3.081	3.767	4.501	-						
					46	-	-	2.290	2.890	3.542	4.239	-						
OP-MCRN048	114X5726 114X5792	A02 A14	MTZ028	E	27	2.691	3.594	4.632	5.805	7.110	8.538	10.081						
					32	2.432	3.289	4.270	5.375	6.601	7.942	9.391	3.323	1.619	2.05			
					38	-	2.918	3.830	4.852	5.984	7.220	-					74	43
					43	-	2.606	3.460	4.414	5.467	6.617	-						
					46	-	-	3.239	4.151	5.156	6.254	-						
OP-MCRN048	114X5728 114X5791	A02 A14	MTZ028	G	27	2.628	3.553	4.612	5.796	7.097	8.501	9.993						
					32	2.380	3.256	4.251	5.359	6.573	7.882	9.272	3.289	1.655	1.99			
					38	-	2.896	3.819	4.840	5.953	7.149	-					74	43
					43	-	2.591	3.458	4.409	5.440	6.545	-						
					46	-	-	3.239	4.149	5.133	6.184	-						
OP-MCRN054	114X5729	A02	MTZ032	E	27	3.242	4.203	5.297	6.520	7.864	9.321	10.877						
					32	2.942	3.851	4.881	6.028	7.287	8.650	10.106	3.894	1.839	2.12			
					38	-	3.428	4.381	5.438	6.594	7.845	-					74	43
					43	-	3.077	3.966	4.948	6.019	7.176	-						
					46	-	-	3.718	4.655	5.675	6.776	-						
OP-MCRN054	114X5731	A02	MTZ032	G	27	3.171	4.164	5.291	6.549	7.929	9.424	11.020						
					32	2.862	3.806	4.871	6.055	7.351	8.753	10.250	3.848	1.877	2.05			
					38	-	3.373	4.365	5.461	6.658	7.950	-					74	43
					43	-	3.011	3.943	4.967	6.081	7.281	-						
					46	-	-	3.689	4.670	5.736	6.880	-						

MBP
(1) E - 400V-3ph-50Hz Compressor & 230V-1ph-50Hz Fan

G - 230V-1ph-50Hz Compressor & 230V-1ph-50Hz Fan

(2) Nominal conditions (EN13215), Evaporating temperatures at dew point, Superheat 10K, Subcooling 0K

(3) Rated conditions (EN13215), Evaporating temperature Midpoint -10°C, Ambient air temperature +32°C, Return Gas Temperature 20°C, Subcooling 0K

COP: Coefficient Of Performance link to EN13215 and ErP (Energy related Products) 2009/125/CE

SEPR: Seasonal Energy Performance Ratio link to EN13215 and ErP (Energy Related Products) 2009/125/CE

Tamb [°C]: Ambient Temperature

Te [°C]: Evaporating Temperature

Q [kW]: Cooling Capacity in Kilo Watt

P [kW]: Power Input in Kilo Watt

Version

A02: Receiver + Stop valves + KP17WB pressure switch + Electrical box

A14: Filter drier + Sight glass + Receiver + Stop valves + KP17WB pressure switch + Electrical box

This table continues on the next page


For regular updates and detailed capacities, please refer to **Coolselector®2** software


Model	Code	Version	Compressor	Electrical code (1)	Tamb [°C]	Cooling capacity Q [kW] (2)							EcoDesign (3)				Sound power level dB(A)	Sound pressure level 10 m dB(A)
						Te [°C]							Q [kW]	P [kW]	COP	SEPR		
						-15°C	-10°C	-5°C	0°C	5°C	10°C	15°C						
OP-MCRN060	114X5732 114X5794	A02 A14	MTZ036	E	27	3.729	4.757	5.914	7.190	8.574	10.052	11.610					74	43
					32	3.415	4.387	5.474	6.669	7.961	9.339	10.792	4.440	2.258	1.97			
					38	-	3.939	4.946	6.046	7.231	8.491	9.817						
					43	-	3.560	4.503	5.526	6.623	7.787	9.008						
					46	-	-	4.235	5.213	6.259	7.365	8.524						
OP-MCRN060	114X5734 114X5793	A02 A14	MTZ036	G	27	3.599	4.677	5.894	7.243	8.711	10.287	11.954					74	43
					32	3.256	4.280	5.431	6.702	8.083	9.563	11.128	4.330	2.219	1.95			
					38	-	3.794	4.867	6.047	7.325	8.692	-						
					43	-	3.378	4.389	5.495	6.688	7.962	-						
					46	-	-	4.098	5.160	6.303	7.521	-						
OP-MCRN068	114X5735	A02	MTZ040	E	27	4.329	5.488	6.800	8.258	9.849	11.559	13.371					76	45
					32	3.999	5.097	6.332	7.698	9.185	10.781	12.471	5.158	2.609	1.98	2.71		
					38	-	4.616	5.761	7.020	8.384	9.844	-						
					43	-	4.203	5.276	6.447	7.711	9.060	-						
					46	-	-	4.979	6.099	7.303	8.586	-						
OP-MCRN086	114X5737 114X5795	A02 A14	MTZ050	E	27	5.009	6.504	8.229	10.181	12.351	14.725	17.285					84	53
					32	4.553	5.959	7.576	9.404	11.435	13.660	16.061	6.024	2.810	2.14	2.89		
					38	-	5.305	6.795	8.475	10.341	12.385	-						
					43	-	4.761	6.146	7.704	9.433	11.329	-						
					46	-	-	5.759	7.244	8.891	10.698	-						
OP-MCRN096	114X5739 114X5796	A02 A14	MTZ056	E	27	5.360	7.008	8.912	11.068	13.461	16.074	18.884					83	52
					32	4.868	6.424	8.216	10.241	12.489	14.944	17.586	6.497	3.026	2.15	3.00		
					38	-	5.723	7.380	9.248	11.319	13.584	-						
					43	-	5.142	6.685	8.421	10.346	12.451	-						
					46	-	-	6.271	7.927	9.763	11.772	-						
OP-MCRN108	114X5740 114X5797	A02 A14	MTZ064	E	27	6.307	8.073	10.102	12.388	14.916	17.666	20.613					83	52
					32	5.745	7.402	9.307	11.453	13.828	16.416	19.193	7.494	3.488	2.15	3.01		
					38	-	6.614	8.364	10.338	12.527	14.916	-						
					43	-	5.977	7.594	9.421	11.451	13.672	-						
					46	-	-	7.142	8.879	10.812	12.930	-						
OP-MGRN108	114X5743	A02	MTZ064	E	27	6.307	8.073	10.102	12.388	14.916	17.666	20.613					83	52
					32	5.745	7.402	9.307	11.453	13.828	16.416	19.193	7.494	3.418	2.19	3.08		
					38	-	6.614	8.364	10.338	12.527	14.916	-						
					43	-	5.977	7.594	9.421	11.451	13.672	-						
					46	-	-	7.142	8.879	10.812	12.930	-						

MBP
(1) E - 400V-3ph-50Hz Compressor & 230V-1ph-50Hz Fan

G - 230V-1ph-50Hz Compressor & 230V-1ph-50Hz Fan

(2) Nominal conditions (EN13215), Evaporating temperatures at dew point, Superheat 10K, Subcooling 0K

(3) Rated conditions (EN13215), Evaporating temperature Midpoint -10°C, Ambient air temperature +32°C, Return Gas Temperature 20°C, Subcooling 0K

COP: Coefficient Of Performance link to EN13215 and ErP (Energy related Products) 2009/125/CE

SEPR: Seasonal Energy Performance Ratio link to EN13215 and ErP (Energy Related Products) 2009/125/CE

Tamb [°C]: Ambient Temperature

Te [°C]: Evaporating Temperature

Q [kW]: Cooling Capacity in Kilo Watt

P [kW]: Power Input in Kilo Watt

Version

A02: Receiver + Stop valves + KP17WB pressure switch + Electrical box

A14: Filter drier + Sight glass + Receiver + Stop valves + KP17WB pressure switch + Electrical box

This table continues on the next page


For regular updates and detailed capacities, please refer to **Coolselector®2** software


Model	Code	Version	Compressor	Electrical code (1)	Tamb [°C]	Cooling capacity Q [kW] (2)							EcoDesign (3)				Sound power level dB(A)	Sound pressure level 10 m dB(A)
						Te [°C]							Q [kW]	P [kW]	COP	SEPR		
						-15°C	-10°C	-5°C	0°C	5°C	10°C	15°C						
OP-MCRN121	114X5744	A02	MTZ072	E	27	6.985	8.954	11.199	13.702	16.439	19.380	22.492					82	51
					32	6.375	8.232	10.341	12.689	15.256	18.013	20.932	8.342	4.120	2.02	2.79		
					38	-	7.367	9.309	11.468	13.826	16.362	-						
					43	-	6.657	8.454	10.452	12.634	14.982	-						
					46	-	-	7.947	9.845	11.920	14.155	-						
OP-MGRN121	114X5746	A02	MTZ072	E	27	6.985	8.954	11.199	13.702	16.439	19.380	22.492					82	51
					32	6.375	8.232	10.341	12.689	15.256	18.013	20.932	8.342	4.050	2.06	2.84		
					38	-	7.367	9.309	11.468	13.826	16.362	-						
					43	-	6.657	8.454	10.452	12.634	14.982	-						
					46	-	-	7.947	9.845	11.920	14.155	-						
OP-MCRN136	114X5747	A02	MTZ080	E	27	7.817	9.984	12.410	15.067	17.922	20.935	24.064					82	51
					32	7.164	9.213	11.495	13.985	16.653	19.466	22.386	9.348	4.827	1.94	2.67		
					38	-	8.281	10.387	12.675	15.120	17.692	-						
					43	-	7.503	9.462	11.579	13.836	16.208	-						
					46	-	-	8.907	10.922	13.065	15.316	-						
OP-MGRN136	114X5749	A02	MTZ080	E	27	7.817	9.984	12.410	15.067	17.922	20.935	24.064					82	51
					32	7.164	9.213	11.495	13.985	16.653	19.466	22.386	9.348	4.757	1.97	2.72		
					38	-	8.281	10.387	12.675	15.120	17.692	-						
					43	-	7.503	9.462	11.579	13.836	16.208	-						
					46	-	-	8.907	10.922	13.065	15.316	-						
OP-MGRN171	114X5750	A02	MTZ100	E	27	9.666	12.729	16.283	20.326	24.844	29.813	35.202					87	56
					32	8.732	11.621	14.965	18.763	23.008	27.680	32.752	11.740	6.002	1.96	2.81		
					38	-	10.297	13.381	16.882	20.795	25.106	-						
					43	-	9.211	12.073	15.321	18.952	22.959	-						
					46	-	-	11.299	14.392	17.852	21.674	-						
OP-MGRN215	114X5753	A02	MTZ125	E	27	13.147	16.747	20.846	25.435	30.489	35.972	41.839					86	55
					32	12.015	15.424	19.289	23.605	28.353	33.502	39.015	15.610	7.511	2.08	2.90		
					38	-	13.814	17.398	21.386	25.766	30.515	-						
					43	-	12.463	15.810	19.524	23.597	28.013	-						
					46	-	-	14.856	18.405	22.294	26.508	-						
OP-MGRN242	114X5754	A02	MTZ144	E	27	14.195	18.105	22.542	27.487	32.910	38.768	45.009					85	54
					32	12.972	16.673	20.856	25.507	30.603	36.106	41.971	16.890	8.499	1.99	2.76		
					38	-	14.953	18.826	23.122	27.822	32.898	-						
					43	-	13.529	17.139	21.134	25.502	30.219	-						
					46	-	-	16.133	19.946	24.112	28.613	-						
OP-MGRN271	114X5757	A02	MTZ160	E	27	16.529	20.700	25.412	30.631	36.310	42.387	48.793					84	53
					32	15.200	19.138	23.567	28.462	33.781	39.472	45.474	19.410	9.849	1.97	2.71		
					38	-	17.256	21.345	25.848	30.735	35.962	-						
					43	-	15.686	19.489	23.665	28.190	33.028	-						
					46	-	-	18.376	22.355	26.662	31.267	-						

MBP
(1) E - 400V-3ph-50Hz Compressor & 230V-1ph-50Hz Fan

G - 230V-1ph-50Hz Compressor & 230V-1ph-50Hz Fan

(2) Nominal conditions (EN13215), Evaporating temperatures at dew point, Superheat 10K, Subcooling 0K

(3) Rated conditions (EN13215), Evaporating temperature Midpoint -10°C, Ambient air temperature +32°C, Return Gas Temperature 20°C, Subcooling 0K

COP: Coefficient Of Performance link to EN13215 and ErP (Energy related Products) 2009/125/CE

SEPR: Seasonal Energy Performance Ratio link to EN13215 and ErP (Energy Related Products) 2009/125/CE

Tamb [°C]: Ambient Temperature

Te [°C]: Evaporating Temperature

Q [kW]: Cooling Capacity in Kilo Watt

P [kW]: Power Input in Kilo Watt

Version

A02: Receiver + Stop valves + KP17WB pressure switch + Electrical box


For regular updates and detailed capacities, please refer to **Coolselector®2** software


Model	Code	Version	Compressor	Electrical code (1)	Tamb [°C]	Cooling capacity Q [kW] (2)						EcoDesign (3)			
						Te [°C]						Q [kW]	P [kW]	COP	SEPR
						-20°C	-15°C	-10°C	-5°C	0°C	5°C				
OP-MCHC004	114X0301 114X0302 114X0303	A00 A01 A04	TL4DL	G	27	0.262	0.294	0.348	0.422	0.515	0.622	0.330	0.206	1.60	
					32	0.230	0.262	0.315	0.386	0.474	0.574				
					38	0.195	0.226	0.276	0.342	0.422	0.513				
					43	0.167	0.196	0.243	0.303	0.376	0.458				
OP-MCHC006	114X2316 114X2317 114X2319	A00 A01 A04	FR6DL	G	27	0.376	0.455	0.552	0.666	0.796	0.941	0.524	0.372	1.41	
					32	0.337	0.409	0.499	0.603	0.723	0.856				
					38	0.293	0.357	0.435	0.528	0.633	0.751				
					43	0.259	0.314	0.383	0.464	0.557	-				
OP-MCHC007	114X2424 114X2425 114X2427	A00 A01 A04	NF7MLX	G	27	-	0.588	0.720	0.869	1.037	1.223	0.690	0.444	1.55	
					32	-	0.535	0.657	0.796	0.952	1.127				
					38	-	0.470	0.581	0.708	0.850	1.010				
					43	-	0.417	0.518	0.634	0.764	0.911				
OP-MCHC010	114X0403 114X0404 114X0405	A00 A01 A04	SC10MLX	G	27	0.620	0.767	0.938	1.132	1.348	1.583	0.898	0.515	1.74	
					32	0.560	0.696	0.853	1.031	1.229	1.445				
					38	0.487	0.609	0.749	0.908	1.085	1.279				
					43	0.426	0.535	0.661	0.804	0.963	1.138				
OP-MCHC013	114X0406 114X0407 114X0408	A00 A01 A04	SC12MLX	G	27	0.737	0.905	1.098	1.316	1.555	1.813	1.053	0.620	1.70	
					32	0.666	0.820	0.997	1.196	1.416	1.653				
					38	0.579	0.717	0.875	1.052	1.247	1.458				
					43	0.506	0.630	0.771	0.930	1.104	1.294				
OP-MCHC015	114X2649 114X2651	A01 A04	SC15MLX	G	27	0.934	1.148	1.396	1.677	1.991	2.337	1.341	0.836	1.60	
					32	0.844	1.043	1.273	1.534	1.826	2.150				
					38	0.738	0.916	1.124	1.360	1.625	1.919				
					43	0.651	0.811	0.998	1.212	1.453	1.722				
OP-MCHC018	114X0702 114X0703	A01 A04	SC18MLX	G	27	1.073	1.315	1.594	1.909	2.259	2.642	1.533	0.873	1.76	
					32	0.970	1.195	1.453	1.745	2.070	2.428				
					38	0.848	1.050	1.282	1.545	1.840	2.164				
					43	0.748	0.929	1.139	1.377	1.644	1.939				
OP-MCHC021	114X2765 114X2767	A01 A04	GS21MLX	G	27	1.259	1.557	1.898	2.278	2.694	3.141	1.810	1.039	1.74	
					32	1.128	1.402	1.715	2.064	2.446	2.859				
					38	0.978	1.222	1.500	1.811	2.152	2.523				
					43	0.858	1.076	1.325	1.603	1.910	2.244				

MBP
(1) E - 400V-3ph-50Hz Compressor & 230V-1ph-50Hz Fan

G - 230V-1ph-50Hz Compressor & 230V-1ph-50Hz Fan

(2) Nominal conditions (EN13215), Evaporating temperatures at dew point, Superheat 10K, Subcooling 0K

(3) Rated conditions (EN13215), Evaporating temperature Midpoint -10°C, Ambient air temperature +32°C, Return Gas Temperature 20°C, Subcooling 0K

COP: Coefficient Of Performance link to EN13215 and ErP (Energy related Products) 2009/125/CE

SEPR: Seasonal Energy Performance Ratio link to EN13215 and ErP (Energy Related Products) 2009/125/CE

Tamb [°C]: Ambient Temperature

Te [°C]: Evaporating Temperature

Q [kW]: Cooling Capacity in Kilo Watt

P [kW]: Power Input in Kilo Watt

Version

A00: Without valves and receiver for capillary tubes

A01: With receiver, 2 stop valves, brackets and copper pipes for KP

A04: A01 + KP17 WB + FSA-kit + power cord


For regular updates and detailed capacities, please refer to **Coolselector®2** software


Model	Code	Version	Compressor	Electrical code (1)	Tamb [°C]	Cooling capacity Q [kW] (2)								EcoDesign (3)				Sound power level dB(A)	Sound pressure level 10 m dB(A)
						Te [°C]								Q [kW]	P [kW]	COP	SEPR		
						-25°C	-20°C	-15°C	-10°C	-5°C	0°C	5°C	10°C						
OP-MCRN030	114X5721	A02	MTZ018	E	27	0.980	1.391	1.884	2.457	3.109	3.837	4.636	5.500					76	45
					32	0.867	1.243	1.692	2.217	2.814	3.482	4.218	5.016	2.329	1.241	1.88			
					38	0.737	1.070	1.469	1.934	2.465	3.062	3.721	4.439						
					43	-	0.931	1.287	1.702	2.179	2.715	-	-						
					46	-	0.849	1.180	1.565	2.008	2.509	-	-						
OP-MCRN030	114X5722	A02	MTZ018	G	27	0.980	1.391	1.884	2.457	3.109	3.837	4.636	5.500					76	45
					32	0.867	1.243	1.692	2.217	2.814	3.482	4.218	5.016	2.329	1.241	1.88			
					38	0.737	1.070	1.469	1.934	2.465	3.062	3.721	4.439						
					43	-	0.931	1.287	1.702	2.179	2.715	-	-						
					46	-	0.849	1.180	1.565	2.008	2.509	-	-						
OP-MCRN038	114X5724 114X5790	A02 A14	MTZ022	E	27	1.455	1.959	2.556	3.243	4.017	4.873	5.802	6.798					74	43
					32	1.279	1.741	2.287	2.917	3.630	4.418	5.278	6.200	3.071	1.519	2.02			
					38	1.076	1.484	1.969	2.531	3.167	3.874	4.648	5.481						
					43	-	1.277	1.710	2.212	2.784	3.423	-	-						
					46	-	1.156	1.556	2.023	2.556	3.153	-	-						
OP-MCRN038	114X5723 114X5789	A02 A14	MTZ022	G	27	2.979	1.959	2.556	3.243	4.017	4.873	5.802	6.798					74	43
					32	1.279	1.741	2.287	2.917	3.630	4.418	5.278	6.200	3.071	1.519	2.02			
					38	1.076	1.484	1.969	2.531	3.167	3.874	4.648	5.481						
					43	-	1.277	1.710	2.212	2.784	3.423	-	-						
					46	-	1.156	1.556	2.023	2.556	3.153	-	-						
OP-MCRN048	114X5726 114X5792	A02 A14	MTZ028	E	27	2.012	2.709	3.524	4.461	5.522	6.706	8.012	9.436					74	43
					32	1.750	2.397	3.154	4.024	5.010	6.112	7.330	8.661	4.225	2.028	2.08			
					38	1.451	2.038	2.722	3.510	4.405	5.407	6.518	7.735						
					43	-	1.750	2.373	3.091	3.908	4.826	-	-						
					46	-	1.582	2.168	2.844	3.614	4.481	-	-						
OP-MCRN048	114X5728 114X5791	A02 A14	MTZ028	G	27	2.012	2.709	3.524	4.461	5.522	6.706	8.012	9.436					74	43
					32	1.750	2.397	3.154	4.024	5.010	6.112	7.330	8.661	4.225	2.028	2.08			
					38	1.451	2.038	2.722	3.510	4.405	5.407	6.518	7.735						
					43	-	1.750	2.373	3.091	3.908	4.826	-	-						
					46	-	1.582	2.168	2.844	3.614	4.481	-	-						
OP-MCRN054	114X5729	A02	MTZ032	E	27	2.378	3.136	4.021	5.037	6.182	7.453	8.847	10.356					74	43
					32	2.100	2.803	3.623	4.562	5.623	6.802	8.096	9.499	4.796	2.234	2.15			
					38	1.776	2.410	3.148	3.994	4.950	6.016	7.189	8.464						
					43	-	2.088	2.755	3.522	4.390	5.360	6.430	-						
					46	-	1.897	2.522	3.240	4.054	4.966	-	-						
OP-MCRN054	114X5731	A02	MTZ032	G	27	2.378	3.136	4.021	5.037	6.182	7.453	8.847	10.356					74	43
					32	2.100	2.803	3.623	4.562	5.623	6.802	8.096	9.499	4.796	2.234	2.15			
					38	1.776	2.410	3.148	3.994	4.950	6.016	7.189	8.464						
					43	-	2.088	2.755	3.522	4.390	5.360	-	-						
					46	-	1.897	2.522	3.240	4.054	4.966	-	-						

MBP
(1) E - 400V-3ph-50Hz Compressor & 230V-1ph-50Hz Fan

G - 230V-1ph-50Hz Compressor & 230V-1ph-50Hz Fan

(2) Nominal conditions (EN13215), Evaporating temperatures at dew point, Superheat 10K, Subcooling 0K

(3) Rated conditions (EN13215), Evaporating temperature Midpoint -10°C, Ambient air temperature +32°C, Return Gas Temperature 20°C, Subcooling 0K

COP: Coefficient Of Performance link to EN13215 and ErP (Energy related Products) 2009/125/CE

SEPR: Seasonal Energy Performance Ratio link to EN13215 and ErP (Energy Related Products) 2009/125/CE

Tamb [°C]: Ambient Temperature

Te [°C]: Evaporating Temperature

Q [kW]: Cooling Capacity in Kilo Watt

P [kW]: Power Input in Kilo Watt

Version

A02: Receiver + Stop valves + KP17WB pressure switch + Electrical box

A14: Filter drier + Sight glass + Receiver + Stop valves + KP17WB pressure switch + Electrical box

This table continues on the next page


For regular updates and detailed capacities, please refer to **Coolselector®2** software


Model	Code	Version	Compressor	Electrical code (1)	Tamb [°C]	Cooling capacity Q [kW] (2)								EcoDesign (3)				Sound power level dB(A)	Sound pressure level 10 m dB(A)
						Te [°C]								Q [kW]	P [kW]	COP	SEPR		
						-25°C	-20°C	-15°C	-10°C	-5°C	0°C	5°C	10°C						
OP-MCRN060	114X5732 114X5794	A02 A14	MTZ036	E	27	2.738	3.588	4.572	5.687	6.929	8.290	9.762	11.333					74	43
					32	2.450	3.238	4.146	5.174	6.317	7.570	8.926	10.376	5.448	2.707	2.01	2.85		
					38	2.104	2.817	3.634	4.555	5.579	6.702	7.919	9.222						
					43	-	2.465	3.205	4.037	4.961	5.975	-	-						
					46	-	2.254	2.947	3.725	4.589	5.537	-	-						
OP-MCRN060	114X5734 114X5793	A02 A14	MTZ036	G	27	2.738	3.588	4.572	5.687	6.929	8.290	9.762	11.333					74	43
					32	2.450	3.238	4.146	5.174	6.317	7.570	8.926	10.376	5.448	2.707	2.01	2.85		
					38	2.104	2.817	3.634	4.555	5.579	6.702	7.919	9.222						
					43	-	2.465	3.205	4.037	4.961	5.975	-	-						
					46	-	2.254	2.947	3.725	4.589	5.537	-	-						
OP-MCRN068	114X5735	A02	MTZ040	E	27	3.282	4.266	5.409	6.717	8.190	9.826	11.623	13.572					76	45
					32	2.964	3.880	4.942	6.152	7.514	9.027	10.689	12.494	6.463	3.005	2.15	2.77		
					38	2.575	3.409	4.368	5.459	6.686	8.048	9.547	11.177						
					43	-	3.009	3.881	4.871	5.982	7.217	-	-						
					46	-	2.767	3.585	4.512	5.554	6.712	-	-						
OP-MCRN086	114X5737 114X5795	A02 A14	MTZ050	E	27	3.782	5.021	6.492	8.200	10.149	12.335	14.754	17.396					84	53
					32	3.338	4.474	5.823	7.393	9.189	11.211	13.453	15.911	7.759	3.283	2.36	3.34		
					38	2.837	3.849	5.051	6.456	8.067	9.889	11.919	14.153						
					43	-	3.352	4.432	5.697	7.154	8.808	-	-						
					46	-	3.063	4.070	5.251	6.615	8.168	-	-						
OP-MCRN096	114X5739 114X5796	A02 A14	MTZ056	E	27	3.925	5.245	6.814	8.640	10.727	13.071	15.668	18.506					83	52
					32	3.465	4.680	6.125	7.809	9.738	11.912	14.326	16.972	8.201	3.578	2.29	3.14		
					38	2.947	4.037	5.332	6.845	8.583	10.550	12.743	15.156						
					43	-	3.526	4.696	6.065	7.644	9.436	-	-						
					46	-	3.228	4.323	5.606	7.089	8.776	-	-						
OP-MCRN108	114X5740 114X5797	A02 A14	MTZ064	E	27	4.700	6.176	7.927	9.961	12.280	14.880	17.750	20.876					83	52
					32	4.171	5.537	7.154	9.033	11.178	13.588	16.254	19.166	9.500	4.287	2.22	3.07		
					38	3.551	4.780	6.233	7.923	9.856	12.035	14.456	17.108						
					43	-	4.159	5.472	7.002	8.757	10.742	-	-						
					46	-	3.791	5.019	6.451	8.098	9.966	-	-						
OP-MGRN108	114X5743	A02	MTZ064	E	27	4.700	6.176	7.927	9.961	12.280	14.880	17.750	20.876					83	52
					32	4.171	5.537	7.154	9.033	11.178	13.588	16.254	19.166	9.500	4.217	2.25	3.13		
					38	3.551	4.780	6.233	7.923	9.856	12.035	14.456	17.108						
					43	-	4.159	5.472	7.002	8.757	10.742	-	-						
					46	-	3.791	5.019	6.451	8.098	9.966	-	-						

MBP
(1) E - 400V-3ph-50Hz Compressor & 230V-1ph-50Hz Fan

G - 230V-1ph-50Hz Compressor & 230V-1ph-50Hz Fan

(2) Nominal conditions (EN13215), Evaporating temperatures at dew point, Superheat 10K, Subcooling 0K

(3) Rated conditions (EN13215), Evaporating temperature Midpoint -10°C, Ambient air temperature +32°C, Return Gas Temperature 20°C, Subcooling 0K

COP: Coefficient Of Performance link to EN13215 and ErP (Energy related Products) 2009/125/CE

SEPR: Seasonal Energy Performance Ratio link to EN13215 and ErP (Energy Related Products) 2009/125/CE

Tamb [°C]: Ambient Temperature

Te [°C]: Evaporating Temperature

Q [kW]: Cooling Capacity in Kilo Watt

P [kW]: Power Input in Kilo Watt

Version

A02: Receiver + Stop valves + KP17WB pressure switch + Electrical box

A14: Filter drier + Sight glass + Receiver + Stop valves + KP17WB pressure switch + Electrical box

This table continues on the next page


For regular updates and detailed capacities, please refer to **Coolselector®2** software


Model	Code	Version	Compressor	Electrical code (1)	Tamb [°C]	Cooling capacity Q [kW] (2)								EcoDesign (3)				Sound power level dB(A)	Sound pressure level 10 m dB(A)
						Te [°C]								Q [kW]	P [kW]	COP	SEPR		
						-25°C	-20°C	-15°C	-10°C	-5°C	0°C	5°C	10°C						
OP-MCRN121	114X5744	A02	MTZ072	E	27	5.284	6.897	8.788	10.957	13.401	16.109	19.069	22.261					82	51
					32	4.675	6.160	7.903	9.907	12.170	14.685	17.440	20.419	10.430	4.787	2.18	3.03		
					38	3.993	5.320	6.881	8.682	10.723	13.001	15.507	18.228						
					43	-	4.652	6.058	7.686	9.540	11.618	-	-						
					46	-	4.264	5.576	7.099	8.839	10.795	-	-						
OP-MGRN121	114X5746	A02	MTZ072	E	27	5.284	6.897	8.788	10.957	13.401	16.109	19.069	22.261					82	51
					32	4.675	6.160	7.903	9.907	12.170	14.685	17.440	20.419	10.430	4.717	2.21	3.08		
					38	3.993	5.320	6.881	8.682	10.723	13.001	15.507	18.228						
					43	-	4.652	6.058	7.686	9.540	11.618	-	-						
					46	-	4.264	5.576	7.099	8.839	10.795	-	-						
OP-MCRN136	114X5747	A02	MTZ080	E	27	6.204	7.979	10.021	12.327	14.886	17.685	20.702	23.917					82	51
					32	5.548	7.192	9.079	11.209	13.574	16.164	18.961	21.948	11.820	5.719	2.07	2.83		
					38	4.789	6.272	7.969	9.884	12.012	14.347	16.877	19.586						
					43	-	5.522	7.058	8.789	10.717	12.838	-	-						
					46	-	5.077	6.515	8.136	9.942	11.933	-	-						
OP-MGRN136	114X5749	A02	MTZ080	E	27	6.204	7.979	10.021	12.327	14.886	17.685	20.702	23.917					82	51
					32	5.548	7.192	9.079	11.209	13.574	16.164	18.961	21.948	11.820	5.649	2.09	2.87		
					38	4.789	6.272	7.969	9.884	12.012	14.347	16.877	19.586						
					43	-	5.522	7.058	8.789	10.717	12.838	-	-						
					46	-	5.077	6.515	8.136	9.942	11.933	-	-						
OP-MGRN171	114X5750	A02	MTZ100	E	27	7.159	9.542	12.363	15.630	19.338	23.478	28.030	32.971					87	56
					32	6.441	8.648	11.249	14.253	17.662	21.470	25.665	30.227	14.970	7.150	2.09	3.02		
					38	5.553	7.554	9.894	12.587	15.641	19.055	22.823	26.932						
					43	-	6.622	8.749	11.186	13.947	17.036	-	-						
					46	-	6.053	8.053	10.340	12.926	15.821	-	-						
OP-MGRN215	114X5753	A02	MTZ125	E	27	9.526	12.393	15.755	19.618	23.976	28.816	34.117	39.850					86	55
					32	8.441	11.075	14.168	17.730	21.759	26.245	31.173	36.516	18.650	8.915	2.09	3.03		
					38	7.227	9.575	12.339	15.533	19.160	23.216	27.688	32.556						
					43	-	8.385	10.870	13.752	17.039	20.730	-	-						
					46	-	7.694	10.010	12.703	15.783	19.254	-	-						
OP-MGRN242	114X5754	A02	MTZ144	E	27	11.170	14.359	18.047	22.232	26.901	32.033	37.594	43.548					85	54
					32	9.988	12.938	16.342	20.204	24.515	29.259	34.407	39.929	21.290	10.310	2.06	2.91		
					38	8.608	11.260	14.314	17.779	21.653	25.923	30.571	35.570						
					43	-	9.883	12.637	15.764	19.266	23.138	-	-						
					46	-	9.066	11.636	14.557	17.834	21.464	-	-						
OP-MGRN271	114X5757	A02	MTZ160	E	27	12.084	15.502	19.434	23.875	28.803	34.187	39.984	46.143					84	53
					32	10.816	13.982	17.616	21.717	26.270	31.249	36.617	42.330	22.911	11.650	1.97	2.74		
					38	9.337	12.187	15.452	19.135	23.229	27.713	32.560	37.731						
					43	-	10.714	13.661	16.987	20.690	24.756	-	-						
					46	-	9.838	12.590	15.698	19.163	22.975	-	-						

MBP
(1) E - 400V-3ph-50Hz Compressor & 230V-1ph-50Hz Fan

G - 230V-1ph-50Hz Compressor & 230V-1ph-50Hz Fan

(2) Nominal conditions (EN13215), Evaporating temperatures at dew point, Superheat 10K, Subcooling 0K

(3) Rated conditions (EN13215), Evaporating temperature Midpoint -10°C, Ambient air temperature +32°C, Return Gas Temperature 20°C, Subcooling 0K

COP: Coefficient Of Performance link to EN13215 and ErP (Energy related Products) 2009/125/CE

SEPR: Seasonal Energy Performance Ratio link to EN13215 and ErP (Energy Related Products) 2009/125/CE

Tamb [°C]: Ambient Temperature

Te [°C]: Evaporating Temperature

Q [kW]: Cooling Capacity in Kilo Watt

P [kW]: Power Input in Kilo Watt

Version

A02: Receiver + Stop valves + KP17WB pressure switch + Electrical box


For regular updates and detailed capacities, please refer to **Coolselector®2** software


Application	Code number			Model number	Compressor Model	Electrical Code (1)	Refrigerant (2)	Condenser Coil			Fan		Receiver	Dimensions				Connection		Weight	
								Type	Airflow (m³/h)	Internal Volume (dm³)	Number	Blade ø (mm)	Volume (L)	Chassis	Height mm	Width mm	Length mm	Suction valve mm	Liquid valve mm	Gross Kg	Net Kg
	A09	A10	A11																		
LBP	114F0202	114F0203	114F0201	OP-LCNC004NY	NLY45LAB	G	N	BG2	231	0.25	1	200	0.114	3	226	271	513	6	6	21	19
LBP	114F0205	114F0206	114F0204	OP-LCNC006NY	NLY60LAB	G	N	BG2	231	0.25	1	200	0.114	3	226	271	513	6	6	19	17
LBP	114F0308	114F0309	114F0307	OP-LCNC008NY	NLY80LAB	G	N	BG3	518	0.31	1	230	0.114	4	256	307	513	6	6	20	18
LBP	114F0411	114F0412	114F0410	OP-LCNC011NY	NPY12LAB	G	N	BG4/5	631	0.4	1	254	0.165	8	296	321	513	8	6	25	22
LBP	114F0414	114F0415	114F0413	OP-LCNC016NP	NPT16LA	G	N	BG4/5	631	0.4	1	254	0.165	8	296	321	513	8	6	26	23
LBP	114F0417	114F0418	114F0416	OP-LCNC023NX	NX23FBa	G	N	BG4/5	631	0.4	1	254	0.165	8	296	321	513	10	6	31	28
LBP	114F0620	114F0621	114F0619	OP-LCNC034NS	NS34FB	G	N	BG6	1132	0.63	1	300	0.32	13	350	445	480	12	6	47	41
MBP	114F1202	114F1203	114F1201	OP-MCNC003NB	NBC30RA	G	N	BG2	231	0.25	1	200	0.114	3	226	286	513	6	6	16	14
MBP	114F1205	114F1206	114F1204	OP-MCNC004NY	NLY45RAB	G	N	BG2	231	0.25	1	200	0.114	3	226	278	513	6	6	21	19
MBP	114F1308	114F1309	114F1307	OP-MCNC006NY	NLY60RAB	G	N	BG3	518	0.31	1	230	0.114	4	256	307	513	6	6	20	18
MBP	114F1411	114F1412	114F1410	OP-MCNC008NY	NLY80RAB	G	N	BG4/5	631	0.4	1	254	0.165	8	296	321	513	6	6	25	22
MBP	114F1414	114F1415	114F1413	OP-MCNC009NY	NLY90RAB	G	N	BG4/5	631	0.4	1	254	0.165	8	296	321	513	6	6	25	22
MBP	114F1417	114F1418	114F1416	OP-MCNC011NY	NLY12RAB	G	N	BG4/5	631	0.4	1	254	0.165	8	296	321	513	8	6	26	23
MBP	114F1420	114F1421	114F1419	OP-MCNC014NP	NPT14RA	G	N	BG4/5	631	0.4	1	254	0.165	8	296	321	513	8	6	27	24
MBP	114F1623	114F1624	114F1622	OP-MCNC016NP	NPT16RA	G	N	BG6	1132	0.63	1	300	0.32	13	350	445	480	8	6	36	32
MBP	114F1626	114F1627	114F1625	OP-MCNC018NX	NX18TBa	G	N	BG6	1132	0.63	1	300	0.32	13	350	445	480	10	6	29	26
MBP	114F1629	114F1630	114F1628	OP-MCNC020NX	NX21TBa	G	N	BG6	1132	0.63	1	300	0.32	13	350	445	480	10	6	39	35

(1) E - 400V-3ph-50Hz Compressor & 230V-1ph-50Hz Fan

G - 230V-1ph-50Hz Compressor & 230V-1ph-50Hz Fan

(2) N - R290

Application	Code number			Model number	Compressor Model	Electrical Code (1)	Refrigerant (2)	Condenser Coil			Fan		Receiver	Dimensions				Connection		Weight	
								Type	Airflow (m³/h)	Internal Volume (dm³)	Number	Blade ø (mm)	Volume (L)	Chassis	Height mm	Width mm	Length mm	Suction valve inch	Liquid valve inch	Gross Kg	Net Kg
	A00	A01	A04																		
LBP	114X1208	114X1209	114X1211	OP-LCHC004TL	TL4CL	G	H	BG2	231	0.25	1	200	0.8	2	226	303	446	1/4"	1/4"	19	17
LBP		114X1221		OP-LCQC004ML	MLY45LAb	G	Q	BG2	231	0.25	1	200	0.8	2	226	303	504	3/8"	1/4"	19	17
LBP	114X1216	114X1217	114X1219	OP-LCHC006FR	FR6CL	G	H	BG2	231	0.25	1	200	0.8	2	226	312	446	3/8"	1/4"	19	17
LBP		114X1337		OP-LCQC006ML	MLY60LAb	G	Q	BG3	518	0.31	1	230	1.1	6	256	318	506	3/8"	1/4"	22	20
LBP	114X1328	114X1329	114X1331	OP-LCHC007NL	NL7CLX	G	H	BG3	518	0.31	1	230	1.1	5	256	318	470	3/8"	1/4"	22	20
LBP	114X1324	114X1325	114X1327	OP-LCHC008FR	FR8.5CL	G	H	BG3	518	0.31	1	230	1.1	5	256	318	470	3/8"	1/4"	22	20
LBP	114X1304	114X1301	114X1302	OP-LCHC008NL	NL8.4CLX	G	H	BG3	518	0.31	1	230	1.1	5	256	318	470	3/8"	1/4"	22	20
LBP		114X1341		OP-LCQC008ML	MLY80LAb	G	Q	BG3	518	0.31	1	230	1.1	6	256	318	506	3/8"	1/4"	22	20
LBP	114X1440	114X1441	114X1443	OP-LCHC012SC	SC12CL	G	H	BG4/5	631	0.4	1	254	1.1	9	296	328	465	3/8"	1/4"	26	23
LBP	114X1444			OP-LCHC012SC	SC12CLX.2	G	H	BG4/5	631	0.4	1	254	1.1	9	296	328	465	3/8"	1/4"	26	23
LBP		114X1449		OP-LCQC012ML	MLY12LAb	G	Q	BG4/5	631	0.4	1	254	1.1	12	296	331	504	3/8"	1/4"	26	23
LBP		114X1569		OP-LCQC012MP	MPT12LA	G	Q	BG4/5	631	0.4	1	254	1.1	12	296	328	504	3/8"	1/4"	26	23
LBP		114X1573		OP-LCQC014MP	MPT14LA	G	Q	BG4/5	631	0.4	1	254	1.1	12	296	322	504	1/2"	1/4"	26	23
LBP	114X1548	114X1549	114X1551	OP-LCHC015SC	SC15CLX	G	H	BG4/5	631	0.4	1	254	1.1	10	296	328	487	3/8"	1/4"	26	23
LBP	114X1556	114X1557	114X1559	OP-LCHC018SC	SC18CL	G	H	BG4/5	631	0.4	1	254	1.1	11	296	328	516	1/2"	1/4"	26	23
LBP	114X1600	114X1601	114X1602	OP-LCHC021SC	SC21CL	G	H	BG6	1150	0.63	1	300	1.1	14	347	445	610	1/2"	1/4"	48	42
LBP		114X1673		OP-LCHC026GS	GS26CLX	G	H	BG6	1150	0.63	1	300	2.4	13	337	425	480	1/2"	3/8"	48	42
LBP		114X1781	114X1783	OP-LCHC034GS	GS34CLX	G	H	BG7	990	0.84	1	300	2.4	13	337	425	480	1/2"	3/8"	50	44
MBP	114X0104	114X0105	114X0107	OP-MCGC003TL	TL3GX	G	G	BG1	243	0.13	1	172	0.8	1	198	290	424	1/4"	1/4"	16	14
MBP	114X0108	114X0109	114X0111	OP-MCGC004TL	TL4GX	G	G	BG1	243	0.13	1	172	0.8	1	202	290	424	1/4"	1/4"	16	14
MBP	114X0301	114X0302	114X0303	OP-MCHC004TL	TL4DL	G	H	BG3	518	0.31	1	230	1.1	7	256	320	458	3/8"	1/4"	22	20
MBP	114X0112	114X0113	114X0115	OP-MCGC005TL	TL5GX	G	G	BG1	243	0.13	1	172	0.8	1	202	290	424	1/4"	1/4"	16	14
MBP	114X0200	114X0201	114X0203	OP-MCGC006FR	FR6GX	G	G	BG2	231	0.25	1	200	0.8	2	226	318	446	3/8"	1/4"	19	17
MBP	114X2316	114X2317	114X2319	OP-MCHC006FR	FR6DLX	G	H	BG3	518	0.31	1	230	1.1	7	256	318	458	3/8"	1/4"	22	20
MBP	114X0228			OP-MCGC006NL	NL6.1MF	G	G	BG2	231	0.25	1	200	0.8	2	226	303	432	3/8"	1/4"	19	17
MBP	114X0216	114X0217	114X0219	OP-MCGC007FR	FR7.5GX	G	G	BG2	231	0.25	1	200	0.8	2	226	318	446	3/8"	1/4"	19	17
MBP	114X0244			OP-MCGC007NL	NL7.3MF	G	G	BG2	231	0.25	1	200	0.8	2	226	303	432	3/8"	1/4"	19	17
MBP	114X2424	114X2425	114X2427	OP-MCHB007NF	NF7MLX	G	H	BG4/5	631	0.4	1	254	1.1	9	296	328	465	3/8"	1/4"	26	23
MBP	114X0224	114X0225	114X0227	OP-MCGC008FR	FR8.5GX	G	G	BG2	231	0.25	1	200	0.8	2	226	318	446	3/8"	1/4"	19	17
MBP	114X0204	114X0205		OP-MCGC008NL	NL8.4MF	G	G	BG2	231	0.25	1	200	0.8	2	226	303	446	3/8"	1/4"	19	17
MBP	114X0352			OP-MCGC008NL	NL8.4MF	G	G	BG3	518	0.31	1	230	-	4	256	307	444	3/8"	1/4"	22	20
MBP			114X0223	OP-MCGC010SC	SC10GX	G	G	BG2	231	0.25	1	200	0.8	2	226	303	446	3/8"	1/4"	19	17
MBP	114X0403	114X0404	114X0405	OP-MCHC010SC	SC10MLX	G	H	BG4/5	631	0.4	1	254	1.1	10	296	328	487	3/8"	1/4"	26	23
MBP	114X0336	114X0337	114X0339	OP-MCGC011FR	FR11GX	G	G	BG3	518	0.31	1	230	1.1	7	256	320	458	3/8"	1/4"	22	20
MBP	114X0340	114X0341	114X0343	OP-MCGC012SC	SC12GX	G	G	BG3	518	0.31	1	230	1.1	7	256	320	458	3/8"	1/4"	22	20
MBP	114X0406	114X0407	114X0408	OP-MCHC013SC	SC12MLX	G	H	BG4/5	631	0.4	1	254	1.1	10	296	328	487	3/8"	1/4"	26	23
MBP	114X0448	114X0449	114X0451	OP-MCGC015SC	SC15GX	G	G	BG4/5	631	0.4	1	254	1.1	9	296	328	465	3/8"	1/4"	26	23
MBP		114X2649	114X2651	OP-MCHC015SC	SC15MLX	G	H	BG6	1132	1.1	1	300	1.1	14	347	445	610	1/2"	1/4"	48	42
MBP	114X0556	114X0557	114X0559	OP-MCGC018SC	SC18G	G	G	BG4/5	631	0.4	1	254	1.1	10	296	328	487	3/8"	1/4"	26	23
MBP		114X0702	114X0703	OP-MCHC018SC	SC18MLX	G	H	BG7	990	0.84	1	300	1.1	14	347	445	610	1/2"	1/4"	50	44
MBP	114X0568			OP-MCGC021SC	SC21MF	G	G	BG4/5	631	0.4	1	254	1.1	10	296	328	473	3/8"	1/4"	26	23
MBP	114X0564	114X0565	114X0567	OP-MCGC021SC	SC21GX	G	G	BG4/5	631	0.4	1	254	1.1	11	296	328	473	3/8"	1/4"	26	23
MBP		114X2765	114X2767	OP-MCHC021GS	GS21MLX	G	H	BG7	990	0.84	1	300	1.6	13	337	425	480	5/8"	3/8"	50	44
MBP		114X0773		OP-MCGC026GS	GS26MFX	G	G	BG7	990	0.84	1	300	2.4	13	337	425	480	3/8"	1/4"	50	44
MBP		114X0781		OP-MCGC034GS	GS34MFX	G	G	BG7	990	0.84	1	300	2.4	13	337	425	480	1/2"	3/8"	50	44

(1) E - 400V-3ph-50Hz Compressor & 230V-1ph-50Hz Fan

G - 230V-1ph-50Hz Compressor & 230V-1ph-50Hz Fan

(2) G - R134a/R513A

H - R404A/R507

Q - R452A/R404A/R507

Application	Code number	Model number	Compressor Model	Electrical Code (1)	Refrigerant (2)	Condenser Coil			Fan		Receiver	Dimensions				Connection		Weight	
						Type	Airflow	Internal Volume	Number	Blade ø		Volume	Chassis	Height	Width	Length	Suction valve	Liquid valve	Gross
							(m²/h)	(dm³)			(mm)			(L)	mm	mm	mm	inch	
LBP	114X5758	OP-LCQN048NTA02E	NTZ048	E	Q	A7	1550	0.6	1	350	3	A	545	630	650	5/8"	3/8"	62	52
LBP	114X5759	OP-LCQN048NTA02G	NTZ048	G	Q	A7	1550	0.6	1	350	3	A	545	630	650	5/8"	3/8"	62	52
LBP	114X5761	OP-LCQN068NTA02E	NTZ068	E	Q	D7	3550	0.6	1	450	5.2	C	705	900	900	5/8"	1/2"	88	78
LBP	114X5784	OP-LCQN068NTA14E	NTZ068	E	Q	D7	3550	0.6	1	450	5.2	C	705	900	900	5/8"	1/2"	88	78
LBP	114X5762	OP-LCQN068NTA02G	NTZ068	G	Q	D7	3550	0.6	1	450	5.2	C	705	900	900	5/8"	1/2"	88	78
LBP	114X5783	OP-LCQN068NTA14G	NTZ068	G	Q	D7	3550	0.6	1	450	5.2	C	705	900	900	5/8"	1/2"	88	78
LBP	114X5764	OP-LCQN096NTA02E	NTZ096	E	Q	G7	4300	1.62	1	500	7.3	D	836.5	1200	800	7/8"	1/2"	120	103
LBP	114X5766	OP-LGQN096NTA02E	NTZ096	E	Q	N8	3450	1.54	2	350	7.3	B	693.5	1500	870	7/8"	1/2"	127	105
LBP	114X5785	OP-LGQN096NTA14E	NTZ096	E	Q	N8	3450	1.54	2	350	7.3	B	693.5	1500	870	7/8"	1/2"	127	105
LBP	114X5768	OP-LCQN108NTA02E	NTZ108	E	Q	G7	4300	1.62	1	500	7.3	D	836.5	1200	800	7/8"	1/2"	120	103
LBP	114X5786	OP-LCQN108NTA14E	NTZ108	E	Q	G7	4300	1.62	1	500	7.3	D	836.5	1200	800	7/8"	1/2"	120	103
LBP	114X5769	OP-LGQN108NTA02E	NTZ108	E	Q	N8	3450	1.54	2	350	7.3	B	693.5	1500	870	7/8"	1/2"	127	105
LBP	114X5771	OP-LGQN136NTA02E	NTZ136	E	Q	N8	3450	1.54	2	350	7.3	B	693.5	1500	870	7/8"	1/2"	127	105
LBP	114X5772	OP-LCQN136NTA02E	NTZ136	E	Q	G7	4300	1.62	1	500	7.3	D	836.5	1200	800	7/8"	1/2"	120	103
LBP	114X5787	OP-LCQN136NTA14E	NTZ136	E	Q	G7	4300	1.62	1	500	7.3	D	836.5	1200	800	7/8"	1/2"	120	103
LBP	114X5774	OP-LGQN215NTA02E	NTZ215	E	Q	J7	10700	1.97	2	560	14	E	836.5	1500	870	11/8"	5/8"	192	170
LBP	114X5788	OP-LGQN215NTA14E	NTZ215	E	Q	J7	10700	1.97	2	560	14	E	836.5	1500	870	11/8"	5/8"	192	170
LBP	114X5776	OP-LGQN271NTA02E	NTZ271	E	Q	J7	10700	1.97	2	560	14	E	836.5	1500	870	11/8"	5/8"	194	172
MBP	114X5721	OP-MCRN030MTA02E	MTZ018	E	R	A7	1550	0.4	1	350	3	A	545	630	650	1/2"	3/8"	62	52
MBP	114X5722	OP-MCRN030MTA02G	MTZ018	G	R	A7	1550	0.4	1	350	3	A	545	630	650	1/2"	3/8"	62	52
MBP	114X5723	OP-MCRN038MTA02G	MTZ022	G	R	A7	1550	0.4	1	350	3	A	545	630	650	1/2"	3/8"	62	52
MBP	114X5789	OP-MCRN038MTA14G	MTZ022	G	R	A7	1550	0.4	1	350	3	F	545	900	900	1/2"	3/8"	62	52
MBP	114X5724	OP-MCRN038MTA02E	MTZ022	E	R	A7	1550	0.4	1	350	3	A	545	630	650	1/2"	3/8"	62	52
MBP	114X5790	OP-MCRN038MTA14E	MTZ022	E	R	A7	1550	0.4	1	350	3	F	545	900	900	1/2"	3/8"	62	52
MBP	114X5726	OP-MCRN048MTA02E	MTZ028	E	R	D7	3550	0.6	1	450	5.2	C	705	900	900	1/2"	1/2"	87	77
MBP	114X5792	OP-MCRN048MTA14E	MTZ028	E	R	D7	3550	0.6	1	450	5.2	C	705	900	900	1/2"	1/2"	87	77
MBP	114X5728	OP-MCRN048MTA02G	MTZ028	G	R	D7	3550	0.6	1	450	5.2	C	705	900	900	1/2"	1/2"	87	77
MBP	114X5791	OP-MCRN048MTA14G	MTZ028	G	R	D7	3550	0.6	1	450	5.2	C	705	900	900	1/2"	1/2"	87	77
MBP	114X5729	OP-MCRN054MTA02E	MTZ032	E	R	D7	3550	0.6	1	450	5.2	C	705	900	900	5/8"	1/2"	89	79
MBP	114X5731	OP-MCRN054MTA02G	MTZ032	G	R	D7	3550	0.6	1	450	5.2	C	705	900	900	5/8"	1/2"	89	79
MBP	114X5732	OP-MCRN060MTA02E	MTZ036	E	R	D7	4180	0.6	1	500	5.2	C	705	900	900	5/8"	1/2"	92	82
MBP	114X5794	OP-MCRN060MTA14E	MTZ036	E	R	D7	4180	0.6	1	500	5.2	C	705	900	900	5/8"	1/2"	92	82
MBP	114X5734	OP-MCRN060MTA02G	MTZ036	G	R	D7	4180	0.6	1	500	5.2	C	705	900	900	5/8"	1/2"	92	82
MBP	114X5793	OP-MCRN060MTA14G	MTZ036	G	R	D7	4180	0.6	1	500	5.2	C	705	900	900	5/8"	1/2"	92	82
MBP	114X5735	OP-MCRN068MTA02E	MTZ040	E	R	G7	4300	1.62	1	500	7.3	D	836.5	1200	800	5/8"	1/2"	111	94
MBP	114X5737	OP-MCRN086MTA02E	MTZ050	E	R	G7	4300	1.62	1	500	7.3	D	836.5	1200	800	7/8"	1/2"	122	105
MBP	114X5795	OP-MCRN086MTA14E	MTZ050	E	R	G7	4300	1.62	1	500	7.3	D	836.5	1200	800	7/8"	1/2"	122	105
MBP	114X5739	OP-MCRN096MTA02E	MTZ056	E	R	G7	4300	1.62	1	500	7.3	D	836.5	1200	800	7/8"	1/2"	124	107
MBP	114X5796	OP-MCRN096MTA14E	MTZ056	E	R	G7	4300	1.62	1	500	7.3	D	836.5	1200	800	7/8"	1/2"	124	107
MBP	114X5740	OP-MCRN108MTA02E	MTZ064	E	R	G7	4300	1.62	1	500	7.3	D	836.5	1200	800	7/8"	1/2"	124	107
MBP	114X5797	OP-MCRN108MTA14E	MTZ064	E	R	G7	4300	1.62	1	500	7.3	D	836.5	1200	800	7/8"	1/2"	124	107
MBP	114X5743	OP-MGRN108MTA02E	MTZ064	E	R	N8	3450	1.54	2	350	7.3	B	693.5	1500	870	7/8"	1/2"	131	109
MBP	114X5744	OP-MCRN121MTA02E	MTZ072	E	R	G7	4300	1.62	1	500	7.3	D	836.5	1200	800	11/8"	1/2"	125	108
MBP	114X5746	OP-MGRN121MTA02E	MTZ072	E	R	N8	3450	1.54	2	350	7.3	B	693.5	1500	870	11/8"	1/2"	132	110
MBP	114X5747	OP-MCRN136MTA02E	MTZ080	E	R	G7	4300	1.62	1	500	7.3	D	836.5	1200	800	11/8"	1/2"	125	108
MBP	114X5749	OP-MGRN136MTA02E	MTZ080	E	R	N8	3450	1.54	2	350	7.3	B	693.5	1500	870	11/8"	1/2"	132	110
MBP	114X5750	OP-MGRN171MTA02E	MTZ100	E	R	J7	10700	1.97	2	560	14	E	836.5	1500	870	11/8"	5/8"	190	168
MBP	114X5753	OP-MGRN215MTA02E	MTZ125	E	R	J7	10700	1.97	2	560	14	E	836.5	1500	870	11/8"	5/8"	197	175
MBP	114X5754	OP-MGRN242MTA02E	MTZ144	E	R	J7	10700	1.97	2	560	14	E	836.5	1500	870	11/8"	5/8"	197	175
MBP	114X5757	OP-MGRN271MTA02E	MTZ160	E	R	J7	10700	1.97	2	560	14	E	836.5	1500	870	11/8"	5/8"	199	177

(1) E - 400V-3ph-50Hz Compressor & 230V-1ph-50Hz Fan

G - 230V-1ph-50Hz Compressor & 230V-1ph-50Hz Fan

(2) R - R134a, R404A/R507, R407A, R407C, R407F, R448A/R449A, R452A, R134a/R513A

Q - R404A/R507, R452A

Designation	OP-LCNC004	OP-LCNC006	OP-LCNC008	OP-LCNC011	OP-LCNC016	OP-LCNC023	OP-LCNC034
Compressor Description	NLY45LAb	NLY60LAb	NLY80LAb	NPY12LAb	NPT16LA	NX23FBa	NS34FB
A09	114F0202	114F0205	114F0308	114F0411	114F0414	114F0417	114F0620
A10	114F0203	114F0206	114F0309	114F0412	114F0415	114F0418	114F0621
A11	114F0201	114F0204	114F0307	114F0410	114F0413	114F0416	114F0619
Condenser coil type	BG2	BG2	BG3	BG4/5	BG4/5	BG4/5	BG6
Electrical code	G	G	G	G	G	G	G
Refrigerant letter code	N	N	N	N	N	N	N
Spare Parts							
Compressor single pack	123B3103	123B3107	123B3115	123B3121	123B3124	123B3128	123B3167
Compressor Industrial pack	123F3103	123F3107	123F3115	123F3121	123F3124	123F3128	123F3167
Condenser	118U0029	118U0029	118U0030	118U0031	118U0031	118U0031	118U0068
HP switch	061F6701	061F6701	061F6701	061F6701	061F6701	061F6701	061F6701
LP switch	061F7959	061F7959	061F7959	061F7959	061F7959	061F7959	061F7959
Fan blade	118U0037	118U0037	118U0038	118U0039	118U0039	118U0039	118U0040
Fan motor	118U1008*	118U1008*	118U1008*	118U1009*	118U1009*	118U1009*	118U1010*
Fan guard	118U0042	118U0042	118U0043	118U0044	118U0044	118U0044	118U0066
Combo filter drier receiver	023Z7012	023Z7012	023Z7012	023Z7013	023Z7013	023Z7013	023Z7007
E box	118U0049	118U0049	118U0049	118U0049	118U0049	118U0049	118U0049
Electrical Characteristics							
MCC Fan (A)	0.25	0.25	0.25	0.39	0.39	0.39	0.19
LRA Compressor (A)	6.7	10	10.5	14.2	19	30	34.5

MCC - Max Continuous Current
LRA - Locked Rotor Amps

Electrical code
E : 400V-3ph-50Hz Compressor & 230V-1ph-50Hz Fan
G : 230V-1ph-50Hz Compressor & 230V-1ph-50Hz Fan

* EC fans

Designation	OP-LCHC004	OP-LCQC004	OP-LCHC006	OP-LCQC006	OP-LCHC007	OP-LCHC008	OP-LCQC008	OP-LCHC012
Compressor Description	TL4CLX	MLY45Lab	FR6CLX	MLY60Lab	NL7CLX	NL8.4CLX	MLY80Lab	SC12CLX
A00	114X1208		114X1216		114X1328	114X1304		114X1440
A01	114X1209	114X1221	114X1217	114X1337	114X1329	114X1301	114X1341	114X1441
A04	114X1211		114X1219		114X1331	114X1302		114X1443
Condenser coil type	BG2	BG2	BG2	BG3	BG3	BG3	BG3	BG4
Electrical code	G	G	G	G	G	G	G	G
Refrigerant letter code	H	H	H	H	H	H	H	H
Spare Parts								
Compressor single pack	195B0021	123B2106	195B0032	123B2110	195B0350	195B0481	123G2114	195B0379
Condenser	118U0029	118U0029	118U0029	118U0030	118U0030	118U0030	118U0030	118U0031
Dual pressure switch	060-539366	-	060-539366	-	060-539366	060-539366	-	060-539366
Fan motor	118U0032	118U0032	118U0032	118U0033	118U0033	118U0033	118U0033	118U0034
Fan guard	118U0042	118U0042	118U0042	118U0043	118U0043	118U0043	118U0043	118U0044
Receiver	118U1024	118U1024	118U1024	118U1025	118U1025	118U1025	118U1025	118U1025
Suction valve	118U0485	118U0079	118U0079	118U0079	118U0079	118U0079	118U0079	118U0079
Liquid valve	118U0045	118U0045	118U0045	118U0045	118U0045	118U0045	118U0045	118U0045
E box	118U0049	118U0049	118U0049	118U0049	118U0049	118U0049	118U0049	118U0049
Electrical Characteristics								
LRA Compressor (A)	5.7	8.1	8.2	10	10.4	2.5	14	14.8
MCC Fan (A)	0.19	0.19	0.19	0.25	0.25	0.25	0.25	0.39

Designation	OP-LCHC012	OP-LCHC021	OP-LCQC012	OP-LCQC012	OP-LCQC014	OP-LCHC015	OP-LCHC018	OP-LCHC026	OP-LCHC034
Compressor Description	SC12CLX.2	SC21CL	MPT12LA	MLY12Lab	MPT14LA	SC15CLX	SC18CLX	GS26CLX	GS34CLX
A00	114X1444	114X1600				114X1548	114X1556		
A01		114X1601	114X1449	114X1569	114X1573	114X1549	114X1557	114X1673	114X1781
A04		114X1602				114X1551	114X1559		114X1783
Condenser coil type	BG4	BG6	BG4	BG4	BG4	BG4	BG4/5	BG6	BG7
Electrical code	G	G	G	G	G	G	G	G	G
Refrigerant letter code	H	H	H	H	H	H	H	H	H
Spare Parts									
Compressor single pack	195B0379	195B0640	123B2120	123B2123	123B2126	195B0646	195B0066	195B0501	195B0439
Condenser	118U0031	118U0068	118U0031	118U0031	118U0031	118U0031	118U0031	118U0054	118U0069
Dual pressure switch	-	060-539366	-	-	-	060-539366	060-539366	-	060-539366
Fan motor	118U0034	118U1010*	118U0034	118U0034	118U0034	118U0034	118U0034	118U0058	118U0058
Fan guard	118U0044	118U0066	118U0044	118U0044	118U0044	118U0044	118U0044	118U0066	-
Receiver	-	118U1025	118U1025	118U1025	118U1025	118U1025	118U1025	118U1027	118U1027
Suction valve	-	118U0047	118U0079	118U0047	118U0047	118U0047	118U0047	118U0047	118U0047
Liquid valve	-	118U0045	118U0045	118U0045	118U0045	118U0045	118U0045	118U0079	118U0079
E box	118U0049	118U0049	118U0049	118U0049	118U0049	118U0049	118U0049	118U0049	118U0049
Electrical Characteristics									
LRA Compressor (A)	19.6	8.2	13.9	20	16	18.6	20	25.7	40
MCC Fan (A)	0.39	0.19	0.39	0.39	0.39	0.39	0.39	0.75	0.75

MCC - Max Continuous Current
LRA - Locked Rotor Amps

Electrical code
E : 400V-3ph-50Hz Compressor & 230V-1ph-50Hz Fan
G : 230V-1ph-50Hz Compressor & 230V-1ph-50Hz Fan

* EC fans

Designation	OP-MCNC003	OP-MCNC004	OP-MCNC006	OP-MCNC008	OP-MCNC009
Compressor Description	NBC30RA	NLY45RAb	NLY60RAb	NLY80RAb	NLY90RAb
A09	114F1202	114F1205	114F1308	114F1411	114F1414
A10	114F1203	114F1206	114F1309	114F1412	114F1415
A11	114F1201	114F1204	114F1307	114F1410	114F1413
Condenser coil type	BG2	BG2	BG3	BG4/5	BG4/5
Electrical code	G	G	G	G	G
Refrigerant letter code	N	N	N	N	N
Spare Parts					
Compressor single pack	123B8310	123B3505	123B3507	123B3511	123B3513
Compressor Industrial pack	123B8310	123F3505	123F3507	123F3511	123F3513
Condenser	118U0029	118U0029	118U0030	118U0031	118U0031
HP switch	061F6701	061F6701	061F6701	061F6701	061F6701
LP switch	061F7958	061F7958	061F7958	061F7958	061F7958
Fan blade	118U0037	118U0037	118U0038	118U0039	118U0039
Fan motor	118U1008*	118U1008*	118U1008*	118U1009*	118U1009*
Fan guard	118U0042	118U0042	118U0043	118U0044	118U0044
Combo filter drier receiver	023Z7012	023Z7012	023Z7012	023Z7013	023Z7013
E box	118U0049	118U0049	118U0049	118U0049	118U0049
Electrical Characteristics					
MCC Fan (A)	0.25	0.25	0.25	0.39	0.39
LRA Compressor (A)	8.2	8.2	10	13.5	14

Designation	OP-MCNC011	OP-MCNC014	OP-MCNC016	OP-MCNC018	OP-MCNC020
Compressor Description	NLY12RAb	NPT14RA	123B3712	123B3514	123B3515
A09	114F1417	114F1420	123B3712	123B3514	123F3515
A10	114F1418	114F1421	118U0068	118U0068	118U0068
A11	114F1416	114F1419	114F1622	114F1625	114F1628
Condenser coil type	BG4/5	BG4/5	BG6	BG6	BG6
Electrical code	G	G	G	G	G
Refrigerant letter code	N	N	N	N	N
Spare Parts					
Compressor single pack	123B3530	123B3703	123B3712	123B3514	123B3515
Compressor Industrial pack	123B3530	123B3703	123B3712	123B3514	123F3515
Condenser	118U0031	118U0031	118U0054	118U0054	118U0054
HP switch	061F6701	061F6701	061F6701	061F6701	061F6701
LP switch	061F7958	061F7958	061F7958	061F7958	061F7958
Fan blade	118U0039	118U0039	118U0040	118U0040	118U0040
Fan motor	118U1009*	118U1009*	118U1010*	118U1010*	118U1010*
Fan guard	118U0044	118U0044	118U0066	118U0066	118U0066
Combo filter drier receiver	023Z7013	023Z7013	023Z7007	023Z7007	023Z7007
E box	118U0049	118U0049	118U0049	118U0049	118U0049
Electrical Characteristics					
MCC Fan (A)	0.39	0.39	0.19	0.19	0.19
LRA Compressor (A)	18.5	21	21	31.5	34.5

MCC - Max Continuous Current
LRA - Locked Rotor Amps

Electrical code
E : 400V-3ph-50Hz Compressor & 230V-1ph-50Hz Fan
G : 230V-1ph-50Hz Compressor & 230V-1ph-50Hz Fan

* EC fans

Designation	OP-MCGC003	OP-MCGC004	OP-MCHC004	OP-MCGC005	OP-MCHC006	OP-MCGC006	OP-MCGC006	OP-MCGC007	OP-MCHC007
Compressor Description	TL3G	TL4G	TL4DL	TL5G	FR6DLX	FR6G	NL6.1MF	FR7.5G	NF7MLX
A00	114X0104	114X0108	114X0301	114X0112	114X2316	114X0200	114X0228	114X0216	114X2424
A01	114X0105	114X0109	114X0302	114X0113	114X2317	114X0201		114X0217	114X2425
A04	114X0107	114X0111	114X0303	114X0115	114X2319	114X0203		114X0219	114X2427
Condenser coil type	BG1	BG1	BG3	BG1	BG3	BG2	BG2	BG2	BG4
Electrical code	G	G	G	G	G	G	G	G	G
Refrigerant	G	G	H	G	H	G	G	G	H
Spare Parts									
Compressor single pack	195B0340	195B0570	195B0166	195B0011	195B0032	195B0023	195B0411	195B0024	195B0443
Condenser	118U0028	118U0028	118U0030	118U0028	118U0030	118U0029	118U0029	118U0029	118U0031
Dual pressure switch	060-539366	060-539366	060-539366	060-539466	060-539366	060-539466	-	060-539466	060-539366
Fan motor	118U0032	118U0032	118U0033	118U0032	118U0033	118U0032	118U0032	118U0032	118U0034
Fan guard	118U0041	118U0041	118U0042	118U0041	118U0043	118U0042	118U0042	118U0042	118U0044
Receiver	118U1024	118U1024	118U1025	118U1024	118U1025	118U1024	-	118U1024	118U1025
Suction valve	118U0485	118U0485	118U0485	118U0485	118U0079	118U0079	-	118U0079	118U0079
Liquid valve	118U0045	118U0045	118U0045	118U0045	118U0045	118U0045	-	118U0045	118U0045
E box	118U0049	118U0049	118U0049	118U0049	118U0049	118U0049	118U0049	118U0049	118U0049
Electrical Characteristics									
LRA Compressor (A)	5.7	5.7	7.5	5.7	10	7.5	9.2	8.1	20
MCC Fan (A)	0.19	0.19	0.25	0.19	0.25	0.19	0.19	0.19	0.39

Designation	OP-MCGC007	OP-MCGC008	OP-MCGC008	OP-MCGC008	OP-MCGC010	OP-MCHC010	OP-MCGC011	OP-MCGC012	OP-MCHC013
Compressor Description	NL7.3MF	NL8.4MF	FR8.5G	NL8.4MF	SC10GX	SC10MLX	FR11GX	SC12GX	SC12MLX
A00	114X0244	114X0204	114X0224	114X0352		114X0403	114X0336	114X0340	114X0406
A01		114X0205	114X0225			114X0404	114X0337	114X0341	114X0407
A04			114X0227		114X0223	114X0405	114X0339	114X0343	114X0408
Condenser coil type	BG2	BG2	BG2	BG2	BG2	BG4	BG3	BG3	BG4
Electrical code	G	G	G	G	G	G	G	G	G
Refrigerant	G	G	G	G	G	H	G	G	H
Spare Parts									
Compressor single pack	195B0370	195B0371	195B0026	195B0371	195B0027	195B0345	195B0028	195B0050	195B0323
Condenser	118U0029	118U0029	118U0029	118U0030	118U0029	118U0031	118U0030	118U0030	118U0031
Dual pressure switch	-	-	060-539466	-	060-539466	060-539366	060-539466	060-539466	060-539366
Fan motor	118U0032	118U0032	118U0032	118U0033	118U0032	118U1009*	118U0033	118U0033	118U1009*
Fan guard	118U0042	118U0042	118U0042	118U0043	118U0042	118U0044	118U0043	118U0043	118U0044
Receiver	-	118U1024	118U1024	-	118U1024	118U1025	118U1025	118U1025	118U1025
Suction valve	-	118U0079	118U0079	-	118U0079	118U0079	118U0079	118U0079	118U0079
Liquid valve	-	118U0045	118U0045	-	118U0045	118U0045	118U0045	118U0045	118U0045
E box	118U0049	118U0049	118U0049	118U0049	118U0049	118U0049	118U0049	118U0049	118U0049
Electrical Characteristics									
LRA Compressor (A)	11.3	11.7	8.2	11.7	11.1	19.5	10	12.6	23.6
MCC Fan (A)	0.19	0.19	0.19	0.19	0.19	0.39	0.25	0.25	0.39

Designation	OP-MCHC015	OP-MCGC015	OP-MCGC018	OP-MCHC018	OP-MCGC021	OP-MCGC021	OP-MCHC021	OP-MCGC026	OP-MCGC034
Compressor Description	SC15MLX	SC15GX	SC18G	SC18MLX	SC21G	SC21MF	GS21MLX	GS26MFX	GS34MFX
A00		114X0448	114X0556		114X0564	114X0568	114X2765		
A01	114X2649	114X0449	114X0557	114X0702	114X0565			114X0773	114X0781
A04	114X2651	114X0451	114X0559	114X0703	114X0567		114X2767		
Condenser coil type	BG6	BG4	BG4/5	BG7	BG4	BG4	BG7	BG7	BG7
Electrical code	G	G	G	G	G	G	G	G	G
Refrigerant	H	G	G	H	G	G	H	G	G
Spare Parts									
Compressor single pack	195B0391	195B0053	195B0548	195B0624	195B0636	195B0682	195B0436	195B0433	195B0435
Condenser	118U0068	118U0031	118U0031	118U0377	118U0031	118U0031	118U0069	118U0069	118U0069
Dual pressure switch	060-539366	060-539466	060-539466	060-539366	060-539466	-	060-539366	-	-
Fan motor	118U0035	118U0034	118U0034	118U1010*	118U0034	118U0034	118U0058	118U0058	118U0058
Fan guard	118U0066	118U0044	118U0044	118U0407	118U0044	118U0044	-	118U0067	118U0067
Receiver	118U1025	118U1025	118U1025	118U1025	118U1025	-	-	118U1027	118U1027
Suction valve	118U0047	118U0079	118U0079	118U0047	118U0047	-	118U0079		
Liquid valve	118U0045	118U0045	118U0045	118U0045	118U0045	-	118U0079		
E box	118U0049	118U0049	118U0049	118U0049	118U0049	118U0049	118U0049	118U0049	118U0049
Electrical Characteristics									
LRA Compressor (A)	23.5	14.8	20.4	23.6	21.8	23.6	24.4	20.2	25.7
MCC Fan (A)	0.48	0.39	0.39	0.75	0.39	0.39	0.75	0.75	0.75

MCC - Max Continuous Current
LRA - Locked Rotor Amps

Electrical code

E : 400V-3ph-50Hz Compressor & 230V-1ph-50Hz Fan

G : 230V-1ph-50Hz Compressor & 230V-1ph-50Hz Fan

* EC fans

Designation	OP-LCQN048	OP-LCQN048	OP-LCQN068	OP-LCQN068	OP-LCQN068	OP-LCQN068
Code Number	114X5758	114X5759	114X5761	114X5784	114X5762	114X5783
Compressor Description	NTZ048-4B	NTZ048-5B	NTZ068-4B	NTZ068-4B	NTZ068-5B	NTZ068-5B
Condenser coil type	A7	A7	D7	D7	D7	D7
Electrical Code	E	G	E	E	G	G
Refrigerant	Q	Q	Q	Q	Q	Q
Oil	175PZ - POE	175PZ - POE	175PZ - POE	175PZ - POE	175PZ - POE	175PZ - POE
Version	A02	A02	A02	A14	A02	A14
Spare Parts						
Compressor single pack	120F0226	120F0228	120F0230	120F0230	120F0232	120F0232
Condenser	118U5217	118U5217	118U5218	118U5218	118U5218	118U5218
Crankcase heater	120Z0459	120Z0459	120Z0459	120Z0459	120Z0459	120Z0459
Contact	-	-	-	118U5262	-	118U5261
Dual pressure switch	060-539766	060-539766	060-539766	060-539766	060-539766	060-539766
Fan assembly	118U0390	118U0390	118U0391	118U0391	118U0391	118U0391
Filter drier type	023Z4562	023Z4562	023Z4562	023Z5061	023Z4562	023Z5061
Receiver	8168179	8168179	8168180	8168180	8168180	8168180
Rotalock valve discharge	7968019	7968019	7968013	7968013	7968013	7968013
Rotalock valve suction	7968014	7968014	7968014	7968014	7968014	7968014
Sight glass	014-0182	014-0182	014-0183	014L0183	014-0183	014L0183
Overload Relay	-	-	-	118U5266	-	118U5265
Discharge gas thermostat*	7750009	7750009	7750009	7750009	7750009	7750009
Fan speed controller*	061H3144	061H3144	061H3144	061H3144	061H3144	061H3144
Electrical Characteristics						
MCC Compressor (A)	4.8	11	8.4	8.4	17	17
LRA compressor (A)	16	37	25	25	53	53
MCC Fan (A)	0.43	0.43	0.82	0.82	0.82	0.82
Fan power (W)	75	75	155	155	155	155

Designation	OP-LCQN096	OP-LGQN096	OP-LGQN096	OP-LCQN108	OP-LCQN108	OP-LGQN108
Code Number	114X5764	114X5766	114X5785	114X5768	114X5786	114X5769
Compressor Description	NTZ096-4B	NTZ096-4B	NTZ096-4B	NTZ108-4B	NTZ108-4B	NTZ108-4B
Condenser coil type	G7	N8	N8	G7	G7	N8
Electrical Code	E	E	E	E	E	E
Refrigerant	Q	Q	Q	Q	Q	Q
Oil	175PZ - POE	175PZ - POE	175PZ - POE	175PZ - POE	175PZ - POE	175PZ - POE
Version	A02	A02	A14	A02	A14	A02
Spare Parts						
Compressor single pack	120F0234	120F0234	120F0234	120F0238	120F0238	120F0238
Condenser	118U5219	118U1004	118U1004	118U5219	118U5219	118U1004
Crankcase heater	120Z0459	120Z0459	120Z0459	120Z0459	120Z0459	120Z0459
Contact	-	-	118U5263	-	118U5263	-
Dual pressure switch	060-539766	060-539766	060-539766	060-539766	060-539766	060-539766
Fan assembly	118U0392	118U0390	118U0390	118U0392	118U0392	118U0390
Filter drier type	023Z4562	023Z4562	023Z5061	023Z4562	023Z5061	023Z4562
Receiver	8168181	8168181	8168181	8168181	8168181	8168181
Rotalock valve discharge	7968014	7968014	7968014	7968014	7968014	7968014
Rotalock valve suction	7968017	7968017	7968017	7968017	7968017	7968017
Sight glass	014-0183	014-0183	014L0183	014-0183	014L0183	014-0183
Overload Relay	-	-	118U5267	-	118U5268	-
Discharge gas thermostat**	7750009	7750009	7750009	7750009	7750009	7750009
Fan speed controller**	061H3144	061H3144	061H3144	061H3144	061H3144	061H3144
Electrical Characteristics						
MCC Compressor (A)	10.1	10.1	10.1	12.1	12.1	12.1
LRA compressor (A)	32	32	32	45	45	45
MCC Fan (A)	1.22	2 X 0.43	2 X 0.43	1.22	1.22	2 X 0.43
Fan power (W)	220	2 X 75	2 X 75	220	220	2 X 75

MCC - Max Continuous Current
LRA - Locked Rotor Amps
FSC - Fan Speed Controller

Electrical code
E : 400V-3ph-50Hz Compressor & 230V-1ph-50Hz Fan
G : 230V-1ph-50Hz Compressor & 230V-1ph-50Hz Fan

** Not Premounted

Designation	OP-LGQN136	OP-LCQN136	OP-LCQN136	OP-LGQN215	OP-LGQN215	OP-LGQN271
Code Number	114X5771	114X5772	114X5787	114X5774	114X5788	114X5776
Compressor Description	NTZ136-4B	NTZ136-4B	NTZ136-4B	NTZ215-4B	NTZ215-4B	NTZ271-4B
Condenser coil type	N8	G7	G7	J7	J7	J7
Electrical Code	E	E	E	E	E	E
Refrigerant	Q	Q	Q	Q	Q	Q
Oil	175PZ - POE	175PZ - POE	175PZ - POE	175PZ - POE	175PZ - POE	175PZ - POE
Version	A02	A02	A14	A02	A14	A02
Spare Parts						
Compressor single pack	120F0236	120F0236	120F0236	120F0240	120F0240	120F0242
Condenser	118U1004	118U5219	118U5219	118U5220	118U5220	118U5220
Crankcase heater	120Z0459	120Z0459	120Z0459	120Z0459	120Z0459	120Z0459
Contact	-	-	118U5263	-	118U5261	-
Dual pressure switch	060-539766	060-539766	060-539766	060-539766	060-539766	060-539766
Fan assembly	118U0390	118U0392	118U0392	118U0393	118U0393	118U0393
Filter drier type	023Z4562	023Z4562	023Z5061	023Z4581	023Z8067	023Z4581
Receiver	8168181	8168181	8168181	8168183	8168183	8168183
Rotalock valve discharge	7968014	7968014	7968014	7968015	7968015	7968015
Rotalock valve suction	7968017	7968017	7968017	7968018	7968018	7968018
Sight glass	014-0183	014-0183	014L0183	014-0184	014L0183	014-0184
Overload Relay	-	-	118U5268	-	118U5269	-
Discharge gas thermostat**	7750009	7750009	7750009	7750009	7750009	7750009
Fan speed controller**	061H3144	061H3144	061H3144	061H3144	061H3144	061H3144
Electrical Characteristics						
MCC Compressor (A)	14.3	14.3	14.3	22.3	22.3	27
LRA compressor (A)	51	51	51	74	74	96
MCC Fan (A)	2 X 0.43	1.22	1.22	2 X 2.23	2 X 2.23	2 X 2.23
Fan power (W)	2 X 75	220	220	2 X 390	2 X 390	2 X 390

MCC - Max Continuous Current

LRA - Locked Rotor Amps

FSC - Fan Speed Controller

Designation	OP-MCRN030	OP-MCRN030	OP-MCRN038	OP-MCRN038	OP-MCRN038	OP-MCRN038	OP-MCRN038	OP-MCRN048	OP-MCRN048	OP-MCRN048
Code Number	114X5721	114X5722	114X5723	114X5789	114X5724	114X5790	114X5726	114X5792	114X5728	
Compressor Description	MTZ018-4	MTZ018-5	MTZ022-5	MTZ022-5	MTZ022-4	MTZ022-4	MTZ028-4	MTZ028-4	MTZ028-5	
Condenser coil type	A7	A7	A7	A7	A7	A7	D7	D7	D7	
Electrical Code	E	G	G	G	E	E	E	E	G	
Refrigerant	R	R	R	R	R	R	R	R	R	
Oil	175PZ - POE	175PZ - POE	175PZ - POE	175PZ - POE	175PZ - POE	175PZ - POE	175PZ - POE	175PZ - POE	175PZ - POE	
Version	A02	A02	A02	A14	A02	A14	A02	A14	A02	
Spare Parts										
Compressor single pack	MTZ18-4VI	MTZ18-5VI	MTZ22-5VI	MTZ22-5VI	MTZ22-4VI	MTZ22-4VI	MTZ28-4VI	MTZ28-4VI	MTZ28-5VI	
Condenser	118U5217	118U5217	118U5217	118U5217	118U5217	118U5217	118U5218	118U5218	118U5218	
Crankcase heater	120Z0459	120Z0459	120Z0459	120Z0459	120Z0459	120Z0459	120Z0459	120Z0459	120Z0459	
Contact	-	-	-	118U5261	-	118U5264	-	118U5264	-	
Dual pressure switch	060-539766	060-539766	060-539766	060-539766	060-539766	060-539766	060-539766	060-539766	060-539766	
Fan assembly	118U0390	118U0390	118U0390	118U0390	118U0390	118U0390	118U0391	118U0391	118U0391	
Filter drier type	023Z4562	023Z4562	023Z4562	023Z5058	023Z4562	023Z5058	023Z4572	023Z5061	023Z4572	
Receiver	8168179	8168179	8168179	8168179	8168179	8168179	8168180	8168180	8168180	
Rotalock valve discharge	7968019	7968019	7968019	7968019	7968019	7968019	7968013	7968013	7968013	
Rotalock valve suction	7968013	7968013	7968013	7968013	7968013	7968013	7968013	7968013	7968013	
Sight glass	014-0182	014-0182	014-0182	014L0182	014-0182	014L0182	014-0183	014L0183	014-0183	
Overload Relay	-	-	-	118U5265	-	118U5270	-	118U5270	-	
Discharge gas thermostat	7750009	7750009	7750009	7750009	7750009	7750009	7750009	7750009	7750009	
Fan speed controller	061H3144	061H3144	061H3144	061H3144	061H3144	061H3144	061H3144	061H3144	061H3144	
Electrical Characteristics										
MCC Compressor (A)	5	10	15	15	6	6	7.5	7.5	20	
LRA compressor (A)	20	40	41	41	20	20	29	29	51	
MCC Fan (A)	0.43	0.43	0.43	0.43	0.43	0.43	0.82	0.82	0.82	
Fan power (W)	75	75	75	75	75	75	155	155	155	

Designation	OP-MCRN048	OP-MCRN054	OP-MCRN054	OP-MCRN060	OP-MCRN060	OP-MCRN060	OP-MCRN060	OP-MCRN068	OP-MCRN086
Code Number	114X5791	114X5729	114X5731	114X5732	114X5794	114X5734	114X5793	114X5735	114X5737
Compressor Description	MTZ028-5	MTZ032-4	MTZ032-5	MTZ036-4	MTZ036-4	MTZ036-5	MTZ036-5	MTZ040-4	MTZ050-4
Condenser coil type	D7	D7	D7	D7	D7	D7	D7	G7	G7
Electrical Code	G	E	G	E	E	G	G	E	E
Refrigerant	R	R	R	R	R	R	R	R	R
Oil	175PZ - POE	175PZ - POE	175PZ - POE	175PZ - POE	175PZ - POE	175PZ - POE	175PZ - POE	175PZ - POE	175PZ - POE
Version	A14	A02	A02	A02	A14	A02	A14	A02	A02
Spare Parts									
Compressor single pack	MTZ28-5VI	MTZ32-4VI	MTZ32-5VI	MTZ36-4VI	MTZ36-4VI	MTZ36-5VI	MTZ36-5VI	MTZ40-4VI	MTZ50-4VI
Condenser	118U5218	118U5218	118U5218	118U5218	118U5218	118U5218	118U5218	118U5219	118U5219
Crankcase heater	120Z0459	120Z0459	120Z0459	120Z0459	120Z0459	120Z0459	120Z0459	120Z0459	120Z0459
Contact	118U5261	-	-	-	118U5262	-	118U5261	-	-
Dual pressure switch	060-539766	060-539766	060-539766	060-539766	060-539766	060-539766	060-539766	060-539766	060-539766
Fan assembly	118U0391	118U0391	118U0391	118U0392	118U0392	118U0392	118U0392	118U0392	118U0392
Filter drier type	023Z5061	023Z4572	023Z4572	023Z4572	023Z8067	023Z4572	023Z8067	023Z4572	023Z4572
Receiver	8168180	8168180	8168180	8168180	8168180	8168180	8168180	8168181	8168181
Rotalock valve discharge	7968013	7968013	7968013	7968013	7968013	7968013	7968013	7968013	7968013
Rotalock valve suction	7968013	7968014	7968014	7968014	7968014	7968014	7968014	7968014	7968017
Sight glass	014L0183	014-0183	014-0183	014-0183	014L0183	014-0183	014L0183	014-0183	014-0183
Overload Relay	118U5271	-	-	-	118U5266	-	118U5269	-	-
Discharge gas thermostat	7750009	7750009	7750009	7750009	7750009	7750009	7750009	7750009	7750009
Fan speed controller	061H3144	061H3144	061H3144	061H3144	061H3144	061H3144	061H3144	061H3144	061H3144
Electrical Characteristics									
MCC Compressor (A)	20	8	20	9	9	22	22	10	12
LRA compressor (A)	51	25	70	38	38	60	60	38	47
MCC Fan (A)	0.82	0.82	0.82	1.22	1.22	1.22	1.22	1.22	1.22
Fan power (W)	155	155	155	220	220	220	220	220	220

MCC - Max Continuous Current

LRA - Locked Rotor Amps

FSC - Fan Speed Controller

Electrical code

E : 400V-3ph-50Hz Compressor & 230V-1ph-50Hz Fan

G : 230V-1ph-50Hz Compressor & 230V-1ph-50Hz Fan

Designation	OP-MCRN086	OP-MCRN096	OP-MCRN096	OP-MCRN108	OP-MCRN108	OP-MGRN108	OP-MCRN121
Code Number	114X5795	114X5739	114X5796	114X5740	114X5797	114X5743	114X5744
Compressor Description	MTZ050-4	MTZ056-4	MTZ056-4	MTZ064-4	MTZ064-4	MTZ064-4	MTZ072-4
Condenser coil type	G7	G7	G7	G7	G7	N8	G7
Electrical Code	E	E	E	E	E	E	E
Refrigerant	R	R	R	R	R	R	R
Oil	175PZ - POE	175PZ - POE	175PZ - POE	175PZ - POE	175PZ - POE	175PZ - POE	175PZ - POE
Version	A14	A02	A14	A02	A14	A02	A02
Spare Parts							
Compressor single pack	MTZ50-4VI	MTZ56-4VI	MTZ56-4VI	MTZ64-4VI	MTZ64-4VI	MTZ64-4VI	MTZ72-4VI
Condenser	118U5219	118U5219	118U5219	118U5219	118U5219	118U1004	118U5219
Crankcase heater	120Z0459	120Z0459	120Z0459	120Z0459	120Z0459	120Z0459	120Z0459
Contacttor	118U5263	-	118U5263	-	118U5263	-	-
Dual pressure switch	060-539766	060-539766	060-539766	060-539766	060-539766	060-539766	060-539766
Fan assembly	118U0392	118U0392	118U0392	118U0392	118U0392	118U0390	118U0392
Filter drier type	023Z8067	023Z4572	023Z8067	023Z4572	023Z8067	023Z4572	023Z4572
Receiver	8168181	8168181	8168181	8168181	8168181	8168181	8168181
Rotalock valve discharge	7968013	7968014	7968014	7968014	7968014	7968014	7968015
Rotalock valve suction	7968017	7968017	7968017	7968017	7968017	7968017	7968018
Sight glass	014L0183	014-0183	014L0183	014-0183	014L0183	014-0183	014-0183
Overload Relay	118U5268	-	118U5268	-	118U5268	-	-
Discharge gas thermostat	7750009	7750009	7750009	7750009	7750009	7750009	7750009
Fan speed controller	061H3144	061H3144	061H3144	061H3144	061H3144	061H3144	061H3144
Electrical Characteristics							
MCC Compressor (A)	12	12.5	12.5	13.5	13.5	13.5	17.5
LRA compressor (A)	47	64	64	64	64	64	80
MCC Fan (A)	1.22	1.22	1.22	1.22	1.22	2 X 0.43	1.22
Fan power (W)	220	220	220	220	220	2 X 75	220

Designation	OP-MGRN121	OP-MCRN136M	OP-MGRN136M	OP-MGRN171	OP-MGRN215	OP-MGRN242	OP-MGRN271
Code Number	114X5746	114X5747	114X5749	114X5750	114X5753	114X5754	114X5757
Compressor Description	MTZ072-4	MTZ080-4	MTZ080-4	MTZ100-4	MTZ125-4	MTZ144-4	MTZ160-4
Condenser coil type	N8	G7	N8	J7	J7	J7	J7
Electrical Code	E	E	E	E	E	E	E
Refrigerant	R	R	R	R	R	R	R
Oil	175PZ - POE	175PZ - POE	175PZ - POE	175PZ - POE	175PZ - POE	175PZ - POE	175PZ - POE
Version	A02	A02	A02	A02	A02	A02	A02
Spare Parts							
Compressor single pack	MTZ72-4VI	MTZ80-4VI	MTZ80-4VI	MTZ100-4VI	MTZ125-4VI	MTZ144-4VI	MTZ160-4VI
Condenser	118U1004	118U5219	118U1004	118U5220	118U5220	118U5220	118U5220
Crankcase heater	120Z0459	120Z0459	120Z0459	120Z0459	120Z0459	120Z0459	120Z0459
Dual pressure switch	060-539766	060-539766	060-539766	060-539766	060-539766	060-539766	060-539766
Fan assembly	118U0390	118U0392	118U0390	118U0393	118U0393	118U0393	118U0393
Filter drier type	023Z4572	023Z4572	023Z4572	023Z4581	023Z4581	023Z4581	023Z4581
Receiver	8168181	8168181	8168181	8168183	8168183	8168183	8168183
Rotalock valve discharge	7968015	7968015	7968015	7968015	7968016	7968016	7968016
Rotalock valve suction	7968018	7968018	7968018	7968018	7968018	7968018	7968018
Sight glass	014-0183	014-0183	014-0183	014-0184	014-0184	014-0184	014-0184
Discharge gas thermostat	7750009	7750009	7750009	7750009	7750009	7750009	7750009
Fan speed controller	061H3144	061H3144	061H3144	061H3144	061H3144	061H3144	061H3144
Electrical Characteristics							
MCC Compressor (A)	17.5	18.5	18.5	22	27	36	36
LRA compressor (A)	80	80	80	90	105	130	130
MCC Fan (A)	2 X 0.43	1.22	2 X 0.43	2 X 2.23	2 X 2.23	2 X 2.23	2 X 2.23
Fan power (W)	2 X 75	220	2 X 75	2 X 390	2 X 390	2 X 390	2 X 390

MCC - Max Continuous Current

LRA - Locked Rotor Amps

FSC - Fan Speed Controller

Electrical code

E : 400V-3ph-50Hz Compressor & 230V-1ph-50Hz Fan

G : 230V-1ph-50Hz Compressor & 230V-1ph-50Hz Fan






Catalogue

Optyma™ Light Commercial - Spare parts & accessories list



Component type	Component code	Component description	Additional informations
Compressor single pack	195B0481	SERVICE-Kit NL8.4CLX	
Compressor single pack	195B0640	Service-KIT SC21CL COMPRESSOR	
Compressor single pack	195B0032	KIT FR6DLX COMPRESSOR	
Compressor single pack	195B0038	KIT FR8,5CLX COMPRESSOR	
Compressor single pack	195B0501	SERVICE-Kit GS 26CLX	
Compressor single pack	195B0021	TL4CL COMPRESSOREN	
Compressor single pack	195B0350	NL7CLX COM	
Compressor single pack	195B0379	SC12CLX.2 LBP	
Compressor single pack	195B0646	SC15CLX LBP	
Compressor single pack	195B0439	GS34CLX COMPRESSOR	
Compressor single pack	195B0066	SC18CL LBP/MBP	
Compressor single pack	123B2106	Spare part, MLY45Lab	
Compressor single pack	123B2110	Spare part, MLY60Lab	
Compressor single pack	123G2114	MLY80LAB SINGLE PACK	
Compressor single pack	123B2120	MLY12Lab SINGLE PACK	
Compressor single pack	123B2123	Spare part, MPT12LA	
Compressor single pack	123B2126	Compresseur MPT14LA pour LSQM014G	
Compressor single pack	195B0371	Kit NL 8.4MF	
Compressor single pack	195B0166	KIT TL4DLX COMPRESSOR	
Compressor single pack	195B0345	Kit SC10MLX	
Compressor single pack	195B0323	SERVICE-Kit SC12MLX	
Compressor single pack	195B0624	Spare part, SC18MLX	
Compressor single pack	195B0027	Spare part, FR10G	
Compressor single pack	195B0682	Spare part, SC21MFX	
Compressor single pack	195B0636	Spare part, SC21G	
Compressor single pack	195B0011	Spare part, TL5G	
Compressor single pack	195B0023	FR6G Universal R134a	
Compressor single pack	195B0411	NL6.1MF Std. R134A	
Compressor single pack	195B0024	FR7,5G COMPRESSOR	
Compressor single pack	195B0026	FR8,5G COMPRESSOR	
Compressor single pack	195B0370	NL7,3 MF COMPRESSOR	
Compressor single pack	195B0028	FR11G COMPRESSOR	
Compressor single pack	195B0050	SC12G Universal R134A	
Compressor single pack	195B0053	Spare part, SC15G	
Compressor single pack	195B0433	Spare part, GS26MFX	
Compressor single pack	195B0435	Spare part, GS34MFX	
Compressor single pack	195B0391	Spare part, SC15MLX	
Compressor single pack	195B0443	Spare part, NF7MLX	
Compressor single pack	195B0436	GS21MLX Compressor	
Compressor single pack	195B0548	Spare part, SC18G 220V 50HZ R 134A	
Compressor single pack	195B0340	Spare part, TL3G	
Compressor single pack	195B0570	Spare part, TL4G	
Compressor single pack	123B8310	NBC30RA; 220-240V 50Hz	
Compressor single pack	123B3505	NLY45RAb/ 220-240V 50Hz	
Compressor single pack	123B3507	NLY60RAb/ 220-240V 50Hz	
Compressor single pack	123B3511	NLY80RAb/ 220-240V 50Hz	
Compressor single pack	123B3513	NLY90RAb/ 220-240V 50Hz	
Compressor single pack	123B3530	NLY12RAb; 220-240V 50Hz	
Compressor single pack	123B3703	NPT14RA/ 220-240V 50Hz	
Compressor single pack	123B3712	NPT16RA; 220-240V 50Hz	
Compressor single pack	123B3514	NX18TBa / 220-240V 50Hz	
Compressor single pack	123B3515	NX21TBa/ 220-240V 50Hz	
Compressor single pack	123B3103	NLY45Lab/ 220-240V 50Hz	
Compressor single pack	123B3107	NLY60Lab/ 220-240V 50Hz	
Compressor single pack	123B3115	NLY80LAB/ 220-240V 50Hz	
Compressor single pack	123B3121	NPY12Lab/ 220-240V 50Hz	
Compressor single pack	123B3124	NPT16LA/ 220-240V 50Hz	
Compressor single pack	123B3128	NX23FBa/ 220-240V 50Hz	
Compressor single pack	123F3167	NS34FB; 220-240V 50Hz	
Condenser	118U0030	CONDENSER COIL BG3	
Condenser	118U0054	CONDENSER COIL BG6	
Condenser	118U0029	CONDENSER COIL BG2	
Condenser	118U0069	CONDENSER COIL BG7 GS	
Condenser	118U0028	CONDENSER COIL BG1	
Condenser	118U0055	CONDENSER COIL BG7	
Condenser	118U0031	CONDENSER COIL BG4/5	

Component type	Component code	Component description	Additional informations
Fan blade	118U0037	FAN BLADES OE200	
Fan blade	118U0038	FAN BLADES OE230	
Fan blade	118U0039	FAN BLADES OE254	
Fan blade	118U0040	FAN BLADES OE300	
Fan motor	118U1010	Spare part, Fan motor EC 25-25	
Fan motor	118U0032	FAN MOTOR 5 WATT	
Fan motor	118U0033	FAN MOTOR 11 WATT	
Fan motor	118U0058	FAN MOTOR 25 WATT	
Fan motor	118U0034	FAN MOTOR 16 WATT	
Fan motor	118U1009	Spare part, Fan motor EC 20-25	
Fan motor	118U0035	FAN MOTOR 18 WATT	
Fan motor	118U1008	Spare part, Fan motor EC 12-10	
Fan guard	118U0407	FAN COWL BG7	
Fan guard	118U0067	FAN COWL BG7	
Fan guard	118U0042	FAN COWL BG2	
Fan guard	118U0043	FAN COWL BG3	
Fan guard	118U0044	FAN COWL BG4/5	
Fan guard	118U0066	FAN COWL BG6	
Receiver	118U1024	Spare part, Receiver 0.8L	Phase out - 118U0517
Receiver	118U1025	Spare part, Receiver 1.1L	Phase out - 118U0523
Receiver	118U1026	Spare part, Receiver 1.6L	Phase out - 118U1025
Receiver	118U1027	Spare part, Receiver 2.4 L	
Receiver	023Z7012	Receiver filter drier DMC 0432S/6mm I/16	
Receiver	023Z7013	Receiver filter drier DMC 0732S I/16	
Receiver	023Z7007	Receiver filter drier DMC 2033S I/10	
Suction valve	118U0047	S-VALVE 10/10	
Suction valve	118U0485	SAUGVENTIL 6/6MM + KP-ANSCHLUSS (Stahl)	
Liquid valve	118U0045	L-VALVE 6/6	
Liquid valve	118U0079	Spare part, Valve 5/8"	
Pressure switch - HP	061F6701	ACB pressure switch 2UB1507W I/100	
Pressure switch - LP	061F7958	ACB pressure switch ACB-2UA1169W	
Pressure switch - LP	061F7959	ACB Cartridge Switch 2UA1170W I/100	

Component type	Component code	Component description	Additional informations
Compressor single pack	MTZ18-4VI	MTZ18-4VI, COMP OSG-EQUAL MULTIREF	
Compressor single pack	MTZ18-5VI	MTZ18-5VI, COMPRESSOR VERSION EGALISATION	
Compressor single pack	MTZ22-5VI	MTZ22-5VI, COMPRESSOR VERSION EGALISATION	
Compressor single pack	MTZ22-4VI	MTZ22-4VI, COMP OSG-EQUAL MULTIREF	
Compressor single pack	MTZ28-4VI	MTZ28-4VI, COMP OSG-EQUAL MULTIREF	
Compressor single pack	MTZ28-5VI	MTZ28-5VI, COMP OSG-EQUAL MULTIREF	
Compressor single pack	MTZ32-4VI	MTZ32-4VI, COMP OSG-EQUAL MULTIREF	
Compressor single pack	MTZ32-5VI	MTZ32-5VI, COMP OSG-EQUAL MULTIREF	
Compressor single pack	MTZ36-4VI	Compressor MTZ36-5VI	
Compressor single pack	MTZ36-5VI	MTZ36-5VI, COMP OSG-EQUAL MULTIREF	
Compressor single pack	MTZ40-4VI	MTZ40-4VI, COMP OSG-EQUAL MULTIREF	
Compressor single pack	MTZ50-4VI	MTZ50-4VI, COMP OSG-EQUAL MULTIREF	
Compressor single pack	MTZ56-4VI	MTZ56-4VI, COMP OSG-EQUAL MULTIREF	
Compressor single pack	MTZ64-4VI	MTZ64-4VI, COMP OSG-EQUAL MULTIREF	
Compressor single pack	MTZ72-4VI	MTZ72-4VI, COMP OSG-EQUAL MULTIREF	
Compressor single pack	MTZ80-4VI	MTZ80-4VI, COMP OSG-EQUAL MULTIREF	
Compressor single pack	MTZ100-4VI	MTZ100-4VI, COMP OSG-EQUAL MULTIREF	
Compressor single pack	MTZ125-4VI	MTZ125-4VI, COMP OSG-EQUAL MULTIREF	
Compressor single pack	MTZ144-4VI	MTZ144-4VI, COMP OSG-EQUAL MULTIREF	
Compressor single pack	MTZ160-4VI	MTZ160-4VI, COMP OSG-EQUAL MULTIREF	
Compressor single pack	120F0226	NTZ048-4LR1-SINGLE	
Compressor single pack	120F0228	NTZ048-5LR1-SINGLE	
Compressor single pack	120F0230	NTZ068-4LR1-SINGLE	
Compressor single pack	120F0232	NTZ068-5LR1-SINGLE	
Compressor single pack	120F0234	NTZ096-4LR1-SINGLE	
Compressor single pack	120F0238	NTZ108-4LR1-SINGLE	
Compressor single pack	120F0236	NTZ136-4LR1- RECIP	
Compressor single pack	120F0240	NTZ215-4LR1-SINGLE RECIP COMP	
Compressor single pack	120F0242	NTZ271-4LR1-SINGLE RECIP COMP	
Condenser	118U3492	Spare part, B1, H1, A7 MCHX	
Condenser	118U3493	Spare part, B2,H2, D7 MCHX	
Condenser	118U3494	Spare part, B3,H3, G7 MCHX	
Condenser	118U1004	CONDENSER COIL MCHX N8	
Condenser	118U3717	Spare part, H4, J7 MCHX	
Crankcase heater	120Z0459	PTC Crankcase heater	
Dual pressure switch	060-127466	KP17B Switch	
Dual pressure switch	060-539766	KP17WB Switch	
Fan assembly	118U0390	Fan assembly Ø350- 6 Pole, 230/1/50-60	
Fan assembly	118U0391	Fan assembly Ø450-6 Pole, 230/1/50-60	
Fan assembly	118U0392	Fan assembly Ø500-6 Pole, 230/1/50-60	
Fan assembly	118U0393	Fan assembly Ø560-6 Pole, 230/1/50-60	
Discharge gas thermostat	7750009	DISCHARGE THERMOSTAT KIT	
Fan speed controller	061H3144	XGE-2C	
Filter drier (Multipack)	023Z4562	DML053S	
Filter drier (Multipack)	023Z4572	DML084S	
Filter drier (Multipack)	023Z4581	DML165S	
Oil	120Z0638	LUBRICANT 175PZ-1L CAN	
Oil	120Z0639	LUBRICANT 175PZ-2.5L CAN	
Receiver	8168179	LIQUID RECEIVER 3L R032	
Receiver	8168180	LIQUID RECEIVER 6L R061	
Receiver	8168181	LIQUID RECEIVER 8L R076	
Receiver	8168183	LIQUID RECEIVER 14L R141	
Rotalock valve discharge	7968019	ROTALOCK valve 1" - 3/8"	
Rotalock valve discharge	7968013	ROTALOCK VALVE 1" - 1/2"	
Rotalock valve discharge	7968014	ROTALOCK VALVE 1 1/4" - 5/8"	
Rotalock valve suction	7968017	ROTALOCK VALVE 1 3/4" - 7/8"	
Rotalock valve suction	7968018	ROTALOCK valve 1+3/4" - 1+1/8"	
Sight glass (Multipack)	014-0182	SGN10s	
Sight glass (Multipack)	014-0183	SGN12s	
Sight glass (Multipack)	014-0184	SGN16s	





Chassis A (Single Fan)




S.No	Application	Description	Units	Compressor	H	W	D	X	Y
1	MBP	OP-MCRN030MTA02E	114X5721	MTZ018	545	630	650	400	595
2	MBP	OP-MCRN030MTA02G	114X5722						
3	MBP	OP-MCRN038MTA02G	114X5723	MTZ022					
4	MBP	OP-MCRN038MTA02E	114X5724						
5	LBP	OP-LCQN048NTA02E	114X5758	NTZ048					
6	LBP	OP-LCQN048NTA02G	114X5759						

Chassis B (Two Fan)




S.No	Application	Description	Units	Compressor	H	W	D	X	Y
1	MBP	OP-MGRN108MTA02E	114X5743	MTZ064	693.5	1500	870	580	1465
2	MBP	OP-MGRN121MTA02E	114X5746	MTZ072					
3	MBP	OP-MGRN136MTA02E	114X5749	MTZ080					
4	LBP	OP-LGQN096NTA02E	114X5766	NTZ096					
5	LBP	OP-LGQN096NTA14E	114X5785	NTZ096					
6	LBP	OP-LGQN108NTA02E	114X5769	NTZ108					
7	LBP	OP-LGQN136NTA02E	114X5771	NTZ136					

Chassis C (Single Fan)




S.No	Application	Description	Units	Compressor	H	W	D	X	Y
1	MBP	OP-MCRN048MTA02E	114X5726	MTZ028	705	900	900	600	865
2	MBP	OP-MCRN048MTA14E	114X5792						
3	MBP	OP-MCRN048MTA02G	114X5728						
4	MBP	OP-MCRN048MTA14G	114X5791						
5	MBP	OP-MCRN054MTA02E	114X5729	MTZ032					
6	MBP	OP-MCRN054MTA02G	114X5731						
7	MBP	OP-MCRN060MTA02E	114X5732	MTZ036					
8	MBP	OP-MCRN060MTA14E	114X5794						
9	MBP	OP-MCRN060MTA02G	114X5734						
10	MBP	OP-MCRN060MTA14G	114X5793						
11	LBP	OP-LCQN068NTA02E	114X5761	NTZ068					
12	LBP	OP-LCQN068NTA14E	114X5784						
13	LBP	OP-LCQN068NTA02G	114X5762						
14	LBP	OP-LCQN068NTA14G	114X5783						

Chassis D (Single Fan)




S.No	Application	Description	Units	Compressor	H	W	D	X	Y
1	MBP	OP-MCRN068MTA02E 114X5735		MTZ040	836.5	1200	800	500	1165
2	MBP	OP-MCRN086MTA02E 114X5737		MTZ050					
3	MBP	OP-MCRN086MTA14E 114X5795		MTZ050					
4	MBP	OP-MCRN096MTA02E 114X5739		MTZ056					
5	MBP	OP-MCRN096MTA14E 114X5796		MTZ056					
6	MBP	OP-MCRN108MTA02E 114X5740		MTZ064					
7	MBP	OP-MCRN108MTA14E 114X5797		MTZ064					
8	MBP	OP-MCRN121MTA02E 114X5744		MTZ072					
9	MBP	OP-MCRN136MTA02E 114X5747		MTZ080					
10	LBP	OP-LCQN096NTA02E 114X5764		NTZ096					
11	LBP	OP-LCQN108NTA02E 114X5768		NTZ108					
12	LBP	OP-LCQN108NTA14E 114X5786		NTZ108					
13	LBP	OP-LCQN136NTA02E 114X5772		NTZ136					
14	LBP	OP-LCQN136NTA14E 114X5787		NTZ136					

Chassis E (Two Fan)




S.No	Application	Description	Units	Compressor	H	W	D	X	Y
1	MBP	OP-MGRN171MTA02E	114X5750	MTZ100	836.5	1500	870	580	1465
2	MBP	OP-MGRN215MTA02E	114X5753	MTZ125					
3	MBP	OP-MGRN242MTA02E	114X5754	MTZ144					
4	MBP	OP-MGRN271MTA02E	114X5757	MTZ160					
5	LBP	OP-LGQN215NTA02E	114X5774	NTZ215					
6	LBP	OP-LGQN215NTA14E	114X5788	NTZ215					
7	LBP	OP-LGQN271NTA02E	114X5776	NTZ271					

Chassis F (Single Fan)




S.No	Application	Description	Units	Compressor	H	W	D	X	Y
1	MBP	OP-MCRN038MTA14G	114X5789		545	900	900	600	865
2	MBP	OP-MCRN038MTA14E	114X5790						

Compressor range: NS34




Compressor range: NL and NP and NX




- 1A - Main winding
- 1B - Start winding
- 1C - Start relay
- 1D - Winding protector
- 1E - Start capacitor
- 1F - Bleeder resistance
- 1G - Run capacitor
- 1H - Thermostat
- 1J - Fan
- 1K - Pressure control (version A11)

Compressor range: NBC30




- 1A - Main winding
- 1B - Start winding
- 1C - Start relay
- 1D - Winding protector
- 1E - Start capacitor
- 1F - Bleeder resistance
- 1G - Run capacitor
- 1H - Thermostat
- 1J - Fan
- 1K - Pressure control (version A11)




For compressor:

- NL8,4CLX
- NL8,4MF
- TL4DL
- SX10MLX
- SC12MLX




For compressor:

- SC18MLX
- SC21CL
- SC18CL



For compressor:

- TL4DL
- SC10MLX
- SC12MLX
- NL8,4CLX




For compressor:

- SC18MLX
- SC21CL

- 1A - Main winding
- 1B - Start winding
- 1C - Start relay
- 1D - Winding protector
- 1E - Start capacitor
- 1F - Bleeder resistance
- 1G - Run capacitor
- 1H - Thermostat
- 1J - Fan
- 1K - Pressure control (version A11)

Single Phase models



BK: BLACK
BN: BROWN
RD: RED
One or two fans for Danfoss condensing units

BU: BLUE
WH: WHITE
GY: GREY

* OPTION
OVERLOAD PROTECTOR IF AVAILABLE

50 Hz			
COMPRESSOR MODEL	DISPLACEMENT cm ³	A μF/450VAC	B μF/450VAC
NTZ048	048	30	100
NTZ068	068	30	100

MT-MTZ18	030	30	100
MT-MTZ22	038	30	100
MT-MTZ28	048	30	100
MT-MTZ32	054	35	135
MT-MTZ36	061	35	135


60 Hz			
NTZ048	048	25	100
NTZ068	068	50	135

MT-MTZ18	030	25	100
MT-MTZ22	038	45	100
MT-MTZ28	048	50	135
MT-MTZ32	054	45	100
MT-MTZ36	061	45	100

C (Capacitor Fan)		
FAN DIAMETER	ebmpapst	
	μF/450VAC	
	50 Hz	60 Hz
350	2	2
C1/C2 (Capacitor Fan)		
	3	3
450	3	3
500	5	5
560	10	10

LEGEND	
A	RUN CAPACITOR COMPRESSOR
B	START CAPACITOR COMPRESSOR
CS	CONTROL SWITCH ON/OFF
C/C1/C2	CAPACITOR FAN
F1	FUSE CONTROL CIRCUIT
FAN 1-2	CONDENSER FANS
HP/LP	DUAL PRESSURE SWITCH
KM1	COMPRESSOR CONTACTOR
KM2	FAN CONTACTOR
KM3	FAN CONTACTOR
Q1	MAIN SWITCH + CIRCUIT BREAKER
R1	CRANKCASE HEATER
RA	BLEEDER RESISTOR
RB	BLEEDER RESISTOR
TH	THERMOSTAT

Three Phase models



BK: BLACK
BN: BROWN
RD: RED
YE: YELLOW
One or two fans for Danfoss condensing units


BU: BLUE
WH: WHITE
GY: GREY
GN: GREEN

50/60 Hz	C1/C2: μF/450VAC
FAN Ømm	350 450 500 560
ebmpapst	2 3 5 10

LEGEND	
A	RUN CAPACITOR COMPRESSOR
B	START CAPACITOR COMPRESSOR
CS	CONTROL SWITCH ON/OFF
C/C1/C2	CAPACITOR FAN
F1	FUSE CONTROL CIRCUIT
FAN 1-2	CONDENSER FANS
HP/LP	DUAL PRESSURE SWITCH
KM1	COMPRESSOR CONTACTOR
KM2	FAN CONTACTOR
KM3	FAN CONTACTOR
Q1	MAIN SWITCH + CIRCUIT BREAKER
R1	CRANKCASE HEATER
RA	BLEEDER RESISTOR
RB	BLEEDER RESISTOR
TH	THERMOSTAT


* OPTION
OVERLOAD PROTECTOR IF AVAILABLE

Single phase models



230/1/50

Three phase models



400/3/50

Danfoss Cooling

is a worldwide manufacturer of compressors and condensing units for refrigeration and HVAC applications. With a wide range of high quality and innovative products we help your company to find the best possible energy efficient solution that respects the environment and reduces total life cycle costs.

We have 40 years of experience within the development of hermetic compressors which has brought us amongst the global leaders in our business, and positioned us as distinct variable speed technology specialists. Today we operate from engineering and manufacturing facilities spanning across three continents.



Danfoss Scrolls



Danfoss Inverter Scrolls



Danfoss Turbocor Compressors



Danfoss Optyma™ Condensing Units



Danfoss Light Commercial Refrigeration Compressors



Danfoss Maneurop Reciprocating Compressors

Our products can be found in a variety of applications such as rooftops, chillers, residential air conditioners, heatpumps, coldrooms, supermarkets, milk tank cooling and industrial cooling processes.

Danfoss A/S
Climate Solutions • danfoss.com • +45 7488 2222

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues descriptions, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the product. All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.