

POWER ELECTRONICS FOR SOLAR/ESS



Solar and Energy Storage Systems



Solar Energy

Our portfolio includes a wide range of products for efficient solar inverters in all power ranges: residential, industrial and utility scale. The products are scalable, from individual modules, including dedicated drivers, to high power SKiiP 4/7 IPMs and ready-to-use power electronic stacks.

We also offer a large portfolio of 3-level power modules, IPMs and power electronic stacks, which can reduce system costs significantly as well as optimize annual energy production, especially for increased DC voltages up to $1500V_{DC}$.

STRING INVERTERS

5kW - 250kW

- Residential
- Commercial/industrial
- Utility

$1500V_{DC}$ capability

High efficiency

High reliability to reduce downtime

Products

SEMITOP E

MiniSKiiP

SEMiX 5

Drivers

CENTRAL INVERTERS

250kW - 6MW



- Commercial/industrial
- Utility

$1500V_{DC}$ capability

High efficiency

High reliability to reduce downtime

Products

SEMiX 5

SEMiX 3 Press-Fit

SEMITRANS Classic

SEMITRANS 10

SEMITRANS 20

SKiiP 4/7 IPM

Drivers

Power Electronic Stacks



Energy Storage

With decentralized renewable energy sources in our power grid, the demand for energy storage systems to stabilize fluctuations is quickly growing. Our portfolio includes a wide range of products for energy storage systems: From small and medium power modules for residential/industrial systems to high power components for utility scale systems, these products deliver maximum reliability. A variety of semiconductor packaging technologies are available to meet ESS industry lifetime requirements. From individual modules, including dedicated drivers, to high power SKiiP 4/7 IPMs and ready-to-use power electronic stacks – we have the solution.

LOW/MEDIUM POWER

8kW - 75kW

- Residential
- Commercial/industrial
- Solar plus storage

Compact designs and high power density

High efficiency

High reliability to reduce downtime

Products

SEMITOP E

MiniSKiiP

SEMiX 5

SEMiX 3 Press-Fit

SEMITRANS Classic

Drivers

MEDIUM/HIGH POWER

50kW - 6MW



- Commercial/industrial
- Utility
- Solar plus storage

1500V_{DC} capability

High efficiency

High reliability to reduce downtime

Products

SEMITOP E

SEMiX 5

SEMiX 3 Press-Fit

SEMITRANS Classic

SEMITRANS 10

SEMITRANS 20

SKiiP 4/7 IPM

Drivers

Power Electronics Stacks





Silicon
Carbide

2kV SiC: It's Your Choice

SEMITRANS 20 for Extreme Power Density

Thanks to new 2kV SiC technology, the SEMITRANS 20 boosts the power density of power electronics compared to 3-level silicon solutions. The SEMITRANS 20 has an optimized construction for scaling to even higher power levels through paralleling, while the traction-derived packaging technologies offer unparalleled reliability. A high blocking voltage capability offers safety for 2-level converters operating at 1500V, simplifying converter design.

Key Features


- Industry standard package design
- 2kV blocking voltage enables 1500V_{DC} with 2-level topology
- Scalable through paralleling
- Low thermal resistance package design
- Low inductance for fast switching
- 20% lower losses compared to 3-level silicon design, reducing cooling effort

SKiiP 4 SiC IPM for Reduced Time-to-Profit


The new SKiiP 4 SiC with 2kV SiC devices enable safe operation of 1500V applications thanks to an integrated driver, current sensing, and protection functions. The SKiiP includes an air- or water-cooled heatsink and is 100% tested. The digital driver enables the use of multiple SiC MOSFET suppliers, and the current rating is adjustable based on the quantity of chips in parallel.

Key Features

- 2kV blocking voltage enables 1500V_{DC} with 2-level topology
- Includes driver, current sensor, and liquid- or air-cooled heatsink
- Driver includes Semikron Danfoss ASIC and multiple protection features
- 100% burn-in testing



SEMISTRANS®20
500kW up to 2MW



SKiiP®4 SiC
500kW up to 2MW



PRODUCT HIGHLIGHT

Comprehensive 3-Level and Booster Module Family


The SEMITOP E packages provide supply chain security with a standard industrial design. Press-fit pins offer reduced manufacturing time and a low inductance design. Ideal for fast switching chips, such as SiC, the SEMITOP has a wide portfolio of topologies, ready for your string inverter design.

Key Features

- Low stray inductance case
- Solder-free, press-fit assembly
- Optimized thermal performance
- Flexible architecture
- Available with silicon, full SiC, or hybrid SiC



SEMITOP® E1
Up to 50kW




SEMITOP® E2
Up to 200kW

Increased Performance in 3-Level Topologies

Whenever power quality and efficiency are driving factors in power electronics applications, 3-level topologies are the key. This is especially true for renewable energy applications where the combination with the latest Generation 7 IGBTs sets new benchmarks.

For ANPC topologies, our new SEMITRANS 20 power module combines the low stray inductance, high power density and Generation 7 IGBTs to set a new benchmark. This package design, based on standard half-bridge topology, allows a simple ANPC layout with low inductance DC-link connections.




Three SEMITRANS 20 modules make ANPC phase-leg for up to 2MW



Thanks to the chip shrinkage from Generation 4 to Generation 7 IGBTs, there is more space for diodes. Therefore, the SEMITRANS 10 MLI offers an increased clamping diode current rating. This enables energy storage converters to work at full power while charging and discharging batteries.

Key Features


- Reduced magnetics cost thanks to 3-level topology
- Up to 2MW with liquid cooling
- Based on latest Generation 7 IGBTs
- Reduced cable diameters or cable losses with up to 1500V_{DC} operation
- Reduced cooling requirements thanks to low losses



SEMITRANS® 10 MLI
Split NPC phase-leg among two SEMITRANS 10 MLI modules for up to 1.5MW




SEMITRANS®20
500kW up to 2MW



SEMITRANS®10
500kW up to 1.5MW

Product Portfolio

Power Modules for Solar and Energy Storage Systems



SEMIX® 5

50kW up to 250kW

Extended Portfolio with Superior Thermal and Dynamic Performance

Industry standard baseplate module

650V / 1200V / 1700V IGBT: 150A to 400A

Sixpack, NPC and TNPC topologies

Optimized module layout for maximum heat transfer

Enhanced thermal and electrical diode performance



SEMIX® 3 Press-Fit

100kW up to 400kW

Exceeding the Standard for Superior Performance

Industry standard press-fit design with 17mm high housing


650V / 1200V / 1700V IGBT: 225A to 900A

1200V Hybrid SiC: 600A

Half-bridge and split NPC topologies

Direct driver assembly

Available with integrated shunt resistor



SEMITOP® E

8kW up to 200kW

Exceeding the Standard for Superior Performance

Baseplate-less industry standard power module in two housing sizes

Press-fit pins for solder-less connection to PCB

650V / 1200V IGBT: 10A to 200A

1200V SiC: 30A to 250A

Sixpack, H-bridge, half-bridge, NPC, TNPC, and ANPC topologies

Optimized mounting concept provides lowest thermal resistance in class

Soft and fast switching 650V IGBT S5 and H5



SEMISTRANS® Classic

25kW up to 400kW

The Proven Power Electronics Package

Robust industry standard package for multiple sourcing in six housing sizes

600V / 650V / 1200V / 1700V IGBT: 50A to 800A

1200V SiC: 125 to 500A

1700V SiC: 260A to 400A


Half-bridge, single switch and brake chopper topology

Multiple IGBT sources including Generation 7 IGBTs

Extended 62mm portfolio

1200V IGBT: 800A

1700V IGBT: 500A



SEMISTRANS® 10

500kW up to 1.5MW

Robust High Power Module

Established high power module package


1200V IGBT: 700A to 1400A

1700V IGBT: 1000A and 1800A

2300V IGBT: 1800A

Half-bridge, common emitter, NPC and split NPC topologies

Full second source thanks to alternative 1700V chip source



SEMISTRANS® 20

500kW up to 2MW

The New Standard in High Power

The latest industry standard power module for high power applications

1200V / 1700V IGBT: 900A to 1400A

2000V SiC: 1700A/1mOhm

Half-bridge topology

Low stray inductance, high power density package

Increased reliability thanks to the latest packaging technology





Intelligent Power Modules (IPMs) for **Maximum Reliability** for Solar and Energy Storage Converters

The SKiiP IPM product line set the benchmark for high performance and robust inverter designs. Both SKiiP 4 and SKiiP 7 feature high power densities combined with flexible cooling options such as air or water cooling, as well as with customized heatsinks. Reliable driver technology, integrated current sensors and comprehensive protection functions complete the IPM design.

SKiiP 7 has become increasingly popular through the industrial applications. With its sixpack or half-bridge topologies, it covers a current range of 500A to 2400A.

The SKiiP 4, available in half-bridge topology, has been optimized for ultra-high power cycling requirements and covers a higher power range up to 3600A.

To ensure maximum reliability and service life, the power circuitry is 100% solder-free. Sinter die attach technology replaces the solder layer, the common cause of module lifetime limitations, thus improving power and thermal cycling capability.

High Performance Cooling (HPC) technology has been introduced, to provide 25% more output power capability compared to standard water cooling. A double-sided mounting HPC is also available, enabling ever higher power density.

The integrated gate driver in the SKiiP 4 has set new standards in terms of reliability and enhanced functionality through its CAN interface. The digital driver guarantees safe isolation between the primary and secondary side for both switching signals and parameter measurements. The CAN interface allows setting the SKiiP 4 configuration parameter and reading application parameter.

Key Features


Half-bridges and sixpacks

1200V / 1700V IGBT: 500A to 3600A

2000V SiC: 1200A to 2400A


Flexible cooling options: air, water or customized cooling options

Parallel operation for even higher output power possible



SKiiP®4

Up to 2MW
with SiC MOSFETs



SKiiP®7

150kW up to 2.4MW



Power Electronic **Stack Platforms** for **Fully Qualified** Inverter Assemblies Tailored to Your **Specific Needs**

Standard Stacks

Our Power Electronic Stacks enable our customers to succeed in dynamic markets and meet any global challenge. We deliver Rectifier-, IGBT- and SiC-based stacks for AC voltages from 380V to 1000V. Our standard stacks cover an output current range of 70A to 4000A and building blocks based on three level topologies that are ready to use in 1500V_{DC} environment.

Water-Cooled IGBT Stacks

SEMISTACK RE
SEMIKUBE MLI

Air-Cooled IGBT Stacks

SEMIKUBE 1500V
SEMIKUBE SlimLine
SEMIKUBE MLI (1500V capable)

Customized Stacks

In addition to standard stacks, Semikron Danfoss has vast experience in developing customer-specific solutions. Engineers are available in our stack centers around the globe to offer specific solutions by adapting existing platforms or designing customized converters.


Four Key Factors to Your Success

Shortest time to market

Cost savings in R&D, production and qualification


Global Semikron Danfoss stack production footprint

Highly experienced engineering team




SEMISTACK® MLI

1.5MW 3-Level IGBT Topology



SEMIKUBE®

Air-cooled IGBT Power Stack



Product Portfolio

IGBT Driver

The unique product portfolio enables access to all established industries with a one-stop solution that combines state-of-the-art power modules and driver electronics.

Our IGBT drivers are available as two-channel driver cores suitable for any standard semiconductor power module or as Plug-and-Play solutions, which perfectly fit the SEMiX 3 Press-Fit, SEMITRANS 10 and compatible modules.

Cost Efficient

Achieve outstanding system compactness and create space- and cost-effective inverter designs with our drivers, utilizing highly integrated ASIC technology. Isolated DC-link voltage and temperature sensor signals at the driver's interface along with over-voltage and over-temperature lockout also help to reduce system costs significantly.

Time Efficient

More than 25 years of experience in developing innovative IGBT driver electronics enables Semikron Danfoss to have a short-term solution for almost every challenge related to driver electronics. Our Plug-and-Play drivers connect directly to most common standard IGBT modules. The IGBT driver cores fit with the adapter boards or application sample PCBs. For the latter, Semikron Danfoss shares the entire manufacturing data to decrease development time, speeding up the time-to-market.

Reliable

Our SKYPER are well-known, highly robust and reliable IGBT driver solutions under demanding environmental conditions. Over many years of field operation experience the proprietary IGBT driver technology has been relentlessly developed further. This technology sets new standards for the essential features of safe gate control, reliable gate protection and reinforced insulation.

Compact Design

Our SKIC ASIC technology enables very compact system design with minimal peripheral components. With highly integrated signal processing and multi-channel failure management, our ASICs offer robust gate control



Key Factors

Reinforced insulation for signal and power transmission

Two-channel driver

Up to 1700V transients


Up to 1500V continuous DC bus voltage

8Apk to 35Apk per channel

1W to 4.2W peak per channel

Suitable for multi-level topologies and Generation 7 IGBT


SKYPER 42 LJ PV



Driver Cores

Two-channel driver cores for PCB integration with Semikron Danfoss ASIC technology and integrated safety functions


SKYPER Prime



Plug-and-Play Driver

Two-channel drivers for direct module mounting with electrical or optical interface

SKYPER Prime O



Plug-and-Play Driver

Two-channel drivers for direct module mounting with optical interface



Thermal Interface Materials

Stay Cool: Heat Dissipation is Our Job

Semikron Danfoss was the first power module manufacturer on the market to offer power modules with pre-applied thermal interface material (TIM). We now have over two decades of experience and more than 30 million pre-printed modules in the field.

We design print patterns for each module type for the best TIM distribution and thickness when the module is mounted to a heatsink. These patterns are printed on the modules in a clean environment on an automated silkscreen and stencil printing line. Statistical process control (SPC) is used to guarantee consistency. Special packaging is implemented to ensure that the TIM arrives at your production line in pristine condition.

Semikron Danfoss offers either thermal grease or phase change material depending on customer requirements (e.g. performance increase, reduced handling effort) and module type (with or without baseplate). The reliable assembly of baseplate-less modules is aided by a low-viscosity material such as thermal paste. Our High Performance Thermal Paste (HPTP) achieves this and, with optimized filler content, provides best in class thermal performance.

Alternatively, for ease-of-handling during assembly, most power modules are also available with pre-applied phase change material (PCM). Phase change materials have a solid consistency at room temperature. With the application of heat during first operation, the PCM flows to fill gaps and provide a thermal interface. With HP-PCM, the new Semikron Danfoss-exclusive High

Performance Phase Change Material, we combine the benefits of a phase change material with the performance of the best available paste.



Key Features

- Module-specific patterns for optimized TIM distribution
- Simplified logistics and reduced production costs
- Improved assembly robustness
- Increased lifetime and reliability


Portfolio

HPTP: High Performance Thermal Paste

HP-PCM: High Performance Phase Change Material



Baseplate-less module with pre-applied thermal paste



Baseplate module with pre-applied phase change material

THE ULTIMATE PARTNER IN POWER ELECTRONICS

Semikron Danfoss is a global technology leader in power electronics. Our product offerings include semiconductor devices, power modules, stacks and systems. In a world that is going electric, Semikron Danfoss technologies are more relevant than ever. With our innovative solutions for automotive, industrial and renewable applications we help the world utilize energy more efficiently and sustainably and thus to significantly reduce overall CO₂ emissions – facing one of the biggest challenges today. We take care of our employees and create value for our customers by investing significantly in innovation, technology, capacity, and service to deliver best-in-industry performance and for a sustainable future.



05/2024



Semikron Danfoss GmbH

Husumer Strasse 251
24941 Flensburg, Germany

Semikron Danfoss International GmbH

Sigmundstrasse 200
90431 Nuremberg, Germany

www.semikron-danfoss.com

Note: All information is based on our present knowledge and is to be used for information purposes only. The specifications of our products may not be considered as an assurance of component characteristics.

